

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P233963

Luminaire Tested: **CTN-10-3-D-E1-T1-7030**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P233963  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1707-171-24)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: CTN-10-3-D-E1-T1-7030  
Description: CELESTEON HIGH MAST LUMINAIRE  
(10) 70 CRI, 3000K LEDS AND TYPE I OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 32946 lumens  
Efficiency: N/A  
Efficacy: 155.4 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type I - Short - Semi-Cutoff  
BUG Rating: B5 - U0 - G5

Input Watts (W): 212  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P233963

CATALOG NUMBER: CTN-10-3-D-E1-T1-7030

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 --- 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 5.9 fc  
 Type I - Short - Semi-Cutoff

REPORT NUMBER: P233963

CATALOG NUMBER: CTN-10-3-D-E1-T1-7030

## Luminous Intensity Polar Plot



REPORT NUMBER: P233963

CATALOG NUMBER: CTN-10-3-D-E1-T1-7030


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 16473.0  | 0.0    | 16473.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 16473.0  | 0.0    | 16473.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 32946.0  | 0.0    | 32946.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 504.3   | 1.5       |
| 10°-20°   | 1500.3  | 4.6       |
| 20°-30°   | 2482.5  | 7.5       |
| 30°-40°   | 3637.3  | 11.0      |
| 40°-50°   | 5351.2  | 16.2      |
| 50°-60°   | 6939.2  | 21.1      |
| 60°-70°   | 7374.9  | 22.4      |
| 70°-80°   | 4552.5  | 13.8      |
| 80°-90°   | 603.9   | 1.8       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 32946.0 | 100.0     |
| 0°-180°   | 32946.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P233963


CATALOG NUMBER: CTN-10-3-D-E1-T1-7030

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 2243.5 | 6.8       |                         |      |         |
| FM   | (30°-60°)   | 7963.8 | 24.2      |                         |      |         |
| FH   | (60°-80°)   | 5963.7 | 18.1      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 301.9  | 0.9       |                         |      | G3/500  |
| BL   | (0°-30°)    | 2243.5 | 6.8       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 7963.8 | 24.2      | B4/8500                 |      |         |
| BH   | (60°-80°)   | 5963.7 | 18.1      | B5                      |      | G5      |
| BVH  | (80°-90°)   | 301.9  | 0.9       |                         |      | G3/500  |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B5-U0-G5**

Type I Short



REPORT NUMBER: P233963

CATALOG NUMBER: CTN-10-3-D-E1-T1-7030

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°    | 65°     | 75°     | 85°     | 90°     |
|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|
| 0°    | 5305.7 | 5305.7 | 5305.7 | 5305.7 | 5305.7 | 5305.7 | 5305.7 | 5305.7  | 5305.7  | 5305.7  | 5305.7  |
| 2.5°  | 5320.5 | 5303.7 | 5310.6 | 5335.3 | 5245.5 | 5289.9 | 5274.1 | 5313.6  | 5292.9  | 5310.6  | 5319.5  |
| 5°    | 5283.0 | 5262.3 | 5272.1 | 5318.5 | 5236.6 | 5282.0 | 5270.2 | 5314.6  | 5287.9  | 5312.6  | 5322.5  |
| 7.5°  | 5250.4 | 5228.7 | 5246.5 | 5285.0 | 5222.8 | 5273.1 | 5263.3 | 5323.5  | 5301.8  | 5333.3  | 5343.2  |
| 10°   | 5229.7 | 5206.0 | 5222.8 | 5265.2 | 5199.1 | 5278.1 | 5269.2 | 5349.1  | 5338.3  | 5381.7  | 5393.6  |
| 12.5° | 5178.4 | 5153.7 | 5165.5 | 5221.8 | 5192.2 | 5274.1 | 5295.8 | 5387.6  | 5384.7  | 5437.0  | 5449.8  |
| 15°   | 5086.6 | 5061.9 | 5077.7 | 5152.7 | 5163.6 | 5277.1 | 5344.2 | 5452.8  | 5470.6  | 5522.9  | 5533.7  |
| 17.5° | 4971.1 | 4953.3 | 4977.0 | 5076.7 | 5144.8 | 5317.6 | 5414.3 | 5552.5  | 5595.9  | 5649.2  | 5664.0  |
| 20°   | 4813.1 | 4803.3 | 4845.7 | 4981.9 | 5112.2 | 5347.2 | 5498.2 | 5692.7  | 5771.6  | 5858.5  | 5869.3  |
| 22.5° | 4598.0 | 4586.1 | 4674.9 | 4866.4 | 5054.0 | 5354.1 | 5580.1 | 5837.8  | 5983.9  | 6095.4  | 6124.0  |
| 25°   | 4356.1 | 4352.2 | 4473.6 | 4725.3 | 4975.0 | 5349.1 | 5660.1 | 5992.7  | 6215.8  | 6362.9  | 6394.5  |
| 27.5° | 4118.2 | 4130.1 | 4277.1 | 4574.3 | 4909.9 | 5360.0 | 5751.9 | 6191.1  | 6506.0  | 6689.6  | 6703.5  |
| 30°   | 3915.9 | 3925.7 | 4084.7 | 4425.2 | 4847.7 | 5372.8 | 5865.4 | 6428.1  | 6867.3  | 7115.1  | 7155.6  |
| 32.5° | 3725.3 | 3748.1 | 3909.9 | 4263.3 | 4778.6 | 5397.5 | 6012.5 | 6737.0  | 7310.5  | 7701.4  | 7751.8  |
| 35°   | 3568.4 | 3588.1 | 3746.1 | 4098.5 | 4669.0 | 5417.3 | 6206.9 | 7127.9  | 7970.9  | 8621.4  | 8699.4  |
| 37.5° | 3429.2 | 3452.9 | 3589.1 | 3946.5 | 4538.7 | 5424.2 | 6400.4 | 7609.6  | 8865.2  | 9900.7  | 10143.5 |
| 40°   | 3328.5 | 3347.3 | 3464.8 | 3794.4 | 4398.6 | 5392.6 | 6621.5 | 8148.6  | 9870.1  | 11427.8 | 11694.3 |
| 42.5° | 3245.6 | 3261.4 | 3358.1 | 3645.4 | 4240.6 | 5330.4 | 6827.8 | 8685.6  | 10932.2 | 13045.6 | 13393.1 |
| 45°   | 3161.7 | 3165.7 | 3258.4 | 3517.1 | 4080.7 | 5231.7 | 6982.8 | 9199.9  | 12050.6 | 14696.1 | 15102.8 |
| 47.5° | 3086.7 | 3081.8 | 3154.8 | 3390.7 | 3909.0 | 5065.8 | 7043.0 | 9626.3  | 13137.4 | 16242.9 | 16687.1 |
| 50°   | 3016.6 | 2995.9 | 3059.0 | 3270.3 | 3742.1 | 4827.9 | 6967.0 | 9921.4  | 14280.5 | 17737.4 | 18131.2 |
| 52.5° | 2912.0 | 2902.1 | 2962.3 | 3151.8 | 3575.3 | 4543.7 | 6716.3 | 10077.4 | 15499.6 | 19152.9 | 19564.5 |
| 55°   | 2818.2 | 2811.3 | 2873.5 | 3031.4 | 3411.4 | 4254.4 | 6283.9 | 10034.9 | 16700.9 | 20518.0 | 20974.1 |
| 57.5° | 2714.5 | 2709.6 | 2767.9 | 2900.1 | 3230.8 | 3985.9 | 5748.9 | 9760.5  | 17773.9 | 21696.6 | 22341.2 |
| 60°   | 2612.9 | 2615.8 | 2653.3 | 2766.9 | 3047.2 | 3689.8 | 5138.9 | 9282.8  | 18629.7 | 22763.7 | 23467.5 |
| 62.5° | 2494.4 | 2491.5 | 2519.1 | 2613.9 | 2837.0 | 3370.0 | 4537.7 | 8620.4  | 19131.2 | 23695.5 | 24145.7 |
| 65°   | 2334.5 | 2323.7 | 2355.2 | 2415.5 | 2582.3 | 3042.3 | 3945.5 | 7818.9  | 19144.0 | 24158.5 | 24541.5 |
| 66°   | 2266.4 | 2254.6 | 2283.2 | 2325.6 | 2482.6 | 2910.0 | 3727.3 | 7479.3  | 18947.5 | 24172.3 | 24648.1 |
| 67.5° | 2160.8 | 2147.0 | 2165.7 | 2185.5 | 2326.6 | 2698.8 | 3407.5 | 7094.3  | 18517.2 | 24085.4 | 24716.2 |
| 70°   | 1898.2 | 1900.2 | 1919.9 | 1913.0 | 1985.1 | 2228.9 | 2814.2 | 6379.7  | 16441.3 | 23734.0 | 24351.0 |
| 72.5° | 1477.7 | 1460.9 | 1432.3 | 1404.7 | 1439.2 | 1653.4 | 2131.2 | 5354.1  | 13463.2 | 22218.8 | 23418.2 |
| 75°   | 953.5  | 950.6  | 949.6  | 983.2  | 988.1  | 1133.2 | 1646.5 | 4319.6  | 10494.9 | 18233.9 | 19960.3 |
| 77.5° | 596.2  | 591.3  | 633.7  | 715.7  | 728.5  | 732.4  | 1079.9 | 3283.1  | 7586.9  | 11667.6 | 12572.8 |
| 80°   | 427.4  | 427.4  | 430.4  | 441.2  | 510.3  | 521.2  | 746.3  | 2061.1  | 4314.7  | 5687.7  | 5976.0  |
| 82.5° | 323.8  | 318.8  | 319.8  | 324.8  | 330.7  | 355.4  | 449.1  | 915.0   | 1723.5  | 2882.4  | 3261.4  |
| 85°   | 233.9  | 240.9  | 252.7  | 243.8  | 220.1  | 223.1  | 254.7  | 314.9   | 662.3   | 1116.4  | 1207.2  |
| 87.5° | 84.9   | 97.7   | 100.7  | 104.6  | 100.7  | 101.7  | 104.6  | 98.7    | 134.2   | 275.4   | 317.8   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-6

Luminaire Tested: CST-CA6-230-730-U-T4

Test Date: 04/22/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/22/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-730-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 2914    | CRI (Ra): | 73.2 |      |       |
| CIE u':                   | 0.2541  | R1:       | 70.1 | R9:  | -27.2 |
| CIE v':                   | 0.5212  | R2:       | 83.3 | R10: | 61.9  |
| Duv:                      | -0.0013 | R3:       | 94.2 | R11: | 65.4  |
| CIE x:                    | 0.4410  | R4:       | 69.4 | R12: | 53.3  |
| CIE y:                    | 0.4020  | R5:       | 69.3 | R13: | 72.6  |
| CIE z:                    | 0.1571  | R6:       | 77.3 | R14: | 96.9  |
| Peak Wavelength (nm):     | 599     | R7:       | 77.5 |      |       |
| Dominant Wavelength (nm): | 583     | R8:       | 44.9 |      |       |
| Purity:                   | 53.4    |           |      |      |       |
| Rf:                       | 75.3    |           |      |      |       |
| Rg:                       | 95.7    |           |      |      |       |



### Test Conditions

Stabilization Time: 72M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.6/15%  
 Sphere Temperature (°C): 24.0


REPORT NUMBER: SP1-2104-215-6

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |




REPORT NUMBER: SP1-2104-215-6

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-6

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 12827            | 0.0              | 490       | 80096            | 11.4             | 620       | 649050           | 168.9            | 750       | 30187            | 0.0              | 880       | 19756            | 0.0              |
| 365       | 11336            | 0.0              | 495       | 104447           | 18.9             | 625       | 608162           | 134.2            | 755       | 27442            | 0.0              | 885       | 21245            | 0.0              |
| 370       | 11776            | 0.0              | 500       | 142477           | 31.4             | 630       | 557990           | 101.0            | 760       | 25382            | 0.0              | 890       | 17771            | 0.0              |
| 375       | 13009            | 0.0              | 505       | 187724           | 52.5             | 635       | 506861           | 76.2             | 765       | 23778            | 0.0              | 895       | 14356            | 0.0              |
| 380       | 13906            | 0.0              | 510       | 232209           | 79.8             | 640       | 460827           | 55.1             | 770       | 21474            | 0.0              | 900       | 16683            | 0.0              |
| 385       | 12960            | 0.0              | 515       | 273388           | 113.2            | 645       | 418064           | 40.3             | 775       | 21394            | 0.0              | 905       | 16548            | 0.0              |
| 390       | 11750            | 0.0              | 520       | 308378           | 149.5            | 650       | 376246           | 27.5             | 780       | 18945            | 0.0              | 910       | 15630            | 0.0              |
| 395       | 10399            | 0.0              | 525       | 336804           | 180.8            | 655       | 332016           | 19.0             | 785       | 16318            | 0.0              | 915       | 20907            | 0.0              |
| 400       | 9192             | 0.0              | 530       | 361609           | 212.9            | 660       | 294638           | 12.3             | 790       | 17841            | 0.0              | 920       | 16083            | 0.0              |
| 405       | 8943             | 0.0              | 535       | 382440           | 237.2            | 665       | 259105           | 8.2              | 795       | 16506            | 0.0              | 925       | 20203            | 0.0              |
| 410       | 11120            | 0.0              | 540       | 401976           | 261.9            | 670       | 223041           | 4.9              | 800       | 15058            | 0.0              | 930       | 22625            | 0.0              |
| 415       | 18193            | 0.0              | 545       | 426232           | 283.7            | 675       | 193569           | 3.2              | 805       | 16851            | 0.0              | 935       | 24828            | 0.0              |
| 420       | 32317            | 0.1              | 550       | 455969           | 309.9            | 680       | 167520           | 1.9              | 810       | 16679            | 0.0              | 940       | 21275            | 0.0              |
| 425       | 59220            | 0.3              | 555       | 490448           | 335.0            | 685       | 144697           | 1.2              | 815       | 15851            | 0.0              | 945       | 23270            | 0.0              |
| 430       | 100522           | 0.8              | 560       | 530799           | 360.7            | 690       | 125032           | 0.7              | 820       | 15536            | 0.0              | 950       | 21756            | 0.0              |
| 435       | 155311           | 1.8              | 565       | 572799           | 380.9            | 695       | 107458           | 0.5              | 825       | 16381            | 0.0              | 955       | 24823            | 0.0              |
| 440       | 239817           | 3.8              | 570       | 615361           | 400.1            | 700       | 93549            | 0.3              | 830       | 16149            | 0.0              | 960       | 19499            | 0.0              |
| 445       | 368265           | 7.7              | 575       | 659689           | 410.5            | 705       | 81608            | 0.2              | 835       | 16687            | 0.0              | 965       | 27077            | 0.0              |
| 450       | 439895           | 11.4             | 580       | 700037           | 416.0            | 710       | 71559            | 0.1              | 840       | 16206            | 0.0              | 970       | 28727            | 0.0              |
| 455       | 329010           | 11.0             | 585       | 734518           | 408.1            | 715       | 65193            | 0.1              | 845       | 16062            | 0.0              | 975       | 21725            | 0.0              |
| 460       | 207545           | 8.5              | 590       | 760906           | 393.4            | 720       | 58466            | 0.0              | 850       | 18530            | 0.0              | 980       | 33536            | 0.0              |
| 465       | 154577           | 8.0              | 595       | 763605           | 362.0            | 725       | 52265            | 0.0              | 855       | 17709            | 0.0              | 985       | 30537            | 0.0              |
| 470       | 110708           | 6.9              | 600       | 766048           | 330.1            | 730       | 46287            | 0.0              | 860       | 18086            | 0.0              | 990       | 25187            | 0.0              |
| 475       | 78445            | 6.2              | 605       | 756483           | 293.0            | 735       | 40164            | 0.0              | 865       | 19763            | 0.0              | 995       | 35676            | 0.0              |
| 480       | 68887            | 6.5              | 610       | 730981           | 251.1            | 740       | 35097            | 0.0              | 870       | 19416            | 0.0              | 1000      | 32909            | 0.0              |
| 485       | 69832            | 8.3              | 615       | 694682           | 209.7            | 745       | 32334            | 0.0              | 875       | 19352            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-6

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 43125.2

S/P: 1.19

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 12827                         | 0.0                            | 490               | 80096                         | 123.3                          | 620               | 649050                        | 8.1                            | 750               | 30187                         | 0.0                            | 880               | 19756                         | 0.0                            |
| 365               | 11336                         | 0.0                            | 495               | 104447                        | 168.8                          | 625               | 608162                        | 5.1                            | 755               | 27442                         | 0.0                            | 885               | 21245                         | 0.0                            |
| 370               | 11776                         | 0.0                            | 500               | 142477                        | 238.3                          | 630               | 557990                        | 3.2                            | 760               | 25382                         | 0.0                            | 890               | 17771                         | 0.0                            |
| 375               | 13009                         | 0.0                            | 505               | 187724                        | 319.1                          | 635               | 506861                        | 1.9                            | 765               | 23778                         | 0.0                            | 895               | 14356                         | 0.0                            |
| 380               | 13906                         | 0.0                            | 510               | 232209                        | 393.6                          | 640               | 460827                        | 1.2                            | 770               | 21474                         | 0.0                            | 900               | 16683                         | 0.0                            |
| 385               | 12960                         | 0.0                            | 515               | 273388                        | 453.1                          | 645               | 418064                        | 0.7                            | 775               | 21394                         | 0.0                            | 905               | 16548                         | 0.0                            |
| 390               | 11750                         | 0.0                            | 520               | 308378                        | 490.2                          | 650               | 376246                        | 0.4                            | 780               | 18945                         | 0.0                            | 910               | 15630                         | 0.0                            |
| 395               | 10399                         | 0.1                            | 525               | 336804                        | 503.9                          | 655               | 332016                        | 0.3                            | 785               | 16318                         | 0.0                            | 915               | 20907                         | 0.0                            |
| 400               | 9192                          | 0.1                            | 530               | 361609                        | 498.6                          | 660               | 294638                        | 0.2                            | 790               | 17841                         | 0.0                            | 920               | 16083                         | 0.0                            |
| 405               | 8943                          | 0.3                            | 535               | 382440                        | 476.6                          | 665               | 259105                        | 0.1                            | 795               | 16506                         | 0.0                            | 925               | 20203                         | 0.0                            |
| 410               | 11120                         | 0.7                            | 540               | 401976                        | 444.2                          | 670               | 223041                        | 0.1                            | 800               | 15058                         | 0.0                            | 930               | 22625                         | 0.0                            |
| 415               | 18193                         | 1.9                            | 545               | 426232                        | 408.7                          | 675               | 193569                        | 0.0                            | 805               | 16851                         | 0.0                            | 935               | 24828                         | 0.0                            |
| 420               | 32317                         | 5.3                            | 550               | 455969                        | 372.8                          | 680               | 167520                        | 0.0                            | 810               | 16679                         | 0.0                            | 940               | 21275                         | 0.0                            |
| 425               | 59220                         | 14.5                           | 555               | 490448                        | 335.2                          | 685               | 144697                        | 0.0                            | 815               | 15851                         | 0.0                            | 945               | 23270                         | 0.0                            |
| 430               | 100522                        | 34.2                           | 560               | 530799                        | 296.7                          | 690               | 125032                        | 0.0                            | 820               | 15536                         | 0.0                            | 950               | 21756                         | 0.0                            |
| 435               | 155311                        | 69.4                           | 565               | 572799                        | 257.0                          | 695               | 107458                        | 0.0                            | 825               | 16381                         | 0.0                            | 955               | 24823                         | 0.0                            |
| 440               | 239817                        | 134.0                          | 570               | 615361                        | 217.2                          | 700               | 93549                         | 0.0                            | 830               | 16149                         | 0.0                            | 960               | 19499                         | 0.0                            |
| 445               | 368265                        | 246.6                          | 575               | 659689                        | 179.7                          | 705               | 81608                         | 0.0                            | 835               | 16687                         | 0.0                            | 965               | 27077                         | 0.0                            |
| 450               | 439895                        | 340.9                          | 580               | 700037                        | 144.2                          | 710               | 71559                         | 0.0                            | 840               | 16206                         | 0.0                            | 970               | 28727                         | 0.0                            |
| 455               | 329010                        | 287.5                          | 585               | 734518                        | 112.3                          | 715               | 65193                         | 0.0                            | 845               | 16062                         | 0.0                            | 975               | 21725                         | 0.0                            |
| 460               | 207545                        | 200.5                          | 590               | 760906                        | 84.7                           | 720               | 58466                         | 0.0                            | 850               | 18530                         | 0.0                            | 980               | 33536                         | 0.0                            |
| 465               | 154577                        | 163.3                          | 595               | 763605                        | 60.9                           | 725               | 52265                         | 0.0                            | 855               | 17709                         | 0.0                            | 985               | 30537                         | 0.0                            |
| 470               | 110708                        | 127.5                          | 600               | 766048                        | 43.2                           | 730               | 46287                         | 0.0                            | 860               | 18086                         | 0.0                            | 990               | 25187                         | 0.0                            |
| 475               | 78445                         | 98.1                           | 605               | 756483                        | 29.7                           | 735               | 40164                         | 0.0                            | 865               | 19763                         | 0.0                            | 995               | 35676                         | 0.0                            |
| 480               | 68887                         | 93.1                           | 610               | 730981                        | 19.8                           | 740               | 35097                         | 0.0                            | 870               | 19416                         | 0.0                            | 1000              | 32909                         | 0.0                            |
| 485               | 69832                         | 101.2                          | 615               | 694682                        | 12.8                           | 745               | 32334                         | 0.0                            | 875               | 19352                         | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2104-215-6


### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 15555.2      M/P: 0.43**





| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 12827            | 0.0              | 490       | 80096            | 66.7             | 620       | 649050           | 0.5              | 750       | 30187            | 0.0              | 880       | 19756            | 0.0              |
| 365       | 11336            | 0.0              | 495       | 104447           | 86.2             | 625       | 608162           | 0.3              | 755       | 27442            | 0.0              | 885       | 21245            | 0.0              |
| 370       | 11776            | 0.0              | 500       | 142477           | 114.5            | 630       | 557990           | 0.2              | 760       | 25382            | 0.0              | 890       | 17771            | 0.0              |
| 375       | 13009            | 0.0              | 505       | 187724           | 144.1            | 635       | 506861           | 0.1              | 765       | 23778            | 0.0              | 895       | 14356            | 0.0              |
| 380       | 13906            | 0.0              | 510       | 232209           | 166.7            | 640       | 460827           | 0.1              | 770       | 21474            | 0.0              | 900       | 16683            | 0.0              |
| 385       | 12960            | 0.0              | 515       | 273388           | 178.6            | 645       | 418064           | 0.0              | 775       | 21394            | 0.0              | 905       | 16548            | 0.0              |
| 390       | 11750            | 0.0              | 520       | 308378           | 179.5            | 650       | 376246           | 0.0              | 780       | 18945            | 0.0              | 910       | 15630            | 0.0              |
| 395       | 10399            | 0.1              | 525       | 336804           | 170.8            | 655       | 332016           | 0.0              | 785       | 16318            | 0.0              | 915       | 20907            | 0.0              |
| 400       | 9192             | 0.1              | 530       | 361609           | 156.3            | 660       | 294638           | 0.0              | 790       | 17841            | 0.0              | 920       | 16083            | 0.0              |
| 405       | 8943             | 0.2              | 535       | 382440           | 137.6            | 665       | 259105           | 0.0              | 795       | 16506            | 0.0              | 925       | 20203            | 0.0              |
| 410       | 11120            | 0.4              | 540       | 401976           | 117.6            | 670       | 223041           | 0.0              | 800       | 15058            | 0.0              | 930       | 22625            | 0.0              |
| 415       | 18193            | 1.2              | 545       | 426232           | 99.0             | 675       | 193569           | 0.0              | 805       | 16851            | 0.0              | 935       | 24828            | 0.0              |
| 420       | 32317            | 3.7              | 550       | 455969           | 81.9             | 680       | 167520           | 0.0              | 810       | 16679            | 0.0              | 940       | 21275            | 0.0              |
| 425       | 59220            | 9.2              | 555       | 490448           | 66.1             | 685       | 144697           | 0.0              | 815       | 15851            | 0.0              | 945       | 23270            | 0.0              |
| 430       | 100522           | 21.2             | 560       | 530799           | 52.4             | 690       | 125032           | 0.0              | 820       | 15536            | 0.0              | 950       | 21756            | 0.0              |
| 435       | 155311           | 41.4             | 565       | 572799           | 40.2             | 695       | 107458           | 0.0              | 825       | 16381            | 0.0              | 955       | 24823            | 0.0              |
| 440       | 239817           | 80.1             | 570       | 615361           | 30.1             | 700       | 93549            | 0.0              | 830       | 16149            | 0.0              | 960       | 19499            | 0.0              |
| 445       | 368265           | 145.3            | 575       | 659689           | 22.0             | 705       | 81608            | 0.0              | 835       | 16687            | 0.0              | 965       | 27077            | 0.0              |
| 450       | 439895           | 202.7            | 580       | 700037           | 15.7             | 710       | 71559            | 0.0              | 840       | 16206            | 0.0              | 970       | 28727            | 0.0              |
| 455       | 329010           | 172.4            | 585       | 734518           | 10.9             | 715       | 65193            | 0.0              | 845       | 16062            | 0.0              | 975       | 21725            | 0.0              |
| 460       | 207545           | 122.3            | 590       | 760906           | 7.5              | 720       | 58466            | 0.0              | 850       | 18530            | 0.0              | 980       | 33536            | 0.0              |
| 465       | 154577           | 101.0            | 595       | 763605           | 4.9              | 725       | 52265            | 0.0              | 855       | 17709            | 0.0              | 985       | 30537            | 0.0              |
| 470       | 110708           | 79.3             | 600       | 766048           | 3.2              | 730       | 46287            | 0.0              | 860       | 18086            | 0.0              | 990       | 25187            | 0.0              |
| 475       | 78445            | 59.9             | 605       | 756483           | 2.1              | 735       | 40164            | 0.0              | 865       | 19763            | 0.0              | 995       | 35676            | 0.0              |
| 480       | 68887            | 55.4             | 610       | 730981           | 1.3              | 740       | 35097            | 0.0              | 870       | 19416            | 0.0              | 1000      | 32909            | 0.0              |
| 485       | 69832            | 57.6             | 615       | 694682           | 0.8              | 745       | 32334            | 0.0              | 875       | 19352            | 0.0              |           |                  |                  |

### Summary

$R_f = 75.3$   
 $R_g = 95.7$   
 CIE  $R_a = 73.2$   
 $R_g = -27.2$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 65 | CES51 = 87 | CES76 = 59 |
| CES02 = 63 | CES27 = 88 | CES52 = 86 | CES77 = 78 |
| CES03 = 31 | CES28 = 85 | CES53 = 77 | CES78 = 63 |
| CES04 = 71 | CES29 = 64 | CES54 = 86 | CES79 = 86 |
| CES05 = 49 | CES30 = 77 | CES55 = 85 | CES80 = 84 |
| CES06 = 51 | CES31 = 68 | CES56 = 75 | CES81 = 72 |
| CES07 = 42 | CES32 = 62 | CES57 = 75 | CES82 = 93 |
| CES08 = 40 | CES33 = 74 | CES58 = 76 | CES83 = 89 |
| CES09 = 29 | CES34 = 75 | CES59 = 86 | CES84 = 89 |
| CES10 = 76 | CES35 = 87 | CES60 = 92 | CES85 = 77 |
| CES11 = 59 | CES36 = 98 | CES61 = 84 | CES86 = 64 |
| CES12 = 65 | CES37 = 84 | CES62 = 92 | CES87 = 78 |
| CES13 = 43 | CES38 = 85 | CES63 = 75 | CES88 = 80 |
| CES14 = 74 | CES39 = 95 | CES64 = 70 | CES89 = 67 |
| CES15 = 71 | CES40 = 90 | CES65 = 67 | CES90 = 79 |
| CES16 = 47 | CES41 = 89 | CES66 = 65 | CES91 = 84 |
| CES17 = 50 | CES42 = 84 | CES67 = 63 | CES92 = 60 |
| CES18 = 56 | CES43 = 75 | CES68 = 69 | CES93 = 75 |
| CES19 = 73 | CES44 = 99 | CES69 = 78 | CES94 = 52 |
| CES20 = 66 | CES45 = 83 | CES70 = 63 | CES95 = 70 |
| CES21 = 87 | CES46 = 80 | CES71 = 61 | CES96 = 78 |
| CES22 = 79 | CES47 = 81 | CES72 = 86 | CES97 = 83 |
| CES23 = 92 | CES48 = 72 | CES73 = 55 | CES98 = 77 |
| CES24 = 91 | CES49 = 77 | CES74 = 96 | CES99 = 66 |
| CES25 = 73 | CES50 = 86 | CES75 = 63 |            |





**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)