

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510636

Luminaire Tested: **CTN-CA6-230-722-U-T2-HSS**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510636  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA6-230-722-U-T2-HSS  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (6) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 25557 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type II - Short  
BUG Rating: B3 - U0 - G3

Input Watts (W): 227.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P510636  
 CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd


--- 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9 fc  
 Type II - Short - N/A

REPORT NUMBER: P510636  
CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS

## Luminous Intensity Polar Plot



REPORT NUMBER: P510636

CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 4888.9   | 0.0    | 4888.9  |
|                    | % Fixture | 19.1     | 0.0    | 19.1    |
| <b>Street Side</b> | Lumens    | 20668.1  | 0.0    | 20668.1 |
|                    | % Fixture | 80.9     | 0.0    | 80.9    |
| <b>Total</b>       | Lumens    | 25557.0  | 0.0    | 25557.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 428.1   | 1.7       |
| 10°-20°   | 1287.6  | 5.0       |
| 20°-30°   | 2224.8  | 8.7       |
| 30°-40°   | 3345.5  | 13.1      |
| 40°-50°   | 4460.9  | 17.5      |
| 50°-60°   | 5253.6  | 20.6      |
| 60°-70°   | 5223.0  | 20.4      |
| 70°-80°   | 2998.6  | 11.7      |
| 80°-90°   | 335.0   | 1.3       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 25557.0 | 100.0     |
| 0°-180°   | 25557.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P510636


CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 2691.1  | 10.5      |                         |      |         |
| FM   | (30°-60°)   | 10738.4 | 42.0      |                         |      |         |
| FH   | (60°-80°)   | 6966.4  | 27.3      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 272.1   | 1.1       |                         |      | G3/500  |
| BL   | (0°-30°)    | 1249.4  | 4.9       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 2321.5  | 9.1       | B2/2500                 |      |         |
| BH   | (60°-80°)   | 1255.2  | 4.9       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 62.9    | 0.2       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G3**

Type II Short





REPORT NUMBER: P510636

CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°    | 25°    | 35°    | 45°    | 55°     | 65°     | 73°     | 75°     | 85°     |
|-------|--------|--------|--------|--------|--------|--------|---------|---------|---------|---------|---------|
| 0°    | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1  | 4482.1  | 4482.1  | 4482.1  | 4482.1  |
| 2.5°  | 4795.3 | 4807.4 | 4793.0 | 4786.7 | 4779.9 | 4735.1 | 4682.9  | 4629.6  | 4586.5  | 4579.6  | 4523.4  |
| 5°    | 5132.1 | 5138.4 | 5114.9 | 5087.9 | 5041.4 | 4967.4 | 4873.9  | 4781.6  | 4695.5  | 4672.6  | 4569.9  |
| 7.5°  | 5390.8 | 5378.8 | 5373.0 | 5350.1 | 5309.4 | 5227.9 | 5086.2  | 4934.7  | 4801.7  | 4769.5  | 4613.5  |
| 10°   | 5633.5 | 5628.3 | 5584.7 | 5556.0 | 5491.2 | 5416.1 | 5299.6  | 5107.4  | 4919.8  | 4868.2  | 4651.3  |
| 12.5° | 5896.2 | 5884.7 | 5867.0 | 5805.0 | 5752.2 | 5625.4 | 5484.9  | 5309.9  | 5101.1  | 5032.3  | 4716.2  |
| 15°   | 6132.6 | 6101.6 | 6091.8 | 6027.0 | 5973.7 | 5876.7 | 5735.6  | 5532.5  | 5309.4  | 5250.3  | 4839.5  |
| 17.5° | 6357.5 | 6343.1 | 6321.3 | 6277.1 | 6217.5 | 6142.9 | 6029.9  | 5812.5  | 5581.8  | 5495.8  | 5048.9  |
| 20°   | 6548.5 | 6530.7 | 6511.8 | 6523.8 | 6510.6 | 6463.0 | 6391.9  | 6206.6  | 5924.9  | 5841.7  | 5303.6  |
| 22.5° | 6681.6 | 6681.0 | 6756.7 | 6800.9 | 6826.1 | 6824.4 | 6807.2  | 6702.2  | 6418.8  | 6334.5  | 5684.5  |
| 25°   | 6792.3 | 6800.9 | 6896.7 | 7064.8 | 7215.1 | 7228.9 | 7350.5  | 7300.6  | 7059.6  | 6971.9  | 6257.6  |
| 27.5° | 6825.0 | 6842.2 | 7016.0 | 7280.5 | 7508.8 | 7728.0 | 7906.4  | 7997.6  | 7774.4  | 7669.4  | 6873.8  |
| 30°   | 6848.5 | 6855.4 | 7025.8 | 7342.5 | 7823.8 | 8170.8 | 8489.8  | 8644.1  | 8451.9  | 8375.1  | 7560.5  |
| 32.5° | 6682.7 | 6685.0 | 6946.0 | 7425.6 | 8055.0 | 8656.7 | 9034.2  | 9325.1  | 9274.6  | 9173.0  | 8311.4  |
| 35°   | 6454.4 | 6496.9 | 6796.3 | 7345.3 | 8245.4 | 9103.1 | 9617.1  | 10050.8 | 10151.7 | 10078.9 | 9061.8  |
| 37.5° | 6172.2 | 6205.4 | 6526.1 | 7226.0 | 8287.3 | 9410.0 | 10070.3 | 10788.5 | 11052.4 | 11040.4 | 9967.6  |
| 40°   | 5825.1 | 5865.8 | 6249.6 | 6969.0 | 8266.6 | 9633.1 | 10602.1 | 11605.4 | 11940.5 | 11902.6 | 10866.0 |
| 42.5° | 5414.9 | 5474.6 | 5846.9 | 6638.6 | 8115.8 | 9769.7 | 11037.5 | 12437.3 | 13040.2 | 13015.5 | 11661.1 |
| 45°   | 5009.3 | 5041.4 | 5381.1 | 6178.5 | 7838.1 | 9813.8 | 11447.1 | 13583.5 | 14168.0 | 14140.5 | 12619.1 |
| 47.5° | 4591.1 | 4619.2 | 4973.8 | 5693.7 | 7356.2 | 9724.9 | 11771.2 | 14567.9 | 15317.1 | 15289.6 | 13570.8 |
| 50°   | 3618.2 | 3724.3 | 4451.1 | 5267.5 | 6807.2 | 9473.1 | 12077.0 | 15794.4 | 16519.5 | 16402.5 | 14404.4 |
| 52.5° | 3095.5 | 3134.0 | 3510.9 | 4837.8 | 6259.4 | 9043.4 | 12281.2 | 16930.8 | 17508.5 | 17339.9 | 15256.9 |
| 55°   | 2893.6 | 2919.4 | 3104.2 | 4045.5 | 5744.8 | 8393.4 | 12521.6 | 18070.2 | 18250.3 | 18207.3 | 15952.2 |
| 57.5° | 2740.4 | 2769.1 | 2901.1 | 3378.9 | 5202.7 | 7482.4 | 12446.4 | 18871.6 | 19097.0 | 18959.4 | 16690.5 |
| 60°   | 2523.6 | 2558.6 | 2733.6 | 3033.6 | 4586.5 | 6557.7 | 11785.0 | 19199.7 | 19712.6 | 19557.7 | 17252.1 |
| 62.5° | 2387.1 | 2410.0 | 2510.4 | 2801.3 | 4076.0 | 5907.1 | 10843.6 | 19094.2 | 20021.8 | 20016.1 | 17739.2 |
| 65°   | 2201.8 | 2235.6 | 2342.9 | 2578.7 | 3621.6 | 5402.9 | 9955.5  | 18572.7 | 19888.7 | 19893.9 | 17839.5 |
| 67.5° | 2007.9 | 2021.6 | 2134.1 | 2323.4 | 3086.4 | 4941.1 | 8806.5  | 17680.6 | 18852.1 | 18970.3 | 17144.8 |
| 70°   | 1765.8 | 1758.9 | 1880.5 | 2018.8 | 2522.4 | 4195.3 | 7088.3  | 16093.9 | 17320.4 | 17369.1 | 15739.9 |
| 72.5° | 1389.4 | 1395.7 | 1429.6 | 1525.4 | 1914.9 | 3301.5 | 5143.6  | 13597.2 | 15719.2 | 15805.9 | 13944.3 |
| 75°   | 933.9  | 944.3  | 1102.0 | 1195.5 | 1377.4 | 2372.7 | 3234.4  | 9178.2  | 13288.6 | 13533.0 | 11412.7 |
| 77.5° | 712.5  | 718.8  | 764.7  | 866.8  | 996.5  | 1691.2 | 1753.1  | 5001.3  | 9674.4  | 10254.4 | 8928.1  |
| 80°   | 504.8  | 507.1  | 461.8  | 410.8  | 530.6  | 1147.3 | 1035.5  | 2130.1  | 3855.1  | 4555.5  | 5244.0  |
| 82.5° | 226.0  | 222.6  | 262.2  | 218.0  | 305.8  | 444.0  | 488.8   | 1033.8  | 1601.1  | 1721.0  | 1873.6  |
| 85°   | 105.0  | 117.6  | 134.8  | 113.0  | 181.9  | 171.5  | 190.5   | 440.6   | 750.4   | 828.4   | 823.8   |
| 87.5° | 25.8   | 28.1   | 35.6   | 45.3   | 66.0   | 58.5   | 57.4    | 129.7   | 167.5   | 166.9   | 256.4   |
| 90°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P510636

CATALOG NUMBER: CTN-CA6-230-722-U-T2-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4482.1  | 4482.1  | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 | 4482.1 |
| 2.5°  | 4485.0  | 4455.2  | 4384.6 | 4316.3 | 4251.5 | 4208.5 | 4160.3 | 4109.8 | 4079.4 | 4065.1 | 4096.0 |
| 5°    | 4507.4  | 4450.6  | 4315.8 | 4180.4 | 4065.6 | 3967.5 | 3898.7 | 3840.2 | 3808.6 | 3811.5 | 3813.2 |
| 7.5°  | 4526.3  | 4446.5  | 4257.8 | 4066.8 | 3887.8 | 3766.2 | 3676.1 | 3613.0 | 3576.9 | 3549.3 | 3570.0 |
| 10°   | 4542.9  | 4429.9  | 4190.1 | 3935.4 | 3740.9 | 3560.8 | 3438.6 | 3362.3 | 3295.8 | 3258.5 | 3287.7 |
| 12.5° | 4560.7  | 4423.6  | 4114.4 | 3817.8 | 3566.0 | 3364.6 | 3197.1 | 3121.4 | 3056.0 | 3027.9 | 3045.6 |
| 15°   | 4638.2  | 4447.7  | 4043.8 | 3679.5 | 3393.3 | 3132.8 | 2952.1 | 2859.2 | 2807.6 | 2773.7 | 2781.2 |
| 17.5° | 4771.2  | 4511.4  | 3998.5 | 3535.0 | 3200.5 | 2925.2 | 2691.1 | 2582.7 | 2497.2 | 2473.1 | 2466.8 |
| 20°   | 4960.6  | 4632.4  | 3998.5 | 3412.8 | 2982.0 | 2694.5 | 2424.9 | 2241.9 | 2108.8 | 2058.9 | 2097.4 |
| 22.5° | 5278.4  | 4838.4  | 4038.1 | 3302.1 | 2793.8 | 2455.3 | 2134.1 | 1854.7 | 1675.1 | 1602.3 | 1644.7 |
| 25°   | 5723.0  | 5156.8  | 4102.3 | 3205.1 | 2622.3 | 2180.0 | 1765.2 | 1443.9 | 1246.0 | 1159.4 | 1158.2 |
| 27.5° | 6303.5  | 5643.8  | 4232.0 | 3126.0 | 2416.9 | 1823.7 | 1380.3 | 1071.0 | 885.2  | 833.0  | 840.4  |
| 30°   | 6947.2  | 6171.6  | 4477.0 | 3011.2 | 2167.3 | 1425.0 | 1005.1 | 787.1  | 656.3  | 587.4  | 588.6  |
| 32.5° | 7567.9  | 6718.3  | 4767.8 | 2936.6 | 1843.2 | 1074.5 | 716.5  | 561.6  | 480.2  | 439.4  | 445.7  |
| 35°   | 8233.4  | 7189.9  | 4984.1 | 2811.6 | 1462.9 | 776.8  | 506.6  | 421.1  | 387.2  | 366.0  | 367.2  |
| 37.5° | 8952.2  | 7708.5  | 5161.9 | 2644.1 | 1106.0 | 533.5  | 374.0  | 360.8  | 346.5  | 319.5  | 317.2  |
| 40°   | 9703.1  | 8309.1  | 5268.0 | 2373.3 | 768.7  | 369.4  | 317.8  | 332.7  | 324.7  | 289.7  | 286.8  |
| 42.5° | 10339.9 | 8772.6  | 5294.4 | 2014.7 | 497.4  | 299.5  | 288.0  | 310.9  | 312.7  | 277.1  | 272.5  |
| 45°   | 10951.4 | 9185.7  | 5242.8 | 1542.6 | 344.8  | 281.7  | 269.6  | 301.2  | 303.5  | 271.3  | 263.9  |
| 47.5° | 11635.8 | 9750.7  | 5149.3 | 1029.2 | 285.1  | 266.2  | 263.3  | 285.1  | 293.1  | 266.8  | 257.6  |
| 50°   | 12467.1 | 10210.3 | 4872.2 | 632.2  | 269.1  | 256.4  | 256.4  | 269.6  | 280.5  | 257.6  | 253.0  |
| 52.5° | 13319.6 | 10610.7 | 4462.0 | 433.7  | 259.3  | 246.1  | 253.6  | 259.3  | 263.3  | 242.7  | 246.7  |
| 55°   | 13930.5 | 10965.8 | 3850.5 | 348.8  | 253.6  | 239.2  | 257.0  | 245.5  | 239.8  | 222.0  | 218.0  |
| 57.5° | 14608.6 | 11388.0 | 3225.2 | 309.2  | 246.1  | 243.2  | 245.5  | 223.7  | 207.7  | 189.3  | 185.3  |
| 60°   | 15081.9 | 11615.2 | 2459.9 | 290.9  | 237.5  | 239.2  | 226.6  | 197.3  | 168.1  | 154.9  | 152.0  |
| 62.5° | 15494.9 | 11744.8 | 1803.1 | 267.3  | 229.5  | 228.9  | 205.4  | 168.7  | 138.3  | 123.9  | 121.6  |
| 65°   | 15432.4 | 11542.3 | 1168.6 | 248.4  | 223.2  | 215.7  | 184.1  | 144.6  | 115.3  | 104.4  | 103.3  |
| 67.5° | 14744.6 | 10646.2 | 736.0  | 228.9  | 212.3  | 199.1  | 165.2  | 129.1  | 106.1  | 93.5   | 92.4   |
| 70°   | 13300.6 | 9408.8  | 450.3  | 203.7  | 188.7  | 176.1  | 146.3  | 121.0  | 100.4  | 85.5   | 82.6   |
| 72.5° | 11304.8 | 8058.4  | 318.4  | 179.6  | 164.6  | 149.7  | 123.9  | 115.3  | 95.8   | 76.9   | 74.6   |
| 75°   | 9287.8  | 5935.8  | 266.8  | 156.6  | 140.6  | 120.5  | 105.6  | 107.3  | 90.1   | 70.0   | 68.3   |
| 77.5° | 6540.5  | 3700.8  | 248.4  | 127.9  | 110.7  | 95.8   | 91.2   | 98.1   | 82.6   | 64.3   | 62.5   |
| 80°   | 3817.2  | 2078.4  | 205.4  | 101.0  | 83.2   | 74.0   | 76.3   | 83.2   | 72.3   | 57.9   | 55.6   |
| 82.5° | 1540.9  | 822.6   | 144.6  | 78.6   | 60.8   | 59.1   | 62.5   | 67.7   | 59.7   | 48.8   | 47.6   |
| 85°   | 550.2   | 257.0   | 82.0   | 51.6   | 39.0   | 40.7   | 40.2   | 48.2   | 43.0   | 35.6   | 35.0   |
| 87.5° | 144.6   | 51.1    | 36.7   | 20.7   | 16.6   | 16.6   | 15.5   | 22.4   | 20.7   | 16.1   | 17.8   |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-4

Luminaire Tested: CST-CA10-630-722-U-T3

Test Date: 04/20/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/20/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA10-630-722-U-T3**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 2174    | CRI (Ra): | 72.8 |      |       |
| CIE u':                   | 0.2919  | R1:       | 70.2 | R9:  | -23.3 |
| CIE v':                   | 0.5354  | R2:       | 86.8 | R10: | 71.8  |
| Duv:                      | -0.0007 | R3:       | 92.8 | R11: | 63.6  |
| CIE x:                    | 0.5067  | R4:       | 66.8 | R12: | 66.0  |
| CIE y:                    | 0.4131  | R5:       | 69.1 | R13: | 73.5  |
| CIE z:                    | 0.0802  | R6:       | 84.7 | R14: | 96.9  |
| Peak Wavelength (nm):     | 608     | R7:       | 73.2 |      |       |
| Dominant Wavelength (nm): | 587     | R8:       | 39.0 |      |       |
| Purity:                   | 76.7    |           |      |      |       |
| Rf:                       | 75.7    |           |      |      |       |
| Rg:                       | 96.7    |           |      |      |       |



### Test Conditions

Stabilization Time: 79M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.7/32%  
 Sphere Temperature (°C): 24.8

REPORT NUMBER: SP1-2104-215-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-4

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 19.5             | 620       | 2038916          | 530.6            | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 31.6             | 625       | 1946743          | 429.5            | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 51.3             | 630       | 1814508          | 328.4            | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 84.9             | 635       | 1681061          | 252.6            | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 128.6            | 640       | 1557170          | 186.1            | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 184.5            | 645       | 1430182          | 137.7            | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.0              | 520       | 510296           | 247.5            | 650       | 1300435          | 95.0             | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.0              | 525       | 566771           | 304.3            | 655       | 1165554          | 66.9             | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.0              | 530       | 617892           | 363.8            | 660       | 1044122          | 43.5             | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.0              | 535       | 664903           | 412.3            | 665       | 932131           | 29.6             | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.0              | 540       | 711603           | 463.7            | 670       | 808971           | 17.7             | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 0.1              | 545       | 768835           | 511.7            | 675       | 701208           | 11.7             | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 0.1              | 550       | 841179           | 571.6            | 680       | 610741           | 7.1              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 0.4              | 555       | 932641           | 637.0            | 685       | 533825           | 4.6              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 0.9              | 560       | 1040487          | 707.1            | 690       | 459427           | 2.6              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 2.0              | 565       | 1164360          | 774.2            | 695       | 399973           | 1.7              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 3.6              | 570       | 1307677          | 850.3            | 700       | 347460           | 1.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 6.6              | 575       | 1470810          | 915.2            | 705       | 302187           | 0.6              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 10.6             | 580       | 1637734          | 973.2            | 710       | 262909           | 0.4              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 12.8             | 585       | 1807622          | 1004.4           | 715       | 236689           | 0.3              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 11.0             | 590       | 1958195          | 1012.4           | 720       | 209675           | 0.1              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 10.5             | 595       | 2055425          | 974.3            | 725       | 184999           | 0.1              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 10.2             | 600       | 2141598          | 923.0            | 730       | 160261           | 0.1              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 10.1             | 605       | 2185430          | 846.3            | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 11.0             | 610       | 2170089          | 745.5            | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 14.3             | 615       | 2123505          | 641.1            | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-4

### Scotopic Flux vs. Wavelength


**Scotopic Lumens: 72942.9**
**S/P: 0.88**

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 23398                         | 0.0                            | 490               | 137099                        | 211.1                          | 620               | 2038916                       | 25.5                           | 750               | 99721                         | 0.0                            | 880               | 32326                         | 0.0                            |
| 365               | 18626                         | 0.0                            | 495               | 174286                        | 281.7                          | 625               | 1946743                       | 16.4                           | 755               | 91432                         | 0.0                            | 885               | 29783                         | 0.0                            |
| 370               | 21702                         | 0.0                            | 500               | 232711                        | 389.3                          | 630               | 1814508                       | 10.3                           | 760               | 83300                         | 0.0                            | 890               | 12135                         | 0.0                            |
| 375               | 22606                         | 0.0                            | 505               | 303528                        | 516.0                          | 635               | 1681061                       | 6.4                            | 765               | 72172                         | 0.0                            | 895               | 22953                         | 0.0                            |
| 380               | 25296                         | 0.0                            | 510               | 374456                        | 634.7                          | 640               | 1557170                       | 4.0                            | 770               | 65008                         | 0.0                            | 900               | 27214                         | 0.0                            |
| 385               | 27032                         | 0.1                            | 515               | 445274                        | 738.0                          | 645               | 1430182                       | 2.4                            | 775               | 56809                         | 0.0                            | 905               | 17038                         | 0.0                            |
| 390               | 22156                         | 0.1                            | 520               | 510296                        | 811.1                          | 650               | 1300435                       | 1.5                            | 780               | 49368                         | 0.0                            | 910               | 6896                          | 0.0                            |
| 395               | 20190                         | 0.2                            | 525               | 566771                        | 847.9                          | 655               | 1165554                       | 0.9                            | 785               | 51733                         | 0.0                            | 915               | 17142                         | 0.0                            |
| 400               | 18423                         | 0.3                            | 530               | 617892                        | 851.9                          | 660               | 1044122                       | 0.6                            | 790               | 41796                         | 0.0                            | 920               | 7675                          | 0.0                            |
| 405               | 16139                         | 0.5                            | 535               | 664903                        | 828.5                          | 665               | 932131                        | 0.3                            | 795               | 42601                         | 0.0                            | 925               | 21587                         | 0.0                            |
| 410               | 19812                         | 1.2                            | 540               | 711603                        | 786.3                          | 670               | 808971                        | 0.2                            | 800               | 36382                         | 0.0                            | 930               | 32992                         | 0.0                            |
| 415               | 29121                         | 3.0                            | 545               | 768835                        | 737.2                          | 675               | 701208                        | 0.1                            | 805               | 41419                         | 0.0                            | 935               | 35464                         | 0.0                            |
| 420               | 46007                         | 7.6                            | 550               | 841179                        | 687.8                          | 680               | 610741                        | 0.1                            | 810               | 35865                         | 0.0                            | 940               | 34460                         | 0.0                            |
| 425               | 76329                         | 18.7                           | 555               | 932641                        | 637.4                          | 685               | 533825                        | 0.0                            | 815               | 39722                         | 0.0                            | 945               | 46305                         | 0.0                            |
| 430               | 117696                        | 40.1                           | 560               | 1040487                       | 581.6                          | 690               | 459427                        | 0.0                            | 820               | 37236                         | 0.0                            | 950               | 38353                         | 0.0                            |
| 435               | 166890                        | 74.6                           | 565               | 1164360                       | 522.4                          | 695               | 399973                        | 0.0                            | 825               | 31566                         | 0.0                            | 955               | 30772                         | 0.0                            |
| 440               | 227762                        | 127.3                          | 570               | 1307677                       | 461.5                          | 700               | 347460                        | 0.0                            | 830               | 42647                         | 0.0                            | 960               | 32413                         | 0.0                            |
| 445               | 315427                        | 211.2                          | 575               | 1470810                       | 400.6                          | 705               | 302187                        | 0.0                            | 835               | 41433                         | 0.0                            | 965               | 35310                         | 0.0                            |
| 450               | 409560                        | 317.4                          | 580               | 1637734                       | 337.4                          | 710               | 262909                        | 0.0                            | 840               | 24213                         | 0.0                            | 970               | 28048                         | 0.0                            |
| 455               | 381103                        | 333.0                          | 585               | 1807622                       | 276.3                          | 715               | 236689                        | 0.0                            | 845               | 31358                         | 0.0                            | 975               | 26258                         | 0.0                            |
| 460               | 269221                        | 260.0                          | 590               | 1958195                       | 218.0                          | 720               | 209675                        | 0.0                            | 850               | 30957                         | 0.0                            | 980               | 31067                         | 0.0                            |
| 465               | 203513                        | 214.9                          | 595               | 2055425                       | 163.9                          | 725               | 184999                        | 0.0                            | 855               | 38865                         | 0.0                            | 985               | 40288                         | 0.0                            |
| 470               | 163989                        | 188.8                          | 600               | 2141598                       | 120.7                          | 730               | 160261                        | 0.0                            | 860               | 23238                         | 0.0                            | 990               | 29366                         | 0.0                            |
| 475               | 129159                        | 161.5                          | 605               | 2185430                       | 85.9                           | 735               | 140736                        | 0.0                            | 865               | 32686                         | 0.0                            | 995               | 54854                         | 0.0                            |
| 480               | 115440                        | 155.9                          | 610               | 2170089                       | 58.8                           | 740               | 125207                        | 0.0                            | 870               | 41855                         | 0.0                            | 1000              | 50994                         | 0.0                            |
| 485               | 120959                        | 175.3                          | 615               | 2123505                       | 39.3                           | 745               | 110736                        | 0.0                            | 875               | 35838                         | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2104-215-4

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 23955.7      M/P: 0.29**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 114.1            | 620       | 2038916          | 1.6              | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 143.9            | 625       | 1946743          | 1.0              | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 187.1            | 630       | 1814508          | 0.6              | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 232.9            | 635       | 1681061          | 0.4              | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 268.9            | 640       | 1557170          | 0.2              | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 290.9            | 645       | 1430182          | 0.2              | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.1              | 520       | 510296           | 297.1            | 650       | 1300435          | 0.1              | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.1              | 525       | 566771           | 287.4            | 655       | 1165554          | 0.1              | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.2              | 530       | 617892           | 267.0            | 660       | 1044122          | 0.0              | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.3              | 535       | 664903           | 239.3            | 665       | 932131           | 0.0              | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.8              | 540       | 711603           | 208.3            | 670       | 808971           | 0.0              | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 1.9              | 545       | 768835           | 178.6            | 675       | 701208           | 0.0              | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 5.3              | 550       | 841179           | 151.0            | 680       | 610741           | 0.0              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 11.9             | 555       | 932641           | 125.8            | 685       | 533825           | 0.0              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 24.9             | 560       | 1040487          | 102.6            | 690       | 459427           | 0.0              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 44.5             | 565       | 1164360          | 81.7             | 695       | 399973           | 0.0              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 76.1             | 570       | 1307677          | 63.9             | 700       | 347460           | 0.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 124.4            | 575       | 1470810          | 49.0             | 705       | 302187           | 0.0              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 188.7            | 580       | 1637734          | 36.6             | 710       | 262909           | 0.0              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 199.7            | 585       | 1807622          | 26.9             | 715       | 236689           | 0.0              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 158.6            | 590       | 1958195          | 19.2             | 720       | 209675           | 0.0              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 133.0            | 595       | 2055425          | 13.2             | 725       | 184999           | 0.0              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 117.4            | 600       | 2141598          | 9.0              | 730       | 160261           | 0.0              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 98.6             | 605       | 2185430          | 6.0              | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 92.8             | 610       | 2170089          | 3.9              | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 99.7             | 615       | 2123505          | 2.5              | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |


REPORT NUMBER: SP1-2104-215-4

TM-30-18





### Summary

$R_f = 75.7$   
 $R_g = 96.7$   
 CIE  $R_a = 72.8$   
 $R_g = -23.3$

### Spectral Power Distribution Comparison



### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 68 | CES51 = 84 | CES76 = 70 |
| CES02 = 65 | CES27 = 88 | CES52 = 83 | CES77 = 79 |
| CES03 = 32 | CES28 = 89 | CES53 = 77 | CES78 = 73 |
| CES04 = 72 | CES29 = 66 | CES54 = 87 | CES79 = 85 |
| CES05 = 52 | CES30 = 75 | CES55 = 85 | CES80 = 84 |
| CES06 = 53 | CES31 = 69 | CES56 = 76 | CES81 = 57 |
| CES07 = 44 | CES32 = 65 | CES57 = 75 | CES82 = 93 |
| CES08 = 43 | CES33 = 73 | CES58 = 78 | CES83 = 87 |
| CES09 = 29 | CES34 = 81 | CES59 = 86 | CES84 = 92 |
| CES10 = 79 | CES35 = 91 | CES60 = 94 | CES85 = 72 |
| CES11 = 62 | CES36 = 96 | CES61 = 85 | CES86 = 52 |
| CES12 = 68 | CES37 = 90 | CES62 = 92 | CES87 = 78 |
| CES13 = 45 | CES38 = 81 | CES63 = 78 | CES88 = 77 |
| CES14 = 75 | CES39 = 94 | CES64 = 73 | CES89 = 62 |
| CES15 = 72 | CES40 = 90 | CES65 = 71 | CES90 = 77 |
| CES16 = 49 | CES41 = 86 | CES66 = 71 | CES91 = 91 |
| CES17 = 51 | CES42 = 87 | CES67 = 69 | CES92 = 60 |
| CES18 = 57 | CES43 = 74 | CES68 = 74 | CES93 = 74 |
| CES19 = 74 | CES44 = 99 | CES69 = 85 | CES94 = 49 |
| CES20 = 69 | CES45 = 81 | CES70 = 70 | CES95 = 71 |
| CES21 = 89 | CES46 = 76 | CES71 = 72 | CES96 = 77 |
| CES22 = 81 | CES47 = 77 | CES72 = 89 | CES97 = 79 |
| CES23 = 92 | CES48 = 66 | CES73 = 64 | CES98 = 75 |
| CES24 = 92 | CES49 = 75 | CES74 = 87 | CES99 = 67 |
| CES25 = 74 | CES50 = 84 | CES75 = 75 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**


(END OF REPORT)