

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510441

Luminaire Tested: **CTN-CA10-210-750-U-T4**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510441  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-12)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA10-210-750-U-T4  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (10) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 35069 lumens  
Efficiency: N/A  
Efficacy: 164.7 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G5

Input Watts (W): 212.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P510441

CATALOG NUMBER: CTN-CA10-210-750-U-T4

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 4.4 fc  
 Type IV - Short - N/A

REPORT NUMBER: P510441  
CATALOG NUMBER: CTN-CA10-210-750-U-T4

## Luminous Intensity Polar Plot



REPORT NUMBER: P510441

CATALOG NUMBER: CTN-CA10-210-750-U-T4

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 7990.3   | 0.0    | 7990.3  |
|                    | % Fixture | 22.8     | 0.0    | 22.8    |
| <b>Street Side</b> | Lumens    | 27078.8  | 0.0    | 27078.8 |
|                    | % Fixture | 77.2     | 0.0    | 77.2    |
| <b>Total</b>       | Lumens    | 35069.0  | 0.0    | 35069.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 372.1   | 1.1       |
| 10°-20°   | 1150.4  | 3.3       |
| 20°-30°   | 2075.2  | 5.9       |
| 30°-40°   | 3214.0  | 9.2       |
| 40°-50°   | 4882.1  | 13.9      |
| 50°-60°   | 6766.9  | 19.3      |
| 60°-70°   | 8799.4  | 25.1      |
| 70°-80°   | 6498.2  | 18.5      |
| 80°-90°   | 1310.5  | 3.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 35069.0 | 100.0     |
| 0°-180°   | 35069.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P510441


CATALOG NUMBER: CTN-CA10-210-750-U-T4

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1880.1  | 5.4       |                         |      |         |
| FM   | (30°-60°)   | 10618.8 | 30.3      |                         |      |         |
| FH   | (60°-80°)   | 13460.3 | 38.4      |                         |      | G5      |
| FVH  | (80°-90°)   | 1119.6  | 3.2       |                         |      | G5      |
| BL   | (0°-30°)    | 1717.7  | 4.9       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 4244.3  | 12.1      | B3/5000                 |      |         |
| BH   | (60°-80°)   | 1837.3  | 5.2       | B3/2500                 |      | G3/2500 |
| BVH  | (80°-90°)   | 190.9   | 0.5       |                         |      | G2/225  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B3-U0-G5**

Type IV Short





REPORT NUMBER: P510441

CATALOG NUMBER: CTN-CA10-210-750-U-T4

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 36°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  | 3841.1  |
| 2.5°  | 3817.9  | 3812.8  | 3809.9  | 3815.7  | 3817.9  | 3818.6  | 3820.0  | 3818.6  | 3815.0  | 3828.0  | 3844.0  |
| 5°    | 3818.6  | 3815.7  | 3809.9  | 3804.8  | 3804.8  | 3804.8  | 3805.5  | 3822.2  | 3829.5  | 3828.0  | 3847.6  |
| 7.5°  | 3824.4  | 3822.2  | 3811.3  | 3807.7  | 3816.4  | 3819.3  | 3833.8  | 3828.8  | 3836.7  | 3849.8  | 3866.5  |
| 10°   | 3825.1  | 3822.2  | 3812.8  | 3820.8  | 3845.5  | 3849.8  | 3856.3  | 3870.9  | 3873.8  | 3889.8  | 3906.5  |
| 12.5° | 3832.4  | 3832.4  | 3836.0  | 3853.4  | 3879.6  | 3884.7  | 3909.4  | 3921.0  | 3938.4  | 3946.4  | 3966.7  |
| 15°   | 3870.9  | 3870.1  | 3878.9  | 3898.5  | 3940.6  | 3943.5  | 3974.0  | 4008.8  | 4021.9  | 4041.5  | 4074.2  |
| 17.5° | 3962.4  | 3966.7  | 3967.4  | 3982.0  | 4032.1  | 4033.5  | 4083.6  | 4116.3  | 4146.1  | 4180.9  | 4255.7  |
| 20°   | 4179.5  | 4171.5  | 4162.8  | 4162.8  | 4182.4  | 4192.5  | 4231.0  | 4283.3  | 4344.3  | 4406.0  | 4493.9  |
| 22.5° | 4452.5  | 4468.5  | 4436.5  | 4419.8  | 4429.2  | 4417.6  | 4446.7  | 4488.8  | 4559.9  | 4652.2  | 4763.3  |
| 25°   | 4778.5  | 4780.0  | 4777.8  | 4710.2  | 4689.2  | 4696.5  | 4720.4  | 4759.6  | 4854.0  | 4927.4  | 5088.6  |
| 27.5° | 5096.5  | 5090.0  | 5066.8  | 4995.6  | 4975.3  | 4985.4  | 4984.7  | 5092.9  | 5189.5  | 5283.1  | 5472.7  |
| 30°   | 5385.5  | 5403.0  | 5361.6  | 5241.8  | 5243.9  | 5242.5  | 5275.9  | 5415.3  | 5591.7  | 5766.0  | 5960.6  |
| 32.5° | 5895.3  | 5842.2  | 5786.3  | 5549.6  | 5506.1  | 5501.0  | 5520.6  | 5728.3  | 5989.6  | 6283.7  | 6517.5  |
| 35°   | 6375.2  | 6362.1  | 6307.0  | 6066.6  | 5814.7  | 5810.3  | 5783.4  | 6036.1  | 6403.5  | 6948.1  | 7240.0  |
| 37.5° | 6866.1  | 6847.2  | 6792.7  | 6588.0  | 6337.5  | 6313.5  | 6087.7  | 6364.3  | 6861.0  | 7725.0  | 8141.1  |
| 40°   | 7451.3  | 7439.7  | 7355.5  | 7093.3  | 6836.3  | 6800.0  | 6565.5  | 6709.2  | 7438.2  | 8759.7  | 9053.1  |
| 42.5° | 7964.7  | 7962.5  | 7865.9  | 7622.7  | 7404.1  | 7367.8  | 7168.1  | 7317.7  | 8240.6  | 9773.4  | 9946.2  |
| 45°   | 8341.5  | 8398.9  | 8403.2  | 8264.5  | 8113.5  | 8081.6  | 8028.6  | 8234.8  | 9168.5  | 10693.4 | 10668.0 |
| 47.5° | 8659.5  | 8708.9  | 8657.4  | 8586.2  | 8534.7  | 8536.8  | 8618.9  | 9028.4  | 10084.9 | 11495.0 | 11297.5 |
| 50°   | 9191.1  | 9160.6  | 8892.6  | 8850.5  | 8915.9  | 8954.3  | 9192.5  | 9885.2  | 11134.1 | 12247.2 | 11862.4 |
| 52.5° | 9957.8  | 9840.9  | 9315.2  | 9229.5  | 9477.1  | 9491.7  | 9870.7  | 10651.2 | 12182.6 | 12892.7 | 12379.4 |
| 55°   | 11007.0 | 10910.5 | 10316.5 | 9920.8  | 10045.7 | 10143.7 | 10677.4 | 11436.2 | 13038.7 | 13499.8 | 12777.3 |
| 57.5° | 12558.0 | 12565.3 | 12081.0 | 11343.2 | 10918.5 | 11023.0 | 11439.8 | 12199.3 | 13745.9 | 14008.0 | 13025.6 |
| 60°   | 13801.1 | 14031.3 | 13886.8 | 13549.9 | 12939.9 | 12868.8 | 12551.5 | 12994.4 | 14350.0 | 14440.1 | 13263.1 |
| 62.5° | 14663.0 | 14767.5 | 15264.2 | 15335.4 | 16032.4 | 16062.2 | 14542.5 | 13926.0 | 15013.7 | 14723.3 | 13313.2 |
| 65°   | 14619.4 | 14684.0 | 15469.0 | 16424.5 | 18483.8 | 18576.0 | 17686.5 | 15335.4 | 15468.2 | 14849.6 | 13167.2 |
| 67.5° | 13601.4 | 13698.7 | 14696.4 | 16482.6 | 19790.0 | 19755.2 | 19191.0 | 17297.3 | 15617.8 | 14647.0 | 12471.6 |
| 70°   | 11833.4 | 12133.2 | 12971.2 | 15257.7 | 20198.1 | 20244.6 | 19204.8 | 17923.9 | 15232.3 | 14074.1 | 11312.0 |
| 72.5° | 9753.1  | 9847.5  | 10638.9 | 13197.7 | 19005.1 | 18936.8 | 18417.7 | 17096.9 | 14535.2 | 13038.0 | 9282.5  |
| 75°   | 7417.2  | 7417.2  | 8375.6  | 10517.6 | 16320.7 | 16560.3 | 16762.2 | 15484.9 | 12876.8 | 10626.6 | 6320.8  |
| 77.5° | 4923.7  | 5100.2  | 5872.0  | 7903.7  | 12918.9 | 13096.0 | 13793.1 | 13199.2 | 10543.1 | 7792.6  | 2887.0  |
| 80°   | 2611.8  | 2633.6  | 3461.3  | 5251.9  | 9240.4  | 9574.4  | 10532.9 | 10180.0 | 7583.5  | 3650.9  | 729.7   |
| 82.5° | 913.4   | 996.9   | 1521.9  | 3043.8  | 6088.4  | 6296.8  | 6987.3  | 6049.2  | 2678.6  | 808.2   | 403.7   |
| 85°   | 453.8   | 469.8   | 670.2   | 1449.3  | 3427.9  | 3528.9  | 4082.2  | 2356.2  | 431.3   | 352.9   | 274.5   |
| 87.5° | 218.6   | 223.6   | 257.0   | 518.4   | 1490.0  | 1558.9  | 1650.4  | 766.8   | 159.7   | 134.3   | 119.1   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P510441

CATALOG NUMBER: CTN-CA10-210-750-U-T4

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 3841.1  | 3841.1  | 3841.1 | 3841.1 | 3841.1 | 3841.1 | 3841.1 | 3841.1 | 3841.1 | 3841.1 | 3841.1 |
| 2.5°  | 3847.6  | 3854.2  | 3866.5 | 3870.1 | 3861.4 | 3877.4 | 3892.7 | 3906.5 | 3905.7 | 3910.8 | 3929.0 |
| 5°    | 3856.3  | 3870.1  | 3883.2 | 3906.5 | 3929.0 | 3942.0 | 3954.4 | 3966.0 | 3969.6 | 3980.5 | 3991.4 |
| 7.5°  | 3883.2  | 3897.0  | 3926.8 | 3967.4 | 3968.9 | 4001.6 | 4022.6 | 4026.3 | 4029.2 | 4029.2 | 4054.6 |
| 10°   | 3924.6  | 3950.0  | 3997.9 | 4026.3 | 4051.7 | 4040.8 | 4062.6 | 4048.8 | 4038.6 | 4043.0 | 4060.4 |
| 12.5° | 3995.8  | 4018.3  | 4087.3 | 4118.5 | 4095.2 | 4090.9 | 4069.1 | 4037.9 | 4002.3 | 3998.7 | 4014.6 |
| 15°   | 4107.6  | 4149.7  | 4211.4 | 4241.2 | 4183.1 | 4131.5 | 4058.2 | 3994.3 | 3925.3 | 3899.9 | 3910.1 |
| 17.5° | 4287.7  | 4338.5  | 4406.0 | 4385.7 | 4279.7 | 4178.0 | 4056.8 | 3921.7 | 3788.1 | 3695.2 | 3719.1 |
| 20°   | 4551.2  | 4589.0  | 4644.2 | 4562.1 | 4407.5 | 4239.7 | 4040.8 | 3827.3 | 3601.5 | 3432.3 | 3412.7 |
| 22.5° | 4827.9  | 4885.2  | 4851.8 | 4700.1 | 4497.5 | 4263.7 | 4007.4 | 3690.1 | 3340.8 | 3128.8 | 3096.8 |
| 25°   | 5161.2  | 5180.0  | 5064.6 | 4835.9 | 4522.9 | 4225.9 | 3899.2 | 3489.7 | 3074.3 | 2874.7 | 2865.2 |
| 27.5° | 5514.8  | 5471.9  | 5257.0 | 4898.3 | 4494.6 | 4114.1 | 3682.1 | 3173.1 | 2833.3 | 2656.8 | 2629.2 |
| 30°   | 5914.1  | 5814.7  | 5416.0 | 4904.8 | 4387.9 | 3896.3 | 3407.6 | 2925.5 | 2637.2 | 2460.0 | 2431.7 |
| 32.5° | 6428.2  | 6193.7  | 5563.4 | 4837.3 | 4162.8 | 3576.8 | 3078.0 | 2714.2 | 2460.8 | 2282.9 | 2257.5 |
| 35°   | 7085.3  | 6689.6  | 5719.5 | 4715.3 | 3885.4 | 3257.3 | 2804.9 | 2534.8 | 2317.7 | 2103.5 | 2069.4 |
| 37.5° | 7842.7  | 7381.6  | 5906.1 | 4561.4 | 3581.2 | 2976.3 | 2620.5 | 2420.8 | 2211.7 | 1969.2 | 1928.5 |
| 40°   | 8722.7  | 8074.3  | 6193.7 | 4377.7 | 3308.1 | 2773.7 | 2531.2 | 2381.6 | 2152.9 | 1900.2 | 1853.7 |
| 42.5° | 9485.1  | 8806.9  | 6535.7 | 4180.2 | 3050.4 | 2605.3 | 2491.3 | 2355.5 | 2115.9 | 1848.7 | 1795.7 |
| 45°   | 10190.2 | 9411.8  | 6869.7 | 3940.6 | 2778.8 | 2489.8 | 2443.3 | 2290.1 | 2050.5 | 1784.8 | 1729.6 |
| 47.5° | 10763.1 | 9900.5  | 7160.1 | 3720.6 | 2561.7 | 2383.8 | 2338.8 | 2166.0 | 1940.9 | 1707.8 | 1667.1 |
| 50°   | 11203.1 | 10267.9 | 7319.1 | 3545.6 | 2332.3 | 2263.3 | 2203.7 | 2025.8 | 1809.5 | 1608.3 | 1573.5 |
| 52.5° | 11653.3 | 10636.0 | 7397.6 | 3554.3 | 2118.8 | 2083.9 | 2022.9 | 1870.4 | 1704.9 | 1550.2 | 1512.5 |
| 55°   | 11915.4 | 10787.0 | 7314.8 | 3343.0 | 1922.7 | 1882.1 | 1829.1 | 1749.9 | 1651.2 | 1513.9 | 1478.4 |
| 57.5° | 12068.6 | 10880.7 | 7062.8 | 2726.5 | 1686.7 | 1648.3 | 1657.0 | 1650.4 | 1569.1 | 1424.6 | 1391.9 |
| 60°   | 12179.0 | 10677.4 | 6546.6 | 2004.1 | 1485.6 | 1456.6 | 1528.5 | 1505.2 | 1434.8 | 1322.2 | 1294.6 |
| 62.5° | 12089.7 | 10290.4 | 5617.2 | 1506.7 | 1321.5 | 1383.2 | 1446.4 | 1403.6 | 1307.7 | 1205.3 | 1173.4 |
| 65°   | 11545.1 | 9530.9  | 4269.5 | 1210.4 | 1268.5 | 1353.5 | 1404.3 | 1335.3 | 1238.0 | 1116.8 | 1102.2 |
| 67.5° | 10554.0 | 8154.2  | 2518.1 | 1109.5 | 1228.6 | 1318.6 | 1360.7 | 1269.2 | 1183.6 | 1067.4 | 1049.9 |
| 70°   | 9041.5  | 6104.4  | 1124.7 | 1033.2 | 1158.9 | 1248.2 | 1275.8 | 1189.4 | 1096.4 | 987.5  | 970.1  |
| 72.5° | 6729.6  | 3680.6  | 758.1  | 954.1  | 1055.8 | 1134.9 | 1165.4 | 1073.9 | 1007.8 | 958.5  | 953.4  |
| 75°   | 3737.3  | 1277.9  | 699.2  | 864.1  | 943.2  | 1014.4 | 1052.1 | 987.5  | 935.2  | 867.7  | 840.1  |
| 77.5° | 1190.1  | 543.1   | 664.4  | 772.6  | 872.8  | 931.6  | 925.8  | 828.5  | 811.8  | 729.7  | 722.5  |
| 80°   | 474.9   | 473.4   | 614.3  | 632.4  | 745.0  | 794.4  | 781.3  | 658.6  | 680.4  | 632.4  | 613.6  |
| 82.5° | 372.5   | 433.5   | 492.3  | 482.9  | 579.4  | 637.5  | 619.4  | 483.6  | 546.8  | 502.5  | 459.6  |
| 85°   | 283.2   | 379.8   | 315.9  | 314.4  | 404.4  | 473.4  | 485.0  | 371.8  | 372.5  | 339.1  | 302.1  |
| 87.5° | 145.9   | 140.1   | 121.3  | 120.5  | 135.1  | 192.4  | 236.0  | 211.3  | 167.0  | 125.6  | 120.5  |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-7

Luminaire Tested: CST-CA6-230-750-U-T4

Test Date: 04/22/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/22/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-750-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 4852   | CRI (Ra): | 74.1 |      |       |
| CIE u':                   | 0.2118 | R1:       | 71.0 | R9:  | -25.4 |
| CIE v':                   | 0.4888 | R2:       | 79.6 | R10: | 51.4  |
| Duv:                      | 0.0017 | R3:       | 85.8 | R11: | 70.1  |
| CIE x:                    | 0.3498 | R4:       | 73.5 | R12: | 42.9  |
| CIE y:                    | 0.3588 | R5:       | 71.4 | R13: | 72.5  |
| CIE z:                    | 0.2914 | R6:       | 71.2 | R14: | 92.1  |
| Peak Wavelength (nm):     | 449    | R7:       | 82.9 |      |       |
| Dominant Wavelength (nm): | 572    | R8:       | 57.2 |      |       |
| Purity:                   | 12.7   |           |      |      |       |
| Rf:                       | 75.2   |           |      |      |       |
| Rg:                       | 94.7   |           |      |      |       |



### Test Conditions

Stabilization Time: 72M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.4/13%  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2104-215-7

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2104-215-7

### Photopic Flux vs. Wavelength



#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 15077            | 0.0              | 490       | 146327           | 20.8             | 620       | 434415           | 113.0            | 750       | 22886            | 0.0              | 880       | 20960            | 0.0              |
| 365       | 12138            | 0.0              | 495       | 188585           | 34.2             | 625       | 400670           | 88.4             | 755       | 19692            | 0.0              | 885       | 20315            | 0.0              |
| 370       | 12993            | 0.0              | 500       | 245069           | 54.1             | 630       | 360611           | 65.3             | 760       | 18199            | 0.0              | 890       | 15211            | 0.0              |
| 375       | 14513            | 0.0              | 505       | 307682           | 86.1             | 635       | 326986           | 49.1             | 765       | 19191            | 0.0              | 895       | 15502            | 0.0              |
| 380       | 15679            | 0.0              | 510       | 367102           | 126.1            | 640       | 295583           | 35.3             | 770       | 16229            | 0.0              | 900       | 15935            | 0.0              |
| 385       | 14569            | 0.0              | 515       | 416068           | 172.4            | 645       | 264664           | 25.5             | 775       | 16351            | 0.0              | 905       | 15965            | 0.0              |
| 390       | 13091            | 0.0              | 520       | 457470           | 221.8            | 650       | 238441           | 17.4             | 780       | 14567            | 0.0              | 910       | 16119            | 0.0              |
| 395       | 10927            | 0.0              | 525       | 486980           | 261.4            | 655       | 210047           | 12.1             | 785       | 13349            | 0.0              | 915       | 13972            | 0.0              |
| 400       | 9655             | 0.0              | 530       | 511184           | 301.0            | 660       | 186019           | 7.8              | 790       | 12552            | 0.0              | 920       | 14830            | 0.0              |
| 405       | 10895            | 0.0              | 535       | 527191           | 326.9            | 665       | 164001           | 5.2              | 795       | 11517            | 0.0              | 925       | 13744            | 0.0              |
| 410       | 14929            | 0.0              | 540       | 540658           | 352.3            | 670       | 142007           | 3.1              | 800       | 13250            | 0.0              | 930       | 20340            | 0.0              |
| 415       | 25993            | 0.0              | 545       | 555639           | 369.8            | 675       | 123441           | 2.1              | 805       | 15135            | 0.0              | 935       | 13272            | 0.0              |
| 420       | 49620            | 0.1              | 550       | 572229           | 388.9            | 680       | 106894           | 1.2              | 810       | 9873             | 0.0              | 940       | 16357            | 0.0              |
| 425       | 95836            | 0.5              | 555       | 589788           | 402.8            | 685       | 94026            | 0.8              | 815       | 11566            | 0.0              | 945       | 19257            | 0.0              |
| 430       | 178101           | 1.4              | 560       | 608278           | 413.4            | 690       | 82099            | 0.5              | 820       | 11216            | 0.0              | 950       | 19804            | 0.0              |
| 435       | 300144           | 3.5              | 565       | 619317           | 411.8            | 695       | 70275            | 0.3              | 825       | 15165            | 0.0              | 955       | 14877            | 0.0              |
| 440       | 512674           | 8.1              | 570       | 627176           | 407.8            | 700       | 61784            | 0.2              | 830       | 14983            | 0.0              | 960       | 9882             | 0.0              |
| 445       | 857336           | 17.9             | 575       | 631114           | 392.7            | 705       | 55550            | 0.1              | 835       | 13993            | 0.0              | 965       | 11741            | 0.0              |
| 450       | 1021494          | 26.5             | 580       | 630436           | 374.6            | 710       | 50234            | 0.1              | 840       | 15281            | 0.0              | 970       | 11068            | 0.0              |
| 455       | 730207           | 24.4             | 585       | 625204           | 347.4            | 715       | 44909            | 0.0              | 845       | 15737            | 0.0              | 975       | 18108            | 0.0              |
| 460       | 467897           | 19.2             | 590       | 612752           | 316.8            | 720       | 41441            | 0.0              | 850       | 15148            | 0.0              | 980       | 17506            | 0.0              |
| 465       | 344659           | 17.8             | 595       | 589048           | 279.2            | 725       | 36834            | 0.0              | 855       | 17198            | 0.0              | 985       | 23821            | 0.0              |
| 470       | 230541           | 14.3             | 600       | 567479           | 244.6            | 730       | 32988            | 0.0              | 860       | 19169            | 0.0              | 990       | 25862            | 0.0              |
| 475       | 157156           | 12.3             | 605       | 542722           | 210.2            | 735       | 28984            | 0.0              | 865       | 18632            | 0.0              | 995       | 21133            | 0.0              |
| 480       | 134805           | 12.8             | 610       | 507118           | 174.2            | 740       | 26177            | 0.0              | 870       | 18831            | 0.0              | 1000      | 25640            | 0.0              |
| 485       | 132031           | 15.6             | 615       | 472188           | 142.5            | 745       | 22680            | 0.0              | 875       | 16978            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-7

### Scotopic Flux vs. Wavelength



Scotopic Lumens: 66024.8

S/P: 1.78

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 15077                         | 0.0                            | 490               | 146327                        | 225.3                          | 620               | 434415                        | 5.4                            | 750               | 22886                         | 0.0                            | 880               | 20960                         | 0.0                            |
| 365               | 12138                         | 0.0                            | 495               | 188585                        | 304.9                          | 625               | 400670                        | 3.4                            | 755               | 19692                         | 0.0                            | 885               | 20315                         | 0.0                            |
| 370               | 12993                         | 0.0                            | 500               | 245069                        | 409.9                          | 630               | 360611                        | 2.0                            | 760               | 18199                         | 0.0                            | 890               | 15211                         | 0.0                            |
| 375               | 14513                         | 0.0                            | 505               | 307682                        | 523.1                          | 635               | 326986                        | 1.2                            | 765               | 19191                         | 0.0                            | 895               | 15502                         | 0.0                            |
| 380               | 15679                         | 0.0                            | 510               | 367102                        | 622.2                          | 640               | 295583                        | 0.8                            | 770               | 16229                         | 0.0                            | 900               | 15935                         | 0.0                            |
| 385               | 14569                         | 0.0                            | 515               | 416068                        | 689.6                          | 645               | 264664                        | 0.5                            | 775               | 16351                         | 0.0                            | 905               | 15965                         | 0.0                            |
| 390               | 13091                         | 0.0                            | 520               | 457470                        | 727.1                          | 650               | 238441                        | 0.3                            | 780               | 14567                         | 0.0                            | 910               | 16119                         | 0.0                            |
| 395               | 10927                         | 0.1                            | 525               | 486980                        | 728.5                          | 655               | 210047                        | 0.2                            | 785               | 13349                         | 0.0                            | 915               | 13972                         | 0.0                            |
| 400               | 9655                          | 0.2                            | 530               | 511184                        | 704.8                          | 660               | 186019                        | 0.1                            | 790               | 12552                         | 0.0                            | 920               | 14830                         | 0.0                            |
| 405               | 10895                         | 0.3                            | 535               | 527191                        | 656.9                          | 665               | 164001                        | 0.1                            | 795               | 11517                         | 0.0                            | 925               | 13744                         | 0.0                            |
| 410               | 14929                         | 0.9                            | 540               | 540658                        | 597.4                          | 670               | 142007                        | 0.0                            | 800               | 13250                         | 0.0                            | 930               | 20340                         | 0.0                            |
| 415               | 25993                         | 2.7                            | 545               | 555639                        | 532.7                          | 675               | 123441                        | 0.0                            | 805               | 15135                         | 0.0                            | 935               | 13272                         | 0.0                            |
| 420               | 49620                         | 8.2                            | 550               | 572229                        | 467.9                          | 680               | 106894                        | 0.0                            | 810               | 9873                          | 0.0                            | 940               | 16357                         | 0.0                            |
| 425               | 95836                         | 23.4                           | 555               | 589788                        | 403.1                          | 685               | 94026                         | 0.0                            | 815               | 11566                         | 0.0                            | 945               | 19257                         | 0.0                            |
| 430               | 178101                        | 60.6                           | 560               | 608278                        | 340.0                          | 690               | 82099                         | 0.0                            | 820               | 11216                         | 0.0                            | 950               | 19804                         | 0.0                            |
| 435               | 300144                        | 134.2                          | 565               | 619317                        | 277.8                          | 695               | 70275                         | 0.0                            | 825               | 15165                         | 0.0                            | 955               | 14877                         | 0.0                            |
| 440               | 512674                        | 286.5                          | 570               | 627176                        | 221.3                          | 700               | 61784                         | 0.0                            | 830               | 14983                         | 0.0                            | 960               | 9882                          | 0.0                            |
| 445               | 857336                        | 574.1                          | 575               | 631114                        | 171.9                          | 705               | 55550                         | 0.0                            | 835               | 13993                         | 0.0                            | 965               | 11741                         | 0.0                            |
| 450               | 1021494                       | 791.7                          | 580               | 630436                        | 129.9                          | 710               | 50234                         | 0.0                            | 840               | 15281                         | 0.0                            | 970               | 11068                         | 0.0                            |
| 455               | 730207                        | 638.1                          | 585               | 625204                        | 95.5                           | 715               | 44909                         | 0.0                            | 845               | 15737                         | 0.0                            | 975               | 18108                         | 0.0                            |
| 460               | 467897                        | 451.9                          | 590               | 612752                        | 68.2                           | 720               | 41441                         | 0.0                            | 850               | 15148                         | 0.0                            | 980               | 17506                         | 0.0                            |
| 465               | 344659                        | 364.0                          | 595               | 589048                        | 47.0                           | 725               | 36834                         | 0.0                            | 855               | 17198                         | 0.0                            | 985               | 23821                         | 0.0                            |
| 470               | 230541                        | 265.5                          | 600               | 567479                        | 32.0                           | 730               | 32988                         | 0.0                            | 860               | 19169                         | 0.0                            | 990               | 25862                         | 0.0                            |
| 475               | 157156                        | 196.5                          | 605               | 542722                        | 21.3                           | 735               | 28984                         | 0.0                            | 865               | 18632                         | 0.0                            | 995               | 21133                         | 0.0                            |
| 480               | 134805                        | 182.1                          | 610               | 507118                        | 13.7                           | 740               | 26177                         | 0.0                            | 870               | 18831                         | 0.0                            | 1000              | 25640                         | 0.0                            |
| 485               | 132031                        | 191.4                          | 615               | 472188                        | 8.7                            | 745               | 22680                         | 0.0                            | 875               | 16978                         | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2104-215-7

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 26696.3**      **M/P: 0.72**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 15077            | 0.0              | 490       | 146327           | 121.8            | 620       | 434415           | 0.3              | 750       | 22886            | 0.0              | 880       | 20960            | 0.0              |
| 365       | 12138            | 0.0              | 495       | 188585           | 155.7            | 625       | 400670           | 0.2              | 755       | 19692            | 0.0              | 885       | 20315            | 0.0              |
| 370       | 12993            | 0.0              | 500       | 245069           | 197.0            | 630       | 360611           | 0.1              | 760       | 18199            | 0.0              | 890       | 15211            | 0.0              |
| 375       | 14513            | 0.0              | 505       | 307682           | 236.1            | 635       | 326986           | 0.1              | 765       | 19191            | 0.0              | 895       | 15502            | 0.0              |
| 380       | 15679            | 0.0              | 510       | 367102           | 263.6            | 640       | 295583           | 0.0              | 770       | 16229            | 0.0              | 900       | 15935            | 0.0              |
| 385       | 14569            | 0.0              | 515       | 416068           | 271.9            | 645       | 264664           | 0.0              | 775       | 16351            | 0.0              | 905       | 15965            | 0.0              |
| 390       | 13091            | 0.0              | 520       | 457470           | 266.3            | 650       | 238441           | 0.0              | 780       | 14567            | 0.0              | 910       | 16119            | 0.0              |
| 395       | 10927            | 0.1              | 525       | 486980           | 247.0            | 655       | 210047           | 0.0              | 785       | 13349            | 0.0              | 915       | 13972            | 0.0              |
| 400       | 9655             | 0.1              | 530       | 511184           | 220.9            | 660       | 186019           | 0.0              | 790       | 12552            | 0.0              | 920       | 14830            | 0.0              |
| 405       | 10895            | 0.2              | 535       | 527191           | 189.7            | 665       | 164001           | 0.0              | 795       | 11517            | 0.0              | 925       | 13744            | 0.0              |
| 410       | 14929            | 0.6              | 540       | 540658           | 158.2            | 670       | 142007           | 0.0              | 800       | 13250            | 0.0              | 930       | 20340            | 0.0              |
| 415       | 25993            | 1.7              | 545       | 555639           | 129.1            | 675       | 123441           | 0.0              | 805       | 15135            | 0.0              | 935       | 13272            | 0.0              |
| 420       | 49620            | 5.7              | 550       | 572229           | 102.7            | 680       | 106894           | 0.0              | 810       | 9873             | 0.0              | 940       | 16357            | 0.0              |
| 425       | 95836            | 14.9             | 555       | 589788           | 79.5             | 685       | 94026            | 0.0              | 815       | 11566            | 0.0              | 945       | 19257            | 0.0              |
| 430       | 178101           | 37.6             | 560       | 608278           | 60.0             | 690       | 82099            | 0.0              | 820       | 11216            | 0.0              | 950       | 19804            | 0.0              |
| 435       | 300144           | 80.1             | 565       | 619317           | 43.5             | 695       | 70275            | 0.0              | 825       | 15165            | 0.0              | 955       | 14877            | 0.0              |
| 440       | 512674           | 171.3            | 570       | 627176           | 30.6             | 700       | 61784            | 0.0              | 830       | 14983            | 0.0              | 960       | 9882             | 0.0              |
| 445       | 857336           | 338.2            | 575       | 631114           | 21.0             | 705       | 55550            | 0.0              | 835       | 13993            | 0.0              | 965       | 11741            | 0.0              |
| 450       | 1021494          | 470.7            | 580       | 630436           | 14.1             | 710       | 50234            | 0.0              | 840       | 15281            | 0.0              | 970       | 11068            | 0.0              |
| 455       | 730207           | 382.6            | 585       | 625204           | 9.3              | 715       | 44909            | 0.0              | 845       | 15737            | 0.0              | 975       | 18108            | 0.0              |
| 460       | 467897           | 275.7            | 590       | 612752           | 6.0              | 720       | 41441            | 0.0              | 850       | 15148            | 0.0              | 980       | 17506            | 0.0              |
| 465       | 344659           | 225.2            | 595       | 589048           | 3.8              | 725       | 36834            | 0.0              | 855       | 17198            | 0.0              | 985       | 23821            | 0.0              |
| 470       | 230541           | 165.0            | 600       | 567479           | 2.4              | 730       | 32988            | 0.0              | 860       | 19169            | 0.0              | 990       | 25862            | 0.0              |
| 475       | 157156           | 120.0            | 605       | 542722           | 1.5              | 735       | 28984            | 0.0              | 865       | 18632            | 0.0              | 995       | 21133            | 0.0              |
| 480       | 134805           | 108.3            | 610       | 507118           | 0.9              | 740       | 26177            | 0.0              | 870       | 18831            | 0.0              | 1000      | 25640            | 0.0              |
| 485       | 132031           | 108.8            | 615       | 472188           | 0.6              | 745       | 22680            | 0.0              | 875       | 16978            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-7


TM-30-18

### Summary

$R_f = 75.2$   
 $R_g = 94.7$   
 CIE  $R_a = 74.1$   
 $R_g = -25.4$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 63 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 88 | CES52 = 90 | CES77 = 68 |
| CES03 = 30 | CES28 = 81 | CES53 = 81 | CES78 = 54 |
| CES04 = 69 | CES29 = 67 | CES54 = 86 | CES79 = 81 |
| CES05 = 46 | CES30 = 85 | CES55 = 84 | CES80 = 77 |
| CES06 = 50 | CES31 = 71 | CES56 = 76 | CES81 = 79 |
| CES07 = 39 | CES32 = 63 | CES57 = 75 | CES82 = 91 |
| CES08 = 38 | CES33 = 79 | CES58 = 76 | CES83 = 89 |
| CES09 = 29 | CES34 = 70 | CES59 = 87 | CES84 = 86 |
| CES10 = 73 | CES35 = 83 | CES60 = 89 | CES85 = 79 |
| CES11 = 56 | CES36 = 90 | CES61 = 83 | CES86 = 76 |
| CES12 = 62 | CES37 = 79 | CES62 = 85 | CES87 = 78 |
| CES13 = 42 | CES38 = 94 | CES63 = 76 | CES88 = 82 |
| CES14 = 74 | CES39 = 96 | CES64 = 67 | CES89 = 74 |
| CES15 = 70 | CES40 = 91 | CES65 = 64 | CES90 = 81 |
| CES16 = 46 | CES41 = 95 | CES66 = 61 | CES91 = 74 |
| CES17 = 49 | CES42 = 80 | CES67 = 58 | CES92 = 61 |
| CES18 = 55 | CES43 = 78 | CES68 = 66 | CES93 = 77 |
| CES19 = 71 | CES44 = 99 | CES69 = 74 | CES94 = 56 |
| CES20 = 64 | CES45 = 86 | CES70 = 58 | CES95 = 67 |
| CES21 = 85 | CES46 = 85 | CES71 = 51 | CES96 = 78 |
| CES22 = 77 | CES47 = 88 | CES72 = 83 | CES97 = 86 |
| CES23 = 91 | CES48 = 80 | CES73 = 48 | CES98 = 77 |
| CES24 = 90 | CES49 = 83 | CES74 = 92 | CES99 = 65 |
| CES25 = 71 | CES50 = 90 | CES75 = 52 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)