

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: METALUX

Report Number: P981643

Luminaire Tested: 4PWM-2060C5-845-MEDIUMHIGH

Issue Date: 01/28/2026

Test Information

Test Method: LM-79-2019
Report Number: P981643
Test Lab: INNOVATION CENTER(P3)
Issue Date: 01/28/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: METALUX
Catalog Number: 4PWM-2060C5-845-MEDIUMHIGH
Description: METALUX 8.75 INCH PROWRAP 80CRI 4500K FIXTURE MEDIUM-HIGH OUTPUT SETTING
Light Source: 4500K CCT, 80+ CRI LEDS
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5225.9 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.32 / 1.44
Luminous Opening: Rectangular w/ Sides (W: 0.73' x L: 3.76' x H: 0.19')
CIE Type: Semi-Direct

Input Watts (W): 39.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT

TEST NUMBER: P981643
CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

Luminous Intensity Polar Plot





TEST NUMBER: P981643

CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	116	116	116	116	111	111	111	111	103	103	103	96	96	96	89	89	89	89	89	89	85
1	103	98	93	88	99	94	90	85	87	83	80	81	78	75	75	72	70	75	72	70	67
2	93	84	77	70	89	81	74	68	75	69	64	69	65	61	64	61	57	64	61	57	54
3	84	73	64	57	81	70	62	56	65	59	53	61	55	50	56	52	48	56	52	48	45
4	77	64	55	48	73	62	54	47	58	50	45	54	47	43	50	45	40	50	45	40	38
5	71	57	48	41	67	55	47	40	51	44	38	48	42	37	45	39	35	45	39	35	32
6	65	51	42	35	62	50	41	35	46	39	33	43	37	32	40	35	30	40	35	30	28
7	60	46	37	31	57	45	36	30	42	35	29	39	33	28	37	31	27	37	31	27	25
8	56	42	33	27	53	41	33	27	38	31	26	36	30	25	34	28	24	34	28	24	22
9	52	39	30	25	50	37	29	24	35	28	23	33	27	22	31	26	21	31	26	21	19
10	49	35	27	22	47	34	27	22	32	26	21	31	24	20	29	23	19	29	23	19	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5103	5103	5103
5°	5109	4973	5001
10°	5081	4883	4797
15°	5091	4804	4631
20°	4892	4680	4707
25°	4839	4607	4567
30°	4903	4558	4504
35°	4688	4484	4482
40°	4692	4359	4396
45°	4599	4288	4399
50°	4488	4232	4384
55°	4302	4178	4226
60°	4174	4057	4205
65°	4022	3972	4159
70°	3777	3868	4169
75°	3408	3802	4110
80°	2926	3650	4130
85°	2012	3572	4361

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 4860 cd/sqm



TEST NUMBER: P981643

CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.6	2.4
10°-20°	353.8	6.8
20°-30°	545.1	10.4
30°-40°	672.0	12.9
40°-50°	725.7	13.9
50°-60°	702.0	13.4
60°-70°	605.8	11.6
70°-80°	452.8	8.7
80°-90°	282.6	5.4
90°-100°	185.9	3.6
100°-110°	157.4	3.0
110°-120°	134.5	2.6
120°-130°	107.5	2.1
130°-140°	79.7	1.5
140°-150°	52.6	1.0
150°-160°	29.3	0.6
160°-170°	12.7	0.2
170°-180°	3.0	0.1
0°-30°	1022.5	19.6
0°-40°	1694.5	32.4
0°-60°	3122.1	59.7
0°-90°	4463.3	85.4
90°-120°	477.8	9.1
90°-150°	717.6	13.7
90°-180°	763.0	14.6
0°-180°	5225.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1301	1301	1301	1301	1301	
5°	1304	1313	1287	1299	1299	124
15°	1271	1254	1252	1261	1219	354
25°	1144	1172	1172	1224	1182	534
35°	1013	1039	1079	1119	1105	641
45°	871	887	941	997	997	669
55°	674	718	800	854	845	609
65°	480	538	627	702	695	474
75°	267	346	454	520	531	284
85°	70	162	276	360	382	77
90°	0	98	213	302	318	4
95°	0	80	185	269	288	1
105°	2	77	164	227	248	3
115°	7	73	150	204	222	6
125°	12	68	131	176	194	11
135°	19	63	112	147	159	15
145°	21	49	94	117	124	13
155°	26	40	66	87	94	12
165°	30	33	42	54	61	9
175°	33	33	30	26	33	3
180°	26	26	26	26	26	



TEST NUMBER: P981643

CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1301.2	1301.2	1301.2	1301.2	1301.2
2.5°	1308.3	1315.3	1284.9	1301.2	1301.2
5°	1303.6	1312.9	1287.2	1298.9	1298.9
7.5°	1296.6	1284.9	1289.5	1312.9	1289.5
10°	1287.2	1282.5	1273.2	1303.6	1259.1
12.5°	1294.2	1256.8	1254.4	1284.9	1270.8
15°	1270.8	1254.4	1252.1	1261.4	1219.3
17.5°	1214.6	1224.0	1228.7	1247.4	1247.4
20°	1193.6	1212.3	1210.0	1233.4	1233.4
22.5°	1191.2	1188.9	1191.2	1219.3	1219.3
25°	1144.4	1172.5	1172.5	1224.0	1181.9
27.5°	1135.1	1144.4	1156.1	1188.9	1184.2
30°	1114.0	1102.3	1132.7	1160.8	1142.1
32.5°	1048.5	1064.9	1095.3	1142.1	1128.0
35°	1013.4	1039.1	1078.9	1118.7	1104.6
37.5°	994.6	1006.4	1048.5	1097.6	1081.2
40°	954.9	964.2	1006.4	1055.5	1043.8
42.5°	898.7	931.5	978.3	1027.4	1034.4
45°	870.6	887.0	940.8	997.0	997.0
47.5°	828.5	835.5	910.4	966.6	973.6
50°	779.3	805.1	873.0	931.5	938.5
52.5°	732.5	753.6	835.5	891.7	903.4
55°	674.0	718.5	800.4	854.2	844.9
57.5°	636.6	667.0	760.6	823.8	823.8
60°	578.1	627.2	711.5	779.3	774.7
62.5°	531.3	575.7	667.0	741.9	732.5
65°	479.8	538.3	627.2	702.1	695.1
67.5°	428.3	484.5	589.8	653.0	662.3
70°	374.5	440.0	538.3	608.5	620.2
72.5°	320.6	388.5	493.8	568.7	575.7
75°	266.8	346.4	454.0	519.6	531.3
77.5°	220.0	297.2	402.5	470.4	484.5
80°	166.2	248.1	360.4	435.3	449.3
82.5°	117.0	206.0	313.6	388.5	409.6
85°	70.2	161.5	276.2	360.4	381.5
87.5°	28.1	124.0	243.4	332.3	351.1
90°	0.0	98.3	213.0	301.9	318.3
92.5°	0.0	84.3	198.9	278.5	304.2
95°	0.0	79.6	184.9	269.1	287.9
97.5°	0.0	77.2	175.5	250.4	271.5
100°	2.3	77.2	170.8	238.7	262.1
102.5°	2.3	77.2	166.2	234.0	257.4
105°	2.3	77.2	163.8	227.0	248.1
107.5°	2.3	74.9	161.5	222.3	243.4
110°	4.7	77.2	159.1	217.7	238.7



TEST NUMBER: P981643

CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	4.7	74.9	154.5	210.6	229.4
115°	7.0	72.6	149.8	203.6	222.3
117.5°	7.0	72.6	142.8	198.9	217.7
120°	9.4	70.2	140.4	189.6	208.3
122.5°	11.7	72.6	135.7	182.5	196.6
125°	11.7	67.9	131.1	175.5	194.2
127.5°	14.0	67.9	128.7	168.5	187.2
130°	16.4	65.5	121.7	163.8	173.2
132.5°	18.7	63.2	117.0	154.5	168.5
135°	18.7	63.2	112.3	147.4	159.1
137.5°	21.1	58.5	107.7	140.4	152.1
140°	21.1	56.2	103.0	131.1	140.4
142.5°	21.1	53.8	98.3	126.4	138.1
145°	21.1	49.1	93.6	117.0	124.0
147.5°	21.1	46.8	84.3	110.0	119.4
150°	23.4	44.5	77.2	103.0	110.0
152.5°	23.4	42.1	70.2	93.6	100.6
155°	25.7	39.8	65.5	86.6	93.6
157.5°	25.7	37.4	56.2	81.9	86.6
160°	28.1	35.1	51.5	72.6	79.6
162.5°	30.4	35.1	46.8	63.2	70.2
165°	30.4	32.8	42.1	53.8	60.8
167.5°	30.4	32.8	37.4	44.5	53.8
170°	30.4	32.8	32.8	37.4	44.5
172.5°	30.4	30.4	32.8	30.4	37.4
175°	32.8	32.8	30.4	25.7	32.8
177.5°	32.8	30.4	28.1	23.4	25.7
180°	25.7	25.7	25.7	25.7	25.7



TEST NUMBER: P981643
 CATALOG NUMBER: 4PWM-2060C5-845-MEDIUMHIGH

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room Dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.0	16.4	15.5	17.0	17.6	17.0	18.4	17.6	19.0	19.7
	3H	16.7	18.0	17.3	18.6	19.2	19.5	20.8	20.1	21.4	22.1
	4H	17.3	18.5	17.9	19.1	19.8	20.7	21.9	21.3	22.5	23.2
	6H	17.7	18.8	18.3	19.4	20.2	21.8	22.9	22.4	23.6	24.3
	8H	17.8	18.9	18.4	19.5	20.2	22.4	23.5	23.0	24.1	24.8
	12H	17.8	18.9	18.5	19.5	20.3	23.0	24.1	23.7	24.7	25.5
4H	2H	15.9	17.2	16.5	17.8	18.5	17.5	18.7	18.1	19.4	20.1
	3H	17.9	18.9	18.5	19.6	20.3	20.2	21.3	20.9	21.9	22.6
	4H	18.6	19.6	19.3	20.2	21.0	21.6	22.5	22.2	23.2	23.9
	6H	19.2	20.0	19.8	20.7	21.5	22.9	23.8	23.6	24.4	25.2
	8H	19.3	20.1	20.0	20.8	21.6	23.6	24.4	24.3	25.1	25.8
	12H	19.4	20.1	20.1	20.8	21.6	24.4	25.1	25.0	25.8	26.6
8H	4H	19.4	20.1	20.0	20.8	21.6	21.8	22.6	22.5	23.3	24.1
	6H	20.1	20.8	20.8	21.5	22.3	23.4	24.0	24.1	24.8	25.5
	8H	20.3	21.0	21.0	21.7	22.5	24.2	24.8	24.9	25.5	26.3
	12H	20.5	21.1	21.2	21.8	22.6	25.1	25.7	25.8	26.4	27.2
12H	4H	19.5	20.3	20.2	21.0	21.7	21.8	22.6	22.5	23.3	24.0
	6H	20.4	21.0	21.1	21.7	22.5	23.4	24.0	24.1	24.7	25.6
	8H	20.7	21.3	21.4	22.0	22.8	24.3	24.9	25.0	25.6	26.4

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Report Prepared for

Cooper Lighting Solutions

Metalux

Report Number: SP3-2511-615-14

Test Date: 01/15/2026

Luminaire Tested: PW-S-6K-845-2nd

Data in this report applies to families of products including PW-S-6K*


Test Information

Test Method: LM-79-2019
 Report Number: SP3-2511-615-14
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP3 - 3M SPHERE
 Measurement Geometry: 4π
 Issue Date: 01/20/2026
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: Metalux
 Catalog Number: **PW-S-6K-845-2nd**
 Description: 8.75" Wrap 5 CCT 5 lumen select @6000lms (switch) @4500K 2nd Round

Spectral Parameters

CCT (K): 4535
 CIE u': 0.2164
 CIE v': 0.4929
 Duv: 0.0007
 CIE x: 0.3599
 CIE y: 0.3644
 CIE z: 0.2758
 Peak Wavelength (nm): 451
 Dominant Wavelength (nm): 576
 Purity: 17.31335
 Rf: 85
 Rg: 96.9

CRI (Ra):	85.1		
R1:	83.9	R9:	18.6
R2:	90.0	R10:	75.8
R3:	94.1	R11:	84.2
R4:	84.7	R12:	60.5
R5:	83.8	R13:	85.6
R6:	85.5	R14:	96.9
R7:	88.4	R15:	78.5
R8:	70.0		



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.0

REPORT NUMBER: SP3-2511-615-14


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	3M SPHERE IN02505	1/10/2026	7/10/2026
Power Meter	XITRON INXT2011006	10/21/2025	10/21/2026
AC Power Source	CHROMA 61604 IN6064A	10/20/2025	10/20/2026
DC Power Source	EYSIGHT N5770A IN0534	10/20/2025	10/20/2026
Sphere Thermometer	TANDD IN4036E	10/21/2025	10/21/2026

REPORT NUMBER: SP3-2511-615-14

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles




CCT = 4535K
 CIE x = 0.3599
 CIE y = 0.3644
 Duv = 0.0007

Point lies inside the ANSI 4500K 4-step quadrangle

REPORT NUMBER: SP3-2511-615-14

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	271	NR	620	561	NR	750	17	NR	880	1	NR
365	0	NR	495	316	NR	625	527	NR	755	15	NR	885	1	NR
370	0	NR	500	373	NR	630	489	NR	760	13	NR	890	1	NR
375	0	NR	505	417	NR	635	450	NR	765	11	NR	895	0	NR
380	0	NR	510	458	NR	640	413	NR	770	9	NR	900	0	NR
385	0	NR	515	487	NR	645	375	NR	775	8	NR	905	0	NR
390	2	NR	520	509	NR	650	340	NR	780	7	NR	910	0	NR
395	4	NR	525	522	NR	655	304	NR	785	6	NR	915	0	NR
400	6	NR	530	532	NR	660	270	NR	790	5	NR	920	0	NR
405	8	NR	535	540	NR	665	238	NR	795	4	NR	925	0	NR
410	11	NR	540	550	NR	670	208	NR	800	4	NR	930	0	NR
415	19	NR	545	558	NR	675	182	NR	805	3	NR	935	0	NR
420	34	NR	550	567	NR	680	157	NR	810	3	NR	940	0	NR
425	62	NR	555	579	NR	685	136	NR	815	2	NR	945	0	NR
430	113	NR	560	593	NR	690	117	NR	820	2	NR	950	0	NR
435	202	NR	565	607	NR	695	101	NR	825	2	NR	955	0	NR
440	361	NR	570	616	NR	700	86	NR	830	2	NR	960	0	NR
445	688	NR	575	627	NR	705	73	NR	835	1	NR	965	0	NR
450	992	NR	580	635	NR	710	63	NR	840	1	NR	970	0	NR
455	824	NR	585	641	NR	715	53	NR	845	1	NR	975	0	NR
460	538	NR	590	649	NR	720	46	NR	850	1	NR	980	0	NR
465	433	NR	595	651	NR	725	39	NR	855	1	NR	985	0	NR
470	331	NR	600	645	NR	730	33	NR	860	1	NR	990	0	NR
475	244	NR	605	638	NR	735	28	NR	865	1	NR	995	0	NR
480	228	NR	610	619	NR	740	24	NR	870	1	NR	1000	0	NR
485	242	NR	615	593	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP3-2511-615-14

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.86

λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)	λ (nm)	Power W [^] /nm	Lumens (ϕ /nm)
360	0	NR	490	271	NR	620	561	NR	750	17	NR	880	1	NR
365	0	NR	495	316	NR	625	527	NR	755	15	NR	885	1	NR
370	0	NR	500	373	NR	630	489	NR	760	13	NR	890	1	NR
375	0	NR	505	417	NR	635	450	NR	765	11	NR	895	0	NR
380	0	NR	510	458	NR	640	413	NR	770	9	NR	900	0	NR
385	0	NR	515	487	NR	645	375	NR	775	8	NR	905	0	NR
390	2	NR	520	509	NR	650	340	NR	780	7	NR	910	0	NR
395	4	NR	525	522	NR	655	304	NR	785	6	NR	915	0	NR
400	6	NR	530	532	NR	660	270	NR	790	5	NR	920	0	NR
405	8	NR	535	540	NR	665	238	NR	795	4	NR	925	0	NR
410	11	NR	540	550	NR	670	208	NR	800	4	NR	930	0	NR
415	19	NR	545	558	NR	675	182	NR	805	3	NR	935	0	NR
420	34	NR	550	567	NR	680	157	NR	810	3	NR	940	0	NR
425	62	NR	555	579	NR	685	136	NR	815	2	NR	945	0	NR
430	113	NR	560	593	NR	690	117	NR	820	2	NR	950	0	NR
435	202	NR	565	607	NR	695	101	NR	825	2	NR	955	0	NR
440	361	NR	570	616	NR	700	86	NR	830	2	NR	960	0	NR
445	688	NR	575	627	NR	705	73	NR	835	1	NR	965	0	NR
450	992	NR	580	635	NR	710	63	NR	840	1	NR	970	0	NR
455	824	NR	585	641	NR	715	53	NR	845	1	NR	975	0	NR
460	538	NR	590	649	NR	720	46	NR	850	1	NR	980	0	NR
465	433	NR	595	651	NR	725	39	NR	855	1	NR	985	0	NR
470	331	NR	600	645	NR	730	33	NR	860	1	NR	990	0	NR
475	244	NR	605	638	NR	735	28	NR	865	1	NR	995	0	NR
480	228	NR	610	619	NR	740	24	NR	870	1	NR	1000	0	NR
485	242	NR	615	593	NR	745	20	NR	875	1	NR			

REPORT NUMBER: SP3-2511-615-14

Melanopic Flux vs. Wavelength




Melanopic Lumens: NR

M/P: 3.9





λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	271	NR	620	561	NR	750	17	NR	880	1	NR
365	0	NR	495	316	NR	625	527	NR	755	15	NR	885	1	NR
370	0	NR	500	373	NR	630	489	NR	760	13	NR	890	1	NR
375	0	NR	505	417	NR	635	450	NR	765	11	NR	895	0	NR
380	0	NR	510	458	NR	640	413	NR	770	9	NR	900	0	NR
385	0	NR	515	487	NR	645	375	NR	775	8	NR	905	0	NR
390	2	NR	520	509	NR	650	340	NR	780	7	NR	910	0	NR
395	4	NR	525	522	NR	655	304	NR	785	6	NR	915	0	NR
400	6	NR	530	532	NR	660	270	NR	790	5	NR	920	0	NR
405	8	NR	535	540	NR	665	238	NR	795	4	NR	925	0	NR
410	11	NR	540	550	NR	670	208	NR	800	4	NR	930	0	NR
415	19	NR	545	558	NR	675	182	NR	805	3	NR	935	0	NR
420	34	NR	550	567	NR	680	157	NR	810	3	NR	940	0	NR
425	62	NR	555	579	NR	685	136	NR	815	2	NR	945	0	NR
430	113	NR	560	593	NR	690	117	NR	820	2	NR	950	0	NR
435	202	NR	565	607	NR	695	101	NR	825	2	NR	955	0	NR
440	361	NR	570	616	NR	700	86	NR	830	2	NR	960	0	NR
445	688	NR	575	627	NR	705	73	NR	835	1	NR	965	0	NR
450	992	NR	580	635	NR	710	63	NR	840	1	NR	970	0	NR
455	824	NR	585	641	NR	715	53	NR	845	1	NR	975	0	NR
460	538	NR	590	649	NR	720	46	NR	850	1	NR	980	0	NR
465	433	NR	595	651	NR	725	39	NR	855	1	NR	985	0	NR
470	331	NR	600	645	NR	730	33	NR	860	1	NR	990	0	NR
475	244	NR	605	638	NR	735	28	NR	865	1	NR	995	0	NR
480	228	NR	610	619	NR	740	24	NR	870	1	NR	1000	0	NR
485	242	NR	615	593	NR	745	20	NR	875	1	NR			

Summary

$R_f = 85$
 $R_g = 96.9$
 CIE $R_a = 85.1$
 $R_9 = 18.6$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 82	CES51 = 95	CES76 = 74
CES02 = 61	CES27 = 93	CES52 = 96	CES77 = 82
CES03 = 31	CES28 = 91	CES53 = 91	CES78 = 73
CES04 = 69	CES29 = 87	CES54 = 91	CES79 = 92
CES05 = 47	CES30 = 96	CES55 = 89	CES80 = 88
CES06 = 50	CES31 = 89	CES56 = 87	CES81 = 84
CES07 = 40	CES32 = 81	CES57 = 87	CES82 = 95
CES08 = 39	CES33 = 94	CES58 = 87	CES83 = 96
CES09 = 29	CES34 = 86	CES59 = 92	CES84 = 90
CES10 = 73	CES35 = 92	CES60 = 90	CES85 = 80
CES11 = 56	CES36 = 82	CES61 = 88	CES86 = 79
CES12 = 62	CES37 = 91	CES62 = 84	CES87 = 85
CES13 = 42	CES38 = 91	CES63 = 86	CES88 = 90
CES14 = 74	CES39 = 98	CES64 = 80	CES89 = 80
CES15 = 71	CES40 = 95	CES65 = 78	CES90 = 91
CES16 = 46	CES41 = 99	CES66 = 77	CES91 = 71
CES17 = 49	CES42 = 91	CES67 = 75	CES92 = 67
CES18 = 56	CES43 = 89	CES68 = 79	CES93 = 81
CES19 = 71	CES44 = 99	CES69 = 83	CES94 = 67
CES20 = 65	CES45 = 94	CES70 = 75	CES95 = 74
CES21 = 85	CES46 = 92	CES71 = 68	CES96 = 85
CES22 = 77	CES47 = 97	CES72 = 89	CES97 = 92
CES23 = 91	CES48 = 88	CES73 = 68	CES98 = 87
CES24 = 90	CES49 = 91	CES74 = 92	CES99 = 79
CES25 = 71	CES50 = 96	CES75 = 70	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)