

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P232777

Luminaire Tested: **CTN-10-3-D-E1-T5N-7050**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P232777  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1707-171-22)  
Test Lab: INNOVATION CENTER(G2)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: CTN-10-3-D-E1-T5N-7050  
Description: CELESTEON HIGH MAST LUMINAIRE  
(10) 70 CRI, 5000K LEDS AND TYPE V NARROW OPTICS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 35377 lumens  
Efficiency: N/A  
Efficacy: 166.9 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short - Full Cutoff  
BUG Rating: B5 - U0 - G3

Input Watts (W): 212  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT




REPORT NUMBER: P232777

CATALOG NUMBER: CTN-10-3-D-E1-T5N-7050

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 3.9 fc  
 Type V - Short - Full Cutoff

REPORT NUMBER: P232777

CATALOG NUMBER: CTN-10-3-D-E1-T5N-7050

## Luminous Intensity Polar Plot



REPORT NUMBER: P232777

CATALOG NUMBER: CTN-10-3-D-E1-T5N-7050


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 17688.5  | 0.0    | 17688.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 17688.5  | 0.0    | 17688.5 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 35377.0  | 0.0    | 35377.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 232.7   | 0.7       |
| 10°-20°   | 762.3   | 2.2       |
| 20°-30°   | 1626.5  | 4.6       |
| 30°-40°   | 3542.8  | 10.0      |
| 40°-50°   | 6851.1  | 19.4      |
| 50°-60°   | 10879.8 | 30.8      |
| 60°-70°   | 9811.2  | 27.7      |
| 70°-80°   | 1535.7  | 4.3       |
| 80°-90°   | 134.9   | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 35377.0 | 100.0     |
| 0°-180°   | 35377.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P232777


CATALOG NUMBER: CTN-10-3-D-E1-T5N-7050

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 1310.8  | 3.7       |                         |      |         |
| FM   | (30°-60°)   | 10636.8 | 30.1      |                         |      |         |
| FH   | (60°-80°)   | 5673.5  | 16.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 67.5    | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 1310.8  | 3.7       | B3/2500                 |      |         |
| BM   | (30°-60°)   | 10636.8 | 30.1      | B5                      |      |         |
| BH   | (60°-80°)   | 5673.5  | 16.0      | B5                      |      | G3/7500 |
| BVH  | (80°-90°)   | 67.5    | 0.2       |                         |      | G1/100  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B5-U0-G3**

Type V Short



REPORT NUMBER: P232777

CATALOG NUMBER: CTN-10-3-D-E1-T5N-7050

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  | 2381.4  |
| 2.5°  | 2397.8  | 2392.7  | 2396.8  | 2399.8  | 2364.0  | 2373.2  | 2372.2  | 2396.8  | 2391.6  | 2402.9  | 2409.1  |
| 5°    | 2414.2  | 2406.0  | 2411.1  | 2419.3  | 2385.5  | 2397.8  | 2397.8  | 2420.3  | 2412.1  | 2423.4  | 2434.7  |
| 7.5°  | 2443.9  | 2435.7  | 2441.9  | 2452.1  | 2420.3  | 2433.7  | 2434.7  | 2461.3  | 2450.1  | 2459.3  | 2476.7  |
| 10°   | 2493.1  | 2488.0  | 2490.0  | 2499.2  | 2469.5  | 2485.9  | 2485.9  | 2514.6  | 2502.3  | 2512.6  | 2534.1  |
| 12.5° | 2550.5  | 2548.4  | 2550.5  | 2562.8  | 2535.1  | 2551.5  | 2551.5  | 2579.2  | 2571.0  | 2583.3  | 2603.8  |
| 15°   | 2626.3  | 2624.3  | 2625.3  | 2641.7  | 2619.1  | 2634.5  | 2637.6  | 2666.3  | 2664.2  | 2677.5  | 2696.0  |
| 17.5° | 2733.9  | 2733.9  | 2732.9  | 2747.2  | 2732.9  | 2748.2  | 2754.4  | 2785.1  | 2797.4  | 2813.8  | 2825.1  |
| 20°   | 2897.8  | 2888.6  | 2883.5  | 2890.7  | 2879.4  | 2895.8  | 2906.0  | 2956.3  | 2976.7  | 3002.4  | 3011.6  |
| 22.5° | 3112.0  | 3099.7  | 3083.3  | 3076.1  | 3060.8  | 3082.3  | 3102.8  | 3174.5  | 3204.2  | 3246.2  | 3256.5  |
| 25°   | 3407.1  | 3386.6  | 3355.9  | 3327.2  | 3292.4  | 3323.1  | 3361.0  | 3459.4  | 3520.9  | 3576.2  | 3584.4  |
| 27.5° | 3810.8  | 3780.1  | 3733.0  | 3677.6  | 3616.2  | 3654.1  | 3709.4  | 3852.9  | 3936.9  | 4025.0  | 4038.3  |
| 30°   | 4331.4  | 4326.3  | 4252.5  | 4154.1  | 4072.1  | 4093.7  | 4162.3  | 4339.6  | 4472.8  | 4564.0  | 4589.6  |
| 32.5° | 5026.1  | 5021.0  | 4897.0  | 4731.0  | 4614.2  | 4628.6  | 4692.1  | 4888.8  | 5054.8  | 5203.4  | 5208.5  |
| 35°   | 5854.1  | 5837.7  | 5663.5  | 5434.0  | 5246.5  | 5230.1  | 5292.6  | 5488.3  | 5714.7  | 5887.9  | 5905.3  |
| 37.5° | 6799.9  | 6773.3  | 6572.4  | 6225.0  | 5935.0  | 5867.4  | 5911.5  | 6157.4  | 6419.7  | 6615.4  | 6634.9  |
| 40°   | 7726.2  | 7705.7  | 7482.3  | 7156.5  | 6732.3  | 6561.1  | 6564.2  | 6878.8  | 7166.7  | 7348.1  | 7388.1  |
| 42.5° | 8618.7  | 8635.1  | 8421.0  | 8089.0  | 7645.3  | 7339.9  | 7344.0  | 7649.4  | 7947.6  | 8136.1  | 8188.4  |
| 45°   | 9534.8  | 9520.5  | 9319.6  | 9034.8  | 8625.9  | 8287.8  | 8173.0  | 8478.3  | 8774.5  | 8929.2  | 8985.6  |
| 47.5° | 10284.9 | 10259.3 | 10124.0 | 9973.4  | 9670.1  | 9337.0  | 9135.2  | 9347.3  | 9551.2  | 9655.7  | 9713.1  |
| 50°   | 10938.6 | 10918.2 | 10904.8 | 10841.3 | 10773.7 | 10558.5 | 10226.5 | 10213.2 | 10257.2 | 10279.8 | 10332.0 |
| 52.5° | 11492.0 | 11491.0 | 11562.7 | 11718.4 | 11885.5 | 11960.3 | 11385.4 | 11013.4 | 10861.8 | 10750.1 | 10769.6 |
| 55°   | 11909.0 | 11903.9 | 12107.8 | 12524.9 | 13115.1 | 13453.3 | 12604.8 | 11706.1 | 11306.5 | 11090.3 | 11088.3 |
| 57.5° | 12123.2 | 12132.4 | 12546.4 | 13301.6 | 14396.0 | 14857.1 | 13777.1 | 12342.5 | 11658.0 | 11329.1 | 11325.0 |
| 60°   | 11557.6 | 11596.5 | 12408.1 | 13783.2 | 15528.3 | 16130.8 | 14737.2 | 12474.7 | 11276.8 | 10724.5 | 10710.1 |
| 61°   | 10944.8 | 11091.3 | 11858.8 | 13673.6 | 15886.9 | 16404.4 | 14783.3 | 12146.8 | 10715.3 | 10105.6 | 10092.2 |
| 62.5° | 9597.3  | 9734.6  | 10908.9 | 13400.0 | 15862.3 | 16117.5 | 14521.0 | 11557.6 | 9834.0  | 9154.6  | 9127.0  |
| 65°   | 6963.8  | 7125.7  | 8390.2  | 11872.1 | 14419.5 | 14267.9 | 13208.4 | 10205.0 | 8246.8  | 7482.3  | 7447.5  |
| 67.5° | 3501.4  | 3708.4  | 5127.6  | 8615.7  | 11715.4 | 12003.3 | 11276.8 | 8079.7  | 5844.9  | 4413.4  | 4409.3  |
| 70°   | 904.8   | 992.9   | 1848.6  | 4531.2  | 8448.6  | 9401.6  | 8598.2  | 4680.8  | 2272.8  | 1371.0  | 1286.0  |
| 72.5° | 253.1   | 265.4   | 502.1   | 1650.8  | 4804.8  | 6298.8  | 4661.3  | 1636.4  | 512.3   | 292.0   | 267.4   |
| 75°   | 178.3   | 181.4   | 199.8   | 418.1   | 1814.7  | 2939.9  | 1502.2  | 353.5   | 204.9   | 193.7   | 193.7   |
| 77.5° | 158.8   | 160.9   | 173.2   | 225.4   | 380.2   | 660.9   | 287.9   | 228.5   | 180.3   | 174.2   | 172.1   |
| 80°   | 168.1   | 170.1   | 177.3   | 218.3   | 223.4   | 237.7   | 199.8   | 197.8   | 179.3   | 183.4   | 181.4   |
| 82.5° | 180.3   | 184.4   | 193.7   | 223.4   | 191.6   | 192.6   | 164.0   | 162.9   | 158.8   | 180.3   | 181.4   |
| 85°   | 159.9   | 167.0   | 174.2   | 195.7   | 157.8   | 129.1   | 134.2   | 106.6   | 113.7   | 135.3   | 130.1   |
| 87.5° | 89.1    | 88.1    | 85.0    | 89.1    | 79.9    | 64.6    | 54.3    | 49.2    | 45.1    | 51.2    | 50.2    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-7

Luminaire Tested: CST-CA6-230-750-U-T4

Test Date: 04/22/2021




### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/22/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-750-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

### Spectral Parameters

|                           |        |           |      |      |       |
|---------------------------|--------|-----------|------|------|-------|
| CCT (K):                  | 4852   | CRI (Ra): | 74.1 |      |       |
| CIE u':                   | 0.2118 | R1:       | 71.0 | R9:  | -25.4 |
| CIE v':                   | 0.4888 | R2:       | 79.6 | R10: | 51.4  |
| Duv:                      | 0.0017 | R3:       | 85.8 | R11: | 70.1  |
| CIE x:                    | 0.3498 | R4:       | 73.5 | R12: | 42.9  |
| CIE y:                    | 0.3588 | R5:       | 71.4 | R13: | 72.5  |
| CIE z:                    | 0.2914 | R6:       | 71.2 | R14: | 92.1  |
| Peak Wavelength (nm):     | 449    | R7:       | 82.9 |      |       |
| Dominant Wavelength (nm): | 572    | R8:       | 57.2 |      |       |
| Purity:                   | 12.7   |           |      |      |       |
| Rf:                       | 75.2   |           |      |      |       |
| Rg:                       | 94.7   |           |      |      |       |



### Test Conditions


Stabilization Time: 72M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.4/13%  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2104-215-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2104-215-7

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 15077            | 0.0              | 490       | 146327           | 20.8             | 620       | 434415           | 113.0            | 750       | 22886            | 0.0              | 880       | 20960            | 0.0              |
| 365       | 12138            | 0.0              | 495       | 188585           | 34.2             | 625       | 400670           | 88.4             | 755       | 19692            | 0.0              | 885       | 20315            | 0.0              |
| 370       | 12993            | 0.0              | 500       | 245069           | 54.1             | 630       | 360611           | 65.3             | 760       | 18199            | 0.0              | 890       | 15211            | 0.0              |
| 375       | 14513            | 0.0              | 505       | 307682           | 86.1             | 635       | 326986           | 49.1             | 765       | 19191            | 0.0              | 895       | 15502            | 0.0              |
| 380       | 15679            | 0.0              | 510       | 367102           | 126.1            | 640       | 295583           | 35.3             | 770       | 16229            | 0.0              | 900       | 15935            | 0.0              |
| 385       | 14569            | 0.0              | 515       | 416068           | 172.4            | 645       | 264664           | 25.5             | 775       | 16351            | 0.0              | 905       | 15965            | 0.0              |
| 390       | 13091            | 0.0              | 520       | 457470           | 221.8            | 650       | 238441           | 17.4             | 780       | 14567            | 0.0              | 910       | 16119            | 0.0              |
| 395       | 10927            | 0.0              | 525       | 486980           | 261.4            | 655       | 210047           | 12.1             | 785       | 13349            | 0.0              | 915       | 13972            | 0.0              |
| 400       | 9655             | 0.0              | 530       | 511184           | 301.0            | 660       | 186019           | 7.8              | 790       | 12552            | 0.0              | 920       | 14830            | 0.0              |
| 405       | 10895            | 0.0              | 535       | 527191           | 326.9            | 665       | 164001           | 5.2              | 795       | 11517            | 0.0              | 925       | 13744            | 0.0              |
| 410       | 14929            | 0.0              | 540       | 540658           | 352.3            | 670       | 142007           | 3.1              | 800       | 13250            | 0.0              | 930       | 20340            | 0.0              |
| 415       | 25993            | 0.0              | 545       | 555639           | 369.8            | 675       | 123441           | 2.1              | 805       | 15135            | 0.0              | 935       | 13272            | 0.0              |
| 420       | 49620            | 0.1              | 550       | 572229           | 388.9            | 680       | 106894           | 1.2              | 810       | 9873             | 0.0              | 940       | 16357            | 0.0              |
| 425       | 95836            | 0.5              | 555       | 589788           | 402.8            | 685       | 94026            | 0.8              | 815       | 11566            | 0.0              | 945       | 19257            | 0.0              |
| 430       | 178101           | 1.4              | 560       | 608278           | 413.4            | 690       | 82099            | 0.5              | 820       | 11216            | 0.0              | 950       | 19804            | 0.0              |
| 435       | 300144           | 3.5              | 565       | 619317           | 411.8            | 695       | 70275            | 0.3              | 825       | 15165            | 0.0              | 955       | 14877            | 0.0              |
| 440       | 512674           | 8.1              | 570       | 627176           | 407.8            | 700       | 61784            | 0.2              | 830       | 14983            | 0.0              | 960       | 9882             | 0.0              |
| 445       | 857336           | 17.9             | 575       | 631114           | 392.7            | 705       | 55550            | 0.1              | 835       | 13993            | 0.0              | 965       | 11741            | 0.0              |
| 450       | 1021494          | 26.5             | 580       | 630436           | 374.6            | 710       | 50234            | 0.1              | 840       | 15281            | 0.0              | 970       | 11068            | 0.0              |
| 455       | 730207           | 24.4             | 585       | 625204           | 347.4            | 715       | 44909            | 0.0              | 845       | 15737            | 0.0              | 975       | 18108            | 0.0              |
| 460       | 467897           | 19.2             | 590       | 612752           | 316.8            | 720       | 41441            | 0.0              | 850       | 15148            | 0.0              | 980       | 17506            | 0.0              |
| 465       | 344659           | 17.8             | 595       | 589048           | 279.2            | 725       | 36834            | 0.0              | 855       | 17198            | 0.0              | 985       | 23821            | 0.0              |
| 470       | 230541           | 14.3             | 600       | 567479           | 244.6            | 730       | 32988            | 0.0              | 860       | 19169            | 0.0              | 990       | 25862            | 0.0              |
| 475       | 157156           | 12.3             | 605       | 542722           | 210.2            | 735       | 28984            | 0.0              | 865       | 18632            | 0.0              | 995       | 21133            | 0.0              |
| 480       | 134805           | 12.8             | 610       | 507118           | 174.2            | 740       | 26177            | 0.0              | 870       | 18831            | 0.0              | 1000      | 25640            | 0.0              |
| 485       | 132031           | 15.6             | 615       | 472188           | 142.5            | 745       | 22680            | 0.0              | 875       | 16978            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-7

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 66024.8

S/P: 1.78

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\Phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 15077                         | 0.0                            | 490               | 146327                        | 225.3                          | 620               | 434415                        | 5.4                            | 750               | 22886                         | 0.0                            | 880               | 20960                         | 0.0                            |
| 365               | 12138                         | 0.0                            | 495               | 188585                        | 304.9                          | 625               | 400670                        | 3.4                            | 755               | 19692                         | 0.0                            | 885               | 20315                         | 0.0                            |
| 370               | 12993                         | 0.0                            | 500               | 245069                        | 409.9                          | 630               | 360611                        | 2.0                            | 760               | 18199                         | 0.0                            | 890               | 15211                         | 0.0                            |
| 375               | 14513                         | 0.0                            | 505               | 307682                        | 523.1                          | 635               | 326986                        | 1.2                            | 765               | 19191                         | 0.0                            | 895               | 15502                         | 0.0                            |
| 380               | 15679                         | 0.0                            | 510               | 367102                        | 622.2                          | 640               | 295583                        | 0.8                            | 770               | 16229                         | 0.0                            | 900               | 15935                         | 0.0                            |
| 385               | 14569                         | 0.0                            | 515               | 416068                        | 689.6                          | 645               | 264664                        | 0.5                            | 775               | 16351                         | 0.0                            | 905               | 15965                         | 0.0                            |
| 390               | 13091                         | 0.0                            | 520               | 457470                        | 727.1                          | 650               | 238441                        | 0.3                            | 780               | 14567                         | 0.0                            | 910               | 16119                         | 0.0                            |
| 395               | 10927                         | 0.1                            | 525               | 486980                        | 728.5                          | 655               | 210047                        | 0.2                            | 785               | 13349                         | 0.0                            | 915               | 13972                         | 0.0                            |
| 400               | 9655                          | 0.2                            | 530               | 511184                        | 704.8                          | 660               | 186019                        | 0.1                            | 790               | 12552                         | 0.0                            | 920               | 14830                         | 0.0                            |
| 405               | 10895                         | 0.3                            | 535               | 527191                        | 656.9                          | 665               | 164001                        | 0.1                            | 795               | 11517                         | 0.0                            | 925               | 13744                         | 0.0                            |
| 410               | 14929                         | 0.9                            | 540               | 540658                        | 597.4                          | 670               | 142007                        | 0.0                            | 800               | 13250                         | 0.0                            | 930               | 20340                         | 0.0                            |
| 415               | 25993                         | 2.7                            | 545               | 555639                        | 532.7                          | 675               | 123441                        | 0.0                            | 805               | 15135                         | 0.0                            | 935               | 13272                         | 0.0                            |
| 420               | 49620                         | 8.2                            | 550               | 572229                        | 467.9                          | 680               | 106894                        | 0.0                            | 810               | 9873                          | 0.0                            | 940               | 16357                         | 0.0                            |
| 425               | 95836                         | 23.4                           | 555               | 589788                        | 403.1                          | 685               | 94026                         | 0.0                            | 815               | 11566                         | 0.0                            | 945               | 19257                         | 0.0                            |
| 430               | 178101                        | 60.6                           | 560               | 608278                        | 340.0                          | 690               | 82099                         | 0.0                            | 820               | 11216                         | 0.0                            | 950               | 19804                         | 0.0                            |
| 435               | 300144                        | 134.2                          | 565               | 619317                        | 277.8                          | 695               | 70275                         | 0.0                            | 825               | 15165                         | 0.0                            | 955               | 14877                         | 0.0                            |
| 440               | 512674                        | 286.5                          | 570               | 627176                        | 221.3                          | 700               | 61784                         | 0.0                            | 830               | 14983                         | 0.0                            | 960               | 9882                          | 0.0                            |
| 445               | 857336                        | 574.1                          | 575               | 631114                        | 171.9                          | 705               | 55550                         | 0.0                            | 835               | 13993                         | 0.0                            | 965               | 11741                         | 0.0                            |
| 450               | 1021494                       | 791.7                          | 580               | 630436                        | 129.9                          | 710               | 50234                         | 0.0                            | 840               | 15281                         | 0.0                            | 970               | 11068                         | 0.0                            |
| 455               | 730207                        | 638.1                          | 585               | 625204                        | 95.5                           | 715               | 44909                         | 0.0                            | 845               | 15737                         | 0.0                            | 975               | 18108                         | 0.0                            |
| 460               | 467897                        | 451.9                          | 590               | 612752                        | 68.2                           | 720               | 41441                         | 0.0                            | 850               | 15148                         | 0.0                            | 980               | 17506                         | 0.0                            |
| 465               | 344659                        | 364.0                          | 595               | 589048                        | 47.0                           | 725               | 36834                         | 0.0                            | 855               | 17198                         | 0.0                            | 985               | 23821                         | 0.0                            |
| 470               | 230541                        | 265.5                          | 600               | 567479                        | 32.0                           | 730               | 32988                         | 0.0                            | 860               | 19169                         | 0.0                            | 990               | 25862                         | 0.0                            |
| 475               | 157156                        | 196.5                          | 605               | 542722                        | 21.3                           | 735               | 28984                         | 0.0                            | 865               | 18632                         | 0.0                            | 995               | 21133                         | 0.0                            |
| 480               | 134805                        | 182.1                          | 610               | 507118                        | 13.7                           | 740               | 26177                         | 0.0                            | 870               | 18831                         | 0.0                            | 1000              | 25640                         | 0.0                            |
| 485               | 132031                        | 191.4                          | 615               | 472188                        | 8.7                            | 745               | 22680                         | 0.0                            | 875               | 16978                         | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2104-215-7

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 26696.3**      **M/P: 0.72**


| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 15077            | 0.0              | 490       | 146327           | 121.8            | 620       | 434415           | 0.3              | 750       | 22886            | 0.0              | 880       | 20960            | 0.0              |
| 365       | 12138            | 0.0              | 495       | 188585           | 155.7            | 625       | 400670           | 0.2              | 755       | 19692            | 0.0              | 885       | 20315            | 0.0              |
| 370       | 12993            | 0.0              | 500       | 245069           | 197.0            | 630       | 360611           | 0.1              | 760       | 18199            | 0.0              | 890       | 15211            | 0.0              |
| 375       | 14513            | 0.0              | 505       | 307682           | 236.1            | 635       | 326986           | 0.1              | 765       | 19191            | 0.0              | 895       | 15502            | 0.0              |
| 380       | 15679            | 0.0              | 510       | 367102           | 263.6            | 640       | 295583           | 0.0              | 770       | 16229            | 0.0              | 900       | 15935            | 0.0              |
| 385       | 14569            | 0.0              | 515       | 416068           | 271.9            | 645       | 264664           | 0.0              | 775       | 16351            | 0.0              | 905       | 15965            | 0.0              |
| 390       | 13091            | 0.0              | 520       | 457470           | 266.3            | 650       | 238441           | 0.0              | 780       | 14567            | 0.0              | 910       | 16119            | 0.0              |
| 395       | 10927            | 0.1              | 525       | 486980           | 247.0            | 655       | 210047           | 0.0              | 785       | 13349            | 0.0              | 915       | 13972            | 0.0              |
| 400       | 9655             | 0.1              | 530       | 511184           | 220.9            | 660       | 186019           | 0.0              | 790       | 12552            | 0.0              | 920       | 14830            | 0.0              |
| 405       | 10895            | 0.2              | 535       | 527191           | 189.7            | 665       | 164001           | 0.0              | 795       | 11517            | 0.0              | 925       | 13744            | 0.0              |
| 410       | 14929            | 0.6              | 540       | 540658           | 158.2            | 670       | 142007           | 0.0              | 800       | 13250            | 0.0              | 930       | 20340            | 0.0              |
| 415       | 25993            | 1.7              | 545       | 555639           | 129.1            | 675       | 123441           | 0.0              | 805       | 15135            | 0.0              | 935       | 13272            | 0.0              |
| 420       | 49620            | 5.7              | 550       | 572229           | 102.7            | 680       | 106894           | 0.0              | 810       | 9873             | 0.0              | 940       | 16357            | 0.0              |
| 425       | 95836            | 14.9             | 555       | 589788           | 79.5             | 685       | 94026            | 0.0              | 815       | 11566            | 0.0              | 945       | 19257            | 0.0              |
| 430       | 178101           | 37.6             | 560       | 608278           | 60.0             | 690       | 82099            | 0.0              | 820       | 11216            | 0.0              | 950       | 19804            | 0.0              |
| 435       | 300144           | 80.1             | 565       | 619317           | 43.5             | 695       | 70275            | 0.0              | 825       | 15165            | 0.0              | 955       | 14877            | 0.0              |
| 440       | 512674           | 171.3            | 570       | 627176           | 30.6             | 700       | 61784            | 0.0              | 830       | 14983            | 0.0              | 960       | 9882             | 0.0              |
| 445       | 857336           | 338.2            | 575       | 631114           | 21.0             | 705       | 55550            | 0.0              | 835       | 13993            | 0.0              | 965       | 11741            | 0.0              |
| 450       | 1021494          | 470.7            | 580       | 630436           | 14.1             | 710       | 50234            | 0.0              | 840       | 15281            | 0.0              | 970       | 11068            | 0.0              |
| 455       | 730207           | 382.6            | 585       | 625204           | 9.3              | 715       | 44909            | 0.0              | 845       | 15737            | 0.0              | 975       | 18108            | 0.0              |
| 460       | 467897           | 275.7            | 590       | 612752           | 6.0              | 720       | 41441            | 0.0              | 850       | 15148            | 0.0              | 980       | 17506            | 0.0              |
| 465       | 344659           | 225.2            | 595       | 589048           | 3.8              | 725       | 36834            | 0.0              | 855       | 17198            | 0.0              | 985       | 23821            | 0.0              |
| 470       | 230541           | 165.0            | 600       | 567479           | 2.4              | 730       | 32988            | 0.0              | 860       | 19169            | 0.0              | 990       | 25862            | 0.0              |
| 475       | 157156           | 120.0            | 605       | 542722           | 1.5              | 735       | 28984            | 0.0              | 865       | 18632            | 0.0              | 995       | 21133            | 0.0              |
| 480       | 134805           | 108.3            | 610       | 507118           | 0.9              | 740       | 26177            | 0.0              | 870       | 18831            | 0.0              | 1000      | 25640            | 0.0              |
| 485       | 132031           | 108.8            | 615       | 472188           | 0.6              | 745       | 22680            | 0.0              | 875       | 16978            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-7





TM-30-18

### Summary

$R_f = 75.2$   
 $R_g = 94.7$   
 CIE  $R_a = 74.1$   
 $R_g = -25.4$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 63 | CES51 = 90 | CES76 = 52 |
| CES02 = 60 | CES27 = 88 | CES52 = 90 | CES77 = 68 |
| CES03 = 30 | CES28 = 81 | CES53 = 81 | CES78 = 54 |
| CES04 = 69 | CES29 = 67 | CES54 = 86 | CES79 = 81 |
| CES05 = 46 | CES30 = 85 | CES55 = 84 | CES80 = 77 |
| CES06 = 50 | CES31 = 71 | CES56 = 76 | CES81 = 79 |
| CES07 = 39 | CES32 = 63 | CES57 = 75 | CES82 = 91 |
| CES08 = 38 | CES33 = 79 | CES58 = 76 | CES83 = 89 |
| CES09 = 29 | CES34 = 70 | CES59 = 87 | CES84 = 86 |
| CES10 = 73 | CES35 = 83 | CES60 = 89 | CES85 = 79 |
| CES11 = 56 | CES36 = 90 | CES61 = 83 | CES86 = 76 |
| CES12 = 62 | CES37 = 79 | CES62 = 85 | CES87 = 78 |
| CES13 = 42 | CES38 = 94 | CES63 = 76 | CES88 = 82 |
| CES14 = 74 | CES39 = 96 | CES64 = 67 | CES89 = 74 |
| CES15 = 70 | CES40 = 91 | CES65 = 64 | CES90 = 81 |
| CES16 = 46 | CES41 = 95 | CES66 = 61 | CES91 = 74 |
| CES17 = 49 | CES42 = 80 | CES67 = 58 | CES92 = 61 |
| CES18 = 55 | CES43 = 78 | CES68 = 66 | CES93 = 77 |
| CES19 = 71 | CES44 = 99 | CES69 = 74 | CES94 = 56 |
| CES20 = 64 | CES45 = 86 | CES70 = 58 | CES95 = 67 |
| CES21 = 85 | CES46 = 85 | CES71 = 51 | CES96 = 78 |
| CES22 = 77 | CES47 = 88 | CES72 = 83 | CES97 = 86 |
| CES23 = 91 | CES48 = 80 | CES73 = 48 | CES98 = 77 |
| CES24 = 90 | CES49 = 83 | CES74 = 92 | CES99 = 65 |
| CES25 = 71 | CES50 = 90 | CES75 = 52 |            |







Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)