

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510762

Luminaire Tested: **CTN-CA8-330-722-U-T5**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510762  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA8-330-722-U-T5  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (8) 2200K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 41154 lumens  
Efficiency: N/A  
Efficacy: 124.1 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G5

Input Watts (W): 331.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P510762

CATALOG NUMBER: CTN-CA8-330-722-U-T5

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 30 foot mounting height. Maximum calculated value = 2.7 fc

Type V - Short - N/A

REPORT NUMBER: P510762  
CATALOG NUMBER: CTN-CA8-330-722-U-T5

## Luminous Intensity Polar Plot



REPORT NUMBER: P510762

CATALOG NUMBER: CTN-CA8-330-722-U-T5


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 20577.0  | 0.0    | 20577.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 20577.0  | 0.0    | 20577.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 41154.0  | 0.0    | 41154.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 228.6   | 0.6       |
| 10°-20°   | 744.6   | 1.8       |
| 20°-30°   | 1474.0  | 3.6       |
| 30°-40°   | 2549.9  | 6.2       |
| 40°-50°   | 4242.6  | 10.3      |
| 50°-60°   | 7399.7  | 18.0      |
| 60°-70°   | 12249.9 | 29.8      |
| 70°-80°   | 10266.3 | 24.9      |
| 80°-90°   | 1998.5  | 4.9       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 41154.0 | 100.0     |
| 0°-180°   | 41154.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P510762


CATALOG NUMBER: CTN-CA8-330-722-U-T5

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 1223.6  | 3.0       |                         |      |          |
| FM   | (30°-60°)   | 7096.1  | 17.2      |                         |      |          |
| FH   | (60°-80°)   | 11258.1 | 27.4      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 999.3   | 2.4       |                         |      | G5       |
| BL   | (0°-30°)    | 1223.6  | 3.0       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 7096.1  | 17.2      | B4/8500                 |      |          |
| BH   | (60°-80°)   | 11258.1 | 27.4      | B5                      |      | G4/12000 |
| BVH  | (80°-90°)   | 999.3   | 2.4       |                         |      | G5       |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B5-U0-G5**

Type V Short





REPORT NUMBER: P510762

CATALOG NUMBER: CTN-CA8-330-722-U-T5

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  | 2352.1  |
| 2.5°  | 2366.8  | 2359.4  | 2357.0  | 2354.5  | 2356.2  | 2355.3  | 2359.4  | 2361.0  | 2362.7  | 2370.0  | 2365.9  |
| 5°    | 2381.4  | 2375.7  | 2374.9  | 2371.6  | 2370.8  | 2370.8  | 2376.5  | 2377.3  | 2378.2  | 2383.1  | 2378.2  |
| 7.5°  | 2408.3  | 2402.6  | 2401.0  | 2399.4  | 2398.5  | 2395.3  | 2399.4  | 2397.7  | 2399.4  | 2401.8  | 2396.1  |
| 10°   | 2450.7  | 2444.2  | 2442.5  | 2438.5  | 2440.9  | 2436.0  | 2439.3  | 2435.2  | 2427.9  | 2429.5  | 2421.4  |
| 12.5° | 2508.6  | 2502.9  | 2505.3  | 2504.5  | 2514.3  | 2511.8  | 2505.3  | 2497.2  | 2484.9  | 2476.8  | 2467.8  |
| 15°   | 2594.1  | 2585.2  | 2591.7  | 2598.2  | 2608.0  | 2612.1  | 2607.2  | 2585.2  | 2567.2  | 2554.2  | 2546.9  |
| 17.5° | 2698.5  | 2683.8  | 2696.8  | 2709.9  | 2731.1  | 2735.1  | 2717.2  | 2690.3  | 2670.7  | 2665.0  | 2652.8  |
| 20°   | 2819.9  | 2817.4  | 2818.3  | 2839.5  | 2872.1  | 2877.8  | 2854.1  | 2822.3  | 2802.8  | 2803.6  | 2789.7  |
| 22.5° | 2966.6  | 2953.5  | 2957.6  | 2978.8  | 3025.3  | 3040.8  | 3001.6  | 2966.6  | 2954.4  | 2957.6  | 2956.0  |
| 25°   | 3134.5  | 3122.3  | 3116.5  | 3126.3  | 3186.6  | 3213.5  | 3176.0  | 3135.3  | 3129.6  | 3136.9  | 3125.5  |
| 27.5° | 3318.7  | 3307.3  | 3300.7  | 3305.6  | 3352.9  | 3403.4  | 3361.9  | 3327.6  | 3326.8  | 3337.4  | 3330.9  |
| 30°   | 3528.1  | 3511.0  | 3503.7  | 3509.4  | 3542.0  | 3590.9  | 3557.5  | 3537.1  | 3554.2  | 3561.5  | 3559.1  |
| 32.5° | 3740.0  | 3731.9  | 3729.4  | 3727.8  | 3767.7  | 3795.4  | 3779.1  | 3783.2  | 3797.1  | 3830.5  | 3819.9  |
| 35°   | 3981.3  | 3957.6  | 3964.1  | 3969.0  | 4021.2  | 4023.6  | 4025.3  | 4032.6  | 4069.3  | 4116.6  | 4088.8  |
| 37.5° | 4232.3  | 4226.6  | 4230.7  | 4216.8  | 4255.1  | 4270.6  | 4293.4  | 4317.9  | 4375.7  | 4430.3  | 4418.9  |
| 40°   | 4542.8  | 4532.2  | 4536.3  | 4520.0  | 4538.7  | 4550.9  | 4597.4  | 4650.4  | 4724.5  | 4783.2  | 4756.3  |
| 42.5° | 4954.4  | 4927.5  | 4927.5  | 4932.4  | 4971.5  | 4958.4  | 5057.9  | 5072.5  | 5164.6  | 5214.4  | 5198.9  |
| 45°   | 5438.5  | 5428.7  | 5377.4  | 5291.0  | 5242.1  | 5241.2  | 5321.1  | 5440.1  | 5592.5  | 5696.0  | 5695.2  |
| 47.5° | 6053.8  | 6023.6  | 5900.6  | 5692.8  | 5568.9  | 5538.7  | 5622.7  | 5854.1  | 6134.5  | 6295.9  | 6293.4  |
| 50°   | 6860.6  | 6822.3  | 6635.7  | 6313.0  | 6071.7  | 5997.6  | 6132.0  | 6432.0  | 6809.3  | 7024.5  | 7042.4  |
| 52.5° | 7763.7  | 7766.9  | 7555.8  | 7067.7  | 6710.7  | 6577.0  | 6719.7  | 7148.3  | 7618.6  | 7913.6  | 7948.7  |
| 55°   | 8812.6  | 8787.3  | 8587.6  | 8034.2  | 7542.8  | 7255.9  | 7471.9  | 8039.9  | 8580.3  | 8805.2  | 8867.2  |
| 57.5° | 9904.7  | 9806.0  | 9652.8  | 9135.3  | 8560.7  | 8194.0  | 8453.2  | 9009.0  | 9526.5  | 9813.4  | 9803.6  |
| 60°   | 10872.9 | 10807.7 | 10719.7 | 10307.3 | 9866.4  | 9447.4  | 9647.1  | 10117.4 | 10560.7 | 10734.3 | 10741.7 |
| 62.5° | 11930.7 | 11876.1 | 11797.1 | 11571.3 | 11328.5 | 11172.8 | 10991.9 | 11209.5 | 11555.8 | 11745.7 | 11807.7 |
| 65°   | 12969.1 | 12949.5 | 12995.1 | 12960.9 | 13063.6 | 13040.8 | 12607.2 | 12470.3 | 12476.0 | 12422.2 | 12394.5 |
| 67.5° | 12907.9 | 12900.6 | 13169.5 | 13705.8 | 14729.4 | 15019.6 | 13907.1 | 12668.3 | 12110.0 | 11968.2 | 11947.9 |
| 70°   | 11966.6 | 12045.7 | 12543.6 | 13593.3 | 15461.3 | 15795.5 | 14272.2 | 12023.7 | 11309.7 | 10954.4 | 10866.4 |
| 72.5° | 10155.7 | 10310.5 | 11074.2 | 12620.2 | 14853.3 | 14929.9 | 13354.5 | 11053.8 | 10002.5 | 9578.7  | 9515.9  |
| 75°   | 7836.2  | 7855.8  | 8637.3  | 10602.3 | 13255.9 | 13352.1 | 11912.8 | 9271.4  | 8237.2  | 7709.9  | 7693.6  |
| 77.5° | 4772.6  | 5050.5  | 6190.7  | 7949.5  | 10537.9 | 11038.3 | 9963.3  | 7384.7  | 6154.9  | 5687.9  | 5427.1  |
| 80°   | 2341.5  | 2468.6  | 3290.1  | 5026.1  | 7532.2  | 8370.8  | 7393.7  | 5107.6  | 3796.3  | 3203.8  | 3138.6  |
| 82.5° | 1066.0  | 1133.7  | 1556.6  | 2627.6  | 4545.2  | 5584.4  | 4563.2  | 2925.0  | 2026.9  | 1585.2  | 1570.5  |
| 85°   | 414.0   | 411.6   | 630.0   | 1102.7  | 2176.0  | 3092.1  | 2310.5  | 1395.3  | 927.5   | 689.5   | 650.4   |
| 87.5° | 120.6   | 128.8   | 185.0   | 361.9   | 644.7   | 868.8   | 712.3   | 482.5   | 285.2   | 183.4   | 168.7   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-4

Luminaire Tested: CST-CA10-630-722-U-T3

Test Date: 04/20/2021





REPORT NUMBER: SP1-2104-215-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-4

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-4

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 19.5             | 620       | 2038916          | 530.6            | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 31.6             | 625       | 1946743          | 429.5            | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 51.3             | 630       | 1814508          | 328.4            | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 84.9             | 635       | 1681061          | 252.6            | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 128.6            | 640       | 1557170          | 186.1            | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 184.5            | 645       | 1430182          | 137.7            | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.0              | 520       | 510296           | 247.5            | 650       | 1300435          | 95.0             | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.0              | 525       | 566771           | 304.3            | 655       | 1165554          | 66.9             | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.0              | 530       | 617892           | 363.8            | 660       | 1044122          | 43.5             | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.0              | 535       | 664903           | 412.3            | 665       | 932131           | 29.6             | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.0              | 540       | 711603           | 463.7            | 670       | 808971           | 17.7             | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 0.1              | 545       | 768835           | 511.7            | 675       | 701208           | 11.7             | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 0.1              | 550       | 841179           | 571.6            | 680       | 610741           | 7.1              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 0.4              | 555       | 932641           | 637.0            | 685       | 533825           | 4.6              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 0.9              | 560       | 1040487          | 707.1            | 690       | 459427           | 2.6              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 2.0              | 565       | 1164360          | 774.2            | 695       | 399973           | 1.7              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 3.6              | 570       | 1307677          | 850.3            | 700       | 347460           | 1.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 6.6              | 575       | 1470810          | 915.2            | 705       | 302187           | 0.6              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 10.6             | 580       | 1637734          | 973.2            | 710       | 262909           | 0.4              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 12.8             | 585       | 1807622          | 1004.4           | 715       | 236689           | 0.3              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 11.0             | 590       | 1958195          | 1012.4           | 720       | 209675           | 0.1              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 10.5             | 595       | 2055425          | 974.3            | 725       | 184999           | 0.1              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 10.2             | 600       | 2141598          | 923.0            | 730       | 160261           | 0.1              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 10.1             | 605       | 2185430          | 846.3            | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 11.0             | 610       | 2170089          | 745.5            | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 14.3             | 615       | 2123505          | 641.1            | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-4

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 72942.9

S/P: 0.88

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 211.1            | 620       | 2038916          | 25.5             | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 281.7            | 625       | 1946743          | 16.4             | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 389.3            | 630       | 1814508          | 10.3             | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 516.0            | 635       | 1681061          | 6.4              | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 634.7            | 640       | 1557170          | 4.0              | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.1              | 515       | 445274           | 738.0            | 645       | 1430182          | 2.4              | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.1              | 520       | 510296           | 811.1            | 650       | 1300435          | 1.5              | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.2              | 525       | 566771           | 847.9            | 655       | 1165554          | 0.9              | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.3              | 530       | 617892           | 851.9            | 660       | 1044122          | 0.6              | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.5              | 535       | 664903           | 828.5            | 665       | 932131           | 0.3              | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 1.2              | 540       | 711603           | 786.3            | 670       | 808971           | 0.2              | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 3.0              | 545       | 768835           | 737.2            | 675       | 701208           | 0.1              | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 7.6              | 550       | 841179           | 687.8            | 680       | 610741           | 0.1              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 18.7             | 555       | 932641           | 637.4            | 685       | 533825           | 0.0              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 40.1             | 560       | 1040487          | 581.6            | 690       | 459427           | 0.0              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 74.6             | 565       | 1164360          | 522.4            | 695       | 399973           | 0.0              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 127.3            | 570       | 1307677          | 461.5            | 700       | 347460           | 0.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 211.2            | 575       | 1470810          | 400.6            | 705       | 302187           | 0.0              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 317.4            | 580       | 1637734          | 337.4            | 710       | 262909           | 0.0              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 333.0            | 585       | 1807622          | 276.3            | 715       | 236689           | 0.0              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 260.0            | 590       | 1958195          | 218.0            | 720       | 209675           | 0.0              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 214.9            | 595       | 2055425          | 163.9            | 725       | 184999           | 0.0              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 188.8            | 600       | 2141598          | 120.7            | 730       | 160261           | 0.0              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 161.5            | 605       | 2185430          | 85.9             | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 155.9            | 610       | 2170089          | 58.8             | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 175.3            | 615       | 2123505          | 39.3             | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-4

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: 23955.7      M/P: 0.29**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 23398            | 0.0              | 490       | 137099           | 114.1            | 620       | 2038916          | 1.6              | 750       | 99721            | 0.0              | 880       | 32326            | 0.0              |
| 365       | 18626            | 0.0              | 495       | 174286           | 143.9            | 625       | 1946743          | 1.0              | 755       | 91432            | 0.0              | 885       | 29783            | 0.0              |
| 370       | 21702            | 0.0              | 500       | 232711           | 187.1            | 630       | 1814508          | 0.6              | 760       | 83300            | 0.0              | 890       | 12135            | 0.0              |
| 375       | 22606            | 0.0              | 505       | 303528           | 232.9            | 635       | 1681061          | 0.4              | 765       | 72172            | 0.0              | 895       | 22953            | 0.0              |
| 380       | 25296            | 0.0              | 510       | 374456           | 268.9            | 640       | 1557170          | 0.2              | 770       | 65008            | 0.0              | 900       | 27214            | 0.0              |
| 385       | 27032            | 0.0              | 515       | 445274           | 290.9            | 645       | 1430182          | 0.2              | 775       | 56809            | 0.0              | 905       | 17038            | 0.0              |
| 390       | 22156            | 0.1              | 520       | 510296           | 297.1            | 650       | 1300435          | 0.1              | 780       | 49368            | 0.0              | 910       | 6896             | 0.0              |
| 395       | 20190            | 0.1              | 525       | 566771           | 287.4            | 655       | 1165554          | 0.1              | 785       | 51733            | 0.0              | 915       | 17142            | 0.0              |
| 400       | 18423            | 0.2              | 530       | 617892           | 267.0            | 660       | 1044122          | 0.0              | 790       | 41796            | 0.0              | 920       | 7675             | 0.0              |
| 405       | 16139            | 0.3              | 535       | 664903           | 239.3            | 665       | 932131           | 0.0              | 795       | 42601            | 0.0              | 925       | 21587            | 0.0              |
| 410       | 19812            | 0.8              | 540       | 711603           | 208.3            | 670       | 808971           | 0.0              | 800       | 36382            | 0.0              | 930       | 32992            | 0.0              |
| 415       | 29121            | 1.9              | 545       | 768835           | 178.6            | 675       | 701208           | 0.0              | 805       | 41419            | 0.0              | 935       | 35464            | 0.0              |
| 420       | 46007            | 5.3              | 550       | 841179           | 151.0            | 680       | 610741           | 0.0              | 810       | 35865            | 0.0              | 940       | 34460            | 0.0              |
| 425       | 76329            | 11.9             | 555       | 932641           | 125.8            | 685       | 533825           | 0.0              | 815       | 39722            | 0.0              | 945       | 46305            | 0.0              |
| 430       | 117696           | 24.9             | 560       | 1040487          | 102.6            | 690       | 459427           | 0.0              | 820       | 37236            | 0.0              | 950       | 38353            | 0.0              |
| 435       | 166890           | 44.5             | 565       | 1164360          | 81.7             | 695       | 399973           | 0.0              | 825       | 31566            | 0.0              | 955       | 30772            | 0.0              |
| 440       | 227762           | 76.1             | 570       | 1307677          | 63.9             | 700       | 347460           | 0.0              | 830       | 42647            | 0.0              | 960       | 32413            | 0.0              |
| 445       | 315427           | 124.4            | 575       | 1470810          | 49.0             | 705       | 302187           | 0.0              | 835       | 41433            | 0.0              | 965       | 35310            | 0.0              |
| 450       | 409560           | 188.7            | 580       | 1637734          | 36.6             | 710       | 262909           | 0.0              | 840       | 24213            | 0.0              | 970       | 28048            | 0.0              |
| 455       | 381103           | 199.7            | 585       | 1807622          | 26.9             | 715       | 236689           | 0.0              | 845       | 31358            | 0.0              | 975       | 26258            | 0.0              |
| 460       | 269221           | 158.6            | 590       | 1958195          | 19.2             | 720       | 209675           | 0.0              | 850       | 30957            | 0.0              | 980       | 31067            | 0.0              |
| 465       | 203513           | 133.0            | 595       | 2055425          | 13.2             | 725       | 184999           | 0.0              | 855       | 38865            | 0.0              | 985       | 40288            | 0.0              |
| 470       | 163989           | 117.4            | 600       | 2141598          | 9.0              | 730       | 160261           | 0.0              | 860       | 23238            | 0.0              | 990       | 29366            | 0.0              |
| 475       | 129159           | 98.6             | 605       | 2185430          | 6.0              | 735       | 140736           | 0.0              | 865       | 32686            | 0.0              | 995       | 54854            | 0.0              |
| 480       | 115440           | 92.8             | 610       | 2170089          | 3.9              | 740       | 125207           | 0.0              | 870       | 41855            | 0.0              | 1000      | 50994            | 0.0              |
| 485       | 120959           | 99.7             | 615       | 2123505          | 2.5              | 745       | 110736           | 0.0              | 875       | 35838            | 0.0              |           |                  |                  |


REPORT NUMBER: SP1-2104-215-4

TM-30-18





### Summary

$R_f = 75.7$   
 $R_g = 96.7$   
 CIE  $R_a = 72.8$   
 $R_g = -23.3$

### Spectral Power Distribution Comparison



### Color Vector Graphics




**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 68 | CES51 = 84 | CES76 = 70 |
| CES02 = 65 | CES27 = 88 | CES52 = 83 | CES77 = 79 |
| CES03 = 32 | CES28 = 89 | CES53 = 77 | CES78 = 73 |
| CES04 = 72 | CES29 = 66 | CES54 = 87 | CES79 = 85 |
| CES05 = 52 | CES30 = 75 | CES55 = 85 | CES80 = 84 |
| CES06 = 53 | CES31 = 69 | CES56 = 76 | CES81 = 57 |
| CES07 = 44 | CES32 = 65 | CES57 = 75 | CES82 = 93 |
| CES08 = 43 | CES33 = 73 | CES58 = 78 | CES83 = 87 |
| CES09 = 29 | CES34 = 81 | CES59 = 86 | CES84 = 92 |
| CES10 = 79 | CES35 = 91 | CES60 = 94 | CES85 = 72 |
| CES11 = 62 | CES36 = 96 | CES61 = 85 | CES86 = 52 |
| CES12 = 68 | CES37 = 90 | CES62 = 92 | CES87 = 78 |
| CES13 = 45 | CES38 = 81 | CES63 = 78 | CES88 = 77 |
| CES14 = 75 | CES39 = 94 | CES64 = 73 | CES89 = 62 |
| CES15 = 72 | CES40 = 90 | CES65 = 71 | CES90 = 77 |
| CES16 = 49 | CES41 = 86 | CES66 = 71 | CES91 = 91 |
| CES17 = 51 | CES42 = 87 | CES67 = 69 | CES92 = 60 |
| CES18 = 57 | CES43 = 74 | CES68 = 74 | CES93 = 74 |
| CES19 = 74 | CES44 = 99 | CES69 = 85 | CES94 = 49 |
| CES20 = 69 | CES45 = 81 | CES70 = 70 | CES95 = 71 |
| CES21 = 89 | CES46 = 76 | CES71 = 72 | CES96 = 77 |
| CES22 = 81 | CES47 = 77 | CES72 = 89 | CES97 = 79 |
| CES23 = 92 | CES48 = 66 | CES73 = 64 | CES98 = 75 |
| CES24 = 92 | CES49 = 75 | CES74 = 87 | CES99 = 67 |
| CES25 = 74 | CES50 = 84 | CES75 = 75 |            |





### Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)