

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P510493

Luminaire Tested: **CTN-CA10-310-740-U-T5N**

Issue Date: 4/6/2021

**Test Information**

Test Method: LM-79-08  
Report Number: P510493  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2102-151-13)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/6/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: CTN-CA10-310-740-U-T5N  
Description: CELESTEON HIGH MAST LUMINAIRE  
Light Source: (10) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 51638 lumens  
Efficiency: N/A  
Efficacy: 165.3 lumens/watt  
Luminous Opening: Circular (Dia: 2.08' x H: 0')  
IES Classification: Type V - Short  
BUG Rating: B5 - U0 - G4


Input Watts (W): 312.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT



REPORT NUMBER: P510493  
 CATALOG NUMBER: CTN-CA10-310-740-U-T5N

## Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 30 foot mounting height. Maximum calculated value = 5.7 fc  
 Type V - Short - N/A

REPORT NUMBER: P510493  
CATALOG NUMBER: CTN-CA10-310-740-U-T5N

## Luminous Intensity Polar Plot



REPORT NUMBER: P510493

CATALOG NUMBER: CTN-CA10-310-740-U-T5N


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 25819.0  | 0.0    | 25819.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Street Side</b> | Lumens    | 25819.0  | 0.0    | 25819.0 |
|                    | % Fixture | 50.0     | 0.0    | 50.0    |
| <b>Total</b>       | Lumens    | 51638.0  | 0.0    | 51638.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 362.9   | 0.7       |
| 10°-20°   | 1182.9  | 2.3       |
| 20°-30°   | 2512.4  | 4.9       |
| 30°-40°   | 5327.2  | 10.3      |
| 40°-50°   | 10130.9 | 19.6      |
| 50°-60°   | 16072.2 | 31.1      |
| 60°-70°   | 13585.2 | 26.3      |
| 70°-80°   | 2235.0  | 4.3       |
| 80°-90°   | 229.2   | 0.4       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 51638.0 | 100.0     |
| 0°-180°   | 51638.0 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P510493


CATALOG NUMBER: CTN-CA10-310-740-U-T5N

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 2029.1  | 3.9       |                         |      |          |
| FM   | (30°-60°)   | 15765.2 | 30.5      |                         |      |          |
| FH   | (60°-80°)   | 7910.1  | 15.3      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 114.6   | 0.2       |                         |      | G2/225   |
| BL   | (0°-30°)    | 2029.1  | 3.9       | B3/2500                 |      |          |
| BM   | (30°-60°)   | 15765.2 | 30.5      | B5                      |      |          |
| BH   | (60°-80°)   | 7910.1  | 15.3      | B5                      |      | G4/12000 |
| BVH  | (80°-90°)   | 114.6   | 0.2       |                         |      | G2/225   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B5-U0-G4**

Type V Short





REPORT NUMBER: P510493

CATALOG NUMBER: CTN-CA10-310-740-U-T5N

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 85°     | 90°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  | 3707.4  |
| 2.5°  | 3734.2  | 3724.9  | 3722.0  | 3718.1  | 3720.1  | 3721.1  | 3726.4  | 3726.9  | 3726.9  | 3731.8  | 3740.0  |
| 5°    | 3776.0  | 3763.9  | 3759.5  | 3754.6  | 3757.1  | 3759.5  | 3764.4  | 3767.3  | 3766.8  | 3769.7  | 3777.0  |
| 7.5°  | 3821.3  | 3816.9  | 3811.6  | 3808.7  | 3808.7  | 3815.5  | 3812.1  | 3817.4  | 3816.9  | 3820.3  | 3824.7  |
| 10°   | 3888.5  | 3878.7  | 3878.2  | 3872.9  | 3875.3  | 3881.2  | 3882.1  | 3881.2  | 3882.1  | 3884.1  | 3894.3  |
| 12.5° | 3973.6  | 3971.2  | 3972.7  | 3968.3  | 3966.8  | 3973.1  | 3974.6  | 3980.9  | 3982.9  | 3988.7  | 3995.0  |
| 15°   | 4110.9  | 4095.3  | 4093.4  | 4092.9  | 4095.8  | 4105.5  | 4108.4  | 4120.1  | 4125.5  | 4133.7  | 4147.9  |
| 17.5° | 4266.1  | 4271.5  | 4261.7  | 4260.8  | 4260.3  | 4268.1  | 4275.9  | 4301.6  | 4309.9  | 4328.9  | 4341.1  |
| 20°   | 4513.8  | 4504.1  | 4498.3  | 4474.9  | 4469.1  | 4482.7  | 4510.9  | 4545.0  | 4561.0  | 4591.2  | 4614.1  |
| 22.5° | 4844.8  | 4828.2  | 4788.3  | 4760.6  | 4748.9  | 4772.3  | 4802.9  | 4857.4  | 4922.1  | 4959.6  | 4969.8  |
| 25°   | 5323.2  | 5257.9  | 5208.3  | 5159.2  | 5141.6  | 5176.2  | 5225.8  | 5312.5  | 5393.7  | 5468.7  | 5503.2  |
| 27.5° | 5905.7  | 5864.3  | 5765.5  | 5688.2  | 5657.5  | 5686.7  | 5789.9  | 5912.0  | 6060.9  | 6138.8  | 6150.5  |
| 30°   | 6645.4  | 6624.0  | 6498.0  | 6352.9  | 6298.4  | 6349.1  | 6470.7  | 6637.2  | 6844.5  | 7004.6  | 7032.8  |
| 32.5° | 7561.3  | 7452.8  | 7277.6  | 7111.7  | 7053.3  | 7115.1  | 7237.2  | 7476.2  | 7755.5  | 7932.7  | 7993.0  |
| 35°   | 8611.6  | 8488.9  | 8225.6  | 7970.6  | 7895.2  | 7903.0  | 8098.6  | 8435.4  | 8817.4  | 9064.6  | 9132.3  |
| 37.5° | 9769.8  | 9644.8  | 9334.3  | 8938.6  | 8763.9  | 8777.0  | 9033.0  | 9471.0  | 9994.7  | 10264.3 | 10353.8 |
| 40°   | 11006.0 | 10876.5 | 10556.3 | 10110.5 | 9823.4  | 9765.0  | 10107.1 | 10640.5 | 11172.4 | 11497.5 | 11532.0 |
| 42.5° | 12214.4 | 12061.1 | 11803.6 | 11357.8 | 11096.0 | 10939.3 | 11352.5 | 11835.7 | 12372.0 | 12665.0 | 12687.9 |
| 45°   | 13293.8 | 13264.1 | 13057.3 | 12734.1 | 12518.5 | 12379.8 | 12674.7 | 13154.6 | 13529.3 | 13714.7 | 13782.4 |
| 47.5° | 14337.2 | 14318.7 | 14252.5 | 14139.6 | 14193.1 | 13962.5 | 14104.1 | 14321.6 | 14527.5 | 14663.7 | 14716.3 |
| 50°   | 15251.6 | 15271.1 | 15401.0 | 15593.3 | 15980.7 | 15747.1 | 15702.8 | 15468.7 | 15474.5 | 15485.2 | 15539.7 |
| 52.5° | 16006.9 | 16110.1 | 16437.2 | 17017.3 | 17853.8 | 17848.5 | 17178.4 | 16560.3 | 16280.9 | 16156.8 | 16168.0 |
| 55°   | 16665.4 | 16842.1 | 17382.3 | 18580.0 | 19777.2 | 19837.0 | 18925.5 | 17556.5 | 17032.8 | 16768.1 | 16802.6 |
| 57.5° | 17028.9 | 17298.1 | 18212.5 | 20030.7 | 21737.0 | 21809.0 | 20793.8 | 18659.8 | 17460.6 | 16790.5 | 16819.2 |
| 60°   | 15781.1 | 16234.2 | 17920.0 | 20966.6 | 23235.9 | 23269.0 | 21936.0 | 18746.4 | 16137.9 | 14951.9 | 14778.1 |
| 62.5° | 12914.2 | 13542.0 | 15920.3 | 20241.4 | 22541.4 | 22438.7 | 21221.1 | 17123.4 | 13256.8 | 11818.2 | 11672.2 |
| 65°   | 9700.7  | 10291.0 | 12781.3 | 17331.7 | 19778.6 | 19643.3 | 18403.3 | 13533.2 | 9719.2  | 8192.1  | 8012.5  |
| 67.5° | 5250.2  | 6141.7  | 8471.9  | 13239.3 | 15767.0 | 16225.9 | 14508.0 | 9432.6  | 5656.0  | 4100.7  | 3943.0  |
| 70°   | 1813.3  | 2343.3  | 4319.7  | 8310.8  | 11372.4 | 11832.8 | 9893.4  | 5058.9  | 2475.2  | 1547.6  | 1389.4  |
| 72.5° | 643.9   | 742.2   | 1624.0  | 4013.5  | 6474.6  | 7174.0  | 5338.2  | 2034.8  | 788.9   | 574.8   | 563.1   |
| 75°   | 454.5   | 469.1   | 577.2   | 1308.6  | 2803.2  | 3433.4  | 2104.8  | 675.5   | 492.0   | 459.9   | 457.0   |
| 77.5° | 405.9   | 414.2   | 467.7   | 532.9   | 856.5   | 1096.5  | 647.8   | 490.1   | 427.3   | 409.3   | 403.0   |
| 80°   | 385.9   | 392.3   | 407.8   | 437.0   | 485.7   | 505.2   | 437.0   | 419.0   | 388.8   | 381.1   | 378.6   |
| 82.5° | 337.3   | 335.8   | 340.2   | 352.3   | 374.2   | 379.1   | 350.9   | 328.5   | 329.0   | 319.7   | 315.4   |
| 85°   | 228.2   | 241.9   | 231.7   | 219.0   | 271.6   | 273.0   | 254.5   | 190.8   | 216.6   | 212.2   | 194.2   |
| 87.5° | 69.1    | 77.9    | 61.8    | 42.8    | 58.9    | 45.7    | 41.4    | 42.8    | 40.9    | 35.5    | 32.1    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

LM-79-08: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

STREETWORKS

Report Number: SP1-2104-215-1

Luminaire Tested: CST-CA6-230-740-U-T4

Test Date: 04/20/2021

### Test Information

Test Method: LM-79-08  
 Report Number: SP1-2104-215-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1  
 Measurement Geometry:  $4\pi$   
 Issue Date: 04/20/2021  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: STREETWORKS  
 Catalog Number: **CST-CA6-230-740-U-T4**  
 Description: STREETWORKS HIGH MAST LUMINAIRE

230W

### Spectral Parameters

|                           |         |           |      |      |       |
|---------------------------|---------|-----------|------|------|-------|
| CCT (K):                  | 3783    | CRI (Ra): | 75.1 |      |       |
| CIE u':                   | 0.2297  | R1:       | 72.8 | R9:  | -19.0 |
| CIE v':                   | 0.5046  | R2:       | 81.9 | R10: | 57.0  |
| Duv:                      | -0.0008 | R3:       | 89.0 | R11: | 70.7  |
| CIE x:                    | 0.3897  | R4:       | 74.1 | R12: | 48.2  |
| CIE y:                    | 0.3804  | R5:       | 72.3 | R13: | 74.4  |
| CIE z:                    | 0.2299  | R6:       | 74.5 | R14: | 93.7  |
| Peak Wavelength (nm):     | 450     | R7:       | 81.7 |      |       |
| Dominant Wavelength (nm): | 580     | R8:       | 54.6 |      |       |
| Purity:                   | 31.3    |           |      |      |       |
| Rf:                       | 76.5    |           |      |      |       |
| Rg:                       | 95.6    |           |      |      |       |



### Test Conditions

Stabilization Time: 47M  
 Operation Time: 12H  
 Room Temperature (°C) / RH%: 25.5/39%  
 Sphere Temperature (°C): 24.0

REPORT NUMBER: SP1-2104-215-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 1/31/2021        | 7/31/2021            |
| Power Meter                    | IN0071                | 12/1/2020        | 12/1/2021            |
| AC Power Source                | IN0063                | 12/1/2020        | 12/1/2021            |
| DC Power Source                | IN0208                | 12/1/2020        | 12/1/2021            |
| Sphere Thermometer             | IN0085                | 12/1/2020        | 12/1/2021            |
| Room Thermometer               | IN0046                | 12/1/2020        | 12/1/2021            |

REPORT NUMBER: SP1-2104-215-1

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 7-step quadrangle

REPORT NUMBER: SP1-2104-215-1

### Photopic Flux vs. Wavelength




#####

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 13329            | 0.0              | 490       | 105235           | 15.0             | 620       | 524343           | 136.4            | 750       | 24224            | 0.0              | 880       | 16135            | 0.0              |
| 365       | 11697            | 0.0              | 495       | 137678           | 25.0             | 625       | 488932           | 107.9            | 755       | 22376            | 0.0              | 885       | 16876            | 0.0              |
| 370       | 10917            | 0.0              | 500       | 186689           | 41.2             | 630       | 445400           | 80.6             | 760       | 20109            | 0.0              | 890       | 13554            | 0.0              |
| 375       | 12548            | 0.0              | 505       | 244611           | 68.4             | 635       | 403534           | 60.6             | 765       | 18097            | 0.0              | 895       | 11525            | 0.0              |
| 380       | 13932            | 0.0              | 510       | 298987           | 102.7            | 640       | 366414           | 43.8             | 770       | 17366            | 0.0              | 900       | 14656            | 0.0              |
| 385       | 13265            | 0.0              | 515       | 348170           | 144.2            | 645       | 331272           | 31.9             | 775       | 16226            | 0.0              | 905       | 11999            | 0.0              |
| 390       | 11808            | 0.0              | 520       | 390427           | 189.3            | 650       | 297360           | 21.7             | 780       | 14803            | 0.0              | 910       | 12965            | 0.0              |
| 395       | 10395            | 0.0              | 525       | 421211           | 226.1            | 655       | 263291           | 15.1             | 785       | 15199            | 0.0              | 915       | 15939            | 0.0              |
| 400       | 9348             | 0.0              | 530       | 446063           | 262.6            | 660       | 232931           | 9.7              | 790       | 12989            | 0.0              | 920       | 16238            | 0.0              |
| 405       | 9479             | 0.0              | 535       | 465110           | 288.4            | 665       | 204719           | 6.5              | 795       | 12106            | 0.0              | 925       | 14419            | 0.0              |
| 410       | 12414            | 0.0              | 540       | 479189           | 312.2            | 670       | 177096           | 3.9              | 800       | 12942            | 0.0              | 930       | 14788            | 0.0              |
| 415       | 21574            | 0.0              | 545       | 495864           | 330.0            | 675       | 153254           | 2.6              | 805       | 13253            | 0.0              | 935       | 18619            | 0.0              |
| 420       | 41448            | 0.1              | 550       | 516625           | 351.1            | 680       | 132874           | 1.5              | 810       | 12808            | 0.0              | 940       | 13995            | 0.0              |
| 425       | 79385            | 0.4              | 555       | 538555           | 367.8            | 685       | 115378           | 1.0              | 815       | 12903            | 0.0              | 945       | 18047            | 0.0              |
| 430       | 141845           | 1.1              | 560       | 562412           | 382.2            | 690       | 100157           | 0.6              | 820       | 12621            | 0.0              | 950       | 21418            | 0.0              |
| 435       | 231290           | 2.7              | 565       | 585835           | 389.5            | 695       | 85561            | 0.4              | 825       | 13903            | 0.0              | 955       | 23138            | 0.0              |
| 440       | 374482           | 5.9              | 570       | 608681           | 395.8            | 700       | 75396            | 0.2              | 830       | 11870            | 0.0              | 960       | 13665            | 0.0              |
| 445       | 596715           | 12.4             | 575       | 629563           | 391.7            | 705       | 65658            | 0.1              | 835       | 11069            | 0.0              | 965       | 14793            | 0.0              |
| 450       | 719656           | 18.7             | 580       | 646820           | 384.3            | 710       | 58172            | 0.1              | 840       | 15291            | 0.0              | 970       | 14396            | 0.0              |
| 455       | 530438           | 17.8             | 585       | 659231           | 366.3            | 715       | 52563            | 0.1              | 845       | 15125            | 0.0              | 975       | 11155            | 0.0              |
| 460       | 330446           | 13.5             | 590       | 665630           | 344.2            | 720       | 47085            | 0.0              | 850       | 15336            | 0.0              | 980       | 17987            | 0.0              |
| 465       | 241999           | 12.5             | 595       | 656228           | 311.1            | 725       | 41741            | 0.0              | 855       | 15791            | 0.0              | 985       | 16185            | 0.0              |
| 470       | 167096           | 10.4             | 600       | 646946           | 278.8            | 730       | 37415            | 0.0              | 860       | 14660            | 0.0              | 990       | 22120            | 0.0              |
| 475       | 113791           | 8.9              | 605       | 628643           | 243.4            | 735       | 32125            | 0.0              | 865       | 12528            | 0.0              | 995       | 11943            | 0.0              |
| 480       | 96126            | 9.1              | 610       | 599057           | 205.8            | 740       | 29322            | 0.0              | 870       | 14089            | 0.0              | 1000      | 16020            | 0.0              |
| 485       | 94467            | 11.2             | 615       | 565669           | 170.8            | 745       | 26862            | 0.0              | 875       | 11732            | 0.0              |           |                  |                  |

REPORT NUMBER: SP1-2104-215-1

### Scotopic Flux vs. Wavelength




Scotopic Lumens: 54268.8

S/P: 1.5

| $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>( $\mu\text{W/nm}$ ) | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 13329                         | 0.0                            | 490               | 105235                        | 162.0                          | 620               | 524343                        | 6.6                            | 750               | 24224                         | 0.0                            | 880               | 16135                         | 0.0                            |
| 365               | 11697                         | 0.0                            | 495               | 137678                        | 222.6                          | 625               | 488932                        | 4.1                            | 755               | 22376                         | 0.0                            | 885               | 16876                         | 0.0                            |
| 370               | 10917                         | 0.0                            | 500               | 186689                        | 312.3                          | 630               | 445400                        | 2.5                            | 760               | 20109                         | 0.0                            | 890               | 13554                         | 0.0                            |
| 375               | 12548                         | 0.0                            | 505               | 244611                        | 415.8                          | 635               | 403534                        | 1.5                            | 765               | 18097                         | 0.0                            | 895               | 11525                         | 0.0                            |
| 380               | 13932                         | 0.0                            | 510               | 298987                        | 506.8                          | 640               | 366414                        | 0.9                            | 770               | 17366                         | 0.0                            | 900               | 14656                         | 0.0                            |
| 385               | 13265                         | 0.0                            | 515               | 348170                        | 577.1                          | 645               | 331272                        | 0.6                            | 775               | 16226                         | 0.0                            | 905               | 11999                         | 0.0                            |
| 390               | 11808                         | 0.0                            | 520               | 390427                        | 620.6                          | 650               | 297360                        | 0.3                            | 780               | 14803                         | 0.0                            | 910               | 12965                         | 0.0                            |
| 395               | 10395                         | 0.1                            | 525               | 421211                        | 630.1                          | 655               | 263291                        | 0.2                            | 785               | 15199                         | 0.0                            | 915               | 15939                         | 0.0                            |
| 400               | 9348                          | 0.1                            | 530               | 446063                        | 615.0                          | 660               | 232931                        | 0.1                            | 790               | 12989                         | 0.0                            | 920               | 16238                         | 0.0                            |
| 405               | 9479                          | 0.3                            | 535               | 465110                        | 579.6                          | 665               | 204719                        | 0.1                            | 795               | 12106                         | 0.0                            | 925               | 14419                         | 0.0                            |
| 410               | 12414                         | 0.7                            | 540               | 479189                        | 529.5                          | 670               | 177096                        | 0.0                            | 800               | 12942                         | 0.0                            | 930               | 14788                         | 0.0                            |
| 415               | 21574                         | 2.2                            | 545               | 495864                        | 475.4                          | 675               | 153254                        | 0.0                            | 805               | 13253                         | 0.0                            | 935               | 18619                         | 0.0                            |
| 420               | 41448                         | 6.8                            | 550               | 516625                        | 422.4                          | 680               | 132874                        | 0.0                            | 810               | 12808                         | 0.0                            | 940               | 13995                         | 0.0                            |
| 425               | 79385                         | 19.4                           | 555               | 538555                        | 368.0                          | 685               | 115378                        | 0.0                            | 815               | 12903                         | 0.0                            | 945               | 18047                         | 0.0                            |
| 430               | 141845                        | 48.3                           | 560               | 562412                        | 314.4                          | 690               | 100157                        | 0.0                            | 820               | 12621                         | 0.0                            | 950               | 21418                         | 0.0                            |
| 435               | 231290                        | 103.4                          | 565               | 585835                        | 262.8                          | 695               | 85561                         | 0.0                            | 825               | 13903                         | 0.0                            | 955               | 23138                         | 0.0                            |
| 440               | 374482                        | 209.3                          | 570               | 608681                        | 214.8                          | 700               | 75396                         | 0.0                            | 830               | 11870                         | 0.0                            | 960               | 13665                         | 0.0                            |
| 445               | 596715                        | 399.6                          | 575               | 629563                        | 171.5                          | 705               | 65658                         | 0.0                            | 835               | 11069                         | 0.0                            | 965               | 14793                         | 0.0                            |
| 450               | 719656                        | 557.8                          | 580               | 646820                        | 133.3                          | 710               | 58172                         | 0.0                            | 840               | 15291                         | 0.0                            | 970               | 14396                         | 0.0                            |
| 455               | 530438                        | 463.5                          | 585               | 659231                        | 100.8                          | 715               | 52563                         | 0.0                            | 845               | 15125                         | 0.0                            | 975               | 11155                         | 0.0                            |
| 460               | 330446                        | 319.2                          | 590               | 665630                        | 74.1                           | 720               | 47085                         | 0.0                            | 850               | 15336                         | 0.0                            | 980               | 17987                         | 0.0                            |
| 465               | 241999                        | 255.6                          | 595               | 656228                        | 52.3                           | 725               | 41741                         | 0.0                            | 855               | 15791                         | 0.0                            | 985               | 16185                         | 0.0                            |
| 470               | 167096                        | 192.4                          | 600               | 646946                        | 36.5                           | 730               | 37415                         | 0.0                            | 860               | 14660                         | 0.0                            | 990               | 22120                         | 0.0                            |
| 475               | 113791                        | 142.3                          | 605               | 628643                        | 24.7                           | 735               | 32125                         | 0.0                            | 865               | 12528                         | 0.0                            | 995               | 11943                         | 0.0                            |
| 480               | 96126                         | 129.8                          | 610               | 599057                        | 16.2                           | 740               | 29322                         | 0.0                            | 870               | 14089                         | 0.0                            | 1000              | 16020                         | 0.0                            |
| 485               | 94467                         | 136.9                          | 615               | 565669                        | 10.5                           | 745               | 26862                         | 0.0                            | 875               | 11732                         | 0.0                            |                   |                               |                                |

REPORT NUMBER: SP1-2104-215-1

### Melanopic Flux vs. Wavelength



**Melanopic Lumens: 20938.3**      **M/P: 0.58**

| λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>(μW/nm) | Lumens<br>(Φ/nm) |
|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|-----------|------------------|------------------|
| 360       | 13329            | 0.0              | 490       | 105235           | 87.6             | 620       | 524343           | 0.4              | 750       | 24224            | 0.0              | 880       | 16135            | 0.0              |
| 365       | 11697            | 0.0              | 495       | 137678           | 113.7            | 625       | 488932           | 0.3              | 755       | 22376            | 0.0              | 885       | 16876            | 0.0              |
| 370       | 10917            | 0.0              | 500       | 186689           | 150.1            | 630       | 445400           | 0.2              | 760       | 20109            | 0.0              | 890       | 13554            | 0.0              |
| 375       | 12548            | 0.0              | 505       | 244611           | 187.7            | 635       | 403534           | 0.1              | 765       | 18097            | 0.0              | 895       | 11525            | 0.0              |
| 380       | 13932            | 0.0              | 510       | 298987           | 214.7            | 640       | 366414           | 0.1              | 770       | 17366            | 0.0              | 900       | 14656            | 0.0              |
| 385       | 13265            | 0.0              | 515       | 348170           | 227.5            | 645       | 331272           | 0.0              | 775       | 16226            | 0.0              | 905       | 11999            | 0.0              |
| 390       | 11808            | 0.0              | 520       | 390427           | 227.3            | 650       | 297360           | 0.0              | 780       | 14803            | 0.0              | 910       | 12965            | 0.0              |
| 395       | 10395            | 0.1              | 525       | 421211           | 213.6            | 655       | 263291           | 0.0              | 785       | 15199            | 0.0              | 915       | 15939            | 0.0              |
| 400       | 9348             | 0.1              | 530       | 446063           | 192.8            | 660       | 232931           | 0.0              | 790       | 12989            | 0.0              | 920       | 16238            | 0.0              |
| 405       | 9479             | 0.2              | 535       | 465110           | 167.4            | 665       | 204719           | 0.0              | 795       | 12106            | 0.0              | 925       | 14419            | 0.0              |
| 410       | 12414            | 0.5              | 540       | 479189           | 140.2            | 670       | 177096           | 0.0              | 800       | 12942            | 0.0              | 930       | 14788            | 0.0              |
| 415       | 21574            | 1.4              | 545       | 495864           | 115.2            | 675       | 153254           | 0.0              | 805       | 13253            | 0.0              | 935       | 18619            | 0.0              |
| 420       | 41448            | 4.7              | 550       | 516625           | 92.7             | 680       | 132874           | 0.0              | 810       | 12808            | 0.0              | 940       | 13995            | 0.0              |
| 425       | 79385            | 12.4             | 555       | 538555           | 72.6             | 685       | 115378           | 0.0              | 815       | 12903            | 0.0              | 945       | 18047            | 0.0              |
| 430       | 141845           | 30.0             | 560       | 562412           | 55.5             | 690       | 100157           | 0.0              | 820       | 12621            | 0.0              | 950       | 21418            | 0.0              |
| 435       | 231290           | 61.7             | 565       | 585835           | 41.1             | 695       | 85561            | 0.0              | 825       | 13903            | 0.0              | 955       | 23138            | 0.0              |
| 440       | 374482           | 125.1            | 570       | 608681           | 29.7             | 700       | 75396            | 0.0              | 830       | 11870            | 0.0              | 960       | 13665            | 0.0              |
| 445       | 596715           | 235.4            | 575       | 629563           | 21.0             | 705       | 65658            | 0.0              | 835       | 11069            | 0.0              | 965       | 14793            | 0.0              |
| 450       | 719656           | 331.6            | 580       | 646820           | 14.5             | 710       | 58172            | 0.0              | 840       | 15291            | 0.0              | 970       | 14396            | 0.0              |
| 455       | 530438           | 277.9            | 585       | 659231           | 9.8              | 715       | 52563            | 0.0              | 845       | 15125            | 0.0              | 975       | 11155            | 0.0              |
| 460       | 330446           | 194.7            | 590       | 665630           | 6.5              | 720       | 47085            | 0.0              | 850       | 15336            | 0.0              | 980       | 17987            | 0.0              |
| 465       | 241999           | 158.1            | 595       | 656228           | 4.2              | 725       | 41741            | 0.0              | 855       | 15791            | 0.0              | 985       | 16185            | 0.0              |
| 470       | 167096           | 119.6            | 600       | 646946           | 2.7              | 730       | 37415            | 0.0              | 860       | 14660            | 0.0              | 990       | 22120            | 0.0              |
| 475       | 113791           | 86.9             | 605       | 628643           | 1.7              | 735       | 32125            | 0.0              | 865       | 12528            | 0.0              | 995       | 11943            | 0.0              |
| 480       | 96126            | 77.2             | 610       | 599057           | 1.1              | 740       | 29322            | 0.0              | 870       | 14089            | 0.0              | 1000      | 16020            | 0.0              |
| 485       | 94467            | 77.9             | 615       | 565669           | 0.7              | 745       | 26862            | 0.0              | 875       | 11732            | 0.0              |           |                  |                  |

### Summary

$R_f = 76.5$   
 $R_g = 95.6$   
 CIE  $R_a = 75.1$   
 $R_g = -19.0$



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 66 | CES51 = 90 | CES76 = 56 |
| CES02 = 61 | CES27 = 89 | CES52 = 89 | CES77 = 73 |
| CES03 = 31 | CES28 = 83 | CES53 = 81 | CES78 = 58 |
| CES04 = 70 | CES29 = 69 | CES54 = 87 | CES79 = 84 |
| CES05 = 48 | CES30 = 84 | CES55 = 86 | CES80 = 81 |
| CES06 = 51 | CES31 = 72 | CES56 = 77 | CES81 = 79 |
| CES07 = 40 | CES32 = 64 | CES57 = 77 | CES82 = 92 |
| CES08 = 39 | CES33 = 79 | CES58 = 77 | CES83 = 90 |
| CES09 = 29 | CES34 = 73 | CES59 = 87 | CES84 = 87 |
| CES10 = 74 | CES35 = 85 | CES60 = 90 | CES85 = 78 |
| CES11 = 57 | CES36 = 91 | CES61 = 84 | CES86 = 73 |
| CES12 = 63 | CES37 = 81 | CES62 = 87 | CES87 = 79 |
| CES13 = 42 | CES38 = 94 | CES63 = 75 | CES88 = 83 |
| CES14 = 74 | CES39 = 96 | CES64 = 69 | CES89 = 73 |
| CES15 = 71 | CES40 = 91 | CES65 = 66 | CES90 = 83 |
| CES16 = 47 | CES41 = 94 | CES66 = 63 | CES91 = 76 |
| CES17 = 49 | CES42 = 82 | CES67 = 60 | CES92 = 62 |
| CES18 = 56 | CES43 = 78 | CES68 = 68 | CES93 = 77 |
| CES19 = 72 | CES44 = 99 | CES69 = 76 | CES94 = 57 |
| CES20 = 65 | CES45 = 86 | CES70 = 60 | CES95 = 69 |
| CES21 = 86 | CES46 = 84 | CES71 = 54 | CES96 = 79 |
| CES22 = 78 | CES47 = 87 | CES72 = 85 | CES97 = 86 |
| CES23 = 92 | CES48 = 80 | CES73 = 52 | CES98 = 79 |
| CES24 = 91 | CES49 = 82 | CES74 = 94 | CES99 = 69 |
| CES25 = 72 | CES50 = 90 | CES75 = 56 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)