

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P531185

Luminaire Tested: **GALN-SA6C-727-U-5MQ-GRSBK**

Issue Date: 5/27/2021

Test Information

Test Method: LM-79-08
Report Number: P531185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-057-3)
Test Lab: INNOVATION CENTER
Issue Date: 5/27/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SA6C-727-U-5MQ-GRSBK
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(6) 70 CRI, 2700K, 1050mA LIGHTSQUARES WITH 16 LEDS EACH AND TYPE V
MEDIUM OPTICS WITH BLACK GLARE REDUCTION SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20925 lumens
Efficiency: N/A
Efficacy: 65.2 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type V - Short
BUG Rating: B4 - U0 - G1


Input Watts (W): 321
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P531185
 CATALOG NUMBER: GALN-SA6C-727-U-5MQ-GRSBK

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.9 fc
 Type V - Short - N/A

REPORT NUMBER: P531185
CATALOG NUMBER: GALN-SA6C-727-U-5MQ-GRSBK

Luminous Intensity Polar Plot



— Vertical Plane Through 35-Deg Lateral - - - Horizontal Cone Through 56-Deg Vertical

REPORT NUMBER: P531185
 CATALOG NUMBER: GALN-SA6C-727-U-5MQ-GRSBK

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10462.5	0.0	10462.5
	% Fixture	50.0	0.0	50.0
Street Side	Lumens	10462.5	0.0	10462.5
	% Fixture	50.0	0.0	50.0
Total	Lumens	20925.0	0.0	20925.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	344.6	1.6
10°-20°	1006.1	4.8
20°-30°	1821.8	8.7
30°-40°	3378.3	16.1
40°-50°	5545.3	26.5
50°-60°	7143.9	34.1
60°-70°	1574.4	7.5
70°-80°	91.3	0.4
80°-90°	19.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20925.0	100.0
0°-180°	20925.0	100.0

Coefficient of Utilization




REPORT NUMBER: P531185
 CATALOG NUMBER: GALN-SA6C-727-U-5MQ-GRSBK

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1586.2	7.6			
FM (30°-60°)	8033.8	38.4			
FH (60°-80°)	832.9	4.0			G1/1800
FVH (80°-90°)	9.6	0.0			G0/10
BL (0°-30°)	1586.2	7.6	B3/2500		
BM (30°-60°)	8033.8	38.4	B4/8500		
BH (60°-80°)	832.9	4.0	B2/1000		G1/1800
BVH (80°-90°)	9.6	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G1
 Type V Short





REPORT NUMBER: P531185

CATALOG NUMBER: GALN-SA6C-727-U-5MQ-GRSBK

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	85°	90°
0°	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5	3666.5
2.5°	3674.1	3674.1	3677.9	3681.7	3655.1	3643.8	3647.6	3640.0	3636.2	3647.6	3647.6
5°	3662.7	3662.7	3651.3	3655.1	3655.1	3621.0	3621.0	3628.6	3628.6	3605.8	3598.3
7.5°	3632.4	3624.8	3609.6	3628.6	3617.2	3617.2	3590.7	3571.7	3564.1	3579.3	3564.1
10°	3567.9	3571.7	3586.9	3594.5	3586.9	3609.6	3564.1	3537.6	3511.1	3499.7	3499.7
12.5°	3537.6	3560.3	3537.6	3556.6	3583.1	3564.1	3537.6	3518.6	3480.7	3465.6	3465.6
15°	3533.8	3549.0	3556.6	3583.1	3571.7	3579.3	3526.2	3503.5	3446.6	3420.1	3408.7
17.5°	3530.0	3549.0	3560.3	3609.6	3617.2	3621.0	3579.3	3511.1	3461.8	3435.2	3408.7
20°	3571.7	3579.3	3602.1	3651.3	3681.7	3734.8	3658.9	3586.9	3480.7	3450.4	3439.0
22.5°	3624.8	3662.7	3685.5	3738.6	3818.2	3863.7	3765.1	3674.1	3564.1	3526.2	3480.7
25°	3795.4	3787.8	3825.8	3935.7	4000.2	4034.3	3954.7	3822.0	3677.9	3632.4	3640.0
27.5°	4007.8	4015.3	4049.5	4170.8	4265.6	4318.7	4223.9	4049.5	3909.2	3833.3	3825.8
30°	4284.5	4277.0	4314.9	4477.9	4648.5	4728.2	4561.3	4356.6	4220.1	4121.5	4144.3
32.5°	4576.5	4580.3	4686.5	4834.3	5111.1	5266.6	4997.4	4747.1	4542.4	4474.1	4440.0
35°	5008.7	5027.7	5111.1	5338.6	5645.7	5846.7	5551.0	5251.4	5016.3	4891.2	4906.4
37.5°	5543.4	5524.4	5664.7	5911.2	6233.4	6381.3	6131.1	5789.8	5551.0	5467.5	5520.6
40°	6112.1	6131.1	6203.1	6426.8	6787.0	6885.6	6514.0	6328.2	6119.7	6078.0	6142.4
42.5°	6680.9	6669.5	6722.6	6923.5	7185.1	7116.9	6897.0	6787.0	6639.2	6555.7	6642.9
45°	7097.9	7079.0	7177.6	7314.1	7408.9	7279.9	7181.4	7143.4	7067.6	6976.6	7056.2
47.5°	7503.6	7488.5	7583.3	7621.2	7628.8	7458.1	7477.1	7545.4	7355.8	7166.2	7257.2
50°	7848.7	7822.1	7939.7	8023.1	8004.1	7731.1	7799.4	7731.1	7435.4	7211.7	7177.6
52.5°	8425.0	8436.4	8561.5	8713.2	8667.7	8440.2	8341.6	8030.7	7651.5	7450.6	7333.0
55°	8789.0	8732.1	8948.3	9429.8	9482.9	9247.8	8811.8	8353.0	7784.2	7537.8	7507.4
56°	8447.8	8519.8	8861.0	9399.5	9672.5	9456.3	8823.1	8273.3	7647.7	7314.1	7291.3
57.5°	7579.5	7541.6	8004.1	8739.7	9482.9	9391.9	8512.2	7704.6	6976.6	6601.2	6555.7
60°	4716.8	4826.7	5232.5	6142.4	7135.9	7181.4	6309.3	5615.4	4766.1	4432.4	4512.0
62.5°	1846.5	1751.7	2005.8	2684.5	3367.0	3518.6	3188.8	2650.4	2176.4	1846.5	1823.8
65°	428.5	417.1	470.2	648.4	906.2	1050.3	997.2	716.6	527.0	500.5	462.6
67.5°	242.7	242.7	231.3	231.3	254.0	269.2	257.8	254.0	265.4	276.8	273.0
70°	170.6	166.8	159.2	163.0	155.5	155.5	166.8	185.8	201.0	201.0	204.7
72.5°	102.4	102.4	102.4	113.7	113.7	113.7	125.1	140.3	144.1	140.3	136.5
75°	45.5	45.5	53.1	64.5	72.0	75.8	87.2	94.8	102.4	94.8	87.2
77.5°	11.4	11.4	19.0	26.5	34.1	41.7	56.9	68.2	72.0	68.2	56.9
80°	3.8	3.8	7.6	19.0	34.1	41.7	56.9	60.7	64.5	56.9	45.5
82.5°	3.8	3.8	7.6	19.0	26.5	34.1	45.5	53.1	56.9	49.3	45.5
85°	0.0	3.8	7.6	15.2	22.7	30.3	30.3	22.7	19.0	11.4	15.2
87.5°	0.0	0.0	3.8	3.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)