

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P453916

Luminaire Tested: **GALN-SA5A-727-U-SLR-HSS**

Issue Date: 1/4/2021

Test Information

Test Method: LM-79-08
Report Number: P453916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-042-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/4/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA5A-727-U-SLR-HSS
Description: GALLEON AREA AND ROADWAY LUMINAIRE
(5) 70 CRI, 2700K, 615mA LIGHTSQUARES WITH 16 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13755 lumens
Efficiency: N/A
Efficacy: 89.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 154
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P453916
 CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 7.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P453916
CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 60-Deg Vertical

REPORT NUMBER: P453916

CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1696.5	0.0	1696.5
	% Fixture	12.3	0.0	12.3
Street Side	Lumens	12058.5	0.0	12058.5
	% Fixture	87.7	0.0	87.7
Total	Lumens	13755.0	0.0	13755.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	338.1	2.5
10°-20°	671.5	4.9
20°-30°	984.7	7.2
30°-40°	1464.3	10.6
40°-50°	2131.1	15.5
50°-60°	3073.2	22.3
60°-70°	3380.2	24.6
70°-80°	1514.0	11.0
80°-90°	197.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	13755.0	100.0
0°-180°	13755.0	100.0

Coefficient of Utilization



REPORT NUMBER: P453916


CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1509.6	11.0			
FM (30°-60°)	5862.8	42.6			
FH (60°-80°)	4505.2	32.8			G2/5000
FVH (80°-90°)	180.9	1.3			G2/225
BL (0°-30°)	484.8	3.5	B1/500		
BM (30°-60°)	805.8	5.9	B1/1000		
BH (60°-80°)	389.1	2.8	B1/500		G1/500
BVH (80°-90°)	16.9	0.1			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2

Type IV Short





REPORT NUMBER: P453916

CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

CANDELA DISTRIBUTION (FULL):

	0°	1°	5°	15°	25°	35°	45°	55°	65°	75°	85°
0°	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2
2.5°	4997.9	4976.0	4925.8	4773.1	4640.3	4466.8	4291.1	4153.1	4068.4	3912.6	3841.5
5°	4842.1	4852.6	4707.2	4393.6	4044.3	3805.9	3545.6	3338.6	3110.6	2966.3	2814.7
7.5°	4435.4	4414.5	4256.6	3819.5	3395.0	3050.0	2720.6	2453.0	2284.6	2149.7	2036.8
10°	4087.2	4071.5	3869.7	3307.2	2851.3	2593.1	2370.4	2136.1	1955.3	1757.6	1599.8
12.5°	3868.7	3833.1	3601.0	3013.4	2642.2	2401.7	2159.1	1915.5	1665.6	1465.9	1274.6
15°	3795.5	3744.3	3486.0	2912.0	2508.4	2203.1	1898.8	1618.6	1331.0	1110.4	966.1
17.5°	3928.3	3843.6	3568.6	2894.2	2348.4	1943.8	1569.4	1204.5	905.5	737.1	648.3
20°	4232.5	4135.3	3777.7	2876.4	2170.6	1653.1	1193.0	851.1	626.3	534.3	485.2
22.5°	4684.2	4550.4	4087.2	2904.6	2006.5	1369.7	861.6	601.2	497.7	440.2	405.7
25°	5226.9	5115.0	4479.3	3005.0	1876.8	1147.0	666.0	491.4	419.3	383.7	357.6
27.5°	5821.8	5643.0	4986.4	3125.3	1758.7	974.5	584.5	439.1	373.3	340.9	327.3
30°	6245.3	6106.2	5410.9	3208.9	1611.3	844.8	534.3	432.9	374.3	335.6	310.5
32.5°	6663.5	6485.8	5766.4	3247.6	1503.6	754.9	462.2	377.5	328.3	308.4	283.4
35°	7111.1	6924.9	6120.9	3226.7	1423.0	695.3	419.3	336.7	281.3	247.8	222.7
37.5°	7563.8	7367.2	6473.2	3151.4	1372.9	671.3	385.8	320.0	265.6	231.1	203.9
40°	8101.2	7838.8	6803.7	3089.7	1320.6	658.7	363.9	309.5	254.1	217.5	190.3
42.5°	8540.4	8290.5	7116.3	3057.3	1285.0	629.4	363.9	301.1	246.8	206.0	177.8
45°	8956.5	8697.2	7454.0	3083.4	1270.4	592.8	368.0	300.1	241.5	197.6	169.4
47.5°	9304.7	9079.9	7801.1	3181.7	1251.6	553.1	346.1	314.7	238.4	190.3	161.0
50°	9715.6	9498.1	8260.2	3380.4	1218.1	513.4	318.9	338.8	237.3	184.0	153.7
52.5°	10294.9	10059.6	8893.8	3606.2	1164.8	452.7	293.8	335.6	233.2	173.6	146.4
55°	11002.7	10812.4	9627.8	3877.0	1091.6	384.8	254.1	298.0	220.6	155.8	133.8
57.5°	11456.5	11294.5	10177.8	3994.2	979.7	314.7	223.8	249.9	201.8	139.1	119.2
59°	11509.9	11363.5	10292.8	3955.5	906.5	287.5	209.1	214.3	196.6	129.7	110.8
60°	11464.9	11313.3	10246.8	3880.2	838.6	268.7	196.6	190.3	197.6	124.4	104.6
62.5°	11176.3	10917.0	9800.3	3498.5	733.0	246.8	174.6	155.8	174.6	111.9	93.1
65°	10619.0	10230.0	8916.8	2961.1	691.1	234.2	148.5	130.7	132.8	98.3	80.5
67.5°	9645.6	9155.2	7740.5	2405.9	673.4	235.3	125.5	117.1	102.5	83.6	71.1
70°	8106.5	7617.1	6210.8	1979.3	665.0	235.3	106.7	100.4	85.7	70.1	61.7
72.5°	5744.5	5217.5	4189.7	1554.8	599.1	234.2	91.0	91.0	70.1	58.6	50.2
75°	3245.5	3249.7	2633.8	1100.0	497.7	193.4	73.2	72.1	51.2	45.0	37.6
77.5°	1891.5	1858.0	1775.4	472.6	231.1	87.8	51.2	43.9	35.6	32.4	27.2
80°	972.4	799.9	779.0	171.5	82.6	55.4	35.6	25.1	23.0	20.9	18.8
82.5°	287.5	288.6	257.2	69.0	46.0	36.6	17.8	13.6	12.5	11.5	11.5
85°	19.9	12.5	14.6	20.9	28.2	14.6	1.0	3.1	3.1	4.2	5.2
87.5°	2.1	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P453916

CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2
2.5°	3763.1	3809.1	3723.3	3725.4	3654.3	3677.3	3593.7	3620.9	3571.7	3609.4	3720.2
5°	2831.5	2841.9	2772.9	2750.9	2761.4	2804.3	2821.0	2744.7	2777.1	2713.3	2709.1
7.5°	1995.0	2007.5	1967.8	1962.6	2037.9	2020.1	2052.5	1974.1	1899.8	1932.2	1872.7
10°	1549.6	1497.3	1415.7	1392.7	1378.1	1387.5	1387.5	1316.4	1305.9	1277.7	1320.6
12.5°	1223.3	1159.6	1082.2	977.6	951.5	949.4	910.7	848.0	828.1	804.1	839.6
15°	888.8	862.6	797.8	739.2	679.6	668.1	605.4	554.2	486.2	476.8	473.7
17.5°	625.3	586.6	585.5	552.1	517.6	494.6	436.0	377.5	351.3	348.2	348.2
20°	468.4	454.8	432.9	428.7	418.2	392.1	339.8	308.4	295.9	296.9	301.1
22.5°	394.2	384.8	364.9	355.5	351.3	328.3	289.6	268.7	262.4	262.4	263.5
25°	352.4	344.0	322.0	307.4	302.2	285.4	255.1	239.4	234.2	234.2	234.2
27.5°	321.0	310.5	287.5	275.0	265.6	246.8	227.9	212.3	207.0	207.0	208.1
30°	299.0	287.5	266.6	249.9	235.3	218.5	202.8	189.3	183.0	181.9	183.0
32.5°	269.8	259.3	238.4	227.9	211.2	191.3	178.8	166.2	160.0	161.0	160.0
35°	210.2	207.0	192.4	195.5	186.1	169.4	157.9	144.3	137.0	135.9	138.0
37.5°	191.3	178.8	162.1	163.1	160.0	153.7	134.9	120.2	115.0	115.0	116.1
40°	176.7	164.2	145.3	135.9	137.0	137.0	117.1	101.4	96.2	95.1	97.2
42.5°	164.2	151.6	130.7	115.0	110.8	116.1	99.3	83.6	78.4	76.3	78.4
45°	155.8	142.2	118.2	100.4	87.8	94.1	81.6	69.0	62.7	62.7	61.7
47.5°	147.4	134.9	108.7	86.8	73.2	70.1	66.9	55.4	49.1	48.1	49.1
50°	140.1	127.6	98.3	75.3	61.7	54.4	54.4	43.9	39.7	37.6	38.7
52.5°	132.8	119.2	88.9	66.9	53.3	43.9	38.7	35.6	32.4	31.4	32.4
55°	122.3	108.7	79.5	57.5	46.0	36.6	30.3	29.3	27.2	25.1	27.2
57.5°	109.8	97.2	70.1	49.1	36.6	28.2	25.1	24.0	22.0	20.9	20.9
59°	102.5	91.0	64.8	42.9	32.4	25.1	23.0	22.0	19.9	17.8	18.8
60°	98.3	88.9	61.7	39.7	29.3	23.0	20.9	19.9	17.8	16.7	17.8
62.5°	86.8	79.5	54.4	32.4	23.0	16.7	14.6	15.7	14.6	13.6	14.6
65°	76.3	70.1	46.0	25.1	17.8	11.5	10.5	13.6	12.5	11.5	12.5
67.5°	68.0	60.6	38.7	18.8	12.5	6.3	7.3	11.5	11.5	10.5	11.5
70°	58.6	52.3	31.4	13.6	6.3	3.1	5.2	8.4	10.5	9.4	10.5
72.5°	48.1	40.8	24.0	9.4	3.1	0.0	3.1	7.3	10.5	9.4	10.5
75°	37.6	30.3	17.8	5.2	0.0	0.0	1.0	6.3	10.5	9.4	10.5
77.5°	27.2	22.0	10.5	1.0	0.0	0.0	1.0	6.3	10.5	9.4	10.5
80°	17.8	15.7	4.2	0.0	0.0	0.0	1.0	6.3	10.5	10.5	11.5
82.5°	11.5	8.4	0.0	0.0	0.0	0.0	2.1	8.4	11.5	12.5	12.5
85°	5.2	0.0	0.0	0.0	0.0	0.0	4.2	10.5	13.6	13.6	13.6
87.5°	0.0	0.0	0.0	0.0	0.0	2.1	7.3	12.5	15.7	15.7	15.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P453916

CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	185°	195°	205°	215°	225°	235°	245°	255°	265°	270°	275°
0°	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2
2.5°	3739.0	3804.9	3898.0	4041.2	4157.3	4340.2	4480.4	4671.7	4865.1	4923.7	5014.6
5°	2752.0	2836.7	3047.9	3240.3	3361.6	3748.4	3993.1	4378.9	4725.0	4891.3	5072.2
7.5°	1911.3	2011.7	2172.7	2441.5	2696.6	3011.3	3406.5	3847.8	4354.9	4592.2	4847.4
10°	1341.5	1467.0	1693.9	1914.5	2235.5	2534.5	2924.5	3411.8	3971.1	4251.4	4571.3
12.5°	846.9	958.8	1258.9	1506.7	1907.2	2254.3	2614.0	3055.2	3703.5	3991.0	4326.7
15°	484.1	578.2	718.3	1036.2	1480.6	1939.6	2388.1	2900.5	3566.5	3921.0	4283.8
17.5°	360.7	385.8	448.6	628.4	1033.0	1569.4	2180.1	2853.4	3659.6	4075.7	4489.8
20°	303.2	320.0	349.2	420.3	658.7	1208.7	1977.2	2861.8	3960.7	4483.5	4876.6
22.5°	271.9	282.3	306.4	352.4	449.6	880.4	1739.9	2910.9	4325.6	4984.3	5438.1
25°	238.4	252.0	272.9	312.6	374.3	610.6	1505.6	3020.7	4836.9	5620.0	6046.6
27.5°	212.3	224.8	245.7	282.3	328.3	466.3	1232.8	3114.8	5376.4	6259.9	6609.2
30°	186.1	198.7	219.6	248.9	290.7	377.5	938.9	3170.2	5900.3	6739.9	7008.6
32.5°	164.2	174.6	194.5	220.6	255.1	320.0	740.3	3112.7	6300.7	7175.9	7355.7
35°	142.2	154.7	171.5	195.5	225.8	272.9	615.9	2914.1	6644.7	7624.4	7689.3
37.5°	119.2	133.8	151.6	173.6	197.6	250.9	494.6	2694.5	7012.8	8183.8	8077.2
40°	100.4	114.0	130.7	154.7	176.7	230.0	380.6	2460.3	7410.1	8708.7	8500.6
42.5°	81.6	96.2	116.1	138.0	174.6	200.8	294.9	2217.7	7766.6	9165.6	8883.3
45°	64.8	77.4	98.3	126.5	173.6	172.5	227.9	1978.3	8035.4	9491.9	9168.8
47.5°	51.2	61.7	82.6	123.4	160.0	146.4	183.0	1829.8	8317.7	9785.7	9387.3
50°	40.8	51.2	71.1	128.6	140.1	125.5	153.7	1853.8	8590.6	9935.2	9477.2
52.5°	34.5	45.0	61.7	101.4	107.7	109.8	134.9	1964.7	8942.9	10095.2	9656.0
55°	30.3	39.7	52.3	71.1	83.6	98.3	123.4	2045.2	9414.5	10438.1	10050.2
57.5°	24.0	34.5	47.1	60.6	69.0	85.7	114.0	2051.4	9841.1	10878.3	10574.0
59°	22.0	31.4	43.9	57.5	61.7	77.4	107.7	1998.1	9856.8	10944.2	10814.5
60°	19.9	30.3	41.8	53.3	58.6	73.2	102.5	1936.4	9714.6	10839.6	10913.9
62.5°	16.7	26.1	36.6	42.9	50.2	60.6	88.9	1712.7	9025.5	10366.0	10729.8
65°	14.6	23.0	31.4	35.6	41.8	52.3	78.4	1370.8	8264.3	9724.0	10202.9
67.5°	13.6	20.9	27.2	30.3	36.6	48.1	70.1	968.2	7278.4	8909.5	9411.4
70°	12.5	19.9	24.0	28.2	32.4	40.8	59.6	564.6	5606.5	7481.2	8011.3
72.5°	12.5	18.8	20.9	24.0	28.2	36.6	55.4	305.3	3833.1	5706.8	6391.7
75°	12.5	17.8	18.8	20.9	25.1	33.5	49.1	160.0	2478.0	3964.9	4893.4
77.5°	12.5	16.7	18.8	19.9	24.0	29.3	42.9	100.4	1651.0	2777.1	3307.2
80°	13.6	16.7	17.8	19.9	23.0	27.2	35.6	66.9	970.3	1670.9	2012.8
82.5°	14.6	16.7	18.8	20.9	24.0	26.1	31.4	41.8	447.5	1105.2	1250.5
85°	15.7	17.8	19.9	22.0	25.1	26.1	29.3	30.3	73.2	498.7	674.4
87.5°	16.7	18.8	20.9	23.0	27.2	27.2	27.2	27.2	25.1	53.3	135.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P453916

CATALOG NUMBER: GALN-SA5A-727-U-SLR-HSS

CANDELA DISTRIBUTION (continued):

	285°	295°	305°	315°	325°	335°	345°	355°	359°	360°
0°	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2	4546.2
2.5°	5129.7	5247.8	5330.4	5351.3	5291.7	5264.5	5189.3	5072.2	5001.1	4997.9
5°	5405.7	5682.8	5875.2	5907.6	5792.6	5598.1	5367.0	5069.0	4894.4	4842.1
7.5°	5358.6	5843.8	6153.3	6198.3	6004.8	5633.6	5186.1	4706.2	4515.9	4435.4
10°	5165.2	5757.0	6199.3	6270.4	6012.1	5489.3	4920.5	4385.2	4148.9	4087.2
12.5°	5000.0	5598.1	5991.2	6089.5	5894.0	5372.2	4761.6	4179.2	3926.2	3868.7
15°	4927.9	5409.9	5650.4	5700.6	5668.1	5299.0	4744.9	4147.9	3858.2	3795.5
17.5°	5000.0	5249.9	5280.2	5331.5	5403.6	5291.7	4905.9	4318.3	4005.7	3928.3
20°	5189.3	5110.8	4985.4	5007.3	5172.5	5322.1	5192.4	4695.7	4315.1	4232.5
22.5°	5511.3	5076.3	4791.9	4773.1	4982.2	5423.5	5612.7	5207.0	4765.8	4684.2
25°	5906.5	5163.1	4720.8	4680.1	4908.0	5571.9	6069.6	5833.3	5351.3	5226.9
27.5°	6337.3	5343.0	4720.8	4681.1	4901.7	5703.7	6460.7	6387.5	5957.8	5821.8
30°	6573.6	5491.4	4788.8	4743.8	4979.1	5780.0	6669.8	6880.0	6413.6	6245.3
32.5°	6784.8	5697.4	4921.6	4836.9	5141.2	5892.9	6857.0	7298.2	6776.5	6663.5
35°	6979.3	5918.0	5104.6	5006.3	5354.5	6047.7	7064.0	7737.4	7281.5	7111.1
37.5°	7193.7	6174.2	5390.0	5306.4	5711.0	6348.8	7309.7	8314.5	7778.1	7563.8
40°	7426.8	6471.2	5859.5	5823.9	6277.7	6689.7	7620.3	8930.4	8344.9	8101.2
42.5°	7664.2	6813.1	6434.6	6493.1	6919.7	7167.5	7939.2	9404.0	8809.1	8540.4
45°	7879.6	7250.1	7182.2	7471.8	7668.4	7633.9	8175.5	9737.6	9213.7	8956.5
47.5°	8151.4	7886.9	8086.6	8533.1	8538.3	8141.0	8354.3	10010.5	9561.9	9304.7
50°	8455.7	8638.7	9254.5	9709.3	9587.0	8639.7	8563.4	10333.6	9921.6	9715.6
52.5°	8808.0	9480.4	10333.6	10838.6	10553.1	9183.4	8911.6	10682.8	10492.5	10294.9
55°	9217.9	10054.4	11409.5	11812.0	11524.5	9858.9	9440.6	11156.4	11137.6	11002.7
57.5°	9681.1	10660.8	12032.6	12577.4	12321.2	10651.4	10179.9	11602.9	11531.8	11456.5
59°	10047.1	10972.4	12307.6	12872.3	12717.5	11206.6	10676.5	11881.0	11622.8	11509.9
60°	10268.7	11183.6	12409.1	12912.0	12876.4	11537.0	10991.2	12017.0	11621.7	11464.9
62.5°	10926.4	11552.7	12370.4	12735.3	12874.3	12170.7	11914.5	12166.5	11406.3	11176.3
65°	11160.6	11430.4	11729.4	11684.5	11803.7	12138.3	12504.2	12002.3	10946.3	10619.0
67.5°	10704.7	10088.9	10194.5	9894.4	9835.9	10791.5	12264.8	11199.3	10046.0	9645.6
70°	9023.4	7729.0	7675.7	7813.7	7435.2	8736.9	11013.2	9652.9	8560.2	8106.5
72.5°	7102.7	5462.2	5012.6	5520.7	5509.2	6665.6	9148.9	6849.7	5783.2	5744.5
75°	5585.5	3802.8	3337.5	3420.1	3579.1	4825.4	7286.7	4349.7	3561.3	3245.5
77.5°	3749.5	2694.5	2513.6	2412.2	2583.7	3098.1	4610.0	2358.9	1997.1	1891.5
80°	2161.2	1957.3	2222.9	2018.0	2110.0	1952.1	2293.0	1082.2	898.2	972.4
82.5°	1406.3	1114.6	1187.8	882.5	1206.6	1217.1	736.1	320.0	270.8	287.5
85°	879.3	522.8	293.8	209.1	416.1	765.4	230.0	19.9	23.0	19.9
87.5°	227.9	86.8	36.6	54.4	66.9	59.6	53.3	3.1	1.0	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)