

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047111

Luminaire Tested: **GALN-SA7C-727-U-T3BC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1047111  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA7C-727-U-T3BC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE  
70CRI 2700K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL  
Light Source: (98) 2700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 36828.1 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G5

Input Watts (W): 330  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT




REPORT NUMBER: P1047111

CATALOG NUMBER: GALN-SA7C-727-U-T3BC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 41.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1047111

CATALOG NUMBER: GALN-SA7C-727-U-T3BC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1047111

CATALOG NUMBER: GALN-SA7C-727-U-T3BC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 134.4    | 0.0    | 134.4   |
|                    | % Fixture | 0.4      | 0.0    | 0.4     |
| <b>Street Side</b> | Lumens    | 36693.7  | 0.0    | 36693.7 |
|                    | % Fixture | 99.6     | 0.0    | 99.6    |
| <b>Total</b>       | Lumens    | 36828.1  | 0.0    | 36828.1 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 35.3    | 0.1       |
| 10°-20°   | 423.3   | 1.1       |
| 20°-30°   | 1525.8  | 4.1       |
| 30°-40°   | 3491.1  | 9.5       |
| 40°-50°   | 5888.1  | 16.0      |
| 50°-60°   | 9716.7  | 26.4      |
| 60°-70°   | 10859.8 | 29.5      |
| 70°-80°   | 4483.8  | 12.2      |
| 80°-90°   | 404.2   | 1.1       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 36828.1 | 100.0     |
| 0°-180°   | 36828.1 | 100.0     |



REPORT NUMBER: P1047111


CATALOG NUMBER: GALN-SA7C-727-U-T3BC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 1949.4  | 5.3       |                         |      |        |
| FM   | (30°-60°)   | 19063.7 | 51.8      |                         |      |        |
| FH   | (60°-80°)   | 15282.0 | 41.5      |                         |      | G5     |
| FVH  | (80°-90°)   | 398.7   | 1.1       |                         |      | G3/500 |
| BL   | (0°-30°)    | 35.1    | 0.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 32.2    | 0.1       | B0/220                  |      |        |
| BH   | (60°-80°)   | 61.6    | 0.2       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 5.5     | 0.0       |                         |      | G0/10  |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G5**

Type III Short





REPORT NUMBER: P1047111

CATALOG NUMBER: GALN-SA7C-727-U-T3BC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 43°     | 45°     | 55°     | 65°     | 75°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   | 240.8   |
| 2.5°  | 289.0   | 298.6   | 289.0   | 289.0   | 289.0   | 279.3   | 279.3   | 269.7   | 269.7   | 260.1   | 250.4   |
| 5°    | 423.8   | 423.8   | 394.9   | 375.7   | 356.4   | 346.8   | 337.1   | 317.9   | 298.6   | 279.3   | 260.1   |
| 7.5°  | 943.9   | 943.9   | 857.3   | 741.7   | 587.6   | 500.9   | 481.6   | 394.9   | 337.1   | 298.6   | 260.1   |
| 10°   | 2253.9  | 2253.9  | 2061.3  | 1743.4  | 1348.5  | 1001.7  | 895.8   | 568.3   | 404.5   | 317.9   | 269.7   |
| 12.5° | 3746.9  | 3795.0  | 3554.2  | 3149.7  | 2562.1  | 1955.3  | 1743.4  | 1040.3  | 539.4   | 346.8   | 269.7   |
| 15°   | 5085.7  | 4970.1  | 4902.7  | 4517.4  | 3958.8  | 3236.4  | 2966.7  | 1753.0  | 780.2   | 394.9   | 269.7   |
| 17.5° | 5991.1  | 5991.1  | 5894.8  | 5634.8  | 5124.3  | 4488.5  | 4267.0  | 2831.8  | 1261.8  | 452.7   | 279.3   |
| 20°   | 7050.7  | 7050.7  | 6877.3  | 6694.3  | 6241.6  | 5702.2  | 5490.3  | 4026.2  | 1955.3  | 577.9   | 279.3   |
| 22.5° | 8331.7  | 8351.0  | 8158.4  | 7830.9  | 7397.4  | 6800.2  | 6617.2  | 5133.9  | 2831.8  | 770.6   | 289.0   |
| 25°   | 9892.1  | 9911.4  | 9632.1  | 9323.8  | 8659.2  | 8013.9  | 7734.6  | 6405.3  | 3901.0  | 1078.8  | 289.0   |
| 27.5° | 11616.3 | 11751.1 | 11336.9 | 10807.2 | 10104.0 | 9294.9  | 9083.0  | 7551.5  | 4960.5  | 1521.9  | 308.2   |
| 30°   | 13764.2 | 13764.2 | 13215.2 | 12473.5 | 11712.6 | 10710.9 | 10441.2 | 8755.5  | 6087.5  | 2109.4  | 327.5   |
| 32.5° | 15613.6 | 15469.1 | 14766.0 | 13985.8 | 13176.7 | 12242.4 | 11953.4 | 10017.4 | 7243.3  | 2841.5  | 366.0   |
| 35°   | 17029.5 | 16904.3 | 16037.4 | 15199.4 | 14496.3 | 13639.0 | 13292.3 | 11385.1 | 8466.6  | 3669.8  | 423.8   |
| 37.5° | 18243.1 | 18195.0 | 17019.9 | 15970.0 | 15507.6 | 14756.3 | 14448.1 | 12675.8 | 9670.6  | 4565.6  | 491.2   |
| 40°   | 19572.4 | 19418.2 | 18166.1 | 16865.8 | 16172.2 | 15565.4 | 15286.1 | 13716.1 | 10826.4 | 5615.5  | 587.6   |
| 42.5° | 20708.9 | 20525.9 | 19399.0 | 18127.6 | 16942.8 | 16124.1 | 15854.4 | 14592.6 | 11953.4 | 6665.4  | 712.8   |
| 45°   | 21970.7 | 21874.4 | 20737.8 | 19774.6 | 18195.0 | 16885.0 | 16528.6 | 15295.7 | 12984.0 | 7917.6  | 876.5   |
| 47.5° | 23868.3 | 23694.9 | 22635.4 | 21845.5 | 20015.4 | 18040.9 | 17530.4 | 16018.1 | 13976.1 | 9150.5  | 1127.0  |
| 50°   | 26074.0 | 25958.4 | 25332.3 | 24706.3 | 22885.8 | 20015.4 | 19408.6 | 17058.4 | 15083.8 | 10614.5 | 1454.4  |
| 52.5° | 27875.2 | 27855.9 | 27933.0 | 27942.6 | 26565.2 | 23338.5 | 22433.1 | 18734.4 | 16355.3 | 12059.3 | 1916.8  |
| 55°   | 27836.7 | 27923.4 | 28771.0 | 29743.8 | 29849.8 | 27875.2 | 26998.7 | 21556.6 | 18012.0 | 13841.3 | 2562.1  |
| 57.5° | 26796.4 | 26729.0 | 27624.8 | 29088.8 | 30119.5 | 30331.4 | 30186.9 | 25939.2 | 20506.7 | 15989.2 | 3554.2  |
| 58°   | 26459.3 | 26401.5 | 27249.1 | 28742.1 | 29926.8 | 30495.1 | 30350.6 | 26931.3 | 21065.3 | 16297.5 | 3823.9  |
| 60°   | 25236.0 | 25245.6 | 25746.5 | 27104.6 | 28289.4 | 29637.9 | 29772.7 | 29763.1 | 23849.0 | 18358.7 | 5182.1  |
| 62.5° | 23617.8 | 23540.8 | 24003.1 | 25110.8 | 26151.1 | 27056.5 | 27287.6 | 29955.7 | 27923.4 | 20978.6 | 7773.1  |
| 65°   | 21383.2 | 21267.6 | 21758.8 | 23011.0 | 24128.3 | 24715.9 | 24725.5 | 27374.3 | 29840.1 | 23791.2 | 11471.8 |
| 67.5° | 17231.8 | 17135.4 | 18117.9 | 19726.5 | 21450.6 | 22221.2 | 22567.9 | 23752.7 | 28222.0 | 25698.4 | 13590.8 |
| 70°   | 10556.7 | 10759.0 | 12126.8 | 14650.4 | 17597.8 | 19013.7 | 19533.8 | 19899.9 | 24032.0 | 25409.4 | 11365.8 |
| 72.5° | 4873.8  | 4633.0  | 5798.5  | 7561.2  | 10922.8 | 14072.5 | 14611.8 | 16047.0 | 19052.2 | 22057.4 | 8476.2  |
| 75°   | 2273.2  | 2186.5  | 2456.2  | 3303.8  | 4950.9  | 7599.7  | 8582.2  | 12810.7 | 14611.8 | 15343.9 | 6116.4  |
| 77.5° | 1165.5  | 1175.1  | 1396.6  | 1502.6  | 2042.0  | 3515.7  | 4035.8  | 8428.1  | 10710.9 | 8562.9  | 4103.3  |
| 80°   | 510.5   | 529.8   | 539.4   | 587.6   | 828.4   | 1358.1  | 1531.5  | 3910.6  | 7320.4  | 4363.3  | 2244.3  |
| 82.5° | 327.5   | 337.1   | 337.1   | 337.1   | 394.9   | 539.4   | 616.5   | 1570.0  | 3650.6  | 2167.2  | 693.5   |
| 85°   | 173.4   | 173.4   | 192.6   | 240.8   | 279.3   | 327.5   | 346.8   | 500.9   | 1204.0  | 645.3   | 163.7   |
| 87.5° | 96.3    | 106.0   | 115.6   | 144.5   | 183.0   | 221.5   | 240.8   | 346.8   | 462.3   | 443.1   | 38.5    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1047111

CATALOG NUMBER: GALN-SA7C-727-U-T3BC

**CANDELA DISTRIBUTION (continued):**

|       | 90°    | 95°   | 105°  | 115°  | 125°  | 135°  | 145°  | 155°  | 165°  | 175°  | 180°  |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 240.8  | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 | 240.8 |
| 2.5°  | 250.4  | 240.8 | 231.2 | 221.5 | 211.9 | 202.3 | 202.3 | 202.3 | 202.3 | 202.3 | 202.3 |
| 5°    | 240.8  | 231.2 | 221.5 | 202.3 | 183.0 | 173.4 | 163.7 | 154.1 | 154.1 | 154.1 | 154.1 |
| 7.5°  | 240.8  | 231.2 | 202.3 | 183.0 | 163.7 | 144.5 | 125.2 | 125.2 | 125.2 | 125.2 | 125.2 |
| 10°   | 240.8  | 221.5 | 192.6 | 163.7 | 134.8 | 115.6 | 106.0 | 96.3  | 96.3  | 96.3  | 96.3  |
| 12.5° | 240.8  | 211.9 | 183.0 | 144.5 | 115.6 | 96.3  | 86.7  | 77.1  | 77.1  | 77.1  | 77.1  |
| 15°   | 240.8  | 211.9 | 173.4 | 134.8 | 106.0 | 77.1  | 67.4  | 57.8  | 57.8  | 57.8  | 57.8  |
| 17.5° | 231.2  | 202.3 | 163.7 | 115.6 | 86.7  | 57.8  | 48.2  | 38.5  | 38.5  | 48.2  | 48.2  |
| 20°   | 221.5  | 192.6 | 144.5 | 96.3  | 67.4  | 48.2  | 28.9  | 28.9  | 28.9  | 28.9  | 28.9  |
| 22.5° | 221.5  | 192.6 | 134.8 | 86.7  | 57.8  | 28.9  | 19.3  | 19.3  | 19.3  | 19.3  | 28.9  |
| 25°   | 221.5  | 183.0 | 115.6 | 67.4  | 38.5  | 19.3  | 9.6   | 9.6   | 9.6   | 9.6   | 9.6   |
| 27.5° | 221.5  | 183.0 | 106.0 | 57.8  | 28.9  | 19.3  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   |
| 30°   | 211.9  | 173.4 | 96.3  | 48.2  | 19.3  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 32.5° | 211.9  | 163.7 | 77.1  | 38.5  | 19.3  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°   | 221.5  | 154.1 | 67.4  | 28.9  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 9.6   |
| 37.5° | 231.2  | 144.5 | 57.8  | 19.3  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°   | 240.8  | 134.8 | 57.8  | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5° | 260.1  | 134.8 | 48.2  | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°   | 279.3  | 134.8 | 38.5  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5° | 317.9  | 144.5 | 38.5  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°   | 346.8  | 154.1 | 28.9  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5° | 385.3  | 144.5 | 28.9  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°   | 433.4  | 144.5 | 28.9  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5° | 472.0  | 134.8 | 28.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 58°   | 491.2  | 125.2 | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°   | 587.6  | 115.6 | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5° | 915.0  | 96.3  | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°   | 1859.0 | 86.7  | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5° | 3467.5 | 77.1  | 19.3  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°   | 3881.7 | 86.7  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5° | 2446.5 | 67.4  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°   | 1290.7 | 67.4  | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5° | 645.3  | 67.4  | 9.6   | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°   | 298.6  | 48.2  | 9.6   | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5° | 125.2  | 28.9  | 19.3  | 9.6   | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°   | 57.8   | 28.9  | 19.3  | 19.3  | 9.6   | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5° | 28.9   | 28.9  | 28.9  | 19.3  | 19.3  | 9.6   | 9.6   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-3

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-727-U-5WQ

Data in this report applies to families of products including GSS-SB1A-727-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-3  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-727-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 2700K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 2672     | CRI (Ra): | 71.1 |      |       |
| CIE u':                   | 0.2638   | R1:       | 68.3 | R9:  | -27.8 |
| CIE v':                   | 0.5276   | R2:       | 79.8 | R10: | 54.4  |
| Duv:                      | -0.0002  | R3:       | 91.2 | R11: | 65.8  |
| CIE x:                    | 0.4619   | R4:       | 69.4 | R12: | 45.6  |
| CIE y:                    | 0.4106   | R5:       | 66.5 | R13: | 69.8  |
| CIE z:                    | 0.1275   | R6:       | 72.6 | R14: | 94.5  |
| Peak Wavelength (nm):     | 601      | R7:       | 77.0 | R15: | 60.1  |
| Dominant Wavelength (nm): | 584      | R8:       | 44.1 |      |       |
| Purity:                   | 61.88407 |           |      |      |       |
| Rf:                       | 67.9     |           |      |      |       |
| Rg:                       | 98.6     |           |      |      |       |



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-3

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-3

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



REPORT NUMBER: SP1-2407-184-3

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 52                          | NR               | 620       | 888                         | NR               | 750       | 27                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 87                          | NR               | 625       | 834                         | NR               | 755       | 23                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 135                         | NR               | 630       | 776                         | NR               | 760       | 20                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 196                         | NR               | 635       | 712                         | NR               | 765       | 17                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 258                         | NR               | 640       | 648                         | NR               | 770       | 15                          | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 317                         | NR               | 645       | 583                         | NR               | 775       | 12                          | NR               | 905       | 0                           | NR               |
| 390       | 2                           | NR               | 520       | 368                         | NR               | 650       | 523                         | NR               | 780       | 11                          | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 408                         | NR               | 655       | 465                         | NR               | 785       | 9                           | NR               | 915       | 0                           | NR               |
| 400       | 6                           | NR               | 530       | 443                         | NR               | 660       | 410                         | NR               | 790       | 8                           | NR               | 920       | 0                           | NR               |
| 405       | 11                          | NR               | 535       | 473                         | NR               | 665       | 360                         | NR               | 795       | 7                           | NR               | 925       | 0                           | NR               |
| 410       | 23                          | NR               | 540       | 498                         | NR               | 670       | 313                         | NR               | 800       | 6                           | NR               | 930       | 0                           | NR               |
| 415       | 51                          | NR               | 545       | 530                         | NR               | 675       | 272                         | NR               | 805       | 5                           | NR               | 935       | 0                           | NR               |
| 420       | 111                         | NR               | 550       | 563                         | NR               | 680       | 236                         | NR               | 810       | 4                           | NR               | 940       | 0                           | NR               |
| 425       | 214                         | NR               | 555       | 605                         | NR               | 685       | 203                         | NR               | 815       | 4                           | NR               | 945       | 0                           | NR               |
| 430       | 339                         | NR               | 560       | 651                         | NR               | 690       | 175                         | NR               | 820       | 3                           | NR               | 950       | 0                           | NR               |
| 435       | 467                         | NR               | 565       | 705                         | NR               | 695       | 150                         | NR               | 825       | 3                           | NR               | 955       | 0                           | NR               |
| 440       | 535                         | NR               | 570       | 765                         | NR               | 700       | 128                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 372                         | NR               | 575       | 824                         | NR               | 705       | 110                         | NR               | 835       | 2                           | NR               | 965       | 0                           | NR               |
| 450       | 160                         | NR               | 580       | 882                         | NR               | 710       | 94                          | NR               | 840       | 2                           | NR               | 970       | 0                           | NR               |
| 455       | 89                          | NR               | 585       | 930                         | NR               | 715       | 80                          | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 53                          | NR               | 590       | 968                         | NR               | 720       | 69                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 31                          | NR               | 595       | 991                         | NR               | 725       | 59                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 23                          | NR               | 600       | 999                         | NR               | 730       | 50                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 21                          | NR               | 605       | 992                         | NR               | 735       | 43                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 23                          | NR               | 610       | 969                         | NR               | 740       | 36                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 32                          | NR               | 615       | 935                         | NR               | 745       | 31                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-3

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.02

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 52                                   | NR                             | 620               | 888                                  | NR                             | 750               | 27                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 87                                   | NR                             | 625               | 834                                  | NR                             | 755               | 23                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 135                                  | NR                             | 630               | 776                                  | NR                             | 760               | 20                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 196                                  | NR                             | 635               | 712                                  | NR                             | 765               | 17                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 258                                  | NR                             | 640               | 648                                  | NR                             | 770               | 15                                   | NR                             | 900               | 0                                    | NR                             |
| 385               | 1                                    | NR                             | 515               | 317                                  | NR                             | 645               | 583                                  | NR                             | 775               | 12                                   | NR                             | 905               | 0                                    | NR                             |
| 390               | 2                                    | NR                             | 520               | 368                                  | NR                             | 650               | 523                                  | NR                             | 780               | 11                                   | NR                             | 910               | 0                                    | NR                             |
| 395               | 4                                    | NR                             | 525               | 408                                  | NR                             | 655               | 465                                  | NR                             | 785               | 9                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 6                                    | NR                             | 530               | 443                                  | NR                             | 660               | 410                                  | NR                             | 790               | 8                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 11                                   | NR                             | 535               | 473                                  | NR                             | 665               | 360                                  | NR                             | 795               | 7                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 23                                   | NR                             | 540               | 498                                  | NR                             | 670               | 313                                  | NR                             | 800               | 6                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 51                                   | NR                             | 545               | 530                                  | NR                             | 675               | 272                                  | NR                             | 805               | 5                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 111                                  | NR                             | 550               | 563                                  | NR                             | 680               | 236                                  | NR                             | 810               | 4                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 214                                  | NR                             | 555               | 605                                  | NR                             | 685               | 203                                  | NR                             | 815               | 4                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 339                                  | NR                             | 560               | 651                                  | NR                             | 690               | 175                                  | NR                             | 820               | 3                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 467                                  | NR                             | 565               | 705                                  | NR                             | 695               | 150                                  | NR                             | 825               | 3                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 535                                  | NR                             | 570               | 765                                  | NR                             | 700               | 128                                  | NR                             | 830               | 3                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 372                                  | NR                             | 575               | 824                                  | NR                             | 705               | 110                                  | NR                             | 835               | 2                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 160                                  | NR                             | 580               | 882                                  | NR                             | 710               | 94                                   | NR                             | 840               | 2                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 89                                   | NR                             | 585               | 930                                  | NR                             | 715               | 80                                   | NR                             | 845               | 2                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 53                                   | NR                             | 590               | 968                                  | NR                             | 720               | 69                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 31                                   | NR                             | 595               | 991                                  | NR                             | 725               | 59                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 23                                   | NR                             | 600               | 999                                  | NR                             | 730               | 50                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 21                                   | NR                             | 605               | 992                                  | NR                             | 735               | 43                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 23                                   | NR                             | 610               | 969                                  | NR                             | 740               | 36                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 32                                   | NR                             | 615               | 935                                  | NR                             | 745               | 31                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-3

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 1.71

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 52                       | NR            | 620    | 888                      | NR            | 750    | 27                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 87                       | NR            | 625    | 834                      | NR            | 755    | 23                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 135                      | NR            | 630    | 776                      | NR            | 760    | 20                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 196                      | NR            | 635    | 712                      | NR            | 765    | 17                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 258                      | NR            | 640    | 648                      | NR            | 770    | 15                       | NR            | 900    | 0                        | NR            |
| 385    | 1                        | NR            | 515    | 317                      | NR            | 645    | 583                      | NR            | 775    | 12                       | NR            | 905    | 0                        | NR            |
| 390    | 2                        | NR            | 520    | 368                      | NR            | 650    | 523                      | NR            | 780    | 11                       | NR            | 910    | 0                        | NR            |
| 395    | 4                        | NR            | 525    | 408                      | NR            | 655    | 465                      | NR            | 785    | 9                        | NR            | 915    | 0                        | NR            |
| 400    | 6                        | NR            | 530    | 443                      | NR            | 660    | 410                      | NR            | 790    | 8                        | NR            | 920    | 0                        | NR            |
| 405    | 11                       | NR            | 535    | 473                      | NR            | 665    | 360                      | NR            | 795    | 7                        | NR            | 925    | 0                        | NR            |
| 410    | 23                       | NR            | 540    | 498                      | NR            | 670    | 313                      | NR            | 800    | 6                        | NR            | 930    | 0                        | NR            |
| 415    | 51                       | NR            | 545    | 530                      | NR            | 675    | 272                      | NR            | 805    | 5                        | NR            | 935    | 0                        | NR            |
| 420    | 111                      | NR            | 550    | 563                      | NR            | 680    | 236                      | NR            | 810    | 4                        | NR            | 940    | 0                        | NR            |
| 425    | 214                      | NR            | 555    | 605                      | NR            | 685    | 203                      | NR            | 815    | 4                        | NR            | 945    | 0                        | NR            |
| 430    | 339                      | NR            | 560    | 651                      | NR            | 690    | 175                      | NR            | 820    | 3                        | NR            | 950    | 0                        | NR            |
| 435    | 467                      | NR            | 565    | 705                      | NR            | 695    | 150                      | NR            | 825    | 3                        | NR            | 955    | 0                        | NR            |
| 440    | 535                      | NR            | 570    | 765                      | NR            | 700    | 128                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 372                      | NR            | 575    | 824                      | NR            | 705    | 110                      | NR            | 835    | 2                        | NR            | 965    | 0                        | NR            |
| 450    | 160                      | NR            | 580    | 882                      | NR            | 710    | 94                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 89                       | NR            | 585    | 930                      | NR            | 715    | 80                       | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 53                       | NR            | 590    | 968                      | NR            | 720    | 69                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 31                       | NR            | 595    | 991                      | NR            | 725    | 59                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 999                      | NR            | 730    | 50                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 21                       | NR            | 605    | 992                      | NR            | 735    | 43                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 23                       | NR            | 610    | 969                      | NR            | 740    | 36                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 32                       | NR            | 615    | 935                      | NR            | 745    | 31                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-3

TM-30-18



### Summary

$R_f = 67.9$   
 $R_g = 98.6$   
 $CIE R_a = 71.1$   
 $R_g = -27.8$

### Spectral Power Distribution Comparison



### Color Vector Graphics



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 53 | CES51 = 75 | CES76 = 51 |
| CES02 = 63 | CES27 = 70 | CES52 = 80 | CES77 = 79 |
| CES03 = 31 | CES28 = 81 | CES53 = 64 | CES78 = 58 |
| CES04 = 71 | CES29 = 37 | CES54 = 73 | CES79 = 82 |
| CES05 = 50 | CES30 = 33 | CES55 = 69 | CES80 = 82 |
| CES06 = 52 | CES31 = 44 | CES56 = 60 | CES81 = 69 |
| CES07 = 42 | CES32 = 47 | CES57 = 54 | CES82 = 92 |
| CES08 = 41 | CES33 = 45 | CES58 = 59 | CES83 = 82 |
| CES09 = 29 | CES34 = 67 | CES59 = 85 | CES84 = 92 |
| CES10 = 77 | CES35 = 84 | CES60 = 86 | CES85 = 87 |
| CES11 = 60 | CES36 = 68 | CES61 = 86 | CES86 = 60 |
| CES12 = 66 | CES37 = 77 | CES62 = 59 | CES87 = 79 |
| CES13 = 44 | CES38 = 40 | CES63 = 66 | CES88 = 70 |
| CES14 = 74 | CES39 = 88 | CES64 = 69 | CES89 = 66 |
| CES15 = 72 | CES40 = 82 | CES65 = 64 | CES90 = 64 |
| CES16 = 48 | CES41 = 70 | CES66 = 65 | CES91 = 81 |
| CES17 = 51 | CES42 = 76 | CES67 = 64 | CES92 = 69 |
| CES18 = 57 | CES43 = 63 | CES68 = 73 | CES93 = 81 |
| CES19 = 73 | CES44 = 97 | CES69 = 83 | CES94 = 53 |
| CES20 = 67 | CES45 = 74 | CES70 = 64 | CES95 = 77 |
| CES21 = 88 | CES46 = 67 | CES71 = 60 | CES96 = 79 |
| CES22 = 80 | CES47 = 55 | CES72 = 87 | CES97 = 78 |
| CES23 = 92 | CES48 = 42 | CES73 = 57 | CES98 = 69 |
| CES24 = 92 | CES49 = 65 | CES74 = 84 | CES99 = 60 |
| CES25 = 73 | CES50 = 74 | CES75 = 60 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)