

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1048978

Luminaire Tested: **GALN-SA6B-730-U-RBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1048978  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA6B-730-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 6xLight Square PACKAGE  
70CRI 3000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (84) 3000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 23642 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4

Input Watts (W): 213.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3.5 fc

Type III - Short - N/A

REPORT NUMBER: P1048978  
CATALOG NUMBER: GALN-SA6B-730-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 118.4    | 0.0    | 118.4   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 23523.6  | 0.0    | 23523.6 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 23642.0  | 0.0    | 23642.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 9.3     | 0.0       |
| 10°-20°   | 51.9    | 0.2       |
| 20°-30°   | 560.3   | 2.4       |
| 30°-40°   | 1656.9  | 7.0       |
| 40°-50°   | 4937.9  | 20.9      |
| 50°-60°   | 7829.7  | 33.1      |
| 60°-70°   | 6535.9  | 27.6      |
| 70°-80°   | 2015.4  | 8.5       |
| 80°-90°   | 44.8    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 23642.0 | 100.0     |
| 0°-180°   | 23642.0 | 100.0     |



REPORT NUMBER: P1048978


CATALOG NUMBER: GALN-SA6B-730-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 599.7   | 2.5       |                         |      |          |
| FM   | (30°-60°)   | 14382.1 | 60.8      |                         |      |          |
| FH   | (60°-80°)   | 8507.2  | 36.0      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 34.6    | 0.1       |                         |      | G1/100   |
| BL   | (0°-30°)    | 21.7    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 42.3    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 44.2    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 10.2    | 0.0       |                         |      | G1/100   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 103.6  | 103.6  | 103.6  | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 |
| 2.5°   | 94.7   | 94.7   | 94.7   | 94.7  | 92.9  | 92.9  | 91.1  | 91.1  | 89.3  | 89.3  |
| 5°     | 100.1  | 100.1  | 98.3   | 96.5  | 96.5  | 94.7  | 92.9  | 91.1  | 91.1  | 89.3  |
| 7.5°   | 109.0  | 107.2  | 105.4  | 103.6 | 100.1 | 98.3  | 94.7  | 92.9  | 91.1  | 87.5  |
| 10°    | 119.7  | 116.1  | 112.6  | 109.0 | 105.4 | 101.8 | 98.3  | 96.5  | 92.9  | 91.1  |
| 12.5°  | 134.0  | 128.6  | 121.5  | 116.1 | 112.6 | 107.2 | 103.6 | 100.1 | 94.7  | 91.1  |
| 15°    | 146.5  | 139.4  | 130.4  | 123.3 | 117.9 | 110.8 | 105.4 | 100.1 | 96.5  | 91.1  |
| 17.5°  | 164.4  | 151.9  | 137.6  | 128.6 | 121.5 | 112.6 | 103.6 | 98.3  | 92.9  | 85.8  |
| 20°    | 194.7  | 169.7  | 142.9  | 132.2 | 121.5 | 110.8 | 100.1 | 92.9  | 87.5  | 80.4  |
| 22.5°  | 243.0  | 200.1  | 157.2  | 141.1 | 126.8 | 110.8 | 96.5  | 89.3  | 82.2  | 75.0  |
| 25°    | 335.9  | 259.1  | 182.2  | 160.8 | 139.4 | 117.9 | 96.5  | 87.5  | 80.4  | 71.5  |
| 27.5°  | 446.7  | 332.3  | 216.2  | 185.8 | 157.2 | 126.8 | 96.5  | 85.8  | 76.8  | 66.1  |
| 30°    | 559.2  | 407.3  | 253.7  | 214.4 | 175.1 | 135.8 | 96.5  | 84.0  | 73.3  | 60.7  |
| 32.5°  | 666.4  | 477.0  | 285.9  | 239.4 | 193.0 | 144.7 | 98.3  | 84.0  | 69.7  | 55.4  |
| 35°    | 775.4  | 534.2  | 291.2  | 243.0 | 194.7 | 144.7 | 96.5  | 80.4  | 66.1  | 50.0  |
| 37.5°  | 914.7  | 598.5  | 280.5  | 232.3 | 185.8 | 137.6 | 91.1  | 76.8  | 62.5  | 46.5  |
| 40°    | 1125.6 | 705.7  | 285.9  | 235.8 | 185.8 | 135.8 | 85.8  | 71.5  | 59.0  | 44.7  |
| 42.5°  | 1515.0 | 913.0  | 309.1  | 251.9 | 194.7 | 135.8 | 78.6  | 66.1  | 55.4  | 42.9  |
| 45°    | 2619.2 | 1516.8 | 414.5  | 328.7 | 243.0 | 157.2 | 71.5  | 60.7  | 51.8  | 41.1  |
| 47.5°  | 4332.5 | 2538.8 | 745.0  | 575.3 | 407.3 | 237.6 | 69.7  | 60.7  | 51.8  | 41.1  |
| 50°    | 5529.5 | 3233.8 | 938.0  | 721.8 | 505.6 | 289.4 | 73.3  | 62.5  | 53.6  | 42.9  |
| 52.5°  | 5520.6 | 3283.8 | 1045.2 | 802.2 | 561.0 | 318.0 | 76.8  | 66.1  | 57.2  | 46.5  |
| 55°    | 4907.8 | 2987.2 | 1064.8 | 818.3 | 573.5 | 326.9 | 82.2  | 71.5  | 60.7  | 50.0  |
| 57.5°  | 4102.1 | 2537.0 | 971.9  | 752.2 | 534.2 | 314.4 | 94.7  | 82.2  | 71.5  | 59.0  |
| 60°    | 3244.5 | 2001.0 | 757.5  | 598.5 | 441.3 | 282.3 | 125.1 | 109.0 | 94.7  | 78.6  |
| 62.5°  | 2240.4 | 1450.7 | 661.0  | 530.6 | 402.0 | 271.6 | 142.9 | 126.8 | 112.6 | 96.5  |
| 65°    | 1584.7 | 1091.6 | 596.7  | 486.0 | 377.0 | 266.2 | 155.4 | 137.6 | 121.5 | 103.6 |
| 67.5°  | 1184.5 | 868.3  | 550.3  | 455.6 | 360.9 | 266.2 | 171.5 | 150.1 | 130.4 | 109.0 |
| 70°    | 907.6  | 712.9  | 516.3  | 439.5 | 364.5 | 287.6 | 210.8 | 180.4 | 151.9 | 121.5 |
| 72.5°  | 739.7  | 609.2  | 477.0  | 421.6 | 366.3 | 310.9 | 255.5 | 216.2 | 176.9 | 135.8 |
| 75°    | 612.8  | 521.7  | 430.6  | 384.1 | 339.5 | 293.0 | 246.6 | 210.8 | 176.9 | 141.1 |
| 77.5°  | 407.3  | 371.6  | 334.1  | 307.3 | 280.5 | 251.9 | 225.1 | 194.7 | 166.2 | 135.8 |
| 80°    | 142.9  | 137.6  | 132.2  | 142.9 | 153.6 | 164.4 | 175.1 | 153.6 | 134.0 | 112.6 |
| 82.5°  | 21.4   | 19.7   | 17.9   | 19.7  | 21.4  | 23.2  | 25.0  | 26.8  | 28.6  | 30.4  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 |
| 0.0 | 2.5°   | 87.5  | 87.5  | 85.8  | 85.8  | 85.8  | 84.0  | 84.0  | 82.2  | 82.2  | 82.2  |
| 0.0 | 5°     | 85.8  | 85.8  | 84.0  | 82.2  | 80.4  | 80.4  | 78.6  | 76.8  | 76.8  | 75.0  |
| 0.0 | 7.5°   | 84.0  | 82.2  | 80.4  | 78.6  | 76.8  | 75.0  | 73.3  | 71.5  | 71.5  | 69.7  |
| 0.0 | 10°    | 85.8  | 82.2  | 80.4  | 76.8  | 75.0  | 73.3  | 69.7  | 67.9  | 66.1  | 66.1  |
| 0.0 | 12.5°  | 82.2  | 80.4  | 76.8  | 73.3  | 71.5  | 67.9  | 66.1  | 62.5  | 60.7  | 60.7  |
| 0.0 | 15°    | 82.2  | 78.6  | 73.3  | 69.7  | 66.1  | 64.3  | 60.7  | 57.2  | 55.4  | 53.6  |
| 0.0 | 17.5°  | 76.8  | 73.3  | 67.9  | 64.3  | 60.7  | 57.2  | 53.6  | 50.0  | 48.2  | 46.5  |
| 0.0 | 20°    | 69.7  | 66.1  | 60.7  | 55.4  | 51.8  | 48.2  | 44.7  | 41.1  | 39.3  | 37.5  |
| 0.0 | 22.5°  | 62.5  | 59.0  | 53.6  | 48.2  | 44.7  | 41.1  | 35.7  | 32.2  | 30.4  | 26.8  |
| 0.0 | 25°    | 59.0  | 53.6  | 48.2  | 42.9  | 37.5  | 33.9  | 28.6  | 23.2  | 19.7  | 16.1  |
| 0.0 | 27.5°  | 50.0  | 44.7  | 39.3  | 33.9  | 28.6  | 23.2  | 17.9  | 12.5  | 8.9   | 7.1   |
| 0.0 | 30°    | 42.9  | 37.5  | 32.2  | 26.8  | 19.7  | 14.3  | 8.9   | 1.8   | 1.8   | 1.8   |
| 0.0 | 32.5°  | 35.7  | 30.4  | 23.2  | 17.9  | 14.3  | 8.9   | 5.4   | 0.0   | 0.0   | 0.0   |
| 0.0 | 35°    | 28.6  | 23.2  | 16.1  | 10.7  | 8.9   | 5.4   | 3.6   | 0.0   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 25.0  | 19.7  | 12.5  | 5.4   | 3.6   | 3.6   | 1.8   | 0.0   | 0.0   | 0.0   |
| 0.0 | 40°    | 23.2  | 16.1  | 8.9   | 1.8   | 1.8   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 23.2  | 16.1  | 7.1   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 23.2  | 16.1  | 7.1   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 23.2  | 16.1  | 7.1   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 25.0  | 17.9  | 8.9   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 28.6  | 21.4  | 14.3  | 7.1   | 5.4   | 3.6   | 1.8   | 0.0   | 0.0   | 0.0   |
| 0.0 | 55°    | 35.7  | 32.2  | 26.8  | 23.2  | 17.9  | 12.5  | 5.4   | 0.0   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 46.5  | 46.5  | 44.7  | 42.9  | 32.2  | 21.4  | 10.7  | 0.0   | 0.0   | 0.0   |
| 0.0 | 60°    | 62.5  | 62.5  | 62.5  | 62.5  | 46.5  | 32.2  | 16.1  | 0.0   | 0.0   | 0.0   |
| 0.0 | 62.5°  | 76.8  | 73.3  | 67.9  | 64.3  | 48.2  | 32.2  | 16.1  | 0.0   | 0.0   | 0.0   |
| 0.0 | 65°    | 76.8  | 69.7  | 60.7  | 51.8  | 39.3  | 26.8  | 12.5  | 0.0   | 0.0   | 0.0   |
| 0.0 | 67.5°  | 71.5  | 57.2  | 41.1  | 26.8  | 19.7  | 14.3  | 7.1   | 0.0   | 0.0   | 0.0   |
|     | 70°    | 71.5  | 50.0  | 28.6  | 7.1   | 5.4   | 3.6   | 1.8   | 0.0   | 0.0   | 0.0   |
|     | 72.5°  | 71.5  | 48.2  | 23.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 78.6  | 53.6  | 26.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 78.6  | 53.6  | 26.8  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 69.7  | 46.5  | 23.2  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 23.2  | 16.1  | 7.1   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 |
| 0.0   | 2.5°   | 80.4  | 80.4  | 80.4  | 78.6  | 78.6  | 78.6  | 78.6  | 76.8  | 76.8  | 76.8  |
| 0.0   | 5°     | 73.3  | 73.3  | 71.5  | 71.5  | 69.7  | 69.7  | 67.9  | 67.9  | 66.1  | 66.1  |
| 0.0   | 7.5°   | 67.9  | 66.1  | 66.1  | 64.3  | 62.5  | 62.5  | 60.7  | 60.7  | 59.0  | 57.2  |
| 0.0   | 10°    | 62.5  | 60.7  | 60.7  | 59.0  | 57.2  | 55.4  | 55.4  | 53.6  | 51.8  | 50.0  |
| 0.0   | 12.5°  | 57.2  | 55.4  | 53.6  | 51.8  | 50.0  | 48.2  | 48.2  | 46.5  | 44.7  | 42.9  |
| 0.0   | 15°    | 50.0  | 48.2  | 46.5  | 44.7  | 42.9  | 41.1  | 41.1  | 39.3  | 37.5  | 35.7  |
| 0.0   | 17.5°  | 42.9  | 41.1  | 41.1  | 39.3  | 37.5  | 35.7  | 33.9  | 30.4  | 28.6  | 26.8  |
| 0.0   | 20°    | 32.2  | 30.4  | 28.6  | 26.8  | 25.0  | 21.4  | 19.7  | 16.1  | 12.5  | 10.7  |
| 0.0   | 22.5°  | 21.4  | 17.9  | 16.1  | 12.5  | 8.9   | 7.1   | 5.4   | 1.8   | 0.0   | 0.0   |
| 0.0   | 25°    | 7.1   | 5.4   | 3.6   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6 | 103.6  | 103.6 |
| 0.0 | 2.5°   | 75.0  | 75.0  | 75.0  | 73.3  | 73.3  | 73.3  | 73.3  | 73.3  | 73.3   | 73.3  |
| 0.0 | 5°     | 64.3  | 64.3  | 64.3  | 62.5  | 62.5  | 60.7  | 60.7  | 60.7  | 59.0   | 59.0  |
| 0.0 | 7.5°   | 55.4  | 53.6  | 53.6  | 51.8  | 51.8  | 50.0  | 50.0  | 50.0  | 48.2   | 48.2  |
| 0.0 | 10°    | 46.5  | 44.7  | 44.7  | 42.9  | 42.9  | 41.1  | 41.1  | 39.3  | 39.3   | 37.5  |
| 0.0 | 12.5°  | 41.1  | 39.3  | 37.5  | 35.7  | 35.7  | 33.9  | 32.2  | 32.2  | 30.4   | 28.6  |
| 0.0 | 15°    | 32.2  | 30.4  | 28.6  | 26.8  | 25.0  | 23.2  | 21.4  | 21.4  | 19.7   | 17.9  |
| 0.0 | 17.5°  | 21.4  | 17.9  | 16.1  | 14.3  | 14.3  | 12.5  | 10.7  | 8.9   | 7.1    | 5.4   |
| 0.0 | 20°    | 5.4   | 3.6   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  |
| 0.0    | 2.5°   | 73.3  | 71.5   | 71.5  | 71.5   | 73.3  | 73.3   | 73.3  | 73.3   | 73.3  | 73.3   |
| 0.0    | 5°     | 59.0  | 57.2   | 57.2  | 57.2   | 57.2  | 57.2   | 57.2  | 57.2   | 57.2  | 57.2   |
| 0.0    | 7.5°   | 48.2  | 46.5   | 46.5  | 46.5   | 46.5  | 44.7   | 44.7  | 44.7   | 44.7  | 44.7   |
| 0.0    | 10°    | 37.5  | 35.7   | 35.7  | 35.7   | 35.7  | 33.9   | 33.9  | 33.9   | 33.9  | 33.9   |
| 0.0    | 12.5°  | 26.8  | 26.8   | 25.0  | 25.0   | 25.0  | 23.2   | 23.2  | 23.2   | 23.2  | 21.4   |
| 0.0    | 15°    | 16.1  | 14.3   | 12.5  | 12.5   | 12.5  | 10.7   | 10.7  | 10.7   | 10.7  | 8.9    |
| 0.0    | 17.5°  | 3.6   | 3.6    | 1.8   | 1.8    | 1.8   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 |
| 0.0  | 2.5°   | 75.0   | 75.0  | 76.8   | 76.8  | 78.6   | 82.2  | 84.0   | 85.8  | 89.3   | 92.9  |
| 0.0  | 5°     | 59.0   | 60.7  | 60.7   | 62.5  | 64.3   | 66.1  | 67.9   | 69.7  | 73.3   | 76.8  |
| 0.0  | 7.5°   | 46.5   | 46.5  | 48.2   | 48.2  | 50.0   | 53.6  | 55.4   | 57.2  | 60.7   | 66.1  |
| 0.0  | 10°    | 35.7   | 35.7  | 37.5   | 37.5  | 39.3   | 42.9  | 44.7   | 46.5  | 50.0   | 55.4  |
| 0.0  | 12.5°  | 23.2   | 25.0  | 25.0   | 26.8  | 28.6   | 32.2  | 33.9   | 35.7  | 39.3   | 42.9  |
| 0.0  | 15°    | 10.7   | 12.5  | 12.5   | 14.3  | 16.1   | 19.7  | 21.4   | 23.2  | 26.8   | 32.2  |
| 0.0  | 17.5°  | 1.8    | 1.8   | 3.6    | 3.6   | 5.4    | 7.1   | 8.9    | 10.7  | 16.1   | 19.7  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.6    | 7.1   |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 1.8   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  |
| 0.0    | 2.5°   | 98.3  | 101.8  | 105.4 | 109.0  | 112.6 | 116.1  | 117.9 | 121.5  | 123.3 | 125.1  |
| 0.0    | 5°     | 84.0  | 87.5   | 92.9  | 96.5   | 100.1 | 103.6  | 107.2 | 109.0  | 110.8 | 112.6  |
| 0.0    | 7.5°   | 73.3  | 76.8   | 82.2  | 85.8   | 89.3  | 92.9   | 96.5  | 100.1  | 101.8 | 103.6  |
| 0.0    | 10°    | 62.5  | 67.9   | 71.5  | 76.8   | 80.4  | 84.0   | 87.5  | 91.1   | 94.7  | 96.5   |
| 0.0    | 12.5°  | 50.0  | 55.4   | 60.7  | 64.3   | 69.7  | 75.0   | 78.6  | 82.2   | 85.8  | 89.3   |
| 0.0    | 15°    | 39.3  | 44.7   | 50.0  | 53.6   | 59.0  | 64.3   | 69.7  | 73.3   | 76.8  | 80.4   |
| 0.0    | 17.5°  | 28.6  | 33.9   | 39.3  | 42.9   | 48.2  | 53.6   | 57.2  | 62.5   | 66.1  | 69.7   |
| 0.0    | 20°    | 14.3  | 19.7   | 25.0  | 30.4   | 35.7  | 41.1   | 44.7  | 50.0   | 53.6  | 57.2   |
| 0.0    | 22.5°  | 1.8   | 7.1    | 12.5  | 16.1   | 21.4  | 26.8   | 30.4  | 35.7   | 39.3  | 42.9   |
| 0.0    | 25°    | 0.0   | 1.8    | 5.4   | 7.1    | 8.9   | 12.5   | 16.1  | 19.7   | 23.2  | 26.8   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 3.6   | 7.1    | 10.7  | 14.3   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.6    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 1.8   | 3.6    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.6    | 5.4   | 8.9    | 10.7  | 12.5   |
|        | 87.5°  | 0.0   | 1.8    | 3.6   | 5.4    | 7.1   | 10.7   | 14.3  | 17.9   | 19.7  | 21.4   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 103.6 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125.1 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.4 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100.1 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.1  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 84.0  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.0  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60.7  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.5  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.2  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17.9  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5.4   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.8   |        |      |        |      |        |      |        |      |        |      |        |
| 7.1   |        |      |        |      |        |      |        |      |        |      |        |
| 16.1  |        |      |        |      |        |      |        |      |        |      |        |
| 23.2  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 |
| 0.0  | 2.5°   | 126.8  | 126.8 | 126.8  | 126.8 | 125.1  | 125.1 | 125.1  | 123.3 | 123.3  | 121.5 |
| 0.0  | 5°     | 116.1  | 117.9 | 117.9  | 117.9 | 117.9  | 117.9 | 117.9  | 117.9 | 116.1  | 116.1 |
| 0.0  | 7.5°   | 107.2  | 109.0 | 110.8  | 110.8 | 112.6  | 112.6 | 112.6  | 110.8 | 110.8  | 109.0 |
| 0.0  | 10°    | 101.8  | 103.6 | 103.6  | 105.4 | 105.4  | 105.4 | 105.4  | 105.4 | 105.4  | 105.4 |
| 0.0  | 12.5°  | 94.7   | 96.5  | 98.3   | 98.3  | 100.1  | 100.1 | 100.1  | 100.1 | 98.3   | 98.3  |
| 0.0  | 15°    | 85.8   | 89.3  | 91.1   | 92.9  | 92.9   | 94.7  | 94.7   | 94.7  | 94.7   | 94.7  |
| 0.0  | 17.5°  | 78.6   | 82.2  | 84.0   | 85.8  | 85.8   | 87.5  | 87.5   | 89.3  | 89.3   | 89.3  |
| 0.0  | 20°    | 64.3   | 67.9  | 69.7   | 73.3  | 75.0   | 76.8  | 78.6   | 80.4  | 80.4   | 82.2  |
| 0.0  | 22.5°  | 50.0   | 53.6  | 55.4   | 59.0  | 60.7   | 62.5  | 64.3   | 66.1  | 67.9   | 69.7  |
| 0.0  | 25°    | 35.7   | 39.3  | 41.1   | 44.7  | 46.5   | 48.2  | 50.0   | 51.8  | 51.8   | 53.6  |
| 0.0  | 27.5°  | 19.7   | 23.2  | 26.8   | 28.6  | 32.2   | 33.9  | 35.7   | 37.5  | 39.3   | 41.1  |
| 0.0  | 30°    | 8.9    | 10.7  | 12.5   | 16.1  | 17.9   | 19.7  | 21.4   | 25.0  | 26.8   | 28.6  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.8    | 5.4   | 7.1    | 8.9   | 10.7   | 12.5  | 12.5   | 14.3  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 3.6   | 5.4    | 7.1   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.6    | 3.6   | 3.6    | 5.4   | 5.4    | 5.4   | 5.4    | 5.4   | 5.4    | 5.4   |
|      | 82.5°  | 8.9    | 10.7  | 12.5   | 12.5  | 14.3   | 14.3  | 14.3   | 14.3  | 12.5   | 12.5  |
|      | 85°    | 17.9   | 19.7  | 21.4   | 21.4  | 23.2   | 23.2  | 23.2   | 23.2  | 23.2   | 23.2  |
|      | 87.5°  | 25.0   | 26.8  | 28.6   | 28.6  | 30.4   | 30.4  | 30.4   | 30.4  | 30.4   | 30.4  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 103.6  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 121.5  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 116.1  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109.0  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 105.4  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 98.3   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 94.7   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 89.3   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 80.4   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 69.7   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 55.4   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.9   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30.4   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 17.9   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 10.7   | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.6    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.6    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 5.4    |        |        |      |        |      |        |      |        |      |        |      |
| 12.5   |        |        |      |        |      |        |      |        |      |        |      |
| 23.2   |        |        |      |        |      |        |      |        |      |        |      |
| 30.4   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  |
| 0.0    | 2.5°   | 119.7 | 119.7  | 117.9 | 117.9  | 117.9 | 117.9  | 117.9 | 119.7  | 121.5 | 121.5  |
| 0.0    | 5°     | 114.3 | 114.3  | 112.6 | 112.6  | 112.6 | 114.3  | 114.3 | 116.1  | 117.9 | 119.7  |
| 0.0    | 7.5°   | 109.0 | 107.2  | 107.2 | 109.0  | 109.0 | 110.8  | 110.8 | 112.6  | 114.3 | 116.1  |
| 0.0    | 10°    | 105.4 | 103.6  | 103.6 | 103.6  | 105.4 | 105.4  | 107.2 | 109.0  | 110.8 | 112.6  |
| 0.0    | 12.5°  | 98.3  | 98.3   | 98.3  | 98.3   | 100.1 | 100.1  | 101.8 | 103.6  | 107.2 | 109.0  |
| 0.0    | 15°    | 94.7  | 92.9   | 92.9  | 92.9   | 92.9  | 94.7   | 94.7  | 98.3   | 101.8 | 103.6  |
| 0.0    | 17.5°  | 87.5  | 87.5   | 85.8  | 85.8   | 87.5  | 87.5   | 89.3  | 92.9   | 96.5  | 98.3   |
| 0.0    | 20°    | 80.4  | 78.6   | 76.8  | 76.8   | 78.6  | 78.6   | 80.4  | 84.0   | 87.5  | 89.3   |
| 0.0    | 22.5°  | 69.7  | 67.9   | 67.9  | 67.9   | 67.9  | 69.7   | 69.7  | 73.3   | 78.6  | 82.2   |
| 0.0    | 25°    | 55.4  | 57.2   | 57.2  | 59.0   | 59.0  | 60.7   | 62.5  | 66.1   | 71.5  | 75.0   |
| 0.0    | 27.5°  | 42.9  | 44.7   | 44.7  | 48.2   | 50.0  | 51.8   | 53.6  | 59.0   | 64.3  | 67.9   |
| 0.0    | 30°    | 32.2  | 33.9   | 35.7  | 37.5   | 41.1  | 44.7   | 48.2  | 53.6   | 59.0  | 62.5   |
| 0.0    | 32.5°  | 19.7  | 23.2   | 25.0  | 28.6   | 32.2  | 35.7   | 39.3  | 44.7   | 51.8  | 57.2   |
| 0.0    | 35°    | 14.3  | 16.1   | 19.7  | 21.4   | 25.0  | 28.6   | 32.2  | 39.3   | 44.7  | 51.8   |
| 0.0    | 37.5°  | 7.1   | 10.7   | 14.3  | 17.9   | 21.4  | 25.0   | 28.6  | 35.7   | 42.9  | 48.2   |
| 0.0    | 40°    | 5.4   | 8.9    | 10.7  | 14.3   | 19.7  | 23.2   | 26.8  | 33.9   | 41.1  | 48.2   |
| 0.0    | 42.5°  | 3.6   | 5.4    | 7.1   | 12.5   | 16.1  | 21.4   | 26.8  | 33.9   | 41.1  | 48.2   |
| 0.0    | 45°    | 3.6   | 3.6    | 5.4   | 10.7   | 16.1  | 23.2   | 28.6  | 35.7   | 41.1  | 48.2   |
| 0.0    | 47.5°  | 3.6   | 5.4    | 7.1   | 14.3   | 17.9  | 23.2   | 28.6  | 33.9   | 41.1  | 46.5   |
| 0.0    | 50°    | 5.4   | 7.1    | 8.9   | 16.1   | 19.7  | 25.0   | 28.6  | 35.7   | 41.1  | 48.2   |
| 0.0    | 52.5°  | 3.6   | 5.4    | 7.1   | 14.3   | 19.7  | 26.8   | 32.2  | 39.3   | 46.5  | 51.8   |
| 0.0    | 55°    | 1.8   | 1.8    | 1.8   | 10.7   | 21.4  | 30.4   | 41.1  | 46.5   | 53.6  | 59.0   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 7.1    | 21.4  | 33.9   | 46.5  | 53.6   | 60.7  | 66.1   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 7.1    | 21.4  | 33.9   | 46.5  | 55.4   | 64.3  | 73.3   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 7.1    | 17.9  | 28.6   | 39.3  | 53.6   | 69.7  | 84.0   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 5.4    | 14.3  | 23.2   | 32.2  | 53.6   | 75.0  | 94.7   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 5.4    | 14.3  | 21.4   | 30.4  | 53.6   | 75.0  | 98.3   |
|        | 70°    | 0.0   | 0.0    | 0.0   | 5.4    | 14.3  | 23.2   | 32.2  | 53.6   | 75.0  | 96.5   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 5.4    | 16.1  | 25.0   | 35.7  | 53.6   | 71.5  | 89.3   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 7.1    | 16.1  | 26.8   | 37.5  | 53.6   | 69.7  | 84.0   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 5.4    | 16.1  | 25.0   | 35.7  | 51.8   | 67.9  | 82.2   |
|        | 80°    | 5.4   | 3.6    | 3.6   | 8.9    | 16.1  | 23.2   | 30.4  | 46.5   | 64.3  | 80.4   |
|        | 82.5°  | 10.7  | 10.7   | 8.9   | 12.5   | 16.1  | 21.4   | 26.8  | 41.1   | 57.2  | 71.5   |
|        | 85°    | 21.4  | 21.4   | 19.7  | 21.4   | 21.4  | 23.2   | 25.0  | 32.2   | 39.3  | 46.5   |
|        | 87.5°  | 28.6  | 28.6   | 26.8  | 26.8   | 26.8  | 25.0   | 25.0  | 25.0   | 25.0  | 23.2   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 103.6 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 123.3 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 121.5 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.9 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.8 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.2 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.8 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.9  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.8  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78.6  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 73.3  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.9  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.5  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.2  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.4  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.4  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.4  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.6  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 51.8  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.6  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.3  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 73.3  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 82.2  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 98.3  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 116.1 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 119.7 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.9 |        |      |        |      |        |      |        |      |        |      |        |
| 107.2 |        |      |        |      |        |      |        |      |        |      |        |
| 100.1 |        |      |        |      |        |      |        |      |        |      |        |
| 98.3  |        |      |        |      |        |      |        |      |        |      |        |
| 96.5  |        |      |        |      |        |      |        |      |        |      |        |
| 85.8  |        |      |        |      |        |      |        |      |        |      |        |
| 53.6  |        |      |        |      |        |      |        |      |        |      |        |
| 23.2  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6 | 103.6  | 103.6  |
| 0.0  | 2.5°   | 125.1  | 126.8 | 126.8  | 128.6 | 130.4  | 132.2 | 132.2  | 134.0 | 134.0  | 134.0  |
| 0.0  | 5°     | 123.3  | 126.8 | 128.6  | 130.4 | 132.2  | 134.0 | 135.8  | 137.6 | 139.4  | 139.4  |
| 0.0  | 7.5°   | 121.5  | 123.3 | 126.8  | 128.6 | 132.2  | 134.0 | 137.6  | 139.4 | 141.1  | 142.9  |
| 0.0  | 10°    | 117.9  | 121.5 | 125.1  | 128.6 | 132.2  | 135.8 | 139.4  | 142.9 | 146.5  | 148.3  |
| 0.0  | 12.5°  | 114.3  | 119.7 | 123.3  | 126.8 | 132.2  | 137.6 | 141.1  | 146.5 | 150.1  | 153.6  |
| 0.0  | 15°    | 112.6  | 116.1 | 121.5  | 125.1 | 132.2  | 139.4 | 144.7  | 151.9 | 159.0  | 164.4  |
| 0.0  | 17.5°  | 107.2  | 114.3 | 119.7  | 125.1 | 132.2  | 141.1 | 148.3  | 155.4 | 166.2  | 176.9  |
| 0.0  | 20°    | 100.1  | 105.4 | 112.6  | 117.9 | 128.6  | 137.6 | 148.3  | 157.2 | 173.3  | 189.4  |
| 0.0  | 22.5°  | 92.9   | 100.1 | 105.4  | 112.6 | 125.1  | 135.8 | 148.3  | 159.0 | 185.8  | 210.8  |
| 0.0  | 25°    | 85.8   | 94.7  | 101.8  | 109.0 | 123.3  | 137.6 | 151.9  | 166.2 | 210.8  | 255.5  |
| 0.0  | 27.5°  | 82.2   | 89.3  | 98.3   | 105.4 | 123.3  | 142.9 | 160.8  | 178.7 | 250.1  | 319.8  |
| 0.0  | 30°    | 76.8   | 85.8  | 92.9   | 101.8 | 125.1  | 148.3 | 171.5  | 194.7 | 303.7  | 412.7  |
| 0.0  | 32.5°  | 71.5   | 80.4  | 89.3   | 98.3  | 128.6  | 159.0 | 187.6  | 218.0 | 360.9  | 502.0  |
| 0.0  | 35°    | 66.1   | 76.8  | 85.8   | 94.7  | 134.0  | 175.1 | 214.4  | 253.7 | 412.7  | 569.9  |
| 0.0  | 37.5°  | 64.3   | 75.0  | 84.0   | 92.9  | 135.8  | 176.9 | 219.8  | 260.8 | 418.1  | 575.3  |
| 0.0  | 40°    | 66.1   | 75.0  | 85.8   | 94.7  | 130.4  | 166.2 | 200.1  | 235.8 | 400.2  | 562.8  |
| 0.0  | 42.5°  | 66.1   | 76.8  | 87.5   | 98.3  | 126.8  | 155.4 | 184.0  | 212.6 | 394.8  | 577.1  |
| 0.0  | 45°    | 64.3   | 75.0  | 85.8   | 96.5  | 123.3  | 148.3 | 175.1  | 200.1 | 427.0  | 652.1  |
| 0.0  | 47.5°  | 62.5   | 73.3  | 84.0   | 94.7  | 121.5  | 148.3 | 175.1  | 201.9 | 552.1  | 900.5  |
| 0.0  | 50°    | 62.5   | 73.3  | 82.2   | 91.1  | 123.3  | 157.2 | 189.4  | 221.5 | 804.0  | 1384.6 |
| 0.0  | 52.5°  | 66.1   | 75.0  | 82.2   | 89.3  | 126.8  | 166.2 | 203.7  | 241.2 | 1021.9 | 1800.9 |
| 0.0  | 55°    | 71.5   | 76.8  | 84.0   | 89.3  | 135.8  | 180.4 | 226.9  | 271.6 | 1088.0 | 1904.5 |
| 0.0  | 57.5°  | 78.6   | 84.0  | 89.3   | 94.7  | 151.9  | 209.0 | 264.4  | 321.6 | 1093.4 | 1863.4 |
| 0.0  | 60°    | 87.5   | 94.7  | 100.1  | 105.4 | 166.2  | 228.7 | 289.4  | 350.2 | 989.8  | 1627.6 |
| 0.0  | 62.5°  | 107.2  | 116.1 | 123.3  | 132.2 | 191.2  | 248.3 | 307.3  | 364.5 | 821.8  | 1279.2 |
| 0.0  | 65°    | 123.3  | 130.4 | 137.6  | 144.7 | 201.9  | 260.8 | 318.0  | 375.2 | 696.8  | 1018.4 |
| 0.0  | 67.5°  | 126.8  | 134.0 | 139.4  | 146.5 | 205.5  | 264.4 | 321.6  | 380.5 | 596.7  | 811.1  |
|      | 70°    | 128.6  | 137.6 | 148.3  | 157.2 | 218.0  | 278.7 | 337.7  | 398.4 | 528.8  | 659.3  |
|      | 72.5°  | 123.3  | 141.1 | 157.2  | 173.3 | 230.5  | 285.9 | 343.0  | 398.4 | 491.3  | 584.2  |
|      | 75°    | 123.3  | 148.3 | 171.5  | 194.7 | 237.6  | 278.7 | 321.6  | 362.7 | 434.1  | 505.6  |
|      | 77.5°  | 130.4  | 162.6 | 194.7  | 226.9 | 251.9  | 275.1 | 300.2  | 323.4 | 369.8  | 416.3  |
|      | 80°    | 130.4  | 164.4 | 196.5  | 230.5 | 241.2  | 253.7 | 264.4  | 275.1 | 280.5  | 285.9  |
|      | 82.5°  | 112.6  | 139.4 | 166.2  | 193.0 | 180.4  | 167.9 | 155.4  | 142.9 | 134.0  | 123.3  |
|      | 85°    | 57.2   | 62.5  | 66.1   | 69.7  | 64.3   | 59.0  | 53.6   | 48.2  | 44.7   | 39.3   |
|      | 87.5°  | 23.2   | 23.2  | 21.4   | 21.4  | 21.4   | 21.4  | 19.7   | 19.7  | 19.7   | 19.7   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 103.6  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 134.0  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 139.4  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 144.7  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 151.9  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 159.0  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 173.3  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 191.2  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 219.8  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 280.5  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 380.5  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 528.8  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 716.4  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 895.1  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1016.6 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1107.7 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1198.8 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1377.5 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1734.8 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2644.2 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4050.2 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5099.0 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5215.1 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4705.9 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4023.4 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3144.4 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2376.2 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1754.4 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1241.7 |        |        |      |        |      |        |      |        |      |        |      |
| 923.7  |        |        |      |        |      |        |      |        |      |        |      |
| 671.8  |        |        |      |        |      |        |      |        |      |        |      |
| 505.6  |        |        |      |        |      |        |      |        |      |        |      |
| 284.1  |        |        |      |        |      |        |      |        |      |        |      |
| 128.6  |        |        |      |        |      |        |      |        |      |        |      |
| 37.5   |        |        |      |        |      |        |      |        |      |        |      |
| 17.9   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 103.6  | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   |
| 0.0    | 2.5°   | 134.0  | 132.2   | 132.2   | 130.4   | 128.6   | 126.8   | 125.1   | 123.3   | 121.5   | 119.7   |
| 0.0    | 5°     | 139.4  | 139.4   | 139.4   | 137.6   | 137.6   | 135.8   | 135.8   | 134.0   | 132.2   | 130.4   |
| 0.0    | 7.5°   | 144.7  | 146.5   | 146.5   | 148.3   | 148.3   | 148.3   | 148.3   | 146.5   | 146.5   | 146.5   |
| 0.0    | 10°    | 153.6  | 155.4   | 157.2   | 159.0   | 160.8   | 162.6   | 162.6   | 164.4   | 164.4   | 164.4   |
| 0.0    | 12.5°  | 164.4  | 169.7   | 173.3   | 178.7   | 182.2   | 187.6   | 191.2   | 196.5   | 200.1   | 203.7   |
| 0.0    | 15°    | 180.4  | 189.4   | 200.1   | 209.0   | 218.0   | 230.5   | 244.8   | 257.3   | 269.8   | 289.4   |
| 0.0    | 17.5°  | 203.7  | 232.3   | 260.8   | 287.6   | 316.2   | 378.8   | 441.3   | 502.0   | 564.6   | 655.7   |
| 0.0    | 20°    | 248.3  | 334.1   | 418.1   | 503.8   | 587.8   | 807.5   | 1025.5  | 1245.3  | 1463.2  | 1697.3  |
| 0.0    | 22.5°  | 348.4  | 559.2   | 770.0   | 980.8   | 1191.7  | 1650.8  | 2108.2  | 2567.4  | 3024.7  | 3562.5  |
| 0.0    | 25°    | 505.6  | 893.3   | 1281.0  | 1666.9  | 2054.6  | 2772.8  | 3492.8  | 4211.0  | 4929.2  | 5627.8  |
| 0.0    | 27.5°  | 736.1  | 1329.2  | 1922.4  | 2513.8  | 3106.9  | 4080.6  | 5056.1  | 6029.8  | 7003.5  | 7793.2  |
| 0.0    | 30°    | 1020.2 | 1824.1  | 2628.1  | 3432.1  | 4236.0  | 5343.7  | 6451.4  | 7557.3  | 8665.0  | 9528.0  |
| 0.0    | 32.5°  | 1288.1 | 2272.6  | 3257.0  | 4239.6  | 5224.0  | 6485.4  | 7748.5  | 9009.9  | 10271.2 | 11214.5 |
| 0.0    | 35°    | 1463.2 | 2653.1  | 3844.8  | 5034.7  | 6224.5  | 7589.5  | 8954.5  | 10317.7 | 11682.6 | 12760.0 |
| 0.0    | 37.5°  | 1638.3 | 3012.2  | 4384.3  | 5758.2  | 7130.4  | 8629.3  | 10128.3 | 11627.2 | 13126.2 | 14457.2 |
| 0.0    | 40°    | 1834.8 | 3446.4  | 5056.1  | 6667.6  | 8277.4  | 10053.2 | 11827.3 | 13603.2 | 15377.3 | 17255.1 |
| 0.0    | 42.5°  | 2176.1 | 4166.4  | 6158.4  | 8148.7  | 10139.0 | 12488.4 | 14837.8 | 17185.4 | 19534.8 | 22214.7 |
| 0.0    | 45°    | 2817.5 | 5622.5  | 8429.2  | 11234.2 | 14039.2 | 17151.4 | 20265.5 | 23377.8 | 26490.0 | 30056.1 |
| 0.0    | 47.5°  | 4387.9 | 8247.0  | 12104.3 | 15963.3 | 19820.6 | 23181.2 | 26540.1 | 29900.7 | 33259.5 | 36811.3 |
| 0.0    | 50°    | 6714.1 | 11205.6 | 15697.1 | 20186.9 | 24678.4 | 27719.2 | 30758.2 | 33799.0 | 36838.1 | 40216.5 |
| 0.0    | 52.5°  | 8397.1 | 13076.2 | 17757.1 | 22436.2 | 27115.3 | 29859.6 | 32605.6 | 35349.8 | 38094.0 | 41251.0 |
| 0.0    | 55°    | 8523.9 | 13176.2 | 17830.3 | 22482.7 | 27135.0 | 29891.7 | 32648.5 | 35405.2 | 38161.9 | 41508.3 |
| 0.0    | 57.5°  | 7546.6 | 12161.4 | 16774.5 | 21389.3 | 26002.3 | 29141.4 | 32278.6 | 35417.7 | 38555.0 | 42172.9 |
| 0.0    | 60°    | 6419.3 | 11035.9 | 15650.7 | 20267.3 | 24882.1 | 28498.2 | 32116.1 | 35732.1 | 39348.2 | 42737.4 |
| 0.0    | 62.5°  | 5007.9 | 9756.7  | 14507.3 | 19256.1 | 24004.9 | 27676.3 | 31347.8 | 35017.5 | 38689.0 | 41231.3 |
| 0.0    | 65°    | 3732.2 | 8343.5  | 12954.7 | 17564.1 | 22175.4 | 25116.1 | 28056.9 | 30995.9 | 33936.6 | 35510.6 |
| 0.0    | 67.5°  | 2697.8 | 6674.8  | 10650.0 | 14627.0 | 18602.2 | 20706.8 | 22811.4 | 24914.2 | 27018.9 | 28223.0 |
|        | 70°    | 1824.1 | 4579.1  | 7332.2  | 10087.2 | 12840.3 | 14569.8 | 16301.0 | 18030.4 | 19759.9 | 21385.7 |
|        | 72.5°  | 1263.1 | 2810.3  | 4359.3  | 5906.5  | 7453.7  | 9193.9  | 10932.3 | 12672.4 | 14410.8 | 16131.3 |
|        | 75°    | 837.9  | 1541.8  | 2247.6  | 2951.5  | 3655.4  | 4943.5  | 6233.5  | 7521.6  | 8809.8  | 9835.3  |
|        | 77.5°  | 594.9  | 805.8   | 1018.4  | 1229.2  | 1440.0  | 1681.2  | 1924.2  | 2165.4  | 2406.6  | 2772.8  |
|        | 80°    | 282.3  | 309.1   | 335.9   | 360.9   | 387.7   | 475.2   | 562.8   | 650.3   | 737.9   | 830.8   |
|        | 82.5°  | 134.0  | 144.7   | 155.4   | 164.4   | 175.1   | 184.0   | 193.0   | 201.9   | 210.8   | 201.9   |
|        | 85°    | 35.7   | 35.7    | 37.5    | 37.5    | 37.5    | 37.5    | 37.5    | 37.5    | 37.5    | 35.7    |
|        | 87.5°  | 16.1   | 16.1    | 16.1    | 16.1    | 16.1    | 16.1    | 16.1    | 14.3    | 14.3    | 12.5    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    | 275°   | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|--------|------|--------|------|--------|------|--------|------|--------|
| 103.6   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 117.9   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 128.6   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 144.7   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 166.2   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 205.5   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 310.9   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 745.0   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1933.1  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4100.3  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6326.4  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8582.9  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10392.7 | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12159.7 | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13837.3 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15790.0 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19132.8 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24894.6 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 33622.2 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40363.0 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43595.0 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44407.9 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44856.4 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45790.7 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46124.8 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43775.5 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37086.4 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29429.0 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23009.7 |        |        |      |        |      |        |      |        |      |        |
| 17851.8 |        |        |      |        |      |        |      |        |      |        |
| 10860.8 |        |        |      |        |      |        |      |        |      |        |
| 3139.1  |        |        |      |        |      |        |      |        |      |        |
| 923.7   |        |        |      |        |      |        |      |        |      |        |
| 191.2   |        |        |      |        |      |        |      |        |      |        |
| 33.9    |        |        |      |        |      |        |      |        |      |        |
| 12.5    |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |
| 0.0     |        |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   |
| 0.0  | 2.5°   | 116.1   | 114.3   | 112.6   | 110.8   | 109.0   | 105.4   | 105.4   | 103.6   | 103.6   |
| 0.0  | 5°     | 126.8   | 125.1   | 123.3   | 121.5   | 121.5   | 119.7   | 117.9   | 117.9   | 116.1   |
| 0.0  | 7.5°   | 144.7   | 142.9   | 141.1   | 139.4   | 139.4   | 137.6   | 137.6   | 135.8   | 135.8   |
| 0.0  | 10°    | 166.2   | 166.2   | 166.2   | 166.2   | 166.2   | 164.4   | 164.4   | 164.4   | 162.6   |
| 0.0  | 12.5°  | 209.0   | 210.8   | 214.4   | 218.0   | 223.3   | 223.3   | 223.3   | 221.5   | 221.5   |
| 0.0  | 15°    | 330.5   | 350.2   | 364.5   | 378.8   | 391.3   | 419.9   | 416.3   | 410.9   | 407.3   |
| 0.0  | 17.5°  | 836.1   | 925.5   | 973.7   | 1020.2  | 1068.4  | 1200.6  | 1179.2  | 1157.7  | 1138.1  |
| 0.0  | 20°    | 2167.2  | 2401.2  | 2556.6  | 2712.1  | 2869.3  | 3117.6  | 3056.9  | 2996.1  | 2935.4  |
| 0.0  | 22.5°  | 4636.2  | 5174.0  | 5408.1  | 5642.1  | 5874.4  | 6174.5  | 5979.8  | 5785.0  | 5592.1  |
| 0.0  | 25°    | 7023.2  | 7721.7  | 8116.6  | 8511.4  | 8904.5  | 9076.0  | 8822.3  | 8566.8  | 8313.1  |
| 0.0  | 27.5°  | 9372.5  | 10162.2 | 10510.6 | 10857.2 | 11205.6 | 11564.7 | 11250.3 | 10934.0 | 10619.6 |
| 0.0  | 30°    | 11255.6 | 12118.6 | 12495.5 | 12870.7 | 13247.7 | 13497.8 | 13172.7 | 12845.7 | 12520.5 |
| 0.0  | 32.5°  | 13103.0 | 14046.3 | 14459.0 | 14871.7 | 15282.6 | 15641.7 | 15241.5 | 14839.6 | 14439.4 |
| 0.0  | 35°    | 14912.8 | 15990.1 | 16558.3 | 17126.4 | 17694.6 | 18028.7 | 17553.4 | 17076.4 | 16601.2 |
| 0.0  | 37.5°  | 17121.1 | 18452.1 | 19088.1 | 19724.1 | 20360.2 | 20969.4 | 20445.9 | 19920.7 | 19397.2 |
| 0.0  | 40°    | 21010.5 | 22888.2 | 23863.7 | 24841.0 | 25816.5 | 26602.6 | 25941.5 | 25280.5 | 24619.5 |
| 0.0  | 42.5°  | 27574.5 | 30254.4 | 31656.9 | 33057.6 | 34460.1 | 35687.5 | 34992.5 | 34297.5 | 33602.5 |
| 0.0  | 45°    | 37188.2 | 40754.3 | 42464.1 | 44172.1 | 45881.9 | 46778.7 | 45778.2 | 44776.0 | 43775.5 |
| 0.0  | 47.5°  | 43913.0 | 47464.8 | 48987.0 | 50509.2 | 52031.4 | 53055.1 | 51831.3 | 50607.4 | 49385.4 |
| 0.0  | 50°    | 46971.7 | 50350.2 | 51877.7 | 53403.5 | 54931.0 | 55743.9 | 54330.7 | 52915.7 | 51502.5 |
| 0.0  | 52.5°  | 47563.1 | 50720.0 | 52542.3 | 54366.5 | 56188.8 | 57275.1 | 55606.4 | 53935.9 | 52267.2 |
| 0.0  | 55°    | 48202.7 | 51549.0 | 53662.5 | 55777.9 | 57891.4 | 59395.8 | 57509.1 | 55620.7 | 53734.0 |
| 0.0  | 57.5°  | 49406.8 | 53024.7 | 55132.9 | 57239.3 | 59347.5 | 60624.9 | 58732.9 | 56839.1 | 54947.1 |
| 0.0  | 60°    | 49514.0 | 52901.4 | 54713.1 | 56526.5 | 58338.1 | 59142.1 | 57332.2 | 55520.6 | 53710.8 |
| 0.0  | 62.5°  | 46317.8 | 48860.1 | 50117.9 | 51375.7 | 52633.5 | 53507.1 | 51618.7 | 49728.4 | 47840.0 |
| 0.0  | 65°    | 38660.4 | 40234.4 | 41236.7 | 42239.0 | 43241.3 | 44282.9 | 42553.4 | 40824.0 | 39094.5 |
| 0.0  | 67.5°  | 30633.2 | 31837.3 | 33157.6 | 34478.0 | 35798.3 | 36911.3 | 35526.7 | 34140.3 | 32755.7 |
|      | 70°    | 24635.5 | 26259.6 | 27744.2 | 29228.9 | 30713.6 | 31624.7 | 30234.8 | 28843.0 | 27453.0 |
|      | 72.5°  | 19572.3 | 21292.8 | 22532.7 | 23770.8 | 25010.7 | 25234.0 | 24212.1 | 23190.2 | 22170.0 |
|      | 75°    | 11884.5 | 12910.0 | 12935.0 | 12958.3 | 12983.3 | 13195.9 | 12349.0 | 11502.2 | 10657.1 |
|      | 77.5°  | 3505.3  | 3871.6  | 4173.5  | 4473.7  | 4775.6  | 5140.1  | 4829.2  | 4516.5  | 4205.7  |
|      | 80°    | 1014.8  | 1107.7  | 1186.3  | 1263.1  | 1341.7  | 1295.3  | 1222.0  | 1148.8  | 1075.5  |
|      | 82.5°  | 182.2   | 171.5   | 169.7   | 167.9   | 167.9   | 159.0   | 144.7   | 130.4   | 116.1   |
|      | 85°    | 32.2    | 30.4    | 28.6    | 26.8    | 25.0    | 23.2    | 19.7    | 17.9    | 14.3    |
|      | 87.5°  | 10.7    | 8.9     | 7.1     | 5.4     | 5.4     | 1.8     | 1.8     | 1.8     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   | 103.6   |
| 0.0  | 0.0    | 2.5°   | 101.8   | 100.1   | 100.1   | 100.1   | 100.1   | 98.3    | 98.3    | 98.3    | 98.3    |
| 0.0  | 0.0    | 5°     | 112.6   | 112.6   | 110.8   | 110.8   | 109.0   | 109.0   | 107.2   | 107.2   | 105.4   |
| 0.0  | 0.0    | 7.5°   | 132.2   | 130.4   | 128.6   | 126.8   | 125.1   | 121.5   | 119.7   | 117.9   | 117.9   |
| 0.0  | 0.0    | 10°    | 159.0   | 155.4   | 153.6   | 150.1   | 148.3   | 144.7   | 141.1   | 137.6   | 134.0   |
| 0.0  | 0.0    | 12.5°  | 209.0   | 201.9   | 196.5   | 189.4   | 182.2   | 176.9   | 169.7   | 164.4   | 157.2   |
| 0.0  | 0.0    | 15°    | 362.7   | 344.8   | 325.2   | 301.9   | 276.9   | 253.7   | 228.7   | 214.4   | 198.3   |
| 0.0  | 0.0    | 17.5°  | 927.2   | 834.3   | 739.7   | 662.8   | 586.0   | 511.0   | 434.1   | 378.8   | 323.4   |
| 0.0  | 0.0    | 20°    | 2360.1  | 2102.8  | 1845.6  | 1591.9  | 1336.4  | 1082.7  | 827.2   | 698.6   | 569.9   |
| 0.0  | 0.0    | 22.5°  | 4441.5  | 3964.5  | 3485.7  | 3022.9  | 2558.4  | 2095.7  | 1633.0  | 1341.7  | 1052.3  |
| 0.0  | 0.0    | 25°    | 6855.2  | 6254.9  | 5654.6  | 4893.5  | 4130.6  | 3369.5  | 2608.4  | 2135.0  | 1661.5  |
| 0.0  | 0.0    | 27.5°  | 8920.5  | 8229.1  | 7537.7  | 6612.2  | 5686.8  | 4761.3  | 3835.8  | 3130.1  | 2426.2  |
| 0.0  | 0.0    | 30°    | 10708.9 | 9965.7  | 9222.5  | 8145.1  | 7067.8  | 5990.5  | 4913.2  | 4030.6  | 3148.0  |
| 0.0  | 0.0    | 32.5°  | 12259.7 | 11370.0 | 10480.2 | 9369.0  | 8257.7  | 7146.4  | 6035.2  | 4952.5  | 3869.8  |
| 0.0  | 0.0    | 35°    | 14048.1 | 13010.1 | 11970.3 | 10737.5 | 9503.0  | 8270.2  | 7037.4  | 5815.4  | 4591.6  |
| 0.0  | 0.0    | 37.5°  | 16320.7 | 15046.8 | 13771.2 | 12397.3 | 11023.4 | 9651.3  | 8277.4  | 6880.2  | 5483.1  |
| 0.0  | 0.0    | 40°    | 20671.0 | 19027.4 | 17383.7 | 15638.2 | 13890.9 | 12145.4 | 10399.8 | 8684.7  | 6969.6  |
| 0.0  | 0.0    | 42.5°  | 28466.0 | 26245.3 | 24024.5 | 21701.9 | 19377.5 | 17055.0 | 14730.6 | 12311.5 | 9890.7  |
| 0.0  | 0.0    | 45°    | 37263.3 | 34508.3 | 31751.6 | 29144.9 | 26536.5 | 23929.8 | 21323.2 | 18003.6 | 14684.1 |
| 0.0  | 0.0    | 47.5°  | 42210.4 | 39235.7 | 36261.0 | 33793.7 | 31326.4 | 28859.1 | 26391.8 | 22813.2 | 19234.6 |
| 0.0  | 0.0    | 50°    | 44030.9 | 41002.6 | 37974.3 | 35703.6 | 33431.0 | 31160.2 | 28887.7 | 25303.7 | 21718.0 |
| 0.0  | 0.0    | 52.5°  | 44418.6 | 41329.6 | 38240.5 | 35955.5 | 33670.4 | 31387.1 | 29102.0 | 25541.3 | 21980.6 |
| 0.0  | 0.0    | 55°    | 45215.5 | 41901.3 | 38585.4 | 35980.5 | 33375.6 | 30770.7 | 28165.9 | 24548.0 | 20930.1 |
| 0.0  | 0.0    | 57.5°  | 46257.1 | 42858.9 | 39460.8 | 36493.2 | 33525.7 | 30559.9 | 27592.4 | 23636.8 | 19681.3 |
| 0.0  | 0.0    | 60°    | 45983.7 | 43026.9 | 40068.2 | 36889.9 | 33709.7 | 30531.3 | 27351.2 | 23000.8 | 18648.6 |
| 0.0  | 0.0    | 62.5°  | 41238.5 | 38883.7 | 36527.2 | 33913.4 | 31297.8 | 28684.0 | 26070.2 | 21591.2 | 17112.1 |
| 0.0  | 0.0    | 65°    | 33925.9 | 32207.2 | 30488.5 | 28385.6 | 26281.0 | 24178.2 | 22075.3 | 18059.0 | 14044.5 |
| 0.0  | 0.0    | 67.5°  | 27495.9 | 25559.2 | 23620.7 | 21944.9 | 20267.3 | 18591.4 | 16913.8 | 13753.3 | 10592.8 |
|      |        | 70°    | 21844.8 | 19738.4 | 17630.2 | 15993.7 | 14355.4 | 12718.9 | 11082.3 | 8981.3  | 6882.0  |
|      |        | 72.5°  | 17348.0 | 15448.8 | 13549.6 | 11804.1 | 10056.8 | 8311.3  | 6564.0  | 5322.3  | 4080.6  |
|      |        | 75°    | 8291.6  | 7532.3  | 6773.0  | 5860.1  | 4947.1  | 4034.2  | 3121.2  | 2579.9  | 2040.3  |
|      |        | 77.5°  | 3073.0  | 2663.8  | 2252.9  | 1881.3  | 1509.7  | 1139.9  | 768.2   | 703.9   | 639.6   |
|      |        | 80°    | 795.0   | 693.2   | 589.6   | 516.3   | 441.3   | 368.0   | 294.8   | 266.2   | 239.4   |
|      |        | 82.5°  | 91.1    | 84.0    | 78.6    | 75.0    | 69.7    | 66.1    | 60.7    | 55.4    | 50.0    |
|      |        | 85°    | 5.4     | 3.6     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1048978  
CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5°  | 360°   |
|--------|------|--------|---------|--------|
| 0.0    | 0.0  | 0°     | 103.6   | 103.6  |
| 0.0    | 0.0  | 2.5°   | 96.5    | 94.7   |
| 0.0    | 0.0  | 5°     | 101.8   | 100.1  |
| 0.0    | 0.0  | 7.5°   | 112.6   | 109.0  |
| 0.0    | 0.0  | 10°    | 123.3   | 119.7  |
| 0.0    | 0.0  | 12.5°  | 139.4   | 134.0  |
| 0.0    | 0.0  | 15°    | 157.2   | 146.5  |
| 0.0    | 0.0  | 17.5°  | 187.6   | 164.4  |
| 0.0    | 0.0  | 20°    | 253.7   | 194.7  |
| 0.0    | 0.0  | 22.5°  | 357.3   | 243.0  |
| 0.0    | 0.0  | 25°    | 525.3   | 335.9  |
| 0.0    | 0.0  | 27.5°  | 730.7   | 446.7  |
| 0.0    | 0.0  | 30°    | 971.9   | 559.2  |
| 0.0    | 0.0  | 32.5°  | 1184.5  | 666.4  |
| 0.0    | 0.0  | 35°    | 1461.4  | 775.4  |
| 0.0    | 0.0  | 37.5°  | 1802.7  | 914.7  |
| 0.0    | 0.0  | 40°    | 2331.5  | 1125.6 |
| 0.0    | 0.0  | 42.5°  | 3283.8  | 1515.0 |
| 0.0    | 0.0  | 45°    | 5333.0  | 2619.2 |
| 0.0    | 0.0  | 47.5°  | 8205.9  | 4332.5 |
| 0.0    | 0.0  | 50°    | 10038.9 | 5529.5 |
| 0.0    | 0.0  | 52.5°  | 10189.0 | 5520.6 |
| 0.0    | 0.0  | 55°    | 9301.1  | 4907.8 |
| 0.0    | 0.0  | 57.5°  | 7936.1  | 4102.1 |
| 0.0    | 0.0  | 60°    | 6596.2  | 3244.5 |
| 0.0    | 0.0  | 62.5°  | 5197.2  | 2240.4 |
| 0.0    | 0.0  | 65°    | 3798.3  | 1584.7 |
| 0.0    | 0.0  | 67.5°  | 2728.1  | 1184.5 |
|        |      | 70°    | 1793.8  | 907.6  |
|        |      | 72.5°  | 1168.4  | 739.7  |
|        |      | 75°    | 786.1   | 612.8  |
|        |      | 77.5°  | 459.2   | 407.3  |
|        |      | 80°    | 162.6   | 142.9  |
|        |      | 82.5°  | 30.4    | 21.4   |
|        |      | 85°    | 0.0     | 0.0    |
|        |      | 87.5°  | 0.0     | 0.0    |
|        |      | 90°    | 0.0     | 0.0    |
|        |      | 92.5°  | 0.0     | 0.0    |
|        |      | 95°    | 0.0     | 0.0    |
|        |      | 97.5°  | 0.0     | 0.0    |
|        |      | 100°   | 0.0     | 0.0    |
|        |      | 102.5° | 0.0     | 0.0    |
|        |      | 105°   | 0.0     | 0.0    |
|        |      | 107.5° | 0.0     | 0.0    |
|        |      | 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1048978

CATALOG NUMBER: GALN-SA6B-730-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2985  
 CIE  $u'$ : 0.2504  
 CIE  $v'$ : 0.5243  
 Duv: 0.0019  
 CIE x: 0.4408  
 CIE y: 0.4101  
 CIE z: 0.1491  
 Peak Wavelength (nm): 595  
 Dominant Wavelength (nm): 582  
 Purity: 55.41818  
 R<sub>f</sub>: 73.8  
 R<sub>g</sub>: 94.4

CRI (Ra): 70.8  
 R1: 66.3  
 R2: 80.6  
 R3: 94.5  
 R4: 68.2  
 R5: 66.5  
 R6: 74.7  
 R7: 76.2  
 R8: 39.6  
 R9: -43.2  
 R10: 57.6  
 R11: 64.8  
 R12: 53.5  
 R13: 68.7  
 R14: 97.0  
 R15: 56.4



### Test Conditions

Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

**CIE 1931 Chromaticity Diagram**



**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

### Photopic Flux vs. Wavelength



### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-4

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.19

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 142                         | NR               | 620       | 803                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 189                         | NR               | 625       | 734                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 240                         | NR               | 630       | 670                         | NR               | 760       | 13                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 290                         | NR               | 635       | 600                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 335                         | NR               | 640       | 535                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 0                           | NR               | 515       | 375                         | NR               | 645       | 473                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 1                           | NR               | 520       | 408                         | NR               | 650       | 415                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 434                         | NR               | 655       | 362                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 461                         | NR               | 660       | 313                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 8                           | NR               | 535       | 486                         | NR               | 665       | 271                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 16                          | NR               | 540       | 514                         | NR               | 670       | 231                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 33                          | NR               | 545       | 549                         | NR               | 675       | 198                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 69                          | NR               | 550       | 591                         | NR               | 680       | 169                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 131                         | NR               | 555       | 640                         | NR               | 685       | 144                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 227                         | NR               | 560       | 695                         | NR               | 690       | 123                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 369                         | NR               | 565       | 757                         | NR               | 695       | 104                         | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 822                         | NR               | 700       | 88                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 498                         | NR               | 575       | 882                         | NR               | 705       | 75                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 315                         | NR               | 580       | 935                         | NR               | 710       | 63                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 204                         | NR               | 585       | 972                         | NR               | 715       | 54                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 145                         | NR               | 590       | 996                         | NR               | 720       | 46                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 100                         | NR               | 595       | 1000                        | NR               | 725       | 39                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 78                          | NR               | 600       | 989                         | NR               | 730       | 33                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 76                          | NR               | 605       | 960                         | NR               | 735       | 28                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 83                          | NR               | 610       | 918                         | NR               | 740       | 24                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 105                         | NR               | 615       | 864                         | NR               | 745       | 20                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-4

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 2.13**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 142                                  | NR                             | 620               | 803                                  | NR                             | 750               | 17                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 189                                  | NR                             | 625               | 734                                  | NR                             | 755               | 15                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 240                                  | NR                             | 630               | 670                                  | NR                             | 760               | 13                                   | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 290                                  | NR                             | 635               | 600                                  | NR                             | 765               | 11                                   | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 335                                  | NR                             | 640               | 535                                  | NR                             | 770               | 9                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 375                                  | NR                             | 645               | 473                                  | NR                             | 775               | 8                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 1                                    | NR                             | 520               | 408                                  | NR                             | 650               | 415                                  | NR                             | 780               | 7                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 2                                    | NR                             | 525               | 434                                  | NR                             | 655               | 362                                  | NR                             | 785               | 6                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 4                                    | NR                             | 530               | 461                                  | NR                             | 660               | 313                                  | NR                             | 790               | 5                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 8                                    | NR                             | 535               | 486                                  | NR                             | 665               | 271                                  | NR                             | 795               | 4                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 16                                   | NR                             | 540               | 514                                  | NR                             | 670               | 231                                  | NR                             | 800               | 4                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 33                                   | NR                             | 545               | 549                                  | NR                             | 675               | 198                                  | NR                             | 805               | 3                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 69                                   | NR                             | 550               | 591                                  | NR                             | 680               | 169                                  | NR                             | 810               | 3                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 131                                  | NR                             | 555               | 640                                  | NR                             | 685               | 144                                  | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 227                                  | NR                             | 560               | 695                                  | NR                             | 690               | 123                                  | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 369                                  | NR                             | 565               | 757                                  | NR                             | 695               | 104                                  | NR                             | 825               | 2                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 517                                  | NR                             | 570               | 822                                  | NR                             | 700               | 88                                   | NR                             | 830               | 2                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 498                                  | NR                             | 575               | 882                                  | NR                             | 705               | 75                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 315                                  | NR                             | 580               | 935                                  | NR                             | 710               | 63                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 204                                  | NR                             | 585               | 972                                  | NR                             | 715               | 54                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 145                                  | NR                             | 590               | 996                                  | NR                             | 720               | 46                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 100                                  | NR                             | 595               | 1000                                 | NR                             | 725               | 39                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 78                                   | NR                             | 600               | 989                                  | NR                             | 730               | 33                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 76                                   | NR                             | 605               | 960                                  | NR                             | 735               | 28                                   | NR                             | 865               | 1                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 83                                   | NR                             | 610               | 918                                  | NR                             | 740               | 24                                   | NR                             | 870               | 1                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 105                                  | NR                             | 615               | 864                                  | NR                             | 745               | 20                                   | NR                             | 875               | 1                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-4


TM-30-18

### Summary

$R_f = 73.8$   
 $R_g = 94.4$   
 $CIE\ R_a = 70.8$   
 $R_g = -43.2$



### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)