

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047789

Luminaire Tested: **GALN-SA6A-735-U-T2BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047789
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA6A-735-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 6xLight Square PACKAGE
70CRI 3500K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (84) 3500K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20922.6 lumens
Efficiency: N/A
Efficacy: 128.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G3

Input Watts (W): 162.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047789

CATALOG NUMBER: GALN-SA6A-735-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 27.7 fc
 Type II - Short - N/A

REPORT NUMBER: P1047789

CATALOG NUMBER: GALN-SA6A-735-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047789

CATALOG NUMBER: GALN-SA6A-735-U-T2BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	89.3	0.0	89.3
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	20833.3	0.0	20833.3
	% Fixture	99.6	0.0	99.6
Total	Lumens	20922.6	0.0	20922.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	0.1
10°-20°	172.0	0.8
20°-30°	617.5	3.0
30°-40°	1643.9	7.9
40°-50°	4318.5	20.6
50°-60°	6690.2	32.0
60°-70°	5609.7	26.8
70°-80°	1650.8	7.9
80°-90°	203.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20922.6	100.0
0°-180°	20922.6	100.0



REPORT NUMBER: P1047789


CATALOG NUMBER: GALN-SA6A-735-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	785.8	3.8			
FM	(30°-60°)	12618.7	60.3			
FH	(60°-80°)	7229.0	34.6			G3/7500
FVH	(80°-90°)	199.9	1.0			G2/225
BL	(0°-30°)	20.0	0.1	B0/110		
BM	(30°-60°)	34.0	0.2	B0/220		
BH	(60°-80°)	31.5	0.2	B0/110		G0/110
BVH	(80°-90°)	3.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G3

Type II Short



REPORT NUMBER: P1047789

CATALOG NUMBER: GALN-SA6A-735-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1
2.5°	155.4	156.9	154.0	148.2	143.9	143.9	142.5	138.2	138.2	133.9	131.0
5°	217.3	214.4	208.7	197.2	187.1	177.0	167.0	156.9	155.4	142.5	133.9
7.5°	355.5	358.4	339.7	303.7	273.5	234.6	198.6	177.0	174.1	152.6	135.3
10°	780.1	758.5	715.3	575.7	473.5	356.9	264.8	205.8	202.9	164.1	138.2
12.5°	1422.0	1404.7	1325.5	1181.6	918.2	639.0	387.2	254.7	246.1	174.1	139.6
15°	2049.5	2022.1	1979.0	1833.6	1525.6	1145.6	633.3	348.3	325.3	188.5	138.2
17.5°	2449.6	2453.9	2415.1	2353.2	2154.6	1695.4	1093.8	519.6	475.0	214.4	135.3
20°	2799.3	2789.3	2810.9	2777.7	2638.1	2304.2	1591.8	823.2	747.0	256.2	136.7
22.5°	3202.3	3226.8	3242.6	3235.4	3081.4	2796.5	2157.4	1232.0	1135.6	332.5	141.0
25°	3742.0	3739.2	3740.6	3721.9	3572.2	3255.6	2724.5	1740.1	1642.2	456.2	151.1
27.5°	4307.7	4324.9	4332.1	4264.5	4068.8	3757.9	3249.8	2295.6	2180.5	654.9	164.1
30°	5080.5	5066.2	5033.1	4894.9	4657.4	4271.7	3768.0	2878.5	2757.6	932.6	184.2
32.5°	6122.6	6106.7	5939.8	5634.7	5279.2	4807.1	4289.0	3462.8	3316.0	1279.5	211.6
35°	7839.6	7864.1	7453.9	6663.7	6026.1	5450.4	4866.1	4044.3	3914.8	1706.9	249.0
37.5°	10469.1	10335.2	9778.3	8382.2	7009.1	6253.5	5417.3	4631.5	4519.2	2233.7	297.9
40°	13023.8	12891.3	12730.1	11407.5	8717.5	7138.7	6188.8	5320.9	5175.5	2828.1	369.9
42.5°	15709.4	15636.0	15628.8	14631.4	11834.9	8530.4	7117.1	6128.3	6004.5	3480.1	487.9
45°	17612.1	17538.7	17692.7	17866.8	16080.7	11512.5	8733.4	7177.5	6997.6	4271.7	676.4
47.5°	17868.3	17871.1	18282.8	18828.2	19235.6	16125.3	10886.5	8567.8	8349.1	5404.4	993.1
50°	17016.2	17049.3	17704.2	18680.0	19776.7	19995.5	14683.2	10585.7	10261.8	6747.2	1442.1
52.5°	15394.2	15431.6	16344.1	17948.9	19278.7	20925.2	19153.5	13225.3	12852.5	8422.5	2075.4
55°	13933.4	13956.4	15002.7	17030.6	18678.6	20420.1	21807.5	16750.0	16260.6	10483.5	2700.0
57.5°	12486.9	12433.7	13114.4	15435.9	18576.4	19799.7	22199.0	20766.9	20227.2	12735.9	3186.5
60°	10552.6	10463.3	11010.2	12486.9	17232.1	20207.0	21466.4	22989.1	22866.8	15872.0	3562.1
61°	9440.0	9402.6	9952.4	11218.9	16100.9	20103.4	21290.8	23082.7	23095.6	17355.9	3730.5
62.5°	6741.4	6847.9	7688.5	9335.0	13485.8	19431.3	21313.8	22793.4	22921.5	19327.7	4166.6
65°	2996.5	3167.8	3821.2	5161.1	7842.5	16164.2	21109.5	22158.7	22095.3	19868.8	5669.2
67.5°	1777.5	1803.4	2128.6	2924.6	4153.7	8694.5	18628.2	21319.6	21234.7	17296.9	7053.8
70°	1400.4	1413.3	1517.0	1835.0	2410.7	3330.4	10631.7	18445.4	18815.3	14025.5	6905.5
72.5°	1328.4	1325.5	1339.9	1396.1	1518.4	1652.3	4116.2	12261.0	13013.7	10100.6	5790.1
75°	1311.2	1305.4	1291.0	1269.4	1099.6	972.9	1275.2	5423.1	5859.2	6901.2	4359.5
77.5°	1272.3	1273.7	1276.6	1217.6	942.7	688.0	617.4	1740.1	2140.2	4379.6	3098.7
80°	860.7	873.6	895.2	872.2	847.7	498.0	436.1	618.9	627.5	2458.2	2046.6
82.5°	436.1	436.1	426.0	380.0	328.1	323.8	346.9	449.0	454.8	1243.5	962.9
85°	263.4	277.8	283.5	257.6	236.0	217.3	264.8	356.9	369.9	482.1	224.5
87.5°	59.0	60.4	66.2	87.8	128.1	174.1	246.1	326.7	332.5	309.4	27.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1047789

CATALOG NUMBER: GALN-SA6A-735-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1	128.1
2.5°	129.5	126.7	125.2	120.9	116.6	112.3	109.4	107.9	109.4	110.8	110.8
5°	128.1	123.8	116.6	109.4	103.6	97.9	92.1	90.7	90.7	92.1	92.1
7.5°	128.1	120.9	110.8	102.2	93.6	84.9	80.6	77.7	79.2	79.2	79.2
10°	128.1	119.5	106.5	93.6	83.5	73.4	66.2	63.3	63.3	63.3	63.3
12.5°	126.7	118.0	102.2	86.4	72.0	60.4	51.8	47.5	48.9	48.9	48.9
15°	123.8	113.7	96.4	73.4	57.6	46.1	37.4	33.1	34.5	37.4	38.9
17.5°	119.5	109.4	86.4	61.9	46.1	34.5	25.9	23.0	24.5	28.8	28.8
20°	118.0	105.1	76.3	50.4	34.5	24.5	17.3	14.4	15.8	21.6	23.0
22.5°	118.0	102.2	69.1	41.7	25.9	15.8	10.1	5.8	5.8	10.1	10.1
25°	119.5	100.7	63.3	34.5	18.7	11.5	5.8	2.9	5.8	15.8	18.7
27.5°	122.3	99.3	60.4	28.8	14.4	10.1	4.3	10.1	17.3	17.3	17.3
30°	125.2	96.4	56.1	24.5	13.0	7.2	7.2	14.4	14.4	17.3	18.7
32.5°	129.5	95.0	53.3	21.6	10.1	5.8	10.1	8.6	8.6	10.1	11.5
35°	138.2	96.4	50.4	21.6	10.1	7.2	8.6	4.3	2.9	2.9	2.9
37.5°	149.7	97.9	46.1	18.7	8.6	8.6	4.3	0.0	0.0	0.0	0.0
40°	168.4	102.2	43.2	17.3	7.2	7.2	1.4	0.0	0.0	0.0	0.0
42.5°	200.1	110.8	41.7	15.8	7.2	5.8	0.0	0.0	0.0	0.0	0.0
45°	263.4	131.0	38.9	14.4	7.2	2.9	0.0	0.0	0.0	0.0	0.0
47.5°	378.5	178.5	37.4	11.5	4.3	0.0	0.0	0.0	0.0	0.0	0.0
50°	552.7	241.8	36.0	10.1	1.4	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	705.2	254.7	24.5	8.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	722.5	175.6	18.7	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	575.7	113.7	15.8	4.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	436.1	86.4	14.4	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	418.8	77.7	14.4	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	462.0	67.6	13.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	751.3	56.1	11.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1305.4	48.9	10.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1649.4	46.1	8.6	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1437.8	41.7	8.6	2.9	1.4	0.0	0.0	0.0	0.0	0.0	0.0
75°	865.0	36.0	8.6	5.8	2.9	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	453.4	27.3	8.6	7.2	4.3	1.4	0.0	0.0	0.0	0.0	0.0
80°	220.2	24.5	10.1	7.2	5.8	2.9	0.0	0.0	0.0	0.0	0.0
82.5°	86.4	20.1	11.5	10.1	7.2	4.3	1.4	0.0	0.0	0.0	0.0
85°	38.9	17.3	13.0	11.5	10.1	5.8	1.4	0.0	0.0	0.0	0.0
87.5°	20.1	15.8	14.4	13.0	10.1	7.2	2.9	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-5

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-735-U-5WQ

Data in this report applies to families of products including GSS-SB1A-735-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-5
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-735-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K):	3369	CRI (Ra):	70.1		
CIE u':	0.2386	R1:	66.6	R9:	-40.2
CIE v':	0.5156	R2:	77.6	R10:	49.1
Duv:	0.0013	R3:	88.5	R11:	66.3
CIE x:	0.4143	R4:	69.5	R12:	45.7
CIE y:	0.3980	R5:	66.4	R13:	68.0
CIE z:	0.1877	R6:	69.6	R14:	93.4
Peak Wavelength (nm):	590	R7:	77.5	R15:	57.6
Dominant Wavelength (nm):	580	R8:	44.9		
Purity:	43.80166				
Rf:	71.4				
Rg:	96				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-5

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-5

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.29

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.36

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	119	NR	620	778	NR	750	19	NR	880	1	NR
365	0	NR	495	173	NR	625	711	NR	755	16	NR	885	0	NR
370	0	NR	500	239	NR	630	648	NR	760	14	NR	890	0	NR
375	0	NR	505	313	NR	635	582	NR	765	12	NR	895	0	NR
380	0	NR	510	383	NR	640	520	NR	770	11	NR	900	0	NR
385	0	NR	515	448	NR	645	460	NR	775	9	NR	905	0	NR
390	2	NR	520	500	NR	650	406	NR	780	8	NR	910	0	NR
395	4	NR	525	539	NR	655	355	NR	785	7	NR	915	0	NR
400	6	NR	530	575	NR	660	309	NR	790	6	NR	920	0	NR
405	11	NR	535	606	NR	665	269	NR	795	5	NR	925	0	NR
410	22	NR	540	633	NR	670	231	NR	800	4	NR	930	0	NR
415	45	NR	545	666	NR	675	199	NR	805	4	NR	935	0	NR
420	96	NR	550	701	NR	680	171	NR	810	3	NR	940	0	NR
425	193	NR	555	743	NR	685	147	NR	815	3	NR	945	0	NR
430	341	NR	560	788	NR	690	126	NR	820	3	NR	950	0	NR
435	547	NR	565	837	NR	695	107	NR	825	2	NR	955	0	NR
440	799	NR	570	887	NR	700	92	NR	830	2	NR	960	0	NR
445	831	NR	575	931	NR	705	78	NR	835	2	NR	965	0	NR
450	461	NR	580	967	NR	710	67	NR	840	2	NR	970	0	NR
455	256	NR	585	990	NR	715	57	NR	845	1	NR	975	0	NR
460	176	NR	590	1000	NR	720	49	NR	850	1	NR	980	0	NR
465	107	NR	595	994	NR	725	42	NR	855	1	NR	985	0	NR
470	74	NR	600	973	NR	730	36	NR	860	1	NR	990	0	NR
475	67	NR	605	938	NR	735	31	NR	865	1	NR	995	0	NR
480	68	NR	610	892	NR	740	26	NR	870	1	NR	1000	0	NR
485	84	NR	615	838	NR	745	22	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-5

TM-30-18

Summary

$R_f = 71.4$
 $R_g = 96$
 CIE $R_a = 70.1$
 $R_g = -40.2$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 57	CES51 = 84	CES76 = 50
CES02 = 62	CES27 = 80	CES52 = 86	CES77 = 74
CES03 = 31	CES28 = 81	CES53 = 72	CES78 = 54
CES04 = 70	CES29 = 50	CES54 = 79	CES79 = 81
CES05 = 48	CES30 = 55	CES55 = 78	CES80 = 79
CES06 = 51	CES31 = 56	CES56 = 67	CES81 = 74
CES07 = 40	CES32 = 54	CES57 = 65	CES82 = 91
CES08 = 39	CES33 = 60	CES58 = 68	CES83 = 86
CES09 = 29	CES34 = 69	CES59 = 85	CES84 = 89
CES10 = 75	CES35 = 83	CES60 = 91	CES85 = 83
CES11 = 58	CES36 = 88	CES61 = 85	CES86 = 66
CES12 = 64	CES37 = 78	CES62 = 78	CES87 = 77
CES13 = 43	CES38 = 64	CES63 = 71	CES88 = 75
CES14 = 74	CES39 = 92	CES64 = 70	CES89 = 68
CES15 = 71	CES40 = 86	CES65 = 64	CES90 = 72
CES16 = 47	CES41 = 81	CES66 = 65	CES91 = 95
CES17 = 50	CES42 = 79	CES67 = 63	CES92 = 62
CES18 = 56	CES43 = 71	CES68 = 69	CES93 = 78
CES19 = 72	CES44 = 98	CES69 = 80	CES94 = 51
CES20 = 65	CES45 = 80	CES70 = 60	CES95 = 70
CES21 = 87	CES46 = 75	CES71 = 58	CES96 = 76
CES22 = 79	CES47 = 71	CES72 = 85	CES97 = 82
CES23 = 92	CES48 = 61	CES73 = 51	CES98 = 72
CES24 = 91	CES49 = 74	CES74 = 94	CES99 = 60
CES25 = 72	CES50 = 83	CES75 = 57	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)