

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049478

Luminaire Tested: **GALN-SA5B-740-U-LBC**

Issue Date: 07/10/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1049478  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA5B-740-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 5xLight Square PACKAGE  
70CRI 4000K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (70) 4000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20308.9 lumens  
Efficiency: N/A  
Efficacy: 113.6 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3


Input Watts (W): 178.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 35.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049478  
CATALOG NUMBER: GALN-SA5B-740-U-LBC

## Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral    - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 138.7    | 0.0    | 138.7   |
|                    | % Fixture | 0.7      | 0.0    | 0.7     |
| <b>Street Side</b> | Lumens    | 20170.2  | 0.0    | 20170.2 |
|                    | % Fixture | 99.3     | 0.0    | 99.3    |
| <b>Total</b>       | Lumens    | 20308.9  | 0.0    | 20308.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 7.9     | 0.0       |
| 10°-20°   | 44.5    | 0.2       |
| 20°-30°   | 481.1   | 2.4       |
| 30°-40°   | 1422.8  | 7.0       |
| 40°-50°   | 4240.8  | 20.9      |
| 50°-60°   | 6729.2  | 33.1      |
| 60°-70°   | 5612.9  | 27.6      |
| 70°-80°   | 1731.1  | 8.5       |
| 80°-90°   | 38.4    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20308.9 | 100.0     |
| 0°-180°   | 20308.9 | 100.0     |



REPORT NUMBER: P1049478


CATALOG NUMBER: GALN-SA5B-740-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 520.0   | 2.6       |                         |      |         |
| FM   | (30°-60°)   | 12316.9 | 60.6      |                         |      |         |
| FH   | (60°-80°)   | 7296.7  | 35.9      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 36.6    | 0.2       |                         |      | G1/100  |
| BL   | (0°-30°)    | 13.6    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 75.9    | 0.4       | B0/220                  |      |         |
| BH   | (60°-80°)   | 47.3    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 1.9     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°     | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°     |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 89.0   | 89.0   | 89.0    | 89.0    | 89.0    | 89.0    | 89.0    | 89.0    | 89.0    | 89.0    |
| 2.5°  | 115.1  | 115.1  | 110.5   | 104.3   | 98.2    | 92.0    | 90.5    | 87.4    | 85.9    | 84.4    |
| 5°    | 119.7  | 119.7  | 118.1   | 113.5   | 107.4   | 102.8   | 102.8   | 98.2    | 95.1    | 92.0    |
| 7.5°  | 122.7  | 124.3  | 127.3   | 125.8   | 122.7   | 118.1   | 118.1   | 115.1   | 110.5   | 102.8   |
| 10°   | 127.3  | 131.9  | 138.1   | 141.1   | 142.7   | 142.7   | 141.1   | 139.6   | 131.9   | 121.2   |
| 12.5° | 131.9  | 141.1  | 156.5   | 171.8   | 181.0   | 193.3   | 191.8   | 188.7   | 168.8   | 145.7   |
| 15°   | 141.1  | 155.0  | 187.2   | 231.7   | 300.7   | 343.7   | 360.5   | 345.2   | 279.2   | 196.4   |
| 17.5° | 151.9  | 174.9  | 271.5   | 484.8   | 794.7   | 942.0   | 1031.0  | 958.9   | 635.1   | 372.8   |
| 20°   | 162.6  | 213.2  | 504.7   | 1256.5  | 2061.9  | 2543.6  | 2677.1  | 2468.5  | 1584.8  | 710.3   |
| 22.5° | 181.0  | 299.2  | 1023.3  | 2597.3  | 4442.9  | 5165.5  | 5302.1  | 4634.7  | 2993.2  | 1402.2  |
| 25°   | 219.4  | 434.2  | 1764.3  | 4232.8  | 6630.7  | 7850.3  | 7793.6  | 6919.1  | 4855.6  | 2239.9  |
| 27.5° | 274.6  | 632.1  | 2667.9  | 6013.9  | 8726.3  | 9801.8  | 9930.7  | 8849.1  | 6472.6  | 3293.9  |
| 30°   | 354.4  | 876.0  | 3637.5  | 7440.7  | 10406.2 | 11569.1 | 11590.6 | 10472.2 | 7919.4  | 4219.0  |
| 32.5° | 431.1  | 1106.1 | 4485.9  | 8819.9  | 12061.6 | 13336.5 | 13431.6 | 12055.5 | 8999.4  | 5182.4  |
| 35°   | 489.4  | 1256.5 | 5345.0  | 10031.9 | 13730.8 | 15487.4 | 15481.3 | 13847.4 | 10278.9 | 6043.1  |
| 37.5° | 494.0  | 1406.8 | 6122.9  | 11271.5 | 15844.9 | 17811.7 | 18006.5 | 16205.4 | 11825.3 | 7107.8  |
| 40°   | 483.3  | 1575.6 | 7107.8  | 13204.6 | 19654.2 | 22671.9 | 22843.7 | 20573.2 | 14927.4 | 8930.4  |
| 42.5° | 495.5  | 1868.6 | 8706.4  | 16774.6 | 25979.6 | 30313.6 | 30645.0 | 28257.8 | 20629.9 | 12649.2 |
| 45°   | 560.0  | 2419.4 | 12055.5 | 22747.1 | 34995.8 | 40279.5 | 40169.0 | 36731.0 | 27265.2 | 18310.3 |
| 47.5° | 773.2  | 3767.9 | 17020.0 | 28560.0 | 40758.2 | 45463.5 | 45558.6 | 41356.5 | 31137.4 | 22662.7 |
| 50°   | 1189.0 | 5765.4 | 21191.4 | 31633.0 | 43235.8 | 47956.5 | 47867.5 | 43011.9 | 32608.7 | 24805.9 |
| 52.5° | 1546.4 | 7210.6 | 23284.0 | 32711.5 | 43553.4 | 49188.4 | 49182.3 | 43447.6 | 32837.3 | 24990.0 |
| 55°   | 1635.4 | 7319.5 | 23300.9 | 32769.8 | 44265.3 | 50800.8 | 51003.3 | 44519.9 | 33133.4 | 24186.1 |
| 57.5° | 1600.1 | 6480.3 | 22328.2 | 33107.3 | 45532.5 | 52048.1 | 52058.8 | 45558.6 | 33885.1 | 23693.6 |
| 58°   | 1569.5 | 6348.4 | 22131.9 | 33299.1 | 45750.3 | 52100.3 | 52074.2 | 45606.1 | 34497.2 | 23675.2 |
| 60°   | 1397.6 | 5512.3 | 21366.3 | 33788.5 | 45426.6 | 51029.4 | 50785.5 | 44567.5 | 34406.7 | 23486.5 |
| 62.5° | 1098.5 | 4300.3 | 20613.0 | 33222.3 | 41956.4 | 45845.5 | 45946.7 | 39457.2 | 31366.0 | 22386.5 |
| 65°   | 874.5  | 3204.9 | 19042.1 | 29141.5 | 34549.4 | 37648.4 | 38025.8 | 32085.5 | 26180.5 | 18956.1 |
| 67.5° | 696.5  | 2316.6 | 15973.7 | 23201.2 | 27338.8 | 31421.2 | 31695.9 | 26938.4 | 20283.2 | 14523.9 |
| 70°   | 566.1  | 1566.4 | 11026.0 | 16967.9 | 22549.2 | 27139.4 | 27156.3 | 22378.9 | 15139.1 | 9516.4  |
| 72.5° | 501.7  | 1084.7 | 6400.5  | 12374.6 | 18284.2 | 22115.0 | 21668.6 | 18159.9 | 11635.1 | 5636.5  |
| 75°   | 434.2  | 719.5  | 3138.9  | 7565.0  | 11085.9 | 11161.1 | 11331.3 | 8424.1  | 5816.0  | 2680.2  |
| 77.5° | 357.5  | 510.9  | 1236.5  | 2066.5  | 3324.5  | 4255.8  | 4413.8  | 3344.5  | 1934.6  | 659.7   |
| 80°   | 245.5  | 242.4  | 332.9   | 633.6   | 951.2   | 1192.0  | 1112.3  | 860.7   | 506.3   | 253.1   |
| 82.5° | 105.9  | 115.1  | 150.3   | 181.0   | 147.3   | 142.7   | 136.5   | 87.4    | 67.5    | 52.2    |
| 85°   | 33.8   | 30.7   | 32.2    | 32.2    | 26.1    | 19.9    | 19.9    | 9.2     | 0.0     | 0.0     |
| 87.5° | 16.9   | 13.8   | 13.8    | 12.3    | 7.7     | 3.1     | 1.5     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°     |       | 90°    | 95°   | 105°  | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|---------|-------|--------|-------|-------|------|------|------|------|------|------|------|
| 89.0    | 0°    | 89.0   | 89.0  | 89.0  | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 |
| 82.8    | 2.5°  | 81.3   | 81.3  | 78.2  | 75.2 | 73.6 | 70.6 | 69.0 | 67.5 | 66.0 | 64.4 |
| 89.0    | 5°    | 85.9   | 84.4  | 79.8  | 75.2 | 70.6 | 66.0 | 62.9 | 59.8 | 56.8 | 55.2 |
| 98.2    | 7.5°  | 93.6   | 90.5  | 81.3  | 73.6 | 67.5 | 61.4 | 58.3 | 53.7 | 50.6 | 46.0 |
| 108.9   | 10°   | 102.8  | 96.7  | 84.4  | 75.2 | 66.0 | 58.3 | 53.7 | 49.1 | 44.5 | 38.4 |
| 124.3   | 12.5° | 115.1  | 104.3 | 89.0  | 73.6 | 62.9 | 53.7 | 49.1 | 43.0 | 38.4 | 33.8 |
| 144.2   | 15°   | 125.8  | 112.0 | 90.5  | 73.6 | 59.8 | 49.1 | 43.0 | 36.8 | 32.2 | 26.1 |
| 181.0   | 17.5° | 141.1  | 118.1 | 89.0  | 69.0 | 55.2 | 43.0 | 36.8 | 32.2 | 24.5 | 15.3 |
| 268.5   | 20°   | 167.2  | 122.7 | 85.9  | 64.4 | 47.6 | 35.3 | 27.6 | 21.5 | 10.7 | 3.1  |
| 403.5   | 22.5° | 208.6  | 135.0 | 82.8  | 58.3 | 41.4 | 27.6 | 18.4 | 7.7  | 0.0  | 0.0  |
| 613.7   | 25°   | 288.4  | 156.5 | 82.8  | 55.2 | 36.8 | 19.9 | 6.1  | 0.0  | 0.0  | 0.0  |
| 871.4   | 27.5° | 383.5  | 185.6 | 82.8  | 47.6 | 29.1 | 10.7 | 0.0  | 0.0  | 0.0  | 0.0  |
| 1187.4  | 30°   | 480.2  | 217.9 | 82.8  | 41.4 | 23.0 | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1462.1  | 32.5° | 572.2  | 245.5 | 84.4  | 35.3 | 15.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1842.5  | 35°   | 665.8  | 250.1 | 82.8  | 30.7 | 9.2  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2308.9  | 37.5° | 785.5  | 240.9 | 78.2  | 27.6 | 4.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3037.6  | 40°   | 966.5  | 245.5 | 73.6  | 26.1 | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4337.1  | 42.5° | 1301.0 | 265.4 | 67.5  | 26.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 6908.3  | 45°   | 2249.1 | 355.9 | 61.4  | 27.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 10371.0 | 47.5° | 3720.4 | 639.7 | 59.8  | 27.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 12492.7 | 50°   | 4748.2 | 805.4 | 62.9  | 29.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 12758.1 | 52.5° | 4740.6 | 897.5 | 66.0  | 30.7 | 6.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 11759.4 | 55°   | 4214.4 | 914.4 | 70.6  | 33.8 | 19.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 10105.5 | 57.5° | 3522.4 | 834.6 | 81.3  | 41.4 | 36.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 9846.3  | 58°   | 3399.7 | 797.8 | 84.4  | 43.0 | 39.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 8540.7  | 60°   | 2786.0 | 650.5 | 107.4 | 53.7 | 53.7 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 7001.9  | 62.5° | 1923.8 | 567.6 | 122.7 | 69.0 | 55.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5162.5  | 65°   | 1360.8 | 512.4 | 133.5 | 73.6 | 44.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3668.2  | 67.5° | 1017.2 | 472.5 | 147.3 | 75.2 | 23.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2301.2  | 70°   | 779.4  | 443.4 | 181.0 | 79.8 | 6.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1371.5  | 72.5° | 635.1  | 409.6 | 219.4 | 82.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 822.3   | 75°   | 526.2  | 369.7 | 211.7 | 90.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 438.8   | 77.5° | 349.8  | 286.9 | 193.3 | 90.5 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 156.5   | 80°   | 122.7  | 113.5 | 150.3 | 79.8 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 32.2    | 82.5° | 18.4   | 15.3  | 21.5  | 27.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 85°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 87.5° | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 90°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270°  |
|------|-------|------|------|------|------|------|------|------|------|------|-------|
| 89.0 | 0°    | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0 | 89.0  |
| 62.9 | 2.5°  | 62.9 | 62.9 | 61.4 | 62.9 | 62.9 | 66.0 | 73.6 | 84.4 | 96.7 | 101.3 |
| 53.7 | 5°    | 52.2 | 50.6 | 49.1 | 49.1 | 49.1 | 53.7 | 59.8 | 72.1 | 85.9 | 92.0  |
| 44.5 | 7.5°  | 43.0 | 41.4 | 39.9 | 38.4 | 38.4 | 41.4 | 49.1 | 62.9 | 76.7 | 82.8  |
| 36.8 | 10°   | 35.3 | 32.2 | 30.7 | 29.1 | 29.1 | 32.2 | 39.9 | 53.7 | 69.0 | 75.2  |
| 30.7 | 12.5° | 29.1 | 24.5 | 21.5 | 19.9 | 18.4 | 23.0 | 30.7 | 43.0 | 59.8 | 67.5  |
| 23.0 | 15°   | 19.9 | 15.3 | 10.7 | 9.2  | 7.7  | 12.3 | 19.9 | 33.8 | 50.6 | 59.8  |
| 12.3 | 17.5° | 10.7 | 4.6  | 1.5  | 0.0  | 0.0  | 3.1  | 9.2  | 24.5 | 41.4 | 49.1  |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 12.3 | 30.7 | 38.4  |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.5  | 18.4 | 26.1  |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 7.7  | 13.8  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 3.1   |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 4.6   |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.1  | 12.3  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |



REPORT NUMBER: P1049478

CATALOG NUMBER: GALN-SA5B-740-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275°  |       | 285°  | 295°  | 305°  | 315°  | 316°  | 325°  | 335°  | 345°  | 355°  | 360°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 89.0  | 0°    | 89.0  | 89.0  | 89.0  | 89.0  | 89.0  | 89.0  | 89.0  | 89.0  | 89.0  | 89.0   |
| 105.9 | 2.5°  | 108.9 | 107.4 | 104.3 | 101.3 | 101.3 | 101.3 | 105.9 | 110.5 | 115.1 | 115.1  |
| 95.1  | 5°    | 101.3 | 101.3 | 99.7  | 96.7  | 96.7  | 98.2  | 104.3 | 112.0 | 118.1 | 119.7  |
| 87.4  | 7.5°  | 93.6  | 96.7  | 93.6  | 92.0  | 93.6  | 95.1  | 101.3 | 110.5 | 119.7 | 122.7  |
| 81.3  | 10°   | 89.0  | 90.5  | 90.5  | 89.0  | 89.0  | 92.0  | 98.2  | 110.5 | 122.7 | 127.3  |
| 73.6  | 12.5° | 82.8  | 85.9  | 84.4  | 84.4  | 84.4  | 87.4  | 95.1  | 108.9 | 125.8 | 131.9  |
| 66.0  | 15°   | 76.7  | 81.3  | 81.3  | 79.8  | 79.8  | 81.3  | 92.0  | 107.4 | 130.4 | 141.1  |
| 56.8  | 17.5° | 70.6  | 75.2  | 76.7  | 73.6  | 73.6  | 76.7  | 87.4  | 107.4 | 133.5 | 151.9  |
| 46.0  | 20°   | 58.3  | 66.0  | 70.6  | 66.0  | 66.0  | 69.0  | 79.8  | 101.3 | 135.0 | 162.6  |
| 33.8  | 22.5° | 46.0  | 53.7  | 59.8  | 58.3  | 58.3  | 59.8  | 73.6  | 96.7  | 136.5 | 181.0  |
| 19.9  | 25°   | 33.8  | 41.4  | 46.0  | 49.1  | 49.1  | 53.7  | 67.5  | 93.6  | 142.7 | 219.4  |
| 9.2   | 27.5° | 19.9  | 29.1  | 35.3  | 38.4  | 39.9  | 46.0  | 62.9  | 90.5  | 153.4 | 274.6  |
| 0.0   | 30°   | 9.2   | 16.9  | 24.5  | 30.7  | 30.7  | 41.4  | 58.3  | 87.4  | 167.2 | 354.4  |
| 0.0   | 32.5° | 0.0   | 7.7   | 12.3  | 21.5  | 23.0  | 33.8  | 53.7  | 84.4  | 187.2 | 431.1  |
| 0.0   | 35°   | 0.0   | 0.0   | 6.1   | 16.9  | 16.9  | 27.6  | 49.1  | 81.3  | 217.9 | 489.4  |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 12.3  | 13.8  | 24.5  | 47.6  | 79.8  | 224.0 | 494.0  |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 9.2   | 10.7  | 23.0  | 47.6  | 81.3  | 202.5 | 483.3  |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 6.1   | 7.7   | 23.0  | 47.6  | 84.4  | 182.6 | 495.5  |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 4.6   | 6.1   | 24.5  | 46.0  | 82.8  | 171.8 | 560.0  |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 6.1   | 9.2   | 24.5  | 44.5  | 81.3  | 173.4 | 773.2  |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 7.7   | 10.7  | 24.5  | 46.0  | 78.2  | 190.2 | 1189.0 |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 6.1   | 9.2   | 27.6  | 50.6  | 76.7  | 207.1 | 1546.4 |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 1.5   | 4.6   | 35.3  | 55.2  | 76.7  | 233.2 | 1635.4 |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 39.9  | 62.9  | 81.3  | 276.1 | 1600.1 |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 39.9  | 64.4  | 81.3  | 279.2 | 1569.5 |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 39.9  | 70.6  | 90.5  | 300.7 | 1397.6 |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 33.8  | 84.4  | 113.5 | 313.0 | 1098.5 |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 27.6  | 99.7  | 124.3 | 322.2 | 874.5  |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 26.1  | 102.8 | 125.8 | 326.8 | 696.5  |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 27.6  | 101.3 | 135.0 | 342.1 | 566.1  |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 30.7  | 92.0  | 148.8 | 342.1 | 501.7  |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 32.2  | 85.9  | 167.2 | 311.4 | 434.2  |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 30.7  | 84.4  | 194.8 | 277.7 | 357.5  |
| 0.0   | 80°   | 3.1   | 4.6   | 4.6   | 3.1   | 3.1   | 26.1  | 82.8  | 197.9 | 236.3 | 245.5  |
| 1.5   | 82.5° | 9.2   | 12.3  | 10.7  | 7.7   | 7.7   | 23.0  | 73.6  | 165.7 | 122.7 | 105.9  |
| 9.2   | 85°   | 16.9  | 19.9  | 19.9  | 16.9  | 16.9  | 21.5  | 46.0  | 59.8  | 41.4  | 33.8   |
| 16.9  | 87.5° | 23.0  | 26.1  | 26.1  | 23.0  | 23.0  | 21.5  | 19.9  | 18.4  | 16.9  | 16.9   |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-1

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-740-U-5WQ


Data in this report applies to families of products including GSS-SB1A-740-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-1  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-740-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 3949     | CRI (Ra): | 70.7 |      |       |
| CIE u':                   | 0.2248   | R1:       | 68.0 | R9:  | -36.7 |
| CIE v':                   | 0.5053   | R2:       | 76.0 | R10: | 45.1  |
| Duv:                      | 0.0022   | R3:       | 84.3 | R11: | 70.7  |
| CIE x:                    | 0.3844   | R4:       | 72.0 | R12: | 47.1  |
| CIE y:                    | 0.3840   | R5:       | 68.6 | R13: | 68.5  |
| CIE z:                    | 0.2316   | R6:       | 68.3 | R14: | 91.1  |
| Peak Wavelength (nm):     | 440      | R7:       | 77.9 | R15: | 58.7  |
| Dominant Wavelength (nm): | 578      | R8:       | 50.3 |      |       |
| Purity:                   | 30.60026 |           |      |      |       |
| Rf:                       | 71.8     |           |      |      |       |
| Rg:                       | 96.5     |           |      |      |       |



### Test Conditions

Stabilization Time: 34M  
 Operation Time: 1H 34M  
 Sphere Temperature (°C): 25.2


REPORT NUMBER: SP1-2407-184-1

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |



REPORT NUMBER: SP1-2407-184-1

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 139                      | NR            | 620    | 607                      | NR            | 750    | 15                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 198                      | NR            | 625    | 554                      | NR            | 755    | 13                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 267                      | NR            | 630    | 504                      | NR            | 760    | 11                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 343                      | NR            | 635    | 452                      | NR            | 765    | 10                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 410                      | NR            | 640    | 403                      | NR            | 770    | 8                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 470                      | NR            | 645    | 357                      | NR            | 775    | 7                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 516                      | NR            | 650    | 314                      | NR            | 780    | 6                        | NR            | 910    | 0                        | NR            |
| 395    | 7                        | NR            | 525    | 550                      | NR            | 655    | 275                      | NR            | 785    | 5                        | NR            | 915    | 0                        | NR            |
| 400    | 10                       | NR            | 530    | 578                      | NR            | 660    | 240                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 17                       | NR            | 535    | 601                      | NR            | 665    | 208                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 35                       | NR            | 540    | 620                      | NR            | 670    | 179                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 70                       | NR            | 545    | 641                      | NR            | 675    | 155                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 147                      | NR            | 550    | 664                      | NR            | 680    | 133                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 285                      | NR            | 555    | 689                      | NR            | 685    | 114                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 487                      | NR            | 560    | 715                      | NR            | 690    | 98                       | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 787                      | NR            | 565    | 743                      | NR            | 695    | 84                       | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 1000                     | NR            | 570    | 771                      | NR            | 700    | 72                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 783                      | NR            | 575    | 794                      | NR            | 705    | 61                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 417                      | NR            | 580    | 811                      | NR            | 710    | 52                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 261                      | NR            | 585    | 817                      | NR            | 715    | 45                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 167                      | NR            | 590    | 815                      | NR            | 720    | 39                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 104                      | NR            | 595    | 801                      | NR            | 725    | 33                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 79                       | NR            | 600    | 777                      | NR            | 730    | 28                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 73                       | NR            | 605    | 744                      | NR            | 735    | 24                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 76                       | NR            | 610    | 704                      | NR            | 740    | 21                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 98                       | NR            | 615    | 657                      | NR            | 745    | 18                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-1

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.47

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 139                         | NR               | 620       | 607                         | NR               | 750       | 15                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 198                         | NR               | 625       | 554                         | NR               | 755       | 13                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 267                         | NR               | 630       | 504                         | NR               | 760       | 11                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 343                         | NR               | 635       | 452                         | NR               | 765       | 10                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 410                         | NR               | 640       | 403                         | NR               | 770       | 8                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 470                         | NR               | 645       | 357                         | NR               | 775       | 7                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 516                         | NR               | 650       | 314                         | NR               | 780       | 6                           | NR               | 910       | 0                           | NR               |
| 395       | 7                           | NR               | 525       | 550                         | NR               | 655       | 275                         | NR               | 785       | 5                           | NR               | 915       | 0                           | NR               |
| 400       | 10                          | NR               | 530       | 578                         | NR               | 660       | 240                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 17                          | NR               | 535       | 601                         | NR               | 665       | 208                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 35                          | NR               | 540       | 620                         | NR               | 670       | 179                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 70                          | NR               | 545       | 641                         | NR               | 675       | 155                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 147                         | NR               | 550       | 664                         | NR               | 680       | 133                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 285                         | NR               | 555       | 689                         | NR               | 685       | 114                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 487                         | NR               | 560       | 715                         | NR               | 690       | 98                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 787                         | NR               | 565       | 743                         | NR               | 695       | 84                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 1000                        | NR               | 570       | 771                         | NR               | 700       | 72                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 783                         | NR               | 575       | 794                         | NR               | 705       | 61                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 417                         | NR               | 580       | 811                         | NR               | 710       | 52                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 261                         | NR               | 585       | 817                         | NR               | 715       | 45                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 167                         | NR               | 590       | 815                         | NR               | 720       | 39                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 104                         | NR               | 595       | 801                         | NR               | 725       | 33                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 79                          | NR               | 600       | 777                         | NR               | 730       | 28                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 73                          | NR               | 605       | 744                         | NR               | 735       | 24                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 704                         | NR               | 740       | 21                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 98                          | NR               | 615       | 657                         | NR               | 745       | 18                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-1

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.78


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 139                         | NR               | 620       | 607                         | NR               | 750       | 15                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 198                         | NR               | 625       | 554                         | NR               | 755       | 13                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 267                         | NR               | 630       | 504                         | NR               | 760       | 11                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 343                         | NR               | 635       | 452                         | NR               | 765       | 10                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 410                         | NR               | 640       | 403                         | NR               | 770       | 8                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 470                         | NR               | 645       | 357                         | NR               | 775       | 7                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 516                         | NR               | 650       | 314                         | NR               | 780       | 6                           | NR               | 910       | 0                           | NR               |
| 395       | 7                           | NR               | 525       | 550                         | NR               | 655       | 275                         | NR               | 785       | 5                           | NR               | 915       | 0                           | NR               |
| 400       | 10                          | NR               | 530       | 578                         | NR               | 660       | 240                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 17                          | NR               | 535       | 601                         | NR               | 665       | 208                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 35                          | NR               | 540       | 620                         | NR               | 670       | 179                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 70                          | NR               | 545       | 641                         | NR               | 675       | 155                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 147                         | NR               | 550       | 664                         | NR               | 680       | 133                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 285                         | NR               | 555       | 689                         | NR               | 685       | 114                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 487                         | NR               | 560       | 715                         | NR               | 690       | 98                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 787                         | NR               | 565       | 743                         | NR               | 695       | 84                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 1000                        | NR               | 570       | 771                         | NR               | 700       | 72                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 783                         | NR               | 575       | 794                         | NR               | 705       | 61                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 417                         | NR               | 580       | 811                         | NR               | 710       | 52                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 261                         | NR               | 585       | 817                         | NR               | 715       | 45                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 167                         | NR               | 590       | 815                         | NR               | 720       | 39                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 104                         | NR               | 595       | 801                         | NR               | 725       | 33                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 79                          | NR               | 600       | 777                         | NR               | 730       | 28                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 73                          | NR               | 605       | 744                         | NR               | 735       | 24                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 704                         | NR               | 740       | 21                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 98                          | NR               | 615       | 657                         | NR               | 745       | 18                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-1





TM-30-18

### Summary

$R_f = 71.8$   
 $R_g = 96.5$   
 $CIE R_a = 70.7$   
 $R_g = -36.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 56 | CES51 = 86 | CES76 = 48 |
| CES02 = 61 | CES27 = 79 | CES52 = 88 | CES77 = 71 |
| CES03 = 30 | CES28 = 80 | CES53 = 73 | CES78 = 52 |
| CES04 = 70 | CES29 = 49 | CES54 = 79 | CES79 = 79 |
| CES05 = 47 | CES30 = 53 | CES55 = 77 | CES80 = 77 |
| CES06 = 50 | CES31 = 55 | CES56 = 67 | CES81 = 75 |
| CES07 = 40 | CES32 = 53 | CES57 = 64 | CES82 = 90 |
| CES08 = 39 | CES33 = 59 | CES58 = 67 | CES83 = 84 |
| CES09 = 29 | CES34 = 67 | CES59 = 87 | CES84 = 89 |
| CES10 = 74 | CES35 = 82 | CES60 = 91 | CES85 = 86 |
| CES11 = 57 | CES36 = 86 | CES61 = 87 | CES86 = 71 |
| CES12 = 63 | CES37 = 76 | CES62 = 76 | CES87 = 78 |
| CES13 = 42 | CES38 = 62 | CES63 = 73 | CES88 = 76 |
| CES14 = 74 | CES39 = 91 | CES64 = 71 | CES89 = 72 |
| CES15 = 71 | CES40 = 84 | CES65 = 64 | CES90 = 72 |
| CES16 = 46 | CES41 = 81 | CES66 = 67 | CES91 = 97 |
| CES17 = 49 | CES42 = 76 | CES67 = 65 | CES92 = 66 |
| CES18 = 56 | CES43 = 71 | CES68 = 72 | CES93 = 81 |
| CES19 = 72 | CES44 = 98 | CES69 = 82 | CES94 = 55 |
| CES20 = 65 | CES45 = 80 | CES70 = 61 | CES95 = 73 |
| CES21 = 86 | CES46 = 76 | CES71 = 59 | CES96 = 78 |
| CES22 = 78 | CES47 = 71 | CES72 = 86 | CES97 = 83 |
| CES23 = 92 | CES48 = 61 | CES73 = 52 | CES98 = 72 |
| CES24 = 91 | CES49 = 76 | CES74 = 93 | CES99 = 60 |
| CES25 = 72 | CES50 = 84 | CES75 = 56 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)