

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047207

Luminaire Tested: **GALN-SA4C-750-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047207
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA4C-750-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 4xLight Square PACKAGE
70CRI 5000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (56) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 23678.7 lumens
Efficiency: N/A
Efficacy: 124.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 190.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047207

CATALOG NUMBER: GALN-SA4C-750-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 26.6 fc
 Type III - Short - N/A

REPORT NUMBER: P1047207

CATALOG NUMBER: GALN-SA4C-750-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047207

CATALOG NUMBER: GALN-SA4C-750-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	86.5	0.0	86.5
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	23592.3	0.0	23592.3
	% Fixture	99.6	0.0	99.6
Total	Lumens	23678.7	0.0	23678.7
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.7	0.1
10°-20°	272.2	1.1
20°-30°	981.0	4.1
30°-40°	2244.6	9.5
40°-50°	3785.8	16.0
50°-60°	6247.4	26.4
60°-70°	6982.3	29.5
70°-80°	2882.9	12.2
80°-90°	259.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	23678.7	100.0
0°-180°	23678.7	100.0



REPORT NUMBER: P1047207


CATALOG NUMBER: GALN-SA4C-750-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1253.4	5.3			
FM	(30°-60°)	12257.0	51.8			
FH	(60°-80°)	9825.6	41.5			G4/12000
FVH	(80°-90°)	256.3	1.1			G3/500
BL	(0°-30°)	22.5	0.1	B0/110		
BM	(30°-60°)	20.7	0.1	B0/220		
BH	(60°-80°)	39.6	0.2	B0/110		G0/110
BVH	(80°-90°)	3.6	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type III Short



REPORT NUMBER: P1047207

CATALOG NUMBER: GALN-SA4C-750-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8
2.5°	185.8	192.0	185.8	185.8	185.8	179.6	179.6	173.4	173.4	167.2	161.0
5°	272.5	272.5	253.9	241.5	229.1	222.9	216.8	204.4	192.0	179.6	167.2
7.5°	606.9	606.9	551.2	476.9	377.8	322.0	309.6	253.9	216.8	192.0	167.2
10°	1449.2	1449.2	1325.3	1120.9	867.0	644.1	575.9	365.4	260.1	204.4	173.4
12.5°	2409.1	2440.0	2285.2	2025.1	1647.3	1257.2	1120.9	668.8	346.8	222.9	173.4
15°	3269.9	3195.6	3152.2	2904.5	2545.3	2080.8	1907.4	1127.1	501.6	253.9	173.4
17.5°	3852.0	3852.0	3790.1	3622.9	3294.7	2885.9	2743.5	1820.7	811.3	291.1	179.6
20°	4533.2	4533.2	4421.8	4304.1	4013.0	3666.2	3530.0	2588.7	1257.2	371.6	179.6
22.5°	5356.9	5369.3	5245.4	5034.9	4756.2	4372.2	4254.6	3300.8	1820.7	495.4	185.8
25°	6360.2	6372.6	6193.0	5994.8	5567.5	5152.5	4972.9	4118.3	2508.1	693.6	185.8
27.5°	7468.7	7555.4	7289.1	6948.5	6496.4	5976.2	5840.0	4855.3	3189.4	978.5	198.2
30°	8849.7	8849.7	8496.7	8019.9	7530.6	6886.6	6713.2	5629.4	3913.9	1356.3	210.6
32.5°	10038.8	9945.9	9493.8	8992.2	8472.0	7871.2	7685.5	6440.7	4657.1	1826.9	235.3
35°	10949.1	10868.6	10311.3	9772.5	9320.4	8769.2	8546.3	7320.1	5443.6	2359.5	272.5
37.5°	11729.5	11698.5	10943.0	10267.9	9970.7	9487.6	9289.4	8149.9	6217.7	2935.5	315.8
40°	12584.1	12485.0	11679.9	10843.9	10398.0	10007.8	9828.2	8818.8	6960.9	3610.5	377.8
42.5°	13314.9	13197.2	12472.6	11655.1	10893.4	10367.0	10193.6	9382.3	7685.5	4285.5	458.3
45°	14126.1	14064.2	13333.4	12714.1	11698.5	10856.3	10627.1	9834.4	8348.1	5090.6	563.6
47.5°	15346.1	15234.7	14553.4	14045.6	12869.0	11599.4	11271.2	10298.9	8986.0	5883.3	724.6
50°	16764.3	16690.0	16287.5	15884.9	14714.5	12869.0	12478.8	10967.7	9698.2	6824.6	935.1
52.5°	17922.4	17910.0	17959.6	17965.8	17080.2	15005.5	14423.4	12045.3	10515.6	7753.6	1232.4
55°	17897.6	17953.4	18498.4	19123.9	19192.0	17922.4	17358.9	13859.8	11580.8	8899.3	1647.3
57.5°	17228.8	17185.5	17761.4	18702.7	19365.4	19501.6	19408.7	16677.6	13184.8	10280.3	2285.2
58°	17012.1	16974.9	17519.9	18479.8	19241.5	19606.9	19514.0	17315.5	13544.0	10478.5	2458.6
60°	16225.5	16231.7	16553.8	17427.0	18188.7	19055.7	19142.4	19136.2	15333.8	11803.8	3331.8
62.5°	15185.1	15135.6	15432.8	16145.0	16813.9	17396.0	17544.6	19260.1	17953.4	13488.3	4997.7
65°	13748.4	13674.0	13989.9	14795.0	15513.4	15891.1	15897.3	17600.4	19185.8	15296.6	7375.8
67.5°	11079.2	11017.3	11649.0	12683.2	13791.7	14287.2	14510.1	15271.8	18145.4	16522.8	8738.3
70°	6787.5	6917.5	7796.9	9419.5	11314.5	12224.9	12559.3	12794.6	15451.4	16337.0	7307.7
72.5°	3133.6	2978.8	3728.2	4861.5	7022.8	9047.9	9394.7	10317.5	12249.7	14181.9	5449.8
75°	1461.5	1405.8	1579.2	2124.2	3183.2	4886.2	5517.9	8236.6	9394.7	9865.4	3932.5
77.5°	749.3	755.5	898.0	966.1	1312.9	2260.4	2594.8	5418.8	6886.6	5505.5	2638.2
80°	328.2	340.6	346.8	377.8	532.6	873.2	984.7	2514.3	4706.6	2805.4	1443.0
82.5°	210.6	216.8	216.8	216.8	253.9	346.8	396.3	1009.5	2347.1	1393.4	445.9
85°	111.5	111.5	123.9	154.8	179.6	210.6	222.9	322.0	774.1	414.9	105.3
87.5°	61.9	68.1	74.3	92.9	117.7	142.4	154.8	222.9	297.3	284.9	24.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1047207

CATALOG NUMBER: GALN-SA4C-750-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8	154.8
2.5°	161.0	154.8	148.6	142.4	136.2	130.1	130.1	130.1	130.1	130.1	130.1
5°	154.8	148.6	142.4	130.1	117.7	111.5	105.3	99.1	99.1	99.1	99.1
7.5°	154.8	148.6	130.1	117.7	105.3	92.9	80.5	80.5	80.5	80.5	80.5
10°	154.8	142.4	123.9	105.3	86.7	74.3	68.1	61.9	61.9	61.9	61.9
12.5°	154.8	136.2	117.7	92.9	74.3	61.9	55.7	49.5	49.5	49.5	49.5
15°	154.8	136.2	111.5	86.7	68.1	49.5	43.4	37.2	37.2	37.2	37.2
17.5°	148.6	130.1	105.3	74.3	55.7	37.2	31.0	24.8	24.8	31.0	31.0
20°	142.4	123.9	92.9	61.9	43.4	31.0	18.6	18.6	18.6	18.6	18.6
22.5°	142.4	123.9	86.7	55.7	37.2	18.6	12.4	12.4	12.4	12.4	18.6
25°	142.4	117.7	74.3	43.4	24.8	12.4	6.2	6.2	6.2	6.2	6.2
27.5°	142.4	117.7	68.1	37.2	18.6	12.4	6.2	0.0	0.0	0.0	0.0
30°	136.2	111.5	61.9	31.0	12.4	6.2	0.0	0.0	0.0	0.0	0.0
32.5°	136.2	105.3	49.5	24.8	12.4	6.2	0.0	0.0	0.0	0.0	0.0
35°	142.4	99.1	43.4	18.6	6.2	0.0	0.0	0.0	0.0	0.0	6.2
37.5°	148.6	92.9	37.2	12.4	6.2	0.0	0.0	0.0	0.0	0.0	0.0
40°	154.8	86.7	37.2	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	167.2	86.7	31.0	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	179.6	86.7	24.8	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	204.4	92.9	24.8	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	222.9	99.1	18.6	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	247.7	92.9	18.6	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	278.7	92.9	18.6	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	303.5	86.7	18.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	315.8	80.5	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	377.8	74.3	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	588.3	61.9	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1195.2	55.7	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2229.5	49.5	12.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2495.8	55.7	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1573.0	43.4	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	829.9	43.4	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	414.9	43.4	6.2	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	192.0	31.0	6.2	6.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	80.5	18.6	12.4	6.2	6.2	0.0	0.0	0.0	0.0	0.0	0.0
85°	37.2	18.6	12.4	12.4	6.2	6.2	0.0	0.0	0.0	0.0	0.0
87.5°	18.6	18.6	18.6	12.4	12.4	6.2	6.2	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ

Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-750-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896	CRI (Ra):	70.2		
CIE u':	0.2101	R1:	68.1	R9:	-35.1
CIE v':	0.4901	R2:	73.9	R10:	39.3
Duv:	0.0035	R3:	79.4	R11:	71.1
CIE x:	0.3489	R4:	72.1	R12:	43.8
CIE y:	0.3618	R5:	69.2	R13:	68.1
CIE z:	0.2893	R6:	65.7	R14:	88.4
Peak Wavelength (nm):	443	R7:	78.1	R15:	59.7
Dominant Wavelength (nm):	570	R8:	55.3		
Purity:	13.25435				
Rf:	70.7				
Rg:	96.8				



Test Conditions

Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-6

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.7

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.37

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

TM-30-18

Summary

$R_f = 70.7$
 $R_g = 96.8$
 $CIE R_a = 70.2$
 $R_g = -35.1$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)