

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049641

Luminaire Tested: **GALN-SA1A-750-U-LBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1049641  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA1A-750-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 1xLight Square PACKAGE  
70CRI 5000K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (14) 5000K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3342.5 lumens  
Efficiency: N/A  
Efficacy: 115.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G1

Input Watts (W): 29  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049641  
 CATALOG NUMBER: GALN-SA1A-750-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.8 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049641  
CATALOG NUMBER: GALN-SA1A-750-U-LBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049641

CATALOG NUMBER: GALN-SA1A-750-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 22.8     | 0.0    | 22.8   |
|                    | % Fixture | 0.7      | 0.0    | 0.7    |
| <b>Street Side</b> | Lumens    | 3319.6   | 0.0    | 3319.6 |
|                    | % Fixture | 99.3     | 0.0    | 99.3   |
| <b>Total</b>       | Lumens    | 3342.5   | 0.0    | 3342.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1.3    | 0.0       |
| 10°-20°   | 7.3    | 0.2       |
| 20°-30°   | 79.2   | 2.4       |
| 30°-40°   | 234.2  | 7.0       |
| 40°-50°   | 698.0  | 20.9      |
| 50°-60°   | 1107.5 | 33.1      |
| 60°-70°   | 923.8  | 27.6      |
| 70°-80°   | 284.9  | 8.5       |
| 80°-90°   | 6.3    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 3342.5 | 100.0     |
| 0°-180°   | 3342.5 | 100.0     |



REPORT NUMBER: P1049641


CATALOG NUMBER: GALN-SA1A-750-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 85.6   | 2.6       |                         |      |         |
| FM   | (30°-60°)   | 2027.1 | 60.6      |                         |      |         |
| FH   | (60°-80°)   | 1200.9 | 35.9      |                         |      | G1/1800 |
| FVH  | (80°-90°)   | 6.0    | 0.2       |                         |      | G0/10   |
| BL   | (0°-30°)    | 2.2    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 12.5   | 0.4       | B0/220                  |      |         |
| BH   | (60°-80°)   | 7.8    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 0.3    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G1**

Type III Short





REPORT NUMBER: P1049641

CATALOG NUMBER: GALN-SA1A-750-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°     | 15°    | 25°    | 35°    | 44°    | 45°    | 55°    | 65°    | 75°    |
|-------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 14.6  | 14.6   | 14.6   | 14.6   | 14.6   | 14.6   | 14.6   | 14.6   | 14.6   | 14.6   |
| 2.5°  | 18.9  | 18.9   | 18.2   | 17.2   | 16.2   | 15.1   | 14.9   | 14.4   | 14.1   | 13.9   |
| 5°    | 19.7  | 19.7   | 19.4   | 18.7   | 17.7   | 16.9   | 16.9   | 16.2   | 15.7   | 15.1   |
| 7.5°  | 20.2  | 20.5   | 21.0   | 20.7   | 20.2   | 19.4   | 19.4   | 18.9   | 18.2   | 16.9   |
| 10°   | 21.0  | 21.7   | 22.7   | 23.2   | 23.5   | 23.5   | 23.2   | 23.0   | 21.7   | 19.9   |
| 12.5° | 21.7  | 23.2   | 25.8   | 28.3   | 29.8   | 31.8   | 31.6   | 31.1   | 27.8   | 24.0   |
| 15°   | 23.2  | 25.5   | 30.8   | 38.1   | 49.5   | 56.6   | 59.3   | 56.8   | 46.0   | 32.3   |
| 17.5° | 25.0  | 28.8   | 44.7   | 79.8   | 130.8  | 155.0  | 169.7  | 157.8  | 104.5  | 61.4   |
| 20°   | 26.8  | 35.1   | 83.1   | 206.8  | 339.4  | 418.6  | 440.6  | 406.3  | 260.8  | 116.9  |
| 22.5° | 29.8  | 49.2   | 168.4  | 427.5  | 731.2  | 850.1  | 872.6  | 762.8  | 492.6  | 230.8  |
| 25°   | 36.1  | 71.5   | 290.4  | 696.6  | 1091.3 | 1292.0 | 1282.7 | 1138.7 | 799.1  | 368.6  |
| 27.5° | 45.2  | 104.0  | 439.1  | 989.8  | 1436.2 | 1613.2 | 1634.4 | 1456.4 | 1065.3 | 542.1  |
| 30°   | 58.3  | 144.2  | 598.7  | 1224.6 | 1712.7 | 1904.1 | 1907.6 | 1723.5 | 1303.4 | 694.4  |
| 32.5° | 71.0  | 182.0  | 738.3  | 1451.6 | 1985.1 | 2194.9 | 2210.6 | 1984.1 | 1481.1 | 852.9  |
| 35°   | 80.5  | 206.8  | 879.7  | 1651.1 | 2259.8 | 2548.9 | 2547.9 | 2279.0 | 1691.7 | 994.6  |
| 37.5° | 81.3  | 231.5  | 1007.7 | 1855.1 | 2607.8 | 2931.5 | 2963.5 | 2667.1 | 1946.2 | 1169.8 |
| 40°   | 79.5  | 259.3  | 1169.8 | 2173.2 | 3234.7 | 3731.4 | 3759.6 | 3385.9 | 2456.8 | 1469.8 |
| 42.5° | 81.6  | 307.5  | 1432.9 | 2760.8 | 4275.7 | 4989.0 | 5043.6 | 4650.7 | 3395.3 | 2081.8 |
| 45°   | 92.2  | 398.2  | 1984.1 | 3743.7 | 5759.6 | 6629.2 | 6611.1 | 6045.2 | 4487.3 | 3013.5 |
| 47.5° | 127.3 | 620.1  | 2801.2 | 4700.4 | 6708.0 | 7482.4 | 7498.1 | 6806.5 | 5124.6 | 3729.8 |
| 50°   | 195.7 | 948.9  | 3487.7 | 5206.2 | 7115.8 | 7892.7 | 7878.1 | 7078.9 | 5366.8 | 4082.6 |
| 52.5° | 254.5 | 1186.7 | 3832.1 | 5383.7 | 7168.1 | 8095.5 | 8094.5 | 7150.6 | 5404.4 | 4112.9 |
| 55°   | 269.2 | 1204.6 | 3834.9 | 5393.3 | 7285.2 | 8360.8 | 8394.2 | 7327.1 | 5453.1 | 3980.6 |
| 57.5° | 263.4 | 1066.5 | 3674.8 | 5448.8 | 7493.8 | 8566.1 | 8567.9 | 7498.1 | 5576.8 | 3899.5 |
| 58°   | 258.3 | 1044.8 | 3642.5 | 5480.4 | 7529.6 | 8574.7 | 8570.4 | 7505.9 | 5677.6 | 3896.5 |
| 60°   | 230.0 | 907.2  | 3516.5 | 5560.9 | 7476.3 | 8398.5 | 8358.3 | 7335.0 | 5662.7 | 3865.4 |
| 62.5° | 180.8 | 707.7  | 3392.5 | 5467.8 | 6905.2 | 7545.3 | 7561.9 | 6493.9 | 5162.2 | 3684.4 |
| 65°   | 143.9 | 527.5  | 3134.0 | 4796.1 | 5686.2 | 6196.2 | 6258.3 | 5280.7 | 4308.8 | 3119.8 |
| 67.5° | 114.6 | 381.3  | 2629.0 | 3818.5 | 4499.4 | 5171.3 | 5216.5 | 4433.5 | 3338.2 | 2390.4 |
| 70°   | 93.2  | 257.8  | 1814.7 | 2792.6 | 3711.2 | 4466.6 | 4469.4 | 3683.1 | 2491.6 | 1566.2 |
| 72.5° | 82.6  | 178.5  | 1053.4 | 2036.6 | 3009.2 | 3639.7 | 3566.2 | 2988.8 | 1914.9 | 927.7  |
| 75°   | 71.5  | 118.4  | 516.6  | 1245.0 | 1824.5 | 1836.9 | 1864.9 | 1386.4 | 957.2  | 441.1  |
| 77.5° | 58.8  | 84.1   | 203.5  | 340.1  | 547.2  | 700.4  | 726.4  | 550.4  | 318.4  | 108.6  |
| 80°   | 40.4  | 39.9   | 54.8   | 104.3  | 156.5  | 196.2  | 183.1  | 141.6  | 83.3   | 41.7   |
| 82.5° | 17.4  | 18.9   | 24.7   | 29.8   | 24.2   | 23.5   | 22.5   | 14.4   | 11.1   | 8.6    |
| 85°   | 5.6   | 5.0    | 5.3    | 5.3    | 4.3    | 3.3    | 3.3    | 1.5    | 0.0    | 0.0    |
| 87.5° | 2.8   | 2.3    | 2.3    | 2.0    | 1.3    | 0.5    | 0.3    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

REPORT NUMBER: P1049641

CATALOG NUMBER: GALN-SA1A-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°    |       | 90°   | 95°   | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|--------|-------|-------|-------|------|------|------|------|------|------|------|------|
| 14.6   | 0°    | 14.6  | 14.6  | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 |
| 13.6   | 2.5°  | 13.4  | 13.4  | 12.9 | 12.4 | 12.1 | 11.6 | 11.4 | 11.1 | 10.9 | 10.6 |
| 14.6   | 5°    | 14.1  | 13.9  | 13.1 | 12.4 | 11.6 | 10.9 | 10.4 | 9.8  | 9.3  | 9.1  |
| 16.2   | 7.5°  | 15.4  | 14.9  | 13.4 | 12.1 | 11.1 | 10.1 | 9.6  | 8.8  | 8.3  | 7.6  |
| 17.9   | 10°   | 16.9  | 15.9  | 13.9 | 12.4 | 10.9 | 9.6  | 8.8  | 8.1  | 7.3  | 6.3  |
| 20.5   | 12.5° | 18.9  | 17.2  | 14.6 | 12.1 | 10.4 | 8.8  | 8.1  | 7.1  | 6.3  | 5.6  |
| 23.7   | 15°   | 20.7  | 18.4  | 14.9 | 12.1 | 9.8  | 8.1  | 7.1  | 6.1  | 5.3  | 4.3  |
| 29.8   | 17.5° | 23.2  | 19.4  | 14.6 | 11.4 | 9.1  | 7.1  | 6.1  | 5.3  | 4.0  | 2.5  |
| 44.2   | 20°   | 27.5  | 20.2  | 14.1 | 10.6 | 7.8  | 5.8  | 4.5  | 3.5  | 1.8  | 0.5  |
| 66.4   | 22.5° | 34.3  | 22.2  | 13.6 | 9.6  | 6.8  | 4.5  | 3.0  | 1.3  | 0.0  | 0.0  |
| 101.0  | 25°   | 47.5  | 25.8  | 13.6 | 9.1  | 6.1  | 3.3  | 1.0  | 0.0  | 0.0  | 0.0  |
| 143.4  | 27.5° | 63.1  | 30.6  | 13.6 | 7.8  | 4.8  | 1.8  | 0.0  | 0.0  | 0.0  | 0.0  |
| 195.4  | 30°   | 79.0  | 35.9  | 13.6 | 6.8  | 3.8  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  |
| 240.6  | 32.5° | 94.2  | 40.4  | 13.9 | 5.8  | 2.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 303.2  | 35°   | 109.6 | 41.2  | 13.6 | 5.0  | 1.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 380.0  | 37.5° | 129.3 | 39.6  | 12.9 | 4.5  | 0.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 499.9  | 40°   | 159.1 | 40.4  | 12.1 | 4.3  | 0.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 713.8  | 42.5° | 214.1 | 43.7  | 11.1 | 4.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1137.0 | 45°   | 370.2 | 58.6  | 10.1 | 4.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1706.9 | 47.5° | 612.3 | 105.3 | 9.8  | 4.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2056.1 | 50°   | 781.5 | 132.6 | 10.4 | 4.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2099.7 | 52.5° | 780.2 | 147.7 | 10.9 | 5.0  | 1.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1935.4 | 55°   | 693.6 | 150.5 | 11.6 | 5.6  | 3.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1663.2 | 57.5° | 579.7 | 137.4 | 13.4 | 6.8  | 6.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1620.5 | 58°   | 559.5 | 131.3 | 13.9 | 7.1  | 6.6  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1405.6 | 60°   | 458.5 | 107.1 | 17.7 | 8.8  | 8.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1152.4 | 62.5° | 316.6 | 93.4  | 20.2 | 11.4 | 9.1  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 849.6  | 65°   | 224.0 | 84.3  | 22.0 | 12.1 | 7.3  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 603.7  | 67.5° | 167.4 | 77.8  | 24.2 | 12.4 | 3.8  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 378.7  | 70°   | 128.3 | 73.0  | 29.8 | 13.1 | 1.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 225.7  | 72.5° | 104.5 | 67.4  | 36.1 | 13.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 135.3  | 75°   | 86.6  | 60.9  | 34.8 | 14.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 72.2   | 77.5° | 57.6  | 47.2  | 31.8 | 14.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 25.8   | 80°   | 20.2  | 18.7  | 24.7 | 13.1 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5.3    | 82.5° | 3.0   | 2.5   | 3.5  | 4.5  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 85°   | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 87.5° | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0    | 90°   | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |



REPORT NUMBER: P1049641

CATALOG NUMBER: GALN-SA1A-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265° | 270° |
|------|-------|------|------|------|------|------|------|------|------|------|------|
| 14.6 | 0°    | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 |
| 10.4 | 2.5°  | 10.4 | 10.4 | 10.1 | 10.4 | 10.4 | 10.9 | 12.1 | 13.9 | 15.9 | 16.7 |
| 8.8  | 5°    | 8.6  | 8.3  | 8.1  | 8.1  | 8.1  | 8.8  | 9.8  | 11.9 | 14.1 | 15.1 |
| 7.3  | 7.5°  | 7.1  | 6.8  | 6.6  | 6.3  | 6.3  | 6.8  | 8.1  | 10.4 | 12.6 | 13.6 |
| 6.1  | 10°   | 5.8  | 5.3  | 5.0  | 4.8  | 4.8  | 5.3  | 6.6  | 8.8  | 11.4 | 12.4 |
| 5.0  | 12.5° | 4.8  | 4.0  | 3.5  | 3.3  | 3.0  | 3.8  | 5.0  | 7.1  | 9.8  | 11.1 |
| 3.8  | 15°   | 3.3  | 2.5  | 1.8  | 1.5  | 1.3  | 2.0  | 3.3  | 5.6  | 8.3  | 9.8  |
| 2.0  | 17.5° | 1.8  | 0.8  | 0.3  | 0.0  | 0.0  | 0.5  | 1.5  | 4.0  | 6.8  | 8.1  |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 2.0  | 5.0  | 6.3  |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.3  | 3.0  | 4.3  |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.3  | 2.3  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.5  |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.8  |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.0  | 2.0  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1049641

CATALOG NUMBER: GALN-SA1A-750-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275° |       | 285° | 295° | 305° | 315° | 316° | 325° | 335° | 345° | 355° | 360°  |
|------|-------|------|------|------|------|------|------|------|------|------|-------|
| 14.6 | 0°    | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6 | 14.6  |
| 17.4 | 2.5°  | 17.9 | 17.7 | 17.2 | 16.7 | 16.7 | 16.7 | 17.4 | 18.2 | 18.9 | 18.9  |
| 15.7 | 5°    | 16.7 | 16.7 | 16.4 | 15.9 | 15.9 | 16.2 | 17.2 | 18.4 | 19.4 | 19.7  |
| 14.4 | 7.5°  | 15.4 | 15.9 | 15.4 | 15.1 | 15.4 | 15.7 | 16.7 | 18.2 | 19.7 | 20.2  |
| 13.4 | 10°   | 14.6 | 14.9 | 14.9 | 14.6 | 14.6 | 15.1 | 16.2 | 18.2 | 20.2 | 21.0  |
| 12.1 | 12.5° | 13.6 | 14.1 | 13.9 | 13.9 | 13.9 | 14.4 | 15.7 | 17.9 | 20.7 | 21.7  |
| 10.9 | 15°   | 12.6 | 13.4 | 13.4 | 13.1 | 13.1 | 13.4 | 15.1 | 17.7 | 21.5 | 23.2  |
| 9.3  | 17.5° | 11.6 | 12.4 | 12.6 | 12.1 | 12.1 | 12.6 | 14.4 | 17.7 | 22.0 | 25.0  |
| 7.6  | 20°   | 9.6  | 10.9 | 11.6 | 10.9 | 10.9 | 11.4 | 13.1 | 16.7 | 22.2 | 26.8  |
| 5.6  | 22.5° | 7.6  | 8.8  | 9.8  | 9.6  | 9.6  | 9.8  | 12.1 | 15.9 | 22.5 | 29.8  |
| 3.3  | 25°   | 5.6  | 6.8  | 7.6  | 8.1  | 8.1  | 8.8  | 11.1 | 15.4 | 23.5 | 36.1  |
| 1.5  | 27.5° | 3.3  | 4.8  | 5.8  | 6.3  | 6.6  | 7.6  | 10.4 | 14.9 | 25.2 | 45.2  |
| 0.0  | 30°   | 1.5  | 2.8  | 4.0  | 5.0  | 5.0  | 6.8  | 9.6  | 14.4 | 27.5 | 58.3  |
| 0.0  | 32.5° | 0.0  | 1.3  | 2.0  | 3.5  | 3.8  | 5.6  | 8.8  | 13.9 | 30.8 | 71.0  |
| 0.0  | 35°   | 0.0  | 0.0  | 1.0  | 2.8  | 2.8  | 4.5  | 8.1  | 13.4 | 35.9 | 80.5  |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 2.0  | 2.3  | 4.0  | 7.8  | 13.1 | 36.9 | 81.3  |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 1.5  | 1.8  | 3.8  | 7.8  | 13.4 | 33.3 | 79.5  |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 1.0  | 1.3  | 3.8  | 7.8  | 13.9 | 30.0 | 81.6  |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.8  | 1.0  | 4.0  | 7.6  | 13.6 | 28.3 | 92.2  |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 1.0  | 1.5  | 4.0  | 7.3  | 13.4 | 28.5 | 127.3 |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 1.3  | 1.8  | 4.0  | 7.6  | 12.9 | 31.3 | 195.7 |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 1.0  | 1.5  | 4.5  | 8.3  | 12.6 | 34.1 | 254.5 |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.3  | 0.8  | 5.8  | 9.1  | 12.6 | 38.4 | 269.2 |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.6  | 10.4 | 13.4 | 45.4 | 263.4 |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.6  | 10.6 | 13.4 | 46.0 | 258.3 |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.6  | 11.6 | 14.9 | 49.5 | 230.0 |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 5.6  | 13.9 | 18.7 | 51.5 | 180.8 |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 4.5  | 16.4 | 20.5 | 53.0 | 143.9 |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 4.3  | 16.9 | 20.7 | 53.8 | 114.6 |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 4.5  | 16.7 | 22.2 | 56.3 | 93.2  |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 5.0  | 15.1 | 24.5 | 56.3 | 82.6  |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 5.3  | 14.1 | 27.5 | 51.3 | 71.5  |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 5.0  | 13.9 | 32.1 | 45.7 | 58.8  |
| 0.0  | 80°   | 0.5  | 0.8  | 0.8  | 0.5  | 0.5  | 4.3  | 13.6 | 32.6 | 38.9 | 40.4  |
| 0.3  | 82.5° | 1.5  | 2.0  | 1.8  | 1.3  | 1.3  | 3.8  | 12.1 | 27.3 | 20.2 | 17.4  |
| 1.5  | 85°   | 2.8  | 3.3  | 3.3  | 2.8  | 2.8  | 3.5  | 7.6  | 9.8  | 6.8  | 5.6   |
| 2.8  | 87.5° | 3.8  | 4.3  | 4.3  | 3.8  | 3.8  | 3.5  | 3.3  | 3.0  | 2.8  | 2.8   |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ


Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-6  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-750-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 4896     | CRI (Ra): | 70.2 |      |       |
| CIE u':                   | 0.2101   | R1:       | 68.1 | R9:  | -35.1 |
| CIE v':                   | 0.4901   | R2:       | 73.9 | R10: | 39.3  |
| Duv:                      | 0.0035   | R3:       | 79.4 | R11: | 71.1  |
| CIE x:                    | 0.3489   | R4:       | 72.1 | R12: | 43.8  |
| CIE y:                    | 0.3618   | R5:       | 69.2 | R13: | 68.1  |
| CIE z:                    | 0.2893   | R6:       | 65.7 | R14: | 88.4  |
| Peak Wavelength (nm):     | 443      | R7:       | 78.1 | R15: | 59.7  |
| Dominant Wavelength (nm): | 570      | R8:       | 55.3 |      |       |
| Purity:                   | 13.25435 |           |      |      |       |
| Rf:                       | 70.7     |           |      |      |       |
| Rg:                       | 96.8     |           |      |      |       |



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-6


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-6

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 118                                  | NR                             | 620               | 401                                  | NR                             | 750               | 12                                   | NR                             | 880               | 0                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 168                                  | NR                             | 625               | 365                                  | NR                             | 755               | 10                                   | NR                             | 885               | 0                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 230                                  | NR                             | 630               | 331                                  | NR                             | 760               | 9                                    | NR                             | 890               | 0                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 299                                  | NR                             | 635               | 298                                  | NR                             | 765               | 8                                    | NR                             | 895               | 0                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 362                                  | NR                             | 640               | 266                                  | NR                             | 770               | 6                                    | NR                             | 900               | 0                                    | NR                             |
| 385               | 2                                    | NR                             | 515               | 418                                  | NR                             | 645               | 236                                  | NR                             | 775               | 6                                    | NR                             | 905               | 0                                    | NR                             |
| 390               | 4                                    | NR                             | 520               | 461                                  | NR                             | 650               | 209                                  | NR                             | 780               | 5                                    | NR                             | 910               | 0                                    | NR                             |
| 395               | 6                                    | NR                             | 525               | 491                                  | NR                             | 655               | 184                                  | NR                             | 785               | 4                                    | NR                             | 915               | 0                                    | NR                             |
| 400               | 9                                    | NR                             | 530               | 514                                  | NR                             | 660               | 160                                  | NR                             | 790               | 4                                    | NR                             | 920               | 0                                    | NR                             |
| 405               | 14                                   | NR                             | 535               | 530                                  | NR                             | 665               | 140                                  | NR                             | 795               | 3                                    | NR                             | 925               | 0                                    | NR                             |
| 410               | 27                                   | NR                             | 540               | 539                                  | NR                             | 670               | 122                                  | NR                             | 800               | 3                                    | NR                             | 930               | 0                                    | NR                             |
| 415               | 55                                   | NR                             | 545               | 549                                  | NR                             | 675               | 106                                  | NR                             | 805               | 2                                    | NR                             | 935               | 0                                    | NR                             |
| 420               | 115                                  | NR                             | 550               | 557                                  | NR                             | 680               | 92                                   | NR                             | 810               | 2                                    | NR                             | 940               | 0                                    | NR                             |
| 425               | 226                                  | NR                             | 555               | 565                                  | NR                             | 685               | 79                                   | NR                             | 815               | 2                                    | NR                             | 945               | 0                                    | NR                             |
| 430               | 395                                  | NR                             | 560               | 572                                  | NR                             | 690               | 68                                   | NR                             | 820               | 2                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 648                                  | NR                             | 565               | 580                                  | NR                             | 695               | 59                                   | NR                             | 825               | 1                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 937                                  | NR                             | 570               | 586                                  | NR                             | 700               | 51                                   | NR                             | 830               | 1                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 953                                  | NR                             | 575               | 588                                  | NR                             | 705               | 44                                   | NR                             | 835               | 1                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 591                                  | NR                             | 580               | 588                                  | NR                             | 710               | 38                                   | NR                             | 840               | 1                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 334                                  | NR                             | 585               | 580                                  | NR                             | 715               | 32                                   | NR                             | 845               | 1                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 221                                  | NR                             | 590               | 568                                  | NR                             | 720               | 28                                   | NR                             | 850               | 1                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 140                                  | NR                             | 595               | 550                                  | NR                             | 725               | 24                                   | NR                             | 855               | 1                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 93                                   | NR                             | 600               | 527                                  | NR                             | 730               | 21                                   | NR                             | 860               | 1                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 79                                   | NR                             | 605               | 499                                  | NR                             | 735               | 18                                   | NR                             | 865               | 0                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 76                                   | NR                             | 610               | 469                                  | NR                             | 740               | 15                                   | NR                             | 870               | 0                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 87                                   | NR                             | 615               | 435                                  | NR                             | 745               | 13                                   | NR                             | 875               | 0                                    | NR                             |                   |                                      |                                |



REPORT NUMBER: SP1-2407-184-6

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.7

| λ<br>(nm) | Power<br>W <sup>Λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>Λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>Λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>Λ</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>Λ</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 118                         | NR               | 620       | 401                         | NR               | 750       | 12                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 168                         | NR               | 625       | 365                         | NR               | 755       | 10                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 331                         | NR               | 760       | 9                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 299                         | NR               | 635       | 298                         | NR               | 765       | 8                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 362                         | NR               | 640       | 266                         | NR               | 770       | 6                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 418                         | NR               | 645       | 236                         | NR               | 775       | 6                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 461                         | NR               | 650       | 209                         | NR               | 780       | 5                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 491                         | NR               | 655       | 184                         | NR               | 785       | 4                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 514                         | NR               | 660       | 160                         | NR               | 790       | 4                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 530                         | NR               | 665       | 140                         | NR               | 795       | 3                           | NR               | 925       | 0                           | NR               |
| 410       | 27                          | NR               | 540       | 539                         | NR               | 670       | 122                         | NR               | 800       | 3                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 549                         | NR               | 675       | 106                         | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 115                         | NR               | 550       | 557                         | NR               | 680       | 92                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 226                         | NR               | 555       | 565                         | NR               | 685       | 79                          | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 395                         | NR               | 560       | 572                         | NR               | 690       | 68                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 648                         | NR               | 565       | 580                         | NR               | 695       | 59                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 937                         | NR               | 570       | 586                         | NR               | 700       | 51                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 953                         | NR               | 575       | 588                         | NR               | 705       | 44                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 591                         | NR               | 580       | 588                         | NR               | 710       | 38                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 334                         | NR               | 585       | 580                         | NR               | 715       | 32                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 221                         | NR               | 590       | 568                         | NR               | 720       | 28                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 140                         | NR               | 595       | 550                         | NR               | 725       | 24                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 93                          | NR               | 600       | 527                         | NR               | 730       | 21                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 79                          | NR               | 605       | 499                         | NR               | 735       | 18                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 469                         | NR               | 740       | 15                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 87                          | NR               | 615       | 435                         | NR               | 745       | 13                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-6

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.37


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 118                         | NR               | 620       | 401                         | NR               | 750       | 12                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 168                         | NR               | 625       | 365                         | NR               | 755       | 10                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 230                         | NR               | 630       | 331                         | NR               | 760       | 9                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 299                         | NR               | 635       | 298                         | NR               | 765       | 8                           | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 362                         | NR               | 640       | 266                         | NR               | 770       | 6                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 418                         | NR               | 645       | 236                         | NR               | 775       | 6                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 461                         | NR               | 650       | 209                         | NR               | 780       | 5                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 491                         | NR               | 655       | 184                         | NR               | 785       | 4                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 514                         | NR               | 660       | 160                         | NR               | 790       | 4                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 530                         | NR               | 665       | 140                         | NR               | 795       | 3                           | NR               | 925       | 0                           | NR               |
| 410       | 27                          | NR               | 540       | 539                         | NR               | 670       | 122                         | NR               | 800       | 3                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 549                         | NR               | 675       | 106                         | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 115                         | NR               | 550       | 557                         | NR               | 680       | 92                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 226                         | NR               | 555       | 565                         | NR               | 685       | 79                          | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 395                         | NR               | 560       | 572                         | NR               | 690       | 68                          | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 648                         | NR               | 565       | 580                         | NR               | 695       | 59                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 937                         | NR               | 570       | 586                         | NR               | 700       | 51                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 953                         | NR               | 575       | 588                         | NR               | 705       | 44                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 591                         | NR               | 580       | 588                         | NR               | 710       | 38                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 334                         | NR               | 585       | 580                         | NR               | 715       | 32                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 221                         | NR               | 590       | 568                         | NR               | 720       | 28                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 140                         | NR               | 595       | 550                         | NR               | 725       | 24                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 93                          | NR               | 600       | 527                         | NR               | 730       | 21                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 79                          | NR               | 605       | 499                         | NR               | 735       | 18                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 76                          | NR               | 610       | 469                         | NR               | 740       | 15                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 87                          | NR               | 615       | 435                         | NR               | 745       | 13                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-6





TM-30-18

### Summary

$R_f = 70.7$   
 $R_g = 96.8$   
 $CIE R_a = 70.2$   
 $R_g = -35.1$







### Color Vector Graphics





**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 53 | CES51 = 87 | CES76 = 42 |
| CES02 = 59 | CES27 = 78 | CES52 = 88 | CES77 = 64 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 45 |
| CES04 = 69 | CES29 = 48 | CES54 = 80 | CES79 = 74 |
| CES05 = 46 | CES30 = 56 | CES55 = 79 | CES80 = 71 |
| CES06 = 50 | CES31 = 54 | CES56 = 68 | CES81 = 72 |
| CES07 = 39 | CES32 = 50 | CES57 = 65 | CES82 = 88 |
| CES08 = 38 | CES33 = 60 | CES58 = 67 | CES83 = 82 |
| CES09 = 29 | CES34 = 62 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 79 | CES60 = 91 | CES85 = 84 |
| CES11 = 56 | CES36 = 90 | CES61 = 87 | CES86 = 74 |
| CES12 = 61 | CES37 = 72 | CES62 = 79 | CES87 = 75 |
| CES13 = 41 | CES38 = 66 | CES63 = 72 | CES88 = 76 |
| CES14 = 74 | CES39 = 91 | CES64 = 70 | CES89 = 74 |
| CES15 = 70 | CES40 = 83 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 83 | CES66 = 64 | CES91 = 92 |
| CES17 = 49 | CES42 = 70 | CES67 = 62 | CES92 = 67 |
| CES18 = 55 | CES43 = 68 | CES68 = 69 | CES93 = 81 |
| CES19 = 71 | CES44 = 98 | CES69 = 80 | CES94 = 56 |
| CES20 = 64 | CES45 = 78 | CES70 = 56 | CES95 = 71 |
| CES21 = 85 | CES46 = 77 | CES71 = 53 | CES96 = 77 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 46 | CES98 = 71 |
| CES24 = 90 | CES49 = 76 | CES74 = 94 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



**Color Rendition by Hue-Angle Bin**


**Measure Comparisons**



(END OF REPORT)