

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047805

Luminaire Tested: **GALN-SA1A-750-U-T2BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047805
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA1A-750-U-T2BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 1xLight Square PACKAGE
70CRI 5000K FIXTURE w/ TYPE II ANGLED BACKLIGHT CONTROL
Light Source: (14) 5000K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3656.1 lumens
Efficiency: N/A
Efficacy: 126.1 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B0 - U0 - G1

Input Watts (W): 29
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047805

CATALOG NUMBER: GALN-SA1A-750-U-T2BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 4.8 fc
 Type II - Short - N/A

REPORT NUMBER: P1047805

CATALOG NUMBER: GALN-SA1A-750-U-T2BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047805

CATALOG NUMBER: GALN-SA1A-750-U-T2BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	15.6	0.0	15.6
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	3640.5	0.0	3640.5
	% Fixture	99.6	0.0	99.6
Total	Lumens	3656.1	0.0	3656.1
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.8	0.1
10°-20°	30.1	0.8
20°-30°	107.9	3.0
30°-40°	287.3	7.9
40°-50°	754.6	20.6
50°-60°	1169.1	32.0
60°-70°	980.2	26.8
70°-80°	288.5	7.9
80°-90°	35.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	3656.1	100.0
0°-180°	3656.1	100.0



REPORT NUMBER: P1047805


CATALOG NUMBER: GALN-SA1A-750-U-T2BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	137.3	3.8			
FM	(30°-60°)	2205.0	60.3			
FH	(60°-80°)	1263.2	34.6			G1/1800
FVH	(80°-90°)	34.9	1.0			G1/100
BL	(0°-30°)	3.5	0.1	B0/110		
BM	(30°-60°)	5.9	0.2	B0/220		
BH	(60°-80°)	5.5	0.2	B0/110		G0/110
BVH	(80°-90°)	0.7	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G1

Type II Short



REPORT NUMBER: P1047805

CATALOG NUMBER: GALN-SA1A-750-U-T2BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	64°	65°	75°	85°
0°	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4
2.5°	27.2	27.4	26.9	25.9	25.1	25.1	24.9	24.1	24.1	23.4	22.9
5°	38.0	37.5	36.5	34.5	32.7	30.9	29.2	27.4	27.2	24.9	23.4
7.5°	62.1	62.6	59.4	53.1	47.8	41.0	34.7	30.9	30.4	26.7	23.6
10°	136.3	132.5	125.0	100.6	82.7	62.4	46.3	36.0	35.5	28.7	24.1
12.5°	248.5	245.5	231.6	206.5	160.5	111.7	67.7	44.5	43.0	30.4	24.4
15°	358.1	353.4	345.8	320.4	266.6	200.2	110.7	60.9	56.8	32.9	24.1
17.5°	428.0	428.8	422.0	411.2	376.5	296.3	191.1	90.8	83.0	37.5	23.6
20°	489.2	487.4	491.2	485.4	461.0	402.6	278.2	143.9	130.5	44.8	23.9
22.5°	559.6	563.9	566.6	565.4	538.5	488.7	377.0	215.3	198.4	58.1	24.6
25°	653.9	653.4	653.6	650.4	624.2	568.9	476.1	304.1	287.0	79.7	26.4
27.5°	752.7	755.8	757.0	745.2	711.0	656.7	567.9	401.1	381.0	114.4	28.7
30°	887.8	885.3	879.5	855.3	813.8	746.4	658.4	503.0	481.9	163.0	32.2
32.5°	1069.9	1067.1	1037.9	984.6	922.5	840.0	749.5	605.1	579.5	223.6	37.0
35°	1369.9	1374.2	1302.5	1164.4	1053.0	952.4	850.3	706.7	684.1	298.3	43.5
37.5°	1829.4	1806.0	1708.7	1464.7	1224.8	1092.8	946.6	809.3	789.7	390.3	52.1
40°	2275.8	2252.7	2224.5	1993.4	1523.3	1247.4	1081.4	929.8	904.4	494.2	64.6
42.5°	2745.1	2732.3	2731.0	2556.7	2068.1	1490.6	1243.7	1070.9	1049.2	608.1	85.3
45°	3077.6	3064.8	3091.7	3122.1	2810.0	2011.7	1526.1	1254.2	1222.8	746.4	118.2
47.5°	3122.3	3122.8	3194.8	3290.1	3361.3	2817.8	1902.3	1497.2	1458.9	944.4	173.5
50°	2973.5	2979.2	3093.7	3264.2	3455.8	3494.1	2565.8	1849.8	1793.2	1179.0	252.0
52.5°	2690.0	2696.6	2856.0	3136.4	3368.8	3656.5	3346.9	2311.0	2245.9	1471.8	362.7
55°	2434.7	2438.8	2621.6	2976.0	3263.9	3568.2	3810.7	2926.9	2841.4	1831.9	471.8
57.5°	2182.0	2172.7	2291.6	2697.3	3246.1	3459.9	3879.1	3628.9	3534.5	2225.5	556.8
60°	1844.0	1828.4	1924.0	2182.0	3011.2	3531.0	3751.1	4017.2	3995.8	2773.5	622.5
61°	1649.6	1643.0	1739.1	1960.4	2813.5	3512.9	3720.4	4033.5	4035.8	3032.8	651.9
62.5°	1178.0	1196.6	1343.5	1631.2	2356.5	3395.5	3724.4	3983.0	4005.4	3377.4	728.1
65°	523.6	553.5	667.7	901.9	1370.4	2824.6	3688.7	3872.1	3861.0	3471.9	990.6
67.5°	310.6	315.1	372.0	511.0	725.8	1519.3	3255.1	3725.4	3710.6	3022.5	1232.6
70°	244.7	247.0	265.1	320.7	421.3	582.0	1857.8	3223.2	3287.8	2450.8	1206.7
72.5°	232.1	231.6	234.1	244.0	265.3	288.7	719.3	2142.5	2274.0	1765.0	1011.8
75°	229.1	228.1	225.6	221.8	192.1	170.0	222.8	947.6	1023.8	1205.9	761.8
77.5°	222.3	222.6	223.1	212.8	164.7	120.2	107.9	304.1	374.0	765.3	541.5
80°	150.4	152.7	156.4	152.4	148.1	87.0	76.2	108.1	109.7	429.6	357.6
82.5°	76.2	76.2	74.4	66.4	57.3	56.6	60.6	78.5	79.5	217.3	168.3
85°	46.0	48.5	49.5	45.0	41.2	38.0	46.3	62.4	64.6	84.3	39.2
87.5°	10.3	10.6	11.6	15.3	22.4	30.4	43.0	57.1	58.1	54.1	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1047805

CATALOG NUMBER: GALN-SA1A-750-U-T2BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.4
2.5°	22.6	22.1	21.9	21.1	20.4	19.6	19.1	18.9	19.1	19.4	19.4
5°	22.4	21.6	20.4	19.1	18.1	17.1	16.1	15.8	15.8	16.1	16.1
7.5°	22.4	21.1	19.4	17.9	16.3	14.8	14.1	13.6	13.8	13.8	13.8
10°	22.4	20.9	18.6	16.3	14.6	12.8	11.6	11.1	11.1	11.1	11.1
12.5°	22.1	20.6	17.9	15.1	12.6	10.6	9.1	8.3	8.6	8.6	8.6
15°	21.6	19.9	16.9	12.8	10.1	8.0	6.5	5.8	6.0	6.5	6.8
17.5°	20.9	19.1	15.1	10.8	8.0	6.0	4.5	4.0	4.3	5.0	5.0
20°	20.6	18.4	13.3	8.8	6.0	4.3	3.0	2.5	2.8	3.8	4.0
22.5°	20.6	17.9	12.1	7.3	4.5	2.8	1.8	1.0	1.0	1.8	1.8
25°	20.9	17.6	11.1	6.0	3.3	2.0	1.0	0.5	1.0	2.8	3.3
27.5°	21.4	17.4	10.6	5.0	2.5	1.8	0.8	1.8	3.0	3.0	3.0
30°	21.9	16.9	9.8	4.3	2.3	1.3	1.3	2.5	2.5	3.0	3.3
32.5°	22.6	16.6	9.3	3.8	1.8	1.0	1.8	1.5	1.5	1.8	2.0
35°	24.1	16.9	8.8	3.8	1.8	1.3	1.5	0.8	0.5	0.5	0.5
37.5°	26.2	17.1	8.0	3.3	1.5	1.5	0.8	0.0	0.0	0.0	0.0
40°	29.4	17.9	7.5	3.0	1.3	1.3	0.3	0.0	0.0	0.0	0.0
42.5°	35.0	19.4	7.3	2.8	1.3	1.0	0.0	0.0	0.0	0.0	0.0
45°	46.0	22.9	6.8	2.5	1.3	0.5	0.0	0.0	0.0	0.0	0.0
47.5°	66.1	31.2	6.5	2.0	0.8	0.0	0.0	0.0	0.0	0.0	0.0
50°	96.6	42.3	6.3	1.8	0.3	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	123.2	44.5	4.3	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	126.3	30.7	3.3	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	100.6	19.9	2.8	0.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	76.2	15.1	2.5	0.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
61°	73.2	13.6	2.5	0.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	80.7	11.8	2.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	131.3	9.8	2.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	228.1	8.6	1.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	288.2	8.0	1.5	0.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	251.2	7.3	1.5	0.5	0.3	0.0	0.0	0.0	0.0	0.0	0.0
75°	151.2	6.3	1.5	1.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	79.2	4.8	1.5	1.3	0.8	0.3	0.0	0.0	0.0	0.0	0.0
80°	38.5	4.3	1.8	1.3	1.0	0.5	0.0	0.0	0.0	0.0	0.0
82.5°	15.1	3.5	2.0	1.8	1.3	0.8	0.3	0.0	0.0	0.0	0.0
85°	6.8	3.0	2.3	2.0	1.8	1.0	0.3	0.0	0.0	0.0	0.0
87.5°	3.5	2.8	2.5	2.3	1.8	1.3	0.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-6

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-750-U-5WQ


Data in this report applies to families of products including GSS-SB1A-750-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-6
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-750-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5000K CCT 26 LEDS

Spectral Parameters

CCT (K):	4896	CRI (Ra):	70.2		
CIE u':	0.2101	R1:	68.1	R9:	-35.1
CIE v':	0.4901	R2:	73.9	R10:	39.3
Duv:	0.0035	R3:	79.4	R11:	71.1
CIE x:	0.3489	R4:	72.1	R12:	43.8
CIE y:	0.3618	R5:	69.2	R13:	68.1
CIE z:	0.2893	R6:	65.7	R14:	88.4
Peak Wavelength (nm):	443	R7:	78.1	R15:	59.7
Dominant Wavelength (nm):	570	R8:	55.3		
Purity:	13.25435				
Rf:	70.7				
Rg:	96.8				



Test Conditions


Stabilization Time: 21M
 Operation Time: 1H 21M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-6


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-6

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-6

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.7

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.37


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	118	NR	620	401	NR	750	12	NR	880	0	NR
365	0	NR	495	168	NR	625	365	NR	755	10	NR	885	0	NR
370	0	NR	500	230	NR	630	331	NR	760	9	NR	890	0	NR
375	0	NR	505	299	NR	635	298	NR	765	8	NR	895	0	NR
380	0	NR	510	362	NR	640	266	NR	770	6	NR	900	0	NR
385	2	NR	515	418	NR	645	236	NR	775	6	NR	905	0	NR
390	4	NR	520	461	NR	650	209	NR	780	5	NR	910	0	NR
395	6	NR	525	491	NR	655	184	NR	785	4	NR	915	0	NR
400	9	NR	530	514	NR	660	160	NR	790	4	NR	920	0	NR
405	14	NR	535	530	NR	665	140	NR	795	3	NR	925	0	NR
410	27	NR	540	539	NR	670	122	NR	800	3	NR	930	0	NR
415	55	NR	545	549	NR	675	106	NR	805	2	NR	935	0	NR
420	115	NR	550	557	NR	680	92	NR	810	2	NR	940	0	NR
425	226	NR	555	565	NR	685	79	NR	815	2	NR	945	0	NR
430	395	NR	560	572	NR	690	68	NR	820	2	NR	950	0	NR
435	648	NR	565	580	NR	695	59	NR	825	1	NR	955	0	NR
440	937	NR	570	586	NR	700	51	NR	830	1	NR	960	0	NR
445	953	NR	575	588	NR	705	44	NR	835	1	NR	965	0	NR
450	591	NR	580	588	NR	710	38	NR	840	1	NR	970	0	NR
455	334	NR	585	580	NR	715	32	NR	845	1	NR	975	0	NR
460	221	NR	590	568	NR	720	28	NR	850	1	NR	980	0	NR
465	140	NR	595	550	NR	725	24	NR	855	1	NR	985	0	NR
470	93	NR	600	527	NR	730	21	NR	860	1	NR	990	0	NR
475	79	NR	605	499	NR	735	18	NR	865	0	NR	995	0	NR
480	76	NR	610	469	NR	740	15	NR	870	0	NR	1000	0	NR
485	87	NR	615	435	NR	745	13	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-6





TM-30-18

Summary

$R_f = 70.7$
 $R_g = 96.8$
 $CIE R_a = 70.2$
 $R_g = -35.1$




Color Vector Graphics







Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 53	CES51 = 87	CES76 = 42
CES02 = 59	CES27 = 78	CES52 = 88	CES77 = 64
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 45
CES04 = 69	CES29 = 48	CES54 = 80	CES79 = 74
CES05 = 46	CES30 = 56	CES55 = 79	CES80 = 71
CES06 = 50	CES31 = 54	CES56 = 68	CES81 = 72
CES07 = 39	CES32 = 50	CES57 = 65	CES82 = 88
CES08 = 38	CES33 = 60	CES58 = 67	CES83 = 82
CES09 = 29	CES34 = 62	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 79	CES60 = 91	CES85 = 84
CES11 = 56	CES36 = 90	CES61 = 87	CES86 = 74
CES12 = 61	CES37 = 72	CES62 = 79	CES87 = 75
CES13 = 41	CES38 = 66	CES63 = 72	CES88 = 76
CES14 = 74	CES39 = 91	CES64 = 70	CES89 = 74
CES15 = 70	CES40 = 83	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 83	CES66 = 64	CES91 = 92
CES17 = 49	CES42 = 70	CES67 = 62	CES92 = 67
CES18 = 55	CES43 = 68	CES68 = 69	CES93 = 81
CES19 = 71	CES44 = 98	CES69 = 80	CES94 = 56
CES20 = 64	CES45 = 78	CES70 = 56	CES95 = 71
CES21 = 85	CES46 = 77	CES71 = 53	CES96 = 77
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 46	CES98 = 71
CES24 = 90	CES49 = 76	CES74 = 94	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons


(END OF REPORT)