

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047237

Luminaire Tested: **GALN-SA3A-757-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047237
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA3A-757-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 3xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (42) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11558 lumens
Efficiency: N/A
Efficacy: 142.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 81.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047237

CATALOG NUMBER: GALN-SA3A-757-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 --- 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 13 fc
 Type III - Short - N/A

REPORT NUMBER: P1047237

CATALOG NUMBER: GALN-SA3A-757-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047237

CATALOG NUMBER: GALN-SA3A-757-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	42.2	0.0	42.2
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	11515.8	0.0	11515.8
	% Fixture	99.6	0.0	99.6
Total	Lumens	11558.0	0.0	11558.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.1	0.1
10°-20°	132.9	1.1
20°-30°	478.9	4.1
30°-40°	1095.6	9.5
40°-50°	1847.9	16.0
50°-60°	3049.5	26.4
60°-70°	3408.2	29.5
70°-80°	1407.2	12.2
80°-90°	126.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	11558.0	100.0
0°-180°	11558.0	100.0



REPORT NUMBER: P1047237


CATALOG NUMBER: GALN-SA3A-757-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	611.8	5.3			
FM	(30°-60°)	5982.9	51.8			
FH	(60°-80°)	4796.1	41.5			G2/5000
FVH	(80°-90°)	125.1	1.1			G2/225
BL	(0°-30°)	11.0	0.1	B0/110		
BM	(30°-60°)	10.1	0.1	B0/220		
BH	(60°-80°)	19.3	0.2	B0/110		G0/110
BVH	(80°-90°)	1.7	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short



REPORT NUMBER: P1047237

CATALOG NUMBER: GALN-SA3A-757-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6
2.5°	90.7	93.7	90.7	90.7	90.7	87.7	87.7	84.6	84.6	81.6	78.6
5°	133.0	133.0	123.9	117.9	111.8	108.8	105.8	99.8	93.7	87.7	81.6
7.5°	296.2	296.2	269.0	232.8	184.4	157.2	151.1	123.9	105.8	93.7	81.6
10°	707.4	707.4	646.9	547.1	423.2	314.4	281.1	178.4	127.0	99.8	84.6
12.5°	1175.9	1191.0	1115.5	988.5	804.1	613.6	547.1	326.5	169.3	108.8	84.6
15°	1596.1	1559.8	1538.7	1417.7	1242.4	1015.7	931.1	550.2	244.9	123.9	84.6
17.5°	1880.2	1880.2	1850.0	1768.4	1608.2	1408.7	1339.1	888.7	396.0	142.1	87.7
20°	2212.8	2212.8	2158.4	2100.9	1958.8	1789.6	1723.1	1263.6	613.6	181.4	87.7
22.5°	2614.8	2620.9	2560.4	2457.6	2321.6	2134.2	2076.7	1611.2	888.7	241.8	90.7
25°	3104.5	3110.6	3022.9	2926.2	2717.6	2515.1	2427.4	2010.2	1224.3	338.6	90.7
27.5°	3645.6	3687.9	3558.0	3391.7	3171.0	2917.1	2850.6	2370.0	1556.8	477.6	96.7
30°	4319.7	4319.7	4147.4	3914.7	3675.8	3361.5	3276.8	2747.8	1910.5	662.0	102.8
32.5°	4900.1	4854.8	4634.1	4389.3	4135.3	3842.1	3751.4	3143.8	2273.2	891.8	114.9
35°	5344.5	5305.2	5033.1	4770.1	4549.5	4280.4	4171.6	3573.1	2657.1	1151.7	133.0
37.5°	5725.4	5710.3	5341.5	5012.0	4866.9	4631.1	4534.4	3978.1	3035.0	1432.9	154.2
40°	6142.5	6094.2	5701.2	5293.1	5075.5	4885.0	4797.3	4304.6	3397.7	1762.4	184.4
42.5°	6499.2	6441.8	6088.1	5689.1	5317.3	5060.3	4975.7	4579.7	3751.4	2091.8	223.7
45°	6895.2	6865.0	6508.3	6206.0	5710.3	5299.1	5187.3	4800.4	4074.9	2484.8	275.1
47.5°	7490.8	7436.3	7103.8	6855.9	6281.6	5661.9	5501.7	5027.1	4386.2	2871.8	353.7
50°	8183.0	8146.7	7950.2	7753.7	7182.4	6281.6	6091.1	5353.6	4733.9	3331.2	456.5
52.5°	8748.3	8742.2	8766.4	8769.4	8337.2	7324.5	7040.3	5879.5	5132.9	3784.7	601.6
55°	8736.2	8763.4	9029.4	9334.7	9368.0	8748.3	8473.2	6765.3	5652.8	4343.9	804.1
57.5°	8409.7	8388.6	8669.7	9129.2	9452.6	9519.1	9473.8	8140.7	6435.8	5018.0	1115.5
58°	8303.9	8285.8	8551.8	9020.3	9392.2	9570.5	9525.2	8452.0	6611.1	5114.8	1200.1
60°	7920.0	7923.0	8080.2	8506.4	8878.3	9301.5	9343.8	9340.8	7484.7	5761.7	1626.3
62.5°	7412.2	7388.0	7533.1	7880.7	8207.2	8491.3	8563.9	9401.2	8763.4	6583.9	2439.5
65°	6710.8	6674.6	6828.7	7221.7	7572.4	7756.8	7759.8	8591.1	9365.0	7466.6	3600.3
67.5°	5408.0	5377.7	5686.1	6190.9	6732.0	6973.8	7082.7	7454.5	8857.1	8065.1	4265.3
70°	3313.1	3376.6	3805.8	4597.8	5522.8	5967.2	6130.4	6245.3	7542.1	7974.4	3567.0
72.5°	1529.6	1454.0	1819.8	2373.0	3428.0	4416.5	4585.7	5036.2	5979.3	6922.4	2660.2
75°	713.4	686.2	770.8	1036.9	1553.8	2385.1	2693.4	4020.5	4585.7	4815.5	1919.5
77.5°	365.8	368.8	438.3	471.6	640.9	1103.4	1266.6	2645.0	3361.5	2687.4	1287.8
80°	160.2	166.3	169.3	184.4	260.0	426.2	480.6	1227.3	2297.4	1369.4	704.3
82.5°	102.8	105.8	105.8	105.8	123.9	169.3	193.5	492.7	1145.7	680.2	217.6
85°	54.4	54.4	60.5	75.6	87.7	102.8	108.8	157.2	377.9	202.5	51.4
87.5°	30.2	33.3	36.3	45.3	57.4	69.5	75.6	108.8	145.1	139.1	12.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1047237

CATALOG NUMBER: GALN-SA3A-757-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6	75.6
2.5°	78.6	75.6	72.5	69.5	66.5	63.5	63.5	63.5	63.5	63.5	63.5
5°	75.6	72.5	69.5	63.5	57.4	54.4	51.4	48.4	48.4	48.4	48.4
7.5°	75.6	72.5	63.5	57.4	51.4	45.3	39.3	39.3	39.3	39.3	39.3
10°	75.6	69.5	60.5	51.4	42.3	36.3	33.3	30.2	30.2	30.2	30.2
12.5°	75.6	66.5	57.4	45.3	36.3	30.2	27.2	24.2	24.2	24.2	24.2
15°	75.6	66.5	54.4	42.3	33.3	24.2	21.2	18.1	18.1	18.1	18.1
17.5°	72.5	63.5	51.4	36.3	27.2	18.1	15.1	12.1	12.1	15.1	15.1
20°	69.5	60.5	45.3	30.2	21.2	15.1	9.1	9.1	9.1	9.1	9.1
22.5°	69.5	60.5	42.3	27.2	18.1	9.1	6.0	6.0	6.0	6.0	9.1
25°	69.5	57.4	36.3	21.2	12.1	6.0	3.0	3.0	3.0	3.0	3.0
27.5°	69.5	57.4	33.3	18.1	9.1	6.0	3.0	0.0	0.0	0.0	0.0
30°	66.5	54.4	30.2	15.1	6.0	3.0	0.0	0.0	0.0	0.0	0.0
32.5°	66.5	51.4	24.2	12.1	6.0	3.0	0.0	0.0	0.0	0.0	0.0
35°	69.5	48.4	21.2	9.1	3.0	0.0	0.0	0.0	0.0	0.0	3.0
37.5°	72.5	45.3	18.1	6.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	75.6	42.3	18.1	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	81.6	42.3	15.1	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	87.7	42.3	12.1	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	99.8	45.3	12.1	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	108.8	48.4	9.1	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	120.9	45.3	9.1	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	136.0	45.3	9.1	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	148.1	42.3	9.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	154.2	39.3	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	184.4	36.3	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	287.2	30.2	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	583.4	27.2	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1088.2	24.2	6.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1218.2	27.2	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	767.8	21.2	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	405.1	21.2	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	202.5	21.2	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	93.7	15.1	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	39.3	9.1	6.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	18.1	9.1	6.0	6.0	3.0	3.0	0.0	0.0	0.0	0.0	0.0
87.5°	9.1	9.1	9.1	6.0	6.0	3.0	3.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-757-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7



TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$



Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)


CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)