

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049086

Luminaire Tested: **GALN-SA6B-760-U-RBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1049086  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA6B-760-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 6xLight Square PACKAGE  
70CRI 5700K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (84) 5700K CCT, 70 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 24452.5 lumens  
Efficiency: N/A  
Efficacy: 114.4 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 213.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3.6 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049086  
CATALOG NUMBER: GALN-SA6B-760-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 122.4    | 0.0    | 122.4   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 24330.0  | 0.0    | 24330.0 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 24452.5  | 0.0    | 24452.5 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 9.6     | 0.0       |
| 10°-20°   | 53.7    | 0.2       |
| 20°-30°   | 579.5   | 2.4       |
| 30°-40°   | 1713.6  | 7.0       |
| 40°-50°   | 5107.2  | 20.9      |
| 50°-60°   | 8098.1  | 33.1      |
| 60°-70°   | 6759.9  | 27.6      |
| 70°-80°   | 2084.5  | 8.5       |
| 80°-90°   | 46.4    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 24452.5 | 100.0     |
| 0°-180°   | 24452.5 | 100.0     |



REPORT NUMBER: P1049086


CATALOG NUMBER: GALN-SA6B-760-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 620.3   | 2.5       |                         |      |          |
| FM   | (30°-60°)   | 14875.1 | 60.8      |                         |      |          |
| FH   | (60°-80°)   | 8798.8  | 36.0      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 35.8    | 0.1       |                         |      | G1/100   |
| BL   | (0°-30°)    | 22.5    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 43.8    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 45.7    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 10.5    | 0.0       |                         |      | G1/100   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 107.2  | 107.2  | 107.2  | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 |
| 2.5°   | 97.9   | 97.9   | 97.9   | 97.9  | 96.1  | 96.1  | 94.2  | 94.2  | 92.4  | 92.4  |
| 5°     | 103.5  | 103.5  | 101.6  | 99.8  | 99.8  | 97.9  | 96.1  | 94.2  | 94.2  | 92.4  |
| 7.5°   | 112.7  | 110.9  | 109.0  | 107.2 | 103.5 | 101.6 | 97.9  | 96.1  | 94.2  | 90.5  |
| 10°    | 123.8  | 120.1  | 116.4  | 112.7 | 109.0 | 105.3 | 101.6 | 99.8  | 96.1  | 94.2  |
| 12.5°  | 138.6  | 133.0  | 125.7  | 120.1 | 116.4 | 110.9 | 107.2 | 103.5 | 97.9  | 94.2  |
| 15°    | 151.5  | 144.1  | 134.9  | 127.5 | 122.0 | 114.6 | 109.0 | 103.5 | 99.8  | 94.2  |
| 17.5°  | 170.0  | 157.1  | 142.3  | 133.0 | 125.7 | 116.4 | 107.2 | 101.6 | 96.1  | 88.7  |
| 20°    | 201.4  | 175.5  | 147.8  | 136.7 | 125.7 | 114.6 | 103.5 | 96.1  | 90.5  | 83.2  |
| 22.5°  | 251.3  | 207.0  | 162.6  | 146.0 | 131.2 | 114.6 | 99.8  | 92.4  | 85.0  | 77.6  |
| 25°    | 347.4  | 267.9  | 188.5  | 166.3 | 144.1 | 122.0 | 99.8  | 90.5  | 83.2  | 73.9  |
| 27.5°  | 462.0  | 343.7  | 223.6  | 192.2 | 162.6 | 131.2 | 99.8  | 88.7  | 79.5  | 68.4  |
| 30°    | 578.4  | 421.3  | 262.4  | 221.7 | 181.1 | 140.4 | 99.8  | 86.8  | 75.8  | 62.8  |
| 32.5°  | 689.2  | 493.4  | 295.7  | 247.6 | 199.6 | 149.7 | 101.6 | 86.8  | 72.1  | 57.3  |
| 35°    | 802.0  | 552.5  | 301.2  | 251.3 | 201.4 | 149.7 | 99.8  | 83.2  | 68.4  | 51.7  |
| 37.5°  | 946.1  | 619.0  | 290.1  | 240.2 | 192.2 | 142.3 | 94.2  | 79.5  | 64.7  | 48.0  |
| 40°    | 1164.1 | 729.9  | 295.7  | 243.9 | 192.2 | 140.4 | 88.7  | 73.9  | 61.0  | 46.2  |
| 42.5°  | 1567.0 | 944.3  | 319.7  | 260.5 | 201.4 | 140.4 | 81.3  | 68.4  | 57.3  | 44.3  |
| 45°    | 2709.0 | 1568.8 | 428.7  | 340.0 | 251.3 | 162.6 | 73.9  | 62.8  | 53.6  | 42.5  |
| 47.5°  | 4481.0 | 2625.8 | 770.6  | 595.0 | 421.3 | 245.8 | 72.1  | 62.8  | 53.6  | 42.5  |
| 50°    | 5719.1 | 3344.6 | 970.1  | 746.5 | 522.9 | 299.4 | 75.8  | 64.7  | 55.4  | 44.3  |
| 52.5°  | 5709.9 | 3396.4 | 1081.0 | 829.7 | 580.2 | 328.9 | 79.5  | 68.4  | 59.1  | 48.0  |
| 55°    | 5076.1 | 3089.6 | 1101.3 | 846.3 | 593.2 | 338.2 | 85.0  | 73.9  | 62.8  | 51.7  |
| 57.5°  | 4242.7 | 2624.0 | 1005.2 | 777.9 | 552.5 | 325.2 | 97.9  | 85.0  | 73.9  | 61.0  |
| 60°    | 3355.7 | 2069.6 | 783.5  | 619.0 | 456.4 | 292.0 | 129.3 | 112.7 | 97.9  | 81.3  |
| 62.5°  | 2317.2 | 1500.5 | 683.7  | 548.8 | 415.8 | 280.9 | 147.8 | 131.2 | 116.4 | 99.8  |
| 65°    | 1639.0 | 1129.0 | 617.2  | 502.6 | 389.9 | 275.3 | 160.8 | 142.3 | 125.7 | 107.2 |
| 67.5°  | 1225.1 | 898.1  | 569.1  | 471.2 | 373.3 | 275.3 | 177.4 | 155.2 | 134.9 | 112.7 |
| 70°    | 938.7  | 737.3  | 534.0  | 454.6 | 377.0 | 297.5 | 218.0 | 186.6 | 157.1 | 125.7 |
| 72.5°  | 765.0  | 630.1  | 493.4  | 436.1 | 378.8 | 321.5 | 264.2 | 223.6 | 182.9 | 140.4 |
| 75°    | 633.8  | 539.6  | 445.3  | 397.3 | 351.1 | 303.0 | 255.0 | 218.0 | 182.9 | 146.0 |
| 77.5°  | 421.3  | 384.4  | 345.5  | 317.8 | 290.1 | 260.5 | 232.8 | 201.4 | 171.9 | 140.4 |
| 80°    | 147.8  | 142.3  | 136.7  | 147.8 | 158.9 | 170.0 | 181.1 | 158.9 | 138.6 | 116.4 |
| 82.5°  | 22.2   | 20.3   | 18.5   | 20.3  | 22.2  | 24.0  | 25.9  | 27.7  | 29.6  | 31.4  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° | 27.5°  | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 |
| 0.0 | 2.5°   | 90.5  | 90.5  | 88.7  | 88.7  | 88.7  | 86.8  | 86.8  | 85.0  | 85.0  |
| 0.0 | 5°     | 88.7  | 88.7  | 86.8  | 85.0  | 83.2  | 83.2  | 81.3  | 79.5  | 79.5  |
| 0.0 | 7.5°   | 86.8  | 85.0  | 83.2  | 81.3  | 79.5  | 77.6  | 75.8  | 73.9  | 73.9  |
| 0.0 | 10°    | 88.7  | 85.0  | 83.2  | 79.5  | 77.6  | 75.8  | 72.1  | 70.2  | 68.4  |
| 0.0 | 12.5°  | 85.0  | 83.2  | 79.5  | 75.8  | 73.9  | 70.2  | 68.4  | 64.7  | 62.8  |
| 0.0 | 15°    | 85.0  | 81.3  | 75.8  | 72.1  | 68.4  | 66.5  | 62.8  | 59.1  | 57.3  |
| 0.0 | 17.5°  | 79.5  | 75.8  | 70.2  | 66.5  | 62.8  | 59.1  | 55.4  | 51.7  | 49.9  |
| 0.0 | 20°    | 72.1  | 68.4  | 62.8  | 57.3  | 53.6  | 49.9  | 46.2  | 42.5  | 40.7  |
| 0.0 | 22.5°  | 64.7  | 61.0  | 55.4  | 49.9  | 46.2  | 42.5  | 37.0  | 33.3  | 31.4  |
| 0.0 | 25°    | 61.0  | 55.4  | 49.9  | 44.3  | 38.8  | 35.1  | 29.6  | 24.0  | 20.3  |
| 0.0 | 27.5°  | 51.7  | 46.2  | 40.7  | 35.1  | 29.6  | 24.0  | 18.5  | 12.9  | 9.2   |
| 0.0 | 30°    | 44.3  | 38.8  | 33.3  | 27.7  | 20.3  | 14.8  | 9.2   | 1.8   | 1.8   |
| 0.0 | 32.5°  | 37.0  | 31.4  | 24.0  | 18.5  | 14.8  | 9.2   | 5.5   | 0.0   | 0.0   |
| 0.0 | 35°    | 29.6  | 24.0  | 16.6  | 11.1  | 9.2   | 5.5   | 3.7   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 25.9  | 20.3  | 12.9  | 5.5   | 3.7   | 3.7   | 1.8   | 0.0   | 0.0   |
| 0.0 | 40°    | 24.0  | 16.6  | 9.2   | 1.8   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 24.0  | 16.6  | 7.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 24.0  | 16.6  | 7.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 24.0  | 16.6  | 7.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 25.9  | 18.5  | 9.2   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 29.6  | 22.2  | 14.8  | 7.4   | 5.5   | 3.7   | 1.8   | 0.0   | 0.0   |
| 0.0 | 55°    | 37.0  | 33.3  | 27.7  | 24.0  | 18.5  | 12.9  | 5.5   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 48.0  | 48.0  | 46.2  | 44.3  | 33.3  | 22.2  | 11.1  | 0.0   | 0.0   |
| 0.0 | 60°    | 64.7  | 64.7  | 64.7  | 64.7  | 48.0  | 33.3  | 16.6  | 0.0   | 0.0   |
| 0.0 | 62.5°  | 79.5  | 75.8  | 70.2  | 66.5  | 49.9  | 33.3  | 16.6  | 0.0   | 0.0   |
| 0.0 | 65°    | 79.5  | 72.1  | 62.8  | 53.6  | 40.7  | 27.7  | 12.9  | 0.0   | 0.0   |
| 0.0 | 67.5°  | 73.9  | 59.1  | 42.5  | 27.7  | 20.3  | 14.8  | 7.4   | 0.0   | 0.0   |
|     | 70°    | 73.9  | 51.7  | 29.6  | 7.4   | 5.5   | 3.7   | 1.8   | 0.0   | 0.0   |
|     | 72.5°  | 73.9  | 49.9  | 24.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 81.3  | 55.4  | 27.7  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 81.3  | 55.4  | 27.7  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 72.1  | 48.0  | 24.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 24.0  | 16.6  | 7.4   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 |
| 0.0   | 2.5°   | 83.2  | 83.2  | 83.2  | 81.3  | 81.3  | 81.3  | 81.3  | 79.5  | 79.5  | 79.5  |
| 0.0   | 5°     | 75.8  | 75.8  | 73.9  | 73.9  | 72.1  | 72.1  | 70.2  | 70.2  | 68.4  | 68.4  |
| 0.0   | 7.5°   | 70.2  | 68.4  | 68.4  | 66.5  | 64.7  | 64.7  | 62.8  | 62.8  | 61.0  | 59.1  |
| 0.0   | 10°    | 64.7  | 62.8  | 62.8  | 61.0  | 59.1  | 57.3  | 57.3  | 55.4  | 53.6  | 51.7  |
| 0.0   | 12.5°  | 59.1  | 57.3  | 55.4  | 53.6  | 51.7  | 49.9  | 49.9  | 48.0  | 46.2  | 44.3  |
| 0.0   | 15°    | 51.7  | 49.9  | 48.0  | 46.2  | 44.3  | 42.5  | 42.5  | 40.7  | 38.8  | 37.0  |
| 0.0   | 17.5°  | 44.3  | 42.5  | 42.5  | 40.7  | 38.8  | 37.0  | 35.1  | 31.4  | 29.6  | 27.7  |
| 0.0   | 20°    | 33.3  | 31.4  | 29.6  | 27.7  | 25.9  | 22.2  | 20.3  | 16.6  | 12.9  | 11.1  |
| 0.0   | 22.5°  | 22.2  | 18.5  | 16.6  | 12.9  | 9.2   | 7.4   | 5.5   | 1.8   | 0.0   | 0.0   |
| 0.0   | 25°    | 7.4   | 5.5   | 3.7   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2 | 107.2  | 107.2 |
| 0.0 | 2.5°   | 77.6  | 77.6  | 77.6  | 75.8  | 75.8  | 75.8  | 75.8  | 75.8  | 75.8   | 75.8  |
| 0.0 | 5°     | 66.5  | 66.5  | 66.5  | 64.7  | 64.7  | 62.8  | 62.8  | 62.8  | 61.0   | 61.0  |
| 0.0 | 7.5°   | 57.3  | 55.4  | 55.4  | 53.6  | 53.6  | 51.7  | 51.7  | 51.7  | 49.9   | 49.9  |
| 0.0 | 10°    | 48.0  | 46.2  | 46.2  | 44.3  | 44.3  | 42.5  | 42.5  | 40.7  | 40.7   | 38.8  |
| 0.0 | 12.5°  | 42.5  | 40.7  | 38.8  | 37.0  | 37.0  | 35.1  | 33.3  | 33.3  | 31.4   | 29.6  |
| 0.0 | 15°    | 33.3  | 31.4  | 29.6  | 27.7  | 25.9  | 24.0  | 22.2  | 22.2  | 20.3   | 18.5  |
| 0.0 | 17.5°  | 22.2  | 18.5  | 16.6  | 14.8  | 14.8  | 12.9  | 11.1  | 9.2   | 7.4    | 5.5   |
| 0.0 | 20°    | 5.5   | 3.7   | 1.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  |
| 0.0    | 2.5°   | 75.8  | 73.9   | 73.9  | 73.9   | 75.8  | 75.8   | 75.8  | 75.8   | 75.8  | 75.8   |
| 0.0    | 5°     | 61.0  | 59.1   | 59.1  | 59.1   | 59.1  | 59.1   | 59.1  | 59.1   | 59.1  | 59.1   |
| 0.0    | 7.5°   | 49.9  | 48.0   | 48.0  | 48.0   | 48.0  | 46.2   | 46.2  | 46.2   | 46.2  | 46.2   |
| 0.0    | 10°    | 38.8  | 37.0   | 37.0  | 37.0   | 37.0  | 35.1   | 35.1  | 35.1   | 35.1  | 35.1   |
| 0.0    | 12.5°  | 27.7  | 27.7   | 25.9  | 25.9   | 25.9  | 24.0   | 24.0  | 24.0   | 24.0  | 22.2   |
| 0.0    | 15°    | 16.6  | 14.8   | 12.9  | 12.9   | 12.9  | 11.1   | 11.1  | 11.1   | 11.1  | 9.2    |
| 0.0    | 17.5°  | 3.7   | 3.7    | 1.8   | 1.8    | 1.8   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 |
| 0.0  | 2.5°   | 77.6   | 77.6  | 79.5   | 79.5  | 81.3   | 85.0  | 86.8   | 88.7  | 92.4   | 96.1  |
| 0.0  | 5°     | 61.0   | 62.8  | 62.8   | 64.7  | 66.5   | 68.4  | 70.2   | 72.1  | 75.8   | 79.5  |
| 0.0  | 7.5°   | 48.0   | 48.0  | 49.9   | 49.9  | 51.7   | 55.4  | 57.3   | 59.1  | 62.8   | 68.4  |
| 0.0  | 10°    | 37.0   | 37.0  | 38.8   | 38.8  | 40.7   | 44.3  | 46.2   | 48.0  | 51.7   | 57.3  |
| 0.0  | 12.5°  | 24.0   | 25.9  | 25.9   | 27.7  | 29.6   | 33.3  | 35.1   | 37.0  | 40.7   | 44.3  |
| 0.0  | 15°    | 11.1   | 12.9  | 12.9   | 14.8  | 16.6   | 20.3  | 22.2   | 24.0  | 27.7   | 33.3  |
| 0.0  | 17.5°  | 1.8    | 1.8   | 3.7    | 3.7   | 5.5    | 7.4   | 9.2    | 11.1  | 16.6   | 20.3  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.7    | 7.4   |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 1.8   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  |
| 0.0    | 2.5°   | 101.6 | 105.3  | 109.0 | 112.7  | 116.4 | 120.1  | 122.0 | 125.7  | 127.5 | 129.3  |
| 0.0    | 5°     | 86.8  | 90.5   | 96.1  | 99.8   | 103.5 | 107.2  | 110.9 | 112.7  | 114.6 | 116.4  |
| 0.0    | 7.5°   | 75.8  | 79.5   | 85.0  | 88.7   | 92.4  | 96.1   | 99.8  | 103.5  | 105.3 | 107.2  |
| 0.0    | 10°    | 64.7  | 70.2   | 73.9  | 79.5   | 83.2  | 86.8   | 90.5  | 94.2   | 97.9  | 99.8   |
| 0.0    | 12.5°  | 51.7  | 57.3   | 62.8  | 66.5   | 72.1  | 77.6   | 81.3  | 85.0   | 88.7  | 92.4   |
| 0.0    | 15°    | 40.7  | 46.2   | 51.7  | 55.4   | 61.0  | 66.5   | 72.1  | 75.8   | 79.5  | 83.2   |
| 0.0    | 17.5°  | 29.6  | 35.1   | 40.7  | 44.3   | 49.9  | 55.4   | 59.1  | 64.7   | 68.4  | 72.1   |
| 0.0    | 20°    | 14.8  | 20.3   | 25.9  | 31.4   | 37.0  | 42.5   | 46.2  | 51.7   | 55.4  | 59.1   |
| 0.0    | 22.5°  | 1.8   | 7.4    | 12.9  | 16.6   | 22.2  | 27.7   | 31.4  | 37.0   | 40.7  | 44.3   |
| 0.0    | 25°    | 0.0   | 1.8    | 5.5   | 7.4    | 9.2   | 12.9   | 16.6  | 20.3   | 24.0  | 27.7   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 3.7   | 7.4    | 11.1  | 14.8   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.7    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 1.8   | 3.7    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.7    | 5.5   | 9.2    | 11.1  | 12.9   |
|        | 87.5°  | 0.0   | 1.8    | 3.7   | 5.5    | 7.4   | 11.1   | 14.8  | 18.5   | 20.3  | 22.2   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 107.2 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 129.3 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 118.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 109.0 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 103.5 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 94.2  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.8  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 77.6  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.8  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.0  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 33.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5.5   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.8   |        |      |        |      |        |      |        |      |        |      |        |
| 7.4   |        |      |        |      |        |      |        |      |        |      |        |
| 16.6  |        |      |        |      |        |      |        |      |        |      |        |
| 24.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 |
| 0.0  | 2.5°   | 131.2  | 131.2 | 131.2  | 131.2 | 129.3  | 129.3 | 129.3  | 127.5 | 127.5  | 125.7 |
| 0.0  | 5°     | 120.1  | 122.0 | 122.0  | 122.0 | 122.0  | 122.0 | 122.0  | 122.0 | 120.1  | 120.1 |
| 0.0  | 7.5°   | 110.9  | 112.7 | 114.6  | 114.6 | 116.4  | 116.4 | 116.4  | 114.6 | 114.6  | 112.7 |
| 0.0  | 10°    | 105.3  | 107.2 | 107.2  | 109.0 | 109.0  | 109.0 | 109.0  | 109.0 | 109.0  | 109.0 |
| 0.0  | 12.5°  | 97.9   | 99.8  | 101.6  | 101.6 | 103.5  | 103.5 | 103.5  | 103.5 | 101.6  | 101.6 |
| 0.0  | 15°    | 88.7   | 92.4  | 94.2   | 96.1  | 96.1   | 97.9  | 97.9   | 97.9  | 97.9   | 97.9  |
| 0.0  | 17.5°  | 81.3   | 85.0  | 86.8   | 88.7  | 88.7   | 90.5  | 90.5   | 92.4  | 92.4   | 92.4  |
| 0.0  | 20°    | 66.5   | 70.2  | 72.1   | 75.8  | 77.6   | 79.5  | 81.3   | 83.2  | 83.2   | 85.0  |
| 0.0  | 22.5°  | 51.7   | 55.4  | 57.3   | 61.0  | 62.8   | 64.7  | 66.5   | 68.4  | 70.2   | 72.1  |
| 0.0  | 25°    | 37.0   | 40.7  | 42.5   | 46.2  | 48.0   | 49.9  | 51.7   | 53.6  | 53.6   | 55.4  |
| 0.0  | 27.5°  | 20.3   | 24.0  | 27.7   | 29.6  | 33.3   | 35.1  | 37.0   | 38.8  | 40.7   | 42.5  |
| 0.0  | 30°    | 9.2    | 11.1  | 12.9   | 16.6  | 18.5   | 20.3  | 22.2   | 25.9  | 27.7   | 29.6  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.8    | 5.5   | 7.4    | 9.2   | 11.1   | 12.9  | 12.9   | 14.8  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.8    | 3.7   | 5.5    | 7.4   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.7    | 3.7   | 3.7    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   | 5.5    | 5.5   |
|      | 82.5°  | 9.2    | 11.1  | 12.9   | 12.9  | 14.8   | 14.8  | 14.8   | 14.8  | 12.9   | 12.9  |
|      | 85°    | 18.5   | 20.3  | 22.2   | 22.2  | 24.0   | 24.0  | 24.0   | 24.0  | 24.0   | 24.0  |
|      | 87.5°  | 25.9   | 27.7  | 29.6   | 29.6  | 31.4   | 31.4  | 31.4   | 31.4  | 31.4   | 31.4  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 107.2  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 125.7  | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 120.1  | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 112.7  | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 109.0  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 101.6  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 97.9   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.4   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 83.2   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 72.1   | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 57.3   | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 44.3   | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 31.4   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 18.5   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 11.1   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.7    | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.7    | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.8    | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 5.5    |        |      |        |      |        |      |        |      |        |      |
| 12.9   |        |      |        |      |        |      |        |      |        |      |
| 24.0   |        |      |        |      |        |      |        |      |        |      |
| 31.4   |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  |
| 0.0    | 2.5°   | 123.8 | 123.8  | 122.0 | 122.0  | 122.0 | 122.0  | 122.0 | 123.8  | 125.7 | 125.7  |
| 0.0    | 5°     | 118.3 | 118.3  | 116.4 | 116.4  | 116.4 | 118.3  | 118.3 | 120.1  | 122.0 | 123.8  |
| 0.0    | 7.5°   | 112.7 | 110.9  | 110.9 | 112.7  | 112.7 | 114.6  | 114.6 | 116.4  | 118.3 | 120.1  |
| 0.0    | 10°    | 109.0 | 107.2  | 107.2 | 107.2  | 109.0 | 109.0  | 110.9 | 112.7  | 114.6 | 116.4  |
| 0.0    | 12.5°  | 101.6 | 101.6  | 101.6 | 101.6  | 103.5 | 103.5  | 105.3 | 107.2  | 110.9 | 112.7  |
| 0.0    | 15°    | 97.9  | 96.1   | 96.1  | 96.1   | 96.1  | 97.9   | 97.9  | 101.6  | 105.3 | 107.2  |
| 0.0    | 17.5°  | 90.5  | 90.5   | 88.7  | 88.7   | 90.5  | 90.5   | 92.4  | 96.1   | 99.8  | 101.6  |
| 0.0    | 20°    | 83.2  | 81.3   | 79.5  | 79.5   | 81.3  | 81.3   | 83.2  | 86.8   | 90.5  | 92.4   |
| 0.0    | 22.5°  | 72.1  | 70.2   | 70.2  | 70.2   | 70.2  | 72.1   | 72.1  | 75.8   | 81.3  | 85.0   |
| 0.0    | 25°    | 57.3  | 59.1   | 59.1  | 61.0   | 61.0  | 62.8   | 64.7  | 68.4   | 73.9  | 77.6   |
| 0.0    | 27.5°  | 44.3  | 46.2   | 46.2  | 49.9   | 51.7  | 53.6   | 55.4  | 61.0   | 66.5  | 70.2   |
| 0.0    | 30°    | 33.3  | 35.1   | 37.0  | 38.8   | 42.5  | 46.2   | 49.9  | 55.4   | 61.0  | 64.7   |
| 0.0    | 32.5°  | 20.3  | 24.0   | 25.9  | 29.6   | 33.3  | 37.0   | 40.7  | 46.2   | 53.6  | 59.1   |
| 0.0    | 35°    | 14.8  | 16.6   | 20.3  | 22.2   | 25.9  | 29.6   | 33.3  | 40.7   | 46.2  | 53.6   |
| 0.0    | 37.5°  | 7.4   | 11.1   | 14.8  | 18.5   | 22.2  | 25.9   | 29.6  | 37.0   | 44.3  | 49.9   |
| 0.0    | 40°    | 5.5   | 9.2    | 11.1  | 14.8   | 20.3  | 24.0   | 27.7  | 35.1   | 42.5  | 49.9   |
| 0.0    | 42.5°  | 3.7   | 5.5    | 7.4   | 12.9   | 16.6  | 22.2   | 27.7  | 35.1   | 42.5  | 49.9   |
| 0.0    | 45°    | 3.7   | 3.7    | 5.5   | 11.1   | 16.6  | 24.0   | 29.6  | 37.0   | 42.5  | 49.9   |
| 0.0    | 47.5°  | 3.7   | 5.5    | 7.4   | 14.8   | 18.5  | 24.0   | 29.6  | 35.1   | 42.5  | 48.0   |
| 0.0    | 50°    | 5.5   | 7.4    | 9.2   | 16.6   | 20.3  | 25.9   | 29.6  | 37.0   | 42.5  | 49.9   |
| 0.0    | 52.5°  | 3.7   | 5.5    | 7.4   | 14.8   | 20.3  | 27.7   | 33.3  | 40.7   | 48.0  | 53.6   |
| 0.0    | 55°    | 1.8   | 1.8    | 1.8   | 11.1   | 22.2  | 31.4   | 42.5  | 48.0   | 55.4  | 61.0   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 7.4    | 22.2  | 35.1   | 48.0  | 55.4   | 62.8  | 68.4   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 7.4    | 22.2  | 35.1   | 48.0  | 57.3   | 66.5  | 75.8   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 7.4    | 18.5  | 29.6   | 40.7  | 55.4   | 72.1  | 86.8   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 5.5    | 14.8  | 24.0   | 33.3  | 55.4   | 77.6  | 97.9   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 5.5    | 14.8  | 22.2   | 31.4  | 55.4   | 77.6  | 101.6  |
|        | 70°    | 0.0   | 0.0    | 0.0   | 5.5    | 14.8  | 24.0   | 33.3  | 55.4   | 77.6  | 99.8   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 5.5    | 16.6  | 25.9   | 37.0  | 55.4   | 73.9  | 92.4   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 7.4    | 16.6  | 27.7   | 38.8  | 55.4   | 72.1  | 86.8   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 5.5    | 16.6  | 25.9   | 37.0  | 53.6   | 70.2  | 85.0   |
|        | 80°    | 5.5   | 3.7    | 3.7   | 9.2    | 16.6  | 24.0   | 31.4  | 48.0   | 66.5  | 83.2   |
|        | 82.5°  | 11.1  | 11.1   | 9.2   | 12.9   | 16.6  | 22.2   | 27.7  | 42.5   | 59.1  | 73.9   |
|        | 85°    | 22.2  | 22.2   | 20.3  | 22.2   | 22.2  | 24.0   | 25.9  | 33.3   | 40.7  | 48.0   |
|        | 87.5°  | 29.6  | 29.6   | 27.7  | 27.7   | 27.7  | 25.9   | 25.9  | 25.9   | 25.9  | 24.0   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 107.2 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125.7 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.0 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 118.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.6 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.9 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.3 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 96.1  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.7  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 81.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.8  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70.2  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.7  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.1  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.3  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.3  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.3  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.4  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.6  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.4  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 61.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66.5  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.8  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.6 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120.1 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 123.8 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.0 |        |      |        |      |        |      |        |      |        |      |        |
| 110.9 |        |      |        |      |        |      |        |      |        |      |        |
| 103.5 |        |      |        |      |        |      |        |      |        |      |        |
| 101.6 |        |      |        |      |        |      |        |      |        |      |        |
| 99.8  |        |      |        |      |        |      |        |      |        |      |        |
| 88.7  |        |      |        |      |        |      |        |      |        |      |        |
| 55.4  |        |      |        |      |        |      |        |      |        |      |        |
| 24.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2 | 107.2  | 107.2  |
| 0.0  | 2.5°   | 129.3  | 131.2 | 131.2  | 133.0 | 134.9  | 136.7 | 136.7  | 138.6 | 138.6  | 138.6  |
| 0.0  | 5°     | 127.5  | 131.2 | 133.0  | 134.9 | 136.7  | 138.6 | 140.4  | 142.3 | 144.1  | 144.1  |
| 0.0  | 7.5°   | 125.7  | 127.5 | 131.2  | 133.0 | 136.7  | 138.6 | 142.3  | 144.1 | 146.0  | 147.8  |
| 0.0  | 10°    | 122.0  | 125.7 | 129.3  | 133.0 | 136.7  | 140.4 | 144.1  | 147.8 | 151.5  | 153.4  |
| 0.0  | 12.5°  | 118.3  | 123.8 | 127.5  | 131.2 | 136.7  | 142.3 | 146.0  | 151.5 | 155.2  | 158.9  |
| 0.0  | 15°    | 116.4  | 120.1 | 125.7  | 129.3 | 136.7  | 144.1 | 149.7  | 157.1 | 164.5  | 170.0  |
| 0.0  | 17.5°  | 110.9  | 118.3 | 123.8  | 129.3 | 136.7  | 146.0 | 153.4  | 160.8 | 171.9  | 182.9  |
| 0.0  | 20°    | 103.5  | 109.0 | 116.4  | 122.0 | 133.0  | 142.3 | 153.4  | 162.6 | 179.2  | 195.9  |
| 0.0  | 22.5°  | 96.1   | 103.5 | 109.0  | 116.4 | 129.3  | 140.4 | 153.4  | 164.5 | 192.2  | 218.0  |
| 0.0  | 25°    | 88.7   | 97.9  | 105.3  | 112.7 | 127.5  | 142.3 | 157.1  | 171.9 | 218.0  | 264.2  |
| 0.0  | 27.5°  | 85.0   | 92.4  | 101.6  | 109.0 | 127.5  | 147.8 | 166.3  | 184.8 | 258.7  | 330.8  |
| 0.0  | 30°    | 79.5   | 88.7  | 96.1   | 105.3 | 129.3  | 153.4 | 177.4  | 201.4 | 314.1  | 426.9  |
| 0.0  | 32.5°  | 73.9   | 83.2  | 92.4   | 101.6 | 133.0  | 164.5 | 194.0  | 225.4 | 373.3  | 519.2  |
| 0.0  | 35°    | 68.4   | 79.5  | 88.7   | 97.9  | 138.6  | 181.1 | 221.7  | 262.4 | 426.9  | 589.5  |
| 0.0  | 37.5°  | 66.5   | 77.6  | 86.8   | 96.1  | 140.4  | 182.9 | 227.3  | 269.8 | 432.4  | 595.0  |
| 0.0  | 40°    | 68.4   | 77.6  | 88.7   | 97.9  | 134.9  | 171.9 | 207.0  | 243.9 | 413.9  | 582.1  |
| 0.0  | 42.5°  | 68.4   | 79.5  | 90.5   | 101.6 | 131.2  | 160.8 | 190.3  | 219.9 | 408.4  | 596.9  |
| 0.0  | 45°    | 66.5   | 77.6  | 88.7   | 99.8  | 127.5  | 153.4 | 181.1  | 207.0 | 441.6  | 674.5  |
| 0.0  | 47.5°  | 64.7   | 75.8  | 86.8   | 97.9  | 125.7  | 153.4 | 181.1  | 208.8 | 571.0  | 931.3  |
| 0.0  | 50°    | 64.7   | 75.8  | 85.0   | 94.2  | 127.5  | 162.6 | 195.9  | 229.1 | 831.5  | 1432.1 |
| 0.0  | 52.5°  | 68.4   | 77.6  | 85.0   | 92.4  | 131.2  | 171.9 | 210.7  | 249.5 | 1057.0 | 1862.6 |
| 0.0  | 55°    | 73.9   | 79.5  | 86.8   | 92.4  | 140.4  | 186.6 | 234.7  | 280.9 | 1125.3 | 1969.8 |
| 0.0  | 57.5°  | 81.3   | 86.8  | 92.4   | 97.9  | 157.1  | 216.2 | 273.5  | 332.6 | 1130.9 | 1927.3 |
| 0.0  | 60°    | 90.5   | 97.9  | 103.5  | 109.0 | 171.9  | 236.5 | 299.4  | 362.2 | 1023.7 | 1683.4 |
| 0.0  | 62.5°  | 110.9  | 120.1 | 127.5  | 136.7 | 197.7  | 256.9 | 317.8  | 377.0 | 850.0  | 1323.1 |
| 0.0  | 65°    | 127.5  | 134.9 | 142.3  | 149.7 | 208.8  | 269.8 | 328.9  | 388.0 | 720.7  | 1053.3 |
| 0.0  | 67.5°  | 131.2  | 138.6 | 144.1  | 151.5 | 212.5  | 273.5 | 332.6  | 393.6 | 617.2  | 838.9  |
|      | 70°    | 133.0  | 142.3 | 153.4  | 162.6 | 225.4  | 288.3 | 349.2  | 412.1 | 547.0  | 681.9  |
|      | 72.5°  | 127.5  | 146.0 | 162.6  | 179.2 | 238.4  | 295.7 | 354.8  | 412.1 | 508.2  | 604.2  |
|      | 75°    | 127.5  | 153.4 | 177.4  | 201.4 | 245.8  | 288.3 | 332.6  | 375.1 | 449.0  | 522.9  |
|      | 77.5°  | 134.9  | 168.2 | 201.4  | 234.7 | 260.5  | 284.6 | 310.4  | 334.5 | 382.5  | 430.5  |
|      | 80°    | 134.9  | 170.0 | 203.3  | 238.4 | 249.5  | 262.4 | 273.5  | 284.6 | 290.1  | 295.7  |
|      | 82.5°  | 116.4  | 144.1 | 171.9  | 199.6 | 186.6  | 173.7 | 160.8  | 147.8 | 138.6  | 127.5  |
|      | 85°    | 59.1   | 64.7  | 68.4   | 72.1  | 66.5   | 61.0  | 55.4   | 49.9  | 46.2   | 40.7   |
|      | 87.5°  | 24.0   | 24.0  | 22.2   | 22.2  | 22.2   | 22.2  | 20.3   | 20.3  | 20.3   | 20.3   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 107.2  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 138.6  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 144.1  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 149.7  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 157.1  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 164.5  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 179.2  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 197.7  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 227.3  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 290.1  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 393.6  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 547.0  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 741.0  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 925.8  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1051.4 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1145.7 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1239.9 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1424.7 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1794.3 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2734.8 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4189.1 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5273.8 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5393.9 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4867.2 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4161.4 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3252.2 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2457.6 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1814.6 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1284.3 |        |        |      |        |      |        |      |        |      |        |      |
| 955.3  |        |        |      |        |      |        |      |        |      |        |      |
| 694.8  |        |        |      |        |      |        |      |        |      |        |      |
| 522.9  |        |        |      |        |      |        |      |        |      |        |      |
| 293.8  |        |        |      |        |      |        |      |        |      |        |      |
| 133.0  |        |        |      |        |      |        |      |        |      |        |      |
| 38.8   |        |        |      |        |      |        |      |        |      |        |      |
| 18.5   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 107.2  | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   |
| 0.0    | 2.5°   | 138.6  | 136.7   | 136.7   | 134.9   | 133.0   | 131.2   | 129.3   | 127.5   | 125.7   | 123.8   |
| 0.0    | 5°     | 144.1  | 144.1   | 144.1   | 142.3   | 142.3   | 140.4   | 140.4   | 138.6   | 136.7   | 134.9   |
| 0.0    | 7.5°   | 149.7  | 151.5   | 151.5   | 153.4   | 153.4   | 153.4   | 153.4   | 151.5   | 151.5   | 151.5   |
| 0.0    | 10°    | 158.9  | 160.8   | 162.6   | 164.5   | 166.3   | 168.2   | 168.2   | 170.0   | 170.0   | 170.0   |
| 0.0    | 12.5°  | 170.0  | 175.5   | 179.2   | 184.8   | 188.5   | 194.0   | 197.7   | 203.3   | 207.0   | 210.7   |
| 0.0    | 15°    | 186.6  | 195.9   | 207.0   | 216.2   | 225.4   | 238.4   | 253.2   | 266.1   | 279.0   | 299.4   |
| 0.0    | 17.5°  | 210.7  | 240.2   | 269.8   | 297.5   | 327.1   | 391.7   | 456.4   | 519.2   | 583.9   | 678.2   |
| 0.0    | 20°    | 256.9  | 345.5   | 432.4   | 521.1   | 607.9   | 835.2   | 1060.7  | 1288.0  | 1513.4  | 1755.5  |
| 0.0    | 22.5°  | 360.3  | 578.4   | 796.4   | 1014.5  | 1232.5  | 1707.4  | 2180.5  | 2655.4  | 3128.4  | 3684.6  |
| 0.0    | 25°    | 522.9  | 923.9   | 1324.9  | 1724.0  | 2125.0  | 2867.9  | 3612.6  | 4355.4  | 5098.2  | 5820.7  |
| 0.0    | 27.5°  | 761.3  | 1374.8  | 1988.3  | 2599.9  | 3213.4  | 4220.5  | 5229.4  | 6236.5  | 7243.6  | 8060.3  |
| 0.0    | 30°    | 1055.1 | 1886.7  | 2718.2  | 3549.7  | 4381.3  | 5526.9  | 6672.6  | 7816.4  | 8962.1  | 9854.6  |
| 0.0    | 32.5°  | 1332.3 | 2350.5  | 3368.6  | 4385.0  | 5403.1  | 6707.7  | 8014.1  | 9318.7  | 10623.3 | 11599.0 |
| 0.0    | 35°    | 1513.4 | 2744.1  | 3976.6  | 5207.2  | 6437.9  | 7849.7  | 9261.4  | 10671.4 | 12083.1 | 13197.4 |
| 0.0    | 37.5°  | 1694.5 | 3115.5  | 4534.6  | 5955.6  | 7374.8  | 8925.1  | 10475.5 | 12025.8 | 13576.2 | 14952.8 |
| 0.0    | 40°    | 1897.7 | 3564.5  | 5229.4  | 6896.2  | 8561.1  | 10397.9 | 12232.8 | 14069.6 | 15904.5 | 17846.6 |
| 0.0    | 42.5°  | 2250.7 | 4309.2  | 6369.5  | 8428.1  | 10486.6 | 12916.5 | 15346.4 | 17774.5 | 20204.4 | 22976.2 |
| 0.0    | 45°    | 2914.1 | 5815.2  | 8718.2  | 11619.3 | 14520.4 | 17739.4 | 20960.2 | 24179.2 | 27398.1 | 31086.4 |
| 0.0    | 47.5°  | 4538.3 | 8529.7  | 12519.2 | 16510.6 | 20500.1 | 23975.9 | 27449.9 | 30925.7 | 34399.6 | 38073.2 |
| 0.0    | 50°    | 6944.2 | 11589.7 | 16235.2 | 20878.9 | 25524.4 | 28669.4 | 31812.6 | 34957.7 | 38100.9 | 41595.2 |
| 0.0    | 52.5°  | 8684.9 | 13524.4 | 18365.8 | 23205.3 | 28044.9 | 30883.2 | 33723.3 | 36561.6 | 39399.9 | 42665.1 |
| 0.0    | 55°    | 8816.1 | 13627.9 | 18441.6 | 23253.4 | 28065.2 | 30916.4 | 33767.7 | 36618.9 | 39470.1 | 42931.2 |
| 0.0    | 57.5°  | 7805.3 | 12578.3 | 17349.5 | 22122.5 | 26893.7 | 30140.3 | 33385.2 | 36631.8 | 39876.7 | 43618.6 |
| 0.0    | 60°    | 6639.3 | 11414.2 | 16187.2 | 20962.0 | 25735.0 | 29475.1 | 33217.0 | 36957.1 | 40697.1 | 44202.5 |
| 0.0    | 62.5°  | 5179.5 | 10091.1 | 15004.6 | 19916.2 | 24827.8 | 28625.1 | 32422.4 | 36217.9 | 40015.3 | 42644.8 |
| 0.0    | 65°    | 3860.2 | 8629.5  | 13398.8 | 18166.2 | 22935.6 | 25977.1 | 29018.7 | 32058.4 | 35100.0 | 36727.9 |
| 0.0    | 67.5°  | 2790.3 | 6903.6  | 11015.1 | 15128.4 | 19239.8 | 21416.6 | 23593.4 | 25768.3 | 27945.1 | 29190.5 |
|        | 70°    | 1886.7 | 4736.0  | 7583.6  | 10433.0 | 13280.5 | 15069.2 | 16859.8 | 18648.5 | 20437.3 | 22118.8 |
|        | 72.5°  | 1306.4 | 2906.7  | 4508.8  | 6109.0  | 7709.2  | 9509.1  | 11307.0 | 13106.8 | 14904.8 | 16684.3 |
|        | 75°    | 866.6  | 1594.7  | 2324.6  | 3052.7  | 3780.7  | 5113.0  | 6447.2  | 7779.5  | 9111.8  | 10172.4 |
|        | 77.5°  | 615.3  | 833.4   | 1053.3  | 1271.3  | 1489.4  | 1738.8  | 1990.1  | 2239.6  | 2489.1  | 2867.9  |
|        | 80°    | 292.0  | 319.7   | 347.4   | 373.3   | 401.0   | 491.5   | 582.1   | 672.6   | 763.2   | 859.3   |
|        | 82.5°  | 138.6  | 149.7   | 160.8   | 170.0   | 181.1   | 190.3   | 199.6   | 208.8   | 218.0   | 208.8   |
|        | 85°    | 37.0   | 37.0    | 38.8    | 38.8    | 38.8    | 38.8    | 38.8    | 38.8    | 38.8    | 37.0    |
|        | 87.5°  | 16.6   | 16.6    | 16.6    | 16.6    | 16.6    | 16.6    | 16.6    | 14.8    | 14.8    | 12.9    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 107.2   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 122.0   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 133.0   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 149.7   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 171.9   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 212.5   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 321.5   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 770.6   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1999.4  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4240.8  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6543.2  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8877.1  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10749.0 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12576.5 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 14311.6 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16331.3 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19788.7 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25748.0 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34774.7 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 41746.7 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45089.5 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45930.2 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46394.0 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47360.5 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47706.0 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45276.1 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38357.7 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30437.8 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23798.5 |        |      |        |      |        |      |        |      |        |      |        |
| 18463.7 |        |      |        |      |        |      |        |      |        |      |        |
| 11233.1 |        |      |        |      |        |      |        |      |        |      |        |
| 3246.7  |        |      |        |      |        |      |        |      |        |      |        |
| 955.3   |        |      |        |      |        |      |        |      |        |      |        |
| 197.7   |        |      |        |      |        |      |        |      |        |      |        |
| 35.1    |        |      |        |      |        |      |        |      |        |      |        |
| 12.9    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   |
| 0.0  | 2.5°   | 120.1   | 118.3   | 116.4   | 114.6   | 112.7   | 109.0   | 109.0   | 107.2   | 107.2   |
| 0.0  | 5°     | 131.2   | 129.3   | 127.5   | 125.7   | 125.7   | 123.8   | 122.0   | 122.0   | 120.1   |
| 0.0  | 7.5°   | 149.7   | 147.8   | 146.0   | 144.1   | 144.1   | 142.3   | 142.3   | 140.4   | 140.4   |
| 0.0  | 10°    | 171.9   | 171.9   | 171.9   | 171.9   | 171.9   | 170.0   | 170.0   | 170.0   | 168.2   |
| 0.0  | 12.5°  | 216.2   | 218.0   | 221.7   | 225.4   | 231.0   | 231.0   | 231.0   | 229.1   | 229.1   |
| 0.0  | 15°    | 341.9   | 362.2   | 377.0   | 391.7   | 404.7   | 434.2   | 430.5   | 425.0   | 421.3   |
| 0.0  | 17.5°  | 864.8   | 957.2   | 1007.1  | 1055.1  | 1105.0  | 1241.8  | 1219.6  | 1197.4  | 1177.1  |
| 0.0  | 20°    | 2241.4  | 2483.5  | 2644.3  | 2805.0  | 2967.7  | 3224.5  | 3161.7  | 3098.8  | 3036.0  |
| 0.0  | 22.5°  | 4795.2  | 5351.4  | 5593.5  | 5835.5  | 6075.7  | 6386.2  | 6184.8  | 5983.3  | 5783.8  |
| 0.0  | 25°    | 7263.9  | 7986.4  | 8394.8  | 8803.2  | 9209.7  | 9387.1  | 9124.7  | 8860.5  | 8598.1  |
| 0.0  | 27.5°  | 9693.8  | 10510.6 | 10870.9 | 11229.4 | 11589.7 | 11961.2 | 11635.9 | 11308.9 | 10983.6 |
| 0.0  | 30°    | 11641.5 | 12534.0 | 12923.9 | 13311.9 | 13701.8 | 13960.5 | 13624.2 | 13286.1 | 12949.8 |
| 0.0  | 32.5°  | 13552.2 | 14527.8 | 14954.7 | 15381.5 | 15806.5 | 16178.0 | 15764.0 | 15348.3 | 14934.3 |
| 0.0  | 35°    | 15424.0 | 16538.3 | 17125.9 | 17713.5 | 18301.1 | 18646.7 | 18155.2 | 17661.8 | 17170.3 |
| 0.0  | 37.5°  | 17708.0 | 19084.6 | 19742.5 | 20400.3 | 21058.1 | 21688.3 | 21146.8 | 20603.6 | 20062.1 |
| 0.0  | 40°    | 21730.8 | 23672.8 | 24681.8 | 25692.5 | 26701.5 | 27514.5 | 26830.8 | 26147.1 | 25463.4 |
| 0.0  | 42.5°  | 28519.8 | 31291.5 | 32742.1 | 34190.8 | 35641.4 | 36910.9 | 36192.1 | 35473.2 | 34754.4 |
| 0.0  | 45°    | 38463.1 | 42151.4 | 43919.8 | 45686.3 | 47454.7 | 48382.3 | 47347.5 | 46310.9 | 45276.1 |
| 0.0  | 47.5°  | 45418.4 | 49091.9 | 50666.3 | 52240.7 | 53815.0 | 54873.8 | 53608.1 | 52342.3 | 51078.4 |
| 0.0  | 50°    | 48581.9 | 52076.2 | 53656.1 | 55234.2 | 56814.1 | 57654.9 | 56193.2 | 54729.7 | 53268.1 |
| 0.0  | 52.5°  | 49193.5 | 52458.7 | 54343.5 | 56230.2 | 58115.0 | 59238.5 | 57512.6 | 55784.8 | 54058.9 |
| 0.0  | 55°    | 49855.1 | 53316.1 | 55502.1 | 57690.0 | 59876.0 | 61431.9 | 59480.5 | 57527.4 | 55576.0 |
| 0.0  | 57.5°  | 51100.5 | 54842.4 | 57022.9 | 59201.5 | 61382.0 | 62703.2 | 60746.3 | 58787.6 | 56830.7 |
| 0.0  | 60°    | 51211.4 | 54714.9 | 56588.7 | 58464.2 | 60337.9 | 61169.5 | 59297.6 | 57423.9 | 55552.0 |
| 0.0  | 62.5°  | 47905.6 | 50535.1 | 51836.0 | 53136.9 | 54437.8 | 55341.4 | 53388.2 | 51433.1 | 49480.0 |
| 0.0  | 65°    | 39985.7 | 41613.7 | 42650.3 | 43686.9 | 44723.6 | 45800.9 | 44012.2 | 42223.4 | 40434.7 |
| 0.0  | 67.5°  | 31683.3 | 32928.7 | 34294.3 | 35659.9 | 37025.4 | 38176.6 | 36744.6 | 35310.6 | 33878.5 |
|      | 70°    | 25480.0 | 27159.7 | 28695.3 | 30230.9 | 31766.4 | 32708.8 | 31271.2 | 29831.7 | 28394.1 |
|      | 72.5°  | 20243.2 | 22022.7 | 23305.1 | 24585.7 | 25868.1 | 26099.1 | 25042.1 | 23985.1 | 22930.0 |
|      | 75°    | 12291.9 | 13352.6 | 13378.5 | 13402.5 | 13428.3 | 13648.2 | 12772.4 | 11896.5 | 11022.4 |
|      | 77.5°  | 3625.5  | 4004.3  | 4316.6  | 4627.0  | 4939.3  | 5316.3  | 4994.7  | 4671.4  | 4349.8  |
|      | 80°    | 1049.6  | 1145.7  | 1227.0  | 1306.4  | 1387.7  | 1339.7  | 1263.9  | 1188.2  | 1112.4  |
|      | 82.5°  | 188.5   | 177.4   | 175.5   | 173.7   | 173.7   | 164.5   | 149.7   | 134.9   | 120.1   |
|      | 85°    | 33.3    | 31.4    | 29.6    | 27.7    | 25.9    | 24.0    | 20.3    | 18.5    | 14.8    |
|      | 87.5°  | 11.1    | 9.2     | 7.4     | 5.5     | 5.5     | 1.8     | 1.8     | 1.8     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   | 107.2   |
| 0.0  | 0.0    | 2.5°   | 105.3   | 103.5   | 103.5   | 103.5   | 103.5   | 101.6   | 101.6   | 101.6   | 101.6   |
| 0.0  | 0.0    | 5°     | 116.4   | 116.4   | 114.6   | 114.6   | 112.7   | 112.7   | 110.9   | 110.9   | 109.0   |
| 0.0  | 0.0    | 7.5°   | 136.7   | 134.9   | 133.0   | 131.2   | 129.3   | 125.7   | 123.8   | 122.0   | 122.0   |
| 0.0  | 0.0    | 10°    | 164.5   | 160.8   | 158.9   | 155.2   | 153.4   | 149.7   | 146.0   | 142.3   | 138.6   |
| 0.0  | 0.0    | 12.5°  | 216.2   | 208.8   | 203.3   | 195.9   | 188.5   | 182.9   | 175.5   | 170.0   | 162.6   |
| 0.0  | 0.0    | 15°    | 375.1   | 356.6   | 336.3   | 312.3   | 286.4   | 262.4   | 236.5   | 221.7   | 205.1   |
| 0.0  | 0.0    | 17.5°  | 959.0   | 862.9   | 765.0   | 685.6   | 606.1   | 528.5   | 449.0   | 391.7   | 334.5   |
| 0.0  | 0.0    | 20°    | 2441.0  | 2174.9  | 1908.8  | 1646.4  | 1382.2  | 1119.8  | 855.6   | 722.5   | 589.5   |
| 0.0  | 0.0    | 22.5°  | 4593.8  | 4100.4  | 3605.2  | 3126.6  | 2646.1  | 2167.5  | 1688.9  | 1387.7  | 1088.4  |
| 0.0  | 0.0    | 25°    | 7090.2  | 6469.3  | 5848.5  | 5061.3  | 4272.2  | 3485.1  | 2697.9  | 2208.2  | 1718.5  |
| 0.0  | 0.0    | 27.5°  | 9226.3  | 8511.2  | 7796.1  | 6838.9  | 5881.7  | 4924.5  | 3967.3  | 3237.4  | 2509.4  |
| 0.0  | 0.0    | 30°    | 11076.0 | 10307.3 | 9538.6  | 8424.4  | 7310.1  | 6195.9  | 5081.6  | 4168.8  | 3255.9  |
| 0.0  | 0.0    | 32.5°  | 12680.0 | 11759.7 | 10839.5 | 9690.1  | 8540.8  | 7391.4  | 6242.0  | 5122.2  | 4002.4  |
| 0.0  | 0.0    | 35°    | 14529.7 | 13456.1 | 12380.6 | 11105.6 | 9828.7  | 8553.7  | 7278.7  | 6014.8  | 4749.0  |
| 0.0  | 0.0    | 37.5°  | 16880.1 | 15562.6 | 14243.3 | 12822.3 | 11401.3 | 9982.1  | 8561.1  | 7116.1  | 5671.1  |
| 0.0  | 0.0    | 40°    | 21379.7 | 19679.6 | 17979.6 | 16174.3 | 14367.1 | 12561.7 | 10756.4 | 8982.4  | 7208.5  |
| 0.0  | 0.0    | 42.5°  | 29441.8 | 27145.0 | 24848.1 | 22445.9 | 20041.8 | 17639.6 | 15235.5 | 12733.6 | 10229.7 |
| 0.0  | 0.0    | 45°    | 38540.7 | 35691.3 | 32840.0 | 30144.0 | 27446.2 | 24750.1 | 22054.1 | 18620.8 | 15187.5 |
| 0.0  | 0.0    | 47.5°  | 43657.4 | 40580.7 | 37504.0 | 34952.1 | 32400.3 | 29848.4 | 27296.5 | 23595.2 | 19894.0 |
| 0.0  | 0.0    | 50°    | 45540.3 | 42408.2 | 39276.1 | 36927.5 | 34577.0 | 32228.4 | 29877.9 | 26171.1 | 22462.5 |
| 0.0  | 0.0    | 52.5°  | 45941.3 | 42746.4 | 39551.4 | 37188.0 | 34824.6 | 32463.1 | 30099.7 | 26416.9 | 22734.1 |
| 0.0  | 0.0    | 55°    | 46765.5 | 43337.7 | 39908.1 | 37213.9 | 34519.7 | 31825.6 | 29131.4 | 25389.5 | 21647.6 |
| 0.0  | 0.0    | 57.5°  | 47842.8 | 44328.1 | 40813.5 | 37744.2 | 34675.0 | 31607.5 | 28538.2 | 24447.1 | 20355.9 |
| 0.0  | 0.0    | 60°    | 47560.0 | 44501.8 | 41441.8 | 38154.5 | 34865.3 | 31578.0 | 28288.8 | 23789.3 | 19287.9 |
| 0.0  | 0.0    | 62.5°  | 42652.1 | 40216.7 | 37779.4 | 35075.9 | 32370.7 | 29667.3 | 26963.9 | 22331.3 | 17698.7 |
| 0.0  | 0.0    | 65°    | 35088.9 | 33311.2 | 31533.6 | 29358.7 | 27181.9 | 25007.0 | 22832.1 | 18678.1 | 14526.0 |
| 0.0  | 0.0    | 67.5°  | 28438.5 | 26435.4 | 24430.5 | 22697.2 | 20962.0 | 19228.8 | 17493.6 | 14224.8 | 10955.9 |
|      |        | 70°    | 22593.7 | 20415.1 | 18234.6 | 16542.0 | 14847.5 | 13154.9 | 11462.2 | 9289.2  | 7117.9  |
|      |        | 72.5°  | 17942.7 | 15978.4 | 14014.1 | 12208.8 | 10401.6 | 8596.2  | 6789.0  | 5504.8  | 4220.5  |
|      |        | 75°    | 8575.9  | 7790.5  | 7005.2  | 6061.0  | 5116.7  | 4172.5  | 3228.2  | 2668.3  | 2110.2  |
|      |        | 77.5°  | 3178.3  | 2755.1  | 2330.1  | 1945.8  | 1561.4  | 1178.9  | 794.6   | 728.1   | 661.5   |
|      |        | 80°    | 822.3   | 717.0   | 609.8   | 534.0   | 456.4   | 380.7   | 304.9   | 275.3   | 247.6   |
|      |        | 82.5°  | 94.2    | 86.8    | 81.3    | 77.6    | 72.1    | 68.4    | 62.8    | 57.3    | 51.7    |
|      |        | 85°    | 5.5     | 3.7     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049086  
CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5°  | 360°   |
|--------|------|--------|---------|--------|
| 0.0    | 0.0  | 0°     | 107.2   | 107.2  |
| 0.0    | 0.0  | 2.5°   | 99.8    | 97.9   |
| 0.0    | 0.0  | 5°     | 105.3   | 103.5  |
| 0.0    | 0.0  | 7.5°   | 116.4   | 112.7  |
| 0.0    | 0.0  | 10°    | 127.5   | 123.8  |
| 0.0    | 0.0  | 12.5°  | 144.1   | 138.6  |
| 0.0    | 0.0  | 15°    | 162.6   | 151.5  |
| 0.0    | 0.0  | 17.5°  | 194.0   | 170.0  |
| 0.0    | 0.0  | 20°    | 262.4   | 201.4  |
| 0.0    | 0.0  | 22.5°  | 369.6   | 251.3  |
| 0.0    | 0.0  | 25°    | 543.3   | 347.4  |
| 0.0    | 0.0  | 27.5°  | 755.8   | 462.0  |
| 0.0    | 0.0  | 30°    | 1005.2  | 578.4  |
| 0.0    | 0.0  | 32.5°  | 1225.1  | 689.2  |
| 0.0    | 0.0  | 35°    | 1511.5  | 802.0  |
| 0.0    | 0.0  | 37.5°  | 1864.5  | 946.1  |
| 0.0    | 0.0  | 40°    | 2411.4  | 1164.1 |
| 0.0    | 0.0  | 42.5°  | 3396.4  | 1567.0 |
| 0.0    | 0.0  | 45°    | 5515.8  | 2709.0 |
| 0.0    | 0.0  | 47.5°  | 8487.2  | 4481.0 |
| 0.0    | 0.0  | 50°    | 10383.1 | 5719.1 |
| 0.0    | 0.0  | 52.5°  | 10538.3 | 5709.9 |
| 0.0    | 0.0  | 55°    | 9619.9  | 5076.1 |
| 0.0    | 0.0  | 57.5°  | 8208.2  | 4242.7 |
| 0.0    | 0.0  | 60°    | 6822.3  | 3355.7 |
| 0.0    | 0.0  | 62.5°  | 5375.4  | 2317.2 |
| 0.0    | 0.0  | 65°    | 3928.5  | 1639.0 |
| 0.0    | 0.0  | 67.5°  | 2821.7  | 1225.1 |
|        |      | 70°    | 1855.2  | 938.7  |
|        |      | 72.5°  | 1208.5  | 765.0  |
|        |      | 75°    | 813.1   | 633.8  |
|        |      | 77.5°  | 474.9   | 421.3  |
|        |      | 80°    | 168.2   | 147.8  |
|        |      | 82.5°  | 31.4    | 22.2   |
|        |      | 85°    | 0.0     | 0.0    |
|        |      | 87.5°  | 0.0     | 0.0    |
|        |      | 90°    | 0.0     | 0.0    |
|        |      | 92.5°  | 0.0     | 0.0    |
|        |      | 95°    | 0.0     | 0.0    |
|        |      | 97.5°  | 0.0     | 0.0    |
|        |      | 100°   | 0.0     | 0.0    |
|        |      | 102.5° | 0.0     | 0.0    |
|        |      | 105°   | 0.0     | 0.0    |
|        |      | 107.5° | 0.0     | 0.0    |
|        |      | 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1049086

CATALOG NUMBER: GALN-SA6B-760-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-757-U-5WQ


Data in this report applies to families of products including GSS-SB1A-757-U-5WQ

### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-7  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-757-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI  
 5700K CCT 26 LEDS

### Spectral Parameters

|                           |          |           |      |      |       |
|---------------------------|----------|-----------|------|------|-------|
| CCT (K):                  | 5571     | CRI (Ra): | 69.9 |      |       |
| CIE u':                   | 0.2033   | R1:       | 68.8 | R9:  | -35.4 |
| CIE v':                   | 0.4806   | R2:       | 72.5 | R10: | 36.7  |
| Duv:                      | 0.0041   | R3:       | 76.8 | R11: | 73.9  |
| CIE x:                    | 0.3308   | R4:       | 72.0 | R12: | 47.8  |
| CIE y:                    | 0.3476   | R5:       | 70.9 | R13: | 68.0  |
| CIE z:                    | 0.3216   | R6:       | 65.6 | R14: | 87.0  |
| Peak Wavelength (nm):     | 442      | R7:       | 75.5 | R15: | 59.8  |
| Dominant Wavelength (nm): | 544      | R8:       | 56.8 |      |       |
| Purity:                   | 3.635698 |           |      |      |       |
| Rf:                       | 70.4     |           |      |      |       |
| Rg:                       | 97.1     |           |      |      |       |



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-7

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 120                         | NR               | 620       | 298                         | NR               | 750       | 9                           | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 167                         | NR               | 625       | 270                         | NR               | 755       | 7                           | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 222                         | NR               | 630       | 245                         | NR               | 760       | 6                           | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 279                         | NR               | 635       | 219                         | NR               | 765       | 6                           | NR               | 895       | 0                           | NR               |
| 380       | 1                           | NR               | 510       | 329                         | NR               | 640       | 196                         | NR               | 770       | 5                           | NR               | 900       | 0                           | NR               |
| 385       | 2                           | NR               | 515       | 371                         | NR               | 645       | 173                         | NR               | 775       | 4                           | NR               | 905       | 0                           | NR               |
| 390       | 4                           | NR               | 520       | 403                         | NR               | 650       | 153                         | NR               | 780       | 4                           | NR               | 910       | 0                           | NR               |
| 395       | 6                           | NR               | 525       | 424                         | NR               | 655       | 135                         | NR               | 785       | 3                           | NR               | 915       | 0                           | NR               |
| 400       | 9                           | NR               | 530       | 439                         | NR               | 660       | 117                         | NR               | 790       | 3                           | NR               | 920       | 0                           | NR               |
| 405       | 14                          | NR               | 535       | 449                         | NR               | 665       | 103                         | NR               | 795       | 2                           | NR               | 925       | 0                           | NR               |
| 410       | 28                          | NR               | 540       | 454                         | NR               | 670       | 89                          | NR               | 800       | 2                           | NR               | 930       | 0                           | NR               |
| 415       | 55                          | NR               | 545       | 459                         | NR               | 675       | 77                          | NR               | 805       | 2                           | NR               | 935       | 0                           | NR               |
| 420       | 118                         | NR               | 550       | 463                         | NR               | 680       | 67                          | NR               | 810       | 2                           | NR               | 940       | 0                           | NR               |
| 425       | 237                         | NR               | 555       | 466                         | NR               | 685       | 58                          | NR               | 815       | 1                           | NR               | 945       | 0                           | NR               |
| 430       | 420                         | NR               | 560       | 467                         | NR               | 690       | 50                          | NR               | 820       | 1                           | NR               | 950       | 0                           | NR               |
| 435       | 677                         | NR               | 565       | 469                         | NR               | 695       | 43                          | NR               | 825       | 1                           | NR               | 955       | 0                           | NR               |
| 440       | 962                         | NR               | 570       | 469                         | NR               | 700       | 37                          | NR               | 830       | 1                           | NR               | 960       | 0                           | NR               |
| 445       | 894                         | NR               | 575       | 466                         | NR               | 705       | 32                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 472                         | NR               | 580       | 461                         | NR               | 710       | 28                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 275                         | NR               | 585       | 450                         | NR               | 715       | 24                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 180                         | NR               | 590       | 437                         | NR               | 720       | 21                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 107                         | NR               | 595       | 420                         | NR               | 725       | 18                          | NR               | 855       | 0                           | NR               | 985       | 0                           | NR               |
| 470       | 76                          | NR               | 600       | 400                         | NR               | 730       | 15                          | NR               | 860       | 0                           | NR               | 990       | 0                           | NR               |
| 475       | 68                          | NR               | 605       | 376                         | NR               | 735       | 13                          | NR               | 865       | 0                           | NR               | 995       | 0                           | NR               |
| 480       | 69                          | NR               | 610       | 352                         | NR               | 740       | 11                          | NR               | 870       | 0                           | NR               | 1000      | 0                           | NR               |
| 485       | 86                          | NR               | 615       | 325                         | NR               | 745       | 10                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-7

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-7

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71


| λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>λ</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 120                      | NR            | 620    | 298                      | NR            | 750    | 9                        | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 167                      | NR            | 625    | 270                      | NR            | 755    | 7                        | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 222                      | NR            | 630    | 245                      | NR            | 760    | 6                        | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 279                      | NR            | 635    | 219                      | NR            | 765    | 6                        | NR            | 895    | 0                        | NR            |
| 380    | 1                        | NR            | 510    | 329                      | NR            | 640    | 196                      | NR            | 770    | 5                        | NR            | 900    | 0                        | NR            |
| 385    | 2                        | NR            | 515    | 371                      | NR            | 645    | 173                      | NR            | 775    | 4                        | NR            | 905    | 0                        | NR            |
| 390    | 4                        | NR            | 520    | 403                      | NR            | 650    | 153                      | NR            | 780    | 4                        | NR            | 910    | 0                        | NR            |
| 395    | 6                        | NR            | 525    | 424                      | NR            | 655    | 135                      | NR            | 785    | 3                        | NR            | 915    | 0                        | NR            |
| 400    | 9                        | NR            | 530    | 439                      | NR            | 660    | 117                      | NR            | 790    | 3                        | NR            | 920    | 0                        | NR            |
| 405    | 14                       | NR            | 535    | 449                      | NR            | 665    | 103                      | NR            | 795    | 2                        | NR            | 925    | 0                        | NR            |
| 410    | 28                       | NR            | 540    | 454                      | NR            | 670    | 89                       | NR            | 800    | 2                        | NR            | 930    | 0                        | NR            |
| 415    | 55                       | NR            | 545    | 459                      | NR            | 675    | 77                       | NR            | 805    | 2                        | NR            | 935    | 0                        | NR            |
| 420    | 118                      | NR            | 550    | 463                      | NR            | 680    | 67                       | NR            | 810    | 2                        | NR            | 940    | 0                        | NR            |
| 425    | 237                      | NR            | 555    | 466                      | NR            | 685    | 58                       | NR            | 815    | 1                        | NR            | 945    | 0                        | NR            |
| 430    | 420                      | NR            | 560    | 467                      | NR            | 690    | 50                       | NR            | 820    | 1                        | NR            | 950    | 0                        | NR            |
| 435    | 677                      | NR            | 565    | 469                      | NR            | 695    | 43                       | NR            | 825    | 1                        | NR            | 955    | 0                        | NR            |
| 440    | 962                      | NR            | 570    | 469                      | NR            | 700    | 37                       | NR            | 830    | 1                        | NR            | 960    | 0                        | NR            |
| 445    | 894                      | NR            | 575    | 466                      | NR            | 705    | 32                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 472                      | NR            | 580    | 461                      | NR            | 710    | 28                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 275                      | NR            | 585    | 450                      | NR            | 715    | 24                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 180                      | NR            | 590    | 437                      | NR            | 720    | 21                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 107                      | NR            | 595    | 420                      | NR            | 725    | 18                       | NR            | 855    | 0                        | NR            | 985    | 0                        | NR            |
| 470    | 76                       | NR            | 600    | 400                      | NR            | 730    | 15                       | NR            | 860    | 0                        | NR            | 990    | 0                        | NR            |
| 475    | 68                       | NR            | 605    | 376                      | NR            | 735    | 13                       | NR            | 865    | 0                        | NR            | 995    | 0                        | NR            |
| 480    | 69                       | NR            | 610    | 352                      | NR            | 740    | 11                       | NR            | 870    | 0                        | NR            | 1000   | 0                        | NR            |
| 485    | 86                       | NR            | 615    | 325                      | NR            | 745    | 10                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-7





TM-30-18

### Summary

$R_f = 70.4$   
 $R_g = 97.1$   
 $CIE R_a = 69.9$   
 $R_g = -35.4$




### Color Vector Graphics






Individual Sample Fidelity Index ( $R_{f,i}$ )


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 52 | CES51 = 87 | CES76 = 40 |
| CES02 = 59 | CES27 = 77 | CES52 = 88 | CES77 = 62 |
| CES03 = 30 | CES28 = 76 | CES53 = 74 | CES78 = 43 |
| CES04 = 68 | CES29 = 46 | CES54 = 79 | CES79 = 72 |
| CES05 = 45 | CES30 = 54 | CES55 = 78 | CES80 = 68 |
| CES06 = 49 | CES31 = 52 | CES56 = 67 | CES81 = 70 |
| CES07 = 38 | CES32 = 49 | CES57 = 64 | CES82 = 87 |
| CES08 = 37 | CES33 = 59 | CES58 = 66 | CES83 = 81 |
| CES09 = 29 | CES34 = 61 | CES59 = 87 | CES84 = 87 |
| CES10 = 72 | CES35 = 78 | CES60 = 91 | CES85 = 83 |
| CES11 = 55 | CES36 = 88 | CES61 = 88 | CES86 = 75 |
| CES12 = 61 | CES37 = 71 | CES62 = 77 | CES87 = 74 |
| CES13 = 41 | CES38 = 64 | CES63 = 74 | CES88 = 76 |
| CES14 = 74 | CES39 = 90 | CES64 = 71 | CES89 = 75 |
| CES15 = 70 | CES40 = 81 | CES65 = 63 | CES90 = 73 |
| CES16 = 46 | CES41 = 82 | CES66 = 66 | CES91 = 93 |
| CES17 = 48 | CES42 = 69 | CES67 = 63 | CES92 = 69 |
| CES18 = 55 | CES43 = 67 | CES68 = 71 | CES93 = 82 |
| CES19 = 70 | CES44 = 98 | CES69 = 81 | CES94 = 58 |
| CES20 = 63 | CES45 = 77 | CES70 = 57 | CES95 = 72 |
| CES21 = 85 | CES46 = 76 | CES71 = 54 | CES96 = 78 |
| CES22 = 77 | CES47 = 73 | CES72 = 84 | CES97 = 82 |
| CES23 = 91 | CES48 = 65 | CES73 = 45 | CES98 = 70 |
| CES24 = 90 | CES49 = 77 | CES74 = 92 | CES99 = 59 |
| CES25 = 71 | CES50 = 85 | CES75 = 49 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)