

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1048462

Luminaire Tested: **GALN-SA3B-760-U-T4BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1048462
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA3B-760-U-T4BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 3xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (42) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14319.8 lumens
Efficiency: N/A
Efficacy: 134.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 106.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1048462

CATALOG NUMBER: GALN-SA3B-760-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 14.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P1048462

CATALOG NUMBER: GALN-SA3B-760-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1048462

CATALOG NUMBER: GALN-SA3B-760-U-T4BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	50.9	0.0	50.9
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	14268.9	0.0	14268.9
	% Fixture	99.6	0.0	99.6
Total	Lumens	14319.8	0.0	14319.8
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.0	0.1
10°-20°	153.0	1.1
20°-30°	545.0	3.8
30°-40°	1313.6	9.2
40°-50°	2198.4	15.4
50°-60°	2823.6	19.7
60°-70°	3573.3	25.0
70°-80°	3185.8	22.2
80°-90°	515.0	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	14319.8	100.0
0°-180°	14319.8	100.0



REPORT NUMBER: P1048462


CATALOG NUMBER: GALN-SA3B-760-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	697.8	4.9			
FM	(30°-60°)	6323.9	44.2			
FH	(60°-80°)	6734.6	47.0			G3/7500
FVH	(80°-90°)	512.6	3.6			G4/750
BL	(0°-30°)	12.3	0.1	B0/110		
BM	(30°-60°)	11.8	0.1	B0/220		
BH	(60°-80°)	24.5	0.2	B0/110		G0/110
BVH	(80°-90°)	2.3	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type IV Short



REPORT NUMBER: P1048462

CATALOG NUMBER: GALN-SA3B-760-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	39°	45°	55°	65°	75°	85°
0°	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5
2.5°	90.2	90.2	90.2	87.2	87.2	86.3	85.3	85.3	83.4	82.4	80.5
5°	136.7	133.8	127.0	123.1	115.4	110.5	105.7	98.9	92.1	87.2	81.4
7.5°	309.2	316.0	293.7	252.0	209.4	191.0	159.9	128.9	106.6	92.1	82.4
10°	788.1	784.2	708.6	625.2	482.7	425.6	333.5	210.4	137.7	100.8	83.4
12.5°	1340.6	1336.8	1247.6	1134.2	946.1	826.9	652.4	392.6	197.8	114.4	83.4
15°	1805.0	1789.5	1761.4	1648.9	1428.9	1329.0	1098.3	694.1	319.9	137.7	85.3
17.5°	2112.3	2098.7	2072.5	2031.8	1892.2	1774.0	1588.8	1090.5	517.6	178.4	89.2
20°	2394.4	2384.7	2363.3	2355.6	2265.4	2202.4	2049.3	1546.2	806.5	242.3	95.0
22.5°	2782.1	2761.7	2770.5	2723.9	2635.7	2560.1	2466.1	2023.1	1159.4	349.0	105.7
25°	3257.1	3247.4	3223.2	3190.2	3068.1	3002.2	2857.7	2472.9	1553.9	488.6	117.3
27.5°	3831.0	3820.3	3814.5	3738.9	3598.3	3526.6	3325.0	2897.5	1997.9	684.4	132.8
30°	4492.1	4496.9	4459.1	4362.2	4198.4	4097.5	3890.1	3342.4	2452.5	914.1	149.3
32.5°	5176.5	5166.8	5108.6	4994.2	4847.8	4753.8	4490.1	3830.0	2929.4	1217.5	168.7
35°	5914.2	5895.7	5742.6	5611.7	5486.7	5368.4	5128.0	4396.1	3406.4	1557.8	194.8
37.5°	6658.6	6572.4	6265.1	6099.3	6013.0	5916.1	5692.2	5000.0	3880.4	1937.8	226.8
40°	7220.9	7154.0	6789.5	6484.1	6415.3	6332.9	6166.2	5521.6	4384.5	2345.9	265.6
42.5°	7532.0	7495.2	7167.6	6866.1	6704.2	6631.5	6489.0	5977.2	4882.7	2796.6	321.8
45°	7664.8	7607.7	7388.6	7248.0	6990.2	6870.0	6700.3	6321.3	5403.3	3308.5	400.4
47.5°	7624.1	7591.2	7434.1	7485.5	7298.4	7111.3	6862.2	6585.0	5848.2	3895.9	508.0
50°	7368.2	7340.1	7291.6	7569.8	7546.6	7325.6	7071.6	6793.4	6211.8	4501.8	674.7
52.5°	6881.6	6870.0	6994.0	7503.9	7687.1	7514.6	7273.2	6977.6	6551.0	5134.8	913.2
55°	6254.4	6301.9	6656.7	7401.2	7758.9	7654.2	7451.6	7150.1	6823.4	5700.9	1265.0
57.5°	5996.6	6009.2	6452.2	7328.5	7790.9	7777.3	7625.1	7314.9	7073.5	6153.6	1802.1
60°	6298.0	6278.6	6512.3	7383.7	7854.8	7887.8	7779.2	7468.1	7290.7	6542.3	2517.5
62.5°	6842.8	6832.2	6906.8	7619.3	8041.9	8108.8	7993.5	7578.6	7482.6	6798.2	3333.7
65°	7329.4	7307.1	7445.8	8037.1	8370.5	8418.0	8317.2	7767.6	7566.9	6984.3	4100.5
67.5°	7539.8	7534.9	7757.9	8434.5	8715.6	8767.0	8678.8	8028.4	7547.5	7043.5	4438.8
70°	7443.8	7425.4	7782.1	8603.2	8910.5	8968.7	8883.3	8125.3	7337.2	6856.4	3937.6
71°	7338.2	7288.7	7709.4	8591.6	8937.6	8987.1	8837.8	8037.1	7125.9	6590.8	3483.0
72.5°	7010.5	7019.2	7509.7	8470.4	8872.7	8858.1	8579.9	7721.1	6870.9	5987.8	2797.6
75°	6204.0	6255.4	6863.2	7961.5	8293.0	8107.8	7682.3	7117.1	6359.1	4293.4	1942.6
77.5°	5069.8	5146.4	5814.3	6982.4	6888.4	6870.0	6852.5	6270.9	5430.4	2306.1	1351.3
80°	2420.5	2586.3	3507.2	4984.5	5414.9	5623.3	5492.5	5053.3	4199.3	1098.3	807.5
82.5°	158.0	156.1	221.0	418.8	1765.2	2281.9	3625.5	3611.9	2927.5	535.1	329.6
85°	74.6	76.6	84.3	96.0	111.5	122.1	168.7	988.8	1400.7	254.9	71.7
87.5°	43.6	44.6	52.3	66.9	87.2	96.9	115.4	148.3	182.2	140.6	15.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1048462

CATALOG NUMBER: GALN-SA3B-760-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5	78.5
2.5°	79.5	78.5	75.6	72.7	69.8	67.9	66.9	67.9	67.9	68.8	68.8
5°	79.5	76.6	71.7	65.9	62.0	58.2	56.2	55.3	56.2	56.2	56.2
7.5°	78.5	73.7	66.9	60.1	55.3	50.4	48.5	47.5	47.5	48.5	48.5
10°	76.6	71.7	63.0	55.3	49.4	43.6	40.7	37.8	37.8	37.8	38.8
12.5°	75.6	68.8	58.2	50.4	42.7	35.9	30.1	27.1	28.1	28.1	28.1
15°	73.7	65.9	55.3	45.6	35.9	27.1	22.3	19.4	20.4	21.3	20.4
17.5°	73.7	64.9	51.4	39.7	28.1	20.4	16.5	14.5	14.5	15.5	15.5
20°	73.7	63.0	48.5	33.9	21.3	15.5	11.6	10.7	10.7	12.6	13.6
22.5°	75.6	63.0	44.6	28.1	17.4	11.6	8.7	7.8	8.7	10.7	11.6
25°	78.5	62.0	40.7	25.2	14.5	8.7	6.8	4.8	5.8	7.8	8.7
27.5°	81.4	61.1	36.8	22.3	11.6	6.8	4.8	3.9	2.9	3.9	3.9
30°	84.3	61.1	33.0	18.4	9.7	4.8	2.9	1.9	1.0	0.0	0.0
32.5°	86.3	59.1	30.1	14.5	7.8	3.9	1.9	1.0	0.0	0.0	0.0
35°	88.2	57.2	26.2	11.6	5.8	2.9	1.0	0.0	0.0	0.0	0.0
37.5°	90.2	54.3	22.3	9.7	4.8	1.9	0.0	0.0	0.0	0.0	0.0
40°	92.1	50.4	18.4	8.7	2.9	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	94.0	47.5	15.5	6.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0
45°	98.9	45.6	12.6	5.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	107.6	43.6	11.6	3.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	120.2	41.7	10.7	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	137.7	40.7	9.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	168.7	39.7	8.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	222.0	38.8	8.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	340.3	36.8	8.7	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	607.8	35.9	7.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1059.5	36.8	7.8	1.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	1519.0	38.8	6.8	2.9	1.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	1299.9	33.9	6.8	3.9	1.9	1.0	0.0	0.0	0.0	0.0	0.0
71°	1059.5	30.1	6.8	3.9	1.9	1.0	1.0	0.0	0.0	0.0	0.0
72.5°	681.5	23.3	5.8	3.9	1.9	1.9	1.0	0.0	0.0	0.0	0.0
75°	287.9	19.4	5.8	3.9	2.9	1.9	1.9	1.0	0.0	0.0	0.0
77.5°	123.1	14.5	5.8	4.8	3.9	2.9	2.9	1.9	1.0	0.0	0.0
80°	46.5	11.6	6.8	5.8	4.8	4.8	3.9	1.9	1.0	0.0	0.0
82.5°	21.3	9.7	6.8	5.8	5.8	4.8	3.9	2.9	1.9	0.0	0.0
85°	13.6	8.7	6.8	5.8	5.8	4.8	4.8	2.9	1.9	0.0	0.0
87.5°	10.7	8.7	6.8	6.8	5.8	5.8	3.9	2.9	1.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-760-U-5WQ


Data in this report applies to families of products including GSS-SB1A-760-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-70-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.71

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7



TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$






Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)