

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047255

Luminaire Tested: **GALN-SA7C-760-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047255
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA7C-760-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE
70CRI 5700K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (98) 5700K CCT, 70 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 40714.3 lumens
Efficiency: N/A
Efficacy: 123.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G5

Input Watts (W): 330
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047255

CATALOG NUMBER: GALN-SA7C-760-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 45.7 fc
 Type III - Short - N/A

REPORT NUMBER: P1047255

CATALOG NUMBER: GALN-SA7C-760-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047255

CATALOG NUMBER: GALN-SA7C-760-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	148.6	0.0	148.6
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	40565.7	0.0	40565.7
	% Fixture	99.6	0.0	99.6
Total	Lumens	40714.3	0.0	40714.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	0.1
10°-20°	468.0	1.1
20°-30°	1686.8	4.1
30°-40°	3859.5	9.5
40°-50°	6509.4	16.0
50°-60°	10742.1	26.4
60°-70°	12005.7	29.5
70°-80°	4957.0	12.2
80°-90°	446.9	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	40714.3	100.0
0°-180°	40714.3	100.0



REPORT NUMBER: P1047255


CATALOG NUMBER: GALN-SA7C-760-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	2155.1	5.3			
FM	(30°-60°)	21075.3	51.8			
FH	(60°-80°)	16894.6	41.5			G5
FVH	(80°-90°)	440.7	1.1			G3/500
BL	(0°-30°)	38.8	0.1	B0/110		
BM	(30°-60°)	35.6	0.1	B0/220		
BH	(60°-80°)	68.1	0.2	B0/110		G0/110
BVH	(80°-90°)	6.1	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G5

Type III Short





REPORT NUMBER: P1047255

CATALOG NUMBER: GALN-SA7C-760-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2
2.5°	319.5	330.1	319.5	319.5	319.5	308.8	308.8	298.2	298.2	287.5	276.9
5°	468.5	468.5	436.6	415.3	394.0	383.3	372.7	351.4	330.1	308.8	287.5
7.5°	1043.6	1043.6	947.7	819.9	649.6	553.7	532.4	436.6	372.7	330.1	287.5
10°	2491.7	2491.7	2278.8	1927.4	1490.8	1107.4	990.3	628.3	447.2	351.4	298.2
12.5°	4142.3	4195.5	3929.3	3482.1	2832.5	2161.6	1927.4	1150.0	596.3	383.3	298.2
15°	5622.4	5494.6	5420.1	4994.1	4376.5	3577.9	3279.7	1938.0	862.5	436.6	298.2
17.5°	6623.4	6623.4	6516.9	6229.4	5665.0	4962.2	4717.3	3130.7	1395.0	500.5	308.8
20°	7794.7	7794.7	7603.0	7400.7	6900.2	6303.9	6069.6	4451.1	2161.6	638.9	308.8
22.5°	9210.9	9232.2	9019.3	8657.2	8178.0	7517.8	7315.5	5675.6	3130.7	851.9	319.5
25°	10936.0	10957.3	10648.5	10307.7	9573.0	8859.5	8550.7	7081.2	4312.6	1192.6	319.5
27.5°	12842.1	12991.1	12533.3	11947.6	11170.3	10275.8	10041.5	8348.4	5484.0	1682.5	340.8
30°	15216.7	15216.7	14609.7	13789.8	12948.6	11841.1	11543.0	9679.5	6729.8	2332.0	362.0
32.5°	17261.2	17101.5	16324.1	15461.6	14567.1	13534.2	13214.8	11074.4	8007.7	3141.3	404.6
35°	18826.5	18688.1	17729.7	16803.3	16026.0	15078.2	14694.9	12586.5	9360.0	4057.1	468.5
37.5°	20168.2	20115.0	18815.9	17655.2	17144.1	16313.5	15972.7	14013.4	10691.1	5047.4	543.1
40°	21637.7	21467.3	20083.0	18645.5	17878.8	17207.9	16899.1	15163.4	11968.9	6208.1	649.6
42.5°	22894.2	22691.9	21446.0	20040.4	18730.7	17825.6	17527.4	16132.4	13214.8	7368.7	788.0
45°	24289.2	24182.7	22926.2	21861.3	20115.0	18666.8	18272.8	16909.8	14354.2	8753.1	969.0
47.5°	26386.9	26195.3	25023.9	24150.8	22127.5	19944.6	19380.2	17708.4	15450.9	10116.1	1245.9
50°	28825.4	28697.7	28005.5	27313.4	25300.8	22127.5	21456.7	18858.5	16675.5	11734.6	1607.9
52.5°	30816.7	30795.4	30880.6	30891.2	29368.5	25801.3	24800.3	20711.3	18081.1	13331.9	2119.0
55°	30774.1	30869.9	31807.0	32882.5	32999.6	30816.7	29847.7	23831.3	19912.7	15301.9	2832.5
57.5°	29624.1	29549.5	30539.8	32158.4	33297.8	33532.1	33372.3	28676.4	22670.6	17676.5	3929.3
58°	29251.4	29187.5	30124.5	31775.1	33084.8	33713.1	33553.4	29773.1	23288.2	18017.2	4227.4
60°	27899.0	27909.7	28463.4	29964.8	31274.6	32765.4	32914.5	32903.8	26365.6	20296.0	5728.9
62.5°	26110.1	26024.9	26536.0	277							

REPORT NUMBER: P1047255

CATALOG NUMBER: GALN-SA7C-760-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2	266.2
2.5°	276.9	266.2	255.6	244.9	234.3	223.6	223.6	223.6	223.6	223.6	223.6
5°	266.2	255.6	244.9	223.6	202.3	191.7	181.0	170.4	170.4	170.4	170.4
7.5°	266.2	255.6	223.6	202.3	181.0	159.7	138.4	138.4	138.4	138.4	138.4
10°	266.2	244.9	213.0	181.0	149.1	127.8	117.1	106.5	106.5	106.5	106.5
12.5°	266.2	234.3	202.3	159.7	127.8	106.5	95.8	85.2	85.2	85.2	85.2
15°	266.2	234.3	191.7	149.1	117.1	85.2	74.5	63.9	63.9	63.9	63.9
17.5°	255.6	223.6	181.0	127.8	95.8	63.9	53.2	42.6	42.6	53.2	53.2
20°	244.9	213.0	159.7	106.5	74.5	53.2	31.9	31.9	31.9	31.9	31.9
22.5°	244.9	213.0	149.1	95.8	63.9	31.9	21.3	21.3	21.3	21.3	31.9
25°	244.9	202.3	127.8	74.5	42.6	21.3	10.6	10.6	10.6	10.6	10.6
27.5°	244.9	202.3	117.1	63.9	31.9	21.3	10.6	0.0	0.0	0.0	0.0
30°	234.3	191.7	106.5	53.2	21.3	10.6	0.0	0.0	0.0	0.0	0.0
32.5°	234.3	181.0	85.2	42.6	21.3	10.6	0.0	0.0	0.0	0.0	0.0
35°	244.9	170.4	74.5	31.9	10.6	0.0	0.0	0.0	0.0	0.0	10.6
37.5°	255.6	159.7	63.9	21.3	10.6	0.0	0.0	0.0	0.0	0.0	0.0
40°	266.2	149.1	63.9	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	287.5	149.1	53.2	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	308.8	149.1	42.6	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	351.4	159.7	42.6	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	383.3	170.4	31.9	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	425.9	159.7	31.9	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	479.2	159.7	31.9	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	521.8	149.1	31.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	543.1	138.4	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	649.6	127.8	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	1011.6	106.5	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	2055.2	95.8	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	3833.5	85.2	21.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	4291.3	95.8	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	2704.7	74.5	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	1426.9	74.5	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	713.4	74.5	10.6	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	330.1	53.2	10.6	10.6	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	138.4	31.9	21.3	10.6	10.6	0.0	0.0				

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-7

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-760-U-5WQ


Data in this report applies to families of products including GSS-SB1A-760-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-7
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-70-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI
 5700K CCT 26 LEDS

Spectral Parameters

CCT (K):	5571	CRI (Ra):	69.9		
CIE u':	0.2033	R1:	68.8	R9:	-35.4
CIE v':	0.4806	R2:	72.5	R10:	36.7
Duv:	0.0041	R3:	76.8	R11:	73.9
CIE x:	0.3308	R4:	72.0	R12:	47.8
CIE y:	0.3476	R5:	70.9	R13:	68.0
CIE z:	0.3216	R6:	65.6	R14:	87.0
Peak Wavelength (nm):	442	R7:	75.5	R15:	59.8
Dominant Wavelength (nm):	544	R8:	56.8		
Purity:	3.635698				
Rf:	70.4				
Rg:	97.1				



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-7


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-7

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 5700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-7

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.84

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.71


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	120	NR	620	298	NR	750	9	NR	880	0	NR
365	0	NR	495	167	NR	625	270	NR	755	7	NR	885	0	NR
370	0	NR	500	222	NR	630	245	NR	760	6	NR	890	0	NR
375	0	NR	505	279	NR	635	219	NR	765	6	NR	895	0	NR
380	1	NR	510	329	NR	640	196	NR	770	5	NR	900	0	NR
385	2	NR	515	371	NR	645	173	NR	775	4	NR	905	0	NR
390	4	NR	520	403	NR	650	153	NR	780	4	NR	910	0	NR
395	6	NR	525	424	NR	655	135	NR	785	3	NR	915	0	NR
400	9	NR	530	439	NR	660	117	NR	790	3	NR	920	0	NR
405	14	NR	535	449	NR	665	103	NR	795	2	NR	925	0	NR
410	28	NR	540	454	NR	670	89	NR	800	2	NR	930	0	NR
415	55	NR	545	459	NR	675	77	NR	805	2	NR	935	0	NR
420	118	NR	550	463	NR	680	67	NR	810	2	NR	940	0	NR
425	237	NR	555	466	NR	685	58	NR	815	1	NR	945	0	NR
430	420	NR	560	467	NR	690	50	NR	820	1	NR	950	0	NR
435	677	NR	565	469	NR	695	43	NR	825	1	NR	955	0	NR
440	962	NR	570	469	NR	700	37	NR	830	1	NR	960	0	NR
445	894	NR	575	466	NR	705	32	NR	835	1	NR	965	0	NR
450	472	NR	580	461	NR	710	28	NR	840	1	NR	970	0	NR
455	275	NR	585	450	NR	715	24	NR	845	1	NR	975	0	NR
460	180	NR	590	437	NR	720	21	NR	850	1	NR	980	0	NR
465	107	NR	595	420	NR	725	18	NR	855	0	NR	985	0	NR
470	76	NR	600	400	NR	730	15	NR	860	0	NR	990	0	NR
475	68	NR	605	376	NR	735	13	NR	865	0	NR	995	0	NR
480	69	NR	610	352	NR	740	11	NR	870	0	NR	1000	0	NR
485	86	NR	615	325	NR	745	10	NR	875	0	NR			

REPORT NUMBER: SP1-2407-184-7





TM-30-18

Summary

$R_f = 70.4$
 $R_g = 97.1$
 $CIE R_a = 69.9$
 $R_g = -35.4$




Color Vector Graphics






Individual Sample Fidelity Index ($R_{f,i}$)



CES01 = 85	CES26 = 52	CES51 = 87	CES76 = 40
CES02 = 59	CES27 = 77	CES52 = 88	CES77 = 62
CES03 = 30	CES28 = 76	CES53 = 74	CES78 = 43
CES04 = 68	CES29 = 46	CES54 = 79	CES79 = 72
CES05 = 45	CES30 = 54	CES55 = 78	CES80 = 68
CES06 = 49	CES31 = 52	CES56 = 67	CES81 = 70
CES07 = 38	CES32 = 49	CES57 = 64	CES82 = 87
CES08 = 37	CES33 = 59	CES58 = 66	CES83 = 81
CES09 = 29	CES34 = 61	CES59 = 87	CES84 = 87
CES10 = 72	CES35 = 78	CES60 = 91	CES85 = 83
CES11 = 55	CES36 = 88	CES61 = 88	CES86 = 75
CES12 = 61	CES37 = 71	CES62 = 77	CES87 = 74
CES13 = 41	CES38 = 64	CES63 = 74	CES88 = 76
CES14 = 74	CES39 = 90	CES64 = 71	CES89 = 75
CES15 = 70	CES40 = 81	CES65 = 63	CES90 = 73
CES16 = 46	CES41 = 82	CES66 = 66	CES91 = 93
CES17 = 48	CES42 = 69	CES67 = 63	CES92 = 69
CES18 = 55	CES43 = 67	CES68 = 71	CES93 = 82
CES19 = 70	CES44 = 98	CES69 = 81	CES94 = 58
CES20 = 63	CES45 = 77	CES70 = 57	CES95 = 72
CES21 = 85	CES46 = 76	CES71 = 54	CES96 = 78
CES22 = 77	CES47 = 73	CES72 = 84	CES97 = 82
CES23 = 91	CES48 = 65	CES73 = 45	CES98 = 70
CES24 = 90	CES49 = 77	CES74 = 92	CES99 = 59
CES25 = 71	CES50 = 85	CES75 = 49	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)