

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047334

Luminaire Tested: **GALN-SA9B-830-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047334
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA9B-830-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 9xLight Square PACKAGE
80CRI 3000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (126) 3000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 37337.9 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G5

Input Watts (W): 312.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047334

CATALOG NUMBER: GALN-SA9B-830-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 41.9 fc
 Type III - Short - N/A

REPORT NUMBER: P1047334

CATALOG NUMBER: GALN-SA9B-830-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047334

CATALOG NUMBER: GALN-SA9B-830-U-T3BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	136.3	0.0	136.3
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	37201.5	0.0	37201.5
	% Fixture	99.6	0.0	99.6
Total	Lumens	37337.9	0.0	37337.9
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.8	0.1
10°-20°	429.2	1.1
20°-30°	1547.0	4.1
30°-40°	3539.4	9.5
40°-50°	5969.6	16.0
50°-60°	9851.2	26.4
60°-70°	11010.1	29.5
70°-80°	4545.9	12.2
80°-90°	409.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	37337.9	100.0
0°-180°	37337.9	100.0



REPORT NUMBER: P1047334


CATALOG NUMBER: GALN-SA9B-830-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1976.4	5.3			
FM	(30°-60°)	19327.5	51.8			
FH	(60°-80°)	15493.5	41.5			G5
FVH	(80°-90°)	404.2	1.1			G3/500
BL	(0°-30°)	35.5	0.1	B0/110		
BM	(30°-60°)	32.7	0.1	B0/220		
BH	(60°-80°)	62.5	0.2	B0/110		G0/110
BVH	(80°-90°)	5.6	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G5

Type III Short



REPORT NUMBER: P1047334

CATALOG NUMBER: GALN-SA9B-830-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1
2.5°	293.0	302.7	293.0	293.0	293.0	283.2	283.2	273.4	273.4	263.7	253.9
5°	429.7	429.7	400.4	380.9	361.3	351.6	341.8	322.3	302.7	283.2	263.7
7.5°	957.0	957.0	869.1	751.9	595.7	507.8	488.3	400.4	341.8	302.7	263.7
10°	2285.1	2285.1	2089.8	1767.5	1367.2	1015.6	908.2	576.2	410.1	322.3	273.4
12.5°	3798.7	3847.6	3603.4	3193.3	2597.6	1982.4	1767.5	1054.7	546.9	351.6	273.4
15°	5156.1	5038.9	4970.6	4580.0	4013.6	3281.2	3007.7	1777.3	791.0	400.4	273.4
17.5°	6074.1	6074.1	5976.4	5712.8	5195.2	4550.7	4326.1	2871.0	1279.3	459.0	283.2
20°	7148.3	7148.3	6972.5	6786.9	6328.0	5781.1	5566.3	4081.9	1982.4	585.9	283.2
22.5°	8447.1	8466.6	8271.3	7939.3	7499.8	6894.4	6708.8	5205.0	2871.0	781.2	293.0
25°	10029.1	10048.6	9765.4	9452.9	8779.1	8124.8	7841.6	6494.0	3955.0	1093.7	293.0
27.5°	11777.1	11913.8	11493.9	10956.8	10243.9	9423.6	9208.8	7656.1	5029.2	1542.9	312.5
30°	13954.7	13954.7	13398.1	12646.2	11874.7	10859.1	10585.7	8876.7	6171.7	2138.6	332.0
32.5°	15829.7	15683.2	14970.3	14179.3	13359.0	12411.8	12118.8	10156.0	7343.6	2880.8	371.1
35°	17265.2	17138.3	16259.4	15409.8	14696.9	13827.8	13476.2	11542.7	8583.8	3720.6	429.7
37.5°	18495.6	18446.8	17255.4	16191.0	15722.3	14960.6	14648.1	12851.2	9804.4	4628.8	498.0
40°	19843.3	19687.0	18417.5	17099.2	16396.1	15780.9	15497.7	13905.9	10976.3	5693.2	595.7
42.5°	20995.6	20810.0	19667.5	18378.5	17177.3	16347.3	16073.8	14794.6	12118.8	6757.6	722.6
45°	22274.8	22177.2	21024.9	20048.3	18446.8	17118.7	16757.4	15507.4	13163.7	8027.1	888.7
47.5°	24198.6	24022.8	22948.7	22147.9	20292.5	18290.6	17773.0	16239.8	14169.6	9277.1	1142.6
50°	26434.9	26317.7	25683.0	25048.2	23202.6	20292.5	19677.3	17294.5	15292.6	10761.5	1474.6
52.5°	28261.0	28241.5	28319.6	28329.4	26932.9	23661.5	22743.6	18993.7	16581.6	12226.3	1943.3
55°	28222.0	28309.9	29169.2	30155.5	30262.9	28261.0	27372.4	21854.9	18261.3	14032.9	2597.6
57.5°	27167.3	27098.9	28007.1	29491.5	30536.4	30751.2	30604.7	26298.2	20790.5	16210.5	3603.4
58°	26825.5	26766.9	27626.3	29139.9	30341.1	30917.2	30770.7	27304.0	21356.9	16523.0	3876.9
60°	25585.3	25595.1	26102.9	27479.8	28680.9	30048.1	30184.8	30175.0	24179.1	18612.8	5253.8
62.5°	23944.7	23866.6	24335.3	25458.4	26513.0	27431.0	27665.3	30370.3	28309.9	21269.0	7880.7
65°	21679.2	21562.0	22060.0	23329.5	24462.3	25058.0	25067.7	27753.2	30253.2	24120.5	11630.6
67.5°	17470.3	17372.6	18368.7	19999.5	21747.5	22528.7	22880.3	24081.4	28612.6	26054.0	13779.0
70°	10702.9	10907.9	12294.6	14853.2	17841.4	19276.9	19804.2	20175.3	24364.6	25761.1	11523.2
72.5°	4941.3	4697.2	5878.8	7665.8	11073.9	14267.2	14814.1	16269.1	19315.9	22362.7	8593.5
75°	2304.6	2216.7	2490.2	3349.5	5019.4	7704.9	8701.0	12988.0	14814.1	15556.3	6201.0
77.5°	1181.6	1191.4	1416.0	1523.4	2070.3	3564.4	4091.7	8544.7	10859.1	8681.4	4160.1
80°	517.6	537.1	546.9	595.7	839.8	1376.9	1552.7	3964.7	7421.7	4423.7	2275.3
82.5°	332.0	341.8	341.8	341.8	400.4	546.9	625.0	1591.8	3701.1	2197.2	703.1
85°	175.8	175.8	195.3	244.1	283.2	332.0	351.6	507.8	1220.7	654.3	166.0
87.5°	97.7	107.4	117.2	146.5	185.5	224.6	244.1	351.6	468.7	449.2	39.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1047334

CATALOG NUMBER: GALN-SA9B-830-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1	244.1
2.5°	253.9	244.1	234.4	224.6	214.8	205.1	205.1	205.1	205.1	205.1	205.1
5°	244.1	234.4	224.6	205.1	185.5	175.8	166.0	156.2	156.2	156.2	156.2
7.5°	244.1	234.4	205.1	185.5	166.0	146.5	127.0	127.0	127.0	127.0	127.0
10°	244.1	224.6	195.3	166.0	136.7	117.2	107.4	97.7	97.7	97.7	97.7
12.5°	244.1	214.8	185.5	146.5	117.2	97.7	87.9	78.1	78.1	78.1	78.1
15°	244.1	214.8	175.8	136.7	107.4	78.1	68.4	58.6	58.6	58.6	58.6
17.5°	234.4	205.1	166.0	117.2	87.9	58.6	48.8	39.1	39.1	48.8	48.8
20°	224.6	195.3	146.5	97.7	68.4	48.8	29.3	29.3	29.3	29.3	29.3
22.5°	224.6	195.3	136.7	87.9	58.6	29.3	19.5	19.5	19.5	19.5	29.3
25°	224.6	185.5	117.2	68.4	39.1	19.5	9.8	9.8	9.8	9.8	9.8
27.5°	224.6	185.5	107.4	58.6	29.3	19.5	9.8	0.0	0.0	0.0	0.0
30°	214.8	175.8	97.7	48.8	19.5	9.8	0.0	0.0	0.0	0.0	0.0
32.5°	214.8	166.0	78.1	39.1	19.5	9.8	0.0	0.0	0.0	0.0	0.0
35°	224.6	156.2	68.4	29.3	9.8	0.0	0.0	0.0	0.0	0.0	9.8
37.5°	234.4	146.5	58.6	19.5	9.8	0.0	0.0	0.0	0.0	0.0	0.0
40°	244.1	136.7	58.6	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	263.7	136.7	48.8	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	283.2	136.7	39.1	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	322.3	146.5	39.1	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	351.6	156.2	29.3	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	390.6	146.5	29.3	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	439.4	146.5	29.3	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	478.5	136.7	29.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	498.0	127.0	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	595.7	117.2	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	927.7	97.7	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1884.7	87.9	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	3515.5	78.1	19.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	3935.5	87.9	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	2480.4	68.4	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	1308.6	68.4	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	654.3	68.4	9.8	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	302.7	48.8	9.8	9.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	127.0	29.3	19.5	9.8	9.8	0.0	0.0	0.0	0.0	0.0	0.0
85°	58.6	29.3	19.5	19.5	9.8	9.8	0.0	0.0	0.0	0.0	0.0
87.5°	29.3	29.3	29.3	19.5	19.5	9.8	9.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-9

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-830-U-5WQ

Data in this report applies to families of products including GSS-SB1A-830-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-9
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-830-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI
 3000K CCT 26 LEDS

Spectral Parameters

CCT (K): 3055
 CIE u' : 0.2475
 CIE v' : 0.5247
 Duv: 0.0032
 CIE x: 0.4377
 CIE y: 0.4124
 CIE z: 0.1499
 Peak Wavelength (nm): 604
 Dominant Wavelength (nm): 581
 Purity: 55.16339
 R_f: 81.5
 R_g: 99.2

CRI (Ra): 80.9
 R1: 79.5
 R2: 85.6
 R3: 92.1
 R4: 82.4
 R5: 78.9
 R6: 81.7
 R7: 85.1
 R8: 61.9
 R9: 6.8
 R10: 67.1
 R11: 82.5
 R12: 63.4
 R13: 80.2
 R14: 95.1
 R15: 71.7



Test Conditions


Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-9


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-9

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-9

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	170	NR	620	938	NR	750	35	NR	880	1	NR
365	0	NR	495	234	NR	625	894	NR	755	30	NR	885	1	NR
370	0	NR	500	302	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	371	NR	635	788	NR	765	22	NR	895	1	NR
380	0	NR	510	431	NR	640	728	NR	770	19	NR	900	1	NR
385	0	NR	515	482	NR	645	665	NR	775	16	NR	905	1	NR
390	0	NR	520	523	NR	650	603	NR	780	14	NR	910	0	NR
395	2	NR	525	553	NR	655	542	NR	785	12	NR	915	0	NR
400	4	NR	530	580	NR	660	484	NR	790	11	NR	920	0	NR
405	8	NR	535	603	NR	665	430	NR	795	9	NR	925	0	NR
410	18	NR	540	622	NR	670	377	NR	800	8	NR	930	0	NR
415	36	NR	545	644	NR	675	330	NR	805	7	NR	935	0	NR
420	71	NR	550	668	NR	680	289	NR	810	6	NR	940	0	NR
425	131	NR	555	693	NR	685	250	NR	815	5	NR	945	0	NR
430	215	NR	560	720	NR	690	218	NR	820	4	NR	950	0	NR
435	341	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	514	NR	570	792	NR	700	161	NR	830	3	NR	960	0	NR
445	576	NR	575	832	NR	705	139	NR	835	3	NR	965	0	NR
450	358	NR	580	875	NR	710	119	NR	840	3	NR	970	0	NR
455	222	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	170	NR	590	950	NR	720	88	NR	850	2	NR	980	0	NR
465	115	NR	595	977	NR	725	76	NR	855	2	NR	985	0	NR
470	88	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	87	NR	605	997	NR	735	56	NR	865	1	NR	995	0	NR
480	96	NR	610	990	NR	740	47	NR	870	1	NR	1000	0	NR
485	122	NR	615	971	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-9


Scotopic Flux vs. Wavelength


Scotopic Lumens: NR
S/P: 1.28

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	170	NR	620	938	NR	750	35	NR	880	1	NR
365	0	NR	495	234	NR	625	894	NR	755	30	NR	885	1	NR
370	0	NR	500	302	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	371	NR	635	788	NR	765	22	NR	895	1	NR
380	0	NR	510	431	NR	640	728	NR	770	19	NR	900	1	NR
385	0	NR	515	482	NR	645	665	NR	775	16	NR	905	1	NR
390	0	NR	520	523	NR	650	603	NR	780	14	NR	910	0	NR
395	2	NR	525	553	NR	655	542	NR	785	12	NR	915	0	NR
400	4	NR	530	580	NR	660	484	NR	790	11	NR	920	0	NR
405	8	NR	535	603	NR	665	430	NR	795	9	NR	925	0	NR
410	18	NR	540	622	NR	670	377	NR	800	8	NR	930	0	NR
415	36	NR	545	644	NR	675	330	NR	805	7	NR	935	0	NR
420	71	NR	550	668	NR	680	289	NR	810	6	NR	940	0	NR
425	131	NR	555	693	NR	685	250	NR	815	5	NR	945	0	NR
430	215	NR	560	720	NR	690	218	NR	820	4	NR	950	0	NR
435	341	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	514	NR	570	792	NR	700	161	NR	830	3	NR	960	0	NR
445	576	NR	575	832	NR	705	139	NR	835	3	NR	965	0	NR
450	358	NR	580	875	NR	710	119	NR	840	3	NR	970	0	NR
455	222	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	170	NR	590	950	NR	720	88	NR	850	2	NR	980	0	NR
465	115	NR	595	977	NR	725	76	NR	855	2	NR	985	0	NR
470	88	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	87	NR	605	997	NR	735	56	NR	865	1	NR	995	0	NR
480	96	NR	610	990	NR	740	47	NR	870	1	NR	1000	0	NR
485	122	NR	615	971	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-9

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.33


λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (φ/nm)
360	0	NR	490	170	NR	620	938	NR	750	35	NR	880	1	NR
365	0	NR	495	234	NR	625	894	NR	755	30	NR	885	1	NR
370	0	NR	500	302	NR	630	847	NR	760	26	NR	890	1	NR
375	0	NR	505	371	NR	635	788	NR	765	22	NR	895	1	NR
380	0	NR	510	431	NR	640	728	NR	770	19	NR	900	1	NR
385	0	NR	515	482	NR	645	665	NR	775	16	NR	905	1	NR
390	0	NR	520	523	NR	650	603	NR	780	14	NR	910	0	NR
395	2	NR	525	553	NR	655	542	NR	785	12	NR	915	0	NR
400	4	NR	530	580	NR	660	484	NR	790	11	NR	920	0	NR
405	8	NR	535	603	NR	665	430	NR	795	9	NR	925	0	NR
410	18	NR	540	622	NR	670	377	NR	800	8	NR	930	0	NR
415	36	NR	545	644	NR	675	330	NR	805	7	NR	935	0	NR
420	71	NR	550	668	NR	680	289	NR	810	6	NR	940	0	NR
425	131	NR	555	693	NR	685	250	NR	815	5	NR	945	0	NR
430	215	NR	560	720	NR	690	218	NR	820	4	NR	950	0	NR
435	341	NR	565	754	NR	695	188	NR	825	4	NR	955	0	NR
440	514	NR	570	792	NR	700	161	NR	830	3	NR	960	0	NR
445	576	NR	575	832	NR	705	139	NR	835	3	NR	965	0	NR
450	358	NR	580	875	NR	710	119	NR	840	3	NR	970	0	NR
455	222	NR	585	913	NR	715	102	NR	845	2	NR	975	0	NR
460	170	NR	590	950	NR	720	88	NR	850	2	NR	980	0	NR
465	115	NR	595	977	NR	725	76	NR	855	2	NR	985	0	NR
470	88	NR	600	994	NR	730	65	NR	860	1	NR	990	0	NR
475	87	NR	605	997	NR	735	56	NR	865	1	NR	995	0	NR
480	96	NR	610	990	NR	740	47	NR	870	1	NR	1000	0	NR
485	122	NR	615	971	NR	745	41	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-9





TM-30-18

Summary

$R_f = 81.5$
 $R_g = 99.2$
 $CIE R_a = 80.9$
 $R_9 = 6.8$







Color Vector Graphics





Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 74	CES51 = 89	CES76 = 70
CES02 = 63	CES27 = 88	CES52 = 91	CES77 = 86
CES03 = 31	CES28 = 89	CES53 = 81	CES78 = 72
CES04 = 70	CES29 = 67	CES54 = 87	CES79 = 90
CES05 = 50	CES30 = 68	CES55 = 85	CES80 = 88
CES06 = 51	CES31 = 71	CES56 = 78	CES81 = 78
CES07 = 42	CES32 = 70	CES57 = 76	CES82 = 95
CES08 = 41	CES33 = 71	CES58 = 78	CES83 = 90
CES09 = 29	CES34 = 82	CES59 = 92	CES84 = 93
CES10 = 76	CES35 = 90	CES60 = 95	CES85 = 86
CES11 = 59	CES36 = 93	CES61 = 93	CES86 = 72
CES12 = 65	CES37 = 87	CES62 = 83	CES87 = 85
CES13 = 43	CES38 = 75	CES63 = 77	CES88 = 83
CES14 = 74	CES39 = 94	CES64 = 83	CES89 = 75
CES15 = 71	CES40 = 89	CES65 = 77	CES90 = 81
CES16 = 47	CES41 = 85	CES66 = 80	CES91 = 96
CES17 = 50	CES42 = 86	CES67 = 79	CES92 = 73
CES18 = 56	CES43 = 81	CES68 = 84	CES93 = 84
CES19 = 72	CES44 = 99	CES69 = 90	CES94 = 64
CES20 = 66	CES45 = 87	CES70 = 77	CES95 = 80
CES21 = 87	CES46 = 82	CES71 = 76	CES96 = 84
CES22 = 79	CES47 = 77	CES72 = 92	CES97 = 87
CES23 = 92	CES48 = 71	CES73 = 71	CES98 = 81
CES24 = 91	CES49 = 81	CES74 = 93	CES99 = 74
CES25 = 72	CES50 = 89	CES75 = 74	



Color Rendition by Hue-Angle Bin


Measure Comparisons



(END OF REPORT)