

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1048563

Luminaire Tested: **GALN-SA1C-835-U-T4BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1048563
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA1C-835-U-T4BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 1xLight Square PACKAGE
80CRI 3500K FIXTURE w/ TYPE IV ANGLED BACKLIGHT CONTROL
Light Source: (14) 3500K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5184.5 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 50.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1048563

CATALOG NUMBER: GALN-SA1C-835-U-T4BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 5.3 fc
 Type IV - Short - N/A

REPORT NUMBER: P1048563

CATALOG NUMBER: GALN-SA1C-835-U-T4BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1048563

CATALOG NUMBER: GALN-SA1C-835-U-T4BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	18.5	0.0	18.5
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	5166.1	0.0	5166.1
	% Fixture	99.6	0.0	99.6
Total	Lumens	5184.5	0.0	5184.5
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	4.3	0.1
10°-20°	55.4	1.1
20°-30°	197.3	3.8
30°-40°	475.6	9.2
40°-50°	795.9	15.4
50°-60°	1022.3	19.7
60°-70°	1293.7	25.0
70°-80°	1153.4	22.2
80°-90°	186.5	3.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5184.5	100.0
0°-180°	5184.5	100.0



REPORT NUMBER: P1048563


CATALOG NUMBER: GALN-SA1C-835-U-T4BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	252.6	4.9			
FM	(30°-60°)	2289.6	44.2			
FH	(60°-80°)	2438.3	47.0			G2/5000
FVH	(80°-90°)	185.6	3.6			G2/225
BL	(0°-30°)	4.5	0.1	B0/110		
BM	(30°-60°)	4.3	0.1	B0/220		
BH	(60°-80°)	8.9	0.2	B0/110		G0/110
BVH	(80°-90°)	0.9	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type IV Short



REPORT NUMBER: P1048563

CATALOG NUMBER: GALN-SA1C-835-U-T4BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	39°	45°	55°	65°	75°	85°
0°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
2.5°	32.6	32.6	32.6	31.6	31.6	31.2	30.9	30.9	30.2	29.8	29.1
5°	49.5	48.4	46.0	44.6	41.8	40.0	38.3	35.8	33.3	31.6	29.5
7.5°	112.0	114.4	106.3	91.3	75.8	69.1	57.9	46.7	38.6	33.3	29.8
10°	285.3	283.9	256.6	226.4	174.8	154.1	120.7	76.2	49.8	36.5	30.2
12.5°	485.4	484.0	451.7	410.6	342.5	299.4	236.2	142.1	71.6	41.4	30.2
15°	653.5	647.9	637.7	597.0	517.3	481.2	397.6	251.3	115.8	49.8	30.9
17.5°	764.7	759.8	750.4	735.6	685.1	642.3	575.2	394.8	187.4	64.6	32.3
20°	866.9	863.4	855.6	852.8	820.2	797.4	741.9	559.8	292.0	87.7	34.4
22.5°	1007.3	999.9	1003.1	986.2	954.3	926.9	892.8	732.5	419.8	126.3	38.3
25°	1179.2	1175.7	1167.0	1155.0	1110.8	1086.9	1034.6	895.3	562.6	176.9	42.5
27.5°	1387.0	1383.1	1381.0	1353.7	1302.8	1276.8	1203.8	1049.0	723.3	247.8	48.1
30°	1626.4	1628.1	1614.4	1579.3	1520.0	1483.5	1408.4	1210.1	887.9	331.0	54.0
32.5°	1874.1	1870.6	1849.6	1808.2	1755.2	1721.1	1625.7	1386.7	1060.6	440.8	61.1
35°	2141.2	2134.6	2079.1	2031.7	1986.4	1943.6	1856.6	1591.6	1233.3	564.0	70.5
37.5°	2410.8	2379.5	2268.3	2208.3	2177.0	2141.9	2060.9	1810.3	1404.9	701.6	82.1
40°	2614.3	2590.1	2458.1	2347.6	2322.7	2292.8	2232.5	1999.1	1587.4	849.3	96.2
42.5°	2727.0	2713.6	2595.0	2485.9	2427.3	2400.9	2349.3	2164.0	1767.8	1012.5	116.5
45°	2775.1	2754.4	2675.0	2624.1	2530.8	2487.3	2425.9	2288.6	1956.3	1197.8	144.9
47.5°	2760.3	2748.4	2691.5	2710.1	2642.4	2574.7	2484.5	2384.1	2117.4	1410.5	183.9
50°	2667.7	2657.5	2639.9	2740.7	2732.2	2652.2	2560.3	2459.5	2249.0	1629.9	244.3
52.5°	2491.5	2487.3	2532.2	2716.8	2783.1	2720.7	2633.3	2526.2	2371.8	1859.0	330.6
55°	2264.4	2281.6	2410.1	2679.6	2809.1	2771.2	2697.8	2588.7	2470.4	2064.0	458.0
57.5°	2171.1	2175.6	2336.0	2653.3	2820.7	2815.8	2760.7	2648.4	2561.0	2227.9	652.4
60°	2280.2	2273.2	2357.8	2673.3	2843.8	2855.8	2816.5	2703.8	2639.6	2368.6	911.4
62.5°	2477.4	2473.6	2500.6	2758.6	2911.6	2935.8	2894.0	2743.8	2709.1	2461.3	1207.0
65°	2653.6	2645.6	2695.7	2909.8	3030.6	3047.8	3011.3	2812.3	2739.6	2528.7	1484.6
67.5°	2729.8	2728.0	2808.8	3053.7	3155.5	3174.1	3142.2	2906.7	2732.6	2550.1	1607.1
70°	2695.0	2688.4	2817.5	3114.8	3226.0	3247.1	3216.2	2941.8	2656.4	2482.4	1425.6
71°	2656.8	2638.9	2791.2	3110.6	3235.9	3253.8	3199.7	2909.8	2579.9	2386.2	1261.0
72.5°	2538.2	2541.3	2718.9	3066.7	3212.4	3207.1	3106.4	2795.4	2487.6	2167.9	1012.9
75°	2246.2	2264.8	2484.8	2882.5	3002.5	2935.5	2781.4	2576.8	2302.3	1554.4	703.3
77.5°	1835.5	1863.3	2105.1	2528.0	2493.9	2487.3	2481.0	2270.4	1966.1	834.9	489.2
80°	876.4	936.4	1269.8	1804.6	1960.5	2035.9	1988.6	1829.6	1520.4	397.6	292.4
82.5°	57.2	56.5	80.0	151.6	639.1	826.2	1312.6	1307.7	1059.9	193.7	119.3
85°	27.0	27.7	30.5	34.7	40.4	44.2	61.1	358.0	507.1	92.3	26.0
87.5°	15.8	16.1	19.0	24.2	31.6	35.1	41.8	53.7	66.0	50.9	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1048563

CATALOG NUMBER: GALN-SA1C-835-U-T4BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4	28.4
2.5°	28.8	28.4	27.4	26.3	25.3	24.6	24.2	24.6	24.6	24.9	24.9
5°	28.8	27.7	26.0	23.9	22.5	21.1	20.4	20.0	20.4	20.4	20.4
7.5°	28.4	26.7	24.2	21.8	20.0	18.3	17.5	17.2	17.2	17.5	17.5
10°	27.7	26.0	22.8	20.0	17.9	15.8	14.7	13.7	13.7	13.7	14.0
12.5°	27.4	24.9	21.1	18.3	15.4	13.0	10.9	9.8	10.2	10.2	10.2
15°	26.7	23.9	20.0	16.5	13.0	9.8	8.1	7.0	7.4	7.7	7.4
17.5°	26.7	23.5	18.6	14.4	10.2	7.4	6.0	5.3	5.3	5.6	5.6
20°	26.7	22.8	17.5	12.3	7.7	5.6	4.2	3.9	3.9	4.6	4.9
22.5°	27.4	22.8	16.1	10.2	6.3	4.2	3.2	2.8	3.2	3.9	4.2
25°	28.4	22.5	14.7	9.1	5.3	3.2	2.5	1.8	2.1	2.8	3.2
27.5°	29.5	22.1	13.3	8.1	4.2	2.5	1.8	1.4	1.1	1.4	1.4
30°	30.5	22.1	11.9	6.7	3.5	1.8	1.1	0.7	0.4	0.0	0.0
32.5°	31.2	21.4	10.9	5.3	2.8	1.4	0.7	0.4	0.0	0.0	0.0
35°	31.9	20.7	9.5	4.2	2.1	1.1	0.4	0.0	0.0	0.0	0.0
37.5°	32.6	19.7	8.1	3.5	1.8	0.7	0.0	0.0	0.0	0.0	0.0
40°	33.3	18.3	6.7	3.2	1.1	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	34.0	17.2	5.6	2.5	0.7	0.0	0.0	0.0	0.0	0.0	0.0
45°	35.8	16.5	4.6	2.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	39.0	15.8	4.2	1.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	43.5	15.1	3.9	1.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	49.8	14.7	3.5	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	61.1	14.4	3.2	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	80.4	14.0	3.2	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	123.2	13.3	3.2	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	220.1	13.0	2.8	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	383.6	13.3	2.8	0.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	550.0	14.0	2.5	1.1	0.4	0.0	0.0	0.0	0.0	0.0	0.0
70°	470.6	12.3	2.5	1.4	0.7	0.4	0.0	0.0	0.0	0.0	0.0
71°	383.6	10.9	2.5	1.4	0.7	0.4	0.4	0.0	0.0	0.0	0.0
72.5°	246.7	8.4	2.1	1.4	0.7	0.7	0.4	0.0	0.0	0.0	0.0
75°	104.2	7.0	2.1	1.4	1.1	0.7	0.7	0.4	0.0	0.0	0.0
77.5°	44.6	5.3	2.1	1.8	1.4	1.1	1.1	0.7	0.4	0.0	0.0
80°	16.8	4.2	2.5	2.1	1.8	1.8	1.4	0.7	0.4	0.0	0.0
82.5°	7.7	3.5	2.5	2.1	2.1	1.8	1.4	1.1	0.7	0.0	0.0
85°	4.9	3.2	2.5	2.1	2.1	1.8	1.8	1.1	0.7	0.0	0.0
87.5°	3.9	3.2	2.5	2.5	2.1	2.1	1.4	1.1	0.4	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-10

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-835-U-5WQ

Data in this report applies to families of products including GSS-SB1A-835-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-10
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-835-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI 3500K CCT 26 LEDS

Spectral Parameters

CCT (K): 3411
 CIE u' : 0.2360
 CIE v' : 0.5189
 Duv: 0.0044
 CIE x: 0.4154
 CIE y: 0.4059
 CIE z: 0.1787
 Peak Wavelength (nm): 601
 Dominant Wavelength (nm): 579
 Purity: 46.51914
 R_f: 86.6
 R_g: 95.9

CRI (Ra): 83.5
 R1: 81.1
 R2: 88.9
 R3: 97.2
 R4: 83.8
 R5: 81.7
 R6: 86.9
 R7: 86.1
 R8: 62.2
 R9: 6.3
 R10: 75.4
 R11: 84.1
 R12: 69.7
 R13: 82.8
 R14: 98.5
 R15: 72.6



Test Conditions


Stabilization Time: 35M
 Operation Time: 1H 35M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-10


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-10

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-10

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)	λ (nm)	Power W/nm	Lumens (ϕ/nm)
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-10

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.48

λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)	λ (nm)	Power W ^λ /nm	Lumens (Φ/nm)
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-10

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 2.88


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	311	NR	620	903	NR	750	26	NR	880	1	NR
365	0	NR	495	376	NR	625	851	NR	755	22	NR	885	1	NR
370	0	NR	500	438	NR	630	797	NR	760	19	NR	890	0	NR
375	0	NR	505	491	NR	635	735	NR	765	16	NR	895	0	NR
380	0	NR	510	533	NR	640	672	NR	770	14	NR	900	0	NR
385	0	NR	515	566	NR	645	607	NR	775	12	NR	905	0	NR
390	0	NR	520	592	NR	650	546	NR	780	10	NR	910	0	NR
395	1	NR	525	608	NR	655	487	NR	785	9	NR	915	0	NR
400	3	NR	530	625	NR	660	429	NR	790	7	NR	920	0	NR
405	6	NR	535	642	NR	665	378	NR	795	6	NR	925	0	NR
410	12	NR	540	657	NR	670	329	NR	800	5	NR	930	0	NR
415	22	NR	545	677	NR	675	286	NR	805	5	NR	935	0	NR
420	43	NR	550	701	NR	680	248	NR	810	4	NR	940	0	NR
425	80	NR	555	728	NR	685	213	NR	815	3	NR	945	0	NR
430	140	NR	560	757	NR	690	184	NR	820	3	NR	950	0	NR
435	243	NR	565	793	NR	695	156	NR	825	3	NR	955	0	NR
440	412	NR	570	831	NR	700	134	NR	830	2	NR	960	0	NR
445	610	NR	575	872	NR	705	114	NR	835	2	NR	965	0	NR
450	597	NR	580	911	NR	710	97	NR	840	2	NR	970	0	NR
455	412	NR	585	944	NR	715	83	NR	845	1	NR	975	0	NR
460	330	NR	590	974	NR	720	70	NR	850	1	NR	980	0	NR
465	274	NR	595	992	NR	725	60	NR	855	1	NR	985	0	NR
470	211	NR	600	999	NR	730	51	NR	860	1	NR	990	0	NR
475	200	NR	605	992	NR	735	43	NR	865	1	NR	995	0	NR
480	220	NR	610	975	NR	740	36	NR	870	1	NR	1000	0	NR
485	255	NR	615	944	NR	745	31	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-10





TM-30-18

Summary

$R_f = 86.6$
 $R_g = 95.9$
 $CIE R_a = 83.5$
 $R_9 = 6.3$




Color Vector Graphics






Individual Sample Fidelity Index (R_{fi})



CES01 = 86	CES26 = 85	CES51 = 97	CES76 = 81
CES02 = 62	CES27 = 95	CES52 = 96	CES77 = 87
CES03 = 31	CES28 = 94	CES53 = 91	CES78 = 80
CES04 = 70	CES29 = 87	CES54 = 92	CES79 = 93
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 91
CES06 = 51	CES31 = 89	CES56 = 88	CES81 = 77
CES07 = 41	CES32 = 84	CES57 = 87	CES82 = 96
CES08 = 40	CES33 = 91	CES58 = 88	CES83 = 95
CES09 = 29	CES34 = 91	CES59 = 93	CES84 = 92
CES10 = 75	CES35 = 95	CES60 = 94	CES85 = 80
CES11 = 58	CES36 = 90	CES61 = 91	CES86 = 72
CES12 = 64	CES37 = 95	CES62 = 95	CES87 = 86
CES13 = 43	CES38 = 100	CES63 = 88	CES88 = 88
CES14 = 74	CES39 = 97	CES64 = 85	CES89 = 77
CES15 = 71	CES40 = 94	CES65 = 80	CES90 = 88
CES16 = 47	CES41 = 97	CES66 = 84	CES91 = 81
CES17 = 49	CES42 = 96	CES67 = 82	CES92 = 67
CES18 = 56	CES43 = 93	CES68 = 85	CES93 = 81
CES19 = 72	CES44 = 99	CES69 = 89	CES94 = 63
CES20 = 66	CES45 = 95	CES70 = 81	CES95 = 76
CES21 = 86	CES46 = 91	CES71 = 79	CES96 = 84
CES22 = 78	CES47 = 93	CES72 = 93	CES97 = 92
CES23 = 91	CES48 = 85	CES73 = 76	CES98 = 86
CES24 = 90	CES49 = 92	CES74 = 95	CES99 = 77
CES25 = 72	CES50 = 96	CES75 = 80	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)