

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049263

Luminaire Tested: **GALN-SA5C-850-U-RBC**

Issue Date: 07/10/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1049263  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA5C-850-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 5xLight Square PACKAGE  
80CRI 5000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (70) 5000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 23010.3 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 236  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049263  
CATALOG NUMBER: GALN-SA5C-850-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 115.2    | 0.0    | 115.2   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 22895.1  | 0.0    | 22895.1 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 23010.3  | 0.0    | 23010.3 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 9.0     | 0.0       |
| 10°-20°   | 50.6    | 0.2       |
| 20°-30°   | 545.3   | 2.4       |
| 30°-40°   | 1612.6  | 7.0       |
| 40°-50°   | 4805.9  | 20.9      |
| 50°-60°   | 7620.5  | 33.1      |
| 60°-70°   | 6361.3  | 27.6      |
| 70°-80°   | 1961.6  | 8.5       |
| 80°-90°   | 43.6    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 23010.3 | 100.0     |
| 0°-180°   | 23010.3 | 100.0     |



REPORT NUMBER: P1049263


CATALOG NUMBER: GALN-SA5C-850-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 583.7   | 2.5       |                         |      |          |
| FM   | (30°-60°)   | 13997.8 | 60.8      |                         |      |          |
| FH   | (60°-80°)   | 8279.8  | 36.0      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 33.7    | 0.1       |                         |      | G1/100   |
| BL   | (0°-30°)    | 21.2    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 41.2    | 0.2       | B0/220                  |      |          |
| BH   | (60°-80°)   | 43.0    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 9.9     | 0.0       |                         |      | G0/10    |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 100.9  | 100.9  | 100.9  | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 |
| 2.5°   | 92.2   | 92.2   | 92.2   | 92.2  | 90.4  | 90.4  | 88.7  | 88.7  | 86.9  | 86.9  |
| 5°     | 97.4   | 97.4   | 95.6   | 93.9  | 93.9  | 92.2  | 90.4  | 88.7  | 88.7  | 86.9  |
| 7.5°   | 106.1  | 104.3  | 102.6  | 100.9 | 97.4  | 95.6  | 92.2  | 90.4  | 88.7  | 85.2  |
| 10°    | 116.5  | 113.0  | 109.5  | 106.1 | 102.6 | 99.1  | 95.6  | 93.9  | 90.4  | 88.7  |
| 12.5°  | 130.4  | 125.2  | 118.2  | 113.0 | 109.5 | 104.3 | 100.9 | 97.4  | 92.2  | 88.7  |
| 15°    | 142.6  | 135.6  | 126.9  | 120.0 | 114.8 | 107.8 | 102.6 | 97.4  | 93.9  | 88.7  |
| 17.5°  | 160.0  | 147.8  | 133.9  | 125.2 | 118.2 | 109.5 | 100.9 | 95.6  | 90.4  | 83.5  |
| 20°    | 189.5  | 165.2  | 139.1  | 128.7 | 118.2 | 107.8 | 97.4  | 90.4  | 85.2  | 78.2  |
| 22.5°  | 236.5  | 194.8  | 153.0  | 137.4 | 123.5 | 107.8 | 93.9  | 86.9  | 80.0  | 73.0  |
| 25°    | 326.9  | 252.1  | 177.4  | 156.5 | 135.6 | 114.8 | 93.9  | 85.2  | 78.2  | 69.6  |
| 27.5°  | 434.7  | 323.4  | 210.4  | 180.8 | 153.0 | 123.5 | 93.9  | 83.5  | 74.8  | 64.3  |
| 30°    | 544.3  | 396.5  | 246.9  | 208.7 | 170.4 | 132.2 | 93.9  | 81.7  | 71.3  | 59.1  |
| 32.5°  | 648.6  | 464.3  | 278.2  | 233.0 | 187.8 | 140.8 | 95.6  | 81.7  | 67.8  | 53.9  |
| 35°    | 754.7  | 519.9  | 283.4  | 236.5 | 189.5 | 140.8 | 93.9  | 78.2  | 64.3  | 48.7  |
| 37.5°  | 890.3  | 582.5  | 273.0  | 226.1 | 180.8 | 133.9 | 88.7  | 74.8  | 60.9  | 45.2  |
| 40°    | 1095.5 | 686.9  | 278.2  | 229.5 | 180.8 | 132.2 | 83.5  | 69.6  | 57.4  | 43.5  |
| 42.5°  | 1474.6 | 888.6  | 300.8  | 245.2 | 189.5 | 132.2 | 76.5  | 64.3  | 53.9  | 41.7  |
| 45°    | 2549.2 | 1476.3 | 403.4  | 320.0 | 236.5 | 153.0 | 69.6  | 59.1  | 50.4  | 40.0  |
| 47.5°  | 4216.8 | 2470.9 | 725.1  | 559.9 | 396.5 | 231.3 | 67.8  | 59.1  | 50.4  | 40.0  |
| 50°    | 5381.8 | 3147.4 | 912.9  | 702.5 | 492.1 | 281.7 | 71.3  | 60.9  | 52.2  | 41.7  |
| 52.5°  | 5373.1 | 3196.0 | 1017.2 | 780.8 | 546.0 | 309.5 | 74.8  | 64.3  | 55.6  | 45.2  |
| 55°    | 4776.7 | 2907.4 | 1036.4 | 796.4 | 558.2 | 318.2 | 80.0  | 69.6  | 59.1  | 48.7  |
| 57.5°  | 3992.4 | 2469.2 | 945.9  | 732.1 | 519.9 | 306.0 | 92.2  | 80.0  | 69.6  | 57.4  |
| 60°    | 3157.8 | 1947.5 | 737.3  | 582.5 | 429.5 | 274.7 | 121.7 | 106.1 | 92.2  | 76.5  |
| 62.5°  | 2180.5 | 1412.0 | 643.4  | 516.4 | 391.2 | 264.3 | 139.1 | 123.5 | 109.5 | 93.9  |
| 65°    | 1542.4 | 1062.5 | 580.8  | 473.0 | 366.9 | 259.1 | 151.3 | 133.9 | 118.2 | 100.9 |
| 67.5°  | 1152.9 | 845.1  | 535.6  | 443.4 | 351.3 | 259.1 | 166.9 | 146.1 | 126.9 | 106.1 |
| 70°    | 883.3  | 693.8  | 502.5  | 427.8 | 354.7 | 280.0 | 205.2 | 175.6 | 147.8 | 118.2 |
| 72.5°  | 719.9  | 593.0  | 464.3  | 410.4 | 356.5 | 302.6 | 248.7 | 210.4 | 172.1 | 132.2 |
| 75°    | 596.4  | 507.8  | 419.1  | 373.9 | 330.4 | 285.2 | 240.0 | 205.2 | 172.1 | 137.4 |
| 77.5°  | 396.5  | 361.7  | 325.2  | 299.1 | 273.0 | 245.2 | 219.1 | 189.5 | 161.7 | 132.2 |
| 80°    | 139.1  | 133.9  | 128.7  | 139.1 | 149.5 | 160.0 | 170.4 | 149.5 | 130.4 | 109.5 |
| 82.5°  | 20.9   | 19.1   | 17.4   | 19.1  | 20.9  | 22.6  | 24.3  | 26.1  | 27.8  | 29.6  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 |
| 0.0 | 2.5°   | 85.2  | 85.2  | 83.5  | 83.5  | 83.5  | 81.7  | 81.7  | 80.0  | 80.0  | 80.0  |
| 0.0 | 5°     | 83.5  | 83.5  | 81.7  | 80.0  | 78.2  | 78.2  | 76.5  | 74.8  | 74.8  | 73.0  |
| 0.0 | 7.5°   | 81.7  | 80.0  | 78.2  | 76.5  | 74.8  | 73.0  | 71.3  | 69.6  | 69.6  | 67.8  |
| 0.0 | 10°    | 83.5  | 80.0  | 78.2  | 74.8  | 73.0  | 71.3  | 67.8  | 66.1  | 64.3  | 64.3  |
| 0.0 | 12.5°  | 80.0  | 78.2  | 74.8  | 71.3  | 69.6  | 66.1  | 64.3  | 60.9  | 59.1  | 59.1  |
| 0.0 | 15°    | 80.0  | 76.5  | 71.3  | 67.8  | 64.3  | 62.6  | 59.1  | 55.6  | 53.9  | 52.2  |
| 0.0 | 17.5°  | 74.8  | 71.3  | 66.1  | 62.6  | 59.1  | 55.6  | 52.2  | 48.7  | 46.9  | 45.2  |
| 0.0 | 20°    | 67.8  | 64.3  | 59.1  | 53.9  | 50.4  | 46.9  | 43.5  | 40.0  | 38.3  | 36.5  |
| 0.0 | 22.5°  | 60.9  | 57.4  | 52.2  | 46.9  | 43.5  | 40.0  | 34.8  | 31.3  | 29.6  | 26.1  |
| 0.0 | 25°    | 57.4  | 52.2  | 46.9  | 41.7  | 36.5  | 33.0  | 27.8  | 22.6  | 19.1  | 15.6  |
| 0.0 | 27.5°  | 48.7  | 43.5  | 38.3  | 33.0  | 27.8  | 22.6  | 17.4  | 12.2  | 8.7   | 7.0   |
| 0.0 | 30°    | 41.7  | 36.5  | 31.3  | 26.1  | 19.1  | 13.9  | 8.7   | 1.7   | 1.7   | 1.7   |
| 0.0 | 32.5°  | 34.8  | 29.6  | 22.6  | 17.4  | 13.9  | 8.7   | 5.2   | 0.0   | 0.0   | 0.0   |
| 0.0 | 35°    | 27.8  | 22.6  | 15.6  | 10.4  | 8.7   | 5.2   | 3.5   | 0.0   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 24.3  | 19.1  | 12.2  | 5.2   | 3.5   | 3.5   | 1.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 40°    | 22.6  | 15.6  | 8.7   | 1.7   | 1.7   | 1.7   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 22.6  | 15.6  | 7.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 22.6  | 15.6  | 7.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 22.6  | 15.6  | 7.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 24.3  | 17.4  | 8.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 27.8  | 20.9  | 13.9  | 7.0   | 5.2   | 3.5   | 1.7   | 0.0   | 0.0   | 0.0   |
| 0.0 | 55°    | 34.8  | 31.3  | 26.1  | 22.6  | 17.4  | 12.2  | 5.2   | 0.0   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 45.2  | 45.2  | 43.5  | 41.7  | 31.3  | 20.9  | 10.4  | 0.0   | 0.0   | 0.0   |
| 0.0 | 60°    | 60.9  | 60.9  | 60.9  | 60.9  | 45.2  | 31.3  | 15.6  | 0.0   | 0.0   | 0.0   |
| 0.0 | 62.5°  | 74.8  | 71.3  | 66.1  | 62.6  | 46.9  | 31.3  | 15.6  | 0.0   | 0.0   | 0.0   |
| 0.0 | 65°    | 74.8  | 67.8  | 59.1  | 50.4  | 38.3  | 26.1  | 12.2  | 0.0   | 0.0   | 0.0   |
| 0.0 | 67.5°  | 69.6  | 55.6  | 40.0  | 26.1  | 19.1  | 13.9  | 7.0   | 0.0   | 0.0   | 0.0   |
|     | 70°    | 69.6  | 48.7  | 27.8  | 7.0   | 5.2   | 3.5   | 1.7   | 0.0   | 0.0   | 0.0   |
|     | 72.5°  | 69.6  | 46.9  | 22.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 76.5  | 52.2  | 26.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 76.5  | 52.2  | 26.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 67.8  | 45.2  | 22.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 22.6  | 15.6  | 7.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 |
| 0.0   | 2.5°   | 78.2  | 78.2  | 78.2  | 76.5  | 76.5  | 76.5  | 76.5  | 74.8  | 74.8  | 74.8  |
| 0.0   | 5°     | 71.3  | 71.3  | 69.6  | 69.6  | 67.8  | 67.8  | 66.1  | 66.1  | 64.3  | 64.3  |
| 0.0   | 7.5°   | 66.1  | 64.3  | 64.3  | 62.6  | 60.9  | 60.9  | 59.1  | 59.1  | 57.4  | 55.6  |
| 0.0   | 10°    | 60.9  | 59.1  | 59.1  | 57.4  | 55.6  | 53.9  | 53.9  | 52.2  | 50.4  | 48.7  |
| 0.0   | 12.5°  | 55.6  | 53.9  | 52.2  | 50.4  | 48.7  | 46.9  | 46.9  | 45.2  | 43.5  | 41.7  |
| 0.0   | 15°    | 48.7  | 46.9  | 45.2  | 43.5  | 41.7  | 40.0  | 40.0  | 38.3  | 36.5  | 34.8  |
| 0.0   | 17.5°  | 41.7  | 40.0  | 40.0  | 38.3  | 36.5  | 34.8  | 33.0  | 29.6  | 27.8  | 26.1  |
| 0.0   | 20°    | 31.3  | 29.6  | 27.8  | 26.1  | 24.3  | 20.9  | 19.1  | 15.6  | 12.2  | 10.4  |
| 0.0   | 22.5°  | 20.9  | 17.4  | 15.6  | 12.2  | 8.7   | 7.0   | 5.2   | 1.7   | 0.0   | 0.0   |
| 0.0   | 25°    | 7.0   | 5.2   | 3.5   | 1.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9 | 100.9  | 100.9 |
| 0.0 | 2.5°   | 73.0  | 73.0  | 73.0  | 71.3  | 71.3  | 71.3  | 71.3  | 71.3  | 71.3   | 71.3  |
| 0.0 | 5°     | 62.6  | 62.6  | 62.6  | 60.9  | 60.9  | 59.1  | 59.1  | 59.1  | 57.4   | 57.4  |
| 0.0 | 7.5°   | 53.9  | 52.2  | 52.2  | 50.4  | 50.4  | 48.7  | 48.7  | 48.7  | 46.9   | 46.9  |
| 0.0 | 10°    | 45.2  | 43.5  | 43.5  | 41.7  | 41.7  | 40.0  | 40.0  | 38.3  | 38.3   | 36.5  |
| 0.0 | 12.5°  | 40.0  | 38.3  | 36.5  | 34.8  | 34.8  | 33.0  | 31.3  | 31.3  | 29.6   | 27.8  |
| 0.0 | 15°    | 31.3  | 29.6  | 27.8  | 26.1  | 24.3  | 22.6  | 20.9  | 20.9  | 19.1   | 17.4  |
| 0.0 | 17.5°  | 20.9  | 17.4  | 15.6  | 13.9  | 13.9  | 12.2  | 10.4  | 8.7   | 7.0    | 5.2   |
| 0.0 | 20°    | 5.2   | 3.5   | 1.7   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  |
| 0.0    | 2.5°   | 71.3  | 69.6   | 69.6  | 69.6   | 71.3  | 71.3   | 71.3  | 71.3   | 71.3  | 71.3   |
| 0.0    | 5°     | 57.4  | 55.6   | 55.6  | 55.6   | 55.6  | 55.6   | 55.6  | 55.6   | 55.6  | 55.6   |
| 0.0    | 7.5°   | 46.9  | 45.2   | 45.2  | 45.2   | 45.2  | 43.5   | 43.5  | 43.5   | 43.5  | 43.5   |
| 0.0    | 10°    | 36.5  | 34.8   | 34.8  | 34.8   | 34.8  | 33.0   | 33.0  | 33.0   | 33.0  | 33.0   |
| 0.0    | 12.5°  | 26.1  | 26.1   | 24.3  | 24.3   | 24.3  | 22.6   | 22.6  | 22.6   | 22.6  | 20.9   |
| 0.0    | 15°    | 15.6  | 13.9   | 12.2  | 12.2   | 12.2  | 10.4   | 10.4  | 10.4   | 10.4  | 8.7    |
| 0.0    | 17.5°  | 3.5   | 3.5    | 1.7   | 1.7    | 1.7   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 |
| 0.0  | 2.5°   | 73.0   | 73.0  | 74.8   | 74.8  | 76.5   | 80.0  | 81.7   | 83.5  | 86.9   | 90.4  |
| 0.0  | 5°     | 57.4   | 59.1  | 59.1   | 60.9  | 62.6   | 64.3  | 66.1   | 67.8  | 71.3   | 74.8  |
| 0.0  | 7.5°   | 45.2   | 45.2  | 46.9   | 46.9  | 48.7   | 52.2  | 53.9   | 55.6  | 59.1   | 64.3  |
| 0.0  | 10°    | 34.8   | 34.8  | 36.5   | 36.5  | 38.3   | 41.7  | 43.5   | 45.2  | 48.7   | 53.9  |
| 0.0  | 12.5°  | 22.6   | 24.3  | 24.3   | 26.1  | 27.8   | 31.3  | 33.0   | 34.8  | 38.3   | 41.7  |
| 0.0  | 15°    | 10.4   | 12.2  | 12.2   | 13.9  | 15.6   | 19.1  | 20.9   | 22.6  | 26.1   | 31.3  |
| 0.0  | 17.5°  | 1.7    | 1.7   | 3.5    | 3.5   | 5.2    | 7.0   | 8.7    | 10.4  | 15.6   | 19.1  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.5    | 7.0   |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 1.7   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

CATALOG NUMBER: GALN-SA5C-850-U-RBC

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  |
| 0.0    | 2.5°   | 95.6  | 99.1   | 102.6 | 106.1  | 109.5 | 113.0  | 114.8 | 118.2  | 120.0 | 121.7  |
| 0.0    | 5°     | 81.7  | 85.2   | 90.4  | 93.9   | 97.4  | 100.9  | 104.3 | 106.1  | 107.8 | 109.5  |
| 0.0    | 7.5°   | 71.3  | 74.8   | 80.0  | 83.5   | 86.9  | 90.4   | 93.9  | 97.4   | 99.1  | 100.9  |
| 0.0    | 10°    | 60.9  | 66.1   | 69.6  | 74.8   | 78.2  | 81.7   | 85.2  | 88.7   | 92.2  | 93.9   |
| 0.0    | 12.5°  | 48.7  | 53.9   | 59.1  | 62.6   | 67.8  | 73.0   | 76.5  | 80.0   | 83.5  | 86.9   |
| 0.0    | 15°    | 38.3  | 43.5   | 48.7  | 52.2   | 57.4  | 62.6   | 67.8  | 71.3   | 74.8  | 78.2   |
| 0.0    | 17.5°  | 27.8  | 33.0   | 38.3  | 41.7   | 46.9  | 52.2   | 55.6  | 60.9   | 64.3  | 67.8   |
| 0.0    | 20°    | 13.9  | 19.1   | 24.3  | 29.6   | 34.8  | 40.0   | 43.5  | 48.7   | 52.2  | 55.6   |
| 0.0    | 22.5°  | 1.7   | 7.0    | 12.2  | 15.6   | 20.9  | 26.1   | 29.6  | 34.8   | 38.3  | 41.7   |
| 0.0    | 25°    | 0.0   | 1.7    | 5.2   | 7.0    | 8.7   | 12.2   | 15.6  | 19.1   | 22.6  | 26.1   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.7    | 3.5   | 7.0    | 10.4  | 13.9   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.5    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.7    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.7    | 1.7   | 3.5    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 3.5    | 5.2   | 8.7    | 10.4  | 12.2   |
|        | 87.5°  | 0.0   | 1.7    | 3.5   | 5.2    | 7.0   | 10.4   | 13.9  | 17.4   | 19.1  | 20.9   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 100.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 121.7 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 111.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.6 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.4  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.7  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 81.7  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 73.0  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.1  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45.2  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17.4  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5.2   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.7   |        |      |        |      |        |      |        |      |        |      |        |
| 7.0   |        |      |        |      |        |      |        |      |        |      |        |
| 15.6  |        |      |        |      |        |      |        |      |        |      |        |
| 22.6  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 |
| 0.0  | 2.5°   | 123.5  | 123.5 | 123.5  | 123.5 | 121.7  | 121.7 | 121.7  | 120.0 | 120.0  | 118.2 |
| 0.0  | 5°     | 113.0  | 114.8 | 114.8  | 114.8 | 114.8  | 114.8 | 114.8  | 114.8 | 113.0  | 113.0 |
| 0.0  | 7.5°   | 104.3  | 106.1 | 107.8  | 107.8 | 109.5  | 109.5 | 109.5  | 107.8 | 107.8  | 106.1 |
| 0.0  | 10°    | 99.1   | 100.9 | 100.9  | 102.6 | 102.6  | 102.6 | 102.6  | 102.6 | 102.6  | 102.6 |
| 0.0  | 12.5°  | 92.2   | 93.9  | 95.6   | 95.6  | 97.4   | 97.4  | 97.4   | 97.4  | 95.6   | 95.6  |
| 0.0  | 15°    | 83.5   | 86.9  | 88.7   | 90.4  | 90.4   | 92.2  | 92.2   | 92.2  | 92.2   | 92.2  |
| 0.0  | 17.5°  | 76.5   | 80.0  | 81.7   | 83.5  | 83.5   | 85.2  | 85.2   | 86.9  | 86.9   | 86.9  |
| 0.0  | 20°    | 62.6   | 66.1  | 67.8   | 71.3  | 73.0   | 74.8  | 76.5   | 78.2  | 78.2   | 80.0  |
| 0.0  | 22.5°  | 48.7   | 52.2  | 53.9   | 57.4  | 59.1   | 60.9  | 62.6   | 64.3  | 66.1   | 67.8  |
| 0.0  | 25°    | 34.8   | 38.3  | 40.0   | 43.5  | 45.2   | 46.9  | 48.7   | 50.4  | 50.4   | 52.2  |
| 0.0  | 27.5°  | 19.1   | 22.6  | 26.1   | 27.8  | 31.3   | 33.0  | 34.8   | 36.5  | 38.3   | 40.0  |
| 0.0  | 30°    | 8.7    | 10.4  | 12.2   | 15.6  | 17.4   | 19.1  | 20.9   | 24.3  | 26.1   | 27.8  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.7    | 5.2   | 7.0    | 8.7   | 10.4   | 12.2  | 12.2   | 13.9  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.7    | 3.5   | 5.2    | 7.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.5    | 3.5   | 3.5    | 5.2   | 5.2    | 5.2   | 5.2    | 5.2   | 5.2    | 5.2   |
|      | 82.5°  | 8.7    | 10.4  | 12.2   | 12.2  | 13.9   | 13.9  | 13.9   | 13.9  | 12.2   | 12.2  |
|      | 85°    | 17.4   | 19.1  | 20.9   | 20.9  | 22.6   | 22.6  | 22.6   | 22.6  | 22.6   | 22.6  |
|      | 87.5°  | 24.3   | 26.1  | 27.8   | 27.8  | 29.6   | 29.6  | 29.6   | 29.6  | 29.6   | 29.6  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 100.9  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118.2  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 113.0  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106.1  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.6  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 95.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.2   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 86.9   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 78.2   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 67.8   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 53.9   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 41.7   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29.6   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 17.4   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 10.4   | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.5    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.5    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.7    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 5.2    |        |        |      |        |      |        |      |        |      |        |      |
| 12.2   |        |        |      |        |      |        |      |        |      |        |      |
| 22.6   |        |        |      |        |      |        |      |        |      |        |      |
| 29.6   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  |
| 0.0    | 2.5°   | 116.5 | 116.5  | 114.8 | 114.8  | 114.8 | 114.8  | 114.8 | 116.5  | 118.2 | 118.2  |
| 0.0    | 5°     | 111.3 | 111.3  | 109.5 | 109.5  | 109.5 | 111.3  | 111.3 | 113.0  | 114.8 | 116.5  |
| 0.0    | 7.5°   | 106.1 | 104.3  | 104.3 | 106.1  | 106.1 | 107.8  | 107.8 | 109.5  | 111.3 | 113.0  |
| 0.0    | 10°    | 102.6 | 100.9  | 100.9 | 100.9  | 102.6 | 102.6  | 104.3 | 106.1  | 107.8 | 109.5  |
| 0.0    | 12.5°  | 95.6  | 95.6   | 95.6  | 95.6   | 97.4  | 97.4   | 99.1  | 100.9  | 104.3 | 106.1  |
| 0.0    | 15°    | 92.2  | 90.4   | 90.4  | 90.4   | 90.4  | 92.2   | 92.2  | 95.6   | 99.1  | 100.9  |
| 0.0    | 17.5°  | 85.2  | 85.2   | 83.5  | 83.5   | 85.2  | 85.2   | 86.9  | 90.4   | 93.9  | 95.6   |
| 0.0    | 20°    | 78.2  | 76.5   | 74.8  | 74.8   | 76.5  | 76.5   | 78.2  | 81.7   | 85.2  | 86.9   |
| 0.0    | 22.5°  | 67.8  | 66.1   | 66.1  | 66.1   | 66.1  | 67.8   | 67.8  | 71.3   | 76.5  | 80.0   |
| 0.0    | 25°    | 53.9  | 55.6   | 55.6  | 57.4   | 57.4  | 59.1   | 60.9  | 64.3   | 69.6  | 73.0   |
| 0.0    | 27.5°  | 41.7  | 43.5   | 43.5  | 46.9   | 48.7  | 50.4   | 52.2  | 57.4   | 62.6  | 66.1   |
| 0.0    | 30°    | 31.3  | 33.0   | 34.8  | 36.5   | 40.0  | 43.5   | 46.9  | 52.2   | 57.4  | 60.9   |
| 0.0    | 32.5°  | 19.1  | 22.6   | 24.3  | 27.8   | 31.3  | 34.8   | 38.3  | 43.5   | 50.4  | 55.6   |
| 0.0    | 35°    | 13.9  | 15.6   | 19.1  | 20.9   | 24.3  | 27.8   | 31.3  | 38.3   | 43.5  | 50.4   |
| 0.0    | 37.5°  | 7.0   | 10.4   | 13.9  | 17.4   | 20.9  | 24.3   | 27.8  | 34.8   | 41.7  | 46.9   |
| 0.0    | 40°    | 5.2   | 8.7    | 10.4  | 13.9   | 19.1  | 22.6   | 26.1  | 33.0   | 40.0  | 46.9   |
| 0.0    | 42.5°  | 3.5   | 5.2    | 7.0   | 12.2   | 15.6  | 20.9   | 26.1  | 33.0   | 40.0  | 46.9   |
| 0.0    | 45°    | 3.5   | 3.5    | 5.2   | 10.4   | 15.6  | 22.6   | 27.8  | 34.8   | 40.0  | 46.9   |
| 0.0    | 47.5°  | 3.5   | 5.2    | 7.0   | 13.9   | 17.4  | 22.6   | 27.8  | 33.0   | 40.0  | 45.2   |
| 0.0    | 50°    | 5.2   | 7.0    | 8.7   | 15.6   | 19.1  | 24.3   | 27.8  | 34.8   | 40.0  | 46.9   |
| 0.0    | 52.5°  | 3.5   | 5.2    | 7.0   | 13.9   | 19.1  | 26.1   | 31.3  | 38.3   | 45.2  | 50.4   |
| 0.0    | 55°    | 1.7   | 1.7    | 1.7   | 10.4   | 20.9  | 29.6   | 40.0  | 45.2   | 52.2  | 57.4   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 7.0    | 20.9  | 33.0   | 45.2  | 52.2   | 59.1  | 64.3   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 7.0    | 20.9  | 33.0   | 45.2  | 53.9   | 62.6  | 71.3   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 7.0    | 17.4  | 27.8   | 38.3  | 52.2   | 67.8  | 81.7   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 5.2    | 13.9  | 22.6   | 31.3  | 52.2   | 73.0  | 92.2   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 5.2    | 13.9  | 20.9   | 29.6  | 52.2   | 73.0  | 95.6   |
|        | 70°    | 0.0   | 0.0    | 0.0   | 5.2    | 13.9  | 22.6   | 31.3  | 52.2   | 73.0  | 93.9   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 5.2    | 15.6  | 24.3   | 34.8  | 52.2   | 69.6  | 86.9   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 7.0    | 15.6  | 26.1   | 36.5  | 52.2   | 67.8  | 81.7   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 5.2    | 15.6  | 24.3   | 34.8  | 50.4   | 66.1  | 80.0   |
|        | 80°    | 5.2   | 3.5    | 3.5   | 8.7    | 15.6  | 22.6   | 29.6  | 45.2   | 62.6  | 78.2   |
|        | 82.5°  | 10.4  | 10.4   | 8.7   | 12.2   | 15.6  | 20.9   | 26.1  | 40.0   | 55.6  | 69.6   |
|        | 85°    | 20.9  | 20.9   | 19.1  | 20.9   | 20.9  | 22.6   | 24.3  | 31.3   | 38.3  | 45.2   |
|        | 87.5°  | 27.8  | 27.8   | 26.1  | 26.1   | 26.1  | 24.3   | 24.3  | 24.3   | 24.3  | 22.6   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 100.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 120.0 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 118.2 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.8 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 111.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.8 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 104.3 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 99.1  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90.4  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.5  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 76.5  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.3  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66.1  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 60.9  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.6  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.9  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.9  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.9  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.2  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.4  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.2  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.4  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.6  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71.3  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95.6  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 113.0 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 116.5 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.8 |        |      |        |      |        |      |        |      |        |      |        |
| 104.3 |        |      |        |      |        |      |        |      |        |      |        |
| 97.4  |        |      |        |      |        |      |        |      |        |      |        |
| 95.6  |        |      |        |      |        |      |        |      |        |      |        |
| 93.9  |        |      |        |      |        |      |        |      |        |      |        |
| 83.5  |        |      |        |      |        |      |        |      |        |      |        |
| 52.2  |        |      |        |      |        |      |        |      |        |      |        |
| 22.6  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9 | 100.9  | 100.9  |
| 0.0  | 2.5°   | 121.7  | 123.5 | 123.5  | 125.2 | 126.9  | 128.7 | 128.7  | 130.4 | 130.4  | 130.4  |
| 0.0  | 5°     | 120.0  | 123.5 | 125.2  | 126.9 | 128.7  | 130.4 | 132.2  | 133.9 | 135.6  | 135.6  |
| 0.0  | 7.5°   | 118.2  | 120.0 | 123.5  | 125.2 | 128.7  | 130.4 | 133.9  | 135.6 | 137.4  | 139.1  |
| 0.0  | 10°    | 114.8  | 118.2 | 121.7  | 125.2 | 128.7  | 132.2 | 135.6  | 139.1 | 142.6  | 144.3  |
| 0.0  | 12.5°  | 111.3  | 116.5 | 120.0  | 123.5 | 128.7  | 133.9 | 137.4  | 142.6 | 146.1  | 149.5  |
| 0.0  | 15°    | 109.5  | 113.0 | 118.2  | 121.7 | 128.7  | 135.6 | 140.8  | 147.8 | 154.8  | 160.0  |
| 0.0  | 17.5°  | 104.3  | 111.3 | 116.5  | 121.7 | 128.7  | 137.4 | 144.3  | 151.3 | 161.7  | 172.1  |
| 0.0  | 20°    | 97.4   | 102.6 | 109.5  | 114.8 | 125.2  | 133.9 | 144.3  | 153.0 | 168.7  | 184.3  |
| 0.0  | 22.5°  | 90.4   | 97.4  | 102.6  | 109.5 | 121.7  | 132.2 | 144.3  | 154.8 | 180.8  | 205.2  |
| 0.0  | 25°    | 83.5   | 92.2  | 99.1   | 106.1 | 120.0  | 133.9 | 147.8  | 161.7 | 205.2  | 248.7  |
| 0.0  | 27.5°  | 80.0   | 86.9  | 95.6   | 102.6 | 120.0  | 139.1 | 156.5  | 173.9 | 243.4  | 311.3  |
| 0.0  | 30°    | 74.8   | 83.5  | 90.4   | 99.1  | 121.7  | 144.3 | 166.9  | 189.5 | 295.6  | 401.7  |
| 0.0  | 32.5°  | 69.6   | 78.2  | 86.9   | 95.6  | 125.2  | 154.8 | 182.6  | 212.1 | 351.3  | 488.6  |
| 0.0  | 35°    | 64.3   | 74.8  | 83.5   | 92.2  | 130.4  | 170.4 | 208.7  | 246.9 | 401.7  | 554.7  |
| 0.0  | 37.5°  | 62.6   | 73.0  | 81.7   | 90.4  | 132.2  | 172.1 | 213.9  | 253.9 | 406.9  | 559.9  |
| 0.0  | 40°    | 64.3   | 73.0  | 83.5   | 92.2  | 126.9  | 161.7 | 194.8  | 229.5 | 389.5  | 547.7  |
| 0.0  | 42.5°  | 64.3   | 74.8  | 85.2   | 95.6  | 123.5  | 151.3 | 179.1  | 206.9 | 384.3  | 561.7  |
| 0.0  | 45°    | 62.6   | 73.0  | 83.5   | 93.9  | 120.0  | 144.3 | 170.4  | 194.8 | 415.6  | 634.7  |
| 0.0  | 47.5°  | 60.9   | 71.3  | 81.7   | 92.2  | 118.2  | 144.3 | 170.4  | 196.5 | 537.3  | 876.4  |
| 0.0  | 50°    | 60.9   | 71.3  | 80.0   | 88.7  | 120.0  | 153.0 | 184.3  | 215.6 | 782.5  | 1347.6 |
| 0.0  | 52.5°  | 64.3   | 73.0  | 80.0   | 86.9  | 123.5  | 161.7 | 198.2  | 234.7 | 994.6  | 1752.8 |
| 0.0  | 55°    | 69.6   | 74.8  | 81.7   | 86.9  | 132.2  | 175.6 | 220.8  | 264.3 | 1059.0 | 1853.6 |
| 0.0  | 57.5°  | 76.5   | 81.7  | 86.9   | 92.2  | 147.8  | 203.4 | 257.4  | 313.0 | 1064.2 | 1813.6 |
| 0.0  | 60°    | 85.2   | 92.2  | 97.4   | 102.6 | 161.7  | 222.6 | 281.7  | 340.8 | 963.3  | 1584.1 |
| 0.0  | 62.5°  | 104.3  | 113.0 | 120.0  | 128.7 | 186.1  | 241.7 | 299.1  | 354.7 | 799.9  | 1245.0 |
| 0.0  | 65°    | 120.0  | 126.9 | 133.9  | 140.8 | 196.5  | 253.9 | 309.5  | 365.2 | 678.2  | 991.2  |
| 0.0  | 67.5°  | 123.5  | 130.4 | 135.6  | 142.6 | 200.0  | 257.4 | 313.0  | 370.4 | 580.8  | 789.4  |
|      | 70°    | 125.2  | 133.9 | 144.3  | 153.0 | 212.1  | 271.3 | 328.6  | 387.8 | 514.7  | 641.6  |
|      | 72.5°  | 120.0  | 137.4 | 153.0  | 168.7 | 224.3  | 278.2 | 333.9  | 387.8 | 478.2  | 568.6  |
|      | 75°    | 120.0  | 144.3 | 166.9  | 189.5 | 231.3  | 271.3 | 313.0  | 353.0 | 422.5  | 492.1  |
|      | 77.5°  | 126.9  | 158.2 | 189.5  | 220.8 | 245.2  | 267.8 | 292.1  | 314.7 | 359.9  | 405.2  |
|      | 80°    | 126.9  | 160.0 | 191.3  | 224.3 | 234.7  | 246.9 | 257.4  | 267.8 | 273.0  | 278.2  |
|      | 82.5°  | 109.5  | 135.6 | 161.7  | 187.8 | 175.6  | 163.5 | 151.3  | 139.1 | 130.4  | 120.0  |
|      | 85°    | 55.6   | 60.9  | 64.3   | 67.8  | 62.6   | 57.4  | 52.2   | 46.9  | 43.5   | 38.3   |
|      | 87.5°  | 22.6   | 22.6  | 20.9   | 20.9  | 20.9   | 20.9  | 19.1   | 19.1  | 19.1   | 19.1   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 100.9  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130.4  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 135.6  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140.8  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.8  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 154.8  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 168.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 186.1  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 213.9  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 273.0  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 370.4  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 514.7  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 697.3  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 871.2  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 989.4  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1078.1 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1166.8 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1340.7 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1688.4 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2573.5 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3942.0 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4962.7 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5075.8 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4580.2 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3915.9 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3060.4 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2312.7 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1707.6 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1208.5 |        |        |      |        |      |        |      |        |      |        |      |
| 899.0  |        |        |      |        |      |        |      |        |      |        |      |
| 653.8  |        |        |      |        |      |        |      |        |      |        |      |
| 492.1  |        |        |      |        |      |        |      |        |      |        |      |
| 276.5  |        |        |      |        |      |        |      |        |      |        |      |
| 125.2  |        |        |      |        |      |        |      |        |      |        |      |
| 36.5   |        |        |      |        |      |        |      |        |      |        |      |
| 17.4   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 100.9  | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   |
| 0.0    | 2.5°   | 130.4  | 128.7   | 128.7   | 126.9   | 125.2   | 123.5   | 121.7   | 120.0   | 118.2   | 116.5   |
| 0.0    | 5°     | 135.6  | 135.6   | 135.6   | 133.9   | 133.9   | 132.2   | 132.2   | 130.4   | 128.7   | 126.9   |
| 0.0    | 7.5°   | 140.8  | 142.6   | 142.6   | 144.3   | 144.3   | 144.3   | 144.3   | 142.6   | 142.6   | 142.6   |
| 0.0    | 10°    | 149.5  | 151.3   | 153.0   | 154.8   | 156.5   | 158.2   | 158.2   | 160.0   | 160.0   | 160.0   |
| 0.0    | 12.5°  | 160.0  | 165.2   | 168.7   | 173.9   | 177.4   | 182.6   | 186.1   | 191.3   | 194.8   | 198.2   |
| 0.0    | 15°    | 175.6  | 184.3   | 194.8   | 203.4   | 212.1   | 224.3   | 238.2   | 250.4   | 262.6   | 281.7   |
| 0.0    | 17.5°  | 198.2  | 226.1   | 253.9   | 280.0   | 307.8   | 368.6   | 429.5   | 488.6   | 549.5   | 638.2   |
| 0.0    | 20°    | 241.7  | 325.2   | 406.9   | 490.4   | 572.1   | 786.0   | 998.1   | 1212.0  | 1424.1  | 1651.9  |
| 0.0    | 22.5°  | 339.1  | 544.3   | 749.5   | 954.6   | 1159.8  | 1606.7  | 2051.9  | 2498.8  | 2943.9  | 3467.3  |
| 0.0    | 25°    | 492.1  | 869.4   | 1246.8  | 1622.4  | 1999.7  | 2698.7  | 3399.5  | 4098.5  | 4797.5  | 5477.4  |
| 0.0    | 27.5°  | 716.4  | 1293.7  | 1871.0  | 2446.6  | 3023.9  | 3971.6  | 4921.0  | 5868.7  | 6816.4  | 7585.0  |
| 0.0    | 30°    | 992.9  | 1775.4  | 2557.9  | 3340.4  | 4122.9  | 5201.0  | 6279.1  | 7355.4  | 8433.5  | 9273.4  |
| 0.0    | 32.5°  | 1253.7 | 2211.8  | 3170.0  | 4126.3  | 5084.5  | 6312.1  | 7541.5  | 8769.1  | 9996.8  | 10914.9 |
| 0.0    | 35°    | 1424.1 | 2582.2  | 3742.1  | 4900.1  | 6058.2  | 7386.7  | 8715.2  | 10042.0 | 11370.5 | 12419.0 |
| 0.0    | 37.5°  | 1594.5 | 2931.7  | 4267.2  | 5604.4  | 6939.8  | 8398.7  | 9857.7  | 11316.6 | 12775.5 | 14070.9 |
| 0.0    | 40°    | 1785.8 | 3354.3  | 4921.0  | 6489.5  | 8056.2  | 9784.6  | 11511.3 | 13239.8 | 14966.5 | 16794.0 |
| 0.0    | 42.5°  | 2117.9 | 4055.0  | 5993.9  | 7931.0  | 9868.1  | 12154.7 | 14441.3 | 16726.2 | 19012.8 | 21621.1 |
| 0.0    | 45°    | 2742.2 | 5472.2  | 8204.0  | 10934.0 | 13664.0 | 16693.2 | 19724.0 | 22753.1 | 25782.2 | 29253.0 |
| 0.0    | 47.5°  | 4270.7 | 8026.6  | 11780.9 | 15536.8 | 19291.0 | 22561.9 | 25830.9 | 29101.7 | 32370.8 | 35827.7 |
| 0.0    | 50°    | 6534.7 | 10906.2 | 15277.7 | 19647.5 | 24019.0 | 26978.6 | 29936.4 | 32896.0 | 35853.8 | 39142.0 |
| 0.0    | 52.5°  | 8172.7 | 12726.8 | 17282.6 | 21836.7 | 26390.8 | 29061.8 | 31734.4 | 34405.3 | 37076.2 | 40148.8 |
| 0.0    | 55°    | 8296.2 | 12824.2 | 17353.9 | 21882.0 | 26410.0 | 29093.1 | 31776.1 | 34459.2 | 37142.3 | 40399.2 |
| 0.0    | 57.5°  | 7345.0 | 11836.5 | 16326.3 | 20817.8 | 25307.5 | 28362.7 | 31416.2 | 34471.4 | 37524.8 | 41046.1 |
| 0.0    | 60°    | 6247.8 | 10741.0 | 15232.5 | 19725.8 | 24217.3 | 27736.7 | 31257.9 | 34777.4 | 38296.9 | 41595.5 |
| 0.0    | 62.5°  | 4874.1 | 9496.0  | 14119.6 | 18741.6 | 23363.5 | 26936.9 | 30510.2 | 34081.9 | 37655.3 | 40129.7 |
| 0.0    | 65°    | 3632.5 | 8120.5  | 12608.6 | 17094.8 | 21582.9 | 24445.0 | 27307.2 | 30167.7 | 33029.9 | 34561.8 |
| 0.0    | 67.5°  | 2625.7 | 6496.4  | 10365.4 | 14236.1 | 18105.1 | 20153.5 | 22201.9 | 24248.6 | 26296.9 | 27468.9 |
|        | 70°    | 1775.4 | 4456.7  | 7136.3  | 9817.7  | 12497.3 | 14180.5 | 15865.5 | 17548.7 | 19231.9 | 20814.3 |
|        | 72.5°  | 1229.4 | 2735.2  | 4242.8  | 5748.7  | 7254.6  | 8948.2  | 10640.2 | 12333.8 | 14025.7 | 15700.3 |
|        | 75°    | 815.5  | 1500.6  | 2187.5  | 2872.6  | 3557.7  | 4811.5  | 6066.9  | 7320.6  | 8574.4  | 9572.5  |
|        | 77.5°  | 579.0  | 784.2   | 991.2   | 1196.3  | 1401.5  | 1636.3  | 1872.8  | 2107.5  | 2342.3  | 2698.7  |
|        | 80°    | 274.7  | 300.8   | 326.9   | 351.3   | 377.3   | 462.5   | 547.7   | 632.9   | 718.2   | 808.6   |
|        | 82.5°  | 130.4  | 140.8   | 151.3   | 160.0   | 170.4   | 179.1   | 187.8   | 196.5   | 205.2   | 196.5   |
|        | 85°    | 34.8   | 34.8    | 36.5    | 36.5    | 36.5    | 36.5    | 36.5    | 36.5    | 36.5    | 34.8    |
|        | 87.5°  | 15.6   | 15.6    | 15.6    | 15.6    | 15.6    | 15.6    | 15.6    | 13.9    | 13.9    | 12.2    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 100.9   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 114.8   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 125.2   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 140.8   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 161.7   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 200.0   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 302.6   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 725.1   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1881.5  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3990.7  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6157.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8353.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10115.0 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11834.8 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13467.6 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15368.1 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18621.6 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24229.4 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32723.8 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39284.6 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42430.2 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43221.4 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 43657.8 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44567.3 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44892.4 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 42605.8 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 36095.5 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28642.7 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22394.9 |        |      |        |      |        |      |        |      |        |      |        |
| 17374.8 |        |      |        |      |        |      |        |      |        |      |        |
| 10570.6 |        |      |        |      |        |      |        |      |        |      |        |
| 3055.2  |        |      |        |      |        |      |        |      |        |      |        |
| 899.0   |        |      |        |      |        |      |        |      |        |      |        |
| 186.1   |        |      |        |      |        |      |        |      |        |      |        |
| 33.0    |        |      |        |      |        |      |        |      |        |      |        |
| 12.2    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   |
| 0.0  | 2.5°   | 113.0   | 111.3   | 109.5   | 107.8   | 106.1   | 102.6   | 102.6   | 100.9   | 100.9   |
| 0.0  | 5°     | 123.5   | 121.7   | 120.0   | 118.2   | 118.2   | 116.5   | 114.8   | 114.8   | 113.0   |
| 0.0  | 7.5°   | 140.8   | 139.1   | 137.4   | 135.6   | 135.6   | 133.9   | 133.9   | 132.2   | 132.2   |
| 0.0  | 10°    | 161.7   | 161.7   | 161.7   | 161.7   | 161.7   | 160.0   | 160.0   | 160.0   | 158.2   |
| 0.0  | 12.5°  | 203.4   | 205.2   | 208.7   | 212.1   | 217.4   | 217.4   | 217.4   | 215.6   | 215.6   |
| 0.0  | 15°    | 321.7   | 340.8   | 354.7   | 368.6   | 380.8   | 408.6   | 405.2   | 399.9   | 396.5   |
| 0.0  | 17.5°  | 813.8   | 900.7   | 947.7   | 992.9   | 1039.8  | 1168.5  | 1147.7  | 1126.8  | 1107.7  |
| 0.0  | 20°    | 2109.3  | 2337.0  | 2488.3  | 2639.6  | 2792.6  | 3034.3  | 2975.2  | 2916.1  | 2857.0  |
| 0.0  | 22.5°  | 4512.4  | 5035.8  | 5263.6  | 5491.4  | 5717.4  | 6009.5  | 5820.0  | 5630.5  | 5442.7  |
| 0.0  | 25°    | 6835.5  | 7515.4  | 7899.7  | 8284.0  | 8666.5  | 8833.5  | 8586.5  | 8337.9  | 8091.0  |
| 0.0  | 27.5°  | 9122.1  | 9890.7  | 10229.8 | 10567.1 | 10906.2 | 11255.7 | 10949.7 | 10641.9 | 10335.8 |
| 0.0  | 30°    | 10954.9 | 11794.8 | 12161.7 | 12526.8 | 12893.7 | 13137.2 | 12820.7 | 12502.5 | 12186.0 |
| 0.0  | 32.5°  | 12752.9 | 13671.0 | 14072.7 | 14474.4 | 14874.3 | 15223.8 | 14834.3 | 14443.1 | 14053.6 |
| 0.0  | 35°    | 14514.4 | 15562.9 | 16115.9 | 16668.8 | 17221.8 | 17546.9 | 17084.4 | 16620.1 | 16157.6 |
| 0.0  | 37.5°  | 16663.6 | 17959.1 | 18578.1 | 19197.1 | 19816.2 | 20409.1 | 19899.6 | 19388.4 | 18878.9 |
| 0.0  | 40°    | 20449.1 | 22276.7 | 23226.1 | 24177.3 | 25126.7 | 25891.8 | 25248.4 | 24605.0 | 23961.6 |
| 0.0  | 42.5°  | 26837.7 | 29446.0 | 30811.1 | 32174.3 | 33539.3 | 34733.9 | 34057.5 | 33381.1 | 32704.7 |
| 0.0  | 45°    | 36194.6 | 39665.4 | 41329.5 | 42991.8 | 44655.9 | 45528.9 | 44555.1 | 43579.6 | 42605.8 |
| 0.0  | 47.5°  | 42739.7 | 46196.6 | 47678.1 | 49159.6 | 50641.1 | 51637.5 | 50446.4 | 49255.3 | 48065.9 |
| 0.0  | 50°    | 45716.7 | 49004.9 | 50491.6 | 51976.6 | 53463.3 | 54254.5 | 52879.1 | 51501.9 | 50126.4 |
| 0.0  | 52.5°  | 46292.2 | 49364.8 | 51138.5 | 52913.8 | 54687.5 | 55744.7 | 54120.6 | 52494.8 | 50870.7 |
| 0.0  | 55°    | 46914.7 | 50171.6 | 52228.7 | 54287.6 | 56344.6 | 57808.8 | 55972.5 | 54134.5 | 52298.3 |
| 0.0  | 57.5°  | 48086.7 | 51608.0 | 53659.8 | 55710.0 | 57761.8 | 59005.1 | 57163.6 | 55320.4 | 53479.0 |
| 0.0  | 60°    | 48191.1 | 51488.0 | 53251.2 | 55016.1 | 56779.4 | 57561.8 | 55800.4 | 54037.2 | 52275.7 |
| 0.0  | 62.5°  | 45080.2 | 47554.6 | 48778.8 | 50003.0 | 51227.1 | 52077.4 | 50239.5 | 48399.7 | 46561.7 |
| 0.0  | 65°    | 37627.4 | 39159.4 | 40134.9 | 41110.4 | 42085.9 | 43099.7 | 41416.4 | 39733.2 | 38050.0 |
| 0.0  | 67.5°  | 29814.7 | 30986.7 | 32271.7 | 33556.7 | 34841.8 | 35925.1 | 34577.5 | 33228.1 | 31880.5 |
|      | 70°    | 23977.3 | 25557.9 | 27002.9 | 28447.9 | 29892.9 | 30779.8 | 29426.9 | 28072.3 | 26719.5 |
|      | 72.5°  | 19049.3 | 20723.9 | 21930.6 | 23135.7 | 24342.5 | 24559.8 | 23565.2 | 22570.5 | 21577.7 |
|      | 75°    | 11567.0 | 12565.1 | 12589.4 | 12612.0 | 12636.4 | 12843.3 | 12019.1 | 11194.9 | 10372.4 |
|      | 77.5°  | 3411.7  | 3768.1  | 4062.0  | 4354.1  | 4648.0  | 5002.7  | 4700.2  | 4395.9  | 4093.3  |
|      | 80°    | 987.7   | 1078.1  | 1154.6  | 1229.4  | 1305.9  | 1260.7  | 1189.4  | 1118.1  | 1046.8  |
|      | 82.5°  | 177.4   | 166.9   | 165.2   | 163.5   | 163.5   | 154.8   | 140.8   | 126.9   | 113.0   |
|      | 85°    | 31.3    | 29.6    | 27.8    | 26.1    | 24.3    | 22.6    | 19.1    | 17.4    | 13.9    |
|      | 87.5°  | 10.4    | 8.7     | 7.0     | 5.2     | 5.2     | 1.7     | 1.7     | 1.7     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   | 100.9   |
| 0.0  | 0.0    | 2.5°   | 99.1    | 97.4    | 97.4    | 97.4    | 97.4    | 95.6    | 95.6    | 95.6    | 95.6    |
| 0.0  | 0.0    | 5°     | 109.5   | 109.5   | 107.8   | 107.8   | 106.1   | 106.1   | 104.3   | 104.3   | 102.6   |
| 0.0  | 0.0    | 7.5°   | 128.7   | 126.9   | 125.2   | 123.5   | 121.7   | 118.2   | 116.5   | 114.8   | 114.8   |
| 0.0  | 0.0    | 10°    | 154.8   | 151.3   | 149.5   | 146.1   | 144.3   | 140.8   | 137.4   | 133.9   | 130.4   |
| 0.0  | 0.0    | 12.5°  | 203.4   | 196.5   | 191.3   | 184.3   | 177.4   | 172.1   | 165.2   | 160.0   | 153.0   |
| 0.0  | 0.0    | 15°    | 353.0   | 335.6   | 316.5   | 293.9   | 269.5   | 246.9   | 222.6   | 208.7   | 193.0   |
| 0.0  | 0.0    | 17.5°  | 902.5   | 812.1   | 719.9   | 645.1   | 570.3   | 497.3   | 422.5   | 368.6   | 314.7   |
| 0.0  | 0.0    | 20°    | 2297.0  | 2046.7  | 1796.3  | 1549.3  | 1300.7  | 1053.8  | 805.1   | 679.9   | 554.7   |
| 0.0  | 0.0    | 22.5°  | 4322.8  | 3858.6  | 3392.5  | 2942.2  | 2490.1  | 2039.7  | 1589.3  | 1305.9  | 1024.2  |
| 0.0  | 0.0    | 25°    | 6672.0  | 6087.8  | 5503.5  | 4762.8  | 4020.3  | 3279.5  | 2538.8  | 2078.0  | 1617.2  |
| 0.0  | 0.0    | 27.5°  | 8682.2  | 8009.2  | 7336.3  | 6435.6  | 5534.8  | 4634.1  | 3733.4  | 3046.5  | 2361.4  |
| 0.0  | 0.0    | 30°    | 10422.8 | 9699.4  | 8976.1  | 7927.5  | 6879.0  | 5830.4  | 4781.9  | 3922.9  | 3063.9  |
| 0.0  | 0.0    | 32.5°  | 11932.1 | 11066.2 | 10200.2 | 9118.6  | 8037.1  | 6955.5  | 5873.9  | 4820.2  | 3766.4  |
| 0.0  | 0.0    | 35°    | 13672.7 | 12662.5 | 11650.4 | 10450.6 | 9249.1  | 8049.2  | 6849.4  | 5660.0  | 4468.9  |
| 0.0  | 0.0    | 37.5°  | 15884.6 | 14644.8 | 13403.2 | 12066.0 | 10728.8 | 9393.4  | 8056.2  | 6696.4  | 5336.6  |
| 0.0  | 0.0    | 40°    | 20118.7 | 18519.0 | 16919.2 | 15220.3 | 13519.7 | 11820.8 | 10122.0 | 8452.7  | 6783.3  |
| 0.0  | 0.0    | 42.5°  | 27705.4 | 25544.0 | 23382.6 | 21122.1 | 18859.8 | 16599.3 | 14337.0 | 11982.6 | 9626.4  |
| 0.0  | 0.0    | 45°    | 36267.6 | 33586.3 | 30903.2 | 28366.2 | 25827.5 | 23290.4 | 20753.4 | 17522.6 | 14291.8 |
| 0.0  | 0.0    | 47.5°  | 41082.6 | 38187.3 | 35292.1 | 32890.7 | 30489.4 | 28088.0 | 25686.6 | 22203.6 | 18720.7 |
| 0.0  | 0.0    | 50°    | 42854.5 | 39907.1 | 36959.7 | 34749.6 | 32537.8 | 30327.6 | 28115.8 | 24627.6 | 21137.7 |
| 0.0  | 0.0    | 52.5°  | 43231.8 | 40225.3 | 37218.8 | 34994.8 | 32770.8 | 30548.5 | 28324.5 | 24858.9 | 21393.3 |
| 0.0  | 0.0    | 55°    | 44007.3 | 40781.7 | 37554.4 | 35019.1 | 32483.8 | 29948.6 | 27413.3 | 23892.1 | 20370.9 |
| 0.0  | 0.0    | 57.5°  | 45021.1 | 41713.8 | 38406.4 | 35518.2 | 32629.9 | 29743.4 | 26855.1 | 23005.3 | 19155.4 |
| 0.0  | 0.0    | 60°    | 44755.1 | 41877.2 | 38997.7 | 35904.2 | 32809.0 | 29715.6 | 26620.4 | 22386.2 | 18150.3 |
| 0.0  | 0.0    | 62.5°  | 40136.6 | 37844.8 | 35551.2 | 33007.2 | 30461.5 | 27917.6 | 25373.6 | 21014.3 | 16654.9 |
| 0.0  | 0.0    | 65°    | 33019.4 | 31346.6 | 29673.8 | 27627.2 | 25578.8 | 23532.1 | 21485.5 | 17576.5 | 13669.3 |
| 0.0  | 0.0    | 67.5°  | 26761.2 | 24876.3 | 22989.6 | 21358.6 | 19725.8 | 18094.7 | 16461.9 | 13385.8 | 10309.8 |
|      |        | 70°    | 21261.2 | 19211.0 | 17159.2 | 15566.4 | 13971.8 | 12379.0 | 10786.2 | 8741.3  | 6698.1  |
|      |        | 72.5°  | 16884.4 | 15036.0 | 13187.6 | 11488.7 | 9788.1  | 8089.2  | 6388.6  | 5180.1  | 3971.6  |
|      |        | 75°    | 8070.1  | 7331.1  | 6592.1  | 5703.5  | 4814.9  | 3926.4  | 3037.8  | 2510.9  | 1985.8  |
|      |        | 77.5°  | 2990.9  | 2592.7  | 2192.7  | 1831.0  | 1469.3  | 1109.4  | 747.7   | 685.1   | 622.5   |
|      |        | 80°    | 773.8   | 674.7   | 573.8   | 502.5   | 429.5   | 358.2   | 286.9   | 259.1   | 233.0   |
|      |        | 82.5°  | 88.7    | 81.7    | 76.5    | 73.0    | 67.8    | 64.3    | 59.1    | 53.9    | 48.7    |
|      |        | 85°    | 5.2     | 3.5     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 100.9  | 100.9  |
| 0.0    | 0.0  | 2.5°   | 93.9   | 92.2   |
| 0.0    | 0.0  | 5°     | 99.1   | 97.4   |
| 0.0    | 0.0  | 7.5°   | 109.5  | 106.1  |
| 0.0    | 0.0  | 10°    | 120.0  | 116.5  |
| 0.0    | 0.0  | 12.5°  | 135.6  | 130.4  |
| 0.0    | 0.0  | 15°    | 153.0  | 142.6  |
| 0.0    | 0.0  | 17.5°  | 182.6  | 160.0  |
| 0.0    | 0.0  | 20°    | 246.9  | 189.5  |
| 0.0    | 0.0  | 22.5°  | 347.8  | 236.5  |
| 0.0    | 0.0  | 25°    | 511.2  | 326.9  |
| 0.0    | 0.0  | 27.5°  | 711.2  | 434.7  |
| 0.0    | 0.0  | 30°    | 945.9  | 544.3  |
| 0.0    | 0.0  | 32.5°  | 1152.9 | 648.6  |
| 0.0    | 0.0  | 35°    | 1422.4 | 754.7  |
| 0.0    | 0.0  | 37.5°  | 1754.5 | 890.3  |
| 0.0    | 0.0  | 40°    | 2269.2 | 1095.5 |
| 0.0    | 0.0  | 42.5°  | 3196.0 | 1474.6 |
| 0.0    | 0.0  | 45°    | 5190.5 | 2549.2 |
| 0.0    | 0.0  | 47.5°  | 7986.6 | 4216.8 |
| 0.0    | 0.0  | 50°    | 9770.7 | 5381.8 |
| 0.0    | 0.0  | 52.5°  | 9916.8 | 5373.1 |
| 0.0    | 0.0  | 55°    | 9052.6 | 4776.7 |
| 0.0    | 0.0  | 57.5°  | 7724.1 | 3992.4 |
| 0.0    | 0.0  | 60°    | 6419.9 | 3157.8 |
| 0.0    | 0.0  | 62.5°  | 5058.4 | 2180.5 |
| 0.0    | 0.0  | 65°    | 3696.8 | 1542.4 |
| 0.0    | 0.0  | 67.5°  | 2655.3 | 1152.9 |
|        |      | 70°    | 1745.8 | 883.3  |
|        |      | 72.5°  | 1137.2 | 719.9  |
|        |      | 75°    | 765.1  | 596.4  |
|        |      | 77.5°  | 446.9  | 396.5  |
|        |      | 80°    | 158.2  | 139.1  |
|        |      | 82.5°  | 29.6   | 20.9   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1049263

CATALOG NUMBER: GALN-SA5C-850-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-12

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-850-U-5WQ

Data in this report applies to families of products including GSS-SB1A-850-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-12  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-850-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 4760  
 CIE  $u'$ : 0.2107  
 CIE  $v'$ : 0.4939  
 Duv: 0.0050  
 CIE x: 0.3537  
 CIE y: 0.3685  
 CIE z: 0.2779  
 Peak Wavelength (nm): 443  
 Dominant Wavelength (nm): 571  
 Purity: 16.69598  
 R<sub>f</sub>: 82  
 R<sub>g</sub>: 99.4

CRI (Ra): 81.1  
 R1: 79.8  
 R2: 83.5  
 R3: 87.9  
 R4: 83.1  
 R5: 80.5  
 R6: 79.1  
 R7: 86.1  
 R8: 69.0  
 R9: 8.7  
 R10: 62.4  
 R11: 83.8  
 R12: 63.0  
 R13: 79.9  
 R14: 93.3  
 R15: 72.7



### Test Conditions


Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-12


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-12

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-12

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 270                      | NR            | 620    | 517                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 335                      | NR            | 625    | 486                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 397                      | NR            | 630    | 454                      | NR            | 760    | 12                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 451                      | NR            | 635    | 419                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 492                      | NR            | 640    | 384                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 1                        | NR            | 515    | 524                      | NR            | 645    | 347                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 3                        | NR            | 520    | 545                      | NR            | 650    | 313                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 5                        | NR            | 525    | 558                      | NR            | 655    | 280                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 7                        | NR            | 530    | 568                      | NR            | 660    | 248                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 13                       | NR            | 535    | 575                      | NR            | 665    | 219                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 24                       | NR            | 540    | 579                      | NR            | 670    | 192                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 47                       | NR            | 545    | 585                      | NR            | 675    | 167                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 95                       | NR            | 550    | 588                      | NR            | 680    | 146                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 181                      | NR            | 555    | 593                      | NR            | 685    | 126                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 319                      | NR            | 560    | 595                      | NR            | 690    | 109                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 539                      | NR            | 565    | 600                      | NR            | 695    | 94                       | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 868                      | NR            | 570    | 603                      | NR            | 700    | 80                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 977                      | NR            | 575    | 606                      | NR            | 705    | 69                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 601                      | NR            | 580    | 609                      | NR            | 710    | 59                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 397                      | NR            | 585    | 611                      | NR            | 715    | 51                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 302                      | NR            | 590    | 610                      | NR            | 720    | 44                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 201                      | NR            | 595    | 604                      | NR            | 725    | 37                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 157                      | NR            | 600    | 596                      | NR            | 730    | 32                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 157                      | NR            | 605    | 583                      | NR            | 735    | 27                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 171                      | NR            | 610    | 566                      | NR            | 740    | 23                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 210                      | NR            | 615    | 543                      | NR            | 745    | 20                       | NR            | 875    | 0                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-12

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.83

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.74


| λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>λ</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 270                         | NR               | 620       | 517                         | NR               | 750       | 17                          | NR               | 880       | 0                           | NR               |
| 365       | 0                           | NR               | 495       | 335                         | NR               | 625       | 486                         | NR               | 755       | 15                          | NR               | 885       | 0                           | NR               |
| 370       | 0                           | NR               | 500       | 397                         | NR               | 630       | 454                         | NR               | 760       | 12                          | NR               | 890       | 0                           | NR               |
| 375       | 0                           | NR               | 505       | 451                         | NR               | 635       | 419                         | NR               | 765       | 11                          | NR               | 895       | 0                           | NR               |
| 380       | 0                           | NR               | 510       | 492                         | NR               | 640       | 384                         | NR               | 770       | 9                           | NR               | 900       | 0                           | NR               |
| 385       | 1                           | NR               | 515       | 524                         | NR               | 645       | 347                         | NR               | 775       | 8                           | NR               | 905       | 0                           | NR               |
| 390       | 3                           | NR               | 520       | 545                         | NR               | 650       | 313                         | NR               | 780       | 7                           | NR               | 910       | 0                           | NR               |
| 395       | 5                           | NR               | 525       | 558                         | NR               | 655       | 280                         | NR               | 785       | 6                           | NR               | 915       | 0                           | NR               |
| 400       | 7                           | NR               | 530       | 568                         | NR               | 660       | 248                         | NR               | 790       | 5                           | NR               | 920       | 0                           | NR               |
| 405       | 13                          | NR               | 535       | 575                         | NR               | 665       | 219                         | NR               | 795       | 4                           | NR               | 925       | 0                           | NR               |
| 410       | 24                          | NR               | 540       | 579                         | NR               | 670       | 192                         | NR               | 800       | 4                           | NR               | 930       | 0                           | NR               |
| 415       | 47                          | NR               | 545       | 585                         | NR               | 675       | 167                         | NR               | 805       | 3                           | NR               | 935       | 0                           | NR               |
| 420       | 95                          | NR               | 550       | 588                         | NR               | 680       | 146                         | NR               | 810       | 3                           | NR               | 940       | 0                           | NR               |
| 425       | 181                         | NR               | 555       | 593                         | NR               | 685       | 126                         | NR               | 815       | 2                           | NR               | 945       | 0                           | NR               |
| 430       | 319                         | NR               | 560       | 595                         | NR               | 690       | 109                         | NR               | 820       | 2                           | NR               | 950       | 0                           | NR               |
| 435       | 539                         | NR               | 565       | 600                         | NR               | 695       | 94                          | NR               | 825       | 2                           | NR               | 955       | 0                           | NR               |
| 440       | 868                         | NR               | 570       | 603                         | NR               | 700       | 80                          | NR               | 830       | 2                           | NR               | 960       | 0                           | NR               |
| 445       | 977                         | NR               | 575       | 606                         | NR               | 705       | 69                          | NR               | 835       | 1                           | NR               | 965       | 0                           | NR               |
| 450       | 601                         | NR               | 580       | 609                         | NR               | 710       | 59                          | NR               | 840       | 1                           | NR               | 970       | 0                           | NR               |
| 455       | 397                         | NR               | 585       | 611                         | NR               | 715       | 51                          | NR               | 845       | 1                           | NR               | 975       | 0                           | NR               |
| 460       | 302                         | NR               | 590       | 610                         | NR               | 720       | 44                          | NR               | 850       | 1                           | NR               | 980       | 0                           | NR               |
| 465       | 201                         | NR               | 595       | 604                         | NR               | 725       | 37                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 596                         | NR               | 730       | 32                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 157                         | NR               | 605       | 583                         | NR               | 735       | 27                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 171                         | NR               | 610       | 566                         | NR               | 740       | 23                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 210                         | NR               | 615       | 543                         | NR               | 745       | 20                          | NR               | 875       | 0                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-12





TM-30-18

### Summary

$R_f = 82$   
 $R_g = 99.4$   
 $CIE R_a = 81.1$   
 $R_9 = 8.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 73 | CES51 = 92 | CES76 = 66 |
| CES02 = 60 | CES27 = 90 | CES52 = 93 | CES77 = 80 |
| CES03 = 30 | CES28 = 87 | CES53 = 84 | CES78 = 65 |
| CES04 = 69 | CES29 = 69 | CES54 = 88 | CES79 = 87 |
| CES05 = 47 | CES30 = 73 | CES55 = 88 | CES80 = 83 |
| CES06 = 50 | CES31 = 72 | CES56 = 80 | CES81 = 84 |
| CES07 = 40 | CES32 = 69 | CES57 = 78 | CES82 = 93 |
| CES08 = 39 | CES33 = 75 | CES58 = 80 | CES83 = 90 |
| CES09 = 29 | CES34 = 78 | CES59 = 93 | CES84 = 92 |
| CES10 = 73 | CES35 = 88 | CES60 = 95 | CES85 = 87 |
| CES11 = 56 | CES36 = 98 | CES61 = 93 | CES86 = 80 |
| CES12 = 62 | CES37 = 85 | CES62 = 88 | CES87 = 84 |
| CES13 = 42 | CES38 = 81 | CES63 = 83 | CES88 = 85 |
| CES14 = 74 | CES39 = 93 | CES64 = 83 | CES89 = 80 |
| CES15 = 71 | CES40 = 88 | CES65 = 77 | CES90 = 83 |
| CES16 = 46 | CES41 = 89 | CES66 = 81 | CES91 = 89 |
| CES17 = 48 | CES42 = 82 | CES67 = 80 | CES92 = 73 |
| CES18 = 55 | CES43 = 80 | CES68 = 83 | CES93 = 85 |
| CES19 = 70 | CES44 = 99 | CES69 = 89 | CES94 = 67 |
| CES20 = 64 | CES45 = 87 | CES70 = 75 | CES95 = 78 |
| CES21 = 85 | CES46 = 85 | CES71 = 73 | CES96 = 84 |
| CES22 = 77 | CES47 = 82 | CES72 = 91 | CES97 = 87 |
| CES23 = 91 | CES48 = 78 | CES73 = 67 | CES98 = 81 |
| CES24 = 90 | CES49 = 84 | CES74 = 98 | CES99 = 74 |
| CES25 = 71 | CES50 = 91 | CES75 = 70 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)