

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047394

Luminaire Tested: **GALN-SA6B-840-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047394
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA6B-840-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 6xLight Square PACKAGE
80CRI 4000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (84) 4000K CCT, 80 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 25496.3 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G4

Input Watts (W): 213.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047394

CATALOG NUMBER: GALN-SA6B-840-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
- - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 28.6 fc
Type III - Short - N/A

REPORT NUMBER: P1047394

CATALOG NUMBER: GALN-SA6B-840-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047394

CATALOG NUMBER: GALN-SA6B-840-U-T3BC


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	93.1	0.0	93.1
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	25403.3	0.0	25403.3
	% Fixture	99.6	0.0	99.6
Total	Lumens	25496.3	0.0	25496.3
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.4	0.1
10°-20°	293.1	1.1
20°-30°	1056.3	4.1
30°-40°	2416.9	9.5
40°-50°	4076.4	16.0
50°-60°	6727.0	26.4
60°-70°	7518.3	29.5
70°-80°	3104.2	12.2
80°-90°	279.8	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25496.3	100.0
0°-180°	25496.3	100.0



REPORT NUMBER: P1047394


CATALOG NUMBER: GALN-SA6B-840-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1349.6	5.3			
FM	(30°-60°)	13197.9	51.8			
FH	(60°-80°)	10579.8	41.5			G4/12000
FVH	(80°-90°)	276.0	1.1			G3/500
BL	(0°-30°)	24.3	0.1	B0/110		
BM	(30°-60°)	22.3	0.1	B0/220		
BH	(60°-80°)	42.7	0.2	B0/110		G0/110
BVH	(80°-90°)	3.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G4

Type III Short





REPORT NUMBER: P1047394

CATALOG NUMBER: GALN-SA6B-840-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7
2.5°	200.1	206.7	200.1	200.1	200.1	193.4	193.4	186.7	186.7	180.0	173.4
5°	293.4	293.4	273.4	260.1	246.7	240.1	233.4	220.1	206.7	193.4	180.0
7.5°	653.5	653.5	593.5	513.5	406.8	346.8	333.4	273.4	233.4	206.7	180.0
10°	1560.4	1560.4	1427.0	1207.0	933.6	693.5	620.2	393.4	280.1	220.1	186.7
12.5°	2594.0	2627.3	2460.6	2180.5	1773.8	1353.7	1207.0	720.2	373.4	240.1	186.7
15°	3520.9	3440.9	3394.2	3127.5	2740.7	2240.6	2053.9	1213.6	540.1	273.4	186.7
17.5°	4147.7	4147.7	4081.0	3901.0	3547.6	3107.4	2954.1	1960.5	873.6	313.4	193.4
20°	4881.2	4881.2	4761.2	4634.5	4321.1	3947.7	3801.0	2787.4	1353.7	400.1	193.4
22.5°	5768.1	5781.5	5648.1	5421.4	5121.3	4707.9	4581.2	3554.2	1960.5	533.5	200.1
25°	6848.4	6861.7	6668.3	6455.0	5994.8	5548.1	5354.7	4434.4	2700.7	746.9	200.1
27.5°	8042.0	8135.4	7848.6	7481.9	6995.1	6435.0	6288.2	5228.0	3434.2	1053.6	213.4
30°	9529.1	9529.1	9149.0	8635.5	8108.7	7415.2	7228.5	6061.5	4214.4	1460.4	226.7
32.5°	10809.4	10709.4	10222.6	9682.4	9122.3	8475.5	8275.4	6935.1	5014.6	1967.2	253.4
35°	11789.6	11702.9	11102.8	10522.6	10035.9	9442.4	9202.3	7882.0	5861.5	2540.6	293.4
37.5°	12629.8	12596.5	11783.0	11056.1	10736.0	10215.9	10002.5	8775.5	6695.0	3160.8	340.1
40°	13550.1	13443.4	12576.5	11676.3	11196.2	10776.0	10582.7	9495.7	7495.2	3887.6	406.8
42.5°	14336.9	14210.2	13430.0	12549.8	11729.6	11162.8	10976.1	10102.5	8275.4	4614.5	493.5
45°	15210.5	15143.8	14356.9	13690.1	12596.5	11689.6	11442.9	10589.3	8988.9	5481.4	606.8
47.5°	16524.2	16404.1	15670.6	15123.8	13856.8	12489.8	12136.4	11089.5	9675.8	6334.9	780.2
50°	18051.2	17971.2	17537.7	17104.3	15844.0	13856.8	13436.7	11809.6	10442.6	7348.5	1006.9
52.5°	19298.2	19284.9	19338.2	19344.9	18391.3	16157.4	15530.6	12969.9	11322.8	8348.8	1327.0
55°	19271.5	19331.5	19918.3	20591.8	20665.2	19298.2	18691.4	14923.8	12469.8	9582.4	1773.8
57.5°	18551.3	18504.7	19124.8	20138.4	20851.9	20998.6	20898.6	17957.9	14196.9	11069.5	2460.6
58°	18317.9	18277.9	18864.7	19898.3	20718.5	21112.0	21012.0	18644.7	14583.7	11282.8	2647.3
60°	17471.1	17477.7	17824.5	18764.7	19584.9	20518.5	20611.9	20605.2	16510.8	12709.9	3587.6
62.5°	16350.8	16297.4	16617.5	17384.4	18104.6	18731.4	18891.4	20738.6	19331.5	14523.7	5381.4
65°	14803.7	14723.7	15063.8	15930.7	16704.2	17111.0	17117.6	18951.4	20658.5	16470.8	7942.0
67.5°	11929.7	11863.0	12543.2	13656.8	14850.4	15383.9	15623.9	16444.1	19538.2	17791.1	9409.0
70°	7308.5	7448.5	8395.4	10142.6	12183.1	13163.3	13523.4	13776.8	16637.5	17591.1	7868.6
72.5°	3374.2	3207.5	4014.3	5234.7	7561.9	9742.5	10115.9	11109.5	13190.0	15270.5	5868.1
75°	1573.7	1513.7	1700.4	2287.2	3427.5	5261.3	5941.5	8868.9	10115.9	10622.7	4234.4
77.5°	806.9	813.5	966.9	1040.3	1413.7	2433.9	2794.0	5834.8	7415.2	5928.2	2840.7
80°	353.4	366.8	373.4	406.8	573.5	940.2	1060.3	2707.3	5067.9	3020.8	1553.7
82.5°	226.7	233.4	233.4	233.4	273.4	373.4	426.8	1086.9	2527.3	1500.4	480.1
85°	120.0	120.0	133.4	166.7	193.4	226.7	240.1	346.8	833.5	446.8	113.4
87.5°	66.7	73.4	80.0	100.0	126.7	153.4	166.7	240.1	320.1	306.7	26.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1047394

CATALOG NUMBER: GALN-SA6B-840-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7	166.7
2.5°	173.4	166.7	160.0	153.4	146.7	140.0	140.0	140.0	140.0	140.0	140.0
5°	166.7	160.0	153.4	140.0	126.7	120.0	113.4	106.7	106.7	106.7	106.7
7.5°	166.7	160.0	140.0	126.7	113.4	100.0	86.7	86.7	86.7	86.7	86.7
10°	166.7	153.4	133.4	113.4	93.4	80.0	73.4	66.7	66.7	66.7	66.7
12.5°	166.7	146.7	126.7	100.0	80.0	66.7	60.0	53.3	53.3	53.3	53.3
15°	166.7	146.7	120.0	93.4	73.4	53.3	46.7	40.0	40.0	40.0	40.0
17.5°	160.0	140.0	113.4	80.0	60.0	40.0	33.3	26.7	26.7	33.3	33.3
20°	153.4	133.4	100.0	66.7	46.7	33.3	20.0	20.0	20.0	20.0	20.0
22.5°	153.4	133.4	93.4	60.0	40.0	20.0	13.3	13.3	13.3	13.3	20.0
25°	153.4	126.7	80.0	46.7	26.7	13.3	6.7	6.7	6.7	6.7	6.7
27.5°	153.4	126.7	73.4	40.0	20.0	13.3	6.7	0.0	0.0	0.0	0.0
30°	146.7	120.0	66.7	33.3	13.3	6.7	0.0	0.0	0.0	0.0	0.0
32.5°	146.7	113.4	53.3	26.7	13.3	6.7	0.0	0.0	0.0	0.0	0.0
35°	153.4	106.7	46.7	20.0	6.7	0.0	0.0	0.0	0.0	0.0	6.7
37.5°	160.0	100.0	40.0	13.3	6.7	0.0	0.0	0.0	0.0	0.0	0.0
40°	166.7	93.4	40.0	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	180.0	93.4	33.3	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	193.4	93.4	26.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	220.1	100.0	26.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	240.1	106.7	20.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	266.7	100.0	20.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	300.1	100.0	20.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	326.7	93.4	20.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	340.1	86.7	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	406.8	80.0	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	633.5	66.7	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1287.0	60.0	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2400.6	53.3	13.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	2687.3	60.0	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1693.8	46.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	893.6	46.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	446.8	46.7	6.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	206.7	33.3	6.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	86.7	20.0	13.3	6.7	6.7	0.0	0.0	0.0	0.0	0.0	0.0
85°	40.0	20.0	13.3	13.3	6.7	6.7	0.0	0.0	0.0	0.0	0.0
87.5°	20.0	20.0	20.0	13.3	13.3	6.7	6.7	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-11

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-840-U-5WQ

Data in this report applies to families of products including GSS-SB1A-840-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-11
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-840-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI 4000K CCT 26 LEDS

Spectral Parameters

CCT (K): 3897
 CIE u' : 0.2249
 CIE v' : 0.5084
 Duv: 0.0039
 CIE x: 0.3882
 CIE y: 0.3900
 CIE z: 0.2218
 Peak Wavelength (nm): 445
 Dominant Wavelength (nm): 577
 Purity: 33.54925
 R_f: 81.8
 R_g: 98.6

CRI (Ra): 80.2
 R1: 78.9
 R2: 83.5
 R3: 88.3
 R4: 82.1
 R5: 78.8
 R6: 78.4
 R7: 85.8
 R8: 65.8
 R9: 6.7
 R10: 61.9
 R11: 81.9
 R12: 58.9
 R13: 79.2
 R14: 93.2
 R15: 71.9



Test Conditions


Stabilization Time: 24M
 Operation Time: 1H 24M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-11


Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-11

CIE 1931 Chromaticity Diagram




CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-11

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	242	NR	620	792	NR	750	29	NR	880	1	NR
365	0	NR	495	320	NR	625	748	NR	755	25	NR	885	1	NR
370	0	NR	500	401	NR	630	703	NR	760	22	NR	890	1	NR
375	0	NR	505	479	NR	635	651	NR	765	19	NR	895	1	NR
380	0	NR	510	546	NR	640	599	NR	770	16	NR	900	1	NR
385	0	NR	515	602	NR	645	545	NR	775	14	NR	905	0	NR
390	2	NR	520	645	NR	650	493	NR	780	12	NR	910	0	NR
395	4	NR	525	674	NR	655	443	NR	785	10	NR	915	0	NR
400	6	NR	530	699	NR	660	394	NR	790	9	NR	920	0	NR
405	11	NR	535	718	NR	665	349	NR	795	8	NR	925	0	NR
410	22	NR	540	732	NR	670	307	NR	800	7	NR	930	0	NR
415	43	NR	545	749	NR	675	269	NR	805	6	NR	935	0	NR
420	86	NR	550	762	NR	680	235	NR	810	5	NR	940	0	NR
425	164	NR	555	778	NR	685	204	NR	815	5	NR	945	0	NR
430	288	NR	560	792	NR	690	178	NR	820	4	NR	950	0	NR
435	478	NR	565	809	NR	695	153	NR	825	3	NR	955	0	NR
440	766	NR	570	827	NR	700	132	NR	830	3	NR	960	0	NR
445	1000	NR	575	845	NR	705	114	NR	835	3	NR	965	0	NR
450	726	NR	580	862	NR	710	98	NR	840	2	NR	970	0	NR
455	425	NR	585	875	NR	715	84	NR	845	2	NR	975	0	NR
460	324	NR	590	887	NR	720	73	NR	850	2	NR	980	0	NR
465	225	NR	595	890	NR	725	63	NR	855	1	NR	985	0	NR
470	157	NR	600	887	NR	730	54	NR	860	1	NR	990	0	NR
475	147	NR	605	875	NR	735	46	NR	865	1	NR	995	0	NR
480	154	NR	610	856	NR	740	40	NR	870	1	NR	1000	0	NR
485	184	NR	615	828	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-11

Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.57

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	242	NR	620	792	NR	750	29	NR	880	1	NR
365	0	NR	495	320	NR	625	748	NR	755	25	NR	885	1	NR
370	0	NR	500	401	NR	630	703	NR	760	22	NR	890	1	NR
375	0	NR	505	479	NR	635	651	NR	765	19	NR	895	1	NR
380	0	NR	510	546	NR	640	599	NR	770	16	NR	900	1	NR
385	0	NR	515	602	NR	645	545	NR	775	14	NR	905	0	NR
390	2	NR	520	645	NR	650	493	NR	780	12	NR	910	0	NR
395	4	NR	525	674	NR	655	443	NR	785	10	NR	915	0	NR
400	6	NR	530	699	NR	660	394	NR	790	9	NR	920	0	NR
405	11	NR	535	718	NR	665	349	NR	795	8	NR	925	0	NR
410	22	NR	540	732	NR	670	307	NR	800	7	NR	930	0	NR
415	43	NR	545	749	NR	675	269	NR	805	6	NR	935	0	NR
420	86	NR	550	762	NR	680	235	NR	810	5	NR	940	0	NR
425	164	NR	555	778	NR	685	204	NR	815	5	NR	945	0	NR
430	288	NR	560	792	NR	690	178	NR	820	4	NR	950	0	NR
435	478	NR	565	809	NR	695	153	NR	825	3	NR	955	0	NR
440	766	NR	570	827	NR	700	132	NR	830	3	NR	960	0	NR
445	1000	NR	575	845	NR	705	114	NR	835	3	NR	965	0	NR
450	726	NR	580	862	NR	710	98	NR	840	2	NR	970	0	NR
455	425	NR	585	875	NR	715	84	NR	845	2	NR	975	0	NR
460	324	NR	590	887	NR	720	73	NR	850	2	NR	980	0	NR
465	225	NR	595	890	NR	725	63	NR	855	1	NR	985	0	NR
470	157	NR	600	887	NR	730	54	NR	860	1	NR	990	0	NR
475	147	NR	605	875	NR	735	46	NR	865	1	NR	995	0	NR
480	154	NR	610	856	NR	740	40	NR	870	1	NR	1000	0	NR
485	184	NR	615	828	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-11

Melanopic Flux vs. Wavelength


Melanopic Lumens: NR
M/P: 3.06


λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	242	NR	620	792	NR	750	29	NR	880	1	NR
365	0	NR	495	320	NR	625	748	NR	755	25	NR	885	1	NR
370	0	NR	500	401	NR	630	703	NR	760	22	NR	890	1	NR
375	0	NR	505	479	NR	635	651	NR	765	19	NR	895	1	NR
380	0	NR	510	546	NR	640	599	NR	770	16	NR	900	1	NR
385	0	NR	515	602	NR	645	545	NR	775	14	NR	905	0	NR
390	2	NR	520	645	NR	650	493	NR	780	12	NR	910	0	NR
395	4	NR	525	674	NR	655	443	NR	785	10	NR	915	0	NR
400	6	NR	530	699	NR	660	394	NR	790	9	NR	920	0	NR
405	11	NR	535	718	NR	665	349	NR	795	8	NR	925	0	NR
410	22	NR	540	732	NR	670	307	NR	800	7	NR	930	0	NR
415	43	NR	545	749	NR	675	269	NR	805	6	NR	935	0	NR
420	86	NR	550	762	NR	680	235	NR	810	5	NR	940	0	NR
425	164	NR	555	778	NR	685	204	NR	815	5	NR	945	0	NR
430	288	NR	560	792	NR	690	178	NR	820	4	NR	950	0	NR
435	478	NR	565	809	NR	695	153	NR	825	3	NR	955	0	NR
440	766	NR	570	827	NR	700	132	NR	830	3	NR	960	0	NR
445	1000	NR	575	845	NR	705	114	NR	835	3	NR	965	0	NR
450	726	NR	580	862	NR	710	98	NR	840	2	NR	970	0	NR
455	425	NR	585	875	NR	715	84	NR	845	2	NR	975	0	NR
460	324	NR	590	887	NR	720	73	NR	850	2	NR	980	0	NR
465	225	NR	595	890	NR	725	63	NR	855	1	NR	985	0	NR
470	157	NR	600	887	NR	730	54	NR	860	1	NR	990	0	NR
475	147	NR	605	875	NR	735	46	NR	865	1	NR	995	0	NR
480	154	NR	610	856	NR	740	40	NR	870	1	NR	1000	0	NR
485	184	NR	615	828	NR	745	34	NR	875	1	NR			

REPORT NUMBER: SP1-2407-184-11





TM-30-18

Summary

$R_f = 81.8$
 $R_g = 98.6$
 $CIE R_a = 80.2$
 $R_9 = 6.7$







Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 85	CES26 = 73	CES51 = 93	CES76 = 66
CES02 = 61	CES27 = 91	CES52 = 93	CES77 = 80
CES03 = 31	CES28 = 87	CES53 = 83	CES78 = 66
CES04 = 69	CES29 = 71	CES54 = 89	CES79 = 88
CES05 = 48	CES30 = 77	CES55 = 88	CES80 = 85
CES06 = 50	CES31 = 74	CES56 = 80	CES81 = 83
CES07 = 41	CES32 = 70	CES57 = 79	CES82 = 93
CES08 = 40	CES33 = 77	CES58 = 80	CES83 = 91
CES09 = 29	CES34 = 79	CES59 = 92	CES84 = 91
CES10 = 74	CES35 = 88	CES60 = 95	CES85 = 84
CES11 = 57	CES36 = 98	CES61 = 91	CES86 = 78
CES12 = 63	CES37 = 85	CES62 = 90	CES87 = 84
CES13 = 42	CES38 = 85	CES63 = 81	CES88 = 85
CES14 = 74	CES39 = 95	CES64 = 81	CES89 = 78
CES15 = 71	CES40 = 90	CES65 = 76	CES90 = 84
CES16 = 47	CES41 = 90	CES66 = 78	CES91 = 85
CES17 = 49	CES42 = 84	CES67 = 76	CES92 = 71
CES18 = 56	CES43 = 81	CES68 = 80	CES93 = 84
CES19 = 71	CES44 = 99	CES69 = 86	CES94 = 65
CES20 = 65	CES45 = 87	CES70 = 73	CES95 = 77
CES21 = 86	CES46 = 85	CES71 = 70	CES96 = 83
CES22 = 78	CES47 = 84	CES72 = 90	CES97 = 87
CES23 = 91	CES48 = 79	CES73 = 65	CES98 = 81
CES24 = 90	CES49 = 84	CES74 = 98	CES99 = 75
CES25 = 71	CES50 = 91	CES75 = 68	



Color Rendition by Hue-Angle Bin


Measure Comparisons


(END OF REPORT)