

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049239

Luminaire Tested: **GALN-SA8C-840-U-RBC**

Issue Date: 07/10/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1049239  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA8C-840-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 8xLight Square PACKAGE  
80CRI 4000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (112) 4000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 36655.6 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G5


Input Watts (W): 372.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 5.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049239  
CATALOG NUMBER: GALN-SA8C-840-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 183.6    | 0.0    | 183.6   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 36472.0  | 0.0    | 36472.0 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 36655.6  | 0.0    | 36655.6 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 14.4    | 0.0       |
| 10°-20°   | 80.5    | 0.2       |
| 20°-30°   | 868.7   | 2.4       |
| 30°-40°   | 2568.9  | 7.0       |
| 40°-50°   | 7655.9  | 20.9      |
| 50°-60°   | 12139.5 | 33.1      |
| 60°-70°   | 10133.5 | 27.6      |
| 70°-80°   | 3124.8  | 8.5       |
| 80°-90°   | 69.5    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 36655.6 | 100.0     |
| 0°-180°   | 36655.6 | 100.0     |



REPORT NUMBER: P1049239


CATALOG NUMBER: GALN-SA8C-840-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |        |
|------|-------------|---------|-----------|-------------------------|------|--------|
|      |             |         |           | B                       | U    | G      |
| FL   | (0°-30°)    | 929.9   | 2.5       |                         |      |        |
| FM   | (30°-60°)   | 22298.6 | 60.8      |                         |      |        |
| FH   | (60°-80°)   | 13189.8 | 36.0      |                         |      | G5     |
| FVH  | (80°-90°)   | 53.7    | 0.1       |                         |      | G1/100 |
| BL   | (0°-30°)    | 33.7    | 0.1       | B0/110                  |      |        |
| BM   | (30°-60°)   | 65.6    | 0.2       | B0/220                  |      |        |
| BH   | (60°-80°)   | 68.5    | 0.2       | B0/110                  |      | G0/110 |
| BVH  | (80°-90°)   | 15.8    | 0.0       |                         |      | G1/100 |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |        |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |        |

**BUG Rating: B0-U0-G5**

Type III Short



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°     | 7.5°   | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|--------|--------|-------|-------|-------|-------|-------|-------|
| 0°     | 160.7  | 160.7  | 160.7  | 160.7  | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 |
| 2.5°   | 146.8  | 146.8  | 146.8  | 146.8  | 144.0 | 144.0 | 141.3 | 141.3 | 138.5 | 138.5 |
| 5°     | 155.1  | 155.1  | 152.4  | 149.6  | 149.6 | 146.8 | 144.0 | 141.3 | 141.3 | 138.5 |
| 7.5°   | 169.0  | 166.2  | 163.4  | 160.7  | 155.1 | 152.4 | 146.8 | 144.0 | 141.3 | 135.7 |
| 10°    | 185.6  | 180.1  | 174.5  | 169.0  | 163.4 | 157.9 | 152.4 | 149.6 | 144.0 | 141.3 |
| 12.5°  | 207.8  | 199.4  | 188.4  | 180.1  | 174.5 | 166.2 | 160.7 | 155.1 | 146.8 | 141.3 |
| 15°    | 227.1  | 216.1  | 202.2  | 191.1  | 182.8 | 171.7 | 163.4 | 155.1 | 149.6 | 141.3 |
| 17.5°  | 254.8  | 235.5  | 213.3  | 199.4  | 188.4 | 174.5 | 160.7 | 152.4 | 144.0 | 133.0 |
| 20°    | 301.9  | 263.2  | 221.6  | 205.0  | 188.4 | 171.7 | 155.1 | 144.0 | 135.7 | 124.7 |
| 22.5°  | 376.7  | 310.2  | 243.8  | 218.8  | 196.7 | 171.7 | 149.6 | 138.5 | 127.4 | 116.3 |
| 25°    | 520.8  | 401.7  | 282.5  | 249.3  | 216.1 | 182.8 | 149.6 | 135.7 | 124.7 | 110.8 |
| 27.5°  | 692.5  | 515.2  | 335.2  | 288.1  | 243.8 | 196.7 | 149.6 | 133.0 | 119.1 | 102.5 |
| 30°    | 867.0  | 631.6  | 393.3  | 332.4  | 271.5 | 210.5 | 149.6 | 130.2 | 113.6 | 94.2  |
| 32.5°  | 1033.2 | 739.6  | 443.2  | 371.2  | 299.2 | 224.4 | 152.4 | 130.2 | 108.0 | 85.9  |
| 35°    | 1202.2 | 828.2  | 451.5  | 376.7  | 301.9 | 224.4 | 149.6 | 124.7 | 102.5 | 77.6  |
| 37.5°  | 1418.3 | 928.0  | 434.9  | 360.1  | 288.1 | 213.3 | 141.3 | 119.1 | 97.0  | 72.0  |
| 40°    | 1745.1 | 1094.2 | 443.2  | 365.6  | 288.1 | 210.5 | 133.0 | 110.8 | 91.4  | 69.3  |
| 42.5°  | 2349.0 | 1415.5 | 479.2  | 390.6  | 301.9 | 210.5 | 121.9 | 102.5 | 85.9  | 66.5  |
| 45°    | 4060.9 | 2351.8 | 642.6  | 509.7  | 376.7 | 243.8 | 110.8 | 94.2  | 80.3  | 63.7  |
| 47.5°  | 6717.3 | 3936.2 | 1155.1 | 891.9  | 631.6 | 368.4 | 108.0 | 94.2  | 80.3  | 63.7  |
| 50°    | 8573.2 | 5013.8 | 1454.3 | 1119.1 | 783.9 | 448.7 | 113.6 | 97.0  | 83.1  | 66.5  |
| 52.5°  | 8559.4 | 5091.3 | 1620.5 | 1243.7 | 869.8 | 493.1 | 119.1 | 102.5 | 88.6  | 72.0  |
| 55°    | 7609.3 | 4631.5 | 1650.9 | 1268.7 | 889.2 | 506.9 | 127.4 | 110.8 | 94.2  | 77.6  |
| 57.5°  | 6360.0 | 3933.4 | 1506.9 | 1166.2 | 828.2 | 487.5 | 146.8 | 127.4 | 110.8 | 91.4  |
| 60°    | 5030.4 | 3102.4 | 1174.5 | 928.0  | 684.2 | 437.7 | 193.9 | 169.0 | 146.8 | 121.9 |
| 62.5°  | 3473.6 | 2249.3 | 1024.9 | 822.7  | 623.3 | 421.0 | 221.6 | 196.7 | 174.5 | 149.6 |
| 65°    | 2457.0 | 1692.5 | 925.2  | 753.4  | 584.5 | 412.7 | 241.0 | 213.3 | 188.4 | 160.7 |
| 67.5°  | 1836.5 | 1346.2 | 853.2  | 706.4  | 559.5 | 412.7 | 265.9 | 232.7 | 202.2 | 169.0 |
| 70°    | 1407.2 | 1105.2 | 800.5  | 681.4  | 565.1 | 446.0 | 326.9 | 279.8 | 235.5 | 188.4 |
| 72.5°  | 1146.8 | 944.6  | 739.6  | 653.7  | 567.9 | 482.0 | 396.1 | 335.2 | 274.2 | 210.5 |
| 75°    | 950.1  | 808.8  | 667.6  | 595.6  | 526.3 | 454.3 | 382.3 | 326.9 | 274.2 | 218.8 |
| 77.5°  | 631.6  | 576.2  | 518.0  | 476.4  | 434.9 | 390.6 | 349.0 | 301.9 | 257.6 | 210.5 |
| 80°    | 221.6  | 213.3  | 205.0  | 221.6  | 238.2 | 254.8 | 271.5 | 238.2 | 207.8 | 174.5 |
| 82.5°  | 33.2   | 30.5   | 27.7   | 30.5   | 33.2  | 36.0  | 38.8  | 41.6  | 44.3  | 47.1  |
| 85°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°   | 32.5° | 35°   | 37.5° | 40°   | 42.5° | 45°   | 47.5° | 50°   |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0 | 0°     | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 |
| 0.0 | 2.5°   | 135.7 | 135.7 | 133.0 | 133.0 | 133.0 | 130.2 | 130.2 | 127.4 | 127.4 | 127.4 |
| 0.0 | 5°     | 133.0 | 133.0 | 130.2 | 127.4 | 124.7 | 124.7 | 121.9 | 119.1 | 119.1 | 116.3 |
| 0.0 | 7.5°   | 130.2 | 127.4 | 124.7 | 121.9 | 119.1 | 116.3 | 113.6 | 110.8 | 110.8 | 108.0 |
| 0.0 | 10°    | 133.0 | 127.4 | 124.7 | 119.1 | 116.3 | 113.6 | 108.0 | 105.3 | 102.5 | 102.5 |
| 0.0 | 12.5°  | 127.4 | 124.7 | 119.1 | 113.6 | 110.8 | 105.3 | 102.5 | 97.0  | 94.2  | 94.2  |
| 0.0 | 15°    | 127.4 | 121.9 | 113.6 | 108.0 | 102.5 | 99.7  | 94.2  | 88.6  | 85.9  | 83.1  |
| 0.0 | 17.5°  | 119.1 | 113.6 | 105.3 | 99.7  | 94.2  | 88.6  | 83.1  | 77.6  | 74.8  | 72.0  |
| 0.0 | 20°    | 108.0 | 102.5 | 94.2  | 85.9  | 80.3  | 74.8  | 69.3  | 63.7  | 60.9  | 58.2  |
| 0.0 | 22.5°  | 97.0  | 91.4  | 83.1  | 74.8  | 69.3  | 63.7  | 55.4  | 49.9  | 47.1  | 41.6  |
| 0.0 | 25°    | 91.4  | 83.1  | 74.8  | 66.5  | 58.2  | 52.6  | 44.3  | 36.0  | 30.5  | 24.9  |
| 0.0 | 27.5°  | 77.6  | 69.3  | 60.9  | 52.6  | 44.3  | 36.0  | 27.7  | 19.4  | 13.9  | 11.1  |
| 0.0 | 30°    | 66.5  | 58.2  | 49.9  | 41.6  | 30.5  | 22.2  | 13.9  | 2.8   | 2.8   | 2.8   |
| 0.0 | 32.5°  | 55.4  | 47.1  | 36.0  | 27.7  | 22.2  | 13.9  | 8.3   | 0.0   | 0.0   | 0.0   |
| 0.0 | 35°    | 44.3  | 36.0  | 24.9  | 16.6  | 13.9  | 8.3   | 5.5   | 0.0   | 0.0   | 0.0   |
| 0.0 | 37.5°  | 38.8  | 30.5  | 19.4  | 8.3   | 5.5   | 5.5   | 2.8   | 0.0   | 0.0   | 0.0   |
| 0.0 | 40°    | 36.0  | 24.9  | 13.9  | 2.8   | 2.8   | 2.8   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 42.5°  | 36.0  | 24.9  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 45°    | 36.0  | 24.9  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 47.5°  | 36.0  | 24.9  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 50°    | 38.8  | 27.7  | 13.9  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0 | 52.5°  | 44.3  | 33.2  | 22.2  | 11.1  | 8.3   | 5.5   | 2.8   | 0.0   | 0.0   | 0.0   |
| 0.0 | 55°    | 55.4  | 49.9  | 41.6  | 36.0  | 27.7  | 19.4  | 8.3   | 0.0   | 0.0   | 0.0   |
| 0.0 | 57.5°  | 72.0  | 72.0  | 69.3  | 66.5  | 49.9  | 33.2  | 16.6  | 0.0   | 0.0   | 0.0   |
| 0.0 | 60°    | 97.0  | 97.0  | 97.0  | 97.0  | 72.0  | 49.9  | 24.9  | 0.0   | 0.0   | 0.0   |
| 0.0 | 62.5°  | 119.1 | 113.6 | 105.3 | 99.7  | 74.8  | 49.9  | 24.9  | 0.0   | 0.0   | 0.0   |
| 0.0 | 65°    | 119.1 | 108.0 | 94.2  | 80.3  | 60.9  | 41.6  | 19.4  | 0.0   | 0.0   | 0.0   |
| 0.0 | 67.5°  | 110.8 | 88.6  | 63.7  | 41.6  | 30.5  | 22.2  | 11.1  | 0.0   | 0.0   | 0.0   |
|     | 70°    | 110.8 | 77.6  | 44.3  | 11.1  | 8.3   | 5.5   | 2.8   | 0.0   | 0.0   | 0.0   |
|     | 72.5°  | 110.8 | 74.8  | 36.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 75°    | 121.9 | 83.1  | 41.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 77.5°  | 121.9 | 83.1  | 41.6  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 80°    | 108.0 | 72.0  | 36.0  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 82.5°  | 36.0  | 24.9  | 11.1  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°   | 57.5° | 60°   | 62.5° | 65°   | 67.5° | 70°   | 72.5° | 75°   | 77.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0.0   | 0°     | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 |
| 0.0   | 2.5°   | 124.7 | 124.7 | 124.7 | 121.9 | 121.9 | 121.9 | 121.9 | 119.1 | 119.1 | 119.1 |
| 0.0   | 5°     | 113.6 | 113.6 | 110.8 | 110.8 | 108.0 | 108.0 | 105.3 | 105.3 | 102.5 | 102.5 |
| 0.0   | 7.5°   | 105.3 | 102.5 | 102.5 | 99.7  | 97.0  | 97.0  | 94.2  | 94.2  | 91.4  | 88.6  |
| 0.0   | 10°    | 97.0  | 94.2  | 94.2  | 91.4  | 88.6  | 85.9  | 85.9  | 83.1  | 80.3  | 77.6  |
| 0.0   | 12.5°  | 88.6  | 85.9  | 83.1  | 80.3  | 77.6  | 74.8  | 74.8  | 72.0  | 69.3  | 66.5  |
| 0.0   | 15°    | 77.6  | 74.8  | 72.0  | 69.3  | 66.5  | 63.7  | 63.7  | 60.9  | 58.2  | 55.4  |
| 0.0   | 17.5°  | 66.5  | 63.7  | 63.7  | 60.9  | 58.2  | 55.4  | 52.6  | 47.1  | 44.3  | 41.6  |
| 0.0   | 20°    | 49.9  | 47.1  | 44.3  | 41.6  | 38.8  | 33.2  | 30.5  | 24.9  | 19.4  | 16.6  |
| 0.0   | 22.5°  | 33.2  | 27.7  | 24.9  | 19.4  | 13.9  | 11.1  | 8.3   | 2.8   | 0.0   | 0.0   |
| 0.0   | 25°    | 11.1  | 8.3   | 5.5   | 2.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 0.0   | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

CATALOG NUMBER: GALN-SA8C-840-U-RBC

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°   | 87.5° | 90°   | 92.5° | 95°   | 97.5° | 100°  | 102.5° | 105°  |
|-----|--------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0.0 | 0°     | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7 | 160.7  | 160.7 |
| 0.0 | 2.5°   | 116.3 | 116.3 | 116.3 | 113.6 | 113.6 | 113.6 | 113.6 | 113.6 | 113.6  | 113.6 |
| 0.0 | 5°     | 99.7  | 99.7  | 99.7  | 97.0  | 97.0  | 94.2  | 94.2  | 94.2  | 91.4   | 91.4  |
| 0.0 | 7.5°   | 85.9  | 83.1  | 83.1  | 80.3  | 80.3  | 77.6  | 77.6  | 77.6  | 74.8   | 74.8  |
| 0.0 | 10°    | 72.0  | 69.3  | 69.3  | 66.5  | 66.5  | 63.7  | 63.7  | 60.9  | 60.9   | 58.2  |
| 0.0 | 12.5°  | 63.7  | 60.9  | 58.2  | 55.4  | 55.4  | 52.6  | 49.9  | 49.9  | 47.1   | 44.3  |
| 0.0 | 15°    | 49.9  | 47.1  | 44.3  | 41.6  | 38.8  | 36.0  | 33.2  | 33.2  | 30.5   | 27.7  |
| 0.0 | 17.5°  | 33.2  | 27.7  | 24.9  | 22.2  | 22.2  | 19.4  | 16.6  | 13.9  | 11.1   | 8.3   |
| 0.0 | 20°    | 8.3   | 5.5   | 2.8   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
| 0.0 | 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 90°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 92.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 95°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 97.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 100°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 102.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 105°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 107.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |
|     | 110°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110°  | 112.5° | 115°  | 117.5° | 120°  | 122.5° | 125°  | 127.5° | 130°  | 132.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  |
| 0.0    | 2.5°   | 113.6 | 110.8  | 110.8 | 110.8  | 113.6 | 113.6  | 113.6 | 113.6  | 113.6 | 113.6  |
| 0.0    | 5°     | 91.4  | 88.6   | 88.6  | 88.6   | 88.6  | 88.6   | 88.6  | 88.6   | 88.6  | 88.6   |
| 0.0    | 7.5°   | 74.8  | 72.0   | 72.0  | 72.0   | 72.0  | 69.3   | 69.3  | 69.3   | 69.3  | 69.3   |
| 0.0    | 10°    | 58.2  | 55.4   | 55.4  | 55.4   | 55.4  | 52.6   | 52.6  | 52.6   | 52.6  | 52.6   |
| 0.0    | 12.5°  | 41.6  | 41.6   | 38.8  | 38.8   | 38.8  | 36.0   | 36.0  | 36.0   | 36.0  | 33.2   |
| 0.0    | 15°    | 24.9  | 22.2   | 19.4  | 19.4   | 19.4  | 16.6   | 16.6  | 16.6   | 16.6  | 13.9   |
| 0.0    | 17.5°  | 5.5   | 5.5    | 2.8   | 2.8    | 2.8   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 20°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 22.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 25°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 87.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

CATALOG NUMBER: GALN-SA8C-840-U-RBC

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140°  | 142.5° | 145°  | 147.5° | 150°  | 152.5° | 155°  | 157.5° | 160°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 |
| 0.0  | 2.5°   | 116.3  | 116.3 | 119.1  | 119.1 | 121.9  | 127.4 | 130.2  | 133.0 | 138.5  | 144.0 |
| 0.0  | 5°     | 91.4   | 94.2  | 94.2   | 97.0  | 99.7   | 102.5 | 105.3  | 108.0 | 113.6  | 119.1 |
| 0.0  | 7.5°   | 72.0   | 72.0  | 74.8   | 74.8  | 77.6   | 83.1  | 85.9   | 88.6  | 94.2   | 102.5 |
| 0.0  | 10°    | 55.4   | 55.4  | 58.2   | 58.2  | 60.9   | 66.5  | 69.3   | 72.0  | 77.6   | 85.9  |
| 0.0  | 12.5°  | 36.0   | 38.8  | 38.8   | 41.6  | 44.3   | 49.9  | 52.6   | 55.4  | 60.9   | 66.5  |
| 0.0  | 15°    | 16.6   | 19.4  | 19.4   | 22.2  | 24.9   | 30.5  | 33.2   | 36.0  | 41.6   | 49.9  |
| 0.0  | 17.5°  | 2.8    | 2.8   | 5.5    | 5.5   | 8.3    | 11.1  | 13.9   | 16.6  | 24.9   | 30.5  |
| 0.0  | 20°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.5    | 11.1  |
| 0.0  | 22.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 2.8   |
| 0.0  | 25°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 27.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 30°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 32.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 80°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 82.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 85°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 87.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165°  | 167.5° | 170°  | 172.5° | 175°  | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  |
| 0.0    | 2.5°   | 152.4 | 157.9  | 163.4 | 169.0  | 174.5 | 180.1  | 182.8 | 188.4  | 191.1 | 193.9  |
| 0.0    | 5°     | 130.2 | 135.7  | 144.0 | 149.6  | 155.1 | 160.7  | 166.2 | 169.0  | 171.7 | 174.5  |
| 0.0    | 7.5°   | 113.6 | 119.1  | 127.4 | 133.0  | 138.5 | 144.0  | 149.6 | 155.1  | 157.9 | 160.7  |
| 0.0    | 10°    | 97.0  | 105.3  | 110.8 | 119.1  | 124.7 | 130.2  | 135.7 | 141.3  | 146.8 | 149.6  |
| 0.0    | 12.5°  | 77.6  | 85.9   | 94.2  | 99.7   | 108.0 | 116.3  | 121.9 | 127.4  | 133.0 | 138.5  |
| 0.0    | 15°    | 60.9  | 69.3   | 77.6  | 83.1   | 91.4  | 99.7   | 108.0 | 113.6  | 119.1 | 124.7  |
| 0.0    | 17.5°  | 44.3  | 52.6   | 60.9  | 66.5   | 74.8  | 83.1   | 88.6  | 97.0   | 102.5 | 108.0  |
| 0.0    | 20°    | 22.2  | 30.5   | 38.8  | 47.1   | 55.4  | 63.7   | 69.3  | 77.6   | 83.1  | 88.6   |
| 0.0    | 22.5°  | 2.8   | 11.1   | 19.4  | 24.9   | 33.2  | 41.6   | 47.1  | 55.4   | 60.9  | 66.5   |
| 0.0    | 25°    | 0.0   | 2.8    | 8.3   | 11.1   | 13.9  | 19.4   | 24.9  | 30.5   | 36.0  | 41.6   |
| 0.0    | 27.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 5.5   | 11.1   | 16.6  | 22.2   |
| 0.0    | 30°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.5    |
| 0.0    | 32.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    |
|        | 82.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 2.8   | 5.5    |
|        | 85°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 5.5    | 8.3   | 13.9   | 16.6  | 19.4   |
|        | 87.5°  | 0.0   | 2.8    | 5.5   | 8.3    | 11.1  | 16.6   | 22.2  | 27.7   | 30.5  | 33.2   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 160.7 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 193.9 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.3 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 163.4 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 155.1 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 141.3 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 130.2 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 116.3 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 94.2  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.0  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 49.9  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8.3   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 2.8   |        |      |        |      |        |      |        |      |        |      |        |
| 11.1  |        |      |        |      |        |      |        |      |        |      |        |
| 24.9  |        |      |        |      |        |      |        |      |        |      |        |
| 36.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 |
| 0.0  | 2.5°   | 196.7  | 196.7 | 196.7  | 196.7 | 193.9  | 193.9 | 193.9  | 191.1 | 191.1  | 188.4 |
| 0.0  | 5°     | 180.1  | 182.8 | 182.8  | 182.8 | 182.8  | 182.8 | 182.8  | 182.8 | 180.1  | 180.1 |
| 0.0  | 7.5°   | 166.2  | 169.0 | 171.7  | 171.7 | 174.5  | 174.5 | 174.5  | 171.7 | 171.7  | 169.0 |
| 0.0  | 10°    | 157.9  | 160.7 | 160.7  | 163.4 | 163.4  | 163.4 | 163.4  | 163.4 | 163.4  | 163.4 |
| 0.0  | 12.5°  | 146.8  | 149.6 | 152.4  | 152.4 | 155.1  | 155.1 | 155.1  | 155.1 | 152.4  | 152.4 |
| 0.0  | 15°    | 133.0  | 138.5 | 141.3  | 144.0 | 144.0  | 146.8 | 146.8  | 146.8 | 146.8  | 146.8 |
| 0.0  | 17.5°  | 121.9  | 127.4 | 130.2  | 133.0 | 133.0  | 135.7 | 135.7  | 138.5 | 138.5  | 138.5 |
| 0.0  | 20°    | 99.7   | 105.3 | 108.0  | 113.6 | 116.3  | 119.1 | 121.9  | 124.7 | 124.7  | 127.4 |
| 0.0  | 22.5°  | 77.6   | 83.1  | 85.9   | 91.4  | 94.2   | 97.0  | 99.7   | 102.5 | 105.3  | 108.0 |
| 0.0  | 25°    | 55.4   | 60.9  | 63.7   | 69.3  | 72.0   | 74.8  | 77.6   | 80.3  | 80.3   | 83.1  |
| 0.0  | 27.5°  | 30.5   | 36.0  | 41.6   | 44.3  | 49.9   | 52.6  | 55.4   | 58.2  | 60.9   | 63.7  |
| 0.0  | 30°    | 13.9   | 16.6  | 19.4   | 24.9  | 27.7   | 30.5  | 33.2   | 38.8  | 41.6   | 44.3  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 2.8    | 8.3   | 11.1   | 13.9  | 16.6   | 19.4  | 19.4   | 22.2  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 2.8    | 5.5   | 8.3    | 11.1  |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 5.5    | 5.5   | 5.5    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   | 8.3    | 8.3   |
|      | 82.5°  | 13.9   | 16.6  | 19.4   | 19.4  | 22.2   | 22.2  | 22.2   | 22.2  | 19.4   | 19.4  |
|      | 85°    | 27.7   | 30.5  | 33.2   | 33.2  | 36.0   | 36.0  | 36.0   | 36.0  | 36.0   | 36.0  |
|      | 87.5°  | 38.8   | 41.6  | 44.3   | 44.3  | 47.1   | 47.1  | 47.1   | 47.1  | 47.1   | 47.1  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 160.7  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 188.4  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 180.1  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 169.0  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 163.4  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.4  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 146.8  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 138.5  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124.7  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 108.0  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 85.9   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 66.5   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.1   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.7   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 16.6   | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.5    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.5    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.8    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.8    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.8    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.8    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2.8    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 8.3    |        |        |      |        |      |        |      |        |      |        |      |
| 19.4   |        |        |      |        |      |        |      |        |      |        |      |
| 36.0   |        |        |      |        |      |        |      |        |      |        |      |
| 47.1   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  |
| 0.0    | 2.5°   | 185.6 | 185.6  | 182.8 | 182.8  | 182.8 | 182.8  | 182.8 | 185.6  | 188.4 | 188.4  |
| 0.0    | 5°     | 177.3 | 177.3  | 174.5 | 174.5  | 174.5 | 177.3  | 177.3 | 180.1  | 182.8 | 185.6  |
| 0.0    | 7.5°   | 169.0 | 166.2  | 166.2 | 169.0  | 169.0 | 171.7  | 171.7 | 174.5  | 177.3 | 180.1  |
| 0.0    | 10°    | 163.4 | 160.7  | 160.7 | 160.7  | 163.4 | 163.4  | 166.2 | 169.0  | 171.7 | 174.5  |
| 0.0    | 12.5°  | 152.4 | 152.4  | 152.4 | 152.4  | 155.1 | 155.1  | 157.9 | 160.7  | 166.2 | 169.0  |
| 0.0    | 15°    | 146.8 | 144.0  | 144.0 | 144.0  | 144.0 | 146.8  | 146.8 | 152.4  | 157.9 | 160.7  |
| 0.0    | 17.5°  | 135.7 | 135.7  | 133.0 | 133.0  | 135.7 | 135.7  | 138.5 | 144.0  | 149.6 | 152.4  |
| 0.0    | 20°    | 124.7 | 121.9  | 119.1 | 119.1  | 121.9 | 121.9  | 124.7 | 130.2  | 135.7 | 138.5  |
| 0.0    | 22.5°  | 108.0 | 105.3  | 105.3 | 105.3  | 105.3 | 108.0  | 108.0 | 113.6  | 121.9 | 127.4  |
| 0.0    | 25°    | 85.9  | 88.6   | 88.6  | 91.4   | 91.4  | 94.2   | 97.0  | 102.5  | 110.8 | 116.3  |
| 0.0    | 27.5°  | 66.5  | 69.3   | 69.3  | 74.8   | 77.6  | 80.3   | 83.1  | 91.4   | 99.7  | 105.3  |
| 0.0    | 30°    | 49.9  | 52.6   | 55.4  | 58.2   | 63.7  | 69.3   | 74.8  | 83.1   | 91.4  | 97.0   |
| 0.0    | 32.5°  | 30.5  | 36.0   | 38.8  | 44.3   | 49.9  | 55.4   | 60.9  | 69.3   | 80.3  | 88.6   |
| 0.0    | 35°    | 22.2  | 24.9   | 30.5  | 33.2   | 38.8  | 44.3   | 49.9  | 60.9   | 69.3  | 80.3   |
| 0.0    | 37.5°  | 11.1  | 16.6   | 22.2  | 27.7   | 33.2  | 38.8   | 44.3  | 55.4   | 66.5  | 74.8   |
| 0.0    | 40°    | 8.3   | 13.9   | 16.6  | 22.2   | 30.5  | 36.0   | 41.6  | 52.6   | 63.7  | 74.8   |
| 0.0    | 42.5°  | 5.5   | 8.3    | 11.1  | 19.4   | 24.9  | 33.2   | 41.6  | 52.6   | 63.7  | 74.8   |
| 0.0    | 45°    | 5.5   | 5.5    | 8.3   | 16.6   | 24.9  | 36.0   | 44.3  | 55.4   | 63.7  | 74.8   |
| 0.0    | 47.5°  | 5.5   | 8.3    | 11.1  | 22.2   | 27.7  | 36.0   | 44.3  | 52.6   | 63.7  | 72.0   |
| 0.0    | 50°    | 8.3   | 11.1   | 13.9  | 24.9   | 30.5  | 38.8   | 44.3  | 55.4   | 63.7  | 74.8   |
| 0.0    | 52.5°  | 5.5   | 8.3    | 11.1  | 22.2   | 30.5  | 41.6   | 49.9  | 60.9   | 72.0  | 80.3   |
| 0.0    | 55°    | 2.8   | 2.8    | 2.8   | 16.6   | 33.2  | 47.1   | 63.7  | 72.0   | 83.1  | 91.4   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 11.1   | 33.2  | 52.6   | 72.0  | 83.1   | 94.2  | 102.5  |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 11.1   | 33.2  | 52.6   | 72.0  | 85.9   | 99.7  | 113.6  |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 11.1   | 27.7  | 44.3   | 60.9  | 83.1   | 108.0 | 130.2  |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 8.3    | 22.2  | 36.0   | 49.9  | 83.1   | 116.3 | 146.8  |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 8.3    | 22.2  | 33.2   | 47.1  | 83.1   | 116.3 | 152.4  |
|        | 70°    | 0.0   | 0.0    | 0.0   | 8.3    | 22.2  | 36.0   | 49.9  | 83.1   | 116.3 | 149.6  |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 8.3    | 24.9  | 38.8   | 55.4  | 83.1   | 110.8 | 138.5  |
|        | 75°    | 0.0   | 0.0    | 0.0   | 11.1   | 24.9  | 41.6   | 58.2  | 83.1   | 108.0 | 130.2  |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 8.3    | 24.9  | 38.8   | 55.4  | 80.3   | 105.3 | 127.4  |
|        | 80°    | 8.3   | 5.5    | 5.5   | 13.9   | 24.9  | 36.0   | 47.1  | 72.0   | 99.7  | 124.7  |
|        | 82.5°  | 16.6  | 16.6   | 13.9  | 19.4   | 24.9  | 33.2   | 41.6  | 63.7   | 88.6  | 110.8  |
|        | 85°    | 33.2  | 33.2   | 30.5  | 33.2   | 33.2  | 36.0   | 38.8  | 49.9   | 60.9  | 72.0   |
|        | 87.5°  | 44.3  | 44.3   | 41.6  | 41.6   | 41.6  | 38.8   | 38.8  | 38.8   | 38.8  | 36.0   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 160.7 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 191.1 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 188.4 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 182.8 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 177.3 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 171.7 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 166.2 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 157.9 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 144.0 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 133.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 121.9 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 113.6 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.3 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.6  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.9  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.9  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.9  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.1  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.3  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 83.1  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 91.4  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 99.7  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 113.6 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.4 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 152.4 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 180.1 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 185.6 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 182.8 |        |      |        |      |        |      |        |      |        |      |        |
| 166.2 |        |      |        |      |        |      |        |      |        |      |        |
| 155.1 |        |      |        |      |        |      |        |      |        |      |        |
| 152.4 |        |      |        |      |        |      |        |      |        |      |        |
| 149.6 |        |      |        |      |        |      |        |      |        |      |        |
| 133.0 |        |      |        |      |        |      |        |      |        |      |        |
| 83.1  |        |      |        |      |        |      |        |      |        |      |        |
| 36.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7 | 160.7  | 160.7  |
| 0.0  | 2.5°   | 193.9  | 196.7 | 196.7  | 199.4 | 202.2  | 205.0 | 205.0  | 207.8 | 207.8  | 207.8  |
| 0.0  | 5°     | 191.1  | 196.7 | 199.4  | 202.2 | 205.0  | 207.8 | 210.5  | 213.3 | 216.1  | 216.1  |
| 0.0  | 7.5°   | 188.4  | 191.1 | 196.7  | 199.4 | 205.0  | 207.8 | 213.3  | 216.1 | 218.8  | 221.6  |
| 0.0  | 10°    | 182.8  | 188.4 | 193.9  | 199.4 | 205.0  | 210.5 | 216.1  | 221.6 | 227.1  | 229.9  |
| 0.0  | 12.5°  | 177.3  | 185.6 | 191.1  | 196.7 | 205.0  | 213.3 | 218.8  | 227.1 | 232.7  | 238.2  |
| 0.0  | 15°    | 174.5  | 180.1 | 188.4  | 193.9 | 205.0  | 216.1 | 224.4  | 235.5 | 246.5  | 254.8  |
| 0.0  | 17.5°  | 166.2  | 177.3 | 185.6  | 193.9 | 205.0  | 218.8 | 229.9  | 241.0 | 257.6  | 274.2  |
| 0.0  | 20°    | 155.1  | 163.4 | 174.5  | 182.8 | 199.4  | 213.3 | 229.9  | 243.8 | 268.7  | 293.6  |
| 0.0  | 22.5°  | 144.0  | 155.1 | 163.4  | 174.5 | 193.9  | 210.5 | 229.9  | 246.5 | 288.1  | 326.9  |
| 0.0  | 25°    | 133.0  | 146.8 | 157.9  | 169.0 | 191.1  | 213.3 | 235.5  | 257.6 | 326.9  | 396.1  |
| 0.0  | 27.5°  | 127.4  | 138.5 | 152.4  | 163.4 | 191.1  | 221.6 | 249.3  | 277.0 | 387.8  | 495.8  |
| 0.0  | 30°    | 119.1  | 133.0 | 144.0  | 157.9 | 193.9  | 229.9 | 265.9  | 301.9 | 470.9  | 639.9  |
| 0.0  | 32.5°  | 110.8  | 124.7 | 138.5  | 152.4 | 199.4  | 246.5 | 290.9  | 337.9 | 559.5  | 778.4  |
| 0.0  | 35°    | 102.5  | 119.1 | 133.0  | 146.8 | 207.8  | 271.5 | 332.4  | 393.3 | 639.9  | 883.6  |
| 0.0  | 37.5°  | 99.7   | 116.3 | 130.2  | 144.0 | 210.5  | 274.2 | 340.7  | 404.4 | 648.2  | 891.9  |
| 0.0  | 40°    | 102.5  | 116.3 | 133.0  | 146.8 | 202.2  | 257.6 | 310.2  | 365.6 | 620.5  | 872.6  |
| 0.0  | 42.5°  | 102.5  | 119.1 | 135.7  | 152.4 | 196.7  | 241.0 | 285.3  | 329.6 | 612.2  | 894.7  |
| 0.0  | 45°    | 99.7   | 116.3 | 133.0  | 149.6 | 191.1  | 229.9 | 271.5  | 310.2 | 662.0  | 1011.1 |
| 0.0  | 47.5°  | 97.0   | 113.6 | 130.2  | 146.8 | 188.4  | 229.9 | 271.5  | 313.0 | 855.9  | 1396.1 |
| 0.0  | 50°    | 97.0   | 113.6 | 127.4  | 141.3 | 191.1  | 243.8 | 293.6  | 343.5 | 1246.5 | 2146.8 |
| 0.0  | 52.5°  | 102.5  | 116.3 | 127.4  | 138.5 | 196.7  | 257.6 | 315.8  | 374.0 | 1584.5 | 2792.2 |
| 0.0  | 55°    | 110.8  | 119.1 | 130.2  | 138.5 | 210.5  | 279.8 | 351.8  | 421.0 | 1686.9 | 2952.9 |
| 0.0  | 57.5°  | 121.9  | 130.2 | 138.5  | 146.8 | 235.5  | 324.1 | 410.0  | 498.6 | 1695.3 | 2889.1 |
| 0.0  | 60°    | 135.7  | 146.8 | 155.1  | 163.4 | 257.6  | 354.6 | 448.7  | 542.9 | 1534.6 | 2523.5 |
| 0.0  | 62.5°  | 166.2  | 180.1 | 191.1  | 205.0 | 296.4  | 385.0 | 476.4  | 565.1 | 1274.2 | 1983.3 |
| 0.0  | 65°    | 191.1  | 202.2 | 213.3  | 224.4 | 313.0  | 404.4 | 493.1  | 581.7 | 1080.3 | 1578.9 |
| 0.0  | 67.5°  | 196.7  | 207.8 | 216.1  | 227.1 | 318.6  | 410.0 | 498.6  | 590.0 | 925.2  | 1257.6 |
|      | 70°    | 199.4  | 213.3 | 229.9  | 243.8 | 337.9  | 432.1 | 523.5  | 617.7 | 819.9  | 1022.1 |
|      | 72.5°  | 191.1  | 218.8 | 243.8  | 268.7 | 357.3  | 443.2 | 531.8  | 617.7 | 761.8  | 905.8  |
|      | 75°    | 191.1  | 229.9 | 265.9  | 301.9 | 368.4  | 432.1 | 498.6  | 562.3 | 673.1  | 783.9  |
|      | 77.5°  | 202.2  | 252.1 | 301.9  | 351.8 | 390.6  | 426.6 | 465.4  | 501.4 | 573.4  | 645.4  |
|      | 80°    | 202.2  | 254.8 | 304.7  | 357.3 | 374.0  | 393.3 | 410.0  | 426.6 | 434.9  | 443.2  |
|      | 82.5°  | 174.5  | 216.1 | 257.6  | 299.2 | 279.8  | 260.4 | 241.0  | 221.6 | 207.8  | 191.1  |
|      | 85°    | 88.6   | 97.0  | 102.5  | 108.0 | 99.7   | 91.4  | 83.1   | 74.8  | 69.3   | 60.9   |
|      | 87.5°  | 36.0   | 36.0  | 33.2   | 33.2  | 33.2   | 33.2  | 30.5   | 30.5  | 30.5   | 30.5   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 160.7  | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 207.8  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 216.1  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 224.4  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 235.5  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 246.5  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 268.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 296.4  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 340.7  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 434.9  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 590.0  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 819.9  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1110.8 | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1387.8 | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1576.1 | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1717.4 | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1858.7 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2135.7 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2689.7 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4099.6 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6279.7 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7905.7 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 8085.7 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 7296.3 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 6238.1 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4875.3 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3684.1 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2720.2 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1925.2 |        |        |      |        |      |        |      |        |      |        |      |
| 1432.1 |        |        |      |        |      |        |      |        |      |        |      |
| 1041.5 |        |        |      |        |      |        |      |        |      |        |      |
| 783.9  |        |        |      |        |      |        |      |        |      |        |      |
| 440.4  |        |        |      |        |      |        |      |        |      |        |      |
| 199.4  |        |        |      |        |      |        |      |        |      |        |      |
| 58.2   |        |        |      |        |      |        |      |        |      |        |      |
| 27.7   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°    | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   |
| 0.0    | 2.5°   | 207.8   | 205.0   | 205.0   | 202.2   | 199.4   | 196.7   | 193.9   | 191.1   | 188.4   | 185.6   |
| 0.0    | 5°     | 216.1   | 216.1   | 216.1   | 213.3   | 213.3   | 210.5   | 210.5   | 207.8   | 205.0   | 202.2   |
| 0.0    | 7.5°   | 224.4   | 227.1   | 227.1   | 229.9   | 229.9   | 229.9   | 229.9   | 227.1   | 227.1   | 227.1   |
| 0.0    | 10°    | 238.2   | 241.0   | 243.8   | 246.5   | 249.3   | 252.1   | 252.1   | 254.8   | 254.8   | 254.8   |
| 0.0    | 12.5°  | 254.8   | 263.2   | 268.7   | 277.0   | 282.5   | 290.9   | 296.4   | 304.7   | 310.2   | 315.8   |
| 0.0    | 15°    | 279.8   | 293.6   | 310.2   | 324.1   | 337.9   | 357.3   | 379.5   | 398.9   | 418.3   | 448.7   |
| 0.0    | 17.5°  | 315.8   | 360.1   | 404.4   | 446.0   | 490.3   | 587.2   | 684.2   | 778.4   | 875.3   | 1016.6  |
| 0.0    | 20°    | 385.0   | 518.0   | 648.2   | 781.1   | 911.3   | 1252.1  | 1590.0  | 1930.7  | 2268.7  | 2631.5  |
| 0.0    | 22.5°  | 540.2   | 867.0   | 1193.9  | 1520.7  | 1847.6  | 2559.5  | 3268.6  | 3980.5  | 4689.7  | 5523.4  |
| 0.0    | 25°    | 783.9   | 1385.0  | 1986.1  | 2584.4  | 3185.5  | 4299.1  | 5415.4  | 6529.0  | 7642.5  | 8725.6  |
| 0.0    | 27.5°  | 1141.3  | 2060.9  | 2980.6  | 3897.4  | 4817.1  | 6326.7  | 7839.2  | 9348.9  | 10858.5 | 12082.9 |
| 0.0    | 30°    | 1581.7  | 2828.2  | 4074.7  | 5321.2  | 6567.7  | 8285.2  | 10002.6 | 11717.2 | 13434.6 | 14772.6 |
| 0.0    | 32.5°  | 1997.2  | 3523.5  | 5049.8  | 6573.3  | 8099.6  | 10055.2 | 12013.6 | 13969.3 | 15924.9 | 17387.5 |
| 0.0    | 35°    | 2268.7  | 4113.5  | 5961.1  | 7805.9  | 9650.8  | 11767.1 | 13883.4 | 15996.9 | 18113.2 | 19783.6 |
| 0.0    | 37.5°  | 2540.1  | 4670.3  | 6797.7  | 8927.8  | 11055.2 | 13379.2 | 15703.3 | 18027.4 | 20351.4 | 22415.1 |
| 0.0    | 40°    | 2844.8  | 5343.4  | 7839.2  | 10337.8 | 12833.5 | 15587.0 | 18337.6 | 21091.0 | 23841.6 | 26752.9 |
| 0.0    | 42.5°  | 3373.9  | 6459.7  | 9548.3  | 12634.1 | 15719.9 | 19362.5 | 23005.1 | 26644.9 | 30287.5 | 34442.6 |
| 0.0    | 45°    | 4368.3  | 8717.3  | 13069.0 | 17417.9 | 21766.9 | 26592.3 | 31420.4 | 36245.8 | 41071.2 | 46600.2 |
| 0.0    | 47.5°  | 6803.2  | 12786.5 | 18767.0 | 24750.2 | 30730.7 | 35941.1 | 41148.8 | 46359.2 | 51566.9 | 57073.7 |
| 0.0    | 50°    | 10409.8 | 17373.6 | 24337.5 | 31298.6 | 38262.4 | 42977.0 | 47688.8 | 52403.4 | 57115.2 | 62353.4 |
| 0.0    | 52.5°  | 13019.1 | 20273.8 | 27531.3 | 34786.0 | 42040.7 | 46295.5 | 50553.0 | 54807.8 | 59062.6 | 63957.2 |
| 0.0    | 55°    | 13215.8 | 20429.0 | 27644.9 | 34858.1 | 42071.2 | 46345.4 | 50619.5 | 54893.7 | 59167.8 | 64356.1 |
| 0.0    | 57.5°  | 11700.6 | 18855.6 | 26007.8 | 33162.8 | 40315.0 | 45182.0 | 50046.1 | 54913.1 | 59777.2 | 65386.6 |
| 0.0    | 60°    | 9952.7  | 17110.5 | 24265.5 | 31423.2 | 38578.2 | 44184.7 | 49794.1 | 55400.6 | 61007.1 | 66261.9 |
| 0.0    | 62.5°  | 7764.4  | 15127.1 | 22492.6 | 29855.4 | 37218.1 | 42910.5 | 48602.9 | 54292.6 | 59985.0 | 63926.8 |
| 0.0    | 65°    | 5786.6  | 12936.0 | 20085.5 | 27232.2 | 34381.6 | 38941.1 | 43500.6 | 48057.2 | 52616.7 | 55057.1 |
| 0.0    | 67.5°  | 4182.7  | 10348.8 | 16512.1 | 22678.2 | 28841.6 | 32104.6 | 35367.7 | 38628.1 | 41891.2 | 43758.2 |
|        | 70°    | 2828.2  | 7099.6  | 11368.2 | 15639.6 | 19908.2 | 22589.6 | 25273.8 | 27955.1 | 30636.5 | 33157.3 |
|        | 72.5°  | 1958.4  | 4357.3  | 6758.9  | 9157.7  | 11556.6 | 14254.6 | 16949.8 | 19647.8 | 22343.1 | 25010.6 |
|        | 75°    | 1299.1  | 2390.5  | 3484.7  | 4576.1  | 5667.5  | 7664.7  | 9664.6  | 11661.8 | 13659.0 | 15249.0 |
|        | 77.5°  | 922.4   | 1249.3  | 1578.9  | 1905.8  | 2232.6  | 2606.6  | 2983.3  | 3357.3  | 3731.2  | 4299.1  |
|        | 80°    | 437.7   | 479.2   | 520.8   | 559.5   | 601.1   | 736.8   | 872.6   | 1008.3  | 1144.0  | 1288.1  |
|        | 82.5°  | 207.8   | 224.4   | 241.0   | 254.8   | 271.5   | 285.3   | 299.2   | 313.0   | 326.9   | 313.0   |
|        | 85°    | 55.4    | 55.4    | 58.2    | 58.2    | 58.2    | 58.2    | 58.2    | 58.2    | 58.2    | 55.4    |
|        | 87.5°  | 24.9    | 24.9    | 24.9    | 24.9    | 24.9    | 24.9    | 24.9    | 22.2    | 22.2    | 19.4    |
|        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 160.7   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 182.8   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 199.4   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 224.4   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 257.6   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 318.6   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 482.0   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1155.1  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2997.2  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6357.2  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9808.7  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13307.2 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16113.3 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18852.8 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21453.9 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24481.5 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29664.3 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38597.6 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52129.2 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62580.5 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67591.5 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 68851.9 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69547.1 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70995.9 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 71513.9 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67871.3 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57500.3 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45627.9 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35675.2 |        |      |        |      |        |      |        |      |        |      |        |
| 27678.1 |        |      |        |      |        |      |        |      |        |      |        |
| 16839.0 |        |      |        |      |        |      |        |      |        |      |        |
| 4866.9  |        |      |        |      |        |      |        |      |        |      |        |
| 1432.1  |        |      |        |      |        |      |        |      |        |      |        |
| 296.4   |        |      |        |      |        |      |        |      |        |      |        |
| 52.6    |        |      |        |      |        |      |        |      |        |      |        |
| 19.4    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   |
| 0.0  | 2.5°   | 180.1   | 177.3   | 174.5   | 171.7   | 169.0   | 163.4   | 163.4   | 160.7   | 160.7   |
| 0.0  | 5°     | 196.7   | 193.9   | 191.1   | 188.4   | 188.4   | 185.6   | 182.8   | 182.8   | 180.1   |
| 0.0  | 7.5°   | 224.4   | 221.6   | 218.8   | 216.1   | 216.1   | 213.3   | 213.3   | 210.5   | 210.5   |
| 0.0  | 10°    | 257.6   | 257.6   | 257.6   | 257.6   | 257.6   | 254.8   | 254.8   | 254.8   | 252.1   |
| 0.0  | 12.5°  | 324.1   | 326.9   | 332.4   | 337.9   | 346.3   | 346.3   | 346.3   | 343.5   | 343.5   |
| 0.0  | 15°    | 512.5   | 542.9   | 565.1   | 587.2   | 606.6   | 651.0   | 645.4   | 637.1   | 631.6   |
| 0.0  | 17.5°  | 1296.4  | 1434.9  | 1509.7  | 1581.7  | 1656.5  | 1861.5  | 1828.2  | 1795.0  | 1764.5  |
| 0.0  | 20°    | 3360.0  | 3722.9  | 3963.9  | 4204.9  | 4448.7  | 4833.7  | 4739.5  | 4645.3  | 4551.2  |
| 0.0  | 22.5°  | 7188.2  | 8022.0  | 8384.9  | 8747.8  | 9107.9  | 9573.2  | 9271.3  | 8969.4  | 8670.2  |
| 0.0  | 25°    | 10889.0 | 11972.1 | 12584.2 | 13196.4 | 13805.8 | 14071.8 | 13678.4 | 13282.3 | 12888.9 |
| 0.0  | 27.5°  | 14531.6 | 15755.9 | 16296.1 | 16833.5 | 17373.6 | 17930.4 | 17442.9 | 16952.6 | 16465.1 |
| 0.0  | 30°    | 17451.2 | 18789.1 | 19373.6 | 19955.3 | 20539.8 | 20927.6 | 20423.4 | 19916.5 | 19412.4 |
| 0.0  | 32.5°  | 20315.4 | 21778.0 | 22417.9 | 23057.7 | 23694.8 | 24251.6 | 23631.1 | 23007.9 | 22387.4 |
| 0.0  | 35°    | 23121.4 | 24791.8 | 25672.6 | 26553.5 | 27434.4 | 27952.4 | 27215.5 | 26475.9 | 25739.1 |
| 0.0  | 37.5°  | 26545.2 | 28608.9 | 29595.0 | 30581.1 | 31567.3 | 32511.8 | 31700.2 | 30885.8 | 30074.2 |
| 0.0  | 40°    | 32575.6 | 35486.9 | 36999.3 | 38514.5 | 40026.9 | 41245.7 | 40220.8 | 39195.9 | 38171.0 |
| 0.0  | 42.5°  | 42752.6 | 46907.7 | 49082.2 | 51253.9 | 53428.3 | 55331.3 | 54253.8 | 53176.3 | 52098.7 |
| 0.0  | 45°    | 57658.2 | 63187.2 | 65838.1 | 68486.2 | 71137.1 | 72527.7 | 70976.5 | 69422.5 | 67871.3 |
| 0.0  | 47.5°  | 68084.6 | 73591.4 | 75951.5 | 78311.5 | 80671.6 | 82258.8 | 80361.3 | 78463.9 | 76569.2 |
| 0.0  | 50°    | 72826.9 | 78065.0 | 80433.4 | 82799.0 | 85167.3 | 86427.7 | 84236.6 | 82042.7 | 79851.7 |
| 0.0  | 52.5°  | 73743.7 | 78638.4 | 81463.8 | 84292.0 | 87117.4 | 88801.6 | 86214.4 | 83624.4 | 81037.2 |
| 0.0  | 55°    | 74735.4 | 79923.7 | 83200.6 | 86480.3 | 89757.3 | 92089.6 | 89164.5 | 86236.6 | 83311.4 |
| 0.0  | 57.5°  | 76602.4 | 82211.7 | 85480.4 | 88746.2 | 92014.9 | 93995.4 | 91062.0 | 88125.7 | 85192.3 |
| 0.0  | 60°    | 76768.6 | 82020.6 | 84829.4 | 87641.0 | 90449.8 | 91696.3 | 88890.3 | 86081.5 | 83275.4 |
| 0.0  | 62.5°  | 71813.0 | 75754.8 | 77704.9 | 79655.0 | 81605.1 | 82959.6 | 80031.7 | 77101.0 | 74173.1 |
| 0.0  | 65°    | 59940.7 | 62381.1 | 63935.1 | 65489.0 | 67043.0 | 68658.0 | 65976.6 | 63295.2 | 60613.8 |
| 0.0  | 67.5°  | 47494.9 | 49361.9 | 51409.0 | 53456.0 | 55503.1 | 57228.8 | 55082.0 | 52932.5 | 50785.7 |
|      | 70°    | 38195.9 | 40713.9 | 43015.8 | 45317.7 | 47619.6 | 49032.3 | 46877.2 | 44719.4 | 42564.3 |
|      | 72.5°  | 30345.7 | 33013.2 | 34935.6 | 36855.2 | 38777.6 | 39123.9 | 37539.4 | 35955.0 | 34373.3 |
|      | 75°    | 18426.2 | 20016.2 | 20055.0 | 20091.0 | 20129.8 | 20459.4 | 19146.4 | 17833.5 | 16523.2 |
|      | 77.5°  | 5434.8  | 6002.7  | 6470.8  | 6936.2  | 7404.3  | 7969.4  | 7487.4  | 7002.6  | 6520.7  |
|      | 80°    | 1573.4  | 1717.4  | 1839.3  | 1958.4  | 2080.3  | 2008.3  | 1894.7  | 1781.1  | 1667.6  |
|      | 82.5°  | 282.5   | 265.9   | 263.2   | 260.4   | 260.4   | 246.5   | 224.4   | 202.2   | 180.1   |
|      | 85°    | 49.9    | 47.1    | 44.3    | 41.6    | 38.8    | 36.0    | 30.5    | 27.7    | 22.2    |
|      | 87.5°  | 16.6    | 13.9    | 11.1    | 8.3     | 8.3     | 2.8     | 2.8     | 2.8     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   | 160.7   |
| 0.0  | 0.0    | 2.5°   | 157.9   | 155.1   | 155.1   | 155.1   | 155.1   | 152.4   | 152.4   | 152.4   | 152.4   |
| 0.0  | 0.0    | 5°     | 174.5   | 174.5   | 171.7   | 171.7   | 169.0   | 169.0   | 166.2   | 166.2   | 163.4   |
| 0.0  | 0.0    | 7.5°   | 205.0   | 202.2   | 199.4   | 196.7   | 193.9   | 188.4   | 185.6   | 182.8   | 182.8   |
| 0.0  | 0.0    | 10°    | 246.5   | 241.0   | 238.2   | 232.7   | 229.9   | 224.4   | 218.8   | 213.3   | 207.8   |
| 0.0  | 0.0    | 12.5°  | 324.1   | 313.0   | 304.7   | 293.6   | 282.5   | 274.2   | 263.2   | 254.8   | 243.8   |
| 0.0  | 0.0    | 15°    | 562.3   | 534.6   | 504.1   | 468.1   | 429.4   | 393.3   | 354.6   | 332.4   | 307.5   |
| 0.0  | 0.0    | 17.5°  | 1437.6  | 1293.6  | 1146.8  | 1027.7  | 908.6   | 792.2   | 673.1   | 587.2   | 501.4   |
| 0.0  | 0.0    | 20°    | 3659.2  | 3260.3  | 2861.4  | 2468.1  | 2072.0  | 1678.6  | 1282.5  | 1083.1  | 883.6   |
| 0.0  | 0.0    | 22.5°  | 6886.3  | 6146.7  | 5404.3  | 4686.9  | 3966.7  | 3249.2  | 2531.8  | 2080.3  | 1631.5  |
| 0.0  | 0.0    | 25°    | 10628.6 | 9697.9  | 8767.1  | 7587.1  | 6404.3  | 5224.3  | 4044.2  | 3310.2  | 2576.1  |
| 0.0  | 0.0    | 27.5°  | 13830.8 | 12758.8 | 11686.8 | 10251.9 | 8817.0  | 7382.1  | 5947.3  | 4853.1  | 3761.7  |
| 0.0  | 0.0    | 30°    | 16603.6 | 15451.2 | 14298.9 | 12628.6 | 10958.2 | 9287.9  | 7617.6  | 6249.2  | 4880.8  |
| 0.0  | 0.0    | 32.5°  | 19007.9 | 17628.5 | 16249.0 | 14526.0 | 12803.1 | 11080.1 | 9357.2  | 7678.5  | 5999.9  |
| 0.0  | 0.0    | 35°    | 21780.7 | 20171.4 | 18559.2 | 16647.9 | 14733.8 | 12822.5 | 10911.1 | 9016.4  | 7119.0  |
| 0.0  | 0.0    | 37.5°  | 25304.2 | 23329.2 | 21351.4 | 19221.2 | 17091.1 | 14963.7 | 12833.5 | 10667.4 | 8501.2  |
| 0.0  | 0.0    | 40°    | 32049.2 | 29500.8 | 26952.4 | 24246.1 | 21537.0 | 18830.7 | 16124.3 | 13465.1 | 10805.9 |
| 0.0  | 0.0    | 42.5°  | 44134.9 | 40691.7 | 37248.6 | 33647.6 | 30043.7 | 26442.7 | 22838.9 | 19088.3 | 15334.9 |
| 0.0  | 0.0    | 45°    | 57774.5 | 53503.1 | 49229.0 | 45187.5 | 41143.3 | 37101.8 | 33060.3 | 27913.6 | 22766.9 |
| 0.0  | 0.0    | 47.5°  | 65444.7 | 60832.6 | 56220.5 | 52395.1 | 48569.7 | 44744.3 | 40918.9 | 35370.5 | 29822.1 |
| 0.0  | 0.0    | 50°    | 68267.4 | 63572.2 | 58877.0 | 55356.3 | 51832.8 | 48312.1 | 44788.6 | 39231.9 | 33672.5 |
| 0.0  | 0.0    | 52.5°  | 68868.5 | 64079.1 | 59289.7 | 55746.9 | 52204.0 | 48663.9 | 45121.0 | 39600.3 | 34079.7 |
| 0.0  | 0.0    | 55°    | 70103.9 | 64965.5 | 59824.3 | 55785.6 | 51746.9 | 47708.2 | 43669.5 | 38060.2 | 32450.9 |
| 0.0  | 0.0    | 57.5°  | 71718.8 | 66450.2 | 61181.7 | 56580.6 | 51979.6 | 47381.4 | 42780.3 | 36647.5 | 30514.6 |
| 0.0  | 0.0    | 60°    | 71295.0 | 66710.6 | 62123.5 | 57195.6 | 52264.9 | 47337.0 | 42406.4 | 35661.4 | 28913.6 |
| 0.0  | 0.0    | 62.5°  | 63937.8 | 60286.9 | 56633.3 | 52580.7 | 48525.4 | 44472.8 | 40420.3 | 33475.8 | 26531.3 |
| 0.0  | 0.0    | 65°    | 52600.1 | 49935.3 | 47270.6 | 44010.2 | 40747.1 | 37486.8 | 34226.5 | 27999.5 | 21775.2 |
| 0.0  | 0.0    | 67.5°  | 42630.8 | 39628.0 | 36622.6 | 34024.3 | 31423.2 | 28824.9 | 26223.9 | 21323.7 | 16423.5 |
|      |        | 70°    | 33869.2 | 30603.3 | 27334.7 | 24797.3 | 22257.2 | 19719.8 | 17182.5 | 13924.9 | 10670.2 |
|      |        | 72.5°  | 26897.0 | 23952.4 | 21007.9 | 18301.6 | 15592.5 | 12886.2 | 10177.1 | 8251.9  | 6326.7  |
|      |        | 75°    | 12855.7 | 11678.4 | 10501.2 | 9085.7  | 7670.2  | 6254.7  | 4839.2  | 3999.9  | 3163.4  |
|      |        | 77.5°  | 4764.5  | 4130.1  | 3493.0  | 2916.8  | 2340.7  | 1767.3  | 1191.1  | 1091.4  | 991.7   |
|      |        | 80°    | 1232.7  | 1074.8  | 914.1   | 800.5   | 684.2   | 570.6   | 457.1   | 412.7   | 371.2   |
|      |        | 82.5°  | 141.3   | 130.2   | 121.9   | 116.3   | 108.0   | 102.5   | 94.2    | 85.9    | 77.6    |
|      |        | 85°    | 8.3     | 5.5     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5°  | 360°   |
|--------|------|--------|---------|--------|
| 0.0    | 0.0  | 0°     | 160.7   | 160.7  |
| 0.0    | 0.0  | 2.5°   | 149.6   | 146.8  |
| 0.0    | 0.0  | 5°     | 157.9   | 155.1  |
| 0.0    | 0.0  | 7.5°   | 174.5   | 169.0  |
| 0.0    | 0.0  | 10°    | 191.1   | 185.6  |
| 0.0    | 0.0  | 12.5°  | 216.1   | 207.8  |
| 0.0    | 0.0  | 15°    | 243.8   | 227.1  |
| 0.0    | 0.0  | 17.5°  | 290.9   | 254.8  |
| 0.0    | 0.0  | 20°    | 393.3   | 301.9  |
| 0.0    | 0.0  | 22.5°  | 554.0   | 376.7  |
| 0.0    | 0.0  | 25°    | 814.4   | 520.8  |
| 0.0    | 0.0  | 27.5°  | 1132.9  | 692.5  |
| 0.0    | 0.0  | 30°    | 1506.9  | 867.0  |
| 0.0    | 0.0  | 32.5°  | 1836.5  | 1033.2 |
| 0.0    | 0.0  | 35°    | 2265.9  | 1202.2 |
| 0.0    | 0.0  | 37.5°  | 2795.0  | 1418.3 |
| 0.0    | 0.0  | 40°    | 3614.9  | 1745.1 |
| 0.0    | 0.0  | 42.5°  | 5091.3  | 2349.0 |
| 0.0    | 0.0  | 45°    | 8268.5  | 4060.9 |
| 0.0    | 0.0  | 47.5°  | 12722.7 | 6717.3 |
| 0.0    | 0.0  | 50°    | 15564.8 | 8573.2 |
| 0.0    | 0.0  | 52.5°  | 15797.5 | 8559.4 |
| 0.0    | 0.0  | 55°    | 14420.8 | 7609.3 |
| 0.0    | 0.0  | 57.5°  | 12304.5 | 6360.0 |
| 0.0    | 0.0  | 60°    | 10227.0 | 5030.4 |
| 0.0    | 0.0  | 62.5°  | 8058.0  | 3473.6 |
| 0.0    | 0.0  | 65°    | 5889.1  | 2457.0 |
| 0.0    | 0.0  | 67.5°  | 4229.8  | 1836.5 |
|        |      | 70°    | 2781.1  | 1407.2 |
|        |      | 72.5°  | 1811.6  | 1146.8 |
|        |      | 75°    | 1218.8  | 950.1  |
|        |      | 77.5°  | 711.9   | 631.6  |
|        |      | 80°    | 252.1   | 221.6  |
|        |      | 82.5°  | 47.1    | 33.2   |
|        |      | 85°    | 0.0     | 0.0    |
|        |      | 87.5°  | 0.0     | 0.0    |
|        |      | 90°    | 0.0     | 0.0    |
|        |      | 92.5°  | 0.0     | 0.0    |
|        |      | 95°    | 0.0     | 0.0    |
|        |      | 97.5°  | 0.0     | 0.0    |
|        |      | 100°   | 0.0     | 0.0    |
|        |      | 102.5° | 0.0     | 0.0    |
|        |      | 105°   | 0.0     | 0.0    |
|        |      | 107.5° | 0.0     | 0.0    |
|        |      | 110°   | 0.0     | 0.0    |



REPORT NUMBER: P1049239

CATALOG NUMBER: GALN-SA8C-840-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-11

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-840-U-5WQ

Data in this report applies to families of products including GSS-SB1A-840-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-11  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-840-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI  
 4000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3897  
 CIE  $u'$ : 0.2249  
 CIE  $v'$ : 0.5084  
 Duv: 0.0039  
 CIE x: 0.3882  
 CIE y: 0.3900  
 CIE z: 0.2218  
 Peak Wavelength (nm): 445  
 Dominant Wavelength (nm): 577  
 Purity: 33.54925  
 R<sub>f</sub>: 81.8  
 R<sub>g</sub>: 98.6

CRI (Ra): 80.2  
 R1: 78.9  
 R2: 83.5  
 R3: 88.3  
 R4: 82.1  
 R5: 78.8  
 R6: 78.4  
 R7: 85.8  
 R8: 65.8  
 R9: 6.7  
 R10: 61.9  
 R11: 81.9  
 R12: 58.9  
 R13: 79.2  
 R14: 93.2  
 R15: 71.9



### Test Conditions


Stabilization Time: 24M  
 Operation Time: 1H 24M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-11


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-11

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-11

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 242                         | NR               | 620       | 792                         | NR               | 750       | 29                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 320                         | NR               | 625       | 748                         | NR               | 755       | 25                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 401                         | NR               | 630       | 703                         | NR               | 760       | 22                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 479                         | NR               | 635       | 651                         | NR               | 765       | 19                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 546                         | NR               | 640       | 599                         | NR               | 770       | 16                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 602                         | NR               | 645       | 545                         | NR               | 775       | 14                          | NR               | 905       | 0                           | NR               |
| 390       | 2                           | NR               | 520       | 645                         | NR               | 650       | 493                         | NR               | 780       | 12                          | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 674                         | NR               | 655       | 443                         | NR               | 785       | 10                          | NR               | 915       | 0                           | NR               |
| 400       | 6                           | NR               | 530       | 699                         | NR               | 660       | 394                         | NR               | 790       | 9                           | NR               | 920       | 0                           | NR               |
| 405       | 11                          | NR               | 535       | 718                         | NR               | 665       | 349                         | NR               | 795       | 8                           | NR               | 925       | 0                           | NR               |
| 410       | 22                          | NR               | 540       | 732                         | NR               | 670       | 307                         | NR               | 800       | 7                           | NR               | 930       | 0                           | NR               |
| 415       | 43                          | NR               | 545       | 749                         | NR               | 675       | 269                         | NR               | 805       | 6                           | NR               | 935       | 0                           | NR               |
| 420       | 86                          | NR               | 550       | 762                         | NR               | 680       | 235                         | NR               | 810       | 5                           | NR               | 940       | 0                           | NR               |
| 425       | 164                         | NR               | 555       | 778                         | NR               | 685       | 204                         | NR               | 815       | 5                           | NR               | 945       | 0                           | NR               |
| 430       | 288                         | NR               | 560       | 792                         | NR               | 690       | 178                         | NR               | 820       | 4                           | NR               | 950       | 0                           | NR               |
| 435       | 478                         | NR               | 565       | 809                         | NR               | 695       | 153                         | NR               | 825       | 3                           | NR               | 955       | 0                           | NR               |
| 440       | 766                         | NR               | 570       | 827                         | NR               | 700       | 132                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 1000                        | NR               | 575       | 845                         | NR               | 705       | 114                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 726                         | NR               | 580       | 862                         | NR               | 710       | 98                          | NR               | 840       | 2                           | NR               | 970       | 0                           | NR               |
| 455       | 425                         | NR               | 585       | 875                         | NR               | 715       | 84                          | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 324                         | NR               | 590       | 887                         | NR               | 720       | 73                          | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 225                         | NR               | 595       | 890                         | NR               | 725       | 63                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 887                         | NR               | 730       | 54                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 147                         | NR               | 605       | 875                         | NR               | 735       | 46                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 154                         | NR               | 610       | 856                         | NR               | 740       | 40                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 184                         | NR               | 615       | 828                         | NR               | 745       | 34                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-11

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.57

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 242                      | NR            | 620    | 792                      | NR            | 750    | 29                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 320                      | NR            | 625    | 748                      | NR            | 755    | 25                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 401                      | NR            | 630    | 703                      | NR            | 760    | 22                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 479                      | NR            | 635    | 651                      | NR            | 765    | 19                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 546                      | NR            | 640    | 599                      | NR            | 770    | 16                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 602                      | NR            | 645    | 545                      | NR            | 775    | 14                       | NR            | 905    | 0                        | NR            |
| 390    | 2                        | NR            | 520    | 645                      | NR            | 650    | 493                      | NR            | 780    | 12                       | NR            | 910    | 0                        | NR            |
| 395    | 4                        | NR            | 525    | 674                      | NR            | 655    | 443                      | NR            | 785    | 10                       | NR            | 915    | 0                        | NR            |
| 400    | 6                        | NR            | 530    | 699                      | NR            | 660    | 394                      | NR            | 790    | 9                        | NR            | 920    | 0                        | NR            |
| 405    | 11                       | NR            | 535    | 718                      | NR            | 665    | 349                      | NR            | 795    | 8                        | NR            | 925    | 0                        | NR            |
| 410    | 22                       | NR            | 540    | 732                      | NR            | 670    | 307                      | NR            | 800    | 7                        | NR            | 930    | 0                        | NR            |
| 415    | 43                       | NR            | 545    | 749                      | NR            | 675    | 269                      | NR            | 805    | 6                        | NR            | 935    | 0                        | NR            |
| 420    | 86                       | NR            | 550    | 762                      | NR            | 680    | 235                      | NR            | 810    | 5                        | NR            | 940    | 0                        | NR            |
| 425    | 164                      | NR            | 555    | 778                      | NR            | 685    | 204                      | NR            | 815    | 5                        | NR            | 945    | 0                        | NR            |
| 430    | 288                      | NR            | 560    | 792                      | NR            | 690    | 178                      | NR            | 820    | 4                        | NR            | 950    | 0                        | NR            |
| 435    | 478                      | NR            | 565    | 809                      | NR            | 695    | 153                      | NR            | 825    | 3                        | NR            | 955    | 0                        | NR            |
| 440    | 766                      | NR            | 570    | 827                      | NR            | 700    | 132                      | NR            | 830    | 3                        | NR            | 960    | 0                        | NR            |
| 445    | 1000                     | NR            | 575    | 845                      | NR            | 705    | 114                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 726                      | NR            | 580    | 862                      | NR            | 710    | 98                       | NR            | 840    | 2                        | NR            | 970    | 0                        | NR            |
| 455    | 425                      | NR            | 585    | 875                      | NR            | 715    | 84                       | NR            | 845    | 2                        | NR            | 975    | 0                        | NR            |
| 460    | 324                      | NR            | 590    | 887                      | NR            | 720    | 73                       | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 225                      | NR            | 595    | 890                      | NR            | 725    | 63                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 157                      | NR            | 600    | 887                      | NR            | 730    | 54                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 147                      | NR            | 605    | 875                      | NR            | 735    | 46                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 154                      | NR            | 610    | 856                      | NR            | 740    | 40                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 184                      | NR            | 615    | 828                      | NR            | 745    | 34                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-11

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.06


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 242                         | NR               | 620       | 792                         | NR               | 750       | 29                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 320                         | NR               | 625       | 748                         | NR               | 755       | 25                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 401                         | NR               | 630       | 703                         | NR               | 760       | 22                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 479                         | NR               | 635       | 651                         | NR               | 765       | 19                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 546                         | NR               | 640       | 599                         | NR               | 770       | 16                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 602                         | NR               | 645       | 545                         | NR               | 775       | 14                          | NR               | 905       | 0                           | NR               |
| 390       | 2                           | NR               | 520       | 645                         | NR               | 650       | 493                         | NR               | 780       | 12                          | NR               | 910       | 0                           | NR               |
| 395       | 4                           | NR               | 525       | 674                         | NR               | 655       | 443                         | NR               | 785       | 10                          | NR               | 915       | 0                           | NR               |
| 400       | 6                           | NR               | 530       | 699                         | NR               | 660       | 394                         | NR               | 790       | 9                           | NR               | 920       | 0                           | NR               |
| 405       | 11                          | NR               | 535       | 718                         | NR               | 665       | 349                         | NR               | 795       | 8                           | NR               | 925       | 0                           | NR               |
| 410       | 22                          | NR               | 540       | 732                         | NR               | 670       | 307                         | NR               | 800       | 7                           | NR               | 930       | 0                           | NR               |
| 415       | 43                          | NR               | 545       | 749                         | NR               | 675       | 269                         | NR               | 805       | 6                           | NR               | 935       | 0                           | NR               |
| 420       | 86                          | NR               | 550       | 762                         | NR               | 680       | 235                         | NR               | 810       | 5                           | NR               | 940       | 0                           | NR               |
| 425       | 164                         | NR               | 555       | 778                         | NR               | 685       | 204                         | NR               | 815       | 5                           | NR               | 945       | 0                           | NR               |
| 430       | 288                         | NR               | 560       | 792                         | NR               | 690       | 178                         | NR               | 820       | 4                           | NR               | 950       | 0                           | NR               |
| 435       | 478                         | NR               | 565       | 809                         | NR               | 695       | 153                         | NR               | 825       | 3                           | NR               | 955       | 0                           | NR               |
| 440       | 766                         | NR               | 570       | 827                         | NR               | 700       | 132                         | NR               | 830       | 3                           | NR               | 960       | 0                           | NR               |
| 445       | 1000                        | NR               | 575       | 845                         | NR               | 705       | 114                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 726                         | NR               | 580       | 862                         | NR               | 710       | 98                          | NR               | 840       | 2                           | NR               | 970       | 0                           | NR               |
| 455       | 425                         | NR               | 585       | 875                         | NR               | 715       | 84                          | NR               | 845       | 2                           | NR               | 975       | 0                           | NR               |
| 460       | 324                         | NR               | 590       | 887                         | NR               | 720       | 73                          | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 225                         | NR               | 595       | 890                         | NR               | 725       | 63                          | NR               | 855       | 1                           | NR               | 985       | 0                           | NR               |
| 470       | 157                         | NR               | 600       | 887                         | NR               | 730       | 54                          | NR               | 860       | 1                           | NR               | 990       | 0                           | NR               |
| 475       | 147                         | NR               | 605       | 875                         | NR               | 735       | 46                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 154                         | NR               | 610       | 856                         | NR               | 740       | 40                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 184                         | NR               | 615       | 828                         | NR               | 745       | 34                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-11





TM-30-18

### Summary

$R_f = 81.8$   
 $R_g = 98.6$   
 $CIE R_a = 80.2$   
 $R_9 = 6.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 85 | CES26 = 73 | CES51 = 93 | CES76 = 66 |
| CES02 = 61 | CES27 = 91 | CES52 = 93 | CES77 = 80 |
| CES03 = 31 | CES28 = 87 | CES53 = 83 | CES78 = 66 |
| CES04 = 69 | CES29 = 71 | CES54 = 89 | CES79 = 88 |
| CES05 = 48 | CES30 = 77 | CES55 = 88 | CES80 = 85 |
| CES06 = 50 | CES31 = 74 | CES56 = 80 | CES81 = 83 |
| CES07 = 41 | CES32 = 70 | CES57 = 79 | CES82 = 93 |
| CES08 = 40 | CES33 = 77 | CES58 = 80 | CES83 = 91 |
| CES09 = 29 | CES34 = 79 | CES59 = 92 | CES84 = 91 |
| CES10 = 74 | CES35 = 88 | CES60 = 95 | CES85 = 84 |
| CES11 = 57 | CES36 = 98 | CES61 = 91 | CES86 = 78 |
| CES12 = 63 | CES37 = 85 | CES62 = 90 | CES87 = 84 |
| CES13 = 42 | CES38 = 85 | CES63 = 81 | CES88 = 85 |
| CES14 = 74 | CES39 = 95 | CES64 = 81 | CES89 = 78 |
| CES15 = 71 | CES40 = 90 | CES65 = 76 | CES90 = 84 |
| CES16 = 47 | CES41 = 90 | CES66 = 78 | CES91 = 85 |
| CES17 = 49 | CES42 = 84 | CES67 = 76 | CES92 = 71 |
| CES18 = 56 | CES43 = 81 | CES68 = 80 | CES93 = 84 |
| CES19 = 71 | CES44 = 99 | CES69 = 86 | CES94 = 65 |
| CES20 = 65 | CES45 = 87 | CES70 = 73 | CES95 = 77 |
| CES21 = 86 | CES46 = 85 | CES71 = 70 | CES96 = 83 |
| CES22 = 78 | CES47 = 84 | CES72 = 90 | CES97 = 87 |
| CES23 = 91 | CES48 = 79 | CES73 = 65 | CES98 = 81 |
| CES24 = 90 | CES49 = 84 | CES74 = 98 | CES99 = 75 |
| CES25 = 71 | CES50 = 91 | CES75 = 68 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)