

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049919

Luminaire Tested: **GALN-SA7C-927-U-LBC**

Issue Date: 07/10/2025



**Test Information**

Test Method: LM-79-08  
Report Number: P1049919  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA7C-927-U-LBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE  
90CRI 2700K FIXTURE w/ LEFT CORNER BACKLIGHT CONTROL  
Light Source: (98) 2700K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 22038 lumens  
Efficiency: N/A  
Efficacy: 66.8 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G4


Input Watts (W): 330  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 38.4 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049919  
CATALOG NUMBER: GALN-SA7C-927-U-LBC

## Luminous Intensity Polar Plot



— Vertical Plane Through 44-Deg Lateral      - - - Horizontal Cone Through 58-Deg Vertical

REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 150.5    | 0.0    | 150.5   |
|                    | % Fixture | 0.7      | 0.0    | 0.7     |
| <b>Street Side</b> | Lumens    | 21887.6  | 0.0    | 21887.6 |
|                    | % Fixture | 99.3     | 0.0    | 99.3    |
| <b>Total</b>       | Lumens    | 22038.0  | 0.0    | 22038.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 8.6     | 0.0       |
| 10°-20°   | 48.3    | 0.2       |
| 20°-30°   | 522.1   | 2.4       |
| 30°-40°   | 1544.0  | 7.0       |
| 40°-50°   | 4601.9  | 20.9      |
| 50°-60°   | 7302.1  | 33.1      |
| 60°-70°   | 6090.8  | 27.6      |
| 70°-80°   | 1878.5  | 8.5       |
| 80°-90°   | 41.7    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 22038.0 | 100.0     |
| 0°-180°   | 22038.0 | 100.0     |



REPORT NUMBER: P1049919


CATALOG NUMBER: GALN-SA7C-927-U-LBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|------|-------------|---------|-----------|-------------------------|------|----------|
|      |             |         |           | B                       | U    | G        |
| FL   | (0°-30°)    | 564.3   | 2.6       |                         |      |          |
| FM   | (30°-60°)   | 13365.6 | 60.6      |                         |      |          |
| FH   | (60°-80°)   | 7917.9  | 35.9      |                         |      | G4/12000 |
| FVH  | (80°-90°)   | 39.7    | 0.2       |                         |      | G1/100   |
| BL   | (0°-30°)    | 14.7    | 0.1       | B0/110                  |      |          |
| BM   | (30°-60°)   | 82.4    | 0.4       | B0/220                  |      |          |
| BH   | (60°-80°)   | 51.4    | 0.2       | B0/110                  |      | G0/110   |
| BVH  | (80°-90°)   | 2.0     | 0.0       |                         |      | G0/10    |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B0-U0-G4**

Type III Short



REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 5°     | 15°     | 25°     | 35°     | 44°     | 45°     | 55°     | 65°     | 75°     |
|-------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 96.6   | 96.6   | 96.6    | 96.6    | 96.6    | 96.6    | 96.6    | 96.6    | 96.6    | 96.6    |
| 2.5°  | 124.9  | 124.9  | 119.9   | 113.2   | 106.5   | 99.9    | 98.2    | 94.9    | 93.2    | 91.6    |
| 5°    | 129.9  | 129.9  | 128.2   | 123.2   | 116.5   | 111.5   | 111.5   | 106.5   | 103.2   | 99.9    |
| 7.5°  | 133.2  | 134.8  | 138.2   | 136.5   | 133.2   | 128.2   | 128.2   | 124.9   | 119.9   | 111.5   |
| 10°   | 138.2  | 143.2  | 149.8   | 153.2   | 154.8   | 154.8   | 153.2   | 151.5   | 143.2   | 131.5   |
| 12.5° | 143.2  | 153.2  | 169.8   | 186.5   | 196.4   | 209.8   | 208.1   | 204.8   | 183.1   | 158.2   |
| 15°   | 153.2  | 168.1  | 203.1   | 251.4   | 326.3   | 372.9   | 391.2   | 374.6   | 303.0   | 213.1   |
| 17.5° | 164.8  | 189.8  | 294.7   | 526.1   | 862.4   | 1022.2  | 1118.7  | 1040.5  | 689.2   | 404.5   |
| 20°   | 176.5  | 231.4  | 547.7   | 1363.5  | 2237.5  | 2760.2  | 2905.1  | 2678.6  | 1719.7  | 770.8   |
| 22.5° | 196.4  | 324.6  | 1110.4  | 2818.5  | 4821.2  | 5605.3  | 5753.5  | 5029.3  | 3248.0  | 1521.6  |
| 25°   | 238.1  | 471.1  | 1914.5  | 4593.1  | 7195.2  | 8518.7  | 8457.1  | 7508.2  | 5269.1  | 2430.6  |
| 27.5° | 298.0  | 685.9  | 2895.1  | 6526.0  | 9469.3  | 10636.3 | 10776.2 | 9602.5  | 7023.7  | 3574.3  |
| 30°   | 384.6  | 950.6  | 3947.2  | 8074.2  | 11292.3 | 12554.2 | 12577.5 | 11363.8 | 8593.6  | 4578.2  |
| 32.5° | 467.8  | 1200.3 | 4867.8  | 9570.9  | 13088.6 | 14472.0 | 14575.2 | 13081.9 | 9765.6  | 5623.7  |
| 35°   | 531.1  | 1363.5 | 5800.1  | 10886.0 | 14899.8 | 16806.0 | 16799.4 | 15026.4 | 11154.1 | 6557.6  |
| 37.5° | 536.1  | 1526.6 | 6644.2  | 12231.2 | 17193.9 | 19328.2 | 19539.6 | 17585.1 | 12832.2 | 7713.0  |
| 40°   | 524.4  | 1709.7 | 7713.0  | 14328.8 | 21327.6 | 24602.2 | 24788.7 | 22324.8 | 16198.4 | 9690.7  |
| 42.5° | 537.7  | 2027.7 | 9447.7  | 18202.8 | 28191.5 | 32894.5 | 33254.1 | 30663.7 | 22386.4 | 13726.2 |
| 45°   | 607.6  | 2625.4 | 13081.9 | 24683.8 | 37975.5 | 43709.0 | 43589.1 | 39858.3 | 29586.6 | 19869.2 |
| 47.5° | 839.1  | 4088.7 | 18469.1 | 30991.7 | 44228.4 | 49334.3 | 49437.5 | 44877.7 | 33788.5 | 24592.2 |
| 50°   | 1290.2 | 6256.3 | 22995.7 | 34326.2 | 46917.0 | 52039.6 | 51943.0 | 46674.0 | 35385.0 | 26917.9 |
| 52.5° | 1678.1 | 7824.5 | 25266.5 | 35496.6 | 47261.6 | 53376.4 | 53369.7 | 47146.8 | 35633.1 | 27117.7 |
| 55°   | 1774.7 | 7942.7 | 25284.8 | 35559.9 | 48034.1 | 55126.1 | 55345.8 | 48310.5 | 35954.4 | 26245.4 |
| 57.5° | 1736.4 | 7032.1 | 24229.3 | 35926.1 | 49409.2 | 56479.6 | 56491.2 | 49437.5 | 36770.2 | 25711.0 |
| 58°   | 1703.1 | 6888.9 | 24016.2 | 36134.2 | 49645.6 | 56536.2 | 56507.9 | 49489.1 | 37434.4 | 25691.0 |
| 60°   | 1516.6 | 5981.6 | 23185.5 | 36665.3 | 49294.3 | 55374.1 | 55109.4 | 48362.1 | 37336.2 | 25486.2 |
| 62.5° | 1192.0 | 4666.4 | 22368.1 | 36051.0 | 45528.6 | 49748.8 | 49858.7 | 42816.7 | 34036.6 | 24292.6 |
| 65°   | 948.9  | 3477.7 | 20663.3 | 31622.6 | 37491.0 | 40853.9 | 41263.4 | 34817.4 | 28409.6 | 20570.1 |
| 67.5° | 755.8  | 2513.8 | 17333.8 | 25176.6 | 29666.5 | 34096.5 | 34394.5 | 29232.0 | 22010.1 | 15760.5 |
| 70°   | 614.3  | 1699.7 | 11964.8 | 18412.5 | 24469.0 | 29450.1 | 29468.4 | 24284.2 | 16428.1 | 10326.7 |
| 72.5° | 544.4  | 1177.0 | 6945.5  | 13428.2 | 19840.9 | 23997.9 | 23513.5 | 19706.1 | 12625.7 | 6116.4  |
| 75°   | 471.1  | 780.8  | 3406.2  | 8209.1  | 12029.8 | 12111.3 | 12296.1 | 9141.3  | 6311.2  | 2908.4  |
| 77.5° | 387.9  | 554.4  | 1341.8  | 2242.5  | 3607.6  | 4618.1  | 4789.6  | 3629.2  | 2099.3  | 715.9   |
| 80°   | 266.4  | 263.0  | 361.3   | 687.6   | 1032.2  | 1293.5  | 1207.0  | 933.9   | 549.4   | 274.7   |
| 82.5° | 114.9  | 124.9  | 163.1   | 196.4   | 159.8   | 154.8   | 148.2   | 94.9    | 73.3    | 56.6    |
| 85°   | 36.6   | 33.3   | 35.0    | 35.0    | 28.3    | 21.6    | 21.6    | 10.0    | 0.0     | 0.0     |
| 87.5° | 18.3   | 15.0   | 15.0    | 13.3    | 8.3     | 3.3     | 1.7     | 0.0     | 0.0     | 0.0     |
| 90°   | 0.0    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 85°     |       | 90°    | 95°   | 105°  | 115° | 125° | 135° | 145° | 155° | 165° | 175° |
|---------|-------|--------|-------|-------|------|------|------|------|------|------|------|
| 96.6    | 0°    | 96.6   | 96.6  | 96.6  | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 |
| 89.9    | 2.5°  | 88.2   | 88.2  | 84.9  | 81.6 | 79.9 | 76.6 | 74.9 | 73.3 | 71.6 | 69.9 |
| 96.6    | 5°    | 93.2   | 91.6  | 86.6  | 81.6 | 76.6 | 71.6 | 68.3 | 64.9 | 61.6 | 59.9 |
| 106.5   | 7.5°  | 101.6  | 98.2  | 88.2  | 79.9 | 73.3 | 66.6 | 63.3 | 58.3 | 54.9 | 49.9 |
| 118.2   | 10°   | 111.5  | 104.9 | 91.6  | 81.6 | 71.6 | 63.3 | 58.3 | 53.3 | 48.3 | 41.6 |
| 134.8   | 12.5° | 124.9  | 113.2 | 96.6  | 79.9 | 68.3 | 58.3 | 53.3 | 46.6 | 41.6 | 36.6 |
| 156.5   | 15°   | 136.5  | 121.5 | 98.2  | 79.9 | 64.9 | 53.3 | 46.6 | 40.0 | 35.0 | 28.3 |
| 196.4   | 17.5° | 153.2  | 128.2 | 96.6  | 74.9 | 59.9 | 46.6 | 40.0 | 35.0 | 26.6 | 16.6 |
| 291.3   | 20°   | 181.5  | 133.2 | 93.2  | 69.9 | 51.6 | 38.3 | 30.0 | 23.3 | 11.7 | 3.3  |
| 437.8   | 22.5° | 226.4  | 146.5 | 89.9  | 63.3 | 44.9 | 30.0 | 20.0 | 8.3  | 0.0  | 0.0  |
| 665.9   | 25°   | 313.0  | 169.8 | 89.9  | 59.9 | 40.0 | 21.6 | 6.7  | 0.0  | 0.0  | 0.0  |
| 945.6   | 27.5° | 416.2  | 201.4 | 89.9  | 51.6 | 31.6 | 11.7 | 0.0  | 0.0  | 0.0  | 0.0  |
| 1288.5  | 30°   | 521.1  | 236.4 | 89.9  | 44.9 | 25.0 | 1.7  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1586.5  | 32.5° | 621.0  | 266.4 | 91.6  | 38.3 | 16.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1999.4  | 35°   | 722.5  | 271.4 | 89.9  | 33.3 | 10.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2505.5  | 37.5° | 852.4  | 261.4 | 84.9  | 30.0 | 5.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3296.3  | 40°   | 1048.8 | 266.4 | 79.9  | 28.3 | 1.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 4706.4  | 42.5° | 1411.7 | 288.0 | 73.3  | 28.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 7496.5  | 45°   | 2440.6 | 386.2 | 66.6  | 30.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 11254.0 | 47.5° | 4037.1 | 694.2 | 64.9  | 30.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 13556.4 | 50°   | 5152.5 | 874.0 | 68.3  | 31.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 13844.4 | 52.5° | 5144.2 | 973.9 | 71.6  | 33.3 | 6.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 12760.6 | 55°   | 4573.2 | 992.2 | 76.6  | 36.6 | 21.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 10966.0 | 57.5° | 3822.4 | 905.6 | 88.2  | 44.9 | 40.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 10684.6 | 58°   | 3689.2 | 865.7 | 91.6  | 46.6 | 43.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 9267.9  | 60°   | 3023.3 | 705.9 | 116.5 | 58.3 | 58.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 7598.1  | 62.5° | 2087.6 | 616.0 | 133.2 | 74.9 | 59.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 5602.0  | 65°   | 1476.7 | 556.0 | 144.8 | 79.9 | 48.3 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 3980.5  | 67.5° | 1103.8 | 512.8 | 159.8 | 81.6 | 25.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 2497.2  | 70°   | 845.7  | 481.1 | 196.4 | 86.6 | 6.7  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 1488.3  | 72.5° | 689.2  | 444.5 | 238.1 | 89.9 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 892.3   | 75°   | 571.0  | 401.2 | 229.7 | 98.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 476.1   | 77.5° | 379.6  | 311.3 | 209.8 | 98.2 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 169.8   | 80°   | 133.2  | 123.2 | 163.1 | 86.6 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 35.0    | 82.5° | 20.0   | 16.6  | 23.3  | 30.0 | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 85°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 87.5° | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |
| 0.0     | 90°   | 0.0    | 0.0   | 0.0   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  |

REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 180° |       | 185° | 195° | 205° | 215° | 225° | 235° | 245° | 255° | 265°  | 270°  |
|------|-------|------|------|------|------|------|------|------|------|-------|-------|
| 96.6 | 0°    | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6 | 96.6  | 96.6  |
| 68.3 | 2.5°  | 68.3 | 68.3 | 66.6 | 68.3 | 68.3 | 71.6 | 79.9 | 91.6 | 104.9 | 109.9 |
| 58.3 | 5°    | 56.6 | 54.9 | 53.3 | 53.3 | 53.3 | 58.3 | 64.9 | 78.2 | 93.2  | 99.9  |
| 48.3 | 7.5°  | 46.6 | 44.9 | 43.3 | 41.6 | 41.6 | 44.9 | 53.3 | 68.3 | 83.2  | 89.9  |
| 40.0 | 10°   | 38.3 | 35.0 | 33.3 | 31.6 | 31.6 | 35.0 | 43.3 | 58.3 | 74.9  | 81.6  |
| 33.3 | 12.5° | 31.6 | 26.6 | 23.3 | 21.6 | 20.0 | 25.0 | 33.3 | 46.6 | 64.9  | 73.3  |
| 25.0 | 15°   | 21.6 | 16.6 | 11.7 | 10.0 | 8.3  | 13.3 | 21.6 | 36.6 | 54.9  | 64.9  |
| 13.3 | 17.5° | 11.7 | 5.0  | 1.7  | 0.0  | 0.0  | 3.3  | 10.0 | 26.6 | 44.9  | 53.3  |
| 0.0  | 20°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 13.3 | 33.3  | 41.6  |
| 0.0  | 22.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 1.7  | 20.0  | 28.3  |
| 0.0  | 25°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 8.3   | 15.0  |
| 0.0  | 27.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 3.3   |
| 0.0  | 30°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 32.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 35°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 37.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 40°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 42.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 45°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 47.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 50°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 52.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 55°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 57.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 58°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 60°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 62.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 65°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 67.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 70°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 72.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 75°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 77.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 80°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 82.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |
| 0.0  | 85°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 5.0   |
| 0.0  | 87.5° | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 6.7   | 13.3  |
| 0.0  | 90°   | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0  | 0.0   | 0.0   |



REPORT NUMBER: P1049919

CATALOG NUMBER: GALN-SA7C-927-U-LBC

**CANDELA DISTRIBUTION (continued):**

| 275°  |       | 285°  | 295°  | 305°  | 315°  | 316°  | 325°  | 335°  | 345°  | 355°  | 360°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 96.6  | 0°    | 96.6  | 96.6  | 96.6  | 96.6  | 96.6  | 96.6  | 96.6  | 96.6  | 96.6  | 96.6   |
| 114.9 | 2.5°  | 118.2 | 116.5 | 113.2 | 109.9 | 109.9 | 109.9 | 114.9 | 119.9 | 124.9 | 124.9  |
| 103.2 | 5°    | 109.9 | 109.9 | 108.2 | 104.9 | 104.9 | 106.5 | 113.2 | 121.5 | 128.2 | 129.9  |
| 94.9  | 7.5°  | 101.6 | 104.9 | 101.6 | 99.9  | 101.6 | 103.2 | 109.9 | 119.9 | 129.9 | 133.2  |
| 88.2  | 10°   | 96.6  | 98.2  | 98.2  | 96.6  | 96.6  | 99.9  | 106.5 | 119.9 | 133.2 | 138.2  |
| 79.9  | 12.5° | 89.9  | 93.2  | 91.6  | 91.6  | 91.6  | 94.9  | 103.2 | 118.2 | 136.5 | 143.2  |
| 71.6  | 15°   | 83.2  | 88.2  | 88.2  | 86.6  | 86.6  | 88.2  | 99.9  | 116.5 | 141.5 | 153.2  |
| 61.6  | 17.5° | 76.6  | 81.6  | 83.2  | 79.9  | 79.9  | 83.2  | 94.9  | 116.5 | 144.8 | 164.8  |
| 49.9  | 20°   | 63.3  | 71.6  | 76.6  | 71.6  | 71.6  | 74.9  | 86.6  | 109.9 | 146.5 | 176.5  |
| 36.6  | 22.5° | 49.9  | 58.3  | 64.9  | 63.3  | 63.3  | 64.9  | 79.9  | 104.9 | 148.2 | 196.4  |
| 21.6  | 25°   | 36.6  | 44.9  | 49.9  | 53.3  | 53.3  | 58.3  | 73.3  | 101.6 | 154.8 | 238.1  |
| 10.0  | 27.5° | 21.6  | 31.6  | 38.3  | 41.6  | 43.3  | 49.9  | 68.3  | 98.2  | 166.5 | 298.0  |
| 0.0   | 30°   | 10.0  | 18.3  | 26.6  | 33.3  | 33.3  | 44.9  | 63.3  | 94.9  | 181.5 | 384.6  |
| 0.0   | 32.5° | 0.0   | 8.3   | 13.3  | 23.3  | 25.0  | 36.6  | 58.3  | 91.6  | 203.1 | 467.8  |
| 0.0   | 35°   | 0.0   | 0.0   | 6.7   | 18.3  | 18.3  | 30.0  | 53.3  | 88.2  | 236.4 | 531.1  |
| 0.0   | 37.5° | 0.0   | 0.0   | 0.0   | 13.3  | 15.0  | 26.6  | 51.6  | 86.6  | 243.1 | 536.1  |
| 0.0   | 40°   | 0.0   | 0.0   | 0.0   | 10.0  | 11.7  | 25.0  | 51.6  | 88.2  | 219.8 | 524.4  |
| 0.0   | 42.5° | 0.0   | 0.0   | 0.0   | 6.7   | 8.3   | 25.0  | 51.6  | 91.6  | 198.1 | 537.7  |
| 0.0   | 45°   | 0.0   | 0.0   | 0.0   | 5.0   | 6.7   | 26.6  | 49.9  | 89.9  | 186.5 | 607.6  |
| 0.0   | 47.5° | 0.0   | 0.0   | 0.0   | 6.7   | 10.0  | 26.6  | 48.3  | 88.2  | 188.1 | 839.1  |
| 0.0   | 50°   | 0.0   | 0.0   | 0.0   | 8.3   | 11.7  | 26.6  | 49.9  | 84.9  | 206.4 | 1290.2 |
| 0.0   | 52.5° | 0.0   | 0.0   | 0.0   | 6.7   | 10.0  | 30.0  | 54.9  | 83.2  | 224.7 | 1678.1 |
| 0.0   | 55°   | 0.0   | 0.0   | 0.0   | 1.7   | 5.0   | 38.3  | 59.9  | 83.2  | 253.0 | 1774.7 |
| 0.0   | 57.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 43.3  | 68.3  | 88.2  | 299.7 | 1736.4 |
| 0.0   | 58°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 43.3  | 69.9  | 88.2  | 303.0 | 1703.1 |
| 0.0   | 60°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 43.3  | 76.6  | 98.2  | 326.3 | 1516.6 |
| 0.0   | 62.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 36.6  | 91.6  | 123.2 | 339.6 | 1192.0 |
| 0.0   | 65°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 30.0  | 108.2 | 134.8 | 349.6 | 948.9  |
| 0.0   | 67.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 28.3  | 111.5 | 136.5 | 354.6 | 755.8  |
| 0.0   | 70°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 30.0  | 109.9 | 146.5 | 371.2 | 614.3  |
| 0.0   | 72.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 33.3  | 99.9  | 161.5 | 371.2 | 544.4  |
| 0.0   | 75°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 35.0  | 93.2  | 181.5 | 338.0 | 471.1  |
| 0.0   | 77.5° | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 33.3  | 91.6  | 211.4 | 301.3 | 387.9  |
| 0.0   | 80°   | 3.3   | 5.0   | 5.0   | 3.3   | 3.3   | 28.3  | 89.9  | 214.8 | 256.4 | 266.4  |
| 1.7   | 82.5° | 10.0  | 13.3  | 11.7  | 8.3   | 8.3   | 25.0  | 79.9  | 179.8 | 133.2 | 114.9  |
| 10.0  | 85°   | 18.3  | 21.6  | 21.6  | 18.3  | 18.3  | 23.3  | 49.9  | 64.9  | 44.9  | 36.6   |
| 18.3  | 87.5° | 25.0  | 28.3  | 28.3  | 25.0  | 25.0  | 23.3  | 21.6  | 20.0  | 18.3  | 18.3   |
| 0.0   | 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

(END OF RI



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-13

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-927-U-5WQ

Data in this report applies to families of products including GSS-SB1A-927-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-13  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-927-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 2700K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2731  
 CIE  $u'$ : 0.2605  
 CIE  $v'$ : 0.5298  
 Duv: 0.0021  
 CIE x: 0.4610  
 CIE y: 0.4166  
 CIE z: 0.1224  
 Peak Wavelength (nm): 622  
 Dominant Wavelength (nm): 583  
 Purity: 63.43685  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 98

CRI (Ra): 91.8  
 R1: 91.4  
 R2: 95.1  
 R3: 97.6  
 R4: 92.3  
 R5: 91.1  
 R6: 94.7  
 R7: 92.3  
 R8: 80.0  
 R9: 54.7  
 R10: 87.7  
 R11: 92.9  
 R12: 84.0  
 R13: 92.2  
 R14: 97.8  
 R15: 86.8



### Test Conditions


Stabilization Time: M  
 Operation Time: 1H 0M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-13


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-13

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-13

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 253                                    | NR                             | 620               | 997                                    | NR                             | 750               | 78                                     | NR                             | 880               | 2                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 285                                    | NR                             | 625               | 996                                    | NR                             | 755               | 67                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 314                                    | NR                             | 630               | 989                                    | NR                             | 760               | 58                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 343                                    | NR                             | 635               | 969                                    | NR                             | 765               | 50                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 372                                    | NR                             | 640               | 939                                    | NR                             | 770               | 42                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 401                                    | NR                             | 645               | 901                                    | NR                             | 775               | 36                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 431                                    | NR                             | 650               | 858                                    | NR                             | 780               | 31                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 459                                    | NR                             | 655               | 806                                    | NR                             | 785               | 26                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 0                                      | NR                             | 530               | 488                                    | NR                             | 660               | 752                                    | NR                             | 790               | 23                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 2                                      | NR                             | 535               | 516                                    | NR                             | 665               | 696                                    | NR                             | 795               | 19                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 5                                      | NR                             | 540               | 540                                    | NR                             | 670               | 636                                    | NR                             | 800               | 17                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 10                                     | NR                             | 545               | 566                                    | NR                             | 675               | 579                                    | NR                             | 805               | 14                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 19                                     | NR                             | 550               | 589                                    | NR                             | 680               | 524                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 34                                     | NR                             | 555               | 612                                    | NR                             | 685               | 470                                    | NR                             | 815               | 11                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 61                                     | NR                             | 560               | 634                                    | NR                             | 690               | 421                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 113                                    | NR                             | 565               | 660                                    | NR                             | 695               | 371                                    | NR                             | 825               | 8                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 198                                    | NR                             | 570               | 688                                    | NR                             | 700               | 327                                    | NR                             | 830               | 7                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 288                                    | NR                             | 575               | 719                                    | NR                             | 705               | 288                                    | NR                             | 835               | 6                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 286                                    | NR                             | 580               | 754                                    | NR                             | 710               | 251                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 228                                    | NR                             | 585               | 791                                    | NR                             | 715               | 220                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 207                                    | NR                             | 590               | 831                                    | NR                             | 720               | 192                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 186                                    | NR                             | 595               | 870                                    | NR                             | 725               | 166                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 168                                    | NR                             | 600               | 907                                    | NR                             | 730               | 144                                    | NR                             | 860               | 3                                      | NR                             | 990               | 1                                      | NR                             |
| 475               | 177                                    | NR                             | 605               | 940                                    | NR                             | 735               | 124                                    | NR                             | 865               | 2                                      | NR                             | 995               | 1                                      | NR                             |
| 480               | 198                                    | NR                             | 610               | 967                                    | NR                             | 740               | 106                                    | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 223                                    | NR                             | 615               | 988                                    | NR                             | 745               | 91                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-13

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.27

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 253                                  | NR                             | 620               | 997                                  | NR                             | 750               | 78                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 285                                  | NR                             | 625               | 996                                  | NR                             | 755               | 67                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 314                                  | NR                             | 630               | 989                                  | NR                             | 760               | 58                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 343                                  | NR                             | 635               | 969                                  | NR                             | 765               | 50                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 372                                  | NR                             | 640               | 939                                  | NR                             | 770               | 42                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 401                                  | NR                             | 645               | 901                                  | NR                             | 775               | 36                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 431                                  | NR                             | 650               | 858                                  | NR                             | 780               | 31                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 459                                  | NR                             | 655               | 806                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 0                                    | NR                             | 530               | 488                                  | NR                             | 660               | 752                                  | NR                             | 790               | 23                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 516                                  | NR                             | 665               | 696                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 5                                    | NR                             | 540               | 540                                  | NR                             | 670               | 636                                  | NR                             | 800               | 17                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 566                                  | NR                             | 675               | 579                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 19                                   | NR                             | 550               | 589                                  | NR                             | 680               | 524                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 34                                   | NR                             | 555               | 612                                  | NR                             | 685               | 470                                  | NR                             | 815               | 11                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 61                                   | NR                             | 560               | 634                                  | NR                             | 690               | 421                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 113                                  | NR                             | 565               | 660                                  | NR                             | 695               | 371                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 198                                  | NR                             | 570               | 688                                  | NR                             | 700               | 327                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 288                                  | NR                             | 575               | 719                                  | NR                             | 705               | 288                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 286                                  | NR                             | 580               | 754                                  | NR                             | 710               | 251                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 228                                  | NR                             | 585               | 791                                  | NR                             | 715               | 220                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 207                                  | NR                             | 590               | 831                                  | NR                             | 720               | 192                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 186                                  | NR                             | 595               | 870                                  | NR                             | 725               | 166                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 168                                  | NR                             | 600               | 907                                  | NR                             | 730               | 144                                  | NR                             | 860               | 3                                    | NR                             | 990               | 1                                    | NR                             |
| 475               | 177                                  | NR                             | 605               | 940                                  | NR                             | 735               | 124                                  | NR                             | 865               | 2                                    | NR                             | 995               | 1                                    | NR                             |
| 480               | 198                                  | NR                             | 610               | 967                                  | NR                             | 740               | 106                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 223                                  | NR                             | 615               | 988                                  | NR                             | 745               | 91                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-13

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.38


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 253                         | NR               | 620       | 997                         | NR               | 750       | 78                          | NR               | 880       | 2                           | NR               |
| 365       | 0                           | NR               | 495       | 285                         | NR               | 625       | 996                         | NR               | 755       | 67                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 314                         | NR               | 630       | 989                         | NR               | 760       | 58                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 343                         | NR               | 635       | 969                         | NR               | 765       | 50                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 372                         | NR               | 640       | 939                         | NR               | 770       | 42                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 401                         | NR               | 645       | 901                         | NR               | 775       | 36                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 431                         | NR               | 650       | 858                         | NR               | 780       | 31                          | NR               | 910       | 1                           | NR               |
| 395       | 0                           | NR               | 525       | 459                         | NR               | 655       | 806                         | NR               | 785       | 26                          | NR               | 915       | 1                           | NR               |
| 400       | 0                           | NR               | 530       | 488                         | NR               | 660       | 752                         | NR               | 790       | 23                          | NR               | 920       | 1                           | NR               |
| 405       | 2                           | NR               | 535       | 516                         | NR               | 665       | 696                         | NR               | 795       | 19                          | NR               | 925       | 1                           | NR               |
| 410       | 5                           | NR               | 540       | 540                         | NR               | 670       | 636                         | NR               | 800       | 17                          | NR               | 930       | 0                           | NR               |
| 415       | 10                          | NR               | 545       | 566                         | NR               | 675       | 579                         | NR               | 805       | 14                          | NR               | 935       | 0                           | NR               |
| 420       | 19                          | NR               | 550       | 589                         | NR               | 680       | 524                         | NR               | 810       | 12                          | NR               | 940       | 0                           | NR               |
| 425       | 34                          | NR               | 555       | 612                         | NR               | 685       | 470                         | NR               | 815       | 11                          | NR               | 945       | 0                           | NR               |
| 430       | 61                          | NR               | 560       | 634                         | NR               | 690       | 421                         | NR               | 820       | 9                           | NR               | 950       | 0                           | NR               |
| 435       | 113                         | NR               | 565       | 660                         | NR               | 695       | 371                         | NR               | 825       | 8                           | NR               | 955       | 0                           | NR               |
| 440       | 198                         | NR               | 570       | 688                         | NR               | 700       | 327                         | NR               | 830       | 7                           | NR               | 960       | 0                           | NR               |
| 445       | 288                         | NR               | 575       | 719                         | NR               | 705       | 288                         | NR               | 835       | 6                           | NR               | 965       | 0                           | NR               |
| 450       | 286                         | NR               | 580       | 754                         | NR               | 710       | 251                         | NR               | 840       | 5                           | NR               | 970       | 0                           | NR               |
| 455       | 228                         | NR               | 585       | 791                         | NR               | 715       | 220                         | NR               | 845       | 4                           | NR               | 975       | 0                           | NR               |
| 460       | 207                         | NR               | 590       | 831                         | NR               | 720       | 192                         | NR               | 850       | 4                           | NR               | 980       | 0                           | NR               |
| 465       | 186                         | NR               | 595       | 870                         | NR               | 725       | 166                         | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 168                         | NR               | 600       | 907                         | NR               | 730       | 144                         | NR               | 860       | 3                           | NR               | 990       | 1                           | NR               |
| 475       | 177                         | NR               | 605       | 940                         | NR               | 735       | 124                         | NR               | 865       | 2                           | NR               | 995       | 1                           | NR               |
| 480       | 198                         | NR               | 610       | 967                         | NR               | 740       | 106                         | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 223                         | NR               | 615       | 988                         | NR               | 745       | 91                          | NR               | 875       | 2                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-13





TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 98$   
 $CIE R_a = 91.8$   
 $R_9 = 54.7$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 98 | CES76 = 90 |
| CES02 = 64 | CES27 = 95 | CES52 = 98 | CES77 = 90 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 89 |
| CES04 = 71 | CES29 = 95 | CES54 = 96 | CES79 = 93 |
| CES05 = 51 | CES30 = 98 | CES55 = 95 | CES80 = 94 |
| CES06 = 52 | CES31 = 96 | CES56 = 94 | CES81 = 82 |
| CES07 = 44 | CES32 = 91 | CES57 = 94 | CES82 = 97 |
| CES08 = 43 | CES33 = 97 | CES58 = 94 | CES83 = 96 |
| CES09 = 29 | CES34 = 96 | CES59 = 96 | CES84 = 96 |
| CES10 = 77 | CES35 = 98 | CES60 = 96 | CES85 = 85 |
| CES11 = 59 | CES36 = 90 | CES61 = 94 | CES86 = 82 |
| CES12 = 66 | CES37 = 95 | CES62 = 95 | CES87 = 93 |
| CES13 = 44 | CES38 = 96 | CES63 = 94 | CES88 = 95 |
| CES14 = 74 | CES39 = 99 | CES64 = 92 | CES89 = 85 |
| CES15 = 72 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 48 | CES41 = 98 | CES66 = 91 | CES91 = 85 |
| CES17 = 50 | CES42 = 97 | CES67 = 90 | CES92 = 82 |
| CES18 = 57 | CES43 = 97 | CES68 = 91 | CES93 = 89 |
| CES19 = 72 | CES44 = 99 | CES69 = 93 | CES94 = 79 |
| CES20 = 68 | CES45 = 99 | CES70 = 90 | CES95 = 87 |
| CES21 = 87 | CES46 = 96 | CES71 = 89 | CES96 = 92 |
| CES22 = 79 | CES47 = 94 | CES72 = 96 | CES97 = 96 |
| CES23 = 92 | CES48 = 93 | CES73 = 87 | CES98 = 93 |
| CES24 = 91 | CES49 = 96 | CES74 = 92 | CES99 = 90 |
| CES25 = 72 | CES50 = 98 | CES75 = 90 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)