

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049349

Luminaire Tested: **GALN-SA9A-930-U-RBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1049349  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA9A-930-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 9xLight Square PACKAGE  
90CRI 3000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (126) 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20285.7 lumens  
Efficiency: N/A  
Efficacy: 82.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3


Input Watts (W): 244.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd  
 - - - 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 3 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 101.6    | 0.0    | 101.6   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 20184.1  | 0.0    | 20184.1 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 20285.7  | 0.0    | 20285.7 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 7.9     | 0.0       |
| 10°-20°   | 44.6    | 0.2       |
| 20°-30°   | 480.7   | 2.4       |
| 30°-40°   | 1421.6  | 7.0       |
| 40°-50°   | 4236.9  | 20.9      |
| 50°-60°   | 6718.1  | 33.1      |
| 60°-70°   | 5608.0  | 27.6      |
| 70°-80°   | 1729.3  | 8.5       |
| 80°-90°   | 38.5    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20285.7 | 100.0     |
| 0°-180°   | 20285.7 | 100.0     |

**Coefficient of Utilization**



REPORT NUMBER: P1049349


CATALOG NUMBER: GALN-SA9A-930-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 514.6   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 12340.3 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 7299.4  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 29.7    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 18.7    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 36.3    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 37.9    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 8.7     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 88.9   | 88.9   | 88.9  | 88.9  | 88.9  | 88.9  | 88.9  | 88.9  | 88.9  | 88.9  |
| 2.5°   | 81.2   | 81.2   | 81.2  | 81.2  | 79.7  | 79.7  | 78.2  | 78.2  | 76.6  | 76.6  |
| 5°     | 85.8   | 85.8   | 84.3  | 82.8  | 82.8  | 81.2  | 79.7  | 78.2  | 78.2  | 76.6  |
| 7.5°   | 93.5   | 92.0   | 90.4  | 88.9  | 85.8  | 84.3  | 81.2  | 79.7  | 78.2  | 75.1  |
| 10°    | 102.7  | 99.6   | 96.6  | 93.5  | 90.4  | 87.4  | 84.3  | 82.8  | 79.7  | 78.2  |
| 12.5°  | 115.0  | 110.4  | 104.2 | 99.6  | 96.6  | 92.0  | 88.9  | 85.8  | 81.2  | 78.2  |
| 15°    | 125.7  | 119.6  | 111.9 | 105.8 | 101.2 | 95.0  | 90.4  | 85.8  | 82.8  | 78.2  |
| 17.5°  | 141.0  | 130.3  | 118.0 | 110.4 | 104.2 | 96.6  | 88.9  | 84.3  | 79.7  | 73.6  |
| 20°    | 167.1  | 145.6  | 122.6 | 113.4 | 104.2 | 95.0  | 85.8  | 79.7  | 75.1  | 69.0  |
| 22.5°  | 208.5  | 171.7  | 134.9 | 121.1 | 108.8 | 95.0  | 82.8  | 76.6  | 70.5  | 64.4  |
| 25°    | 288.2  | 222.3  | 156.4 | 138.0 | 119.6 | 101.2 | 82.8  | 75.1  | 69.0  | 61.3  |
| 27.5°  | 383.2  | 285.1  | 185.5 | 159.4 | 134.9 | 108.8 | 82.8  | 73.6  | 65.9  | 56.7  |
| 30°    | 479.8  | 349.5  | 217.7 | 184.0 | 150.2 | 116.5 | 82.8  | 72.0  | 62.9  | 52.1  |
| 32.5°  | 571.8  | 409.3  | 245.3 | 205.4 | 165.6 | 124.2 | 84.3  | 72.0  | 59.8  | 47.5  |
| 35°    | 665.3  | 458.4  | 249.9 | 208.5 | 167.1 | 124.2 | 82.8  | 69.0  | 56.7  | 42.9  |
| 37.5°  | 784.9  | 513.5  | 240.7 | 199.3 | 159.4 | 118.0 | 78.2  | 65.9  | 53.7  | 39.9  |
| 40°    | 965.8  | 605.5  | 245.3 | 202.4 | 159.4 | 116.5 | 73.6  | 61.3  | 50.6  | 38.3  |
| 42.5°  | 1300.0 | 783.3  | 265.2 | 216.1 | 167.1 | 116.5 | 67.5  | 56.7  | 47.5  | 36.8  |
| 45°    | 2247.3 | 1301.5 | 355.6 | 282.1 | 208.5 | 134.9 | 61.3  | 52.1  | 44.5  | 35.3  |
| 47.5°  | 3717.5 | 2178.4 | 639.2 | 493.6 | 349.5 | 203.9 | 59.8  | 52.1  | 44.5  | 35.3  |
| 50°    | 4744.5 | 2774.7 | 804.8 | 619.3 | 433.8 | 248.3 | 62.9  | 53.7  | 46.0  | 36.8  |
| 52.5°  | 4736.9 | 2817.6 | 896.8 | 688.3 | 481.4 | 272.9 | 65.9  | 56.7  | 49.1  | 39.9  |
| 55°    | 4211.1 | 2563.1 | 913.7 | 702.1 | 492.1 | 280.5 | 70.5  | 61.3  | 52.1  | 42.9  |
| 57.5°  | 3519.7 | 2176.8 | 833.9 | 645.4 | 458.4 | 269.8 | 81.2  | 70.5  | 61.3  | 50.6  |
| 60°    | 2783.9 | 1716.9 | 650.0 | 513.5 | 378.6 | 242.2 | 107.3 | 93.5  | 81.2  | 67.5  |
| 62.5°  | 1922.3 | 1244.8 | 567.2 | 455.3 | 344.9 | 233.0 | 122.6 | 108.8 | 96.6  | 82.8  |
| 65°    | 1359.7 | 936.6  | 512.0 | 417.0 | 323.5 | 228.4 | 133.4 | 118.0 | 104.2 | 88.9  |
| 67.5°  | 1016.4 | 745.0  | 472.2 | 390.9 | 309.7 | 228.4 | 147.2 | 128.8 | 111.9 | 93.5  |
| 70°    | 778.7  | 611.7  | 443.0 | 377.1 | 312.7 | 246.8 | 180.9 | 154.8 | 130.3 | 104.2 |
| 72.5°  | 634.7  | 522.7  | 409.3 | 361.8 | 314.3 | 266.7 | 219.2 | 185.5 | 151.8 | 116.5 |
| 75°    | 525.8  | 447.6  | 369.4 | 329.6 | 291.3 | 251.4 | 211.6 | 180.9 | 151.8 | 121.1 |
| 77.5°  | 349.5  | 318.9  | 286.7 | 263.7 | 240.7 | 216.1 | 193.2 | 167.1 | 142.6 | 116.5 |
| 80°    | 122.6  | 118.0  | 113.4 | 122.6 | 131.8 | 141.0 | 150.2 | 131.8 | 115.0 | 96.6  |
| 82.5°  | 18.4   | 16.9   | 15.3  | 16.9  | 18.4  | 19.9  | 21.5  | 23.0  | 24.5  | 26.1  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 |
| 0.0 | 2.5°   | 75.1  | 75.1 | 73.6  | 73.6 | 73.6  | 72.0 | 72.0  | 70.5 | 70.5  | 70.5 |
| 0.0 | 5°     | 73.6  | 73.6 | 72.0  | 70.5 | 69.0  | 69.0 | 67.5  | 65.9 | 65.9  | 64.4 |
| 0.0 | 7.5°   | 72.0  | 70.5 | 69.0  | 67.5 | 65.9  | 64.4 | 62.9  | 61.3 | 61.3  | 59.8 |
| 0.0 | 10°    | 73.6  | 70.5 | 69.0  | 65.9 | 64.4  | 62.9 | 59.8  | 58.3 | 56.7  | 56.7 |
| 0.0 | 12.5°  | 70.5  | 69.0 | 65.9  | 62.9 | 61.3  | 58.3 | 56.7  | 53.7 | 52.1  | 52.1 |
| 0.0 | 15°    | 70.5  | 67.5 | 62.9  | 59.8 | 56.7  | 55.2 | 52.1  | 49.1 | 47.5  | 46.0 |
| 0.0 | 17.5°  | 65.9  | 62.9 | 58.3  | 55.2 | 52.1  | 49.1 | 46.0  | 42.9 | 41.4  | 39.9 |
| 0.0 | 20°    | 59.8  | 56.7 | 52.1  | 47.5 | 44.5  | 41.4 | 38.3  | 35.3 | 33.7  | 32.2 |
| 0.0 | 22.5°  | 53.7  | 50.6 | 46.0  | 41.4 | 38.3  | 35.3 | 30.7  | 27.6 | 26.1  | 23.0 |
| 0.0 | 25°    | 50.6  | 46.0 | 41.4  | 36.8 | 32.2  | 29.1 | 24.5  | 19.9 | 16.9  | 13.8 |
| 0.0 | 27.5°  | 42.9  | 38.3 | 33.7  | 29.1 | 24.5  | 19.9 | 15.3  | 10.7 | 7.7   | 6.1  |
| 0.0 | 30°    | 36.8  | 32.2 | 27.6  | 23.0 | 16.9  | 12.3 | 7.7   | 1.5  | 1.5   | 1.5  |
| 0.0 | 32.5°  | 30.7  | 26.1 | 19.9  | 15.3 | 12.3  | 7.7  | 4.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 24.5  | 19.9 | 13.8  | 9.2  | 7.7   | 4.6  | 3.1   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 21.5  | 16.9 | 10.7  | 4.6  | 3.1   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 19.9  | 13.8 | 7.7   | 1.5  | 1.5   | 1.5  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 19.9  | 13.8 | 6.1   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 19.9  | 13.8 | 6.1   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 19.9  | 13.8 | 6.1   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 21.5  | 15.3 | 7.7   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 24.5  | 18.4 | 12.3  | 6.1  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 30.7  | 27.6 | 23.0  | 19.9 | 15.3  | 10.7 | 4.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 39.9  | 39.9 | 38.3  | 36.8 | 27.6  | 18.4 | 9.2   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 53.7  | 53.7 | 53.7  | 53.7 | 39.9  | 27.6 | 13.8  | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 65.9  | 62.9 | 58.3  | 55.2 | 41.4  | 27.6 | 13.8  | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 65.9  | 59.8 | 52.1  | 44.5 | 33.7  | 23.0 | 10.7  | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 61.3  | 49.1 | 35.3  | 23.0 | 16.9  | 12.3 | 6.1   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 61.3  | 42.9 | 24.5  | 6.1  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 61.3  | 41.4 | 19.9  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 67.5  | 46.0 | 23.0  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 67.5  | 46.0 | 23.0  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 59.8  | 39.9 | 19.9  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 19.9  | 13.8 | 6.1   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |

CATALOG NUMBER: GALN-SA9A-930-U-RBC

[illegible]

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  |
| 0.0   | 2.5°   | 69.0 | 69.0  | 69.0 | 67.5  | 67.5 | 67.5  | 67.5 | 65.9  | 65.9 | 65.9  |
| 0.0   | 5°     | 62.9 | 62.9  | 61.3 | 61.3  | 59.8 | 59.8  | 58.3 | 58.3  | 56.7 | 56.7  |
| 0.0   | 7.5°   | 58.3 | 56.7  | 56.7 | 55.2  | 53.7 | 53.7  | 52.1 | 52.1  | 50.6 | 49.1  |
| 0.0   | 10°    | 53.7 | 52.1  | 52.1 | 50.6  | 49.1 | 47.5  | 47.5 | 46.0  | 44.5 | 42.9  |
| 0.0   | 12.5°  | 49.1 | 47.5  | 46.0 | 44.5  | 42.9 | 41.4  | 41.4 | 39.9  | 38.3 | 36.8  |
| 0.0   | 15°    | 42.9 | 41.4  | 39.9 | 38.3  | 36.8 | 35.3  | 35.3 | 33.7  | 32.2 | 30.7  |
| 0.0   | 17.5°  | 36.8 | 35.3  | 35.3 | 33.7  | 32.2 | 30.7  | 29.1 | 26.1  | 24.5 | 23.0  |
| 0.0   | 20°    | 27.6 | 26.1  | 24.5 | 23.0  | 21.5 | 18.4  | 16.9 | 13.8  | 10.7 | 9.2   |
| 0.0   | 22.5°  | 18.4 | 15.3  | 13.8 | 10.7  | 7.7  | 6.1   | 4.6  | 1.5   | 0.0  | 0.0   |
| 0.0   | 25°    | 6.1  | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9  | 88.9 | 88.9   | 88.9 |
| 0.0 | 2.5°   | 64.4  | 64.4 | 64.4  | 62.9 | 62.9  | 62.9 | 62.9  | 62.9 | 62.9   | 62.9 |
| 0.0 | 5°     | 55.2  | 55.2 | 55.2  | 53.7 | 53.7  | 52.1 | 52.1  | 52.1 | 50.6   | 50.6 |
| 0.0 | 7.5°   | 47.5  | 46.0 | 46.0  | 44.5 | 44.5  | 42.9 | 42.9  | 42.9 | 41.4   | 41.4 |
| 0.0 | 10°    | 39.9  | 38.3 | 38.3  | 36.8 | 36.8  | 35.3 | 35.3  | 33.7 | 33.7   | 32.2 |
| 0.0 | 12.5°  | 35.3  | 33.7 | 32.2  | 30.7 | 30.7  | 29.1 | 27.6  | 27.6 | 26.1   | 24.5 |
| 0.0 | 15°    | 27.6  | 26.1 | 24.5  | 23.0 | 21.5  | 19.9 | 18.4  | 18.4 | 16.9   | 15.3 |
| 0.0 | 17.5°  | 18.4  | 15.3 | 13.8  | 12.3 | 12.3  | 10.7 | 9.2   | 7.7  | 6.1    | 4.6  |
| 0.0 | 20°    | 4.6   | 3.1  | 1.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GALN-SA9A-930-U-RBC

[illegible]

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   |
| 0.0    | 2.5°   | 62.9 | 61.3   | 61.3 | 61.3   | 62.9 | 62.9   | 62.9 | 62.9   | 62.9 | 62.9   |
| 0.0    | 5°     | 50.6 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   | 49.1 | 49.1   |
| 0.0    | 7.5°   | 41.4 | 39.9   | 39.9 | 39.9   | 39.9 | 38.3   | 38.3 | 38.3   | 38.3 | 38.3   |
| 0.0    | 10°    | 32.2 | 30.7   | 30.7 | 30.7   | 30.7 | 29.1   | 29.1 | 29.1   | 29.1 | 29.1   |
| 0.0    | 12.5°  | 23.0 | 23.0   | 21.5 | 21.5   | 21.5 | 19.9   | 19.9 | 19.9   | 19.9 | 18.4   |
| 0.0    | 15°    | 13.8 | 12.3   | 10.7 | 10.7   | 10.7 | 9.2    | 9.2  | 9.2    | 9.2  | 7.7    |
| 0.0    | 17.5°  | 3.1  | 3.1    | 1.5  | 1.5    | 1.5  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 |
| 0.0  | 2.5°   | 64.4   | 64.4 | 65.9   | 65.9 | 67.5   | 70.5 | 72.0   | 73.6 | 76.6   | 79.7 |
| 0.0  | 5°     | 50.6   | 52.1 | 52.1   | 53.7 | 55.2   | 56.7 | 58.3   | 59.8 | 62.9   | 65.9 |
| 0.0  | 7.5°   | 39.9   | 39.9 | 41.4   | 41.4 | 42.9   | 46.0 | 47.5   | 49.1 | 52.1   | 56.7 |
| 0.0  | 10°    | 30.7   | 30.7 | 32.2   | 32.2 | 33.7   | 36.8 | 38.3   | 39.9 | 42.9   | 47.5 |
| 0.0  | 12.5°  | 19.9   | 21.5 | 21.5   | 23.0 | 24.5   | 27.6 | 29.1   | 30.7 | 33.7   | 36.8 |
| 0.0  | 15°    | 9.2    | 10.7 | 10.7   | 12.3 | 13.8   | 16.9 | 18.4   | 19.9 | 23.0   | 27.6 |
| 0.0  | 17.5°  | 1.5    | 1.5  | 3.1    | 3.1  | 4.6    | 6.1  | 7.7    | 9.2  | 13.8   | 16.9 |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 6.1  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.5  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 88.9 | 88.9   | 88.9 | 88.9   | 88.9 | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   |
| 0.0    | 2.5°   | 84.3 | 87.4   | 90.4 | 93.5   | 96.6 | 99.6   | 101.2 | 104.2  | 105.8 | 107.3  |
| 0.0    | 5°     | 72.0 | 75.1   | 79.7 | 82.8   | 85.8 | 88.9   | 92.0  | 93.5   | 95.0  | 96.6   |
| 0.0    | 7.5°   | 62.9 | 65.9   | 70.5 | 73.6   | 76.6 | 79.7   | 82.8  | 85.8   | 87.4  | 88.9   |
| 0.0    | 10°    | 53.7 | 58.3   | 61.3 | 65.9   | 69.0 | 72.0   | 75.1  | 78.2   | 81.2  | 82.8   |
| 0.0    | 12.5°  | 42.9 | 47.5   | 52.1 | 55.2   | 59.8 | 64.4   | 67.5  | 70.5   | 73.6  | 76.6   |
| 0.0    | 15°    | 33.7 | 38.3   | 42.9 | 46.0   | 50.6 | 55.2   | 59.8  | 62.9   | 65.9  | 69.0   |
| 0.0    | 17.5°  | 24.5 | 29.1   | 33.7 | 36.8   | 41.4 | 46.0   | 49.1  | 53.7   | 56.7  | 59.8   |
| 0.0    | 20°    | 12.3 | 16.9   | 21.5 | 26.1   | 30.7 | 35.3   | 38.3  | 42.9   | 46.0  | 49.1   |
| 0.0    | 22.5°  | 1.5  | 6.1    | 10.7 | 13.8   | 18.4 | 23.0   | 26.1  | 30.7   | 33.7  | 36.8   |
| 0.0    | 25°    | 0.0  | 1.5    | 4.6  | 6.1    | 7.7  | 10.7   | 13.8  | 16.9   | 19.9  | 23.0   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.5    | 3.1   | 6.1    | 9.2   | 12.3   |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 1.5    | 1.5   | 3.1    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 4.6   | 7.7    | 9.2   | 10.7   |
|        | 87.5°  | 0.0  | 1.5    | 3.1  | 4.6    | 6.1  | 9.2    | 12.3  | 15.3   | 16.9  | 18.4   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 88.9  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.3 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 98.1  | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 90.4  | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 85.8  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 78.2  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.0  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.4  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 52.1  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39.9  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.6  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.3  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4.6   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.5   |        |      |        |      |        |      |        |      |        |      |        |
| 6.1   |        |      |        |      |        |      |        |      |        |      |        |
| 13.8  |        |      |        |      |        |      |        |      |        |      |        |
| 19.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  |
| 0.0  | 2.5°   | 108.8  | 108.8 | 108.8  | 108.8 | 107.3  | 107.3 | 107.3  | 105.8 | 105.8  | 104.2 |
| 0.0  | 5°     | 99.6   | 101.2 | 101.2  | 101.2 | 101.2  | 101.2 | 101.2  | 101.2 | 99.6   | 99.6  |
| 0.0  | 7.5°   | 92.0   | 93.5  | 95.0   | 95.0  | 96.6   | 96.6  | 96.6   | 95.0  | 95.0   | 93.5  |
| 0.0  | 10°    | 87.4   | 88.9  | 88.9   | 90.4  | 90.4   | 90.4  | 90.4   | 90.4  | 90.4   | 90.4  |
| 0.0  | 12.5°  | 81.2   | 82.8  | 84.3   | 84.3  | 85.8   | 85.8  | 85.8   | 85.8  | 84.3   | 84.3  |
| 0.0  | 15°    | 73.6   | 76.6  | 78.2   | 79.7  | 79.7   | 81.2  | 81.2   | 81.2  | 81.2   | 81.2  |
| 0.0  | 17.5°  | 67.5   | 70.5  | 72.0   | 73.6  | 73.6   | 75.1  | 75.1   | 76.6  | 76.6   | 76.6  |
| 0.0  | 20°    | 55.2   | 58.3  | 59.8   | 62.9  | 64.4   | 65.9  | 67.5   | 69.0  | 69.0   | 70.5  |
| 0.0  | 22.5°  | 42.9   | 46.0  | 47.5   | 50.6  | 52.1   | 53.7  | 55.2   | 56.7  | 58.3   | 59.8  |
| 0.0  | 25°    | 30.7   | 33.7  | 35.3   | 38.3  | 39.9   | 41.4  | 42.9   | 44.5  | 44.5   | 46.0  |
| 0.0  | 27.5°  | 16.9   | 19.9  | 23.0   | 24.5  | 27.6   | 29.1  | 30.7   | 32.2  | 33.7   | 35.3  |
| 0.0  | 30°    | 7.7    | 9.2   | 10.7   | 13.8  | 15.3   | 16.9  | 18.4   | 21.5  | 23.0   | 24.5  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.5    | 4.6   | 6.1    | 7.7   | 9.2    | 10.7  | 10.7   | 12.3  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.5    | 3.1   | 4.6    | 6.1   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.1    | 3.1   | 3.1    | 4.6   | 4.6    | 4.6   | 4.6    | 4.6   | 4.6    | 4.6   |
|      | 82.5°  | 7.7    | 9.2   | 10.7   | 10.7  | 12.3   | 12.3  | 12.3   | 12.3  | 10.7   | 10.7  |
|      | 85°    | 15.3   | 16.9  | 18.4   | 18.4  | 19.9   | 19.9  | 19.9   | 19.9  | 19.9   | 19.9  |
|      | 87.5°  | 21.5   | 23.0  | 24.5   | 24.5  | 26.1   | 26.1  | 26.1   | 26.1  | 26.1   | 26.1  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 88.9   | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 104.2  | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 99.6   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 93.5   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 90.4   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 84.3   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 81.2   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 76.6   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 69.0   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 59.8   | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 47.5   | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 36.8   | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.1   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15.3   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 9.2    | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.5    | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 4.6    |        |      |        |      |        |      |        |      |        |      |
| 10.7   |        |      |        |      |        |      |        |      |        |      |
| 19.9   |        |      |        |      |        |      |        |      |        |      |
| 26.1   |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   |
| 0.0    | 2.5°   | 102.7 | 102.7  | 101.2 | 101.2  | 101.2 | 101.2  | 101.2 | 102.7  | 104.2 | 104.2  |
| 0.0    | 5°     | 98.1  | 98.1   | 96.6  | 96.6   | 96.6  | 98.1   | 98.1  | 99.6   | 101.2 | 102.7  |
| 0.0    | 7.5°   | 93.5  | 92.0   | 92.0  | 93.5   | 93.5  | 95.0   | 95.0  | 96.6   | 98.1  | 99.6   |
| 0.0    | 10°    | 90.4  | 88.9   | 88.9  | 88.9   | 90.4  | 90.4   | 92.0  | 93.5   | 95.0  | 96.6   |
| 0.0    | 12.5°  | 84.3  | 84.3   | 84.3  | 84.3   | 85.8  | 85.8   | 87.4  | 88.9   | 92.0  | 93.5   |
| 0.0    | 15°    | 81.2  | 79.7   | 79.7  | 79.7   | 79.7  | 81.2   | 81.2  | 84.3   | 87.4  | 88.9   |
| 0.0    | 17.5°  | 75.1  | 75.1   | 73.6  | 73.6   | 75.1  | 75.1   | 76.6  | 79.7   | 82.8  | 84.3   |
| 0.0    | 20°    | 69.0  | 67.5   | 65.9  | 65.9   | 67.5  | 67.5   | 69.0  | 72.0   | 75.1  | 76.6   |
| 0.0    | 22.5°  | 59.8  | 58.3   | 58.3  | 58.3   | 58.3  | 59.8   | 59.8  | 62.9   | 67.5  | 70.5   |
| 0.0    | 25°    | 47.5  | 49.1   | 49.1  | 50.6   | 50.6  | 52.1   | 53.7  | 56.7   | 61.3  | 64.4   |
| 0.0    | 27.5°  | 36.8  | 38.3   | 38.3  | 41.4   | 42.9  | 44.5   | 46.0  | 50.6   | 55.2  | 58.3   |
| 0.0    | 30°    | 27.6  | 29.1   | 30.7  | 32.2   | 35.3  | 38.3   | 41.4  | 46.0   | 50.6  | 53.7   |
| 0.0    | 32.5°  | 16.9  | 19.9   | 21.5  | 24.5   | 27.6  | 30.7   | 33.7  | 38.3   | 44.5  | 49.1   |
| 0.0    | 35°    | 12.3  | 13.8   | 16.9  | 18.4   | 21.5  | 24.5   | 27.6  | 33.7   | 38.3  | 44.5   |
| 0.0    | 37.5°  | 6.1   | 9.2    | 12.3  | 15.3   | 18.4  | 21.5   | 24.5  | 30.7   | 36.8  | 41.4   |
| 0.0    | 40°    | 4.6   | 7.7    | 9.2   | 12.3   | 16.9  | 19.9   | 23.0  | 29.1   | 35.3  | 41.4   |
| 0.0    | 42.5°  | 3.1   | 4.6    | 6.1   | 10.7   | 13.8  | 18.4   | 23.0  | 29.1   | 35.3  | 41.4   |
| 0.0    | 45°    | 3.1   | 3.1    | 4.6   | 9.2    | 13.8  | 19.9   | 24.5  | 30.7   | 35.3  | 41.4   |
| 0.0    | 47.5°  | 3.1   | 4.6    | 6.1   | 12.3   | 15.3  | 19.9   | 24.5  | 29.1   | 35.3  | 39.9   |
| 0.0    | 50°    | 4.6   | 6.1    | 7.7   | 13.8   | 16.9  | 21.5   | 24.5  | 30.7   | 35.3  | 41.4   |
| 0.0    | 52.5°  | 3.1   | 4.6    | 6.1   | 12.3   | 16.9  | 23.0   | 27.6  | 33.7   | 39.9  | 44.5   |
| 0.0    | 55°    | 1.5   | 1.5    | 1.5   | 9.2    | 18.4  | 26.1   | 35.3  | 39.9   | 46.0  | 50.6   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 6.1    | 18.4  | 29.1   | 39.9  | 46.0   | 52.1  | 56.7   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 6.1    | 18.4  | 29.1   | 39.9  | 47.5   | 55.2  | 62.9   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 6.1    | 15.3  | 24.5   | 33.7  | 46.0   | 59.8  | 72.0   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 4.6    | 12.3  | 19.9   | 27.6  | 46.0   | 64.4  | 81.2   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 12.3  | 18.4   | 26.1  | 46.0   | 64.4  | 84.3   |
|        | 70°    | 0.0   | 0.0    | 0.0   | 4.6    | 12.3  | 19.9   | 27.6  | 46.0   | 64.4  | 82.8   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 13.8  | 21.5   | 30.7  | 46.0   | 61.3  | 76.6   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 6.1    | 13.8  | 23.0   | 32.2  | 46.0   | 59.8  | 72.0   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 4.6    | 13.8  | 21.5   | 30.7  | 44.5   | 58.3  | 70.5   |
|        | 80°    | 4.6   | 3.1    | 3.1   | 7.7    | 13.8  | 19.9   | 26.1  | 39.9   | 55.2  | 69.0   |
|        | 82.5°  | 9.2   | 9.2    | 7.7   | 10.7   | 13.8  | 18.4   | 23.0  | 35.3   | 49.1  | 61.3   |
|        | 85°    | 18.4  | 18.4   | 16.9  | 18.4   | 18.4  | 19.9   | 21.5  | 27.6   | 33.7  | 39.9   |
|        | 87.5°  | 24.5  | 24.5   | 23.0  | 23.0   | 23.0  | 21.5   | 21.5  | 21.5   | 21.5  | 19.9   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 88.9  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.8 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 104.2 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.2 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 98.1  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 95.0  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.0  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 87.4  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 79.7  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 73.6  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 67.5  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.9  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 58.3  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.7  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 49.1  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.5  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 44.5  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.0  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.6  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.2  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 62.9  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 70.5  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 84.3  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 99.6  | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.7 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.2 |        |      |        |      |        |      |        |      |        |      |        |
| 92.0  |        |      |        |      |        |      |        |      |        |      |        |
| 85.8  |        |      |        |      |        |      |        |      |        |      |        |
| 84.3  |        |      |        |      |        |      |        |      |        |      |        |
| 82.8  |        |      |        |      |        |      |        |      |        |      |        |
| 73.6  |        |      |        |      |        |      |        |      |        |      |        |
| 46.0  |        |      |        |      |        |      |        |      |        |      |        |
| 19.9  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |





REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9  | 88.9   | 88.9   |
| 0.0  | 2.5°   | 107.3  | 108.8 | 108.8  | 110.4 | 111.9  | 113.4 | 113.4  | 115.0 | 115.0  | 115.0  |
| 0.0  | 5°     | 105.8  | 108.8 | 110.4  | 111.9 | 113.4  | 115.0 | 116.5  | 118.0 | 119.6  | 119.6  |
| 0.0  | 7.5°   | 104.2  | 105.8 | 108.8  | 110.4 | 113.4  | 115.0 | 118.0  | 119.6 | 121.1  | 122.6  |
| 0.0  | 10°    | 101.2  | 104.2 | 107.3  | 110.4 | 113.4  | 116.5 | 119.6  | 122.6 | 125.7  | 127.2  |
| 0.0  | 12.5°  | 98.1   | 102.7 | 105.8  | 108.8 | 113.4  | 118.0 | 121.1  | 125.7 | 128.8  | 131.8  |
| 0.0  | 15°    | 96.6   | 99.6  | 104.2  | 107.3 | 113.4  | 119.6 | 124.2  | 130.3 | 136.4  | 141.0  |
| 0.0  | 17.5°  | 92.0   | 98.1  | 102.7  | 107.3 | 113.4  | 121.1 | 127.2  | 133.4 | 142.6  | 151.8  |
| 0.0  | 20°    | 85.8   | 90.4  | 96.6   | 101.2 | 110.4  | 118.0 | 127.2  | 134.9 | 148.7  | 162.5  |
| 0.0  | 22.5°  | 79.7   | 85.8  | 90.4   | 96.6  | 107.3  | 116.5 | 127.2  | 136.4 | 159.4  | 180.9  |
| 0.0  | 25°    | 73.6   | 81.2  | 87.4   | 93.5  | 105.8  | 118.0 | 130.3  | 142.6 | 180.9  | 219.2  |
| 0.0  | 27.5°  | 70.5   | 76.6  | 84.3   | 90.4  | 105.8  | 122.6 | 138.0  | 153.3 | 214.6  | 274.4  |
| 0.0  | 30°    | 65.9   | 73.6  | 79.7   | 87.4  | 107.3  | 127.2 | 147.2  | 167.1 | 260.6  | 354.1  |
| 0.0  | 32.5°  | 61.3   | 69.0  | 76.6   | 84.3  | 110.4  | 136.4 | 161.0  | 187.0 | 309.7  | 430.8  |
| 0.0  | 35°    | 56.7   | 65.9  | 73.6   | 81.2  | 115.0  | 150.2 | 184.0  | 217.7 | 354.1  | 489.0  |
| 0.0  | 37.5°  | 55.2   | 64.4  | 72.0   | 79.7  | 116.5  | 151.8 | 188.6  | 223.8 | 358.7  | 493.6  |
| 0.0  | 40°    | 56.7   | 64.4  | 73.6   | 81.2  | 111.9  | 142.6 | 171.7  | 202.4 | 343.4  | 482.9  |
| 0.0  | 42.5°  | 56.7   | 65.9  | 75.1   | 84.3  | 108.8  | 133.4 | 157.9  | 182.4 | 338.8  | 495.1  |
| 0.0  | 45°    | 55.2   | 64.4  | 73.6   | 82.8  | 105.8  | 127.2 | 150.2  | 171.7 | 366.4  | 559.5  |
| 0.0  | 47.5°  | 53.7   | 62.9  | 72.0   | 81.2  | 104.2  | 127.2 | 150.2  | 173.2 | 473.7  | 772.6  |
| 0.0  | 50°    | 53.7   | 62.9  | 70.5   | 78.2  | 105.8  | 134.9 | 162.5  | 190.1 | 689.8  | 1188.1 |
| 0.0  | 52.5°  | 56.7   | 64.4  | 70.5   | 76.6  | 108.8  | 142.6 | 174.8  | 207.0 | 876.9  | 1545.2 |
| 0.0  | 55°    | 61.3   | 65.9  | 72.0   | 76.6  | 116.5  | 154.8 | 194.7  | 233.0 | 933.6  | 1634.1 |
| 0.0  | 57.5°  | 67.5   | 72.0  | 76.6   | 81.2  | 130.3  | 179.4 | 226.9  | 275.9 | 938.2  | 1598.9 |
| 0.0  | 60°    | 75.1   | 81.2  | 85.8   | 90.4  | 142.6  | 196.2 | 248.3  | 300.5 | 849.3  | 1396.5 |
| 0.0  | 62.5°  | 92.0   | 99.6  | 105.8  | 113.4 | 164.0  | 213.1 | 263.7  | 312.7 | 705.2  | 1097.6 |
| 0.0  | 65°    | 105.8  | 111.9 | 118.0  | 124.2 | 173.2  | 223.8 | 272.9  | 321.9 | 597.9  | 873.8  |
| 0.0  | 67.5°  | 108.8  | 115.0 | 119.6  | 125.7 | 176.3  | 226.9 | 275.9  | 326.5 | 512.0  | 696.0  |
|      | 70°    | 110.4  | 118.0 | 127.2  | 134.9 | 187.0  | 239.1 | 289.7  | 341.9 | 453.8  | 565.7  |
|      | 72.5°  | 105.8  | 121.1 | 134.9  | 148.7 | 197.8  | 245.3 | 294.3  | 341.9 | 421.6  | 501.3  |
|      | 75°    | 105.8  | 127.2 | 147.2  | 167.1 | 203.9  | 239.1 | 275.9  | 311.2 | 372.5  | 433.8  |
|      | 77.5°  | 111.9  | 139.5 | 167.1  | 194.7 | 216.1  | 236.1 | 257.5  | 277.5 | 317.3  | 357.2  |
|      | 80°    | 111.9  | 141.0 | 168.6  | 197.8 | 207.0  | 217.7 | 226.9  | 236.1 | 240.7  | 245.3  |
|      | 82.5°  | 96.6   | 119.6 | 142.6  | 165.6 | 154.8  | 144.1 | 133.4  | 122.6 | 115.0  | 105.8  |
|      | 85°    | 49.1   | 53.7  | 56.7   | 59.8  | 55.2   | 50.6  | 46.0   | 41.4  | 38.3   | 33.7   |
|      | 87.5°  | 19.9   | 19.9  | 18.4   | 18.4  | 18.4   | 18.4  | 16.9   | 16.9  | 16.9   | 16.9   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 88.9   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 115.0  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 119.6  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 124.2  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 130.3  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 136.4  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 148.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 164.0  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 188.6  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 240.7  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 326.5  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 453.8  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 614.7  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 768.0  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 872.3  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 950.4  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1028.6 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1181.9 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1488.5 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2268.8 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3475.2 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4375.1 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4474.7 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4037.8 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3452.3 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2698.0 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2038.9 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1505.4 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1065.4 |        |        |      |        |      |        |      |        |      |        |      |
| 792.5  |        |        |      |        |      |        |      |        |      |        |      |
| 576.4  |        |        |      |        |      |        |      |        |      |        |      |
| 433.8  |        |        |      |        |      |        |      |        |      |        |      |
| 243.7  |        |        |      |        |      |        |      |        |      |        |      |
| 110.4  |        |        |      |        |      |        |      |        |      |        |      |
| 32.2   |        |        |      |        |      |        |      |        |      |        |      |
| 15.3   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 88.9   | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    |
| 0.0    | 2.5°   | 115.0  | 113.4   | 113.4   | 111.9   | 110.4   | 108.8   | 107.3   | 105.8   | 104.2   | 102.7   |
| 0.0    | 5°     | 119.6  | 119.6   | 119.6   | 118.0   | 118.0   | 116.5   | 116.5   | 115.0   | 113.4   | 111.9   |
| 0.0    | 7.5°   | 124.2  | 125.7   | 125.7   | 127.2   | 127.2   | 127.2   | 127.2   | 125.7   | 125.7   | 125.7   |
| 0.0    | 10°    | 131.8  | 133.4   | 134.9   | 136.4   | 138.0   | 139.5   | 139.5   | 141.0   | 141.0   | 141.0   |
| 0.0    | 12.5°  | 141.0  | 145.6   | 148.7   | 153.3   | 156.4   | 161.0   | 164.0   | 168.6   | 171.7   | 174.8   |
| 0.0    | 15°    | 154.8  | 162.5   | 171.7   | 179.4   | 187.0   | 197.8   | 210.0   | 220.7   | 231.5   | 248.3   |
| 0.0    | 17.5°  | 174.8  | 199.3   | 223.8   | 246.8   | 271.3   | 325.0   | 378.6   | 430.8   | 484.4   | 562.6   |
| 0.0    | 20°    | 213.1  | 286.7   | 358.7   | 432.3   | 504.3   | 692.9   | 879.9   | 1068.5  | 1255.5  | 1456.3  |
| 0.0    | 22.5°  | 298.9  | 479.8   | 660.7   | 841.6   | 1022.5  | 1416.5  | 1808.9  | 2202.9  | 2595.3  | 3056.7  |
| 0.0    | 25°    | 433.8  | 766.5   | 1099.1  | 1430.3  | 1762.9  | 2379.2  | 2997.0  | 3613.2  | 4229.5  | 4828.9  |
| 0.0    | 27.5°  | 631.6  | 1140.5  | 1649.5  | 2156.9  | 2665.8  | 3501.3  | 4338.3  | 5173.8  | 6009.2  | 6686.8  |
| 0.0    | 30°    | 875.3  | 1565.2  | 2255.0  | 2944.8  | 3634.7  | 4585.1  | 5535.6  | 6484.5  | 7434.9  | 8175.3  |
| 0.0    | 32.5°  | 1105.3 | 1949.9  | 2794.6  | 3637.7  | 4482.4  | 5564.7  | 6648.5  | 7730.8  | 8813.1  | 9622.5  |
| 0.0    | 35°    | 1255.5 | 2276.5  | 3299.0  | 4319.9  | 5340.9  | 6512.1  | 7683.3  | 8852.9  | 10024.1 | 10948.5 |
| 0.0    | 37.5°  | 1405.7 | 2584.6  | 3761.9  | 4940.8  | 6118.1  | 7404.3  | 8690.4  | 9976.6  | 11262.7 | 12404.8 |
| 0.0    | 40°    | 1574.4 | 2957.1  | 4338.3  | 5721.0  | 7102.3  | 8626.0  | 10148.3 | 11672.0 | 13194.3 | 14805.4 |
| 0.0    | 42.5°  | 1867.2 | 3574.9  | 5284.2  | 6991.9  | 8699.6  | 10715.5 | 12731.3 | 14745.7 | 16761.5 | 19061.0 |
| 0.0    | 45°    | 2417.5 | 4824.3  | 7232.6  | 9639.3  | 12046.1 | 14716.5 | 17388.5 | 20058.9 | 22729.4 | 25789.2 |
| 0.0    | 47.5°  | 3765.0 | 7076.2  | 10385.9 | 13697.1 | 17006.8 | 19890.3 | 22772.3 | 25655.8 | 28537.8 | 31585.3 |
| 0.0    | 50°    | 5760.9 | 9614.8  | 13468.7 | 17321.0 | 21174.9 | 23784.1 | 26391.6 | 29000.8 | 31608.3 | 34507.2 |
| 0.0    | 52.5°  | 7205.0 | 11219.8 | 15236.2 | 19251.1 | 23265.9 | 25620.6 | 27976.7 | 30331.4 | 32686.0 | 35394.8 |
| 0.0    | 55°    | 7313.8 | 11305.7 | 15299.1 | 19290.9 | 23282.8 | 25648.1 | 28013.5 | 30378.9 | 32744.3 | 35615.5 |
| 0.0    | 57.5°  | 6475.3 | 10434.9 | 14393.1 | 18352.7 | 22310.9 | 25004.3 | 27696.2 | 30389.6 | 33081.5 | 36185.8 |
| 0.0    | 60°    | 5508.0 | 9469.2  | 13428.8 | 17390.0 | 21349.7 | 24452.4 | 27556.7 | 30659.4 | 33762.2 | 36670.2 |
| 0.0    | 62.5°  | 4296.9 | 8371.6  | 12447.7 | 16522.4 | 20597.0 | 23747.3 | 26897.5 | 30046.2 | 33196.5 | 35377.9 |
| 0.0    | 65°    | 3202.4 | 7159.0  | 11115.6 | 15070.6 | 19027.2 | 21550.5 | 24073.8 | 26595.5 | 29118.8 | 30469.3 |
| 0.0    | 67.5°  | 2314.8 | 5727.2  | 9138.0  | 12550.4 | 15961.3 | 17767.1 | 19573.0 | 21377.3 | 23183.1 | 24216.3 |
|        | 70°    | 1565.2 | 3929.0  | 6291.3  | 8655.2  | 11017.5 | 12501.4 | 13986.8 | 15470.7 | 16954.7 | 18349.7 |
|        | 72.5°  | 1083.8 | 2411.4  | 3740.5  | 5068.0  | 6395.6  | 7888.7  | 9380.3  | 10873.4 | 12364.9 | 13841.2 |
|        | 75°    | 719.0  | 1323.0  | 1928.5  | 2532.5  | 3136.5  | 4241.7  | 5348.5  | 6453.8  | 7559.1  | 8439.0  |
|        | 77.5°  | 510.5  | 691.4   | 873.8   | 1054.7  | 1235.6  | 1442.5  | 1651.0  | 1858.0  | 2064.9  | 2379.2  |
|        | 80°    | 242.2  | 265.2   | 288.2   | 309.7   | 332.7   | 407.8   | 482.9   | 558.0   | 633.1   | 712.8   |
|        | 82.5°  | 115.0  | 124.2   | 133.4   | 141.0   | 150.2   | 157.9   | 165.6   | 173.2   | 180.9   | 173.2   |
|        | 85°    | 30.7   | 30.7    | 32.2    | 32.2    | 32.2    | 32.2    | 32.2    | 32.2    | 32.2    | 30.7    |
|        | 87.5°  | 13.8   | 13.8    | 13.8    | 13.8    | 13.8    | 13.8    | 13.8    | 12.3    | 12.3    | 10.7    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 88.9    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 101.2   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.4   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 124.2   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 142.6   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 176.3   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 266.7   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 639.2   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1658.7  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3518.2  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5428.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7364.4  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8917.3  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10433.4 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11872.9 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13548.4 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16416.6 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21360.4 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28849.0 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34632.9 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37406.0 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38103.5 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38488.3 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39290.1 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39576.7 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 37560.9 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31821.4 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25251.1 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19743.1 |        |      |        |      |        |      |        |      |        |      |        |
| 15317.4 |        |      |        |      |        |      |        |      |        |      |        |
| 9318.9  |        |      |        |      |        |      |        |      |        |      |        |
| 2693.4  |        |      |        |      |        |      |        |      |        |      |        |
| 792.5   |        |      |        |      |        |      |        |      |        |      |        |
| 164.0   |        |      |        |      |        |      |        |      |        |      |        |
| 29.1    |        |      |        |      |        |      |        |      |        |      |        |
| 10.7    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    |
| 0.0  | 2.5°   | 99.6    | 98.1    | 96.6    | 95.0    | 93.5    | 90.4    | 90.4    | 88.9    | 88.9    |
| 0.0  | 5°     | 108.8   | 107.3   | 105.8   | 104.2   | 104.2   | 102.7   | 101.2   | 101.2   | 99.6    |
| 0.0  | 7.5°   | 124.2   | 122.6   | 121.1   | 119.6   | 119.6   | 118.0   | 118.0   | 116.5   | 116.5   |
| 0.0  | 10°    | 142.6   | 142.6   | 142.6   | 142.6   | 142.6   | 141.0   | 141.0   | 141.0   | 139.5   |
| 0.0  | 12.5°  | 179.4   | 180.9   | 184.0   | 187.0   | 191.6   | 191.6   | 191.6   | 190.1   | 190.1   |
| 0.0  | 15°    | 283.6   | 300.5   | 312.7   | 325.0   | 335.7   | 360.2   | 357.2   | 352.6   | 349.5   |
| 0.0  | 17.5°  | 717.4   | 794.1   | 835.5   | 875.3   | 916.7   | 1030.2  | 1011.8  | 993.4   | 976.5   |
| 0.0  | 20°    | 1859.5  | 2060.3  | 2193.7  | 2327.1  | 2462.0  | 2675.0  | 2622.9  | 2570.8  | 2518.7  |
| 0.0  | 22.5°  | 3978.1  | 4439.5  | 4640.3  | 4841.1  | 5040.4  | 5297.9  | 5130.9  | 4963.8  | 4798.2  |
| 0.0  | 25°    | 6026.1  | 6625.5  | 6964.3  | 7303.1  | 7640.3  | 7787.5  | 7569.8  | 7350.6  | 7132.9  |
| 0.0  | 27.5°  | 8042.0  | 8719.5  | 9018.5  | 9315.9  | 9614.8  | 9922.9  | 9653.1  | 9381.8  | 9112.0  |
| 0.0  | 30°    | 9657.7  | 10398.1 | 10721.6 | 11043.5 | 11367.0 | 11581.6 | 11302.6 | 11022.1 | 10743.1 |
| 0.0  | 32.5°  | 11242.8 | 12052.2 | 12406.3 | 12760.5 | 13113.0 | 13421.2 | 13077.8 | 12732.9 | 12389.5 |
| 0.0  | 35°    | 12795.7 | 13720.1 | 14207.6 | 14695.1 | 15182.5 | 15469.2 | 15061.4 | 14652.1 | 14244.4 |
| 0.0  | 37.5°  | 14690.5 | 15832.5 | 16378.3 | 16924.0 | 17469.7 | 17992.5 | 17543.3 | 17092.6 | 16643.5 |
| 0.0  | 40°    | 18027.7 | 19638.9 | 20475.9 | 21314.4 | 22151.4 | 22825.9 | 22258.7 | 21691.5 | 21124.3 |
| 0.0  | 42.5°  | 23659.9 | 25959.3 | 27162.7 | 28364.6 | 29568.0 | 30621.1 | 30024.8 | 29428.5 | 28832.1 |
| 0.0  | 45°    | 31908.8 | 34968.6 | 36435.7 | 37901.2 | 39368.2 | 40137.8 | 39279.3 | 38419.3 | 37560.9 |
| 0.0  | 47.5°  | 37678.9 | 40726.4 | 42032.5 | 43338.6 | 44644.7 | 45523.1 | 44473.0 | 43422.9 | 42374.4 |
| 0.0  | 50°    | 40303.3 | 43202.2 | 44512.9 | 45822.0 | 47132.7 | 47830.2 | 46617.7 | 45403.5 | 44191.0 |
| 0.0  | 52.5°  | 40810.8 | 43519.5 | 45083.2 | 46648.3 | 48211.9 | 49144.0 | 47712.2 | 46278.9 | 44847.1 |
| 0.0  | 55°    | 41359.6 | 44230.8 | 46044.3 | 47859.4 | 49672.9 | 50963.6 | 49344.8 | 47724.5 | 46105.6 |
| 0.0  | 57.5°  | 42392.8 | 45497.1 | 47306.0 | 49113.3 | 50922.2 | 52018.3 | 50394.9 | 48770.0 | 47146.5 |
| 0.0  | 60°    | 42484.8 | 45391.3 | 46945.7 | 48501.7 | 50056.1 | 50746.0 | 49193.1 | 47638.6 | 46085.7 |
| 0.0  | 62.5°  | 39742.3 | 41923.7 | 43002.9 | 44082.1 | 45161.3 | 45911.0 | 44290.6 | 42668.7 | 41048.4 |
| 0.0  | 65°    | 33172.0 | 34522.5 | 35382.5 | 36242.5 | 37102.5 | 37996.2 | 36512.3 | 35028.4 | 33544.5 |
| 0.0  | 67.5°  | 26284.3 | 27317.5 | 28450.4 | 29583.3 | 30716.1 | 31671.2 | 30483.1 | 29293.5 | 28105.5 |
|      | 70°    | 21138.1 | 22531.6 | 23805.5 | 25079.4 | 26353.3 | 27135.1 | 25942.5 | 24748.3 | 23555.6 |
|      | 72.5°  | 16793.7 | 18270.0 | 19333.8 | 20396.2 | 21460.1 | 21651.7 | 20774.8 | 19898.0 | 19022.6 |
|      | 75°    | 10197.3 | 11077.3 | 11098.7 | 11118.6 | 11140.1 | 11322.5 | 10595.9 | 9869.3  | 9144.2  |
|      | 77.5°  | 3007.7  | 3321.9  | 3581.0  | 3838.6  | 4097.6  | 4410.4  | 4143.6  | 3875.4  | 3608.6  |
|      | 80°    | 870.7   | 950.4   | 1017.9  | 1083.8  | 1151.3  | 1111.4  | 1048.6  | 985.7   | 922.8   |
|      | 82.5°  | 156.4   | 147.2   | 145.6   | 144.1   | 144.1   | 136.4   | 124.2   | 111.9   | 99.6    |
|      | 85°    | 27.6    | 26.1    | 24.5    | 23.0    | 21.5    | 19.9    | 16.9    | 15.3    | 12.3    |
|      | 87.5°  | 9.2     | 7.7     | 6.1     | 4.6     | 4.6     | 1.5     | 1.5     | 1.5     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    | 88.9    |
| 0.0  | 0.0    | 2.5°   | 87.4    | 85.8    | 85.8    | 85.8    | 85.8    | 84.3    | 84.3    | 84.3    | 84.3    |
| 0.0  | 0.0    | 5°     | 96.6    | 96.6    | 95.0    | 95.0    | 93.5    | 93.5    | 92.0    | 92.0    | 90.4    |
| 0.0  | 0.0    | 7.5°   | 113.4   | 111.9   | 110.4   | 108.8   | 107.3   | 104.2   | 102.7   | 101.2   | 101.2   |
| 0.0  | 0.0    | 10°    | 136.4   | 133.4   | 131.8   | 128.8   | 127.2   | 124.2   | 121.1   | 118.0   | 115.0   |
| 0.0  | 0.0    | 12.5°  | 179.4   | 173.2   | 168.6   | 162.5   | 156.4   | 151.8   | 145.6   | 141.0   | 134.9   |
| 0.0  | 0.0    | 15°    | 311.2   | 295.9   | 279.0   | 259.1   | 237.6   | 217.7   | 196.2   | 184.0   | 170.2   |
| 0.0  | 0.0    | 17.5°  | 795.6   | 715.9   | 634.7   | 568.7   | 502.8   | 438.4   | 372.5   | 325.0   | 277.5   |
| 0.0  | 0.0    | 20°    | 2025.1  | 1804.3  | 1583.6  | 1365.9  | 1146.7  | 929.0   | 709.8   | 599.4   | 489.0   |
| 0.0  | 0.0    | 22.5°  | 3811.0  | 3401.7  | 2990.8  | 2593.8  | 2195.2  | 1798.2  | 1401.1  | 1151.3  | 902.9   |
| 0.0  | 0.0    | 25°    | 5882.0  | 5366.9  | 4851.9  | 4198.8  | 3544.2  | 2891.2  | 2238.1  | 1831.9  | 1425.7  |
| 0.0  | 0.0    | 27.5°  | 7654.1  | 7060.9  | 6467.6  | 5673.5  | 4879.4  | 4085.4  | 3291.3  | 2685.8  | 2081.8  |
| 0.0  | 0.0    | 30°    | 9188.6  | 8550.9  | 7913.2  | 6988.8  | 6064.4  | 5140.1  | 4215.7  | 3458.4  | 2701.1  |
| 0.0  | 0.0    | 32.5°  | 10519.2 | 9755.8  | 8992.4  | 8038.9  | 7085.4  | 6131.9  | 5178.4  | 4249.4  | 3320.4  |
| 0.0  | 0.0    | 35°    | 12053.8 | 11163.1 | 10270.9 | 9213.2  | 8153.9  | 7096.1  | 6038.4  | 4989.8  | 3939.7  |
| 0.0  | 0.0    | 37.5°  | 14003.7 | 12910.7 | 11816.1 | 10637.3 | 9458.4  | 8281.1  | 7102.3  | 5903.5  | 4704.7  |
| 0.0  | 0.0    | 40°    | 17736.5 | 16326.1 | 14915.8 | 13418.1 | 11918.9 | 10421.1 | 8923.4  | 7451.8  | 5980.1  |
| 0.0  | 0.0    | 42.5°  | 24424.8 | 22519.3 | 20613.9 | 18621.0 | 16626.6 | 14633.7 | 12639.3 | 10563.7 | 8486.5  |
| 0.0  | 0.0    | 45°    | 31973.2 | 29609.3 | 27244.0 | 25007.4 | 22769.2 | 20532.6 | 18296.0 | 15447.8 | 12599.5 |
| 0.0  | 0.0    | 47.5°  | 36218.0 | 33665.6 | 31113.2 | 28996.2 | 26879.1 | 24762.1 | 22645.1 | 19574.5 | 16504.0 |
| 0.0  | 0.0    | 50°    | 37780.1 | 35181.7 | 32583.3 | 30634.9 | 28685.0 | 26736.6 | 24786.6 | 21711.5 | 18634.8 |
| 0.0  | 0.0    | 52.5°  | 38112.7 | 35462.2 | 32811.7 | 30851.0 | 28890.4 | 26931.2 | 24970.6 | 21915.4 | 18860.1 |
| 0.0  | 0.0    | 55°    | 38796.4 | 35952.8 | 33107.6 | 30872.5 | 28637.4 | 26402.4 | 24167.3 | 21063.0 | 17958.8 |
| 0.0  | 0.0    | 57.5°  | 39690.2 | 36774.4 | 33858.7 | 31312.5 | 28766.2 | 26221.5 | 23675.2 | 20281.2 | 16887.2 |
| 0.0  | 0.0    | 60°    | 39455.6 | 36918.5 | 34379.9 | 31652.8 | 28924.1 | 26196.9 | 23468.3 | 19735.5 | 16001.2 |
| 0.0  | 0.0    | 62.5°  | 35384.0 | 33363.6 | 31341.6 | 29098.9 | 26854.6 | 24611.9 | 22369.1 | 18526.0 | 14682.8 |
| 0.0  | 0.0    | 65°    | 29109.6 | 27634.9 | 26160.2 | 24355.8 | 22550.0 | 20745.7 | 18941.4 | 15495.3 | 12050.7 |
| 0.0  | 0.0    | 67.5°  | 23592.4 | 21930.7 | 20267.4 | 18829.5 | 17390.0 | 15952.1 | 14512.6 | 11800.8 | 9089.0  |
|      |        | 70°    | 18743.6 | 16936.3 | 15127.4 | 13723.2 | 12317.4 | 10913.2 | 9509.0  | 7706.2  | 5905.0  |
|      |        | 72.5°  | 14885.2 | 13255.6 | 11626.1 | 10128.3 | 8629.1  | 7131.4  | 5632.1  | 4566.7  | 3501.3  |
|      |        | 75°    | 7114.5  | 6463.0  | 5811.5  | 5028.1  | 4244.8  | 3461.4  | 2678.1  | 2213.6  | 1750.7  |
|      |        | 77.5°  | 2636.7  | 2285.7  | 1933.1  | 1614.2  | 1295.4  | 978.0   | 659.2   | 604.0   | 548.8   |
|      |        | 80°    | 682.2   | 594.8   | 505.9   | 443.0   | 378.6   | 315.8   | 252.9   | 228.4   | 205.4   |
|      |        | 82.5°  | 78.2    | 72.0    | 67.5    | 64.4    | 59.8    | 56.7    | 52.1    | 47.5    | 42.9    |
|      |        | 85°    | 4.6     | 3.1     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 88.9   | 88.9   |
| 0.0    | 0.0  | 2.5°   | 82.8   | 81.2   |
| 0.0    | 0.0  | 5°     | 87.4   | 85.8   |
| 0.0    | 0.0  | 7.5°   | 96.6   | 93.5   |
| 0.0    | 0.0  | 10°    | 105.8  | 102.7  |
| 0.0    | 0.0  | 12.5°  | 119.6  | 115.0  |
| 0.0    | 0.0  | 15°    | 134.9  | 125.7  |
| 0.0    | 0.0  | 17.5°  | 161.0  | 141.0  |
| 0.0    | 0.0  | 20°    | 217.7  | 167.1  |
| 0.0    | 0.0  | 22.5°  | 306.6  | 208.5  |
| 0.0    | 0.0  | 25°    | 450.7  | 288.2  |
| 0.0    | 0.0  | 27.5°  | 627.0  | 383.2  |
| 0.0    | 0.0  | 30°    | 833.9  | 479.8  |
| 0.0    | 0.0  | 32.5°  | 1016.4 | 571.8  |
| 0.0    | 0.0  | 35°    | 1254.0 | 665.3  |
| 0.0    | 0.0  | 37.5°  | 1546.8 | 784.9  |
| 0.0    | 0.0  | 40°    | 2000.5 | 965.8  |
| 0.0    | 0.0  | 42.5°  | 2817.6 | 1300.0 |
| 0.0    | 0.0  | 45°    | 4575.9 | 2247.3 |
| 0.0    | 0.0  | 47.5°  | 7040.9 | 3717.5 |
| 0.0    | 0.0  | 50°    | 8613.8 | 4744.5 |
| 0.0    | 0.0  | 52.5°  | 8742.5 | 4736.9 |
| 0.0    | 0.0  | 55°    | 7980.6 | 4211.1 |
| 0.0    | 0.0  | 57.5°  | 6809.5 | 3519.7 |
| 0.0    | 0.0  | 60°    | 5659.7 | 2783.9 |
| 0.0    | 0.0  | 62.5°  | 4459.4 | 1922.3 |
| 0.0    | 0.0  | 65°    | 3259.1 | 1359.7 |
| 0.0    | 0.0  | 67.5°  | 2340.8 | 1016.4 |
|        |      | 70°    | 1539.1 | 778.7  |
|        |      | 72.5°  | 1002.6 | 634.7  |
|        |      | 75°    | 674.5  | 525.8  |
|        |      | 77.5°  | 394.0  | 349.5  |
|        |      | 80°    | 139.5  | 122.6  |
|        |      | 82.5°  | 26.1   | 18.4   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1049349

CATALOG NUMBER: GALN-SA9A-930-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-14

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-930-U-5WQ

Data in this report applies to families of products including GSS-SB1A-930-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-14  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-930-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 3000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 2993  
 CIE  $u'$ : 0.2501  
 CIE  $v'$ : 0.5245  
 Duv: 0.0021  
 CIE x: 0.4406  
 CIE y: 0.4107  
 CIE z: 0.1487  
 Peak Wavelength (nm): 621  
 Dominant Wavelength (nm): 582  
 Purity: 55.53327  
 R<sub>f</sub>: 92.6  
 R<sub>g</sub>: 98.5

CRI (Ra): 92.4  
 R1: 92.2  
 R2: 95.2  
 R3: 97.0  
 R4: 93.1  
 R5: 91.7  
 R6: 94.2  
 R7: 93.3  
 R8: 82.3  
 R9: 58.2  
 R10: 87.7  
 R11: 93.5  
 R12: 81.7  
 R13: 92.9  
 R14: 97.6  
 R15: 88.1



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-14


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-14

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-14

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 310                                  | NR                             | 620               | 998                                  | NR                             | 750               | 77                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 347                                  | NR                             | 625               | 993                                  | NR                             | 755               | 66                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 379                                  | NR                             | 630               | 983                                  | NR                             | 760               | 56                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 412                                  | NR                             | 635               | 960                                  | NR                             | 765               | 48                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 442                                  | NR                             | 640               | 930                                  | NR                             | 770               | 41                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 475                                  | NR                             | 645               | 889                                  | NR                             | 775               | 35                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 506                                  | NR                             | 650               | 846                                  | NR                             | 780               | 30                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 535                                  | NR                             | 655               | 794                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 565                                  | NR                             | 660               | 740                                  | NR                             | 790               | 22                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 592                                  | NR                             | 665               | 684                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 615                                  | NR                             | 670               | 624                                  | NR                             | 800               | 16                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 638                                  | NR                             | 675               | 567                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 20                                   | NR                             | 550               | 658                                  | NR                             | 680               | 513                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 38                                   | NR                             | 555               | 678                                  | NR                             | 685               | 459                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 70                                   | NR                             | 560               | 695                                  | NR                             | 690               | 412                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 136                                  | NR                             | 565               | 716                                  | NR                             | 695               | 363                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 262                                  | NR                             | 570               | 740                                  | NR                             | 700               | 320                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 424                                  | NR                             | 575               | 765                                  | NR                             | 705               | 281                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 406                                  | NR                             | 580               | 796                                  | NR                             | 710               | 245                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 313                                  | NR                             | 585               | 827                                  | NR                             | 715               | 215                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 294                                  | NR                             | 590               | 861                                  | NR                             | 720               | 188                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 250                                  | NR                             | 595               | 894                                  | NR                             | 725               | 162                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 217                                  | NR                             | 600               | 927                                  | NR                             | 730               | 140                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 228                                  | NR                             | 605               | 954                                  | NR                             | 735               | 121                                  | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 249                                  | NR                             | 610               | 976                                  | NR                             | 740               | 104                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 276                                  | NR                             | 615               | 992                                  | NR                             | 745               | 89                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-14

### Scotopic Flux vs. Wavelength



Scotopic Lumens: NR


S/P: 1.39

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 310                                  | NR                             | 620               | 998                                  | NR                             | 750               | 77                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 347                                  | NR                             | 625               | 993                                  | NR                             | 755               | 66                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 379                                  | NR                             | 630               | 983                                  | NR                             | 760               | 56                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 412                                  | NR                             | 635               | 960                                  | NR                             | 765               | 48                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 442                                  | NR                             | 640               | 930                                  | NR                             | 770               | 41                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 475                                  | NR                             | 645               | 889                                  | NR                             | 775               | 35                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 506                                  | NR                             | 650               | 846                                  | NR                             | 780               | 30                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 535                                  | NR                             | 655               | 794                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 565                                  | NR                             | 660               | 740                                  | NR                             | 790               | 22                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 592                                  | NR                             | 665               | 684                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 615                                  | NR                             | 670               | 624                                  | NR                             | 800               | 16                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 638                                  | NR                             | 675               | 567                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 20                                   | NR                             | 550               | 658                                  | NR                             | 680               | 513                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 38                                   | NR                             | 555               | 678                                  | NR                             | 685               | 459                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 70                                   | NR                             | 560               | 695                                  | NR                             | 690               | 412                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 136                                  | NR                             | 565               | 716                                  | NR                             | 695               | 363                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 262                                  | NR                             | 570               | 740                                  | NR                             | 700               | 320                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 424                                  | NR                             | 575               | 765                                  | NR                             | 705               | 281                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 406                                  | NR                             | 580               | 796                                  | NR                             | 710               | 245                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 313                                  | NR                             | 585               | 827                                  | NR                             | 715               | 215                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 294                                  | NR                             | 590               | 861                                  | NR                             | 720               | 188                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 250                                  | NR                             | 595               | 894                                  | NR                             | 725               | 162                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 217                                  | NR                             | 600               | 927                                  | NR                             | 730               | 140                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 228                                  | NR                             | 605               | 954                                  | NR                             | 735               | 121                                  | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 249                                  | NR                             | 610               | 976                                  | NR                             | 740               | 104                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 276                                  | NR                             | 615               | 992                                  | NR                             | 745               | 89                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |



REPORT NUMBER: SP1-2407-184-14

### Melanopic Flux vs. Wavelength


**Melanopic Lumens: NR**
**M/P: 2.69**


| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 310                                  | NR                             | 620               | 998                                  | NR                             | 750               | 77                                   | NR                             | 880               | 2                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 347                                  | NR                             | 625               | 993                                  | NR                             | 755               | 66                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 379                                  | NR                             | 630               | 983                                  | NR                             | 760               | 56                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 412                                  | NR                             | 635               | 960                                  | NR                             | 765               | 48                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 442                                  | NR                             | 640               | 930                                  | NR                             | 770               | 41                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 475                                  | NR                             | 645               | 889                                  | NR                             | 775               | 35                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 506                                  | NR                             | 650               | 846                                  | NR                             | 780               | 30                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 535                                  | NR                             | 655               | 794                                  | NR                             | 785               | 26                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 1                                    | NR                             | 530               | 565                                  | NR                             | 660               | 740                                  | NR                             | 790               | 22                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 2                                    | NR                             | 535               | 592                                  | NR                             | 665               | 684                                  | NR                             | 795               | 19                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 6                                    | NR                             | 540               | 615                                  | NR                             | 670               | 624                                  | NR                             | 800               | 16                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 10                                   | NR                             | 545               | 638                                  | NR                             | 675               | 567                                  | NR                             | 805               | 14                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 20                                   | NR                             | 550               | 658                                  | NR                             | 680               | 513                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 38                                   | NR                             | 555               | 678                                  | NR                             | 685               | 459                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 70                                   | NR                             | 560               | 695                                  | NR                             | 690               | 412                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 136                                  | NR                             | 565               | 716                                  | NR                             | 695               | 363                                  | NR                             | 825               | 8                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 262                                  | NR                             | 570               | 740                                  | NR                             | 700               | 320                                  | NR                             | 830               | 7                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 424                                  | NR                             | 575               | 765                                  | NR                             | 705               | 281                                  | NR                             | 835               | 6                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 406                                  | NR                             | 580               | 796                                  | NR                             | 710               | 245                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 313                                  | NR                             | 585               | 827                                  | NR                             | 715               | 215                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 294                                  | NR                             | 590               | 861                                  | NR                             | 720               | 188                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 250                                  | NR                             | 595               | 894                                  | NR                             | 725               | 162                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 217                                  | NR                             | 600               | 927                                  | NR                             | 730               | 140                                  | NR                             | 860               | 3                                    | NR                             | 990               | 0                                    | NR                             |
| 475               | 228                                  | NR                             | 605               | 954                                  | NR                             | 735               | 121                                  | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 249                                  | NR                             | 610               | 976                                  | NR                             | 740               | 104                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 276                                  | NR                             | 615               | 992                                  | NR                             | 745               | 89                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-14





TM-30-18

### Summary

$R_f = 92.6$   
 $R_g = 98.5$   
 $CIE R_a = 92.4$   
 $R_9 = 58.2$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 94 | CES51 = 98 | CES76 = 90 |
| CES02 = 63 | CES27 = 94 | CES52 = 98 | CES77 = 91 |
| CES03 = 32 | CES28 = 97 | CES53 = 96 | CES78 = 88 |
| CES04 = 70 | CES29 = 95 | CES54 = 95 | CES79 = 94 |
| CES05 = 51 | CES30 = 97 | CES55 = 94 | CES80 = 94 |
| CES06 = 51 | CES31 = 96 | CES56 = 94 | CES81 = 84 |
| CES07 = 43 | CES32 = 91 | CES57 = 94 | CES82 = 97 |
| CES08 = 42 | CES33 = 98 | CES58 = 94 | CES83 = 97 |
| CES09 = 29 | CES34 = 96 | CES59 = 97 | CES84 = 95 |
| CES10 = 76 | CES35 = 97 | CES60 = 95 | CES85 = 85 |
| CES11 = 59 | CES36 = 87 | CES61 = 94 | CES86 = 84 |
| CES12 = 65 | CES37 = 95 | CES62 = 92 | CES87 = 92 |
| CES13 = 44 | CES38 = 93 | CES63 = 93 | CES88 = 95 |
| CES14 = 74 | CES39 = 99 | CES64 = 92 | CES89 = 86 |
| CES15 = 72 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 48 | CES41 = 98 | CES66 = 90 | CES91 = 82 |
| CES17 = 50 | CES42 = 97 | CES67 = 89 | CES92 = 81 |
| CES18 = 57 | CES43 = 97 | CES68 = 90 | CES93 = 89 |
| CES19 = 72 | CES44 = 99 | CES69 = 92 | CES94 = 80 |
| CES20 = 67 | CES45 = 99 | CES70 = 89 | CES95 = 86 |
| CES21 = 86 | CES46 = 96 | CES71 = 87 | CES96 = 92 |
| CES22 = 79 | CES47 = 95 | CES72 = 95 | CES97 = 96 |
| CES23 = 92 | CES48 = 93 | CES73 = 85 | CES98 = 94 |
| CES24 = 91 | CES49 = 97 | CES74 = 93 | CES99 = 91 |
| CES25 = 72 | CES50 = 98 | CES75 = 88 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)