

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049378

Luminaire Tested: **GALN-SA7B-935-U-RBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1049378  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA7B-935-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 7xLight Square PACKAGE  
90CRI 3500K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (98) 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 20829.4 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G3


Input Watts (W): 249.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 3.1 fc  
 Type III - Short - N/A

REPORT NUMBER: P1049378  
CATALOG NUMBER: GALN-SA7B-935-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 104.3    | 0.0    | 104.3   |
|                    | % Fixture | 0.5      | 0.0    | 0.5     |
| <b>Street Side</b> | Lumens    | 20725.1  | 0.0    | 20725.1 |
|                    | % Fixture | 99.5     | 0.0    | 99.5    |
| <b>Total</b>       | Lumens    | 20829.4  | 0.0    | 20829.4 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 8.2     | 0.0       |
| 10°-20°   | 45.8    | 0.2       |
| 20°-30°   | 493.6   | 2.4       |
| 30°-40°   | 1459.7  | 7.0       |
| 40°-50°   | 4350.4  | 20.9      |
| 50°-60°   | 6898.2  | 33.1      |
| 60°-70°   | 5758.3  | 27.6      |
| 70°-80°   | 1775.7  | 8.5       |
| 80°-90°   | 39.5    | 0.2       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 20829.4 | 100.0     |
| 0°-180°   | 20829.4 | 100.0     |



REPORT NUMBER: P1049378


CATALOG NUMBER: GALN-SA7B-935-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|---------|-----------|-------------------------|------|---------|
|      |             |         |           | B                       | U    | G       |
| FL   | (0°-30°)    | 528.4   | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 12671.1 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 7495.1  | 36.0      |                         |      | G3/7500 |
| FVH  | (80°-90°)   | 30.5    | 0.1       |                         |      | G1/100  |
| BL   | (0°-30°)    | 19.2    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 37.3    | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 38.9    | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 9.0     | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0     | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G3**

Type III Short





REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°   | 5°    | 7.5°  | 10°   | 12.5° | 15°   | 17.5° | 20°   | 22.5° |
|--------|--------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°     | 91.3   | 91.3   | 91.3  | 91.3  | 91.3  | 91.3  | 91.3  | 91.3  | 91.3  | 91.3  |
| 2.5°   | 83.4   | 83.4   | 83.4  | 83.4  | 81.9  | 81.9  | 80.3  | 80.3  | 78.7  | 78.7  |
| 5°     | 88.1   | 88.1   | 86.6  | 85.0  | 85.0  | 83.4  | 81.9  | 80.3  | 80.3  | 78.7  |
| 7.5°   | 96.0   | 94.4   | 92.9  | 91.3  | 88.1  | 86.6  | 83.4  | 81.9  | 80.3  | 77.1  |
| 10°    | 105.5  | 102.3  | 99.2  | 96.0  | 92.9  | 89.7  | 86.6  | 85.0  | 81.9  | 80.3  |
| 12.5°  | 118.1  | 113.3  | 107.0 | 102.3 | 99.2  | 94.4  | 91.3  | 88.1  | 83.4  | 80.3  |
| 15°    | 129.1  | 122.8  | 114.9 | 108.6 | 103.9 | 97.6  | 92.9  | 88.1  | 85.0  | 80.3  |
| 17.5°  | 144.8  | 133.8  | 121.2 | 113.3 | 107.0 | 99.2  | 91.3  | 86.6  | 81.9  | 75.6  |
| 20°    | 171.6  | 149.5  | 125.9 | 116.5 | 107.0 | 97.6  | 88.1  | 81.9  | 77.1  | 70.8  |
| 22.5°  | 214.1  | 176.3  | 138.5 | 124.4 | 111.8 | 97.6  | 85.0  | 78.7  | 72.4  | 66.1  |
| 25°    | 295.9  | 228.2  | 160.6 | 141.7 | 122.8 | 103.9 | 85.0  | 77.1  | 70.8  | 63.0  |
| 27.5°  | 393.5  | 292.8  | 190.5 | 163.7 | 138.5 | 111.8 | 85.0  | 75.6  | 67.7  | 58.2  |
| 30°    | 492.7  | 358.9  | 223.5 | 188.9 | 154.3 | 119.6 | 85.0  | 74.0  | 64.5  | 53.5  |
| 32.5°  | 587.1  | 420.3  | 251.8 | 210.9 | 170.0 | 127.5 | 86.6  | 74.0  | 61.4  | 48.8  |
| 35°    | 683.1  | 470.6  | 256.6 | 214.1 | 171.6 | 127.5 | 85.0  | 70.8  | 58.2  | 44.1  |
| 37.5°  | 805.9  | 527.3  | 247.1 | 204.6 | 163.7 | 121.2 | 80.3  | 67.7  | 55.1  | 40.9  |
| 40°    | 991.7  | 621.8  | 251.8 | 207.8 | 163.7 | 119.6 | 75.6  | 63.0  | 51.9  | 39.4  |
| 42.5°  | 1334.8 | 804.3  | 272.3 | 221.9 | 171.6 | 119.6 | 69.3  | 58.2  | 48.8  | 37.8  |
| 45°    | 2307.6 | 1336.4 | 365.2 | 289.6 | 214.1 | 138.5 | 63.0  | 53.5  | 45.6  | 36.2  |
| 47.5°  | 3817.1 | 2236.7 | 656.4 | 506.8 | 358.9 | 209.3 | 61.4  | 53.5  | 45.6  | 36.2  |
| 50°    | 4871.7 | 2849.0 | 826.4 | 635.9 | 445.5 | 255.0 | 64.5  | 55.1  | 47.2  | 37.8  |
| 52.5°  | 4863.8 | 2893.1 | 920.8 | 706.8 | 494.3 | 280.2 | 67.7  | 58.2  | 50.4  | 40.9  |
| 55°    | 4323.9 | 2631.8 | 938.1 | 720.9 | 505.3 | 288.1 | 72.4  | 63.0  | 53.5  | 44.1  |
| 57.5°  | 3614.0 | 2235.2 | 856.3 | 662.7 | 470.6 | 277.0 | 83.4  | 72.4  | 63.0  | 51.9  |
| 60°    | 2858.5 | 1762.9 | 667.4 | 527.3 | 388.8 | 248.7 | 110.2 | 96.0  | 83.4  | 69.3  |
| 62.5°  | 1973.9 | 1278.1 | 582.4 | 467.5 | 354.2 | 239.3 | 125.9 | 111.8 | 99.2  | 85.0  |
| 65°    | 1396.2 | 961.8  | 525.7 | 428.1 | 332.1 | 234.5 | 136.9 | 121.2 | 107.0 | 91.3  |
| 67.5°  | 1043.6 | 765.0  | 484.8 | 401.4 | 318.0 | 234.5 | 151.1 | 132.2 | 114.9 | 96.0  |
| 70°    | 799.6  | 628.0  | 454.9 | 387.2 | 321.1 | 253.4 | 185.7 | 159.0 | 133.8 | 107.0 |
| 72.5°  | 651.7  | 536.8  | 420.3 | 371.5 | 322.7 | 273.9 | 225.1 | 190.5 | 155.8 | 119.6 |
| 75°    | 539.9  | 459.6  | 379.3 | 338.4 | 299.1 | 258.1 | 217.2 | 185.7 | 155.8 | 124.4 |
| 77.5°  | 358.9  | 327.4  | 294.3 | 270.7 | 247.1 | 221.9 | 198.3 | 171.6 | 146.4 | 119.6 |
| 80°    | 125.9  | 121.2  | 116.5 | 125.9 | 135.4 | 144.8 | 154.3 | 135.4 | 118.1 | 99.2  |
| 82.5°  | 18.9   | 17.3   | 15.7  | 17.3  | 18.9  | 20.5  | 22.0  | 23.6  | 25.2  | 26.8  |
| 85°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 92.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 95°    | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 97.5°  | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 100°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 102.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 105°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 107.5° | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 110°   | 0.0    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 |
| 0.0 | 2.5°   | 77.1  | 77.1 | 75.6  | 75.6 | 75.6  | 74.0 | 74.0  | 72.4 | 72.4  | 72.4 |
| 0.0 | 5°     | 75.6  | 75.6 | 74.0  | 72.4 | 70.8  | 70.8 | 69.3  | 67.7 | 67.7  | 66.1 |
| 0.0 | 7.5°   | 74.0  | 72.4 | 70.8  | 69.3 | 67.7  | 66.1 | 64.5  | 63.0 | 63.0  | 61.4 |
| 0.0 | 10°    | 75.6  | 72.4 | 70.8  | 67.7 | 66.1  | 64.5 | 61.4  | 59.8 | 58.2  | 58.2 |
| 0.0 | 12.5°  | 72.4  | 70.8 | 67.7  | 64.5 | 63.0  | 59.8 | 58.2  | 55.1 | 53.5  | 53.5 |
| 0.0 | 15°    | 72.4  | 69.3 | 64.5  | 61.4 | 58.2  | 56.7 | 53.5  | 50.4 | 48.8  | 47.2 |
| 0.0 | 17.5°  | 67.7  | 64.5 | 59.8  | 56.7 | 53.5  | 50.4 | 47.2  | 44.1 | 42.5  | 40.9 |
| 0.0 | 20°    | 61.4  | 58.2 | 53.5  | 48.8 | 45.6  | 42.5 | 39.4  | 36.2 | 34.6  | 33.1 |
| 0.0 | 22.5°  | 55.1  | 51.9 | 47.2  | 42.5 | 39.4  | 36.2 | 31.5  | 28.3 | 26.8  | 23.6 |
| 0.0 | 25°    | 51.9  | 47.2 | 42.5  | 37.8 | 33.1  | 29.9 | 25.2  | 20.5 | 17.3  | 14.2 |
| 0.0 | 27.5°  | 44.1  | 39.4 | 34.6  | 29.9 | 25.2  | 20.5 | 15.7  | 11.0 | 7.9   | 6.3  |
| 0.0 | 30°    | 37.8  | 33.1 | 28.3  | 23.6 | 17.3  | 12.6 | 7.9   | 1.6  | 1.6   | 1.6  |
| 0.0 | 32.5°  | 31.5  | 26.8 | 20.5  | 15.7 | 12.6  | 7.9  | 4.7   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 25.2  | 20.5 | 14.2  | 9.4  | 7.9   | 4.7  | 3.1   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 22.0  | 17.3 | 11.0  | 4.7  | 3.1   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 20.5  | 14.2 | 7.9   | 1.6  | 1.6   | 1.6  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 20.5  | 14.2 | 6.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 20.5  | 14.2 | 6.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 20.5  | 14.2 | 6.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 22.0  | 15.7 | 7.9   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 25.2  | 18.9 | 12.6  | 6.3  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 31.5  | 28.3 | 23.6  | 20.5 | 15.7  | 11.0 | 4.7   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 40.9  | 40.9 | 39.4  | 37.8 | 28.3  | 18.9 | 9.4   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 55.1  | 55.1 | 55.1  | 55.1 | 40.9  | 28.3 | 14.2  | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 67.7  | 64.5 | 59.8  | 56.7 | 42.5  | 28.3 | 14.2  | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 67.7  | 61.4 | 53.5  | 45.6 | 34.6  | 23.6 | 11.0  | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 63.0  | 50.4 | 36.2  | 23.6 | 17.3  | 12.6 | 6.3   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 63.0  | 44.1 | 25.2  | 6.3  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 63.0  | 42.5 | 20.5  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 69.3  | 47.2 | 23.6  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 69.3  | 47.2 | 23.6  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 61.4  | 40.9 | 20.5  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 20.5  | 14.2 | 6.3   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  |
| 0.0   | 2.5°   | 70.8 | 70.8  | 70.8 | 69.3  | 69.3 | 69.3  | 69.3 | 67.7  | 67.7 | 67.7  |
| 0.0   | 5°     | 64.5 | 64.5  | 63.0 | 63.0  | 61.4 | 61.4  | 59.8 | 59.8  | 58.2 | 58.2  |
| 0.0   | 7.5°   | 59.8 | 58.2  | 58.2 | 56.7  | 55.1 | 55.1  | 53.5 | 53.5  | 51.9 | 50.4  |
| 0.0   | 10°    | 55.1 | 53.5  | 53.5 | 51.9  | 50.4 | 48.8  | 48.8 | 47.2  | 45.6 | 44.1  |
| 0.0   | 12.5°  | 50.4 | 48.8  | 47.2 | 45.6  | 44.1 | 42.5  | 42.5 | 40.9  | 39.4 | 37.8  |
| 0.0   | 15°    | 44.1 | 42.5  | 40.9 | 39.4  | 37.8 | 36.2  | 36.2 | 34.6  | 33.1 | 31.5  |
| 0.0   | 17.5°  | 37.8 | 36.2  | 36.2 | 34.6  | 33.1 | 31.5  | 29.9 | 26.8  | 25.2 | 23.6  |
| 0.0   | 20°    | 28.3 | 26.8  | 25.2 | 23.6  | 22.0 | 18.9  | 17.3 | 14.2  | 11.0 | 9.4   |
| 0.0   | 22.5°  | 18.9 | 15.7  | 14.2 | 11.0  | 7.9  | 6.3   | 4.7  | 1.6   | 0.0  | 0.0   |
| 0.0   | 25°    | 6.3  | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3  | 91.3 | 91.3   | 91.3 |
| 0.0 | 2.5°   | 66.1  | 66.1 | 66.1  | 64.5 | 64.5  | 64.5 | 64.5  | 64.5 | 64.5   | 64.5 |
| 0.0 | 5°     | 56.7  | 56.7 | 56.7  | 55.1 | 55.1  | 53.5 | 53.5  | 53.5 | 51.9   | 51.9 |
| 0.0 | 7.5°   | 48.8  | 47.2 | 47.2  | 45.6 | 45.6  | 44.1 | 44.1  | 44.1 | 42.5   | 42.5 |
| 0.0 | 10°    | 40.9  | 39.4 | 39.4  | 37.8 | 37.8  | 36.2 | 36.2  | 34.6 | 34.6   | 33.1 |
| 0.0 | 12.5°  | 36.2  | 34.6 | 33.1  | 31.5 | 31.5  | 29.9 | 28.3  | 28.3 | 26.8   | 25.2 |
| 0.0 | 15°    | 28.3  | 26.8 | 25.2  | 23.6 | 22.0  | 20.5 | 18.9  | 18.9 | 17.3   | 15.7 |
| 0.0 | 17.5°  | 18.9  | 15.7 | 14.2  | 12.6 | 12.6  | 11.0 | 9.4   | 7.9  | 6.3    | 4.7  |
| 0.0 | 20°    | 4.7   | 3.1  | 1.6   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   |
| 0.0    | 2.5°   | 64.5 | 63.0   | 63.0 | 63.0   | 64.5 | 64.5   | 64.5 | 64.5   | 64.5 | 64.5   |
| 0.0    | 5°     | 51.9 | 50.4   | 50.4 | 50.4   | 50.4 | 50.4   | 50.4 | 50.4   | 50.4 | 50.4   |
| 0.0    | 7.5°   | 42.5 | 40.9   | 40.9 | 40.9   | 40.9 | 39.4   | 39.4 | 39.4   | 39.4 | 39.4   |
| 0.0    | 10°    | 33.1 | 31.5   | 31.5 | 31.5   | 31.5 | 29.9   | 29.9 | 29.9   | 29.9 | 29.9   |
| 0.0    | 12.5°  | 23.6 | 23.6   | 22.0 | 22.0   | 22.0 | 20.5   | 20.5 | 20.5   | 20.5 | 18.9   |
| 0.0    | 15°    | 14.2 | 12.6   | 11.0 | 11.0   | 11.0 | 9.4    | 9.4  | 9.4    | 9.4  | 7.9    |
| 0.0    | 17.5°  | 3.1  | 3.1    | 1.6  | 1.6    | 1.6  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 |
| 0.0  | 2.5°   | 66.1   | 66.1 | 67.7   | 67.7 | 69.3   | 72.4 | 74.0   | 75.6 | 78.7   | 81.9 |
| 0.0  | 5°     | 51.9   | 53.5 | 53.5   | 55.1 | 56.7   | 58.2 | 59.8   | 61.4 | 64.5   | 67.7 |
| 0.0  | 7.5°   | 40.9   | 40.9 | 42.5   | 42.5 | 44.1   | 47.2 | 48.8   | 50.4 | 53.5   | 58.2 |
| 0.0  | 10°    | 31.5   | 31.5 | 33.1   | 33.1 | 34.6   | 37.8 | 39.4   | 40.9 | 44.1   | 48.8 |
| 0.0  | 12.5°  | 20.5   | 22.0 | 22.0   | 23.6 | 25.2   | 28.3 | 29.9   | 31.5 | 34.6   | 37.8 |
| 0.0  | 15°    | 9.4    | 11.0 | 11.0   | 12.6 | 14.2   | 17.3 | 18.9   | 20.5 | 23.6   | 28.3 |
| 0.0  | 17.5°  | 1.6    | 1.6  | 3.1    | 3.1  | 4.7    | 6.3  | 7.9    | 9.4  | 14.2   | 17.3 |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 6.3  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 1.6  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180°  | 182.5° | 185°  | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 91.3 | 91.3   | 91.3 | 91.3   | 91.3 | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   |
| 0.0    | 2.5°   | 86.6 | 89.7   | 92.9 | 96.0   | 99.2 | 102.3  | 103.9 | 107.0  | 108.6 | 110.2  |
| 0.0    | 5°     | 74.0 | 77.1   | 81.9 | 85.0   | 88.1 | 91.3   | 94.4  | 96.0   | 97.6  | 99.2   |
| 0.0    | 7.5°   | 64.5 | 67.7   | 72.4 | 75.6   | 78.7 | 81.9   | 85.0  | 88.1   | 89.7  | 91.3   |
| 0.0    | 10°    | 55.1 | 59.8   | 63.0 | 67.7   | 70.8 | 74.0   | 77.1  | 80.3   | 83.4  | 85.0   |
| 0.0    | 12.5°  | 44.1 | 48.8   | 53.5 | 56.7   | 61.4 | 66.1   | 69.3  | 72.4   | 75.6  | 78.7   |
| 0.0    | 15°    | 34.6 | 39.4   | 44.1 | 47.2   | 51.9 | 56.7   | 61.4  | 64.5   | 67.7  | 70.8   |
| 0.0    | 17.5°  | 25.2 | 29.9   | 34.6 | 37.8   | 42.5 | 47.2   | 50.4  | 55.1   | 58.2  | 61.4   |
| 0.0    | 20°    | 12.6 | 17.3   | 22.0 | 26.8   | 31.5 | 36.2   | 39.4  | 44.1   | 47.2  | 50.4   |
| 0.0    | 22.5°  | 1.6  | 6.3    | 11.0 | 14.2   | 18.9 | 23.6   | 26.8  | 31.5   | 34.6  | 37.8   |
| 0.0    | 25°    | 0.0  | 1.6    | 4.7  | 6.3    | 7.9  | 11.0   | 14.2  | 17.3   | 20.5  | 23.6   |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.6    | 3.1   | 6.3    | 9.4   | 12.6   |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 3.1    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 1.6    | 1.6   | 3.1    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 3.1    | 4.7   | 7.9    | 9.4   | 11.0   |
|        | 87.5°  | 0.0  | 1.6    | 3.1  | 4.7    | 6.3  | 9.4    | 12.6  | 15.7   | 17.3  | 18.9   |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190°  |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 91.3  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 110.2 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100.7 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 92.9  | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 88.1  | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 80.3  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 74.0  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 66.1  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 53.5  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.9  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.7  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4.7   | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 1.6   |        |      |        |      |        |      |        |      |        |      |        |
| 6.3   |        |      |        |      |        |      |        |      |        |      |        |
| 14.2  |        |      |        |      |        |      |        |      |        |      |        |
| 20.5  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195°  | 197.5° | 200°  | 202.5° | 205°  | 207.5° | 210°  | 212.5° | 215°  |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|
| 0.0  | 0°     | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  |
| 0.0  | 2.5°   | 111.8  | 111.8 | 111.8  | 111.8 | 110.2  | 110.2 | 110.2  | 108.6 | 108.6  | 107.0 |
| 0.0  | 5°     | 102.3  | 103.9 | 103.9  | 103.9 | 103.9  | 103.9 | 103.9  | 103.9 | 102.3  | 102.3 |
| 0.0  | 7.5°   | 94.4   | 96.0  | 97.6   | 97.6  | 99.2   | 99.2  | 99.2   | 97.6  | 97.6   | 96.0  |
| 0.0  | 10°    | 89.7   | 91.3  | 91.3   | 92.9  | 92.9   | 92.9  | 92.9   | 92.9  | 92.9   | 92.9  |
| 0.0  | 12.5°  | 83.4   | 85.0  | 86.6   | 86.6  | 88.1   | 88.1  | 88.1   | 88.1  | 86.6   | 86.6  |
| 0.0  | 15°    | 75.6   | 78.7  | 80.3   | 81.9  | 81.9   | 83.4  | 83.4   | 83.4  | 83.4   | 83.4  |
| 0.0  | 17.5°  | 69.3   | 72.4  | 74.0   | 75.6  | 75.6   | 77.1  | 77.1   | 78.7  | 78.7   | 78.7  |
| 0.0  | 20°    | 56.7   | 59.8  | 61.4   | 64.5  | 66.1   | 67.7  | 69.3   | 70.8  | 70.8   | 72.4  |
| 0.0  | 22.5°  | 44.1   | 47.2  | 48.8   | 51.9  | 53.5   | 55.1  | 56.7   | 58.2  | 59.8   | 61.4  |
| 0.0  | 25°    | 31.5   | 34.6  | 36.2   | 39.4  | 40.9   | 42.5  | 44.1   | 45.6  | 45.6   | 47.2  |
| 0.0  | 27.5°  | 17.3   | 20.5  | 23.6   | 25.2  | 28.3   | 29.9  | 31.5   | 33.1  | 34.6   | 36.2  |
| 0.0  | 30°    | 7.9    | 9.4   | 11.0   | 14.2  | 15.7   | 17.3  | 18.9   | 22.0  | 23.6   | 25.2  |
| 0.0  | 32.5°  | 0.0    | 0.0   | 1.6    | 4.7   | 6.3    | 7.9   | 9.4    | 11.0  | 11.0   | 12.6  |
| 0.0  | 35°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 1.6    | 3.1   | 4.7    | 6.3   |
| 0.0  | 37.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 40°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 42.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 45°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 47.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 50°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 52.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 55°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 57.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 60°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 62.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 65°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
| 0.0  | 67.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 70°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 72.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 75°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 77.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 80°    | 3.1    | 3.1   | 3.1    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   | 4.7    | 4.7   |
|      | 82.5°  | 7.9    | 9.4   | 11.0   | 11.0  | 12.6   | 12.6  | 12.6   | 12.6  | 11.0   | 11.0  |
|      | 85°    | 15.7   | 17.3  | 18.9   | 18.9  | 20.5   | 20.5  | 20.5   | 20.5  | 20.5   | 20.5  |
|      | 87.5°  | 22.0   | 23.6  | 25.2   | 25.2  | 26.8   | 26.8  | 26.8   | 26.8  | 26.8   | 26.8  |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 91.3   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 107.0  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 102.3  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 96.0   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 92.9   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 86.6   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 83.4   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 78.7   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 70.8   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 61.4   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 48.8   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.8   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.8   | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15.7   | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 9.4    | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.1    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.6    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.6    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.6    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.6    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.6    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 4.7    |        |        |      |        |      |        |      |        |      |        |      |
| 11.0   |        |        |      |        |      |        |      |        |      |        |      |
| 20.5   |        |        |      |        |      |        |      |        |      |        |      |
| 26.8   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220°  | 222.5° | 225°  | 227.5° | 230°  | 232.5° | 235°  | 237.5° | 240°  | 242.5° |
|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|-------|--------|
| 0.0    | 0°     | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   |
| 0.0    | 2.5°   | 105.5 | 105.5  | 103.9 | 103.9  | 103.9 | 103.9  | 103.9 | 105.5  | 107.0 | 107.0  |
| 0.0    | 5°     | 100.7 | 100.7  | 99.2  | 99.2   | 99.2  | 100.7  | 100.7 | 102.3  | 103.9 | 105.5  |
| 0.0    | 7.5°   | 96.0  | 94.4   | 94.4  | 96.0   | 96.0  | 97.6   | 97.6  | 99.2   | 100.7 | 102.3  |
| 0.0    | 10°    | 92.9  | 91.3   | 91.3  | 91.3   | 92.9  | 92.9   | 94.4  | 96.0   | 97.6  | 99.2   |
| 0.0    | 12.5°  | 86.6  | 86.6   | 86.6  | 86.6   | 88.1  | 88.1   | 89.7  | 91.3   | 94.4  | 96.0   |
| 0.0    | 15°    | 83.4  | 81.9   | 81.9  | 81.9   | 81.9  | 83.4   | 83.4  | 86.6   | 89.7  | 91.3   |
| 0.0    | 17.5°  | 77.1  | 77.1   | 75.6  | 75.6   | 77.1  | 77.1   | 78.7  | 81.9   | 85.0  | 86.6   |
| 0.0    | 20°    | 70.8  | 69.3   | 67.7  | 67.7   | 69.3  | 69.3   | 70.8  | 74.0   | 77.1  | 78.7   |
| 0.0    | 22.5°  | 61.4  | 59.8   | 59.8  | 59.8   | 59.8  | 61.4   | 61.4  | 64.5   | 69.3  | 72.4   |
| 0.0    | 25°    | 48.8  | 50.4   | 50.4  | 51.9   | 51.9  | 53.5   | 55.1  | 58.2   | 63.0  | 66.1   |
| 0.0    | 27.5°  | 37.8  | 39.4   | 39.4  | 42.5   | 44.1  | 45.6   | 47.2  | 51.9   | 56.7  | 59.8   |
| 0.0    | 30°    | 28.3  | 29.9   | 31.5  | 33.1   | 36.2  | 39.4   | 42.5  | 47.2   | 51.9  | 55.1   |
| 0.0    | 32.5°  | 17.3  | 20.5   | 22.0  | 25.2   | 28.3  | 31.5   | 34.6  | 39.4   | 45.6  | 50.4   |
| 0.0    | 35°    | 12.6  | 14.2   | 17.3  | 18.9   | 22.0  | 25.2   | 28.3  | 34.6   | 39.4  | 45.6   |
| 0.0    | 37.5°  | 6.3   | 9.4    | 12.6  | 15.7   | 18.9  | 22.0   | 25.2  | 31.5   | 37.8  | 42.5   |
| 0.0    | 40°    | 4.7   | 7.9    | 9.4   | 12.6   | 17.3  | 20.5   | 23.6  | 29.9   | 36.2  | 42.5   |
| 0.0    | 42.5°  | 3.1   | 4.7    | 6.3   | 11.0   | 14.2  | 18.9   | 23.6  | 29.9   | 36.2  | 42.5   |
| 0.0    | 45°    | 3.1   | 3.1    | 4.7   | 9.4    | 14.2  | 20.5   | 25.2  | 31.5   | 36.2  | 42.5   |
| 0.0    | 47.5°  | 3.1   | 4.7    | 6.3   | 12.6   | 15.7  | 20.5   | 25.2  | 29.9   | 36.2  | 40.9   |
| 0.0    | 50°    | 4.7   | 6.3    | 7.9   | 14.2   | 17.3  | 22.0   | 25.2  | 31.5   | 36.2  | 42.5   |
| 0.0    | 52.5°  | 3.1   | 4.7    | 6.3   | 12.6   | 17.3  | 23.6   | 28.3  | 34.6   | 40.9  | 45.6   |
| 0.0    | 55°    | 1.6   | 1.6    | 1.6   | 9.4    | 18.9  | 26.8   | 36.2  | 40.9   | 47.2  | 51.9   |
| 0.0    | 57.5°  | 0.0   | 0.0    | 0.0   | 6.3    | 18.9  | 29.9   | 40.9  | 47.2   | 53.5  | 58.2   |
| 0.0    | 60°    | 0.0   | 0.0    | 0.0   | 6.3    | 18.9  | 29.9   | 40.9  | 48.8   | 56.7  | 64.5   |
| 0.0    | 62.5°  | 0.0   | 0.0    | 0.0   | 6.3    | 15.7  | 25.2   | 34.6  | 47.2   | 61.4  | 74.0   |
| 0.0    | 65°    | 0.0   | 0.0    | 0.0   | 4.7    | 12.6  | 20.5   | 28.3  | 47.2   | 66.1  | 83.4   |
| 0.0    | 67.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 12.6  | 18.9   | 26.8  | 47.2   | 66.1  | 86.6   |
|        | 70°    | 0.0   | 0.0    | 0.0   | 4.7    | 12.6  | 20.5   | 28.3  | 47.2   | 66.1  | 85.0   |
|        | 72.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 14.2  | 22.0   | 31.5  | 47.2   | 63.0  | 78.7   |
|        | 75°    | 0.0   | 0.0    | 0.0   | 6.3    | 14.2  | 23.6   | 33.1  | 47.2   | 61.4  | 74.0   |
|        | 77.5°  | 0.0   | 0.0    | 0.0   | 4.7    | 14.2  | 22.0   | 31.5  | 45.6   | 59.8  | 72.4   |
|        | 80°    | 4.7   | 3.1    | 3.1   | 7.9    | 14.2  | 20.5   | 26.8  | 40.9   | 56.7  | 70.8   |
|        | 82.5°  | 9.4   | 9.4    | 7.9   | 11.0   | 14.2  | 18.9   | 23.6  | 36.2   | 50.4  | 63.0   |
|        | 85°    | 18.9  | 18.9   | 17.3  | 18.9   | 18.9  | 20.5   | 22.0  | 28.3   | 34.6  | 40.9   |
|        | 87.5°  | 25.2  | 25.2   | 23.6  | 23.6   | 23.6  | 22.0   | 22.0  | 22.0   | 22.0  | 20.5   |
|        | 90°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 92.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 95°    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 97.5°  | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 100°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 102.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 105°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 107.5° | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |
|        | 110°   | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245°  |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|-------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 91.3  | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 108.6 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 107.0 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 103.9 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 100.7 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 97.6  | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 94.4  | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 89.7  | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 81.9  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 75.6  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 69.3  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.5  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 59.8  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 55.1  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 50.4  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.8  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.8  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 48.8  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.2  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 45.6  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 47.2  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 51.9  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 56.7  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 64.5  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 72.4  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.6  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 102.3 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 105.5 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 103.9 |        |      |        |      |        |      |        |      |        |      |        |
| 94.4  |        |      |        |      |        |      |        |      |        |      |        |
| 88.1  |        |      |        |      |        |      |        |      |        |      |        |
| 86.6  |        |      |        |      |        |      |        |      |        |      |        |
| 85.0  |        |      |        |      |        |      |        |      |        |      |        |
| 75.6  |        |      |        |      |        |      |        |      |        |      |        |
| 47.2  |        |      |        |      |        |      |        |      |        |      |        |
| 20.5  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |
| 0.0   |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250°  | 252.5° | 255°  | 257.5° | 260°  | 262.5° | 265°  | 267.5° | 270°   |
|------|--------|--------|-------|--------|-------|--------|-------|--------|-------|--------|--------|
| 0.0  | 0°     | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3  | 91.3   | 91.3   |
| 0.0  | 2.5°   | 110.2  | 111.8 | 111.8  | 113.3 | 114.9  | 116.5 | 116.5  | 118.1 | 118.1  | 118.1  |
| 0.0  | 5°     | 108.6  | 111.8 | 113.3  | 114.9 | 116.5  | 118.1 | 119.6  | 121.2 | 122.8  | 122.8  |
| 0.0  | 7.5°   | 107.0  | 108.6 | 111.8  | 113.3 | 116.5  | 118.1 | 121.2  | 122.8 | 124.4  | 125.9  |
| 0.0  | 10°    | 103.9  | 107.0 | 110.2  | 113.3 | 116.5  | 119.6 | 122.8  | 125.9 | 129.1  | 130.6  |
| 0.0  | 12.5°  | 100.7  | 105.5 | 108.6  | 111.8 | 116.5  | 121.2 | 124.4  | 129.1 | 132.2  | 135.4  |
| 0.0  | 15°    | 99.2   | 102.3 | 107.0  | 110.2 | 116.5  | 122.8 | 127.5  | 133.8 | 140.1  | 144.8  |
| 0.0  | 17.5°  | 94.4   | 100.7 | 105.5  | 110.2 | 116.5  | 124.4 | 130.6  | 136.9 | 146.4  | 155.8  |
| 0.0  | 20°    | 88.1   | 92.9  | 99.2   | 103.9 | 113.3  | 121.2 | 130.6  | 138.5 | 152.7  | 166.9  |
| 0.0  | 22.5°  | 81.9   | 88.1  | 92.9   | 99.2  | 110.2  | 119.6 | 130.6  | 140.1 | 163.7  | 185.7  |
| 0.0  | 25°    | 75.6   | 83.4  | 89.7   | 96.0  | 108.6  | 121.2 | 133.8  | 146.4 | 185.7  | 225.1  |
| 0.0  | 27.5°  | 72.4   | 78.7  | 86.6   | 92.9  | 108.6  | 125.9 | 141.7  | 157.4 | 220.4  | 281.8  |
| 0.0  | 30°    | 67.7   | 75.6  | 81.9   | 89.7  | 110.2  | 130.6 | 151.1  | 171.6 | 267.6  | 363.6  |
| 0.0  | 32.5°  | 63.0   | 70.8  | 78.7   | 86.6  | 113.3  | 140.1 | 165.3  | 192.0 | 318.0  | 442.3  |
| 0.0  | 35°    | 58.2   | 67.7  | 75.6   | 83.4  | 118.1  | 154.3 | 188.9  | 223.5 | 363.6  | 502.1  |
| 0.0  | 37.5°  | 56.7   | 66.1  | 74.0   | 81.9  | 119.6  | 155.8 | 193.6  | 229.8 | 368.3  | 506.8  |
| 0.0  | 40°    | 58.2   | 66.1  | 75.6   | 83.4  | 114.9  | 146.4 | 176.3  | 207.8 | 352.6  | 495.8  |
| 0.0  | 42.5°  | 58.2   | 67.7  | 77.1   | 86.6  | 111.8  | 136.9 | 162.1  | 187.3 | 347.9  | 508.4  |
| 0.0  | 45°    | 56.7   | 66.1  | 75.6   | 85.0  | 108.6  | 130.6 | 154.3  | 176.3 | 376.2  | 574.5  |
| 0.0  | 47.5°  | 55.1   | 64.5  | 74.0   | 83.4  | 107.0  | 130.6 | 154.3  | 177.9 | 486.4  | 793.3  |
| 0.0  | 50°    | 55.1   | 64.5  | 72.4   | 80.3  | 108.6  | 138.5 | 166.9  | 195.2 | 708.3  | 1219.9 |
| 0.0  | 52.5°  | 58.2   | 66.1  | 72.4   | 78.7  | 111.8  | 146.4 | 179.4  | 212.5 | 900.4  | 1586.7 |
| 0.0  | 55°    | 63.0   | 67.7  | 74.0   | 78.7  | 119.6  | 159.0 | 199.9  | 239.3 | 958.6  | 1677.9 |
| 0.0  | 57.5°  | 69.3   | 74.0  | 78.7   | 83.4  | 133.8  | 184.2 | 233.0  | 283.3 | 963.3  | 1641.7 |
| 0.0  | 60°    | 77.1   | 83.4  | 88.1   | 92.9  | 146.4  | 201.5 | 255.0  | 308.5 | 872.0  | 1434.0 |
| 0.0  | 62.5°  | 94.4   | 102.3 | 108.6  | 116.5 | 168.4  | 218.8 | 270.7  | 321.1 | 724.1  | 1127.0 |
| 0.0  | 65°    | 108.6  | 114.9 | 121.2  | 127.5 | 177.9  | 229.8 | 280.2  | 330.6 | 613.9  | 897.2  |
| 0.0  | 67.5°  | 111.8  | 118.1 | 122.8  | 129.1 | 181.0  | 233.0 | 283.3  | 335.3 | 525.7  | 714.6  |
|      | 70°    | 113.3  | 121.2 | 130.6  | 138.5 | 192.0  | 245.6 | 297.5  | 351.0 | 465.9  | 580.8  |
|      | 72.5°  | 108.6  | 124.4 | 138.5  | 152.7 | 203.1  | 251.8 | 302.2  | 351.0 | 432.9  | 514.7  |
|      | 75°    | 108.6  | 130.6 | 151.1  | 171.6 | 209.3  | 245.6 | 283.3  | 319.5 | 382.5  | 445.5  |
|      | 77.5°  | 114.9  | 143.2 | 171.6  | 199.9 | 221.9  | 242.4 | 264.4  | 284.9 | 325.8  | 366.8  |
|      | 80°    | 114.9  | 144.8 | 173.1  | 203.1 | 212.5  | 223.5 | 233.0  | 242.4 | 247.1  | 251.8  |
|      | 82.5°  | 99.2   | 122.8 | 146.4  | 170.0 | 159.0  | 148.0 | 136.9  | 125.9 | 118.1  | 108.6  |
|      | 85°    | 50.4   | 55.1  | 58.2   | 61.4  | 56.7   | 51.9  | 47.2   | 42.5  | 39.4   | 34.6   |
|      | 87.5°  | 20.5   | 20.5  | 18.9   | 18.9  | 18.9   | 18.9  | 17.3   | 17.3  | 17.3   | 17.3   |
|      | 90°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 92.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 95°    | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 97.5°  | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 100°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 102.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 105°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 107.5° | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |
|      | 110°   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0   | 0.0    | 0.0    |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 91.3   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 118.1  | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 122.8  | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 127.5  | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 133.8  | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 140.1  | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 152.7  | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 168.4  | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 193.6  | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 247.1  | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 335.3  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 465.9  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 631.2  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 788.6  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 895.6  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 975.9  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1056.2 | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1213.6 | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1528.4 | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2329.6 | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3568.4 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4492.4 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4594.7 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 4146.1 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3544.8 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2770.3 | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 2093.5 | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1545.7 | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1094.0 |        |        |      |        |      |        |      |        |      |        |      |
| 813.8  |        |        |      |        |      |        |      |        |      |        |      |
| 591.8  |        |        |      |        |      |        |      |        |      |        |      |
| 445.5  |        |        |      |        |      |        |      |        |      |        |      |
| 250.3  |        |        |      |        |      |        |      |        |      |        |      |
| 113.3  |        |        |      |        |      |        |      |        |      |        |      |
| 33.1   |        |        |      |        |      |        |      |        |      |        |      |
| 15.7   |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5°  | 280°    | 282.5°  | 285°    | 287.5°  | 290°    | 292.5°  | 295°    | 297.5°  |
|--------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0    | 0°     | 91.3   | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    |
| 0.0    | 2.5°   | 118.1  | 116.5   | 116.5   | 114.9   | 113.3   | 111.8   | 110.2   | 108.6   | 107.0   | 105.5   |
| 0.0    | 5°     | 122.8  | 122.8   | 122.8   | 121.2   | 121.2   | 119.6   | 119.6   | 118.1   | 116.5   | 114.9   |
| 0.0    | 7.5°   | 127.5  | 129.1   | 129.1   | 130.6   | 130.6   | 130.6   | 130.6   | 129.1   | 129.1   | 129.1   |
| 0.0    | 10°    | 135.4  | 136.9   | 138.5   | 140.1   | 141.7   | 143.2   | 143.2   | 144.8   | 144.8   | 144.8   |
| 0.0    | 12.5°  | 144.8  | 149.5   | 152.7   | 157.4   | 160.6   | 165.3   | 168.4   | 173.1   | 176.3   | 179.4   |
| 0.0    | 15°    | 159.0  | 166.9   | 176.3   | 184.2   | 192.0   | 203.1   | 215.6   | 226.7   | 237.7   | 255.0   |
| 0.0    | 17.5°  | 179.4  | 204.6   | 229.8   | 253.4   | 278.6   | 333.7   | 388.8   | 442.3   | 497.4   | 577.7   |
| 0.0    | 20°    | 218.8  | 294.3   | 368.3   | 443.9   | 517.9   | 711.5   | 903.5   | 1097.1  | 1289.2  | 1495.4  |
| 0.0    | 22.5°  | 306.9  | 492.7   | 678.4   | 864.2   | 1049.9  | 1454.4  | 1857.4  | 2261.9  | 2664.9  | 3138.7  |
| 0.0    | 25°    | 445.5  | 787.0   | 1128.6  | 1468.6  | 1810.2  | 2442.9  | 3077.3  | 3710.1  | 4342.8  | 4958.3  |
| 0.0    | 27.5°  | 648.5  | 1171.1  | 1693.7  | 2214.7  | 2737.3  | 3595.2  | 4454.6  | 5312.5  | 6170.3  | 6866.0  |
| 0.0    | 30°    | 898.8  | 1607.1  | 2315.4  | 3023.8  | 3732.1  | 4708.0  | 5683.9  | 6658.3  | 7634.2  | 8394.5  |
| 0.0    | 32.5°  | 1134.9 | 2002.2  | 2869.5  | 3735.2  | 4602.6  | 5713.8  | 6826.7  | 7938.0  | 9049.3  | 9880.4  |
| 0.0    | 35°    | 1289.2 | 2337.5  | 3387.4  | 4435.7  | 5484.0  | 6686.6  | 7889.2  | 9090.2  | 10292.8 | 11241.9 |
| 0.0    | 37.5°  | 1443.4 | 2653.9  | 3862.7  | 5073.2  | 6282.1  | 7602.7  | 8923.3  | 10244.0 | 11564.6 | 12737.3 |
| 0.0    | 40°    | 1616.6 | 3036.4  | 4454.6  | 5874.4  | 7292.6  | 8857.2  | 10420.3 | 11984.9 | 13547.9 | 15202.3 |
| 0.0    | 42.5°  | 1917.2 | 3670.7  | 5425.8  | 7179.3  | 8932.8  | 11002.7 | 13072.6 | 15140.9 | 17210.8 | 19571.9 |
| 0.0    | 45°    | 2482.3 | 4953.6  | 7426.4  | 9897.7  | 12369.0 | 15111.0 | 17854.6 | 20596.6 | 23338.6 | 26480.4 |
| 0.0    | 47.5°  | 3865.9 | 7265.9  | 10664.3 | 14064.2 | 17462.6 | 20423.4 | 23382.7 | 26343.5 | 29302.7 | 32431.9 |
| 0.0    | 50°    | 5915.3 | 9872.5  | 13829.7 | 17785.3 | 21742.5 | 24421.5 | 27099.0 | 29778.1 | 32455.5 | 35432.1 |
| 0.0    | 52.5°  | 7398.1 | 11520.5 | 15644.6 | 19767.0 | 23889.5 | 26307.3 | 28726.6 | 31144.4 | 33562.1 | 36343.5 |
| 0.0    | 55°    | 7509.8 | 11608.7 | 15709.1 | 19808.0 | 23906.8 | 26335.6 | 28764.4 | 31193.1 | 33621.9 | 36570.1 |
| 0.0    | 57.5°  | 6648.8 | 10714.6 | 14778.8 | 18844.6 | 22908.9 | 25674.5 | 28438.5 | 31204.2 | 33968.2 | 37155.7 |
| 0.0    | 60°    | 5655.6 | 9723.0  | 13788.8 | 17856.1 | 21921.9 | 25107.8 | 28295.3 | 31481.2 | 34667.1 | 37653.1 |
| 0.0    | 62.5°  | 4412.1 | 8595.9  | 12781.4 | 16965.2 | 21149.1 | 24383.8 | 27618.5 | 30851.6 | 34086.3 | 36326.2 |
| 0.0    | 65°    | 3288.2 | 7350.9  | 11413.5 | 15474.6 | 19537.2 | 22128.1 | 24719.0 | 27308.4 | 29899.3 | 31286.0 |
| 0.0    | 67.5°  | 2376.8 | 5880.7  | 9383.0  | 12886.8 | 16389.1 | 18243.4 | 20097.6 | 21950.3 | 23804.5 | 24865.4 |
|        | 70°    | 1607.1 | 4034.3  | 6459.9  | 8887.1  | 11312.8 | 12836.5 | 14361.7 | 15885.4 | 17409.1 | 18841.5 |
|        | 72.5°  | 1112.9 | 2476.0  | 3840.7  | 5203.8  | 6567.0  | 8100.1  | 9631.7  | 11164.8 | 12696.4 | 14212.2 |
|        | 75°    | 738.2  | 1358.4  | 1980.2  | 2600.3  | 3220.5  | 4355.4  | 5491.9  | 6626.8  | 7761.7  | 8665.2  |
|        | 77.5°  | 524.2  | 709.9   | 897.2   | 1083.0  | 1268.7  | 1481.2  | 1695.3  | 1907.8  | 2120.3  | 2442.9  |
|        | 80°    | 248.7  | 272.3   | 295.9   | 318.0   | 341.6   | 418.7   | 495.8   | 573.0   | 650.1   | 731.9   |
|        | 82.5°  | 118.1  | 127.5   | 136.9   | 144.8   | 154.3   | 162.1   | 170.0   | 177.9   | 185.7   | 177.9   |
|        | 85°    | 31.5   | 31.5    | 33.1    | 33.1    | 33.1    | 33.1    | 33.1    | 33.1    | 33.1    | 31.5    |
|        | 87.5°  | 14.2   | 14.2    | 14.2    | 14.2    | 14.2    | 14.2    | 14.2    | 12.6    | 12.6    | 11.0    |
|        | 90°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 91.3    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 103.9   | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 113.3   | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 127.5   | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 146.4   | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 181.0   | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 273.9   | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 656.4   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1703.1  | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3612.5  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5573.7  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 7561.8  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9156.3  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10713.1 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12191.1 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13911.5 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16856.6 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21933.0 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29622.2 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35561.2 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38408.6 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39124.8 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 39519.9 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40343.2 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40637.5 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 38567.6 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32674.3 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25927.9 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20272.3 |        |      |        |      |        |      |        |      |        |      |        |
| 15728.0 |        |      |        |      |        |      |        |      |        |      |        |
| 9568.7  |        |      |        |      |        |      |        |      |        |      |        |
| 2765.6  |        |      |        |      |        |      |        |      |        |      |        |
| 813.8   |        |      |        |      |        |      |        |      |        |      |        |
| 168.4   |        |      |        |      |        |      |        |      |        |      |        |
| 29.9    |        |      |        |      |        |      |        |      |        |      |        |
| 11.0    |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    |
| 0.0  | 2.5°   | 102.3   | 100.7   | 99.2    | 97.6    | 96.0    | 92.9    | 92.9    | 91.3    | 91.3    |
| 0.0  | 5°     | 111.8   | 110.2   | 108.6   | 107.0   | 107.0   | 105.5   | 103.9   | 103.9   | 102.3   |
| 0.0  | 7.5°   | 127.5   | 125.9   | 124.4   | 122.8   | 122.8   | 121.2   | 121.2   | 119.6   | 119.6   |
| 0.0  | 10°    | 146.4   | 146.4   | 146.4   | 146.4   | 146.4   | 144.8   | 144.8   | 144.8   | 143.2   |
| 0.0  | 12.5°  | 184.2   | 185.7   | 188.9   | 192.0   | 196.8   | 196.8   | 196.8   | 195.2   | 195.2   |
| 0.0  | 15°    | 291.2   | 308.5   | 321.1   | 333.7   | 344.7   | 369.9   | 366.8   | 362.0   | 358.9   |
| 0.0  | 17.5°  | 736.7   | 815.4   | 857.9   | 898.8   | 941.3   | 1057.8  | 1038.9  | 1020.0  | 1002.7  |
| 0.0  | 20°    | 1909.3  | 2115.5  | 2252.5  | 2389.4  | 2527.9  | 2746.7  | 2693.2  | 2639.7  | 2586.2  |
| 0.0  | 22.5°  | 4084.7  | 4558.5  | 4764.7  | 4970.9  | 5175.5  | 5440.0  | 5268.4  | 5096.8  | 4926.8  |
| 0.0  | 25°    | 6187.6  | 6803.1  | 7151.0  | 7498.8  | 7845.1  | 7996.2  | 7772.7  | 7547.6  | 7324.1  |
| 0.0  | 27.5°  | 8257.5  | 8953.3  | 9260.2  | 9565.6  | 9872.5  | 10188.9 | 9911.9  | 9633.2  | 9356.2  |
| 0.0  | 30°    | 9916.6  | 10676.8 | 11009.0 | 11339.5 | 11671.7 | 11892.0 | 11605.5 | 11317.5 | 11031.0 |
| 0.0  | 32.5°  | 11544.2 | 12375.3 | 12738.9 | 13102.5 | 13464.5 | 13780.9 | 13428.3 | 13074.1 | 12721.6 |
| 0.0  | 35°    | 13138.7 | 14087.8 | 14588.4 | 15088.9 | 15589.5 | 15883.8 | 15465.1 | 15044.9 | 14626.2 |
| 0.0  | 37.5°  | 15084.2 | 16256.9 | 16817.3 | 17377.6 | 17938.0 | 18474.7 | 18013.5 | 17550.8 | 17089.6 |
| 0.0  | 40°    | 18510.9 | 20165.3 | 21024.7 | 21885.7 | 22745.2 | 23437.8 | 22855.4 | 22272.9 | 21690.5 |
| 0.0  | 42.5°  | 24294.0 | 26655.1 | 27890.8 | 29124.8 | 30360.5 | 31441.8 | 30829.5 | 30217.2 | 29604.9 |
| 0.0  | 45°    | 32764.1 | 35905.9 | 37412.3 | 38917.1 | 40423.4 | 41213.6 | 40332.1 | 39449.1 | 38567.6 |
| 0.0  | 47.5°  | 38688.8 | 41818.1 | 43159.2 | 44500.2 | 45841.3 | 46743.3 | 45665.1 | 44586.8 | 43510.2 |
| 0.0  | 50°    | 41383.6 | 44360.2 | 45706.0 | 47050.2 | 48396.0 | 49112.2 | 47867.2 | 46620.5 | 45375.4 |
| 0.0  | 52.5°  | 41904.6 | 44686.0 | 46291.5 | 47898.6 | 49504.2 | 50461.2 | 48991.0 | 47519.3 | 46049.1 |
| 0.0  | 55°    | 42468.1 | 45416.4 | 47278.5 | 49142.2 | 51004.3 | 52329.6 | 50667.4 | 49003.6 | 47341.4 |
| 0.0  | 57.5°  | 43529.1 | 46716.5 | 48573.9 | 50429.7 | 52287.1 | 53412.6 | 51745.6 | 50077.1 | 48410.2 |
| 0.0  | 60°    | 43623.5 | 46607.9 | 48204.0 | 49801.7 | 51397.8 | 52106.1 | 50511.6 | 48915.5 | 47321.0 |
| 0.0  | 62.5°  | 40807.5 | 43047.4 | 44155.5 | 45263.7 | 46371.8 | 47141.5 | 45477.7 | 43812.4 | 42148.6 |
| 0.0  | 65°    | 34061.1 | 35447.8 | 36330.9 | 37213.9 | 38097.0 | 39014.7 | 37491.0 | 35967.3 | 34443.6 |
| 0.0  | 67.5°  | 26988.8 | 28049.7 | 29213.0 | 30376.2 | 31539.4 | 32520.1 | 31300.2 | 30078.7 | 28858.8 |
|      | 70°    | 21704.7 | 23135.5 | 24443.6 | 25751.6 | 27059.7 | 27862.4 | 26637.8 | 25411.6 | 24187.0 |
|      | 72.5°  | 17243.8 | 18759.6 | 19852.0 | 20942.9 | 22035.3 | 22232.0 | 21331.7 | 20431.3 | 19532.5 |
|      | 75°    | 10470.6 | 11374.2 | 11396.2 | 11416.7 | 11438.7 | 11626.0 | 10879.9 | 10133.8 | 9389.3  |
|      | 77.5°  | 3088.3  | 3411.0  | 3677.0  | 3941.4  | 4207.5  | 4528.6  | 4254.7  | 3979.2  | 3705.3  |
|      | 80°    | 894.1   | 975.9   | 1045.2  | 1112.9  | 1182.1  | 1141.2  | 1076.7  | 1012.1  | 947.6   |
|      | 82.5°  | 160.6   | 151.1   | 149.5   | 148.0   | 148.0   | 140.1   | 127.5   | 114.9   | 102.3   |
|      | 85°    | 28.3    | 26.8    | 25.2    | 23.6    | 22.0    | 20.5    | 17.3    | 15.7    | 12.6    |
|      | 87.5°  | 9.4     | 7.9     | 6.3     | 4.7     | 4.7     | 1.6     | 1.6     | 1.6     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°    | 342.5°  | 345°    | 347.5°  | 350°    |
|------|--------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0.0    | 0°     | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    | 91.3    |
| 0.0  | 0.0    | 2.5°   | 89.7    | 88.1    | 88.1    | 88.1    | 88.1    | 86.6    | 86.6    | 86.6    | 86.6    |
| 0.0  | 0.0    | 5°     | 99.2    | 99.2    | 97.6    | 97.6    | 96.0    | 96.0    | 94.4    | 94.4    | 92.9    |
| 0.0  | 0.0    | 7.5°   | 116.5   | 114.9   | 113.3   | 111.8   | 110.2   | 107.0   | 105.5   | 103.9   | 103.9   |
| 0.0  | 0.0    | 10°    | 140.1   | 136.9   | 135.4   | 132.2   | 130.6   | 127.5   | 124.4   | 121.2   | 118.1   |
| 0.0  | 0.0    | 12.5°  | 184.2   | 177.9   | 173.1   | 166.9   | 160.6   | 155.8   | 149.5   | 144.8   | 138.5   |
| 0.0  | 0.0    | 15°    | 319.5   | 303.8   | 286.5   | 266.0   | 244.0   | 223.5   | 201.5   | 188.9   | 174.7   |
| 0.0  | 0.0    | 17.5°  | 816.9   | 735.1   | 651.7   | 584.0   | 516.3   | 450.2   | 382.5   | 333.7   | 284.9   |
| 0.0  | 0.0    | 20°    | 2079.3  | 1852.7  | 1626.0  | 1402.5  | 1177.4  | 953.9   | 728.8   | 615.5   | 502.1   |
| 0.0  | 0.0    | 22.5°  | 3913.1  | 3492.8  | 3071.0  | 2663.3  | 2254.1  | 1846.4  | 1438.7  | 1182.1  | 927.1   |
| 0.0  | 0.0    | 25°    | 6039.7  | 5510.8  | 4981.9  | 4311.4  | 3639.2  | 2968.7  | 2298.1  | 1881.0  | 1463.9  |
| 0.0  | 0.0    | 27.5°  | 7859.3  | 7250.1  | 6641.0  | 5825.6  | 5010.2  | 4194.9  | 3379.5  | 2757.8  | 2137.6  |
| 0.0  | 0.0    | 30°    | 9434.9  | 8780.1  | 8125.3  | 7176.1  | 6227.0  | 5277.8  | 4328.7  | 3551.1  | 2773.5  |
| 0.0  | 0.0    | 32.5°  | 10801.2 | 10017.3 | 9233.4  | 8254.4  | 7275.3  | 6296.2  | 5317.2  | 4363.3  | 3409.4  |
| 0.0  | 0.0    | 35°    | 12376.8 | 11462.3 | 10546.2 | 9460.1  | 8372.4  | 7286.3  | 6200.2  | 5123.6  | 4045.3  |
| 0.0  | 0.0    | 37.5°  | 14379.0 | 13256.7 | 12132.9 | 10922.4 | 9712.0  | 8503.1  | 7292.6  | 6061.7  | 4830.8  |
| 0.0  | 0.0    | 40°    | 18211.9 | 16763.7 | 15315.6 | 13777.7 | 12238.3 | 10700.5 | 9162.6  | 7651.5  | 6140.4  |
| 0.0  | 0.0    | 42.5°  | 25079.5 | 23122.9 | 21166.4 | 19120.1 | 17072.3 | 15026.0 | 12978.1 | 10846.8 | 8714.0  |
| 0.0  | 0.0    | 45°    | 32830.2 | 30403.0 | 27974.2 | 25677.6 | 23379.5 | 21083.0 | 18786.4 | 15861.8 | 12937.2 |
| 0.0  | 0.0    | 47.5°  | 37188.7 | 34567.9 | 31947.1 | 29773.3 | 27599.6 | 25425.8 | 23252.0 | 20099.2 | 16946.3 |
| 0.0  | 0.0    | 50°    | 38792.7 | 36124.7 | 33456.6 | 31456.0 | 29453.8 | 27453.2 | 25451.0 | 22293.4 | 19134.3 |
| 0.0  | 0.0    | 52.5°  | 39134.3 | 36412.7 | 33691.2 | 31678.0 | 29664.7 | 27653.1 | 25639.9 | 22502.8 | 19365.7 |
| 0.0  | 0.0    | 55°    | 39836.3 | 36916.4 | 33995.0 | 31700.0 | 29405.0 | 27110.0 | 24815.1 | 21627.6 | 18440.1 |
| 0.0  | 0.0    | 57.5°  | 40754.0 | 37760.1 | 34766.3 | 32151.7 | 29537.2 | 26924.3 | 24309.8 | 20824.8 | 17339.8 |
| 0.0  | 0.0    | 60°    | 40513.2 | 37908.1 | 35301.4 | 32501.2 | 29699.4 | 26899.1 | 24097.3 | 20264.4 | 16430.0 |
| 0.0  | 0.0    | 62.5°  | 36332.5 | 34257.8 | 32181.7 | 29878.8 | 27574.4 | 25271.5 | 22968.7 | 19022.5 | 15076.3 |
| 0.0  | 0.0    | 65°    | 29889.8 | 28375.6 | 26861.3 | 25008.7 | 23154.4 | 21301.8 | 19449.1 | 15910.6 | 12373.7 |
| 0.0  | 0.0    | 67.5°  | 24224.8 | 22518.5 | 20810.6 | 19334.2 | 17856.1 | 16379.7 | 14901.6 | 12117.1 | 9332.6  |
|      |        | 70°    | 19246.0 | 17390.2 | 15532.8 | 14091.0 | 12647.6 | 11205.7 | 9763.9  | 7912.8  | 6063.3  |
|      |        | 72.5°  | 15284.1 | 13610.9 | 11937.7 | 10399.8 | 8860.4  | 7322.5  | 5783.1  | 4689.1  | 3595.2  |
|      |        | 75°    | 7305.2  | 6636.2  | 5967.3  | 5162.9  | 4358.6  | 3554.2  | 2749.9  | 2272.9  | 1797.6  |
|      |        | 77.5°  | 2707.4  | 2346.9  | 1984.9  | 1657.5  | 1330.1  | 1004.3  | 676.8   | 620.2   | 563.5   |
|      |        | 80°    | 700.5   | 610.7   | 519.4   | 454.9   | 388.8   | 324.3   | 259.7   | 234.5   | 210.9   |
|      |        | 82.5°  | 80.3    | 74.0    | 69.3    | 66.1    | 61.4    | 58.2    | 53.5    | 48.8    | 44.1    |
|      |        | 85°    | 4.7     | 3.1     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 91.3   | 91.3   |
| 0.0    | 0.0  | 2.5°   | 85.0   | 83.4   |
| 0.0    | 0.0  | 5°     | 89.7   | 88.1   |
| 0.0    | 0.0  | 7.5°   | 99.2   | 96.0   |
| 0.0    | 0.0  | 10°    | 108.6  | 105.5  |
| 0.0    | 0.0  | 12.5°  | 122.8  | 118.1  |
| 0.0    | 0.0  | 15°    | 138.5  | 129.1  |
| 0.0    | 0.0  | 17.5°  | 165.3  | 144.8  |
| 0.0    | 0.0  | 20°    | 223.5  | 171.6  |
| 0.0    | 0.0  | 22.5°  | 314.8  | 214.1  |
| 0.0    | 0.0  | 25°    | 462.8  | 295.9  |
| 0.0    | 0.0  | 27.5°  | 643.8  | 393.5  |
| 0.0    | 0.0  | 30°    | 856.3  | 492.7  |
| 0.0    | 0.0  | 32.5°  | 1043.6 | 587.1  |
| 0.0    | 0.0  | 35°    | 1287.6 | 683.1  |
| 0.0    | 0.0  | 37.5°  | 1588.2 | 805.9  |
| 0.0    | 0.0  | 40°    | 2054.1 | 991.7  |
| 0.0    | 0.0  | 42.5°  | 2893.1 | 1334.8 |
| 0.0    | 0.0  | 45°    | 4698.6 | 2307.6 |
| 0.0    | 0.0  | 47.5°  | 7229.7 | 3817.1 |
| 0.0    | 0.0  | 50°    | 8844.6 | 4871.7 |
| 0.0    | 0.0  | 52.5°  | 8976.9 | 4863.8 |
| 0.0    | 0.0  | 55°    | 8194.6 | 4323.9 |
| 0.0    | 0.0  | 57.5°  | 6992.0 | 3614.0 |
| 0.0    | 0.0  | 60°    | 5811.4 | 2858.5 |
| 0.0    | 0.0  | 62.5°  | 4578.9 | 1973.9 |
| 0.0    | 0.0  | 65°    | 3346.5 | 1396.2 |
| 0.0    | 0.0  | 67.5°  | 2403.6 | 1043.6 |
|        |      | 70°    | 1580.4 | 799.6  |
|        |      | 72.5°  | 1029.4 | 651.7  |
|        |      | 75°    | 692.6  | 539.9  |
|        |      | 77.5°  | 404.5  | 358.9  |
|        |      | 80°    | 143.2  | 125.9  |
|        |      | 82.5°  | 26.8   | 18.9   |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1049378

CATALOG NUMBER: GALN-SA7B-935-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-15

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-935-U-5WQ

Data in this report applies to families of products including GSS-SB1A-935-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-15  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-935-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 3500K CCT 26 LEDS

### Spectral Parameters

CCT (K): 3455  
 CIE  $u'$ : 0.2356  
 CIE  $v'$ : 0.5159  
 Duv: 0.0028  
 CIE x: 0.4109  
 CIE y: 0.3999  
 CIE z: 0.1892  
 Peak Wavelength (nm): 616  
 Dominant Wavelength (nm): 579  
 Purity: 43.35383  
 R<sub>f</sub>: 92.3  
 R<sub>g</sub>: 98.5

CRI (Ra): 92.2  
 R1: 92.0  
 R2: 94.4  
 R3: 95.6  
 R4: 93.2  
 R5: 91.4  
 R6: 92.5  
 R7: 94.5  
 R8: 84.2  
 R9: 59.8  
 R10: 85.8  
 R11: 93.2  
 R12: 78.0  
 R13: 92.5  
 R14: 97.0  
 R15: 88.4



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-15


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-15

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 3500K 4-step quadrangle


REPORT NUMBER: SP1-2407-184-15

**Photopic Flux vs. Wavelength**

**Photopic Lumens: NR**

| $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^\wedge/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|-------------------|--------------------------------------|--------------------------------|
| 360               | 0                                    | NR                             | 490               | 410                                  | NR                             | 620               | 997                                  | NR                             | 750               | 74                                   | NR                             | 880               | 1                                    | NR                             |
| 365               | 0                                    | NR                             | 495               | 454                                  | NR                             | 625               | 988                                  | NR                             | 755               | 64                                   | NR                             | 885               | 1                                    | NR                             |
| 370               | 0                                    | NR                             | 500               | 493                                  | NR                             | 630               | 973                                  | NR                             | 760               | 54                                   | NR                             | 890               | 1                                    | NR                             |
| 375               | 0                                    | NR                             | 505               | 530                                  | NR                             | 635               | 946                                  | NR                             | 765               | 47                                   | NR                             | 895               | 1                                    | NR                             |
| 380               | 0                                    | NR                             | 510               | 564                                  | NR                             | 640               | 913                                  | NR                             | 770               | 40                                   | NR                             | 900               | 1                                    | NR                             |
| 385               | 0                                    | NR                             | 515               | 599                                  | NR                             | 645               | 870                                  | NR                             | 775               | 34                                   | NR                             | 905               | 1                                    | NR                             |
| 390               | 0                                    | NR                             | 520               | 634                                  | NR                             | 650               | 826                                  | NR                             | 780               | 29                                   | NR                             | 910               | 1                                    | NR                             |
| 395               | 0                                    | NR                             | 525               | 664                                  | NR                             | 655               | 774                                  | NR                             | 785               | 25                                   | NR                             | 915               | 1                                    | NR                             |
| 400               | 2                                    | NR                             | 530               | 695                                  | NR                             | 660               | 720                                  | NR                             | 790               | 21                                   | NR                             | 920               | 1                                    | NR                             |
| 405               | 4                                    | NR                             | 535               | 722                                  | NR                             | 665               | 664                                  | NR                             | 795               | 18                                   | NR                             | 925               | 1                                    | NR                             |
| 410               | 9                                    | NR                             | 540               | 741                                  | NR                             | 670               | 605                                  | NR                             | 800               | 16                                   | NR                             | 930               | 0                                    | NR                             |
| 415               | 17                                   | NR                             | 545               | 762                                  | NR                             | 675               | 550                                  | NR                             | 805               | 13                                   | NR                             | 935               | 0                                    | NR                             |
| 420               | 32                                   | NR                             | 550               | 777                                  | NR                             | 680               | 497                                  | NR                             | 810               | 12                                   | NR                             | 940               | 0                                    | NR                             |
| 425               | 61                                   | NR                             | 555               | 789                                  | NR                             | 685               | 445                                  | NR                             | 815               | 10                                   | NR                             | 945               | 0                                    | NR                             |
| 430               | 114                                  | NR                             | 560               | 800                                  | NR                             | 690               | 398                                  | NR                             | 820               | 9                                    | NR                             | 950               | 0                                    | NR                             |
| 435               | 218                                  | NR                             | 565               | 813                                  | NR                             | 695               | 352                                  | NR                             | 825               | 7                                    | NR                             | 955               | 0                                    | NR                             |
| 440               | 427                                  | NR                             | 570               | 828                                  | NR                             | 700               | 309                                  | NR                             | 830               | 6                                    | NR                             | 960               | 0                                    | NR                             |
| 445               | 684                                  | NR                             | 575               | 846                                  | NR                             | 705               | 273                                  | NR                             | 835               | 5                                    | NR                             | 965               | 0                                    | NR                             |
| 450               | 611                                  | NR                             | 580               | 866                                  | NR                             | 710               | 237                                  | NR                             | 840               | 5                                    | NR                             | 970               | 0                                    | NR                             |
| 455               | 461                                  | NR                             | 585               | 888                                  | NR                             | 715               | 208                                  | NR                             | 845               | 4                                    | NR                             | 975               | 0                                    | NR                             |
| 460               | 427                                  | NR                             | 590               | 913                                  | NR                             | 720               | 181                                  | NR                             | 850               | 4                                    | NR                             | 980               | 0                                    | NR                             |
| 465               | 349                                  | NR                             | 595               | 936                                  | NR                             | 725               | 157                                  | NR                             | 855               | 3                                    | NR                             | 985               | 0                                    | NR                             |
| 470               | 298                                  | NR                             | 600               | 957                                  | NR                             | 730               | 136                                  | NR                             | 860               | 3                                    | NR                             | 990               | 1                                    | NR                             |
| 475               | 312                                  | NR                             | 605               | 976                                  | NR                             | 735               | 117                                  | NR                             | 865               | 2                                    | NR                             | 995               | 0                                    | NR                             |
| 480               | 335                                  | NR                             | 610               | 990                                  | NR                             | 740               | 100                                  | NR                             | 870               | 2                                    | NR                             | 1000              | 0                                    | NR                             |
| 485               | 367                                  | NR                             | 615               | 999                                  | NR                             | 745               | 86                                   | NR                             | 875               | 2                                    | NR                             |                   |                                      |                                |

REPORT NUMBER: SP1-2407-184-15

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.58

| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(Φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 410                         | NR               | 620       | 997                         | NR               | 750       | 74                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 454                         | NR               | 625       | 988                         | NR               | 755       | 64                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 493                         | NR               | 630       | 973                         | NR               | 760       | 54                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 530                         | NR               | 635       | 946                         | NR               | 765       | 47                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 564                         | NR               | 640       | 913                         | NR               | 770       | 40                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 599                         | NR               | 645       | 870                         | NR               | 775       | 34                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 634                         | NR               | 650       | 826                         | NR               | 780       | 29                          | NR               | 910       | 1                           | NR               |
| 395       | 0                           | NR               | 525       | 664                         | NR               | 655       | 774                         | NR               | 785       | 25                          | NR               | 915       | 1                           | NR               |
| 400       | 2                           | NR               | 530       | 695                         | NR               | 660       | 720                         | NR               | 790       | 21                          | NR               | 920       | 1                           | NR               |
| 405       | 4                           | NR               | 535       | 722                         | NR               | 665       | 664                         | NR               | 795       | 18                          | NR               | 925       | 1                           | NR               |
| 410       | 9                           | NR               | 540       | 741                         | NR               | 670       | 605                         | NR               | 800       | 16                          | NR               | 930       | 0                           | NR               |
| 415       | 17                          | NR               | 545       | 762                         | NR               | 675       | 550                         | NR               | 805       | 13                          | NR               | 935       | 0                           | NR               |
| 420       | 32                          | NR               | 550       | 777                         | NR               | 680       | 497                         | NR               | 810       | 12                          | NR               | 940       | 0                           | NR               |
| 425       | 61                          | NR               | 555       | 789                         | NR               | 685       | 445                         | NR               | 815       | 10                          | NR               | 945       | 0                           | NR               |
| 430       | 114                         | NR               | 560       | 800                         | NR               | 690       | 398                         | NR               | 820       | 9                           | NR               | 950       | 0                           | NR               |
| 435       | 218                         | NR               | 565       | 813                         | NR               | 695       | 352                         | NR               | 825       | 7                           | NR               | 955       | 0                           | NR               |
| 440       | 427                         | NR               | 570       | 828                         | NR               | 700       | 309                         | NR               | 830       | 6                           | NR               | 960       | 0                           | NR               |
| 445       | 684                         | NR               | 575       | 846                         | NR               | 705       | 273                         | NR               | 835       | 5                           | NR               | 965       | 0                           | NR               |
| 450       | 611                         | NR               | 580       | 866                         | NR               | 710       | 237                         | NR               | 840       | 5                           | NR               | 970       | 0                           | NR               |
| 455       | 461                         | NR               | 585       | 888                         | NR               | 715       | 208                         | NR               | 845       | 4                           | NR               | 975       | 0                           | NR               |
| 460       | 427                         | NR               | 590       | 913                         | NR               | 720       | 181                         | NR               | 850       | 4                           | NR               | 980       | 0                           | NR               |
| 465       | 349                         | NR               | 595       | 936                         | NR               | 725       | 157                         | NR               | 855       | 3                           | NR               | 985       | 0                           | NR               |
| 470       | 298                         | NR               | 600       | 957                         | NR               | 730       | 136                         | NR               | 860       | 3                           | NR               | 990       | 1                           | NR               |
| 475       | 312                         | NR               | 605       | 976                         | NR               | 735       | 117                         | NR               | 865       | 2                           | NR               | 995       | 0                           | NR               |
| 480       | 335                         | NR               | 610       | 990                         | NR               | 740       | 100                         | NR               | 870       | 2                           | NR               | 1000      | 0                           | NR               |
| 485       | 367                         | NR               | 615       | 999                         | NR               | 745       | 86                          | NR               | 875       | 2                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-15

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.14


| $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}^{\wedge}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|-------------------|----------------------------------------|--------------------------------|
| 360               | 0                                      | NR                             | 490               | 410                                    | NR                             | 620               | 997                                    | NR                             | 750               | 74                                     | NR                             | 880               | 1                                      | NR                             |
| 365               | 0                                      | NR                             | 495               | 454                                    | NR                             | 625               | 988                                    | NR                             | 755               | 64                                     | NR                             | 885               | 1                                      | NR                             |
| 370               | 0                                      | NR                             | 500               | 493                                    | NR                             | 630               | 973                                    | NR                             | 760               | 54                                     | NR                             | 890               | 1                                      | NR                             |
| 375               | 0                                      | NR                             | 505               | 530                                    | NR                             | 635               | 946                                    | NR                             | 765               | 47                                     | NR                             | 895               | 1                                      | NR                             |
| 380               | 0                                      | NR                             | 510               | 564                                    | NR                             | 640               | 913                                    | NR                             | 770               | 40                                     | NR                             | 900               | 1                                      | NR                             |
| 385               | 0                                      | NR                             | 515               | 599                                    | NR                             | 645               | 870                                    | NR                             | 775               | 34                                     | NR                             | 905               | 1                                      | NR                             |
| 390               | 0                                      | NR                             | 520               | 634                                    | NR                             | 650               | 826                                    | NR                             | 780               | 29                                     | NR                             | 910               | 1                                      | NR                             |
| 395               | 0                                      | NR                             | 525               | 664                                    | NR                             | 655               | 774                                    | NR                             | 785               | 25                                     | NR                             | 915               | 1                                      | NR                             |
| 400               | 2                                      | NR                             | 530               | 695                                    | NR                             | 660               | 720                                    | NR                             | 790               | 21                                     | NR                             | 920               | 1                                      | NR                             |
| 405               | 4                                      | NR                             | 535               | 722                                    | NR                             | 665               | 664                                    | NR                             | 795               | 18                                     | NR                             | 925               | 1                                      | NR                             |
| 410               | 9                                      | NR                             | 540               | 741                                    | NR                             | 670               | 605                                    | NR                             | 800               | 16                                     | NR                             | 930               | 0                                      | NR                             |
| 415               | 17                                     | NR                             | 545               | 762                                    | NR                             | 675               | 550                                    | NR                             | 805               | 13                                     | NR                             | 935               | 0                                      | NR                             |
| 420               | 32                                     | NR                             | 550               | 777                                    | NR                             | 680               | 497                                    | NR                             | 810               | 12                                     | NR                             | 940               | 0                                      | NR                             |
| 425               | 61                                     | NR                             | 555               | 789                                    | NR                             | 685               | 445                                    | NR                             | 815               | 10                                     | NR                             | 945               | 0                                      | NR                             |
| 430               | 114                                    | NR                             | 560               | 800                                    | NR                             | 690               | 398                                    | NR                             | 820               | 9                                      | NR                             | 950               | 0                                      | NR                             |
| 435               | 218                                    | NR                             | 565               | 813                                    | NR                             | 695               | 352                                    | NR                             | 825               | 7                                      | NR                             | 955               | 0                                      | NR                             |
| 440               | 427                                    | NR                             | 570               | 828                                    | NR                             | 700               | 309                                    | NR                             | 830               | 6                                      | NR                             | 960               | 0                                      | NR                             |
| 445               | 684                                    | NR                             | 575               | 846                                    | NR                             | 705               | 273                                    | NR                             | 835               | 5                                      | NR                             | 965               | 0                                      | NR                             |
| 450               | 611                                    | NR                             | 580               | 866                                    | NR                             | 710               | 237                                    | NR                             | 840               | 5                                      | NR                             | 970               | 0                                      | NR                             |
| 455               | 461                                    | NR                             | 585               | 888                                    | NR                             | 715               | 208                                    | NR                             | 845               | 4                                      | NR                             | 975               | 0                                      | NR                             |
| 460               | 427                                    | NR                             | 590               | 913                                    | NR                             | 720               | 181                                    | NR                             | 850               | 4                                      | NR                             | 980               | 0                                      | NR                             |
| 465               | 349                                    | NR                             | 595               | 936                                    | NR                             | 725               | 157                                    | NR                             | 855               | 3                                      | NR                             | 985               | 0                                      | NR                             |
| 470               | 298                                    | NR                             | 600               | 957                                    | NR                             | 730               | 136                                    | NR                             | 860               | 3                                      | NR                             | 990               | 1                                      | NR                             |
| 475               | 312                                    | NR                             | 605               | 976                                    | NR                             | 735               | 117                                    | NR                             | 865               | 2                                      | NR                             | 995               | 0                                      | NR                             |
| 480               | 335                                    | NR                             | 610               | 990                                    | NR                             | 740               | 100                                    | NR                             | 870               | 2                                      | NR                             | 1000              | 0                                      | NR                             |
| 485               | 367                                    | NR                             | 615               | 999                                    | NR                             | 745               | 86                                     | NR                             | 875               | 2                                      | NR                             |                   |                                        |                                |

REPORT NUMBER: SP1-2407-184-15





TM-30-18

### Summary

$R_f = 92.3$   
 $R_g = 98.5$   
 $\text{CIE } R_a = 92.2$   
 $R_9 = 59.8$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**


|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 93 | CES51 = 97 | CES76 = 88 |
| CES02 = 62 | CES27 = 93 | CES52 = 98 | CES77 = 91 |
| CES03 = 31 | CES28 = 96 | CES53 = 96 | CES78 = 85 |
| CES04 = 70 | CES29 = 95 | CES54 = 95 | CES79 = 96 |
| CES05 = 50 | CES30 = 97 | CES55 = 94 | CES80 = 94 |
| CES06 = 51 | CES31 = 96 | CES56 = 94 | CES81 = 87 |
| CES07 = 42 | CES32 = 91 | CES57 = 93 | CES82 = 97 |
| CES08 = 41 | CES33 = 98 | CES58 = 94 | CES83 = 97 |
| CES09 = 29 | CES34 = 94 | CES59 = 96 | CES84 = 94 |
| CES10 = 75 | CES35 = 97 | CES60 = 94 | CES85 = 85 |
| CES11 = 58 | CES36 = 86 | CES61 = 93 | CES86 = 87 |
| CES12 = 64 | CES37 = 95 | CES62 = 91 | CES87 = 92 |
| CES13 = 43 | CES38 = 92 | CES63 = 93 | CES88 = 96 |
| CES14 = 74 | CES39 = 99 | CES64 = 91 | CES89 = 87 |
| CES15 = 71 | CES40 = 98 | CES65 = 89 | CES90 = 96 |
| CES16 = 47 | CES41 = 98 | CES66 = 89 | CES91 = 78 |
| CES17 = 49 | CES42 = 96 | CES67 = 88 | CES92 = 81 |
| CES18 = 56 | CES43 = 96 | CES68 = 89 | CES93 = 89 |
| CES19 = 71 | CES44 = 99 | CES69 = 91 | CES94 = 81 |
| CES20 = 66 | CES45 = 98 | CES70 = 87 | CES95 = 85 |
| CES21 = 86 | CES46 = 97 | CES71 = 84 | CES96 = 92 |
| CES22 = 78 | CES47 = 97 | CES72 = 95 | CES97 = 95 |
| CES23 = 91 | CES48 = 93 | CES73 = 83 | CES98 = 94 |
| CES24 = 90 | CES49 = 96 | CES74 = 94 | CES99 = 91 |
| CES25 = 71 | CES50 = 98 | CES75 = 85 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)