

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047543

Luminaire Tested: **GALN-SA7C-935-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047543
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA7C-935-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 1050mA 7xLight Square PACKAGE
90CRI 3500K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (98) 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 29643.2 lumens
Efficiency: N/A
Efficacy: 89.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G5

Input Watts (W): 330
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047543

CATALOG NUMBER: GALN-SA7C-935-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

× Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 33.3 fc
 Type III - Short - N/A

REPORT NUMBER: P1047543

CATALOG NUMBER: GALN-SA7C-935-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047543

CATALOG NUMBER: GALN-SA7C-935-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	108.2	0.0	108.2
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	29535.0	0.0	29535.0
	% Fixture	99.6	0.0	99.6
Total	Lumens	29643.2	0.0	29643.2
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.4	0.1
10°-20°	340.7	1.1
20°-30°	1228.2	4.1
30°-40°	2810.0	9.5
40°-50°	4739.4	16.0
50°-60°	7821.1	26.4
60°-70°	8741.1	29.5
70°-80°	3609.1	12.2
80°-90°	325.4	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	29643.2	100.0
0°-180°	29643.2	100.0



REPORT NUMBER: P1047543


CATALOG NUMBER: GALN-SA7C-935-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	1569.1	5.3			
FM	(30°-60°)	15344.5	51.8			
FH	(60°-80°)	12300.6	41.5			G5
FVH	(80°-90°)	320.9	1.1			G3/500
BL	(0°-30°)	28.2	0.1	B0/110		
BM	(30°-60°)	25.9	0.1	B0/220		
BH	(60°-80°)	49.6	0.2	B0/110		G0/110
BVH	(80°-90°)	4.5	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G5

Type III Short



REPORT NUMBER: P1047543

CATALOG NUMBER: GALN-SA7C-935-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8
2.5°	232.6	240.3	232.6	232.6	232.6	224.8	224.8	217.1	217.1	209.3	201.6
5°	341.1	341.1	317.9	302.4	286.9	279.1	271.4	255.8	240.3	224.8	209.3
7.5°	759.8	759.8	690.0	597.0	472.9	403.2	387.6	317.9	271.4	240.3	209.3
10°	1814.2	1814.2	1659.1	1403.3	1085.4	806.3	721.0	457.4	325.6	255.8	217.1
12.5°	3015.9	3054.7	2860.8	2535.2	2062.3	1573.8	1403.3	837.3	434.2	279.1	217.1
15°	4093.5	4000.5	3946.2	3636.1	3186.5	2605.0	2387.9	1411.0	628.0	317.9	217.1
17.5°	4822.3	4822.3	4744.8	4535.5	4124.6	3612.9	3434.5	2279.4	1015.6	364.4	224.8
20°	5675.1	5675.1	5535.6	5388.3	5023.9	4589.7	4419.2	3240.7	1573.8	465.2	224.8
22.5°	6706.3	6721.8	6566.7	6303.1	5954.2	5473.6	5326.3	4132.3	2279.4	620.2	232.6
25°	7962.3	7977.8	7752.9	7504.8	6969.9	6450.4	6225.6	5155.7	3139.9	868.3	232.6
27.5°	9350.0	9458.6	9125.2	8698.8	8132.8	7481.6	7311.0	6078.3	3992.8	1225.0	248.1
30°	11078.9	11078.9	10637.0	10040.0	9427.6	8621.3	8404.2	7047.4	4899.8	1697.9	263.6
32.5°	12567.5	12451.2	11885.2	11257.2	10606.0	9854.0	9621.4	8063.0	5830.2	2287.1	294.6
35°	13707.2	13606.4	12908.6	12234.1	11668.2	10978.1	10699.0	9164.0	6814.8	2953.9	341.1
37.5°	14684.0	14645.3	13699.4	12854.3	12482.2	11877.5	11629.4	10202.8	7783.9	3674.9	395.4
40°	15753.9	15629.9	14622.0	13575.4	13017.2	12528.7	12303.9	11040.2	8714.3	4520.0	472.9
42.5°	16668.8	16521.5	15614.4	14591.0	13637.4	12978.4	12761.3	11745.7	9621.4	5365.0	573.7
45°	17684.4	17606.9	16692.0	15916.8	14645.3	13590.9	13304.0	12311.6	10450.9	6372.9	705.5
47.5°	19211.7	19072.2	18219.4	17583.6	16110.6	14521.2	14110.3	12893.1	11249.5	7365.3	907.1
50°	20987.2	20894.1	20390.2	19886.3	18420.9	16110.6	15622.1	13730.4	12141.1	8543.7	1170.7
52.5°	22437.0	22421.5	22483.5	22491.2	21382.6	18785.3	18056.6	15079.4	13164.5	9706.7	1542.8
55°	22406.0	22475.7	23158.0	23941.0	24026.3	22437.0	21731.4	17351.0	14498.0	11141.0	2062.3
57.5°	21568.6	21514.4	22235.4	23413.8	24243.4	24414.0	24297.7	20878.6	16506.0	12869.9	2860.8
58°	21297.3	21250.8	21933.0	23134.7	24088.3	24545.8	24429.5	21677.2	16955.6	13117.9	3077.9
60°	20312.7	20320.4	20723.6	21816.7	22770.3	23855.7	23964.3	23956.5	19196.2	14777.1	4171.1
62.5°	19010.2	18948.1	19320.3	20211.9	21049.2	21778.0	21964.0	24111.6	22475.7	16885.9	6256.6
65°	17211.5	17118.5	17513.9	18521.7	19421.1	19894.0	19901.8	22033.8	24018.6	19149.7	9233.7
67.5°	13870.0	13792.5	14583.3	15878.0	17265.8	17886.0	18165.1	19118.7	22716.1	20684.8	10939.4
70°	8497.2	8660.0	9760.9	11792.2	14164.6	15304.3	15722.9	16017.5	19343.5	20452.2	9148.5
72.5°	3923.0	3729.2	4667.3	6086.0	8791.8	11327.0	11761.2	12916.4	15335.3	17754.2	6822.6
75°	1829.7	1759.9	1977.0	2659.3	3985.0	6117.1	6907.9	10311.4	11761.2	12350.4	4923.1
77.5°	938.1	945.9	1124.2	1209.5	1643.6	2829.8	3248.5	6783.8	8621.3	6892.3	3302.7
80°	410.9	426.4	434.2	472.9	666.8	1093.2	1232.7	3147.7	5892.2	3512.1	1806.4
82.5°	263.6	271.4	271.4	271.4	317.9	434.2	496.2	1263.7	2938.4	1744.4	558.2
85°	139.6	139.6	155.1	193.8	224.8	263.6	279.1	403.2	969.1	519.4	131.8
87.5°	77.5	85.3	93.0	116.3	147.3	178.3	193.8	279.1	372.1	356.6	31.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P1047543

CATALOG NUMBER: GALN-SA7C-935-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8	193.8
2.5°	201.6	193.8	186.1	178.3	170.6	162.8	162.8	162.8	162.8	162.8	162.8
5°	193.8	186.1	178.3	162.8	147.3	139.6	131.8	124.0	124.0	124.0	124.0
7.5°	193.8	186.1	162.8	147.3	131.8	116.3	100.8	100.8	100.8	100.8	100.8
10°	193.8	178.3	155.1	131.8	108.5	93.0	85.3	77.5	77.5	77.5	77.5
12.5°	193.8	170.6	147.3	116.3	93.0	77.5	69.8	62.0	62.0	62.0	62.0
15°	193.8	170.6	139.6	108.5	85.3	62.0	54.3	46.5	46.5	46.5	46.5
17.5°	186.1	162.8	131.8	93.0	69.8	46.5	38.8	31.0	31.0	38.8	38.8
20°	178.3	155.1	116.3	77.5	54.3	38.8	23.3	23.3	23.3	23.3	23.3
22.5°	178.3	155.1	108.5	69.8	46.5	23.3	15.5	15.5	15.5	15.5	23.3
25°	178.3	147.3	93.0	54.3	31.0	15.5	7.8	7.8	7.8	7.8	7.8
27.5°	178.3	147.3	85.3	46.5	23.3	15.5	7.8	0.0	0.0	0.0	0.0
30°	170.6	139.6	77.5	38.8	15.5	7.8	0.0	0.0	0.0	0.0	0.0
32.5°	170.6	131.8	62.0	31.0	15.5	7.8	0.0	0.0	0.0	0.0	0.0
35°	178.3	124.0	54.3	23.3	7.8	0.0	0.0	0.0	0.0	0.0	7.8
37.5°	186.1	116.3	46.5	15.5	7.8	0.0	0.0	0.0	0.0	0.0	0.0
40°	193.8	108.5	46.5	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	209.3	108.5	38.8	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	224.8	108.5	31.0	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	255.8	116.3	31.0	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	279.1	124.0	23.3	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	310.1	116.3	23.3	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	348.9	116.3	23.3	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	379.9	108.5	23.3	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	395.4	100.8	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	472.9	93.0	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	736.5	77.5	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	1496.3	69.8	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	2791.1	62.0	15.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	3124.4	69.8	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	1969.2	54.3	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	1038.9	54.3	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	519.4	54.3	7.8	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	240.3	38.8	7.8	7.8	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	100.8	23.3	15.5	7.8	7.8	0.0	0.0	0.0	0.0	0.0	0.0
85°	46.5	23.3	15.5	15.5	7.8	7.8	0.0	0.0	0.0	0.0	0.0
87.5°	23.3	23.3	23.3	15.5	15.5	7.8	7.8	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-15

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-935-U-5WQ

Data in this report applies to families of products including GSS-SB1A-935-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-15
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-935-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 3500K CCT 26 LEDS

Spectral Parameters

CCT (K): 3455
 CIE u' : 0.2356
 CIE v' : 0.5159
 Duv: 0.0028
 CIE x: 0.4109
 CIE y: 0.3999
 CIE z: 0.1892
 Peak Wavelength (nm): 616
 Dominant Wavelength (nm): 579
 Purity: 43.35383
 R_f: 92.3
 R_g: 98.5

CRI (Ra): 92.2
 R1: 92.0
 R2: 94.4
 R3: 95.6
 R4: 93.2
 R5: 91.4
 R6: 92.5
 R7: 94.5
 R8: 84.2
 R9: 59.8
 R10: 85.8
 R11: 93.2
 R12: 78.0
 R13: 92.5
 R14: 97.0
 R15: 88.4



Test Conditions

Stabilization Time: 20M
 Operation Time: 1H 20M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-15

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-15

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3500K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-15

Photopic Flux vs. Wavelength



Photopic Lumens: NR

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.58

λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)	λ (nm)	Power W [^] /nm	Lumens (Φ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.14

λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	410	NR	620	997	NR	750	74	NR	880	1	NR
365	0	NR	495	454	NR	625	988	NR	755	64	NR	885	1	NR
370	0	NR	500	493	NR	630	973	NR	760	54	NR	890	1	NR
375	0	NR	505	530	NR	635	946	NR	765	47	NR	895	1	NR
380	0	NR	510	564	NR	640	913	NR	770	40	NR	900	1	NR
385	0	NR	515	599	NR	645	870	NR	775	34	NR	905	1	NR
390	0	NR	520	634	NR	650	826	NR	780	29	NR	910	1	NR
395	0	NR	525	664	NR	655	774	NR	785	25	NR	915	1	NR
400	2	NR	530	695	NR	660	720	NR	790	21	NR	920	1	NR
405	4	NR	535	722	NR	665	664	NR	795	18	NR	925	1	NR
410	9	NR	540	741	NR	670	605	NR	800	16	NR	930	0	NR
415	17	NR	545	762	NR	675	550	NR	805	13	NR	935	0	NR
420	32	NR	550	777	NR	680	497	NR	810	12	NR	940	0	NR
425	61	NR	555	789	NR	685	445	NR	815	10	NR	945	0	NR
430	114	NR	560	800	NR	690	398	NR	820	9	NR	950	0	NR
435	218	NR	565	813	NR	695	352	NR	825	7	NR	955	0	NR
440	427	NR	570	828	NR	700	309	NR	830	6	NR	960	0	NR
445	684	NR	575	846	NR	705	273	NR	835	5	NR	965	0	NR
450	611	NR	580	866	NR	710	237	NR	840	5	NR	970	0	NR
455	461	NR	585	888	NR	715	208	NR	845	4	NR	975	0	NR
460	427	NR	590	913	NR	720	181	NR	850	4	NR	980	0	NR
465	349	NR	595	936	NR	725	157	NR	855	3	NR	985	0	NR
470	298	NR	600	957	NR	730	136	NR	860	3	NR	990	1	NR
475	312	NR	605	976	NR	735	117	NR	865	2	NR	995	0	NR
480	335	NR	610	990	NR	740	100	NR	870	2	NR	1000	0	NR
485	367	NR	615	999	NR	745	86	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-15




TM-30-18

Summary

$R_f = 92.3$
 $R_g = 98.5$
 $CIE R_a = 92.2$
 $R_9 = 59.8$



Color Vector Graphics




Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 93	CES51 = 97	CES76 = 88
CES02 = 62	CES27 = 93	CES52 = 98	CES77 = 91
CES03 = 31	CES28 = 96	CES53 = 96	CES78 = 85
CES04 = 70	CES29 = 95	CES54 = 95	CES79 = 96
CES05 = 50	CES30 = 97	CES55 = 94	CES80 = 94
CES06 = 51	CES31 = 96	CES56 = 94	CES81 = 87
CES07 = 42	CES32 = 91	CES57 = 93	CES82 = 97
CES08 = 41	CES33 = 98	CES58 = 94	CES83 = 97
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 94
CES10 = 75	CES35 = 97	CES60 = 94	CES85 = 85
CES11 = 58	CES36 = 86	CES61 = 93	CES86 = 87
CES12 = 64	CES37 = 95	CES62 = 91	CES87 = 92
CES13 = 43	CES38 = 92	CES63 = 93	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 91	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 89	CES90 = 96
CES16 = 47	CES41 = 98	CES66 = 89	CES91 = 78
CES17 = 49	CES42 = 96	CES67 = 88	CES92 = 81
CES18 = 56	CES43 = 96	CES68 = 89	CES93 = 89
CES19 = 71	CES44 = 99	CES69 = 91	CES94 = 81
CES20 = 66	CES45 = 98	CES70 = 87	CES95 = 85
CES21 = 86	CES46 = 97	CES71 = 84	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 95	CES97 = 95
CES23 = 91	CES48 = 93	CES73 = 83	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 94	CES99 = 91
CES25 = 71	CES50 = 98	CES75 = 85	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)