

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1047557

Luminaire Tested: **GALN-SA2A-940-U-T3BC**

Issue Date: 07/10/2025

Test Information

Test Method: LM-79-08
Report Number: P1047557
Test Lab: INNOVATION CENTER(G3)
Issue Date: 07/10/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SA2A-940-U-T3BC
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 615mA 2xLight Square PACKAGE
90CRI 4000K FIXTURE w/ TYPE III ANGLED BACKLIGHT CONTROL
Light Source: (28) 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5610.6 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Short
BUG Rating: B0 - U0 - G2

Input Watts (W): 55.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.97
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 28.75 FT




REPORT NUMBER: P1047557

CATALOG NUMBER: GALN-SA2A-940-U-T3BC

Iso-Footcandle Lines of Horizontal Illumination

✕ Max cd
 - - - 1/2 Max cd




Based on 15 foot mounting height. Maximum calculated value = 6.3 fc
 Type III - Short - N/A

REPORT NUMBER: P1047557

CATALOG NUMBER: GALN-SA2A-940-U-T3BC

Luminous Intensity Polar Plot



REPORT NUMBER: P1047557

CATALOG NUMBER: GALN-SA2A-940-U-T3BC

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	20.5	0.0	20.5
	% Fixture	0.4	0.0	0.4
Street Side	Lumens	5590.1	0.0	5590.1
	% Fixture	99.6	0.0	99.6
Total	Lumens	5610.6	0.0	5610.6
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	5.4	0.1
10°-20°	64.5	1.1
20°-30°	232.5	4.1
30°-40°	531.8	9.5
40°-50°	897.0	16.0
50°-60°	1480.3	26.4
60°-70°	1654.4	29.5
70°-80°	683.1	12.2
80°-90°	61.6	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5610.6	100.0
0°-180°	5610.6	100.0



REPORT NUMBER: P1047557


CATALOG NUMBER: GALN-SA2A-940-U-T3BC

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone		Lumens	% Fixture	Zone Rating/Lumen Limit		
				B	U	G
FL	(0°-30°)	297.0	5.3			
FM	(30°-60°)	2904.3	51.8			
FH	(60°-80°)	2328.1	41.5			G2/5000
FVH	(80°-90°)	60.7	1.1			G1/100
BL	(0°-30°)	5.3	0.1	B0/110		
BM	(30°-60°)	4.9	0.1	B0/220		
BH	(60°-80°)	9.4	0.2	B0/110		G0/110
BVH	(80°-90°)	0.8	0.0			G0/10
UL	(90°-100°)	0.0	0.0		U0/0	
UH	(100°-180°)	0.0	0.0		U0/0	

BUG Rating: B0-U0-G2

Type III Short



REPORT NUMBER: P1047557

CATALOG NUMBER: GALN-SA2A-940-U-T3BC

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	43°	45°	55°	65°	75°	85°
0°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
2.5°	44.0	45.5	44.0	44.0	44.0	42.6	42.6	41.1	41.1	39.6	38.2
5°	64.6	64.6	60.2	57.2	54.3	52.8	51.4	48.4	45.5	42.6	39.6
7.5°	143.8	143.8	130.6	113.0	89.5	76.3	73.4	60.2	51.4	45.5	39.6
10°	343.4	343.4	314.0	265.6	205.4	152.6	136.5	86.6	61.6	48.4	41.1
12.5°	570.8	578.2	541.5	479.8	390.3	297.9	265.6	158.5	82.2	52.8	41.1
15°	774.8	757.2	746.9	688.2	603.1	493.0	452.0	267.1	118.9	60.2	41.1
17.5°	912.7	912.7	898.0	858.4	780.7	683.8	650.1	431.4	192.2	69.0	42.6
20°	1074.1	1074.1	1047.7	1019.8	950.9	868.7	836.4	613.4	297.9	88.0	42.6
22.5°	1269.3	1272.2	1242.9	1193.0	1127.0	1036.0	1008.1	782.1	431.4	117.4	44.0
25°	1507.0	1510.0	1467.4	1420.4	1319.2	1220.9	1178.3	975.8	594.3	164.3	44.0
27.5°	1769.7	1790.2	1727.1	1646.4	1539.3	1416.0	1383.8	1150.4	755.7	231.8	47.0
30°	2096.9	2096.9	2013.3	1900.3	1784.4	1631.7	1590.7	1333.9	927.4	321.4	49.9
32.5°	2378.7	2356.6	2249.5	2130.7	2007.4	1865.1	1821.0	1526.1	1103.5	432.9	55.8
35°	2594.4	2575.3	2443.2	2315.6	2208.4	2077.8	2025.0	1734.5	1289.8	559.1	64.6
37.5°	2779.3	2771.9	2592.9	2432.9	2362.5	2248.1	2201.1	1931.1	1473.3	695.5	74.8
40°	2981.8	2958.3	2767.5	2569.4	2463.8	2371.3	2328.8	2089.6	1649.4	855.5	89.5
42.5°	3154.9	3127.0	2955.3	2761.6	2581.2	2456.4	2415.3	2223.1	1821.0	1015.4	108.6
45°	3347.1	3332.5	3159.3	3012.6	2771.9	2572.4	2518.1	2330.2	1978.1	1206.2	133.5
47.5°	3636.2	3609.8	3448.4	3328.1	3049.3	2748.4	2670.7	2440.3	2129.2	1394.0	171.7
50°	3972.3	3954.6	3859.3	3763.9	3486.5	3049.3	2956.8	2598.8	2297.9	1617.1	221.6
52.5°	4246.7	4243.7	4255.5	4256.9	4047.1	3555.5	3417.6	2854.1	2491.6	1837.2	292.0
55°	4240.8	4254.0	4383.1	4531.3	4547.5	4246.7	4113.1	3284.0	2744.0	2108.7	390.3
57.5°	4082.3	4072.0	4208.5	4431.5	4588.6	4620.8	4598.8	3951.7	3124.1	2435.9	541.5
58°	4030.9	4022.1	4151.3	4378.7	4559.2	4645.8	4623.8	4102.9	3209.2	2482.8	582.6
60°	3844.6	3846.1	3922.4	4129.3	4309.8	4515.2	4535.7	4534.3	3633.3	2796.9	789.5
62.5°	3598.1	3586.3	3656.8	3825.5	3984.0	4121.9	4157.1	4563.6	4254.0	3196.0	1184.2
65°	3257.6	3240.0	3314.9	3505.6	3675.8	3765.3	3766.8	4170.4	4546.0	3624.5	1747.7
67.5°	2625.2	2610.5	2760.2	3005.2	3267.9	3385.3	3438.1	3618.6	4299.5	3915.0	2070.5
70°	1608.3	1639.1	1847.5	2231.9	2680.9	2896.6	2975.9	3031.6	3661.2	3871.0	1731.5
72.5°	742.5	705.8	883.4	1151.9	1664.0	2143.9	2226.0	2444.7	2902.5	3360.3	1291.3
75°	346.3	333.1	374.2	503.3	754.2	1157.8	1307.5	1951.6	2226.0	2337.6	931.8
77.5°	177.6	179.0	212.8	228.9	311.1	535.6	614.8	1284.0	1631.7	1304.5	625.1
80°	77.8	80.7	82.2	89.5	126.2	206.9	233.3	595.8	1115.2	664.7	341.9
82.5°	49.9	51.4	51.4	51.4	60.2	82.2	93.9	239.2	556.1	330.2	105.7
85°	26.4	26.4	29.3	36.7	42.6	49.9	52.8	76.3	183.4	98.3	24.9
87.5°	14.7	16.1	17.6	22.0	27.9	33.8	36.7	52.8	70.4	67.5	5.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P1047557

CATALOG NUMBER: GALN-SA2A-940-U-T3BC

CANDELA DISTRIBUTION (continued):

	90°	95°	105°	115°	125°	135°	145°	155°	165°	175°	180°
0°	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
2.5°	38.2	36.7	35.2	33.8	32.3	30.8	30.8	30.8	30.8	30.8	30.8
5°	36.7	35.2	33.8	30.8	27.9	26.4	24.9	23.5	23.5	23.5	23.5
7.5°	36.7	35.2	30.8	27.9	24.9	22.0	19.1	19.1	19.1	19.1	19.1
10°	36.7	33.8	29.3	24.9	20.5	17.6	16.1	14.7	14.7	14.7	14.7
12.5°	36.7	32.3	27.9	22.0	17.6	14.7	13.2	11.7	11.7	11.7	11.7
15°	36.7	32.3	26.4	20.5	16.1	11.7	10.3	8.8	8.8	8.8	8.8
17.5°	35.2	30.8	24.9	17.6	13.2	8.8	7.3	5.9	5.9	7.3	7.3
20°	33.8	29.3	22.0	14.7	10.3	7.3	4.4	4.4	4.4	4.4	4.4
22.5°	33.8	29.3	20.5	13.2	8.8	4.4	2.9	2.9	2.9	2.9	4.4
25°	33.8	27.9	17.6	10.3	5.9	2.9	1.5	1.5	1.5	1.5	1.5
27.5°	33.8	27.9	16.1	8.8	4.4	2.9	1.5	0.0	0.0	0.0	0.0
30°	32.3	26.4	14.7	7.3	2.9	1.5	0.0	0.0	0.0	0.0	0.0
32.5°	32.3	24.9	11.7	5.9	2.9	1.5	0.0	0.0	0.0	0.0	0.0
35°	33.8	23.5	10.3	4.4	1.5	0.0	0.0	0.0	0.0	0.0	1.5
37.5°	35.2	22.0	8.8	2.9	1.5	0.0	0.0	0.0	0.0	0.0	0.0
40°	36.7	20.5	8.8	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	39.6	20.5	7.3	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	42.6	20.5	5.9	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	48.4	22.0	5.9	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	52.8	23.5	4.4	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	58.7	22.0	4.4	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	66.0	22.0	4.4	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	71.9	20.5	4.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
58°	74.8	19.1	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	89.5	17.6	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	139.4	14.7	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	283.2	13.2	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	528.3	11.7	2.9	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	591.4	13.2	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	372.7	10.3	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	196.6	10.3	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	98.3	10.3	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	45.5	7.3	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	19.1	4.4	2.9	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0
85°	8.8	4.4	2.9	2.9	1.5	1.5	0.0	0.0	0.0	0.0	0.0
87.5°	4.4	4.4	4.4	2.9	2.9	1.5	1.5	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-16

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-940-U-5WQ

Data in this report applies to families of products including GSS-SB1A-940-U-5WQ


Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-16
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-940-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI
 4000K CCT 26 LEDS

Spectral Parameters

CCT (K): 3856
 CIE u' : 0.2261
 CIE v' : 0.5084
 Duv: 0.0032
 CIE x: 0.3896
 CIE y: 0.3894
 CIE z: 0.2211
 Peak Wavelength (nm): 614
 Dominant Wavelength (nm): 578
 Purity: 33.77304
 R_f: 91.8
 R_g: 98.4

CRI (Ra): 92.1
 R1: 91.8
 R2: 94.1
 R3: 95.3
 R4: 92.8
 R5: 91.0
 R6: 91.6
 R7: 95.0
 R8: 85.2
 R9: 60.7
 R10: 85.2
 R11: 92.4
 R12: 74.5
 R13: 92.3
 R14: 97.0
 R15: 88.5



Test Conditions

Stabilization Time: 23M
 Operation Time: 1H 23M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-16

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	IN0058	6/18/2024	12/18/2024
Power Meter	INXT2011004	2/8/2024	2/8/2025
AC Power Source	IN0063	10/24/2023	10/24/2024
DC Power Source	IN0208	10/24/2023	10/24/2024
Sphere Thermometer	IN0085	10/24/2023	10/24/2024
Room Thermometer	IN0046	10/24/2023	10/24/2024

REPORT NUMBER: SP1-2407-184-16

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 4000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-16

Photopic Flux vs. Wavelength




Photopic Lumens: NR

λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^\wedge/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.72

λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)	λ (nm)	Power W [^] /nm	Lumens (φ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 3.52


λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)	λ (nm)	Power $\text{W}^{\wedge}/\text{nm}$	Lumens (ϕ/nm)
360	0	NR	490	492	NR	620	993	NR	750	73	NR	880	1	NR
365	0	NR	495	539	NR	625	978	NR	755	62	NR	885	1	NR
370	0	NR	500	583	NR	630	962	NR	760	54	NR	890	1	NR
375	0	NR	505	623	NR	635	933	NR	765	46	NR	895	1	NR
380	0	NR	510	661	NR	640	898	NR	770	39	NR	900	1	NR
385	0	NR	515	698	NR	645	855	NR	775	34	NR	905	1	NR
390	0	NR	520	733	NR	650	810	NR	780	29	NR	910	1	NR
395	1	NR	525	764	NR	655	759	NR	785	25	NR	915	1	NR
400	3	NR	530	794	NR	660	704	NR	790	21	NR	920	1	NR
405	6	NR	535	820	NR	665	651	NR	795	18	NR	925	1	NR
410	12	NR	540	837	NR	670	592	NR	800	16	NR	930	1	NR
415	22	NR	545	853	NR	675	538	NR	805	13	NR	935	0	NR
420	42	NR	550	864	NR	680	486	NR	810	12	NR	940	0	NR
425	79	NR	555	872	NR	685	435	NR	815	10	NR	945	0	NR
430	147	NR	560	876	NR	690	389	NR	820	9	NR	950	0	NR
435	278	NR	565	883	NR	695	344	NR	825	7	NR	955	0	NR
440	515	NR	570	891	NR	700	303	NR	830	6	NR	960	0	NR
445	832	NR	575	900	NR	705	266	NR	835	5	NR	965	0	NR
450	874	NR	580	914	NR	710	233	NR	840	5	NR	970	0	NR
455	659	NR	585	927	NR	715	203	NR	845	4	NR	975	0	NR
460	567	NR	590	944	NR	720	178	NR	850	4	NR	980	0	NR
465	485	NR	595	961	NR	725	154	NR	855	3	NR	985	0	NR
470	401	NR	600	975	NR	730	133	NR	860	3	NR	990	0	NR
475	393	NR	605	988	NR	735	115	NR	865	2	NR	995	1	NR
480	417	NR	610	996	NR	740	98	NR	870	2	NR	1000	0	NR
485	448	NR	615	998	NR	745	85	NR	875	2	NR			

REPORT NUMBER: SP1-2407-184-16




TM-30-18

Summary

$R_f = 91.8$
 $R_g = 98.4$
 $CIE R_a = 92.1$
 $R_9 = 60.7$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

CES01 = 86	CES26 = 94	CES51 = 96	CES76 = 87
CES02 = 62	CES27 = 91	CES52 = 98	CES77 = 90
CES03 = 31	CES28 = 96	CES53 = 95	CES78 = 84
CES04 = 69	CES29 = 96	CES54 = 94	CES79 = 96
CES05 = 49	CES30 = 93	CES55 = 92	CES80 = 94
CES06 = 50	CES31 = 97	CES56 = 93	CES81 = 89
CES07 = 42	CES32 = 92	CES57 = 92	CES82 = 97
CES08 = 41	CES33 = 99	CES58 = 92	CES83 = 98
CES09 = 29	CES34 = 94	CES59 = 96	CES84 = 94
CES10 = 74	CES35 = 96	CES60 = 93	CES85 = 85
CES11 = 57	CES36 = 82	CES61 = 92	CES86 = 88
CES12 = 63	CES37 = 95	CES62 = 87	CES87 = 92
CES13 = 43	CES38 = 88	CES63 = 92	CES88 = 96
CES14 = 74	CES39 = 99	CES64 = 89	CES89 = 87
CES15 = 71	CES40 = 98	CES65 = 88	CES90 = 96
CES16 = 47	CES41 = 97	CES66 = 87	CES91 = 74
CES17 = 49	CES42 = 96	CES67 = 86	CES92 = 80
CES18 = 56	CES43 = 96	CES68 = 88	CES93 = 88
CES19 = 71	CES44 = 99	CES69 = 89	CES94 = 82
CES20 = 66	CES45 = 98	CES70 = 86	CES95 = 83
CES21 = 85	CES46 = 97	CES71 = 81	CES96 = 92
CES22 = 78	CES47 = 97	CES72 = 94	CES97 = 95
CES23 = 91	CES48 = 91	CES73 = 81	CES98 = 94
CES24 = 90	CES49 = 96	CES74 = 93	CES99 = 91
CES25 = 71	CES50 = 97	CES75 = 83	



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)