

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1049430

Luminaire Tested: **GALN-SA2B-950-U-RBC**

Issue Date: 07/10/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P1049430  
Test Lab: INNOVATION CENTER(G3)  
Issue Date: 07/10/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SA2B-950-U-RBC  
Description: GALLEON II AREA AND ROADWAY LUMINAIRE 800mA 2xLight Square PACKAGE  
90CRI 5000K FIXTURE w/ RIGHT CORNER BACKLIGHT CONTROL  
Light Source: (28) 5000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6604.9 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B0 - U0 - G2

Input Watts (W): 72.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.97  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 28.75 FT


REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

## Iso-Footcandle Lines of Horizontal Illumination

× Max cd

--- 1/2 Max cd




Based on 20 foot mounting height. Maximum calculated value = 1 fc

Type III - Short - N/A

REPORT NUMBER: P1049430  
CATALOG NUMBER: GALN-SA2B-950-U-RBC

## Luminous Intensity Polar Plot



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total  |
|--------------------|-----------|----------|--------|--------|
| <b>House Side</b>  | Lumens    | 33.1     | 0.0    | 33.1   |
|                    | % Fixture | 0.5      | 0.0    | 0.5    |
| <b>Street Side</b> | Lumens    | 6571.8   | 0.0    | 6571.8 |
|                    | % Fixture | 99.5     | 0.0    | 99.5   |
| <b>Total</b>       | Lumens    | 6604.9   | 0.0    | 6604.9 |
|                    | % Fixture | 100.0    | 0.0    | 100.0  |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 2.6    | 0.0       |
| 10°-20°   | 14.5   | 0.2       |
| 20°-30°   | 156.5  | 2.4       |
| 30°-40°   | 462.9  | 7.0       |
| 40°-50°   | 1379.5 | 20.9      |
| 50°-60°   | 2187.4 | 33.1      |
| 60°-70°   | 1825.9 | 27.6      |
| 70°-80°   | 563.0  | 8.5       |
| 80°-90°   | 12.5   | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-90°    | 6604.9 | 100.0     |
| 0°-180°   | 6604.9 | 100.0     |



REPORT NUMBER: P1049430


CATALOG NUMBER: GALN-SA2B-950-U-RBC

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone |             | Lumens | % Fixture | Zone Rating/Lumen Limit |      |         |
|------|-------------|--------|-----------|-------------------------|------|---------|
|      |             |        |           | B                       | U    | G       |
| FL   | (0°-30°)    | 167.6  | 2.5       |                         |      |         |
| FM   | (30°-60°)   | 4017.9 | 60.8      |                         |      |         |
| FH   | (60°-80°)   | 2376.6 | 36.0      |                         |      | G2/5000 |
| FVH  | (80°-90°)   | 9.7    | 0.1       |                         |      | G0/10   |
| BL   | (0°-30°)    | 6.1    | 0.1       | B0/110                  |      |         |
| BM   | (30°-60°)   | 11.8   | 0.2       | B0/220                  |      |         |
| BH   | (60°-80°)   | 12.3   | 0.2       | B0/110                  |      | G0/110  |
| BVH  | (80°-90°)   | 2.8    | 0.0       |                         |      | G0/10   |
| UL   | (90°-100°)  | 0.0    | 0.0       |                         | U0/0 |         |
| UH   | (100°-180°) | 0.0    | 0.0       |                         | U0/0 |         |

**BUG Rating: B0-U0-G2**

Type III Short



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (FULL):**

|        | 0°     | 2.5°  | 5°    | 7.5°  | 10°   | 12.5° | 15°  | 17.5° | 20°  | 22.5° |
|--------|--------|-------|-------|-------|-------|-------|------|-------|------|-------|
| 0°     | 28.9   | 28.9  | 28.9  | 28.9  | 28.9  | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  |
| 2.5°   | 26.5   | 26.5  | 26.5  | 26.5  | 26.0  | 26.0  | 25.5 | 25.5  | 25.0 | 25.0  |
| 5°     | 28.0   | 28.0  | 27.5  | 27.0  | 27.0  | 26.5  | 26.0 | 25.5  | 25.5 | 25.0  |
| 7.5°   | 30.4   | 29.9  | 29.4  | 28.9  | 28.0  | 27.5  | 26.5 | 26.0  | 25.5 | 24.5  |
| 10°    | 33.4   | 32.4  | 31.4  | 30.4  | 29.4  | 28.5  | 27.5 | 27.0  | 26.0 | 25.5  |
| 12.5°  | 37.4   | 35.9  | 33.9  | 32.4  | 31.4  | 29.9  | 28.9 | 28.0  | 26.5 | 25.5  |
| 15°    | 40.9   | 38.9  | 36.4  | 34.4  | 32.9  | 30.9  | 29.4 | 28.0  | 27.0 | 25.5  |
| 17.5°  | 45.9   | 42.4  | 38.4  | 35.9  | 33.9  | 31.4  | 28.9 | 27.5  | 26.0 | 24.0  |
| 20°    | 54.4   | 47.4  | 39.9  | 36.9  | 33.9  | 30.9  | 28.0 | 26.0  | 24.5 | 22.5  |
| 22.5°  | 67.9   | 55.9  | 43.9  | 39.4  | 35.4  | 30.9  | 27.0 | 25.0  | 23.0 | 21.0  |
| 25°    | 93.8   | 72.4  | 50.9  | 44.9  | 38.9  | 32.9  | 27.0 | 24.5  | 22.5 | 20.0  |
| 27.5°  | 124.8  | 92.8  | 60.4  | 51.9  | 43.9  | 35.4  | 27.0 | 24.0  | 21.5 | 18.5  |
| 30°    | 156.2  | 113.8 | 70.9  | 59.9  | 48.9  | 37.9  | 27.0 | 23.5  | 20.5 | 17.0  |
| 32.5°  | 186.2  | 133.3 | 79.9  | 66.9  | 53.9  | 40.4  | 27.5 | 23.5  | 19.5 | 15.5  |
| 35°    | 216.6  | 149.2 | 81.4  | 67.9  | 54.4  | 40.4  | 27.0 | 22.5  | 18.5 | 14.0  |
| 37.5°  | 255.6  | 167.2 | 78.4  | 64.9  | 51.9  | 38.4  | 25.5 | 21.5  | 17.5 | 13.0  |
| 40°    | 314.4  | 197.2 | 79.9  | 65.9  | 51.9  | 37.9  | 24.0 | 20.0  | 16.5 | 12.5  |
| 42.5°  | 423.3  | 255.1 | 86.3  | 70.4  | 54.4  | 37.9  | 22.0 | 18.5  | 15.5 | 12.0  |
| 45°    | 731.7  | 423.8 | 115.8 | 91.8  | 67.9  | 43.9  | 20.0 | 17.0  | 14.5 | 11.5  |
| 47.5°  | 1210.4 | 709.3 | 208.1 | 160.7 | 113.8 | 66.4  | 19.5 | 17.0  | 14.5 | 11.5  |
| 50°    | 1544.8 | 903.4 | 262.0 | 201.6 | 141.3 | 80.9  | 20.5 | 17.5  | 15.0 | 12.0  |
| 52.5°  | 1542.3 | 917.4 | 292.0 | 224.1 | 156.7 | 88.8  | 21.5 | 18.5  | 16.0 | 13.0  |
| 55°    | 1371.1 | 834.5 | 297.5 | 228.6 | 160.2 | 91.3  | 23.0 | 20.0  | 17.0 | 14.0  |
| 57.5°  | 1146.0 | 708.8 | 271.5 | 210.1 | 149.2 | 87.8  | 26.5 | 23.0  | 20.0 | 16.5  |
| 60°    | 906.4  | 559.0 | 211.6 | 167.2 | 123.3 | 78.9  | 34.9 | 30.4  | 26.5 | 22.0  |
| 62.5°  | 625.9  | 405.3 | 184.7 | 148.2 | 112.3 | 75.9  | 39.9 | 35.4  | 31.4 | 27.0  |
| 65°    | 442.7  | 305.0 | 166.7 | 135.8 | 105.3 | 74.4  | 43.4 | 38.4  | 33.9 | 28.9  |
| 67.5°  | 330.9  | 242.6 | 153.7 | 127.3 | 100.8 | 74.4  | 47.9 | 41.9  | 36.4 | 30.4  |
| 70°    | 253.6  | 199.2 | 144.2 | 122.8 | 101.8 | 80.4  | 58.9 | 50.4  | 42.4 | 33.9  |
| 72.5°  | 206.6  | 170.2 | 133.3 | 117.8 | 102.3 | 86.8  | 71.4 | 60.4  | 49.4 | 37.9  |
| 75°    | 171.2  | 145.7 | 120.3 | 107.3 | 94.8  | 81.9  | 68.9 | 58.9  | 49.4 | 39.4  |
| 77.5°  | 113.8  | 103.8 | 93.3  | 85.8  | 78.4  | 70.4  | 62.9 | 54.4  | 46.4 | 37.9  |
| 80°    | 39.9   | 38.4  | 36.9  | 39.9  | 42.9  | 45.9  | 48.9 | 42.9  | 37.4 | 31.4  |
| 82.5°  | 6.0    | 5.5   | 5.0   | 5.5   | 6.0   | 6.5   | 7.0  | 7.5   | 8.0  | 8.5   |
| 85°    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 87.5°  | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 90°    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 92.5°  | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 95°    | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 97.5°  | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 100°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 102.5° | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 105°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 107.5° | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 110°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 25° |        | 27.5° | 30°  | 32.5° | 35°  | 37.5° | 40°  | 42.5° | 45°  | 47.5° | 50°  |
|-----|--------|-------|------|-------|------|-------|------|-------|------|-------|------|
| 0.0 | 0°     | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 |
| 0.0 | 2.5°   | 24.5  | 24.5 | 24.0  | 24.0 | 24.0  | 23.5 | 23.5  | 23.0 | 23.0  | 23.0 |
| 0.0 | 5°     | 24.0  | 24.0 | 23.5  | 23.0 | 22.5  | 22.5 | 22.0  | 21.5 | 21.5  | 21.0 |
| 0.0 | 7.5°   | 23.5  | 23.0 | 22.5  | 22.0 | 21.5  | 21.0 | 20.5  | 20.0 | 20.0  | 19.5 |
| 0.0 | 10°    | 24.0  | 23.0 | 22.5  | 21.5 | 21.0  | 20.5 | 19.5  | 19.0 | 18.5  | 18.5 |
| 0.0 | 12.5°  | 23.0  | 22.5 | 21.5  | 20.5 | 20.0  | 19.0 | 18.5  | 17.5 | 17.0  | 17.0 |
| 0.0 | 15°    | 23.0  | 22.0 | 20.5  | 19.5 | 18.5  | 18.0 | 17.0  | 16.0 | 15.5  | 15.0 |
| 0.0 | 17.5°  | 21.5  | 20.5 | 19.0  | 18.0 | 17.0  | 16.0 | 15.0  | 14.0 | 13.5  | 13.0 |
| 0.0 | 20°    | 19.5  | 18.5 | 17.0  | 15.5 | 14.5  | 13.5 | 12.5  | 11.5 | 11.0  | 10.5 |
| 0.0 | 22.5°  | 17.5  | 16.5 | 15.0  | 13.5 | 12.5  | 11.5 | 10.0  | 9.0  | 8.5   | 7.5  |
| 0.0 | 25°    | 16.5  | 15.0 | 13.5  | 12.0 | 10.5  | 9.5  | 8.0   | 6.5  | 5.5   | 4.5  |
| 0.0 | 27.5°  | 14.0  | 12.5 | 11.0  | 9.5  | 8.0   | 6.5  | 5.0   | 3.5  | 2.5   | 2.0  |
| 0.0 | 30°    | 12.0  | 10.5 | 9.0   | 7.5  | 5.5   | 4.0  | 2.5   | 0.5  | 0.5   | 0.5  |
| 0.0 | 32.5°  | 10.0  | 8.5  | 6.5   | 5.0  | 4.0   | 2.5  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 35°    | 8.0   | 6.5  | 4.5   | 3.0  | 2.5   | 1.5  | 1.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 37.5°  | 7.0   | 5.5  | 3.5   | 1.5  | 1.0   | 1.0  | 0.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 40°    | 6.5   | 4.5  | 2.5   | 0.5  | 0.5   | 0.5  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 42.5°  | 6.5   | 4.5  | 2.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 45°    | 6.5   | 4.5  | 2.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 47.5°  | 6.5   | 4.5  | 2.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 50°    | 7.0   | 5.0  | 2.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 52.5°  | 8.0   | 6.0  | 4.0   | 2.0  | 1.5   | 1.0  | 0.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 55°    | 10.0  | 9.0  | 7.5   | 6.5  | 5.0   | 3.5  | 1.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 57.5°  | 13.0  | 13.0 | 12.5  | 12.0 | 9.0   | 6.0  | 3.0   | 0.0  | 0.0   | 0.0  |
| 0.0 | 60°    | 17.5  | 17.5 | 17.5  | 17.5 | 13.0  | 9.0  | 4.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 62.5°  | 21.5  | 20.5 | 19.0  | 18.0 | 13.5  | 9.0  | 4.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 65°    | 21.5  | 19.5 | 17.0  | 14.5 | 11.0  | 7.5  | 3.5   | 0.0  | 0.0   | 0.0  |
| 0.0 | 67.5°  | 20.0  | 16.0 | 11.5  | 7.5  | 5.5   | 4.0  | 2.0   | 0.0  | 0.0   | 0.0  |
|     | 70°    | 20.0  | 14.0 | 8.0   | 2.0  | 1.5   | 1.0  | 0.5   | 0.0  | 0.0   | 0.0  |
|     | 72.5°  | 20.0  | 13.5 | 6.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 75°    | 22.0  | 15.0 | 7.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 77.5°  | 22.0  | 15.0 | 7.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 80°    | 19.5  | 13.0 | 6.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 82.5°  | 6.5   | 4.5  | 2.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 52.5° |        | 55°  | 57.5° | 60°  | 62.5° | 65°  | 67.5° | 70°  | 72.5° | 75°  | 77.5° |
|-------|--------|------|-------|------|-------|------|-------|------|-------|------|-------|
| 0.0   | 0°     | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  |
| 0.0   | 2.5°   | 22.5 | 22.5  | 22.5 | 22.0  | 22.0 | 22.0  | 22.0 | 21.5  | 21.5 | 21.5  |
| 0.0   | 5°     | 20.5 | 20.5  | 20.0 | 20.0  | 19.5 | 19.5  | 19.0 | 19.0  | 18.5 | 18.5  |
| 0.0   | 7.5°   | 19.0 | 18.5  | 18.5 | 18.0  | 17.5 | 17.5  | 17.0 | 17.0  | 16.5 | 16.0  |
| 0.0   | 10°    | 17.5 | 17.0  | 17.0 | 16.5  | 16.0 | 15.5  | 15.5 | 15.0  | 14.5 | 14.0  |
| 0.0   | 12.5°  | 16.0 | 15.5  | 15.0 | 14.5  | 14.0 | 13.5  | 13.5 | 13.0  | 12.5 | 12.0  |
| 0.0   | 15°    | 14.0 | 13.5  | 13.0 | 12.5  | 12.0 | 11.5  | 11.5 | 11.0  | 10.5 | 10.0  |
| 0.0   | 17.5°  | 12.0 | 11.5  | 11.5 | 11.0  | 10.5 | 10.0  | 9.5  | 8.5   | 8.0  | 7.5   |
| 0.0   | 20°    | 9.0  | 8.5   | 8.0  | 7.5   | 7.0  | 6.0   | 5.5  | 4.5   | 3.5  | 3.0   |
| 0.0   | 22.5°  | 6.0  | 5.0   | 4.5  | 3.5   | 2.5  | 2.0   | 1.5  | 0.5   | 0.0  | 0.0   |
| 0.0   | 25°    | 2.0  | 1.5   | 1.0  | 0.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 27.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 30°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 32.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 35°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 37.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 40°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 42.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 45°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 47.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 50°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 52.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 55°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 57.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 60°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 62.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 65°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 67.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 70°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 72.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 75°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 77.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 80°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 82.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 85°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 87.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 90°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 92.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 95°    | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 97.5°  | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 100°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 102.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 105°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 107.5° | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |
| 0.0   | 110°   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 80° |        | 82.5° | 85°  | 87.5° | 90°  | 92.5° | 95°  | 97.5° | 100° | 102.5° | 105° |
|-----|--------|-------|------|-------|------|-------|------|-------|------|--------|------|
| 0.0 | 0°     | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9  | 28.9 | 28.9   | 28.9 |
| 0.0 | 2.5°   | 21.0  | 21.0 | 21.0  | 20.5 | 20.5  | 20.5 | 20.5  | 20.5 | 20.5   | 20.5 |
| 0.0 | 5°     | 18.0  | 18.0 | 18.0  | 17.5 | 17.5  | 17.0 | 17.0  | 17.0 | 16.5   | 16.5 |
| 0.0 | 7.5°   | 15.5  | 15.0 | 15.0  | 14.5 | 14.5  | 14.0 | 14.0  | 14.0 | 13.5   | 13.5 |
| 0.0 | 10°    | 13.0  | 12.5 | 12.5  | 12.0 | 12.0  | 11.5 | 11.5  | 11.0 | 11.0   | 10.5 |
| 0.0 | 12.5°  | 11.5  | 11.0 | 10.5  | 10.0 | 10.0  | 9.5  | 9.0   | 9.0  | 8.5    | 8.0  |
| 0.0 | 15°    | 9.0   | 8.5  | 8.0   | 7.5  | 7.0   | 6.5  | 6.0   | 6.0  | 5.5    | 5.0  |
| 0.0 | 17.5°  | 6.0   | 5.0  | 4.5   | 4.0  | 4.0   | 3.5  | 3.0   | 2.5  | 2.0    | 1.5  |
| 0.0 | 20°    | 1.5   | 1.0  | 0.5   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 22.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 25°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 27.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 30°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 32.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 35°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 37.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 40°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 42.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 45°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 47.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 50°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 52.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 55°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 57.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 60°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 62.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 65°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
| 0.0 | 67.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 70°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 72.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 75°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 77.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 80°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 82.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 85°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 87.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 90°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 92.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 95°    | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 97.5°  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 100°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 102.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 105°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 107.5° | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |
|     | 110°   | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0   | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GALN-SA2B-950-U-RBC

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 107.5° |        | 110° | 112.5° | 115° | 117.5° | 120° | 122.5° | 125° | 127.5° | 130° | 132.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   |
| 0.0    | 2.5°   | 20.5 | 20.0   | 20.0 | 20.0   | 20.5 | 20.5   | 20.5 | 20.5   | 20.5 | 20.5   |
| 0.0    | 5°     | 16.5 | 16.0   | 16.0 | 16.0   | 16.0 | 16.0   | 16.0 | 16.0   | 16.0 | 16.0   |
| 0.0    | 7.5°   | 13.5 | 13.0   | 13.0 | 13.0   | 13.0 | 12.5   | 12.5 | 12.5   | 12.5 | 12.5   |
| 0.0    | 10°    | 10.5 | 10.0   | 10.0 | 10.0   | 10.0 | 9.5    | 9.5  | 9.5    | 9.5  | 9.5    |
| 0.0    | 12.5°  | 7.5  | 7.5    | 7.0  | 7.0    | 7.0  | 6.5    | 6.5  | 6.5    | 6.5  | 6.0    |
| 0.0    | 15°    | 4.5  | 4.0    | 3.5  | 3.5    | 3.5  | 3.0    | 3.0  | 3.0    | 3.0  | 2.5    |
| 0.0    | 17.5°  | 1.0  | 1.0    | 0.5  | 0.5    | 0.5  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 20°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 22.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 25°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 87.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 135° |        | 137.5° | 140° | 142.5° | 145° | 147.5° | 150° | 152.5° | 155° | 157.5° | 160° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 |
| 0.0  | 2.5°   | 21.0   | 21.0 | 21.5   | 21.5 | 22.0   | 23.0 | 23.5   | 24.0 | 25.0   | 26.0 |
| 0.0  | 5°     | 16.5   | 17.0 | 17.0   | 17.5 | 18.0   | 18.5 | 19.0   | 19.5 | 20.5   | 21.5 |
| 0.0  | 7.5°   | 13.0   | 13.0 | 13.5   | 13.5 | 14.0   | 15.0 | 15.5   | 16.0 | 17.0   | 18.5 |
| 0.0  | 10°    | 10.0   | 10.0 | 10.5   | 10.5 | 11.0   | 12.0 | 12.5   | 13.0 | 14.0   | 15.5 |
| 0.0  | 12.5°  | 6.5    | 7.0  | 7.0    | 7.5  | 8.0    | 9.0  | 9.5    | 10.0 | 11.0   | 12.0 |
| 0.0  | 15°    | 3.0    | 3.5  | 3.5    | 4.0  | 4.5    | 5.5  | 6.0    | 6.5  | 7.5    | 9.0  |
| 0.0  | 17.5°  | 0.5    | 0.5  | 1.0    | 1.0  | 1.5    | 2.0  | 2.5    | 3.0  | 4.5    | 5.5  |
| 0.0  | 20°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.0    | 2.0  |
| 0.0  | 22.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.5  |
| 0.0  | 25°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 27.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 30°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 82.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 85°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 87.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 162.5° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   |
| 0.0    | 2.5°   | 27.5 | 28.5   | 29.4 | 30.4   | 31.4 | 32.4   | 32.9 | 33.9   | 34.4 | 34.9   |
| 0.0    | 5°     | 23.5 | 24.5   | 26.0 | 27.0   | 28.0 | 28.9   | 29.9 | 30.4   | 30.9 | 31.4   |
| 0.0    | 7.5°   | 20.5 | 21.5   | 23.0 | 24.0   | 25.0 | 26.0   | 27.0 | 28.0   | 28.5 | 28.9   |
| 0.0    | 10°    | 17.5 | 19.0   | 20.0 | 21.5   | 22.5 | 23.5   | 24.5 | 25.5   | 26.5 | 27.0   |
| 0.0    | 12.5°  | 14.0 | 15.5   | 17.0 | 18.0   | 19.5 | 21.0   | 22.0 | 23.0   | 24.0 | 25.0   |
| 0.0    | 15°    | 11.0 | 12.5   | 14.0 | 15.0   | 16.5 | 18.0   | 19.5 | 20.5   | 21.5 | 22.5   |
| 0.0    | 17.5°  | 8.0  | 9.5    | 11.0 | 12.0   | 13.5 | 15.0   | 16.0 | 17.5   | 18.5 | 19.5   |
| 0.0    | 20°    | 4.0  | 5.5    | 7.0  | 8.5    | 10.0 | 11.5   | 12.5 | 14.0   | 15.0 | 16.0   |
| 0.0    | 22.5°  | 0.5  | 2.0    | 3.5  | 4.5    | 6.0  | 7.5    | 8.5  | 10.0   | 11.0 | 12.0   |
| 0.0    | 25°    | 0.0  | 0.5    | 1.5  | 2.0    | 2.5  | 3.5    | 4.5  | 5.5    | 6.5  | 7.5    |
| 0.0    | 27.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.5    | 1.0  | 2.0    | 3.0  | 4.0    |
| 0.0    | 30°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.0    |
| 0.0    | 32.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 35°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 37.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 40°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 42.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 45°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 47.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 50°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 52.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 55°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 70°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 75°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 80°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.5    |
|        | 82.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.5    | 0.5  | 1.0    |
|        | 85°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 1.0    | 1.5  | 2.5    | 3.0  | 3.5    |
|        | 87.5°  | 0.0  | 0.5    | 1.0  | 1.5    | 2.0  | 3.0    | 4.0  | 5.0    | 5.5  | 6.0    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 165° | 167.5° | 170° | 172.5° | 175° | 177.5° | 180° | 182.5° | 185° | 187.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 28.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34.9 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31.9 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29.4 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.0 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 25.5 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23.5 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 21.0 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17.0 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 13.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9.0  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5.0  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1.5  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.5  |        |      |        |      |        |      |        |      |        |      |        |
| 2.0  |        |      |        |      |        |      |        |      |        |      |        |
| 4.5  |        |      |        |      |        |      |        |      |        |      |        |
| 6.5  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 190° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 0.0  | 0°     | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 |
| 0.0  | 2.5°   | 35.4   | 35.4 | 35.4   | 35.4 | 34.9   | 34.9 | 34.9   | 34.4 | 34.4   | 33.9 |
| 0.0  | 5°     | 32.4   | 32.9 | 32.9   | 32.9 | 32.9   | 32.9 | 32.9   | 32.9 | 32.4   | 32.4 |
| 0.0  | 7.5°   | 29.9   | 30.4 | 30.9   | 30.9 | 31.4   | 31.4 | 31.4   | 30.9 | 30.9   | 30.4 |
| 0.0  | 10°    | 28.5   | 28.9 | 28.9   | 29.4 | 29.4   | 29.4 | 29.4   | 29.4 | 29.4   | 29.4 |
| 0.0  | 12.5°  | 26.5   | 27.0 | 27.5   | 27.5 | 28.0   | 28.0 | 28.0   | 28.0 | 27.5   | 27.5 |
| 0.0  | 15°    | 24.0   | 25.0 | 25.5   | 26.0 | 26.0   | 26.5 | 26.5   | 26.5 | 26.5   | 26.5 |
| 0.0  | 17.5°  | 22.0   | 23.0 | 23.5   | 24.0 | 24.0   | 24.5 | 24.5   | 25.0 | 25.0   | 25.0 |
| 0.0  | 20°    | 18.0   | 19.0 | 19.5   | 20.5 | 21.0   | 21.5 | 22.0   | 22.5 | 22.5   | 23.0 |
| 0.0  | 22.5°  | 14.0   | 15.0 | 15.5   | 16.5 | 17.0   | 17.5 | 18.0   | 18.5 | 19.0   | 19.5 |
| 0.0  | 25°    | 10.0   | 11.0 | 11.5   | 12.5 | 13.0   | 13.5 | 14.0   | 14.5 | 14.5   | 15.0 |
| 0.0  | 27.5°  | 5.5    | 6.5  | 7.5    | 8.0  | 9.0    | 9.5  | 10.0   | 10.5 | 11.0   | 11.5 |
| 0.0  | 30°    | 2.5    | 3.0  | 3.5    | 4.5  | 5.0    | 5.5  | 6.0    | 7.0  | 7.5    | 8.0  |
| 0.0  | 32.5°  | 0.0    | 0.0  | 0.5    | 1.5  | 2.0    | 2.5  | 3.0    | 3.5  | 3.5    | 4.0  |
| 0.0  | 35°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.5    | 1.0  | 1.5    | 2.0  |
| 0.0  | 37.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 40°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 42.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 45°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 47.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 50°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 52.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 55°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 57.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 60°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 62.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 65°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0  | 67.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 70°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 72.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 75°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 77.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 80°    | 1.0    | 1.0  | 1.0    | 1.5  | 1.5    | 1.5  | 1.5    | 1.5  | 1.5    | 1.5  |
|      | 82.5°  | 2.5    | 3.0  | 3.5    | 3.5  | 4.0    | 4.0  | 4.0    | 4.0  | 3.5    | 3.5  |
|      | 85°    | 5.0    | 5.5  | 6.0    | 6.0  | 6.5    | 6.5  | 6.5    | 6.5  | 6.5    | 6.5  |
|      | 87.5°  | 7.0    | 7.5  | 8.0    | 8.0  | 8.5    | 8.5  | 8.5    | 8.5  | 8.5    | 8.5  |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 192.5° | 195° | 197.5° | 200° | 202.5° | 205° | 207.5° | 210° | 212.5° | 215° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 28.9   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33.9   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32.4   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30.4   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29.4   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27.5   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 26.5   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 25.0   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 22.5   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 19.5   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 15.5   | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 12.0   | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 8.5    | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 5.0    | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 3.0    | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.0    | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1.0    | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.5    | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.5    | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.5    | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.5    | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.5    | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 1.5    |        |        |      |        |      |        |      |        |      |        |      |
| 3.5    |        |        |      |        |      |        |      |        |      |        |      |
| 6.5    |        |        |      |        |      |        |      |        |      |        |      |
| 8.5    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 217.5° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|--------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 0.0    | 0°     | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   |
| 0.0    | 2.5°   | 33.4 | 33.4   | 32.9 | 32.9   | 32.9 | 32.9   | 32.9 | 33.4   | 33.9 | 33.9   |
| 0.0    | 5°     | 31.9 | 31.9   | 31.4 | 31.4   | 31.4 | 31.9   | 31.9 | 32.4   | 32.9 | 33.4   |
| 0.0    | 7.5°   | 30.4 | 29.9   | 29.9 | 30.4   | 30.4 | 30.9   | 30.9 | 31.4   | 31.9 | 32.4   |
| 0.0    | 10°    | 29.4 | 28.9   | 28.9 | 28.9   | 29.4 | 29.4   | 29.9 | 30.4   | 30.9 | 31.4   |
| 0.0    | 12.5°  | 27.5 | 27.5   | 27.5 | 27.5   | 28.0 | 28.0   | 28.5 | 28.9   | 29.9 | 30.4   |
| 0.0    | 15°    | 26.5 | 26.0   | 26.0 | 26.0   | 26.0 | 26.5   | 26.5 | 27.5   | 28.5 | 28.9   |
| 0.0    | 17.5°  | 24.5 | 24.5   | 24.0 | 24.0   | 24.5 | 24.5   | 25.0 | 26.0   | 27.0 | 27.5   |
| 0.0    | 20°    | 22.5 | 22.0   | 21.5 | 21.5   | 22.0 | 22.0   | 22.5 | 23.5   | 24.5 | 25.0   |
| 0.0    | 22.5°  | 19.5 | 19.0   | 19.0 | 19.0   | 19.0 | 19.5   | 19.5 | 20.5   | 22.0 | 23.0   |
| 0.0    | 25°    | 15.5 | 16.0   | 16.0 | 16.5   | 16.5 | 17.0   | 17.5 | 18.5   | 20.0 | 21.0   |
| 0.0    | 27.5°  | 12.0 | 12.5   | 12.5 | 13.5   | 14.0 | 14.5   | 15.0 | 16.5   | 18.0 | 19.0   |
| 0.0    | 30°    | 9.0  | 9.5    | 10.0 | 10.5   | 11.5 | 12.5   | 13.5 | 15.0   | 16.5 | 17.5   |
| 0.0    | 32.5°  | 5.5  | 6.5    | 7.0  | 8.0    | 9.0  | 10.0   | 11.0 | 12.5   | 14.5 | 16.0   |
| 0.0    | 35°    | 4.0  | 4.5    | 5.5  | 6.0    | 7.0  | 8.0    | 9.0  | 11.0   | 12.5 | 14.5   |
| 0.0    | 37.5°  | 2.0  | 3.0    | 4.0  | 5.0    | 6.0  | 7.0    | 8.0  | 10.0   | 12.0 | 13.5   |
| 0.0    | 40°    | 1.5  | 2.5    | 3.0  | 4.0    | 5.5  | 6.5    | 7.5  | 9.5    | 11.5 | 13.5   |
| 0.0    | 42.5°  | 1.0  | 1.5    | 2.0  | 3.5    | 4.5  | 6.0    | 7.5  | 9.5    | 11.5 | 13.5   |
| 0.0    | 45°    | 1.0  | 1.0    | 1.5  | 3.0    | 4.5  | 6.5    | 8.0  | 10.0   | 11.5 | 13.5   |
| 0.0    | 47.5°  | 1.0  | 1.5    | 2.0  | 4.0    | 5.0  | 6.5    | 8.0  | 9.5    | 11.5 | 13.0   |
| 0.0    | 50°    | 1.5  | 2.0    | 2.5  | 4.5    | 5.5  | 7.0    | 8.0  | 10.0   | 11.5 | 13.5   |
| 0.0    | 52.5°  | 1.0  | 1.5    | 2.0  | 4.0    | 5.5  | 7.5    | 9.0  | 11.0   | 13.0 | 14.5   |
| 0.0    | 55°    | 0.5  | 0.5    | 0.5  | 3.0    | 6.0  | 8.5    | 11.5 | 13.0   | 15.0 | 16.5   |
| 0.0    | 57.5°  | 0.0  | 0.0    | 0.0  | 2.0    | 6.0  | 9.5    | 13.0 | 15.0   | 17.0 | 18.5   |
| 0.0    | 60°    | 0.0  | 0.0    | 0.0  | 2.0    | 6.0  | 9.5    | 13.0 | 15.5   | 18.0 | 20.5   |
| 0.0    | 62.5°  | 0.0  | 0.0    | 0.0  | 2.0    | 5.0  | 8.0    | 11.0 | 15.0   | 19.5 | 23.5   |
| 0.0    | 65°    | 0.0  | 0.0    | 0.0  | 1.5    | 4.0  | 6.5    | 9.0  | 15.0   | 21.0 | 26.5   |
| 0.0    | 67.5°  | 0.0  | 0.0    | 0.0  | 1.5    | 4.0  | 6.0    | 8.5  | 15.0   | 21.0 | 27.5   |
|        | 70°    | 0.0  | 0.0    | 0.0  | 1.5    | 4.0  | 6.5    | 9.0  | 15.0   | 21.0 | 27.0   |
|        | 72.5°  | 0.0  | 0.0    | 0.0  | 1.5    | 4.5  | 7.0    | 10.0 | 15.0   | 20.0 | 25.0   |
|        | 75°    | 0.0  | 0.0    | 0.0  | 2.0    | 4.5  | 7.5    | 10.5 | 15.0   | 19.5 | 23.5   |
|        | 77.5°  | 0.0  | 0.0    | 0.0  | 1.5    | 4.5  | 7.0    | 10.0 | 14.5   | 19.0 | 23.0   |
|        | 80°    | 1.5  | 1.0    | 1.0  | 2.5    | 4.5  | 6.5    | 8.5  | 13.0   | 18.0 | 22.5   |
|        | 82.5°  | 3.0  | 3.0    | 2.5  | 3.5    | 4.5  | 6.0    | 7.5  | 11.5   | 16.0 | 20.0   |
|        | 85°    | 6.0  | 6.0    | 5.5  | 6.0    | 6.0  | 6.5    | 7.0  | 9.0    | 11.0 | 13.0   |
|        | 87.5°  | 8.0  | 8.0    | 7.5  | 7.5    | 7.5  | 7.0    | 7.0  | 7.0    | 7.0  | 6.5    |
|        | 90°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 92.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 95°    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 97.5°  | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 100°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 102.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 105°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 107.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
|        | 110°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 220° | 222.5° | 225° | 227.5° | 230° | 232.5° | 235° | 237.5° | 240° | 242.5° |
|------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 28.9 | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 34.4 | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 33.9 | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.9 | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 31.9 | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 30.9 | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 29.9 | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 28.5 | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 26.0 | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 24.0 | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 22.0 | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20.5 | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 19.0 | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 17.5 | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16.0 | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.5 | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.5 | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.5 | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.0 | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 14.5 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 15.0 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 16.5 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 18.0 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 20.5 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 23.0 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 27.5 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.4 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 33.4 | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.9 |        |      |        |      |        |      |        |      |        |      |        |
| 29.9 |        |      |        |      |        |      |        |      |        |      |        |
| 28.0 |        |      |        |      |        |      |        |      |        |      |        |
| 27.5 |        |      |        |      |        |      |        |      |        |      |        |
| 27.0 |        |      |        |      |        |      |        |      |        |      |        |
| 24.0 |        |      |        |      |        |      |        |      |        |      |        |
| 15.0 |        |      |        |      |        |      |        |      |        |      |        |
| 6.5  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |
| 0.0  |        |      |        |      |        |      |        |      |        |      |        |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 245° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265°  | 267.5° | 270°  |
|------|--------|--------|------|--------|------|--------|------|--------|-------|--------|-------|
| 0.0  | 0°     | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9 | 28.9   | 28.9  | 28.9   | 28.9  |
| 0.0  | 2.5°   | 34.9   | 35.4 | 35.4   | 35.9 | 36.4   | 36.9 | 36.9   | 37.4  | 37.4   | 37.4  |
| 0.0  | 5°     | 34.4   | 35.4 | 35.9   | 36.4 | 36.9   | 37.4 | 37.9   | 38.4  | 38.9   | 38.9  |
| 0.0  | 7.5°   | 33.9   | 34.4 | 35.4   | 35.9 | 36.9   | 37.4 | 38.4   | 38.9  | 39.4   | 39.9  |
| 0.0  | 10°    | 32.9   | 33.9 | 34.9   | 35.9 | 36.9   | 37.9 | 38.9   | 39.9  | 40.9   | 41.4  |
| 0.0  | 12.5°  | 31.9   | 33.4 | 34.4   | 35.4 | 36.9   | 38.4 | 39.4   | 40.9  | 41.9   | 42.9  |
| 0.0  | 15°    | 31.4   | 32.4 | 33.9   | 34.9 | 36.9   | 38.9 | 40.4   | 42.4  | 44.4   | 45.9  |
| 0.0  | 17.5°  | 29.9   | 31.9 | 33.4   | 34.9 | 36.9   | 39.4 | 41.4   | 43.4  | 46.4   | 49.4  |
| 0.0  | 20°    | 28.0   | 29.4 | 31.4   | 32.9 | 35.9   | 38.4 | 41.4   | 43.9  | 48.4   | 52.9  |
| 0.0  | 22.5°  | 26.0   | 28.0 | 29.4   | 31.4 | 34.9   | 37.9 | 41.4   | 44.4  | 51.9   | 58.9  |
| 0.0  | 25°    | 24.0   | 26.5 | 28.5   | 30.4 | 34.4   | 38.4 | 42.4   | 46.4  | 58.9   | 71.4  |
| 0.0  | 27.5°  | 23.0   | 25.0 | 27.5   | 29.4 | 34.4   | 39.9 | 44.9   | 49.9  | 69.9   | 89.3  |
| 0.0  | 30°    | 21.5   | 24.0 | 26.0   | 28.5 | 34.9   | 41.4 | 47.9   | 54.4  | 84.9   | 115.3 |
| 0.0  | 32.5°  | 20.0   | 22.5 | 25.0   | 27.5 | 35.9   | 44.4 | 52.4   | 60.9  | 100.8  | 140.3 |
| 0.0  | 35°    | 18.5   | 21.5 | 24.0   | 26.5 | 37.4   | 48.9 | 59.9   | 70.9  | 115.3  | 159.2 |
| 0.0  | 37.5°  | 18.0   | 21.0 | 23.5   | 26.0 | 37.9   | 49.4 | 61.4   | 72.9  | 116.8  | 160.7 |
| 0.0  | 40°    | 18.5   | 21.0 | 24.0   | 26.5 | 36.4   | 46.4 | 55.9   | 65.9  | 111.8  | 157.2 |
| 0.0  | 42.5°  | 18.5   | 21.5 | 24.5   | 27.5 | 35.4   | 43.4 | 51.4   | 59.4  | 110.3  | 161.2 |
| 0.0  | 45°    | 18.0   | 21.0 | 24.0   | 27.0 | 34.4   | 41.4 | 48.9   | 55.9  | 119.3  | 182.2 |
| 0.0  | 47.5°  | 17.5   | 20.5 | 23.5   | 26.5 | 33.9   | 41.4 | 48.9   | 56.4  | 154.2  | 251.6 |
| 0.0  | 50°    | 17.5   | 20.5 | 23.0   | 25.5 | 34.4   | 43.9 | 52.9   | 61.9  | 224.6  | 386.8 |
| 0.0  | 52.5°  | 18.5   | 21.0 | 23.0   | 25.0 | 35.4   | 46.4 | 56.9   | 67.4  | 285.5  | 503.1 |
| 0.0  | 55°    | 20.0   | 21.5 | 23.5   | 25.0 | 37.9   | 50.4 | 63.4   | 75.9  | 304.0  | 532.1 |
| 0.0  | 57.5°  | 22.0   | 23.5 | 25.0   | 26.5 | 42.4   | 58.4 | 73.9   | 89.8  | 305.5  | 520.6 |
| 0.0  | 60°    | 24.5   | 26.5 | 28.0   | 29.4 | 46.4   | 63.9 | 80.9   | 97.8  | 276.5  | 454.7 |
| 0.0  | 62.5°  | 29.9   | 32.4 | 34.4   | 36.9 | 53.4   | 69.4 | 85.8   | 101.8 | 229.6  | 357.4 |
| 0.0  | 65°    | 34.4   | 36.4 | 38.4   | 40.4 | 56.4   | 72.9 | 88.8   | 104.8 | 194.7  | 284.5 |
| 0.0  | 67.5°  | 35.4   | 37.4 | 38.9   | 40.9 | 57.4   | 73.9 | 89.8   | 106.3 | 166.7  | 226.6 |
|      | 70°    | 35.9   | 38.4 | 41.4   | 43.9 | 60.9   | 77.9 | 94.3   | 111.3 | 147.7  | 184.2 |
|      | 72.5°  | 34.4   | 39.4 | 43.9   | 48.4 | 64.4   | 79.9 | 95.8   | 111.3 | 137.3  | 163.2 |
|      | 75°    | 34.4   | 41.4 | 47.9   | 54.4 | 66.4   | 77.9 | 89.8   | 101.3 | 121.3  | 141.3 |
|      | 77.5°  | 36.4   | 45.4 | 54.4   | 63.4 | 70.4   | 76.9 | 83.9   | 90.3  | 103.3  | 116.3 |
|      | 80°    | 36.4   | 45.9 | 54.9   | 64.4 | 67.4   | 70.9 | 73.9   | 76.9  | 78.4   | 79.9  |
|      | 82.5°  | 31.4   | 38.9 | 46.4   | 53.9 | 50.4   | 46.9 | 43.4   | 39.9  | 37.4   | 34.4  |
|      | 85°    | 16.0   | 17.5 | 18.5   | 19.5 | 18.0   | 16.5 | 15.0   | 13.5  | 12.5   | 11.0  |
|      | 87.5°  | 6.5    | 6.5  | 6.0    | 6.0  | 6.0    | 6.0  | 5.5    | 5.5   | 5.5    | 5.5   |
|      | 90°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 92.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 95°    | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 97.5°  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 100°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 102.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 105°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 107.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |
|      | 110°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0   | 0.0    | 0.0   |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 247.5° | 250° | 252.5° | 255° | 257.5° | 260° | 262.5° | 265° | 267.5° | 270° |
|--------|--------|--------|------|--------|------|--------|------|--------|------|--------|------|
| 28.9   | 112.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37.4   | 115°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 38.9   | 117.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40.4   | 120°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.4   | 122.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 44.4   | 125°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 48.4   | 127.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 53.4   | 130°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 61.4   | 132.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 78.4   | 135°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 106.3  | 137.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 147.7  | 140°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 200.1  | 142.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 250.1  | 145°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 284.0  | 147.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 309.5  | 150°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 334.9  | 152.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 384.8  | 155°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 484.6  | 157.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 738.7  | 160°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1131.5 | 162.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1424.5 | 165°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1456.9 | 167.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1314.7 | 170°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 1124.0 | 172.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 878.5  | 175°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 663.8  | 177.5° | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 490.1  | 180°   | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 346.9  |        |        |      |        |      |        |      |        |      |        |      |
| 258.0  |        |        |      |        |      |        |      |        |      |        |      |
| 187.7  |        |        |      |        |      |        |      |        |      |        |      |
| 141.3  |        |        |      |        |      |        |      |        |      |        |      |
| 79.4   |        |        |      |        |      |        |      |        |      |        |      |
| 35.9   |        |        |      |        |      |        |      |        |      |        |      |
| 10.5   |        |        |      |        |      |        |      |        |      |        |      |
| 5.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |
| 0.0    |        |        |      |        |      |        |      |        |      |        |      |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 272.5° |        | 275°   | 277.5° | 280°   | 282.5° | 285°   | 287.5° | 290°   | 292.5° | 295°    | 297.5°  |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|---------|---------|
| 0.0    | 0°     | 28.9   | 28.9   | 28.9   | 28.9   | 28.9   | 28.9   | 28.9   | 28.9   | 28.9    | 28.9    |
| 0.0    | 2.5°   | 37.4   | 36.9   | 36.9   | 36.4   | 35.9   | 35.4   | 34.9   | 34.4   | 33.9    | 33.4    |
| 0.0    | 5°     | 38.9   | 38.9   | 38.9   | 38.4   | 38.4   | 37.9   | 37.9   | 37.4   | 36.9    | 36.4    |
| 0.0    | 7.5°   | 40.4   | 40.9   | 40.9   | 41.4   | 41.4   | 41.4   | 41.4   | 40.9   | 40.9    | 40.9    |
| 0.0    | 10°    | 42.9   | 43.4   | 43.9   | 44.4   | 44.9   | 45.4   | 45.4   | 45.9   | 45.9    | 45.9    |
| 0.0    | 12.5°  | 45.9   | 47.4   | 48.4   | 49.9   | 50.9   | 52.4   | 53.4   | 54.9   | 55.9    | 56.9    |
| 0.0    | 15°    | 50.4   | 52.9   | 55.9   | 58.4   | 60.9   | 64.4   | 68.4   | 71.9   | 75.4    | 80.9    |
| 0.0    | 17.5°  | 56.9   | 64.9   | 72.9   | 80.4   | 88.3   | 105.8  | 123.3  | 140.3  | 157.7   | 183.2   |
| 0.0    | 20°    | 69.4   | 93.3   | 116.8  | 140.8  | 164.2  | 225.6  | 286.5  | 347.9  | 408.8   | 474.2   |
| 0.0    | 22.5°  | 97.3   | 156.2  | 215.1  | 274.0  | 332.9  | 461.2  | 589.0  | 717.2  | 845.0   | 995.3   |
| 0.0    | 25°    | 141.3  | 249.6  | 357.9  | 465.7  | 574.0  | 774.6  | 975.8  | 1176.4 | 1377.1  | 1572.2  |
| 0.0    | 27.5°  | 205.6  | 371.3  | 537.1  | 702.3  | 868.0  | 1140.0 | 1412.5 | 1684.5 | 1956.6  | 2177.2  |
| 0.0    | 30°    | 285.0  | 509.6  | 734.2  | 958.8  | 1183.4 | 1492.9 | 1802.3 | 2111.3 | 2420.8  | 2661.8  |
| 0.0    | 32.5°  | 359.9  | 634.9  | 909.9  | 1184.4 | 1459.4 | 1811.8 | 2164.7 | 2517.1 | 2869.5  | 3133.0  |
| 0.0    | 35°    | 408.8  | 741.2  | 1074.1 | 1406.5 | 1738.9 | 2120.3 | 2501.6 | 2882.4 | 3263.8  | 3564.7  |
| 0.0    | 37.5°  | 457.7  | 841.5  | 1224.9 | 1608.7 | 1992.0 | 2410.8 | 2829.5 | 3248.3 | 3667.1  | 4038.9  |
| 0.0    | 40°    | 512.6  | 962.8  | 1412.5 | 1862.7 | 2312.4 | 2808.6 | 3304.2 | 3800.3 | 4296.0  | 4820.5  |
| 0.0    | 42.5°  | 607.9  | 1164.0 | 1720.5 | 2276.5 | 2832.5 | 3488.9 | 4145.2 | 4801.1 | 5457.4  | 6206.1  |
| 0.0    | 45°    | 787.1  | 1570.7 | 2354.9 | 3138.5 | 3922.1 | 4791.6 | 5661.6 | 6531.0 | 7400.5  | 8396.8  |
| 0.0    | 47.5°  | 1225.8 | 2304.0 | 3381.6 | 4459.7 | 5537.3 | 6476.1 | 7414.5 | 8353.3 | 9291.7  | 10284.0 |
| 0.0    | 50°    | 1875.7 | 3130.5 | 4385.3 | 5639.6 | 6894.4 | 7743.9 | 8592.9 | 9442.4 | 10291.4 | 11235.3 |
| 0.0    | 52.5°  | 2345.9 | 3653.1 | 4960.8 | 6268.0 | 7575.2 | 8341.9 | 9109.0 | 9875.7 | 10642.3 | 11524.3 |
| 0.0    | 55°    | 2381.3 | 3681.0 | 4981.3 | 6281.0 | 7580.7 | 8350.8 | 9121.0 | 9891.1 | 10661.3 | 11596.1 |
| 0.0    | 57.5°  | 2108.3 | 3397.5 | 4686.3 | 5975.5 | 7264.3 | 8141.2 | 9017.7 | 9894.6 | 10771.1 | 11781.8 |
| 0.0    | 60°    | 1793.4 | 3083.1 | 4372.3 | 5662.1 | 6951.3 | 7961.5 | 8972.3 | 9982.5 | 10992.7 | 11939.5 |
| 0.0    | 62.5°  | 1399.0 | 2725.7 | 4052.9 | 5379.6 | 6706.2 | 7731.9 | 8757.6 | 9782.8 | 10808.5 | 11518.8 |
| 0.0    | 65°    | 1042.7 | 2330.9 | 3619.1 | 4906.9 | 6195.1 | 7016.7 | 7838.2 | 8659.3 | 9480.9  | 9920.6  |
| 0.0    | 67.5°  | 753.7  | 1864.7 | 2975.3 | 4086.3 | 5196.9 | 5784.8 | 6372.8 | 6960.3 | 7548.3  | 7884.7  |
|        | 70°    | 509.6  | 1279.3 | 2048.4 | 2818.1 | 3587.2 | 4070.4 | 4554.0 | 5037.2 | 5520.3  | 5974.5  |
|        | 72.5°  | 352.9  | 785.1  | 1217.9 | 1650.1 | 2082.3 | 2568.5 | 3054.1 | 3540.3 | 4025.9  | 4506.6  |
|        | 75°    | 234.1  | 430.7  | 627.9  | 824.6  | 1021.2 | 1381.1 | 1741.4 | 2101.3 | 2461.2  | 2747.7  |
|        | 77.5°  | 166.2  | 225.1  | 284.5  | 343.4  | 402.3  | 469.7  | 537.6  | 604.9  | 672.3   | 774.6   |
|        | 80°    | 78.9   | 86.3   | 93.8   | 100.8  | 108.3  | 132.8  | 157.2  | 181.7  | 206.1   | 232.1   |
|        | 82.5°  | 37.4   | 40.4   | 43.4   | 45.9   | 48.9   | 51.4   | 53.9   | 56.4   | 58.9    | 56.4    |
|        | 85°    | 10.0   | 10.0   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5   | 10.5    | 10.0    |
|        | 87.5°  | 4.5    | 4.5    | 4.5    | 4.5    | 4.5    | 4.5    | 4.5    | 4.0    | 4.0     | 3.5     |
|        | 90°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 92.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 95°    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 97.5°  | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 100°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 102.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 105°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 107.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |
|        | 110°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0     | 0.0     |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300°    |        | 275° | 277.5° | 280° | 282.5° | 285° | 287.5° | 290° | 292.5° | 295° | 297.5° |
|---------|--------|------|--------|------|--------|------|--------|------|--------|------|--------|
| 28.9    | 112.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 32.9    | 115°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 35.9    | 117.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 40.4    | 120°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 46.4    | 122.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 57.4    | 125°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 86.8    | 127.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 208.1   | 130°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 540.1   | 132.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1145.5  | 135°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 1767.4  | 137.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2397.8  | 140°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 2903.4  | 142.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3397.0  | 145°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 3865.7  | 147.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 4411.3  | 150°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 5345.1  | 152.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6954.8  | 155°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 9393.0  | 157.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 11276.2 | 160°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12179.1 | 162.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12406.2 | 165°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12531.5 | 167.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12792.5 | 170°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12885.9 | 172.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 12229.5 | 175°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 10360.8 | 177.5° | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 8221.6  | 180°   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  | 0.0    |
| 6428.2  |        |      |        |      |        |      |        |      |        |      |        |
| 4987.2  |        |      |        |      |        |      |        |      |        |      |        |
| 3034.2  |        |      |        |      |        |      |        |      |        |      |        |
| 877.0   |        |      |        |      |        |      |        |      |        |      |        |
| 258.0   |        |      |        |      |        |      |        |      |        |      |        |
| 53.4    |        |      |        |      |        |      |        |      |        |      |        |
| 9.5     |        |      |        |      |        |      |        |      |        |      |        |
| 3.5     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |
| 0.0     |        |      |        |      |        |      |        |      |        |      |        |

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 300° |        | 302.5°  | 305°    | 307.5°  | 310°    | 312.5°  | 315°    | 317.5°  | 320°    | 322.5°  |
|------|--------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0.0  | 0°     | 28.9    | 28.9    | 28.9    | 28.9    | 28.9    | 28.9    | 28.9    | 28.9    | 28.9    |
| 0.0  | 2.5°   | 32.4    | 31.9    | 31.4    | 30.9    | 30.4    | 29.4    | 29.4    | 28.9    | 28.9    |
| 0.0  | 5°     | 35.4    | 34.9    | 34.4    | 33.9    | 33.9    | 33.4    | 32.9    | 32.9    | 32.4    |
| 0.0  | 7.5°   | 40.4    | 39.9    | 39.4    | 38.9    | 38.9    | 38.4    | 38.4    | 37.9    | 37.9    |
| 0.0  | 10°    | 46.4    | 46.4    | 46.4    | 46.4    | 46.4    | 45.9    | 45.9    | 45.9    | 45.4    |
| 0.0  | 12.5°  | 58.4    | 58.9    | 59.9    | 60.9    | 62.4    | 62.4    | 62.4    | 61.9    | 61.9    |
| 0.0  | 15°    | 92.3    | 97.8    | 101.8   | 105.8   | 109.3   | 117.3   | 116.3   | 114.8   | 113.8   |
| 0.0  | 17.5°  | 233.6   | 258.5   | 272.0   | 285.0   | 298.5   | 335.4   | 329.4   | 323.4   | 317.9   |
| 0.0  | 20°    | 605.4   | 670.8   | 714.2   | 757.7   | 801.6   | 871.0   | 854.0   | 837.0   | 820.1   |
| 0.0  | 22.5°  | 1295.2  | 1445.5  | 1510.8  | 1576.2  | 1641.1  | 1725.0  | 1670.6  | 1616.2  | 1562.3  |
| 0.0  | 25°    | 1962.1  | 2157.2  | 2267.5  | 2377.8  | 2487.6  | 2535.6  | 2464.7  | 2393.3  | 2322.4  |
| 0.0  | 27.5°  | 2618.4  | 2839.0  | 2936.3  | 3033.2  | 3130.5  | 3230.8  | 3143.0  | 3054.6  | 2966.8  |
| 0.0  | 30°    | 3144.5  | 3385.6  | 3490.9  | 3595.7  | 3701.0  | 3770.9  | 3680.0  | 3588.7  | 3497.9  |
| 0.0  | 32.5°  | 3660.6  | 3924.1  | 4039.4  | 4154.7  | 4269.5  | 4369.8  | 4258.0  | 4145.7  | 4033.9  |
| 0.0  | 35°    | 4166.2  | 4467.2  | 4625.9  | 4784.6  | 4943.3  | 5036.7  | 4903.9  | 4770.6  | 4637.9  |
| 0.0  | 37.5°  | 4783.1  | 5155.0  | 5332.6  | 5510.3  | 5688.0  | 5858.2  | 5712.0  | 5565.2  | 5419.0  |
| 0.0  | 40°    | 5869.7  | 6394.3  | 6666.8  | 6939.8  | 7212.3  | 7432.0  | 7247.3  | 7062.6  | 6877.9  |
| 0.0  | 42.5°  | 7703.5  | 8452.2  | 8844.0  | 9235.3  | 9627.1  | 9970.0  | 9775.8  | 9581.7  | 9387.5  |
| 0.0  | 45°    | 10389.3 | 11385.5 | 11863.2 | 12340.3 | 12818.0 | 13068.6 | 12789.1 | 12509.0 | 12229.5 |
| 0.0  | 47.5°  | 12268.0 | 13260.2 | 13685.5 | 14110.7 | 14536.0 | 14822.0 | 14480.1 | 14138.2 | 13796.8 |
| 0.0  | 50°    | 13122.5 | 14066.3 | 14493.1 | 14919.3 | 15346.1 | 15573.2 | 15178.4 | 14783.1 | 14388.2 |
| 0.0  | 52.5°  | 13287.7 | 14169.6 | 14678.7 | 15188.3 | 15697.5 | 16000.9 | 15534.7 | 15068.1 | 14601.9 |
| 0.0  | 55°    | 13466.4 | 14401.2 | 14991.7 | 15582.7 | 16173.1 | 16593.4 | 16066.3 | 15538.7 | 15011.7 |
| 0.0  | 57.5°  | 13802.8 | 14813.5 | 15402.5 | 15990.9 | 16579.9 | 16936.8 | 16408.2 | 15879.1 | 15350.6 |
| 0.0  | 60°    | 13832.7 | 14779.1 | 15285.2 | 15791.8 | 16297.9 | 16522.5 | 16016.9 | 15510.8 | 15005.2 |
| 0.0  | 62.5°  | 12939.8 | 13650.0 | 14001.4 | 14352.8 | 14704.2 | 14948.3 | 14420.7 | 13892.6 | 13365.0 |
| 0.0  | 65°    | 10800.5 | 11240.3 | 11520.3 | 11800.3 | 12080.3 | 12371.3 | 11888.1 | 11405.0 | 10921.8 |
| 0.0  | 67.5°  | 8558.0  | 8894.4  | 9263.2  | 9632.1  | 10000.9 | 10311.9 | 9925.1  | 9537.8  | 9150.9  |
|      | 70°    | 6882.4  | 7336.1  | 7750.9  | 8165.7  | 8580.4  | 8835.0  | 8446.7  | 8057.9  | 7669.5  |
|      | 72.5°  | 5467.9  | 5948.6  | 6295.0  | 6640.8  | 6987.2  | 7049.6  | 6764.1  | 6478.6  | 6193.6  |
|      | 75°    | 3320.2  | 3606.7  | 3613.7  | 3620.1  | 3627.1  | 3686.5  | 3449.9  | 3213.4  | 2977.3  |
|      | 77.5°  | 979.3   | 1081.6  | 1166.0  | 1249.8  | 1334.2  | 1436.0  | 1349.1  | 1261.8  | 1174.9  |
|      | 80°    | 283.5   | 309.5   | 331.4   | 352.9   | 374.8   | 361.9   | 341.4   | 320.9   | 300.5   |
|      | 82.5°  | 50.9    | 47.9    | 47.4    | 46.9    | 46.9    | 44.4    | 40.4    | 36.4    | 32.4    |
|      | 85°    | 9.0     | 8.5     | 8.0     | 7.5     | 7.0     | 6.5     | 5.5     | 5.0     | 4.0     |
|      | 87.5°  | 3.0     | 2.5     | 2.0     | 1.5     | 1.5     | 0.5     | 0.5     | 0.5     | 0.0     |
|      | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |
|      | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 325° | 327.5° |        | 330°    | 332.5°  | 335°    | 337.5°  | 340°   | 342.5° | 345°   | 347.5° | 350°   |
|------|--------|--------|---------|---------|---------|---------|--------|--------|--------|--------|--------|
| 0.0  | 0.0    | 0°     | 28.9    | 28.9    | 28.9    | 28.9    | 28.9   | 28.9   | 28.9   | 28.9   | 28.9   |
| 0.0  | 0.0    | 2.5°   | 28.5    | 28.0    | 28.0    | 28.0    | 28.0   | 27.5   | 27.5   | 27.5   | 27.5   |
| 0.0  | 0.0    | 5°     | 31.4    | 31.4    | 30.9    | 30.9    | 30.4   | 30.4   | 29.9   | 29.9   | 29.4   |
| 0.0  | 0.0    | 7.5°   | 36.9    | 36.4    | 35.9    | 35.4    | 34.9   | 33.9   | 33.4   | 32.9   | 32.9   |
| 0.0  | 0.0    | 10°    | 44.4    | 43.4    | 42.9    | 41.9    | 41.4   | 40.4   | 39.4   | 38.4   | 37.4   |
| 0.0  | 0.0    | 12.5°  | 58.4    | 56.4    | 54.9    | 52.9    | 50.9   | 49.4   | 47.4   | 45.9   | 43.9   |
| 0.0  | 0.0    | 15°    | 101.3   | 96.3    | 90.8    | 84.4    | 77.4   | 70.9   | 63.9   | 59.9   | 55.4   |
| 0.0  | 0.0    | 17.5°  | 259.0   | 233.1   | 206.6   | 185.2   | 163.7  | 142.7  | 121.3  | 105.8  | 90.3   |
| 0.0  | 0.0    | 20°    | 659.3   | 587.5   | 515.6   | 444.7   | 373.3  | 302.5  | 231.1  | 195.2  | 159.2  |
| 0.0  | 0.0    | 22.5°  | 1240.8  | 1107.6  | 973.8   | 844.5   | 714.7  | 585.5  | 456.2  | 374.8  | 294.0  |
| 0.0  | 0.0    | 25°    | 1915.1  | 1747.4  | 1579.7  | 1367.1  | 1154.0 | 941.3  | 728.7  | 596.5  | 464.2  |
| 0.0  | 0.0    | 27.5°  | 2492.1  | 2299.0  | 2105.8  | 1847.3  | 1588.7 | 1330.2 | 1071.6 | 874.5  | 677.8  |
| 0.0  | 0.0    | 30°    | 2991.7  | 2784.1  | 2576.5  | 2275.5  | 1974.5 | 1673.6 | 1372.6 | 1126.0 | 879.5  |
| 0.0  | 0.0    | 32.5°  | 3425.0  | 3176.4  | 2927.9  | 2617.4  | 2307.0 | 1996.5 | 1686.0 | 1383.6 | 1081.1 |
| 0.0  | 0.0    | 35°    | 3924.6  | 3634.6  | 3344.1  | 2999.7  | 2654.8 | 2310.4 | 1966.0 | 1624.6 | 1282.7 |
| 0.0  | 0.0    | 37.5°  | 4559.5  | 4203.6  | 3847.2  | 3463.4  | 3079.6 | 2696.3 | 2312.4 | 1922.1 | 1531.8 |
| 0.0  | 0.0    | 40°    | 5774.9  | 5315.7  | 4856.5  | 4368.8  | 3880.7 | 3393.0 | 2905.4 | 2426.2 | 1947.1 |
| 0.0  | 0.0    | 42.5°  | 7952.5  | 7332.1  | 6711.7  | 6062.9  | 5413.5 | 4764.6 | 4115.3 | 3439.5 | 2763.2 |
| 0.0  | 0.0    | 45°    | 10410.2 | 9640.6  | 8870.4  | 8142.2  | 7413.5 | 6685.3 | 5957.0 | 5029.7 | 4102.3 |
| 0.0  | 0.0    | 47.5°  | 11792.3 | 10961.3 | 10130.2 | 9440.9  | 8751.6 | 8062.4 | 7373.1 | 6373.3 | 5373.6 |
| 0.0  | 0.0    | 50°    | 12300.9 | 11454.9 | 10608.9 | 9974.5  | 9339.6 | 8705.2 | 8070.3 | 7069.1 | 6067.4 |
| 0.0  | 0.0    | 52.5°  | 12409.2 | 11546.2 | 10683.3 | 10044.9 | 9406.5 | 8768.6 | 8130.2 | 7135.5 | 6140.7 |
| 0.0  | 0.0    | 55°    | 12631.8 | 11706.0 | 10779.6 | 10051.9 | 9324.1 | 8596.4 | 7868.7 | 6858.0 | 5847.2 |
| 0.0  | 0.0    | 57.5°  | 12922.8 | 11973.5 | 11024.2 | 10195.1 | 9366.1 | 8537.5 | 7708.5 | 6603.4 | 5498.4 |
| 0.0  | 0.0    | 60°    | 12846.5 | 12020.4 | 11193.9 | 10305.9 | 9417.5 | 8529.5 | 7641.1 | 6425.7 | 5209.9 |
| 0.0  | 0.0    | 62.5°  | 11520.8 | 10862.9 | 10204.6 | 9474.4  | 8743.7 | 8013.4 | 7283.2 | 6031.9 | 4780.6 |
| 0.0  | 0.0    | 65°    | 9477.9  | 8997.7  | 8517.6  | 7930.1  | 7342.1 | 6754.6 | 6167.2 | 5045.1 | 3923.6 |
| 0.0  | 0.0    | 67.5°  | 7681.5  | 7140.5  | 6598.9  | 6130.7  | 5662.1 | 5193.9 | 4725.2 | 3842.3 | 2959.3 |
|      |        | 70°    | 6102.8  | 5514.3  | 4925.4  | 4468.2  | 4010.5 | 3553.3 | 3096.1 | 2509.1 | 1922.6 |
|      |        | 72.5°  | 4846.5  | 4315.9  | 3785.4  | 3297.7  | 2809.6 | 2321.9 | 1833.8 | 1486.9 | 1140.0 |
|      |        | 75°    | 2316.4  | 2104.3  | 1892.2  | 1637.1  | 1382.1 | 1127.0 | 872.0  | 720.7  | 570.0  |
|      |        | 77.5°  | 858.5   | 744.2   | 629.4   | 525.6   | 421.8  | 318.4  | 214.6  | 196.7  | 178.7  |
|      |        | 80°    | 222.1   | 193.7   | 164.7   | 144.2   | 123.3  | 102.8  | 82.4   | 74.4   | 66.9   |
|      |        | 82.5°  | 25.5    | 23.5    | 22.0    | 21.0    | 19.5   | 18.5   | 17.0   | 15.5   | 14.0   |
|      |        | 85°    | 1.5     | 1.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 87.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 90°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 92.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 95°    | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 97.5°  | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 100°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 102.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 105°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 107.5° | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
|      |        | 110°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |



REPORT NUMBER: P1049430  
CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

[illegible]

REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

| 352.5° | 355° |        | 357.5° | 360°   |
|--------|------|--------|--------|--------|
| 0.0    | 0.0  | 0°     | 28.9   | 28.9   |
| 0.0    | 0.0  | 2.5°   | 27.0   | 26.5   |
| 0.0    | 0.0  | 5°     | 28.5   | 28.0   |
| 0.0    | 0.0  | 7.5°   | 31.4   | 30.4   |
| 0.0    | 0.0  | 10°    | 34.4   | 33.4   |
| 0.0    | 0.0  | 12.5°  | 38.9   | 37.4   |
| 0.0    | 0.0  | 15°    | 43.9   | 40.9   |
| 0.0    | 0.0  | 17.5°  | 52.4   | 45.9   |
| 0.0    | 0.0  | 20°    | 70.9   | 54.4   |
| 0.0    | 0.0  | 22.5°  | 99.8   | 67.9   |
| 0.0    | 0.0  | 25°    | 146.7  | 93.8   |
| 0.0    | 0.0  | 27.5°  | 204.1  | 124.8  |
| 0.0    | 0.0  | 30°    | 271.5  | 156.2  |
| 0.0    | 0.0  | 32.5°  | 330.9  | 186.2  |
| 0.0    | 0.0  | 35°    | 408.3  | 216.6  |
| 0.0    | 0.0  | 37.5°  | 503.6  | 255.6  |
| 0.0    | 0.0  | 40°    | 651.4  | 314.4  |
| 0.0    | 0.0  | 42.5°  | 917.4  | 423.3  |
| 0.0    | 0.0  | 45°    | 1489.9 | 731.7  |
| 0.0    | 0.0  | 47.5°  | 2292.5 | 1210.4 |
| 0.0    | 0.0  | 50°    | 2804.6 | 1544.8 |
| 0.0    | 0.0  | 52.5°  | 2846.5 | 1542.3 |
| 0.0    | 0.0  | 55°    | 2598.4 | 1371.1 |
| 0.0    | 0.0  | 57.5°  | 2217.1 | 1146.0 |
| 0.0    | 0.0  | 60°    | 1842.8 | 906.4  |
| 0.0    | 0.0  | 62.5°  | 1452.0 | 625.9  |
| 0.0    | 0.0  | 65°    | 1061.1 | 442.7  |
| 0.0    | 0.0  | 67.5°  | 762.2  | 330.9  |
|        |      | 70°    | 501.1  | 253.6  |
|        |      | 72.5°  | 326.4  | 206.6  |
|        |      | 75°    | 219.6  | 171.2  |
|        |      | 77.5°  | 128.3  | 113.8  |
|        |      | 80°    | 45.4   | 39.9   |
|        |      | 82.5°  | 8.5    | 6.0    |
|        |      | 85°    | 0.0    | 0.0    |
|        |      | 87.5°  | 0.0    | 0.0    |
|        |      | 90°    | 0.0    | 0.0    |
|        |      | 92.5°  | 0.0    | 0.0    |
|        |      | 95°    | 0.0    | 0.0    |
|        |      | 97.5°  | 0.0    | 0.0    |
|        |      | 100°   | 0.0    | 0.0    |
|        |      | 102.5° | 0.0    | 0.0    |
|        |      | 105°   | 0.0    | 0.0    |
|        |      | 107.5° | 0.0    | 0.0    |
|        |      | 110°   | 0.0    | 0.0    |



REPORT NUMBER: P1049430

CATALOG NUMBER: GALN-SA2B-950-U-RBC

**CANDELA DISTRIBUTION (continued):**

|        | 357.5° | 360° |
|--------|--------|------|
| 112.5° | 0.0    | 0.0  |
| 115°   | 0.0    | 0.0  |
| 117.5° | 0.0    | 0.0  |
| 120°   | 0.0    | 0.0  |
| 122.5° | 0.0    | 0.0  |
| 125°   | 0.0    | 0.0  |
| 127.5° | 0.0    | 0.0  |
| 130°   | 0.0    | 0.0  |
| 132.5° | 0.0    | 0.0  |
| 135°   | 0.0    | 0.0  |
| 137.5° | 0.0    | 0.0  |
| 140°   | 0.0    | 0.0  |
| 142.5° | 0.0    | 0.0  |
| 145°   | 0.0    | 0.0  |
| 147.5° | 0.0    | 0.0  |
| 150°   | 0.0    | 0.0  |
| 152.5° | 0.0    | 0.0  |
| 155°   | 0.0    | 0.0  |
| 157.5° | 0.0    | 0.0  |
| 160°   | 0.0    | 0.0  |
| 162.5° | 0.0    | 0.0  |
| 165°   | 0.0    | 0.0  |
| 167.5° | 0.0    | 0.0  |
| 170°   | 0.0    | 0.0  |
| 172.5° | 0.0    | 0.0  |
| 175°   | 0.0    | 0.0  |
| 177.5° | 0.0    | 0.0  |
| 180°   | 0.0    | 0.0  |

LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-17

Test Date: 10/11/2024

Luminaire Tested: GSS-SB1A-950-U-5WQ

Data in this report applies to families of products including GSS-SB1A-950-U-5WQ


### Test Information

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-17  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry:  $4\pi$   
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-950-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 90 CRI  
 5000K CCT 26 LEDS

### Spectral Parameters

CCT (K): 4765  
 CIE  $u'$ : 0.2105  
 CIE  $v'$ : 0.4941  
 Duv: 0.0052  
 CIE x: 0.3536  
 CIE y: 0.3689  
 CIE z: 0.2775  
 Peak Wavelength (nm): 449  
 Dominant Wavelength (nm): 571  
 Purity: 16.80041  
 R<sub>f</sub>: 90.7  
 R<sub>g</sub>: 98

CRI (Ra): 90.8  
 R1: 89.8  
 R2: 93.1  
 R3: 95.3  
 R4: 90.3  
 R5: 89.0  
 R6: 89.7  
 R7: 94.9  
 R8: 84.0  
 R9: 54.9  
 R10: 83.0  
 R11: 89.6  
 R12: 68.0  
 R13: 90.6  
 R14: 97.3  
 R15: 86.2



### Test Conditions


Stabilization Time: 20M  
 Operation Time: 1H 20M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-17


| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-17

**CIE 1931 Chromaticity Diagram**




**CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles**



Point lies inside the ANSI 5000K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-17

### Photopic Flux vs. Wavelength




### Photopic Lumens: NR

| $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) | $\lambda$<br>(nm) | Power<br>$\text{W}/\text{nm}$ | Lumens<br>( $\phi/\text{nm}$ ) |
|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|-------------------|-------------------------------|--------------------------------|
| 360               | 0                             | NR                             | 490               | 462                           | NR                             | 620               | 668                           | NR                             | 750               | 45                            | NR                             | 880               | 1                             | NR                             |
| 365               | 0                             | NR                             | 495               | 498                           | NR                             | 625               | 652                           | NR                             | 755               | 39                            | NR                             | 885               | 1                             | NR                             |
| 370               | 0                             | NR                             | 500               | 533                           | NR                             | 630               | 634                           | NR                             | 760               | 33                            | NR                             | 890               | 1                             | NR                             |
| 375               | 0                             | NR                             | 505               | 562                           | NR                             | 635               | 610                           | NR                             | 765               | 28                            | NR                             | 895               | 1                             | NR                             |
| 380               | 0                             | NR                             | 510               | 590                           | NR                             | 640               | 583                           | NR                             | 770               | 24                            | NR                             | 900               | 1                             | NR                             |
| 385               | 0                             | NR                             | 515               | 617                           | NR                             | 645               | 552                           | NR                             | 775               | 21                            | NR                             | 905               | 1                             | NR                             |
| 390               | 0                             | NR                             | 520               | 642                           | NR                             | 650               | 519                           | NR                             | 780               | 18                            | NR                             | 910               | 0                             | NR                             |
| 395               | 2                             | NR                             | 525               | 661                           | NR                             | 655               | 484                           | NR                             | 785               | 15                            | NR                             | 915               | 0                             | NR                             |
| 400               | 4                             | NR                             | 530               | 681                           | NR                             | 660               | 448                           | NR                             | 790               | 13                            | NR                             | 920               | 0                             | NR                             |
| 405               | 7                             | NR                             | 535               | 695                           | NR                             | 665               | 411                           | NR                             | 795               | 11                            | NR                             | 925               | 0                             | NR                             |
| 410               | 12                            | NR                             | 540               | 702                           | NR                             | 670               | 373                           | NR                             | 800               | 10                            | NR                             | 930               | 0                             | NR                             |
| 415               | 21                            | NR                             | 545               | 708                           | NR                             | 675               | 338                           | NR                             | 805               | 8                             | NR                             | 935               | 0                             | NR                             |
| 420               | 39                            | NR                             | 550               | 707                           | NR                             | 680               | 305                           | NR                             | 810               | 7                             | NR                             | 940               | 0                             | NR                             |
| 425               | 74                            | NR                             | 555               | 706                           | NR                             | 685               | 272                           | NR                             | 815               | 6                             | NR                             | 945               | 0                             | NR                             |
| 430               | 139                           | NR                             | 560               | 700                           | NR                             | 690               | 243                           | NR                             | 820               | 5                             | NR                             | 950               | 0                             | NR                             |
| 435               | 270                           | NR                             | 565               | 696                           | NR                             | 695               | 214                           | NR                             | 825               | 5                             | NR                             | 955               | 0                             | NR                             |
| 440               | 517                           | NR                             | 570               | 692                           | NR                             | 700               | 188                           | NR                             | 830               | 4                             | NR                             | 960               | 0                             | NR                             |
| 445               | 877                           | NR                             | 575               | 689                           | NR                             | 705               | 165                           | NR                             | 835               | 3                             | NR                             | 965               | 0                             | NR                             |
| 450               | 978                           | NR                             | 580               | 688                           | NR                             | 710               | 144                           | NR                             | 840               | 3                             | NR                             | 970               | 0                             | NR                             |
| 455               | 738                           | NR                             | 585               | 688                           | NR                             | 715               | 125                           | NR                             | 845               | 3                             | NR                             | 975               | 0                             | NR                             |
| 460               | 618                           | NR                             | 590               | 689                           | NR                             | 720               | 110                           | NR                             | 850               | 2                             | NR                             | 980               | 0                             | NR                             |
| 465               | 529                           | NR                             | 595               | 690                           | NR                             | 725               | 95                            | NR                             | 855               | 2                             | NR                             | 985               | 0                             | NR                             |
| 470               | 420                           | NR                             | 600               | 690                           | NR                             | 730               | 82                            | NR                             | 860               | 2                             | NR                             | 990               | 0                             | NR                             |
| 475               | 395                           | NR                             | 605               | 688                           | NR                             | 735               | 71                            | NR                             | 865               | 1                             | NR                             | 995               | 0                             | NR                             |
| 480               | 408                           | NR                             | 610               | 685                           | NR                             | 740               | 61                            | NR                             | 870               | 1                             | NR                             | 1000              | 0                             | NR                             |
| 485               | 429                           | NR                             | 615               | 678                           | NR                             | 745               | 52                            | NR                             | 875               | 1                             | NR                             |                   |                               |                                |

REPORT NUMBER: SP1-2407-184-17

### Scotopic Flux vs. Wavelength




Scotopic Lumens: NR

S/P: 1.99

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (Φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 462                      | NR            | 620    | 668                      | NR            | 750    | 45                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 498                      | NR            | 625    | 652                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 533                      | NR            | 630    | 634                      | NR            | 760    | 33                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 562                      | NR            | 635    | 610                      | NR            | 765    | 28                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 590                      | NR            | 640    | 583                      | NR            | 770    | 24                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 617                      | NR            | 645    | 552                      | NR            | 775    | 21                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 642                      | NR            | 650    | 519                      | NR            | 780    | 18                       | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 661                      | NR            | 655    | 484                      | NR            | 785    | 15                       | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 681                      | NR            | 660    | 448                      | NR            | 790    | 13                       | NR            | 920    | 0                        | NR            |
| 405    | 7                        | NR            | 535    | 695                      | NR            | 665    | 411                      | NR            | 795    | 11                       | NR            | 925    | 0                        | NR            |
| 410    | 12                       | NR            | 540    | 702                      | NR            | 670    | 373                      | NR            | 800    | 10                       | NR            | 930    | 0                        | NR            |
| 415    | 21                       | NR            | 545    | 708                      | NR            | 675    | 338                      | NR            | 805    | 8                        | NR            | 935    | 0                        | NR            |
| 420    | 39                       | NR            | 550    | 707                      | NR            | 680    | 305                      | NR            | 810    | 7                        | NR            | 940    | 0                        | NR            |
| 425    | 74                       | NR            | 555    | 706                      | NR            | 685    | 272                      | NR            | 815    | 6                        | NR            | 945    | 0                        | NR            |
| 430    | 139                      | NR            | 560    | 700                      | NR            | 690    | 243                      | NR            | 820    | 5                        | NR            | 950    | 0                        | NR            |
| 435    | 270                      | NR            | 565    | 696                      | NR            | 695    | 214                      | NR            | 825    | 5                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 692                      | NR            | 700    | 188                      | NR            | 830    | 4                        | NR            | 960    | 0                        | NR            |
| 445    | 877                      | NR            | 575    | 689                      | NR            | 705    | 165                      | NR            | 835    | 3                        | NR            | 965    | 0                        | NR            |
| 450    | 978                      | NR            | 580    | 688                      | NR            | 710    | 144                      | NR            | 840    | 3                        | NR            | 970    | 0                        | NR            |
| 455    | 738                      | NR            | 585    | 688                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 618                      | NR            | 590    | 689                      | NR            | 720    | 110                      | NR            | 850    | 2                        | NR            | 980    | 0                        | NR            |
| 465    | 529                      | NR            | 595    | 690                      | NR            | 725    | 95                       | NR            | 855    | 2                        | NR            | 985    | 0                        | NR            |
| 470    | 420                      | NR            | 600    | 690                      | NR            | 730    | 82                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 395                      | NR            | 605    | 688                      | NR            | 735    | 71                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 408                      | NR            | 610    | 685                      | NR            | 740    | 61                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 429                      | NR            | 615    | 678                      | NR            | 745    | 52                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-17

### Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 4.22


| λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) | λ<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>(φ/nm) |
|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|-----------|-----------------------------|------------------|
| 360       | 0                           | NR               | 490       | 462                         | NR               | 620       | 668                         | NR               | 750       | 45                          | NR               | 880       | 1                           | NR               |
| 365       | 0                           | NR               | 495       | 498                         | NR               | 625       | 652                         | NR               | 755       | 39                          | NR               | 885       | 1                           | NR               |
| 370       | 0                           | NR               | 500       | 533                         | NR               | 630       | 634                         | NR               | 760       | 33                          | NR               | 890       | 1                           | NR               |
| 375       | 0                           | NR               | 505       | 562                         | NR               | 635       | 610                         | NR               | 765       | 28                          | NR               | 895       | 1                           | NR               |
| 380       | 0                           | NR               | 510       | 590                         | NR               | 640       | 583                         | NR               | 770       | 24                          | NR               | 900       | 1                           | NR               |
| 385       | 0                           | NR               | 515       | 617                         | NR               | 645       | 552                         | NR               | 775       | 21                          | NR               | 905       | 1                           | NR               |
| 390       | 0                           | NR               | 520       | 642                         | NR               | 650       | 519                         | NR               | 780       | 18                          | NR               | 910       | 0                           | NR               |
| 395       | 2                           | NR               | 525       | 661                         | NR               | 655       | 484                         | NR               | 785       | 15                          | NR               | 915       | 0                           | NR               |
| 400       | 4                           | NR               | 530       | 681                         | NR               | 660       | 448                         | NR               | 790       | 13                          | NR               | 920       | 0                           | NR               |
| 405       | 7                           | NR               | 535       | 695                         | NR               | 665       | 411                         | NR               | 795       | 11                          | NR               | 925       | 0                           | NR               |
| 410       | 12                          | NR               | 540       | 702                         | NR               | 670       | 373                         | NR               | 800       | 10                          | NR               | 930       | 0                           | NR               |
| 415       | 21                          | NR               | 545       | 708                         | NR               | 675       | 338                         | NR               | 805       | 8                           | NR               | 935       | 0                           | NR               |
| 420       | 39                          | NR               | 550       | 707                         | NR               | 680       | 305                         | NR               | 810       | 7                           | NR               | 940       | 0                           | NR               |
| 425       | 74                          | NR               | 555       | 706                         | NR               | 685       | 272                         | NR               | 815       | 6                           | NR               | 945       | 0                           | NR               |
| 430       | 139                         | NR               | 560       | 700                         | NR               | 690       | 243                         | NR               | 820       | 5                           | NR               | 950       | 0                           | NR               |
| 435       | 270                         | NR               | 565       | 696                         | NR               | 695       | 214                         | NR               | 825       | 5                           | NR               | 955       | 0                           | NR               |
| 440       | 517                         | NR               | 570       | 692                         | NR               | 700       | 188                         | NR               | 830       | 4                           | NR               | 960       | 0                           | NR               |
| 445       | 877                         | NR               | 575       | 689                         | NR               | 705       | 165                         | NR               | 835       | 3                           | NR               | 965       | 0                           | NR               |
| 450       | 978                         | NR               | 580       | 688                         | NR               | 710       | 144                         | NR               | 840       | 3                           | NR               | 970       | 0                           | NR               |
| 455       | 738                         | NR               | 585       | 688                         | NR               | 715       | 125                         | NR               | 845       | 3                           | NR               | 975       | 0                           | NR               |
| 460       | 618                         | NR               | 590       | 689                         | NR               | 720       | 110                         | NR               | 850       | 2                           | NR               | 980       | 0                           | NR               |
| 465       | 529                         | NR               | 595       | 690                         | NR               | 725       | 95                          | NR               | 855       | 2                           | NR               | 985       | 0                           | NR               |
| 470       | 420                         | NR               | 600       | 690                         | NR               | 730       | 82                          | NR               | 860       | 2                           | NR               | 990       | 0                           | NR               |
| 475       | 395                         | NR               | 605       | 688                         | NR               | 735       | 71                          | NR               | 865       | 1                           | NR               | 995       | 0                           | NR               |
| 480       | 408                         | NR               | 610       | 685                         | NR               | 740       | 61                          | NR               | 870       | 1                           | NR               | 1000      | 0                           | NR               |
| 485       | 429                         | NR               | 615       | 678                         | NR               | 745       | 52                          | NR               | 875       | 1                           | NR               |           |                             |                  |

REPORT NUMBER: SP1-2407-184-17





TM-30-18

### Summary

$R_f = 90.7$   
 $R_g = 98$   
 CIE  $R_a = 90.8$   
 $R_9 = 54.9$




### Color Vector Graphics






**Individual Sample Fidelity Index ( $R_{f,i}$ )**



|            |             |            |            |
|------------|-------------|------------|------------|
| CES01 = 85 | CES26 = 92  | CES51 = 96 | CES76 = 85 |
| CES02 = 60 | CES27 = 92  | CES52 = 97 | CES77 = 88 |
| CES03 = 31 | CES28 = 95  | CES53 = 94 | CES78 = 82 |
| CES04 = 69 | CES29 = 95  | CES54 = 93 | CES79 = 96 |
| CES05 = 48 | CES30 = 94  | CES55 = 92 | CES80 = 93 |
| CES06 = 50 | CES31 = 96  | CES56 = 92 | CES81 = 89 |
| CES07 = 41 | CES32 = 91  | CES57 = 91 | CES82 = 97 |
| CES08 = 40 | CES33 = 99  | CES58 = 91 | CES83 = 98 |
| CES09 = 29 | CES34 = 93  | CES59 = 95 | CES84 = 93 |
| CES10 = 73 | CES35 = 96  | CES60 = 92 | CES85 = 85 |
| CES11 = 56 | CES36 = 82  | CES61 = 92 | CES86 = 88 |
| CES12 = 62 | CES37 = 95  | CES62 = 87 | CES87 = 90 |
| CES13 = 42 | CES38 = 89  | CES63 = 91 | CES88 = 94 |
| CES14 = 74 | CES39 = 99  | CES64 = 88 | CES89 = 87 |
| CES15 = 71 | CES40 = 98  | CES65 = 86 | CES90 = 94 |
| CES16 = 46 | CES41 = 97  | CES66 = 85 | CES91 = 74 |
| CES17 = 48 | CES42 = 95  | CES67 = 84 | CES92 = 78 |
| CES18 = 56 | CES43 = 95  | CES68 = 86 | CES93 = 87 |
| CES19 = 70 | CES44 = 100 | CES69 = 88 | CES94 = 80 |
| CES20 = 65 | CES45 = 97  | CES70 = 84 | CES95 = 81 |
| CES21 = 85 | CES46 = 96  | CES71 = 79 | CES96 = 90 |
| CES22 = 77 | CES47 = 98  | CES72 = 93 | CES97 = 95 |
| CES23 = 91 | CES48 = 90  | CES73 = 78 | CES98 = 92 |
| CES24 = 90 | CES49 = 95  | CES74 = 93 | CES99 = 88 |
| CES25 = 70 | CES50 = 97  | CES75 = 80 |            |



Color Rendition by Hue-Angle Bin



**Measure Comparisons**



(END OF REPORT)