

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1434629

Luminaire Tested: **GALN-SB8C-722-U-T3LG**

Issue Date: 03/24/202

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1434629  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 03/24/202  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: McGRAW-EDISON  
 Catalog Number: GALN-SB8C-722-U-T3LG  
 Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 615mA 8xLight  
 Square PACKAGE 70CRI 2200K FIXTURE w/ TYPE III LOW GLARE  
 Light Source: (208) 2200K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER  
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |


**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 48806.8 lumens  
 Efficiency: N/A  
 Efficacy: 122.1 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B4 - U0 - G4  
  
 Input Watts (W): 399.8  
 Input Voltage (V): 120  
 Input Current (A<sub>in</sub>): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.97  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1434629  
 CATALOG NUMBER: GALN-SB8C-722-U-T3LG

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 27.9 fc  
 Type III - Short - N/A

REPORT NUMBER: P1434629  
CATALOG NUMBER: GALN-SB8C-722-U-T3LG

### Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral      - - - Horizontal Cone Through 53-Deg Vertical

REPORT NUMBER: P1434629  
 CATALOG NUMBER: GALN-SB8C-722-U-T3LG

**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 12303.8  | 0.0    | 12303.8 |
|                    | % Fixture | 25.2     | 0.0    | 25.2    |
| <b>Street Side</b> | Lumens    | 36503.0  | 0.0    | 36503.0 |
|                    | % Fixture | 74.8     | 0.0    | 74.8    |
| <b>Total</b>       | Lumens    | 48806.8  | 0.0    | 48806.8 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 682.7   | 1.4       |
| 10°-20°   | 2114.1  | 4.3       |
| 20°-30°   | 4042.0  | 8.3       |
| 30°-40°   | 6939.8  | 14.2      |
| 40°-50°   | 9720.5  | 19.9      |
| 50°-60°   | 11031.5 | 22.6      |
| 60°-70°   | 9674.0  | 19.8      |
| 70°-80°   | 3782.7  | 7.8       |
| 80°-90°   | 819.6   | 1.7       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 48806.8 | 100.0     |
| 0°-180°   | 48806.8 | 100.0     |




REPORT NUMBER: P1434629  
 CATALOG NUMBER: GALN-SB8C-722-U-T3LG

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 3879.7  | 7.9       |                         |      |          |
| FM (30°-60°)   | 21273.2 | 43.6      |                         |      |          |
| FH (60°-80°)   | 10952.6 | 22.4      |                         |      | G4/12000 |
| FVH (80°-90°)  | 397.5   | 0.8       |                         |      | G3/500   |
| BL (0°-30°)    | 2959.1  | 6.1       | B4/5000                 |      |          |
| BM (30°-60°)   | 6418.6  | 13.2      | B4/8500                 |      |          |
| BH (60°-80°)   | 2504.0  | 5.1       | B4/5000                 |      | G4/5000  |
| BVH (80°-90°)  | 422.1   | 0.9       |                         |      | G3/500   |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B4-U0-G4**  
 Type III Short





REPORT NUMBER: P1434629  
 CATALOG NUMBER: GALN-SB8C-722-U-T3LG

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 79°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  | 7165.0  |
| 2.5°  | 7175.8  | 7175.8  | 7132.4  | 7175.8  | 7154.1  | 7186.7  | 7208.5  | 7208.5  | 7251.9  | 7241.1  | 7241.1  |
| 5°    | 7056.2  | 7034.5  | 7023.6  | 7099.7  | 7143.2  | 7230.2  | 7328.1  | 7371.5  | 7447.7  | 7447.7  | 7458.5  |
| 7.5°  | 6740.9  | 6730.1  | 6784.4  | 6936.6  | 7078.0  | 7295.4  | 7502.0  | 7621.6  | 7741.2  | 7763.0  | 7763.0  |
| 10°   | 6545.2  | 6534.4  | 6599.6  | 6784.4  | 7012.8  | 7328.1  | 7654.2  | 7904.3  | 8100.0  | 8154.4  | 8154.4  |
| 12.5° | 6545.2  | 6545.2  | 6599.6  | 6784.4  | 7023.6  | 7404.2  | 7849.9  | 8274.0  | 8578.4  | 8643.6  | 8621.9  |
| 15°   | 6730.1  | 6719.2  | 6784.4  | 6980.1  | 7208.5  | 7567.2  | 8110.9  | 8676.2  | 9089.4  | 9209.0  | 9219.9  |
| 17.5° | 6925.8  | 6914.9  | 7012.8  | 7262.8  | 7534.6  | 7893.4  | 8447.9  | 9143.8  | 9730.9  | 9883.1  | 9915.7  |
| 20°   | 7230.2  | 7219.3  | 7338.9  | 7578.1  | 7915.2  | 8328.3  | 8904.6  | 9698.3  | 10513.7 | 10676.8 | 10720.3 |
| 22.5° | 7578.1  | 7589.0  | 7719.5  | 8013.0  | 8350.1  | 8893.7  | 9600.4  | 10481.1 | 11459.6 | 11709.7 | 11753.2 |
| 25°   | 8306.6  | 8274.0  | 8382.7  | 8589.3  | 8948.1  | 9600.4  | 10470.2 | 11427.0 | 12590.3 | 12894.8 | 12949.1 |
| 27.5° | 9274.2  | 9219.9  | 9339.5  | 9546.0  | 9807.0  | 10415.8 | 11416.1 | 12481.6 | 13884.2 | 14264.7 | 14275.6 |
| 30°   | 10144.0 | 10111.4 | 10274.5 | 10698.5 | 10970.3 | 11437.9 | 12503.4 | 13721.1 | 15482.4 | 16036.9 | 16058.7 |
| 32.5° | 10894.2 | 10883.4 | 11187.8 | 11731.4 | 12351.1 | 12851.3 | 13884.2 | 15286.7 | 17504.7 | 18146.2 | 18004.8 |
| 35°   | 11611.8 | 11644.4 | 12025.0 | 12590.3 | 13416.6 | 14416.9 | 15460.7 | 17058.9 | 19635.7 | 20407.7 | 20179.3 |
| 37.5° | 12340.3 | 12362.0 | 12862.1 | 13590.6 | 14460.4 | 15765.1 | 17167.7 | 18983.4 | 21484.0 | 22440.8 | 21940.7 |
| 40°   | 13014.4 | 13079.6 | 13753.7 | 14536.5 | 15667.3 | 16993.7 | 18559.3 | 20320.7 | 22908.3 | 23854.2 | 23310.6 |
| 42.5° | 13688.5 | 13786.3 | 14514.8 | 15591.1 | 16798.0 | 18178.8 | 19527.0 | 21136.1 | 23821.6 | 24876.2 | 24039.1 |
| 45°   | 14384.3 | 14449.5 | 15351.9 | 16471.8 | 17841.7 | 19113.8 | 20081.5 | 21658.0 | 24452.2 | 25593.8 | 24452.2 |
| 47.5° | 14851.8 | 14982.3 | 15971.7 | 17265.5 | 18635.4 | 19831.4 | 20527.3 | 21875.4 | 24854.5 | 26061.3 | 24604.4 |
| 50°   | 15036.6 | 15221.5 | 16287.0 | 17722.2 | 19287.8 | 20505.5 | 20875.2 | 21995.0 | 25300.3 | 26474.5 | 24571.8 |
| 52.5° | 15004.0 | 15178.0 | 16341.3 | 17928.7 | 19809.7 | 21125.2 | 21212.2 | 22125.5 | 25615.6 | 26615.8 | 24289.1 |
| 53°   | 14830.1 | 15069.3 | 16374.0 | 17939.6 | 19885.8 | 21288.3 | 21364.4 | 22136.4 | 25659.1 | 26811.5 | 24245.6 |
| 55°   | 14232.1 | 14362.6 | 16036.9 | 17928.7 | 20244.6 | 21897.2 | 21788.5 | 22462.6 | 25778.7 | 26681.1 | 23767.3 |
| 57.5° | 13688.5 | 13818.9 | 15275.8 | 17722.2 | 20538.1 | 22756.1 | 22473.4 | 22408.2 | 25126.3 | 25941.7 | 22560.4 |
| 60°   | 13340.5 | 13384.0 | 14612.6 | 17069.8 | 20418.5 | 23354.1 | 22919.2 | 21766.7 | 23517.2 | 24191.3 | 20440.3 |
| 62.5° | 13047.0 | 13036.1 | 14123.4 | 16134.8 | 19961.9 | 23441.1 | 23006.2 | 20179.3 | 21157.9 | 21266.6 | 17613.4 |
| 65°   | 12383.8 | 12307.7 | 13362.3 | 15080.1 | 19016.0 | 23049.7 | 21940.7 | 17776.5 | 18026.6 | 17667.8 | 14145.1 |
| 67.5° | 11068.2 | 10905.1 | 11840.1 | 13471.0 | 17091.5 | 21940.7 | 19907.5 | 14982.3 | 14210.3 | 13492.8 | 10655.0 |
| 70°   | 7926.0  | 7926.0  | 8676.2  | 10307.1 | 13721.1 | 18961.6 | 17091.5 | 11340.0 | 9785.2  | 9143.8  | 7121.5  |
| 72.5° | 3881.5  | 3979.3  | 4762.1  | 6088.6  | 9198.1  | 13764.6 | 13090.5 | 7349.8  | 5936.4  | 5621.1  | 4566.4  |
| 75°   | 1652.6  | 1663.5  | 2033.2  | 2696.4  | 4664.3  | 8143.5  | 8197.9  | 4240.3  | 3805.4  | 3653.2  | 3022.6  |
| 77.5° | 1152.5  | 1174.2  | 1337.3  | 1587.4  | 2218.0  | 3740.1  | 4262.0  | 2565.9  | 2555.0  | 2446.3  | 2152.8  |
| 80°   | 880.7   | 902.4   | 1011.1  | 1185.1  | 1489.5  | 1913.6  | 2207.1  | 1739.6  | 1826.6  | 1717.9  | 1554.8  |
| 82.5° | 663.2   | 685.0   | 761.1   | 891.5   | 1065.5  | 1283.0  | 1239.5  | 1283.0  | 1348.2  | 1283.0  | 1119.9  |
| 85°   | 445.8   | 456.6   | 511.0   | 619.7   | 685.0   | 771.9   | 771.9   | 935.0   | 978.5   | 956.8   | 880.7   |
| 87.5° | 228.3   | 228.3   | 271.8   | 326.2   | 347.9   | 358.8   | 315.3   | 413.2   | 467.5   | 511.0   | 413.2   |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1434629  
 CATALOG NUMBER: GALN-SB8C-722-U-T3LG

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 7165.0  | 7165.0  | 7165.0 | 7165.0 | 7165.0 | 7165.0 | 7165.0 | 7165.0 | 7165.0 | 7165.0 | 7165.0 |
| 2.5°  | 7241.1  | 7251.9  | 7219.3 | 7208.5 | 7197.6 | 7143.2 | 7143.2 | 7088.9 | 7078.0 | 7088.9 | 7056.2 |
| 5°    | 7480.3  | 7458.5  | 7371.5 | 7306.3 | 7230.2 | 7078.0 | 6991.0 | 6871.4 | 6838.8 | 6806.2 | 6773.6 |
| 7.5°  | 7773.8  | 7741.2  | 7589.0 | 7415.0 | 7208.5 | 6914.9 | 6751.8 | 6556.1 | 6490.9 | 6436.5 | 6414.8 |
| 10°   | 8143.5  | 8078.3  | 7839.1 | 7469.4 | 7088.9 | 6730.1 | 6501.7 | 6262.6 | 6153.8 | 6132.1 | 6077.7 |
| 12.5° | 8621.9  | 8502.3  | 8056.5 | 7480.3 | 6980.1 | 6512.6 | 6262.6 | 6077.7 | 6034.2 | 6023.4 | 5969.0 |
| 15°   | 9154.6  | 8980.7  | 8263.1 | 7491.1 | 6838.8 | 6327.8 | 6175.6 | 6077.7 | 6077.7 | 6066.8 | 6034.2 |
| 17.5° | 9807.0  | 9524.3  | 8458.8 | 7447.7 | 6664.8 | 6273.4 | 6197.3 | 6110.3 | 6088.6 | 6099.5 | 6056.0 |
| 20°   | 10589.8 | 10122.3 | 8665.4 | 7393.3 | 6588.7 | 6284.3 | 6197.3 | 6077.7 | 6023.4 | 6012.5 | 5979.9 |
| 22.5° | 11492.2 | 10807.2 | 8893.7 | 7306.3 | 6588.7 | 6273.4 | 6132.1 | 5969.0 | 5860.3 | 5816.8 | 5773.3 |
| 25°   | 12525.1 | 11600.9 | 9132.9 | 7273.7 | 6610.5 | 6229.9 | 6001.6 | 5740.7 | 5566.7 | 5501.5 | 5468.9 |
| 27.5° | 13775.4 | 12438.1 | 9306.8 | 7306.3 | 6599.6 | 6132.1 | 5773.3 | 5436.2 | 5240.5 | 5131.8 | 5110.1 |
| 30°   | 15156.2 | 13340.5 | 9426.4 | 7360.7 | 6534.4 | 5947.2 | 5501.5 | 5120.9 | 4849.1 | 4718.7 | 4686.0 |
| 32.5° | 16787.1 | 14351.7 | 9546.0 | 7360.7 | 6371.3 | 5686.3 | 5186.2 | 4773.0 | 4490.3 | 4338.1 | 4316.4 |
| 35°   | 18591.9 | 15591.1 | 9654.8 | 7349.8 | 6175.6 | 5403.6 | 4870.9 | 4446.8 | 4153.3 | 4001.1 | 3990.2 |
| 37.5° | 20125.0 | 16526.2 | 9709.1 | 7241.1 | 5903.8 | 5077.5 | 4577.3 | 4153.3 | 3848.9 | 3685.8 | 3674.9 |
| 40°   | 21070.9 | 16917.6 | 9600.4 | 7023.6 | 5577.6 | 4740.4 | 4251.1 | 3859.7 | 3555.3 | 3359.6 | 3316.1 |
| 42.5° | 21429.7 | 16732.8 | 9252.5 | 6664.8 | 5186.2 | 4403.4 | 3979.3 | 3566.2 | 3163.9 | 3000.8 | 2968.2 |
| 45°   | 21310.1 | 16015.2 | 8513.2 | 6153.8 | 4751.3 | 4098.9 | 3740.1 | 3272.6 | 3011.7 | 2870.3 | 2859.5 |
| 47.5° | 20907.8 | 14906.2 | 7589.0 | 5512.3 | 4294.6 | 3827.1 | 3424.8 | 3196.5 | 2957.3 | 2805.1 | 2794.2 |
| 50°   | 20201.1 | 13721.1 | 6480.0 | 4783.9 | 3881.5 | 3544.4 | 3348.7 | 3163.9 | 2968.2 | 2848.6 | 2826.8 |
| 52.5° | 19298.7 | 12383.8 | 5458.0 | 4077.2 | 3522.7 | 3294.4 | 3272.6 | 3142.1 | 2989.9 | 2859.5 | 2805.1 |
| 53°   | 19092.1 | 12035.8 | 5262.3 | 3957.6 | 3468.3 | 3261.7 | 3250.9 | 3142.1 | 2968.2 | 2848.6 | 2805.1 |
| 55°   | 18102.7 | 10959.5 | 4642.6 | 3533.6 | 3196.5 | 3153.0 | 3250.9 | 3131.3 | 2913.8 | 2816.0 | 2783.4 |
| 57.5° | 16515.3 | 9546.0  | 4044.6 | 3142.1 | 2913.8 | 3022.6 | 3218.3 | 3087.8 | 2848.6 | 2674.6 | 2620.3 |
| 60°   | 14601.7 | 7926.0  | 3587.9 | 2881.2 | 2707.2 | 2859.5 | 3087.8 | 2935.6 | 2609.4 | 2522.4 | 2511.5 |
| 62.5° | 12318.5 | 6414.8  | 3240.0 | 2663.8 | 2533.3 | 2685.5 | 2892.1 | 2631.1 | 2391.9 | 2326.7 | 2305.0 |
| 65°   | 9622.1  | 5099.2  | 2968.2 | 2500.7 | 2359.3 | 2478.9 | 2620.3 | 2457.2 | 2305.0 | 2250.6 | 2239.7 |
| 67.5° | 7154.1  | 4001.1  | 2750.7 | 2359.3 | 2185.4 | 2261.5 | 2424.6 | 2381.1 | 2250.6 | 2218.0 | 2207.1 |
| 70°   | 4936.1  | 3250.9  | 2555.0 | 2228.9 | 1967.9 | 2054.9 | 2305.0 | 2337.6 | 2207.1 | 2185.4 | 2174.5 |
| 72.5° | 3457.5  | 2750.7  | 2348.5 | 2087.5 | 1794.0 | 1880.9 | 2250.6 | 2250.6 | 2109.3 | 2141.9 | 2120.1 |
| 75°   | 2598.5  | 2315.8  | 2109.3 | 1913.6 | 1576.5 | 1707.0 | 2174.5 | 2152.8 | 2011.4 | 2152.8 | 2098.4 |
| 77.5° | 1957.0  | 1870.1  | 1826.6 | 1696.1 | 1380.8 | 1511.3 | 2022.3 | 1978.8 | 1794.0 | 1804.8 | 1707.0 |
| 80°   | 1424.3  | 1446.0  | 1565.6 | 1446.0 | 1152.5 | 1250.3 | 1707.0 | 1685.2 | 1456.9 | 1500.4 | 1380.8 |
| 82.5° | 1022.0  | 1076.4  | 1337.3 | 1163.4 | 837.2  | 891.5  | 1174.2 | 1272.1 | 1141.6 | 1076.4 | 1098.1 |
| 85°   | 771.9   | 804.6   | 1076.4 | 858.9  | 521.9  | 587.1  | 804.6  | 913.3  | 891.5  | 826.3  | 837.2  |
| 87.5° | 326.2   | 369.7   | 500.1  | 402.3  | 304.4  | 304.4  | 500.1  | 641.5  | 576.2  | 489.3  | 511.0  |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-2

Test Date: 10/09/2024

Luminaire Tested: GSS-SB1A-722-U-5WQ

Data in this report applies to families of products including GSS-SB1A-722-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-2  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-722-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 2200K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2160  
 CIE u': 0.2927  
 CIE v': 0.5388  
 Duv: 0.0015  
 CIE x: 0.5130  
 CIE y: 0.4197  
 CIE z: 0.0674  
 Peak Wavelength (nm): 609  
 Dominant Wavelength (nm): 587  
 Purity: 79.96089  
 Rf: 70.6  
 Rg: 97.6

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 71.9 |      |       |
| R1:       | 68.7 | R9:  | -17.8 |
| R2:       | 82.6 | R10: | 60.5  |
| R3:       | 95.5 | R11: | 60.2  |
| R4:       | 66.4 | R12: | 48.2  |
| R5:       | 65.4 | R13: | 70.7  |
| R6:       | 75.9 | R14: | 96.8  |
| R7:       | 77.2 | R15: | 61.8  |
| R8:       | 43.5 |      |       |



**Test Conditions**

Stabilization Time: 21M  
 Operation Time: 1H 21M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-2

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-2

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2200K 7-step quadrangle

REPORT NUMBER: SP1-2407-184-2

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-2

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 0.8**

| $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) | $\lambda$<br>(nm) | Power<br>W <sup>^</sup> /nm | Lumens<br>( $\phi$ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360               | 0                           | NR                      | 490               | 27                          | NR                      | 620               | 966                         | NR                      | 750               | 46                          | NR                      | 880               | 1                           | NR                      |
| 365               | 0                           | NR                      | 495               | 42                          | NR                      | 625               | 930                         | NR                      | 755               | 39                          | NR                      | 885               | 1                           | NR                      |
| 370               | 0                           | NR                      | 500               | 67                          | NR                      | 630               | 888                         | NR                      | 760               | 34                          | NR                      | 890               | 1                           | NR                      |
| 375               | 0                           | NR                      | 505               | 101                         | NR                      | 635               | 835                         | NR                      | 765               | 30                          | NR                      | 895               | 1                           | NR                      |
| 380               | 0                           | NR                      | 510               | 139                         | NR                      | 640               | 778                         | NR                      | 770               | 26                          | NR                      | 900               | 1                           | NR                      |
| 385               | 0                           | NR                      | 515               | 183                         | NR                      | 645               | 717                         | NR                      | 775               | 22                          | NR                      | 905               | 1                           | NR                      |
| 390               | 0                           | NR                      | 520               | 224                         | NR                      | 650               | 656                         | NR                      | 780               | 19                          | NR                      | 910               | 1                           | NR                      |
| 395               | 0                           | NR                      | 525               | 262                         | NR                      | 655               | 595                         | NR                      | 785               | 17                          | NR                      | 915               | 1                           | NR                      |
| 400               | 1                           | NR                      | 530               | 299                         | NR                      | 660               | 536                         | NR                      | 790               | 15                          | NR                      | 920               | 1                           | NR                      |
| 405               | 3                           | NR                      | 535               | 332                         | NR                      | 665               | 480                         | NR                      | 795               | 13                          | NR                      | 925               | 1                           | NR                      |
| 410               | 7                           | NR                      | 540               | 365                         | NR                      | 670               | 425                         | NR                      | 800               | 11                          | NR                      | 930               | 1                           | NR                      |
| 415               | 17                          | NR                      | 545               | 400                         | NR                      | 675               | 376                         | NR                      | 805               | 10                          | NR                      | 935               | 0                           | NR                      |
| 420               | 36                          | NR                      | 550               | 437                         | NR                      | 680               | 332                         | NR                      | 810               | 8                           | NR                      | 940               | 0                           | NR                      |
| 425               | 67                          | NR                      | 555               | 479                         | NR                      | 685               | 291                         | NR                      | 815               | 8                           | NR                      | 945               | 0                           | NR                      |
| 430               | 105                         | NR                      | 560               | 525                         | NR                      | 690               | 255                         | NR                      | 820               | 7                           | NR                      | 950               | 0                           | NR                      |
| 435               | 141                         | NR                      | 565               | 579                         | NR                      | 695               | 221                         | NR                      | 825               | 6                           | NR                      | 955               | 0                           | NR                      |
| 440               | 169                         | NR                      | 570               | 639                         | NR                      | 700               | 192                         | NR                      | 830               | 5                           | NR                      | 960               | 0                           | NR                      |
| 445               | 173                         | NR                      | 575               | 703                         | NR                      | 705               | 167                         | NR                      | 835               | 4                           | NR                      | 965               | 0                           | NR                      |
| 450               | 136                         | NR                      | 580               | 769                         | NR                      | 710               | 144                         | NR                      | 840               | 4                           | NR                      | 970               | 0                           | NR                      |
| 455               | 80                          | NR                      | 585               | 832                         | NR                      | 715               | 125                         | NR                      | 845               | 3                           | NR                      | 975               | 0                           | NR                      |
| 460               | 45                          | NR                      | 590               | 890                         | NR                      | 720               | 109                         | NR                      | 850               | 3                           | NR                      | 980               | 0                           | NR                      |
| 465               | 32                          | NR                      | 595               | 937                         | NR                      | 725               | 94                          | NR                      | 855               | 3                           | NR                      | 985               | 0                           | NR                      |
| 470               | 23                          | NR                      | 600               | 972                         | NR                      | 730               | 81                          | NR                      | 860               | 2                           | NR                      | 990               | 0                           | NR                      |
| 475               | 18                          | NR                      | 605               | 992                         | NR                      | 735               | 70                          | NR                      | 865               | 2                           | NR                      | 995               | 0                           | NR                      |
| 480               | 18                          | NR                      | 610               | 998                         | NR                      | 740               | 61                          | NR                      | 870               | 2                           | NR                      | 1000              | 0                           | NR                      |
| 485               | 20                          | NR                      | 615               | 990                         | NR                      | 745               | 53                          | NR                      | 875               | 2                           | NR                      |                   |                             |                         |

REPORT NUMBER: SP1-2407-184-2

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 1.21**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 27                       | NR            | 620    | 966                      | NR            | 750    | 46                       | NR            | 880    | 1                        | NR            |
| 365    | 0                        | NR            | 495    | 42                       | NR            | 625    | 930                      | NR            | 755    | 39                       | NR            | 885    | 1                        | NR            |
| 370    | 0                        | NR            | 500    | 67                       | NR            | 630    | 888                      | NR            | 760    | 34                       | NR            | 890    | 1                        | NR            |
| 375    | 0                        | NR            | 505    | 101                      | NR            | 635    | 835                      | NR            | 765    | 30                       | NR            | 895    | 1                        | NR            |
| 380    | 0                        | NR            | 510    | 139                      | NR            | 640    | 778                      | NR            | 770    | 26                       | NR            | 900    | 1                        | NR            |
| 385    | 0                        | NR            | 515    | 183                      | NR            | 645    | 717                      | NR            | 775    | 22                       | NR            | 905    | 1                        | NR            |
| 390    | 0                        | NR            | 520    | 224                      | NR            | 650    | 656                      | NR            | 780    | 19                       | NR            | 910    | 1                        | NR            |
| 395    | 0                        | NR            | 525    | 262                      | NR            | 655    | 595                      | NR            | 785    | 17                       | NR            | 915    | 1                        | NR            |
| 400    | 1                        | NR            | 530    | 299                      | NR            | 660    | 536                      | NR            | 790    | 15                       | NR            | 920    | 1                        | NR            |
| 405    | 3                        | NR            | 535    | 332                      | NR            | 665    | 480                      | NR            | 795    | 13                       | NR            | 925    | 1                        | NR            |
| 410    | 7                        | NR            | 540    | 365                      | NR            | 670    | 425                      | NR            | 800    | 11                       | NR            | 930    | 1                        | NR            |
| 415    | 17                       | NR            | 545    | 400                      | NR            | 675    | 376                      | NR            | 805    | 10                       | NR            | 935    | 0                        | NR            |
| 420    | 36                       | NR            | 550    | 437                      | NR            | 680    | 332                      | NR            | 810    | 8                        | NR            | 940    | 0                        | NR            |
| 425    | 67                       | NR            | 555    | 479                      | NR            | 685    | 291                      | NR            | 815    | 8                        | NR            | 945    | 0                        | NR            |
| 430    | 105                      | NR            | 560    | 525                      | NR            | 690    | 255                      | NR            | 820    | 7                        | NR            | 950    | 0                        | NR            |
| 435    | 141                      | NR            | 565    | 579                      | NR            | 695    | 221                      | NR            | 825    | 6                        | NR            | 955    | 0                        | NR            |
| 440    | 169                      | NR            | 570    | 639                      | NR            | 700    | 192                      | NR            | 830    | 5                        | NR            | 960    | 0                        | NR            |
| 445    | 173                      | NR            | 575    | 703                      | NR            | 705    | 167                      | NR            | 835    | 4                        | NR            | 965    | 0                        | NR            |
| 450    | 136                      | NR            | 580    | 769                      | NR            | 710    | 144                      | NR            | 840    | 4                        | NR            | 970    | 0                        | NR            |
| 455    | 80                       | NR            | 585    | 832                      | NR            | 715    | 125                      | NR            | 845    | 3                        | NR            | 975    | 0                        | NR            |
| 460    | 45                       | NR            | 590    | 890                      | NR            | 720    | 109                      | NR            | 850    | 3                        | NR            | 980    | 0                        | NR            |
| 465    | 32                       | NR            | 595    | 937                      | NR            | 725    | 94                       | NR            | 855    | 3                        | NR            | 985    | 0                        | NR            |
| 470    | 23                       | NR            | 600    | 972                      | NR            | 730    | 81                       | NR            | 860    | 2                        | NR            | 990    | 0                        | NR            |
| 475    | 18                       | NR            | 605    | 992                      | NR            | 735    | 70                       | NR            | 865    | 2                        | NR            | 995    | 0                        | NR            |
| 480    | 18                       | NR            | 610    | 998                      | NR            | 740    | 61                       | NR            | 870    | 2                        | NR            | 1000   | 0                        | NR            |
| 485    | 20                       | NR            | 615    | 990                      | NR            | 745    | 53                       | NR            | 875    | 2                        | NR            |        |                          |               |

**Summary**

$R_f = 70.6$   
 $R_g = 97.6$   
 CIE  $R_a = 71.9$   
 $R_9 = -17.8$



**Color Vector Graphics**



**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 87 | CES26 = 60 | CES51 = 74 | CES76 = 58 |
| CES02 = 65 | CES27 = 77 | CES52 = 77 | CES77 = 82 |
| CES03 = 32 | CES28 = 85 | CES53 = 65 | CES78 = 65 |
| CES04 = 72 | CES29 = 50 | CES54 = 77 | CES79 = 86 |
| CES05 = 52 | CES30 = 49 | CES55 = 74 | CES80 = 85 |
| CES06 = 53 | CES31 = 55 | CES56 = 64 | CES81 = 61 |
| CES07 = 44 | CES32 = 55 | CES57 = 60 | CES82 = 93 |
| CES08 = 43 | CES33 = 55 | CES58 = 64 | CES83 = 83 |
| CES09 = 29 | CES34 = 75 | CES59 = 84 | CES84 = 93 |
| CES10 = 79 | CES35 = 88 | CES60 = 89 | CES85 = 81 |
| CES11 = 62 | CES36 = 78 | CES61 = 84 | CES86 = 55 |
| CES12 = 68 | CES37 = 82 | CES62 = 68 | CES87 = 79 |
| CES13 = 45 | CES38 = 54 | CES63 = 68 | CES88 = 72 |
| CES14 = 75 | CES39 = 90 | CES64 = 69 | CES89 = 62 |
| CES15 = 72 | CES40 = 86 | CES65 = 66 | CES90 = 67 |
| CES16 = 49 | CES41 = 75 | CES66 = 64 | CES91 = 89 |
| CES17 = 51 | CES42 = 83 | CES67 = 63 | CES92 = 67 |
| CES18 = 57 | CES43 = 68 | CES68 = 71 | CES93 = 78 |
| CES19 = 74 | CES44 = 98 | CES69 = 81 | CES94 = 52 |
| CES20 = 68 | CES45 = 76 | CES70 = 65 | CES95 = 76 |
| CES21 = 89 | CES46 = 68 | CES71 = 64 | CES96 = 78 |
| CES22 = 81 | CES47 = 60 | CES72 = 88 | CES97 = 76 |
| CES23 = 92 | CES48 = 47 | CES73 = 59 | CES98 = 71 |
| CES24 = 92 | CES49 = 65 | CES74 = 85 | CES99 = 65 |
| CES25 = 74 | CES50 = 74 | CES75 = 66 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)