

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1437551

Luminaire Tested: **GALN-SB5C-730-U-T3LG-HSS**

Issue Date: 03/27/202

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



**Test Information**

Test Method: LM-79-08  
 Report Number: P1437551  
 Test Lab: INNOVATION CENTER(G1)  
 Issue Date: 03/27/202  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: McGRAW-EDISON  
 Catalog Number: GALN-SB5C-730-U-T3LG-HSS  
 Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 615mA 5xLight  
 Square PACKAGE 70CRI 3000K FIXTURE w/ TYPE III LOW GLARE WITH HOUSE SIDE  
 SHIELD  
 Light Source: (130) 3000K CCT, 70 CRI LEDS  
 Ballast/Driver: ELECTRONIC DRIVER  
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a                 | good             | reflector          |
| b                 | good             | lens               |
| c                 | good             | housing            |
| d                 | good             | cord               |


**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 28908 lumens  
 Efficiency: N/A  
 Efficacy: 115.9 lumens/watt  
 Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
 IES Classification: Type III - Short  
 BUG Rating: B2 - U0 - G4  
  
 Input Watts (W): 249.5  
 Input Voltage (V): 120  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: 0.97  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 28.75 FT

REPORT NUMBER: P1437551  
 CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 17.8 fc  
 Type III - Short - N/A

REPORT NUMBER: P1437551  
CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS

### Luminous Intensity Polar Plot



— Vertical Plane Through 80-Deg Lateral    - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P1437551  
 CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS


**FLUX DISTRIBUTION:**

|                    |           | Downward | Upward | Total   |
|--------------------|-----------|----------|--------|---------|
| <b>House Side</b>  | Lumens    | 3514.1   | 0.0    | 3514.1  |
|                    | % Fixture | 12.2     | 0.0    | 12.2    |
| <b>Street Side</b> | Lumens    | 25394.0  | 0.0    | 25394.0 |
|                    | % Fixture | 87.8     | 0.0    | 87.8    |
| <b>Total</b>       | Lumens    | 28908.0  | 0.0    | 28908.0 |
|                    | % Fixture | 100.0    | 0.0    | 100.0   |

**Coefficient of Utilization**

**ZONAL LUMENS:**

| Zone      | Lumens  | % Fixture |
|-----------|---------|-----------|
| 0°-10°    | 337.9   | 1.2       |
| 10°-20°   | 890.9   | 3.1       |
| 20°-30°   | 1744.2  | 6.0       |
| 30°-40°   | 3548.4  | 12.3      |
| 40°-50°   | 5982.0  | 20.7      |
| 50°-60°   | 7643.2  | 26.4      |
| 60°-70°   | 6525.5  | 22.6      |
| 70°-80°   | 2085.3  | 7.2       |
| 80°-90°   | 150.6   | 0.5       |
| 90°-100°  | 0.0     | 0.0       |
| 100°-110° | 0.0     | 0.0       |
| 110°-120° | 0.0     | 0.0       |
| 120°-130° | 0.0     | 0.0       |
| 130°-140° | 0.0     | 0.0       |
| 140°-150° | 0.0     | 0.0       |
| 150°-160° | 0.0     | 0.0       |
| 160°-170° | 0.0     | 0.0       |
| 170°-180° | 0.0     | 0.0       |
| 0°-90°    | 28908.0 | 100.0     |
| 0°-180°   | 28908.0 | 100.0     |




REPORT NUMBER: P1437551  
 CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

| Zone           | Lumens  | % Fixture | Zone Rating/Lumen Limit |      |          |
|----------------|---------|-----------|-------------------------|------|----------|
|                |         |           | B                       | U    | G        |
| FL (0°-30°)    | 2055.4  | 7.1       |                         |      |          |
| FM (30°-60°)   | 14971.2 | 51.8      |                         |      |          |
| FH (60°-80°)   | 8224.6  | 28.5      |                         |      | G4/12000 |
| FVH (80°-90°)  | 142.7   | 0.5       |                         |      | G2/225   |
| BL (0°-30°)    | 917.6   | 3.2       | B2/1000                 |      |          |
| BM (30°-60°)   | 2202.4  | 7.6       | B2/2500                 |      |          |
| BH (60°-80°)   | 386.2   | 1.3       | B1/500                  |      | G1/500   |
| BVH (80°-90°)  | 7.8     | 0.0       |                         |      | G0/10    |
| UL (90°-100°)  | 0.0     | 0.0       |                         | U0/0 |          |
| UH (100°-180°) | 0.0     | 0.0       |                         | U0/0 |          |

**BUG Rating: B2-U0-G4**  
 Type III Short





REPORT NUMBER: P1437551

CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      | 5°      | 15°     | 25°     | 35°     | 45°     | 55°     | 65°     | 75°     | 80°     | 85°     |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0°    | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  | 4026.8  |
| 2.5°  | 4051.5  | 4059.7  | 4051.5  | 4059.7  | 4076.2  | 4067.9  | 4100.8  | 4092.6  | 4092.6  | 4084.4  | 4051.5  |
| 5°    | 3821.4  | 3829.6  | 3846.0  | 3887.1  | 3944.7  | 4002.2  | 4076.2  | 4125.5  | 4174.8  | 4166.6  | 4133.7  |
| 7.5°  | 3369.4  | 3385.8  | 3451.6  | 3533.8  | 3722.8  | 3895.4  | 4084.4  | 4207.6  | 4314.5  | 4347.3  | 4322.7  |
| 10°   | 3114.6  | 3131.1  | 3172.2  | 3254.3  | 3426.9  | 3714.6  | 4084.4  | 4339.1  | 4528.1  | 4593.9  | 4602.1  |
| 12.5° | 3090.0  | 3098.2  | 3131.1  | 3221.5  | 3369.4  | 3615.9  | 4076.2  | 4511.7  | 4832.2  | 4930.8  | 4963.7  |
| 15°   | 3106.4  | 3122.9  | 3155.7  | 3229.7  | 3402.3  | 3681.7  | 4141.9  | 4782.9  | 5234.9  | 5374.6  | 5382.8  |
| 17.5° | 3172.2  | 3188.6  | 3229.7  | 3311.9  | 3500.9  | 3854.3  | 4347.3  | 5062.3  | 5719.8  | 5875.9  | 5966.3  |
| 20°   | 3303.7  | 3311.9  | 3361.2  | 3468.0  | 3681.7  | 4067.9  | 4651.4  | 5440.3  | 6303.2  | 6533.4  | 6599.1  |
| 22.5° | 3476.2  | 3500.9  | 3566.6  | 3698.1  | 3969.3  | 4363.8  | 5070.5  | 5900.6  | 6944.3  | 7182.6  | 7297.6  |
| 25°   | 3665.3  | 3698.1  | 3796.7  | 4010.4  | 4355.6  | 4815.8  | 5588.3  | 6508.7  | 7700.3  | 7987.9  | 8144.1  |
| 27.5° | 4051.5  | 4059.7  | 4125.5  | 4396.7  | 4840.4  | 5407.5  | 6245.7  | 7289.4  | 8587.9  | 8924.8  | 9097.4  |
| 30°   | 4898.0  | 4906.2  | 4848.6  | 4922.6  | 5374.6  | 6106.0  | 7018.2  | 8201.6  | 9623.3  | 10091.8 | 10231.5 |
| 32.5° | 5933.4  | 5974.5  | 5966.3  | 5917.0  | 6122.4  | 6804.5  | 7938.6  | 9294.6  | 10839.6 | 11332.7 | 11464.2 |
| 35°   | 7108.6  | 7207.2  | 7182.6  | 7166.1  | 7190.8  | 7700.3  | 8990.5  | 10502.7 | 12220.2 | 12820.2 | 12927.0 |
| 37.5° | 8259.1  | 8283.8  | 8398.8  | 8538.6  | 8555.0  | 8908.4  | 10206.8 | 11784.7 | 13502.3 | 14266.5 | 14430.9 |
| 40°   | 9146.7  | 9228.9  | 9516.5  | 9795.9  | 10083.5 | 10363.0 | 11209.4 | 12820.2 | 14521.3 | 15548.6 | 15622.5 |
| 42.5° | 9837.0  | 10034.2 | 10453.4 | 10888.9 | 11472.4 | 11784.7 | 12162.7 | 13551.6 | 15351.3 | 16690.9 | 16658.0 |
| 45°   | 10675.2 | 10757.4 | 11349.1 | 11924.4 | 12516.1 | 12992.7 | 12984.5 | 14167.9 | 16000.5 | 17668.8 | 17463.4 |
| 47.5° | 11242.3 | 11340.9 | 12146.3 | 12820.2 | 13428.3 | 13666.6 | 13715.9 | 14833.6 | 16896.3 | 18852.2 | 18367.3 |
| 50°   | 11546.4 | 11718.9 | 12598.3 | 13452.9 | 14110.4 | 14184.4 | 14406.2 | 15704.7 | 18071.5 | 20421.9 | 19509.7 |
| 52.5° | 11579.2 | 11743.6 | 12754.4 | 13855.6 | 14570.6 | 14718.5 | 15096.6 | 16690.9 | 19213.8 | 21679.2 | 20167.1 |
| 55°   | 10897.1 | 10995.8 | 12565.4 | 13921.4 | 14932.2 | 15277.4 | 16049.9 | 17603.1 | 19879.5 | 22262.7 | 20109.6 |
| 57.5° | 10256.1 | 10354.7 | 11718.9 | 13806.3 | 15302.0 | 16008.8 | 17068.9 | 18227.6 | 19361.7 | 21539.5 | 18827.6 |
| 60°   | 9705.5  | 9754.8  | 10995.8 | 13272.2 | 15441.7 | 16723.7 | 17948.2 | 17611.3 | 18022.2 | 19805.5 | 16633.3 |
| 62.5° | 8670.0  | 8702.9  | 10173.9 | 12310.6 | 15162.3 | 17274.3 | 18252.3 | 16304.6 | 16551.2 | 17414.0 | 14052.9 |
| 65°   | 6549.8  | 6673.1  | 8020.8  | 11587.5 | 14702.1 | 17529.1 | 17545.5 | 14710.3 | 14455.6 | 14250.1 | 11053.3 |
| 67.5° | 4446.0  | 4585.7  | 5399.3  | 10420.5 | 13954.2 | 17635.9 | 16173.1 | 12647.6 | 11012.2 | 9952.1  | 7240.1  |
| 70°   | 3550.2  | 3550.2  | 3829.6  | 8374.2  | 12179.2 | 16271.7 | 14472.0 | 9549.4  | 6993.6  | 5497.9  | 3878.9  |
| 72.5° | 2333.9  | 2342.1  | 2605.1  | 5317.1  | 8637.2  | 12409.3 | 11801.1 | 5522.5  | 3632.4  | 2802.4  | 1914.8  |
| 75°   | 846.5   | 846.5   | 1142.3  | 2128.5  | 4569.2  | 7388.0  | 7190.8  | 2638.0  | 1972.3  | 1528.6  | 1158.7  |
| 77.5° | 452.0   | 468.4   | 550.6   | 879.3   | 1750.4  | 3007.8  | 2810.6  | 1347.8  | 1117.7  | 953.3   | 723.2   |
| 80°   | 304.1   | 312.3   | 369.8   | 542.4   | 846.5   | 1158.7  | 904.0   | 756.1   | 756.1   | 641.0   | 484.9   |
| 82.5° | 164.4   | 172.6   | 246.5   | 353.4   | 452.0   | 542.4   | 435.6   | 443.8   | 534.2   | 435.6   | 279.4   |
| 85°   | 115.1   | 115.1   | 189.0   | 254.8   | 254.8   | 263.0   | 189.0   | 279.4   | 312.3   | 271.2   | 189.0   |
| 87.5° | 65.7    | 65.7    | 106.8   | 123.3   | 123.3   | 115.1   | 57.5    | 98.6    | 123.3   | 139.7   | 82.2    |
| 90°   | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     | 0.0     |



REPORT NUMBER: P1437551

CATALOG NUMBER: GALN-SB5C-730-U-T3LG-HSS

**CANDELA DISTRIBUTION (continued):**

|       | 90°     | 95°     | 105°   | 115°   | 125°   | 135°   | 145°   | 155°   | 165°   | 175°   | 180°   |
|-------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0°    | 4026.8  | 4026.8  | 4026.8 | 4026.8 | 4026.8 | 4026.8 | 4026.8 | 4026.8 | 4026.8 | 4026.8 | 4026.8 |
| 2.5°  | 4043.3  | 4018.6  | 3969.3 | 3870.7 | 3821.4 | 3755.6 | 3698.1 | 3624.2 | 3607.7 | 3599.5 | 3566.6 |
| 5°    | 4109.0  | 4059.7  | 3911.8 | 3698.1 | 3517.3 | 3344.7 | 3172.2 | 3073.6 | 2991.4 | 2950.3 | 2942.1 |
| 7.5°  | 4273.4  | 4174.8  | 3903.6 | 3525.5 | 3188.6 | 2892.8 | 2638.0 | 2416.1 | 2301.1 | 2202.4 | 2210.7 |
| 10°   | 4519.9  | 4363.8  | 3920.0 | 3361.2 | 2859.9 | 2383.2 | 2013.4 | 1692.9 | 1462.8 | 1356.0 | 1347.8 |
| 12.5° | 4848.6  | 4626.8  | 3977.5 | 3196.8 | 2457.2 | 1791.5 | 1323.1 | 1134.1 | 1084.8 | 1076.6 | 1068.3 |
| 15°   | 5251.3  | 4939.0  | 4035.1 | 2983.2 | 1914.8 | 1240.9 | 1076.6 | 1035.5 | 1027.3 | 1019.0 | 1019.0 |
| 17.5° | 5736.2  | 5300.6  | 4067.9 | 2621.6 | 1397.1 | 1068.3 | 1010.8 | 986.2  | 977.9  | 969.7  | 969.7  |
| 20°   | 6344.3  | 5703.3  | 4109.0 | 2161.3 | 1183.4 | 1027.3 | 961.5  | 928.6  | 920.4  | 920.4  | 912.2  |
| 22.5° | 6944.3  | 6155.3  | 4076.2 | 1758.7 | 1142.3 | 977.9  | 904.0  | 871.1  | 854.7  | 854.7  | 846.5  |
| 25°   | 7634.6  | 6615.5  | 3977.5 | 1586.1 | 1134.1 | 936.9  | 846.5  | 797.2  | 772.5  | 764.3  | 764.3  |
| 27.5° | 8423.5  | 7141.5  | 3821.4 | 1594.3 | 1134.1 | 904.0  | 772.5  | 706.8  | 690.3  | 673.9  | 673.9  |
| 30°   | 9327.5  | 7782.5  | 3706.3 | 1701.1 | 1150.5 | 871.1  | 706.8  | 624.6  | 599.9  | 583.5  | 591.7  |
| 32.5° | 10363.0 | 8497.5  | 3698.1 | 1873.7 | 1175.2 | 821.8  | 632.8  | 542.4  | 517.7  | 509.5  | 517.7  |
| 35°   | 11538.1 | 9385.0  | 3887.1 | 2005.2 | 1109.4 | 715.0  | 542.4  | 468.4  | 443.8  | 443.8  | 452.0  |
| 37.5° | 12844.8 | 10404.1 | 4141.9 | 1972.3 | 895.8  | 567.0  | 468.4  | 410.9  | 386.2  | 394.5  | 402.7  |
| 40°   | 14036.4 | 11201.2 | 4183.0 | 1684.7 | 673.9  | 484.9  | 402.7  | 361.6  | 345.2  | 353.4  | 361.6  |
| 42.5° | 14940.4 | 11842.2 | 3788.5 | 1306.7 | 567.0  | 410.9  | 345.2  | 312.3  | 304.1  | 320.5  | 320.5  |
| 45°   | 15671.8 | 12097.0 | 3163.9 | 969.7  | 501.3  | 353.4  | 304.1  | 287.6  | 271.2  | 279.4  | 279.4  |
| 47.5° | 16436.1 | 12138.1 | 2580.5 | 780.7  | 443.8  | 320.5  | 279.4  | 263.0  | 246.5  | 246.5  | 246.5  |
| 50°   | 17175.7 | 12039.4 | 1972.3 | 690.3  | 410.9  | 287.6  | 254.8  | 238.3  | 221.9  | 213.7  | 213.7  |
| 52.5° | 17356.5 | 11250.5 | 1446.4 | 641.0  | 378.0  | 271.2  | 238.3  | 221.9  | 205.5  | 197.2  | 197.2  |
| 55°   | 16855.2 | 9754.8  | 1134.1 | 575.3  | 345.2  | 246.5  | 221.9  | 205.5  | 180.8  | 172.6  | 172.6  |
| 57.5° | 15203.4 | 7437.3  | 904.0  | 493.1  | 312.3  | 238.3  | 205.5  | 189.0  | 164.4  | 156.1  | 156.1  |
| 60°   | 13058.5 | 5276.0  | 731.4  | 402.7  | 287.6  | 213.7  | 189.0  | 164.4  | 147.9  | 131.5  | 131.5  |
| 62.5° | 10683.5 | 3788.5  | 591.7  | 336.9  | 271.2  | 189.0  | 172.6  | 147.9  | 115.1  | 90.4   | 90.4   |
| 65°   | 8193.4  | 2720.2  | 460.2  | 271.2  | 246.5  | 164.4  | 147.9  | 123.3  | 90.4   | 65.7   | 65.7   |
| 67.5° | 5300.6  | 1758.7  | 345.2  | 238.3  | 189.0  | 139.7  | 115.1  | 98.6   | 82.2   | 57.5   | 49.3   |
| 70°   | 2794.1  | 1027.3  | 254.8  | 205.5  | 139.7  | 106.8  | 98.6   | 82.2   | 65.7   | 41.1   | 41.1   |
| 72.5° | 1446.4  | 673.9   | 189.0  | 180.8  | 106.8  | 74.0   | 82.2   | 65.7   | 49.3   | 24.7   | 24.7   |
| 75°   | 928.6   | 452.0   | 139.7  | 147.9  | 65.7   | 57.5   | 57.5   | 41.1   | 24.7   | 16.4   | 8.2    |
| 77.5° | 599.9   | 304.1   | 98.6   | 123.3  | 41.1   | 32.9   | 32.9   | 16.4   | 8.2    | 0.0    | 0.0    |
| 80°   | 353.4   | 189.0   | 65.7   | 82.2   | 16.4   | 16.4   | 8.2    | 0.0    | 0.0    | 0.0    | 0.0    |
| 82.5° | 180.8   | 98.6    | 32.9   | 32.9   | 8.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 85°   | 115.1   | 49.3    | 8.2    | 8.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 87.5° | 57.5    | 16.4    | 8.2    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |
| 90°   | 0.0     | 0.0     | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    |

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-4

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-730-U-5WQ

Data in this report applies to families of products including GSS-SB1A-730-U-5WQ

**Test Information**

Test Method: LM-79-2019  
 Report Number: SP1-2407-184-4  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Photometer: SP1 - 76IN SPHERE  
 Measurement Geometry: 4π  
 Issue Date: 10/15/2024  
 Manufacturer: COOPER LIGHTING SOLUTIONS  
 Product Line: McGraw-Edison  
 Catalog Number: **GSS-SB1A-730-U-5WQ**  
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 70 CRI 3000K CCT 26 LEDS

**Spectral Parameters**

CCT (K): 2985  
 CIE u': 0.2504  
 CIE v': 0.5243  
 Duv: 0.0019  
 CIE x: 0.4408  
 CIE y: 0.4101  
 CIE z: 0.1491  
 Peak Wavelength (nm): 595  
 Dominant Wavelength (nm): 582  
 Purity: 55.41818  
 Rf: 73.8  
 Rg: 94.4

|           |      |      |       |
|-----------|------|------|-------|
| CRI (Ra): | 70.8 |      |       |
| R1:       | 66.3 | R9:  | -43.2 |
| R2:       | 80.6 | R10: | 57.6  |
| R3:       | 94.5 | R11: | 64.8  |
| R4:       | 68.2 | R12: | 53.5  |
| R5:       | 66.5 | R13: | 68.7  |
| R6:       | 74.7 | R14: | 97.0  |
| R7:       | 76.2 | R15: | 56.4  |
| R8:       | 39.6 |      |       |



**Test Conditions**

Stabilization Time: 36M  
 Operation Time: 1H 36M  
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-4

| Measurement and Test Equipment |                       |                  |                      |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument                     | Identification Number | Calibration Date | Calibration Due Date |
| Photometer                     | IN0058                | 6/18/2024        | 12/18/2024           |
| Power Meter                    | INXT2011004           | 2/8/2024         | 2/8/2025             |
| AC Power Source                | IN0063                | 10/24/2023       | 10/24/2024           |
| DC Power Source                | IN0208                | 10/24/2023       | 10/24/2024           |
| Sphere Thermometer             | IN0085                | 10/24/2023       | 10/24/2024           |
| Room Thermometer               | IN0046                | 10/24/2023       | 10/24/2024           |

REPORT NUMBER: SP1-2407-184-4

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 3000K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-4

**Photopic Flux vs. Wavelength**



**Photopic Lumens: NR**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-4

**Scotopic Flux vs. Wavelength**



**Scotopic Lumens: NR**

**S/P: 1.19**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

REPORT NUMBER: SP1-2407-184-4

**Melanopic Flux vs. Wavelength**



**Melanopic Lumens: NR**

**M/P: 2.13**

| λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) | λ (nm) | Power W <sup>^</sup> /nm | Lumens (φ/nm) |
|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|--------|--------------------------|---------------|
| 360    | 0                        | NR            | 490    | 142                      | NR            | 620    | 803                      | NR            | 750    | 17                       | NR            | 880    | 0                        | NR            |
| 365    | 0                        | NR            | 495    | 189                      | NR            | 625    | 734                      | NR            | 755    | 15                       | NR            | 885    | 0                        | NR            |
| 370    | 0                        | NR            | 500    | 240                      | NR            | 630    | 670                      | NR            | 760    | 13                       | NR            | 890    | 0                        | NR            |
| 375    | 0                        | NR            | 505    | 290                      | NR            | 635    | 600                      | NR            | 765    | 11                       | NR            | 895    | 0                        | NR            |
| 380    | 0                        | NR            | 510    | 335                      | NR            | 640    | 535                      | NR            | 770    | 9                        | NR            | 900    | 0                        | NR            |
| 385    | 0                        | NR            | 515    | 375                      | NR            | 645    | 473                      | NR            | 775    | 8                        | NR            | 905    | 0                        | NR            |
| 390    | 1                        | NR            | 520    | 408                      | NR            | 650    | 415                      | NR            | 780    | 7                        | NR            | 910    | 0                        | NR            |
| 395    | 2                        | NR            | 525    | 434                      | NR            | 655    | 362                      | NR            | 785    | 6                        | NR            | 915    | 0                        | NR            |
| 400    | 4                        | NR            | 530    | 461                      | NR            | 660    | 313                      | NR            | 790    | 5                        | NR            | 920    | 0                        | NR            |
| 405    | 8                        | NR            | 535    | 486                      | NR            | 665    | 271                      | NR            | 795    | 4                        | NR            | 925    | 0                        | NR            |
| 410    | 16                       | NR            | 540    | 514                      | NR            | 670    | 231                      | NR            | 800    | 4                        | NR            | 930    | 0                        | NR            |
| 415    | 33                       | NR            | 545    | 549                      | NR            | 675    | 198                      | NR            | 805    | 3                        | NR            | 935    | 0                        | NR            |
| 420    | 69                       | NR            | 550    | 591                      | NR            | 680    | 169                      | NR            | 810    | 3                        | NR            | 940    | 0                        | NR            |
| 425    | 131                      | NR            | 555    | 640                      | NR            | 685    | 144                      | NR            | 815    | 2                        | NR            | 945    | 0                        | NR            |
| 430    | 227                      | NR            | 560    | 695                      | NR            | 690    | 123                      | NR            | 820    | 2                        | NR            | 950    | 0                        | NR            |
| 435    | 369                      | NR            | 565    | 757                      | NR            | 695    | 104                      | NR            | 825    | 2                        | NR            | 955    | 0                        | NR            |
| 440    | 517                      | NR            | 570    | 822                      | NR            | 700    | 88                       | NR            | 830    | 2                        | NR            | 960    | 0                        | NR            |
| 445    | 498                      | NR            | 575    | 882                      | NR            | 705    | 75                       | NR            | 835    | 1                        | NR            | 965    | 0                        | NR            |
| 450    | 315                      | NR            | 580    | 935                      | NR            | 710    | 63                       | NR            | 840    | 1                        | NR            | 970    | 0                        | NR            |
| 455    | 204                      | NR            | 585    | 972                      | NR            | 715    | 54                       | NR            | 845    | 1                        | NR            | 975    | 0                        | NR            |
| 460    | 145                      | NR            | 590    | 996                      | NR            | 720    | 46                       | NR            | 850    | 1                        | NR            | 980    | 0                        | NR            |
| 465    | 100                      | NR            | 595    | 1000                     | NR            | 725    | 39                       | NR            | 855    | 1                        | NR            | 985    | 0                        | NR            |
| 470    | 78                       | NR            | 600    | 989                      | NR            | 730    | 33                       | NR            | 860    | 1                        | NR            | 990    | 0                        | NR            |
| 475    | 76                       | NR            | 605    | 960                      | NR            | 735    | 28                       | NR            | 865    | 1                        | NR            | 995    | 0                        | NR            |
| 480    | 83                       | NR            | 610    | 918                      | NR            | 740    | 24                       | NR            | 870    | 1                        | NR            | 1000   | 0                        | NR            |
| 485    | 105                      | NR            | 615    | 864                      | NR            | 745    | 20                       | NR            | 875    | 1                        | NR            |        |                          |               |

**Summary**

$R_f = 73.8$   
 $R_g = 94.4$   
 CIE  $R_a = 70.8$   
 $R_g = -43.2$



**Color Vector Graphics**






**Individual Sample Fidelity Index ( $R_{f,i}$ )**

|            |            |            |            |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 63 | CES51 = 86 | CES76 = 61 |
| CES02 = 62 | CES27 = 83 | CES52 = 86 | CES77 = 81 |
| CES03 = 31 | CES28 = 86 | CES53 = 75 | CES78 = 64 |
| CES04 = 71 | CES29 = 58 | CES54 = 81 | CES79 = 86 |
| CES05 = 49 | CES30 = 61 | CES55 = 80 | CES80 = 86 |
| CES06 = 51 | CES31 = 63 | CES56 = 71 | CES81 = 70 |
| CES07 = 41 | CES32 = 61 | CES57 = 69 | CES82 = 94 |
| CES08 = 40 | CES33 = 65 | CES58 = 72 | CES83 = 88 |
| CES09 = 29 | CES34 = 77 | CES59 = 85 | CES84 = 90 |
| CES10 = 76 | CES35 = 88 | CES60 = 93 | CES85 = 80 |
| CES11 = 59 | CES36 = 89 | CES61 = 86 | CES86 = 60 |
| CES12 = 65 | CES37 = 85 | CES62 = 81 | CES87 = 78 |
| CES13 = 43 | CES38 = 69 | CES63 = 73 | CES88 = 75 |
| CES14 = 74 | CES39 = 93 | CES64 = 72 | CES89 = 66 |
| CES15 = 71 | CES40 = 89 | CES65 = 67 | CES90 = 72 |
| CES16 = 47 | CES41 = 83 | CES66 = 70 | CES91 = 95 |
| CES17 = 50 | CES42 = 87 | CES67 = 68 | CES92 = 59 |
| CES18 = 56 | CES43 = 77 | CES68 = 73 | CES93 = 76 |
| CES19 = 73 | CES44 = 99 | CES69 = 83 | CES94 = 48 |
| CES20 = 66 | CES45 = 83 | CES70 = 66 | CES95 = 70 |
| CES21 = 87 | CES46 = 77 | CES71 = 66 | CES96 = 76 |
| CES22 = 79 | CES47 = 74 | CES72 = 88 | CES97 = 82 |
| CES23 = 92 | CES48 = 62 | CES73 = 59 | CES98 = 73 |
| CES24 = 91 | CES49 = 77 | CES74 = 93 | CES99 = 60 |
| CES25 = 73 | CES50 = 85 | CES75 = 67 |            |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)