

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P949189

Luminaire Tested: **GALN-SB4A-735-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949189
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4A-735-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17914 lumens
Efficiency: N/A
Efficacy: 157.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 114
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.9 fc
 Type IV - Short - N/A

REPORT NUMBER: P949189
CATALOG NUMBER: GALN-SB4A-735-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4552.8	0.0	4552.8
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	13361.2	0.0	13361.2
	% Fixture	74.6	0.0	74.6
Total	Lumens	17914.0	0.0	17914.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.4	1.4
10°-20°	767.1	4.3
20°-30°	1184.9	6.6
30°-40°	1501.6	8.4
40°-50°	2264.7	12.6
50°-60°	3659.0	20.4
60°-70°	4561.6	25.5
70°-80°	2991.2	16.7
80°-90°	739.5	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	17914.0	100.0
0°-180°	17914.0	100.0



REPORT NUMBER: P949189


CATALOG NUMBER: GALN-SB4A-735-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1204.9	6.7			
FM (30°-60°)	5225.1	29.2			
FH (60°-80°)	6321.9	35.3			G3/7500
FVH (80°-90°)	609.2	3.4			G4/750
BL (0°-30°)	991.4	5.5	B2/1000		
BM (30°-60°)	2200.2	12.3	B2/2500		
BH (60°-80°)	1230.9	6.9	B3/2500		G3/2500
BVH (80°-90°)	130.3	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P949189

CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2.5°	2649.1	2628.7	2608.4	2586.8	2565.2	2543.5	2521.7	2501.0	2480.2	2460.0
5°	2848.5	2803.6	2758.7	2713.9	2669.2	2624.1	2579.1	2537.1	2495.0	2455.3
7.5°	3048.9	2974.8	2900.8	2832.4	2763.9	2697.3	2630.6	2571.9	2513.2	2459.1
10°	3202.5	3108.8	3015.2	2924.7	2834.3	2753.4	2672.4	2603.0	2533.5	2466.6
12.5°	3296.6	3193.6	3090.8	2988.3	2885.9	2790.4	2694.9	2616.4	2537.8	2467.6
15°	3353.8	3246.5	3139.2	3028.0	2916.9	2806.9	2697.0	2606.1	2515.1	2437.3
17.5°	3385.9	3277.1	3168.3	3047.0	2925.7	2798.1	2670.5	2561.2	2451.8	2360.3
20°	3421.3	3308.3	3195.1	3061.9	2928.6	2773.9	2619.3	2483.7	2348.2	2241.7
22.5°	3462.5	3347.0	3231.3	3081.9	2932.4	2744.3	2556.2	2392.9	2229.7	2108.4
25°	3515.4	3402.2	3289.0	3118.2	2947.3	2715.0	2482.7	2291.5	2100.4	1976.1
27.5°	3587.2	3479.3	3371.2	3174.9	2978.5	2695.4	2412.3	2198.8	1985.2	1872.1
30°	3684.1	3579.8	3475.5	3248.4	3021.2	2686.2	2351.0	2121.2	1891.5	1796.5
32.5°	3798.5	3695.2	3592.0	3325.0	3058.1	2674.9	2291.5	2054.4	1817.2	1740.7
35°	3937.5	3838.6	3739.6	3412.4	3085.1	2653.5	2222.1	1988.7	1755.3	1691.5
37.5°	4171.4	4045.3	3919.2	3510.2	3101.2	2616.9	2132.7	1911.4	1690.1	1634.3
40°	4524.9	4341.2	4157.4	3634.4	3111.3	2566.6	2021.9	1819.1	1616.4	1565.8
42.5°	4993.8	4728.5	4463.3	3796.9	3130.5	2514.6	1898.8	1717.3	1535.8	1489.2
45°	5572.7	5215.0	4857.2	4010.7	3164.2	2466.3	1768.4	1609.2	1450.0	1402.8
47.5°	6296.8	5793.3	5289.6	4238.5	3187.4	2426.4	1665.3	1523.7	1382.0	1321.0
50°	7245.8	6486.7	5727.5	4449.9	3172.3	2382.9	1593.5	1466.8	1340.2	1260.0
52.5°	8335.2	7215.1	6095.0	4587.1	3079.2	2309.4	1539.8	1429.4	1319.1	1226.9
55°	9495.1	7860.9	6226.9	4556.9	2886.8	2187.7	1488.6	1402.3	1316.0	1230.2
57.5°	10550.0	8318.6	6087.2	4344.0	2600.9	2016.0	1431.1	1370.1	1309.2	1233.6
60°	11187.5	8433.0	5678.3	3947.8	2217.4	1793.1	1368.9	1321.0	1273.1	1223.2
62.5°	10863.8	7951.4	5039.0	3412.2	1785.4	1526.4	1267.4	1235.5	1203.8	1197.6
65°	10215.8	7269.9	4324.1	2865.6	1407.3	1286.4	1165.5	1150.5	1135.4	1136.2
67.5°	9347.6	6459.0	3570.4	2330.2	1090.1	1055.8	1021.3	1029.8	1038.1	1036.0
70°	8304.5	5574.2	2843.8	1834.7	825.7	835.5	845.2	884.2	923.0	923.0
72.5°	7061.5	4614.9	2168.4	1402.7	636.9	666.5	696.2	751.4	806.5	815.8
75°	5489.1	3515.3	1541.5	1018.0	494.6	521.4	548.2	610.1	671.9	714.6
77.5°	3921.9	2460.4	998.9	689.8	380.7	399.0	417.3	477.4	537.4	607.8
80°	2566.8	1585.2	603.5	444.5	285.5	293.0	300.6	351.4	402.2	486.3
82.5°	1492.1	917.5	342.9	273.4	204.0	205.3	206.8	244.3	281.7	353.5
85°	656.5	412.7	169.0	146.1	123.4	122.7	121.9	149.3	176.8	230.2
87.5°	203.2	135.2	67.1	60.6	54.1	53.4	52.7	63.9	75.1	97.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2437.6	2.5°	2419.5	2401.4	2385.1	2368.8	2354.5	2340.3	2325.9	2311.6	2300.6	2289.4
2416.1	5°	2381.8	2347.5	2318.8	2290.2	2264.8	2239.5	2216.5	2193.5	2175.8	2158.0
2408.3	7.5°	2362.8	2317.3	2279.5	2241.7	2209.8	2177.9	2149.7	2121.6	2100.5	2079.6
2412.1	10°	2364.1	2316.1	2278.2	2240.4	2206.1	2171.7	2140.1	2108.4	2083.2	2058.0
2416.8	12.5°	2377.5	2338.4	2313.2	2288.3	2261.2	2234.4	2201.6	2168.9	2136.7	2104.6
2396.7	15°	2377.9	2359.2	2362.6	2366.0	2359.0	2352.0	2323.5	2295.1	2249.3	2203.6
2335.2	17.5°	2342.1	2349.0	2390.2	2431.4	2453.3	2475.1	2452.2	2429.3	2368.7	2308.1
2235.1	20°	2267.2	2299.3	2370.9	2442.5	2488.4	2534.2	2523.6	2513.0	2443.7	2374.5
2121.3	22.5°	2168.9	2216.4	2298.1	2380.0	2439.6	2499.2	2505.7	2512.0	2445.8	2379.7
2011.0	25°	2065.9	2120.7	2194.1	2267.7	2326.4	2385.1	2407.0	2428.8	2374.6	2320.4
1914.6	27.5°	1967.5	2020.5	2080.9	2141.2	2188.3	2235.3	2259.7	2284.2	2245.5	2207.0
1829.8	30°	1871.8	1913.9	1964.0	2014.1	2053.2	2092.3	2112.2	2132.0	2102.6	2073.1
1755.5	32.5°	1780.4	1805.2	1845.2	1885.3	1922.7	1960.3	1982.3	2004.4	1977.4	1950.2
1685.4	35°	1692.2	1699.1	1729.6	1760.1	1797.1	1834.3	1860.7	1887.2	1867.9	1848.7
1611.8	37.5°	1604.3	1596.7	1618.7	1640.5	1677.4	1714.5	1747.2	1779.9	1771.0	1762.1
1531.3	40°	1514.2	1497.1	1512.9	1528.7	1564.4	1600.1	1637.7	1675.5	1677.6	1679.7
1445.8	42.5°	1423.1	1400.4	1413.2	1426.2	1460.0	1494.0	1534.6	1575.3	1586.1	1597.0
1360.7	45°	1338.6	1316.5	1327.3	1338.3	1370.4	1402.6	1444.7	1486.9	1502.5	1518.1
1284.8	47.5°	1266.3	1247.7	1257.9	1268.1	1299.5	1330.9	1372.5	1414.1	1432.1	1450.0
1218.0	50°	1201.5	1185.2	1201.0	1217.0	1246.7	1276.3	1313.5	1350.8	1373.8	1396.9
1168.1	52.5°	1151.9	1135.7	1159.6	1183.5	1210.7	1237.8	1272.5	1307.3	1334.6	1361.9
1141.7	55°	1116.0	1090.3	1124.3	1158.1	1187.4	1216.7	1247.2	1277.5	1306.4	1335.5
1125.8	57.5°	1088.4	1050.9	1087.4	1123.9	1158.3	1192.7	1222.8	1252.9	1282.1	1311.3
1110.9	60°	1062.4	1013.8	1045.8	1077.8	1117.3	1156.8	1187.3	1218.0	1247.3	1276.6
1093.5	62.5°	1032.8	972.2	992.5	1012.8	1058.9	1105.0	1137.6	1170.2	1197.1	1223.9
1056.8	65°	992.3	927.8	935.6	943.4	992.7	1042.1	1073.3	1104.5	1128.2	1151.8
991.4	67.5°	937.7	884.0	881.5	879.1	924.6	970.3	999.9	1029.4	1049.8	1070.2
908.4	70°	870.2	832.0	823.5	815.0	855.1	895.2	920.7	946.2	964.6	983.1
815.9	72.5°	789.8	763.6	751.1	738.7	770.3	801.8	824.8	847.9	865.9	884.0
711.0	75°	690.9	670.7	658.7	646.7	670.2	693.6	714.5	735.4	751.9	768.3
605.9	77.5°	589.7	573.6	561.5	549.4	568.5	587.5	605.4	623.4	640.7	657.9
486.0	80°	472.5	458.9	448.8	438.6	454.5	470.3	485.4	500.5	513.7	526.7
357.5	82.5°	350.9	344.3	337.1	329.9	328.6	327.2	322.0	316.7	344.6	372.6
235.4	85°	228.3	221.2	213.2	205.1	198.3	191.4	176.8	162.1	188.3	214.6
104.0	87.5°	101.1	98.3	96.8	95.3	95.0	94.7	83.6	72.3	83.3	94.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2280.4	2.5°	2271.4	2264.4	2257.5	2251.0	2244.5	2236.5	2244.5	2251.0	2257.5	2264.4
2145.6	5°	2133.2	2124.5	2115.7	2109.0	2102.2	2095.6	2102.2	2109.0	2115.7	2124.5
2064.8	7.5°	2050.1	2040.0	2029.9	2023.9	2017.9	2013.4	2017.9	2023.9	2029.9	2040.0
2041.6	10°	2024.9	2015.4	2005.8	2000.7	1995.6	1993.5	1995.6	2000.7	2005.8	2015.4
2083.3	12.5°	2062.1	2051.4	2040.8	2036.5	2032.1	2031.3	2032.1	2036.5	2040.8	2051.4
2171.2	15°	2138.9	2124.1	2109.3	2103.7	2098.0	2097.5	2098.0	2103.7	2109.3	2124.1
2260.5	17.5°	2212.8	2190.9	2168.9	2161.7	2154.4	2153.3	2154.4	2161.7	2168.9	2190.9
2316.1	20°	2257.7	2229.7	2201.5	2192.5	2183.5	2180.7	2183.5	2192.5	2201.5	2229.7
2319.6	22.5°	2259.3	2229.8	2200.1	2190.2	2180.2	2176.0	2180.2	2190.2	2200.1	2229.8
2266.9	25°	2213.6	2187.9	2162.3	2152.9	2143.6	2138.2	2143.6	2152.9	2162.3	2187.9
2165.5	27.5°	2124.0	2106.8	2089.5	2085.2	2081.0	2079.6	2081.0	2085.2	2089.5	2106.8
2043.4	30°	2013.6	2004.8	1995.9	1995.9	1995.9	1997.3	1995.9	1995.9	1995.9	2004.8
1926.5	32.5°	1902.8	1897.0	1891.3	1892.0	1892.9	1894.3	1892.9	1892.0	1891.3	1897.0
1826.8	35°	1805.0	1796.2	1787.5	1785.6	1783.7	1782.7	1783.7	1785.6	1787.5	1796.2
1742.0	37.5°	1721.8	1705.8	1689.9	1681.5	1673.1	1668.4	1673.1	1681.5	1689.9	1705.8
1662.6	40°	1645.5	1622.2	1599.2	1583.5	1568.0	1558.7	1568.0	1583.5	1599.2	1622.2
1582.5	42.5°	1568.2	1539.3	1510.5	1487.7	1465.0	1450.0	1465.0	1487.7	1510.5	1539.3
1505.0	45°	1492.1	1459.1	1426.2	1399.4	1372.7	1355.5	1372.7	1399.4	1426.2	1459.1
1440.9	47.5°	1431.9	1402.6	1373.3	1348.5	1323.8	1307.3	1323.8	1348.5	1373.3	1402.6
1396.3	50°	1395.9	1372.5	1349.1	1326.2	1303.3	1287.4	1303.3	1326.2	1349.1	1372.5
1366.8	52.5°	1371.8	1352.7	1333.6	1313.1	1292.6	1278.0	1292.6	1313.1	1333.6	1352.7
1342.3	55°	1349.1	1332.4	1315.8	1297.8	1279.9	1266.6	1279.9	1297.8	1315.8	1332.4
1318.2	57.5°	1325.1	1308.2	1291.4	1273.6	1255.8	1242.1	1255.8	1273.6	1291.4	1308.2
1284.1	60°	1291.7	1275.2	1258.9	1240.6	1222.2	1208.0	1222.2	1240.6	1258.9	1275.2
1231.2	62.5°	1238.5	1223.6	1208.8	1189.5	1170.2	1153.2	1170.2	1189.5	1208.8	1223.6
1159.3	65°	1166.6	1152.4	1138.1	1119.4	1100.7	1086.1	1100.7	1119.4	1138.1	1152.4
1077.5	67.5°	1084.7	1071.5	1058.5	1041.1	1023.7	1010.5	1023.7	1041.1	1058.5	1071.5
990.1	70°	997.1	986.4	975.7	959.1	942.4	927.3	942.4	959.1	975.7	986.4
892.3	72.5°	900.6	891.8	882.9	867.0	851.2	836.5	851.2	867.0	882.9	891.8
777.0	75°	785.7	781.3	777.0	763.7	750.3	736.4	750.3	763.7	777.0	781.3
666.0	77.5°	674.2	668.1	661.9	648.4	635.0	623.9	635.0	648.4	661.9	668.1
537.5	80°	548.2	545.6	543.0	525.0	506.8	485.9	506.8	525.0	543.0	545.6
391.0	82.5°	409.3	408.2	406.9	391.7	376.4	363.0	376.4	391.7	406.9	408.2
237.3	85°	259.9	258.1	256.2	244.3	232.3	220.2	232.3	244.3	256.2	258.1
103.5	87.5°	112.7	110.4	107.9	101.9	95.7	89.8	95.7	101.9	107.9	110.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2271.4	2.5°	2280.4	2289.4	2300.6	2311.6	2325.9	2340.3	2354.5	2368.8	2385.1	2401.4
2133.2	5°	2145.6	2158.0	2175.8	2193.5	2216.5	2239.5	2264.8	2290.2	2318.8	2347.5
2050.1	7.5°	2064.8	2079.6	2100.5	2121.6	2149.7	2177.9	2209.8	2241.7	2279.5	2317.3
2024.9	10°	2041.6	2058.0	2083.2	2108.4	2140.1	2171.7	2206.1	2240.4	2278.2	2316.1
2062.1	12.5°	2083.3	2104.6	2136.7	2168.9	2201.6	2234.4	2261.2	2288.3	2313.2	2338.4
2138.9	15°	2171.2	2203.6	2249.3	2295.1	2323.5	2352.0	2359.0	2366.0	2362.6	2359.2
2212.8	17.5°	2260.5	2308.1	2368.7	2429.3	2452.2	2475.1	2453.3	2431.4	2390.2	2349.0
2257.7	20°	2316.1	2374.5	2443.7	2513.0	2523.6	2534.2	2488.4	2442.5	2370.9	2299.3
2259.3	22.5°	2319.6	2379.7	2445.8	2512.0	2505.7	2499.2	2439.6	2380.0	2298.1	2216.4
2213.6	25°	2266.9	2320.4	2374.6	2428.8	2407.0	2385.1	2326.4	2267.7	2194.1	2120.7
2124.0	27.5°	2165.5	2207.0	2245.5	2284.2	2259.7	2235.3	2188.3	2141.2	2080.9	2020.5
2013.6	30°	2043.4	2073.1	2102.6	2132.0	2112.2	2092.3	2053.2	2014.1	1964.0	1913.9
1902.8	32.5°	1926.5	1950.2	1977.4	2004.4	1982.3	1960.3	1922.7	1885.3	1845.2	1805.2
1805.0	35°	1826.8	1848.7	1867.9	1887.2	1860.7	1834.3	1797.1	1760.1	1729.6	1699.1
1721.8	37.5°	1742.0	1762.1	1771.0	1779.9	1747.2	1714.5	1677.4	1640.5	1618.7	1596.7
1645.5	40°	1662.6	1679.7	1677.6	1675.5	1637.7	1600.1	1564.4	1528.7	1512.9	1497.1
1568.2	42.5°	1582.5	1597.0	1586.1	1575.3	1534.6	1494.0	1460.0	1426.2	1413.2	1400.4
1492.1	45°	1505.0	1518.1	1502.5	1486.9	1444.7	1402.6	1370.4	1338.3	1327.3	1316.5
1431.9	47.5°	1440.9	1450.0	1432.1	1414.1	1372.5	1330.9	1299.5	1268.1	1257.9	1247.7
1395.9	50°	1396.3	1396.9	1373.8	1350.8	1313.5	1276.3	1246.7	1217.0	1201.0	1185.2
1371.8	52.5°	1366.8	1361.9	1334.6	1307.3	1272.5	1237.8	1210.7	1183.5	1159.6	1135.7
1349.1	55°	1342.3	1335.5	1306.4	1277.5	1247.2	1216.7	1187.4	1158.1	1124.3	1090.3
1325.1	57.5°	1318.2	1311.3	1282.1	1252.9	1222.8	1192.7	1158.3	1123.9	1087.4	1050.9
1291.7	60°	1284.1	1276.6	1247.3	1218.0	1187.3	1156.8	1117.3	1077.8	1045.8	1013.8
1238.5	62.5°	1231.2	1223.9	1197.1	1170.2	1137.6	1105.0	1058.9	1012.8	992.5	972.2
1166.6	65°	1159.3	1151.8	1128.2	1104.5	1073.3	1042.1	992.7	943.4	935.6	927.8
1084.7	67.5°	1077.5	1070.2	1049.8	1029.4	999.9	970.3	924.6	879.1	881.5	884.0
997.1	70°	990.1	983.1	964.6	946.2	920.7	895.2	855.1	815.0	823.5	832.0
900.6	72.5°	892.3	884.0	865.9	847.9	824.8	801.8	770.3	738.7	751.1	763.6
785.7	75°	777.0	768.3	751.9	735.4	714.5	693.6	670.2	646.7	658.7	670.7
674.2	77.5°	666.0	657.9	640.7	623.4	605.4	587.5	568.5	549.4	561.5	573.6
548.2	80°	537.5	526.7	513.7	500.5	485.4	470.3	454.5	438.6	448.8	458.9
409.3	82.5°	391.0	372.6	344.6	316.7	322.0	327.2	328.6	329.9	337.1	344.3
259.9	85°	237.3	214.6	188.3	162.1	176.8	191.4	198.3	205.1	213.2	221.2
112.7	87.5°	103.5	94.3	83.3	72.3	83.6	94.7	95.0	95.3	96.8	98.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2419.5	2.5°	2437.6	2460.0	2480.2	2501.0	2521.7	2543.5	2565.2	2586.8	2608.4	2628.7
2381.8	5°	2416.1	2455.3	2495.0	2537.1	2579.1	2624.1	2669.2	2713.9	2758.7	2803.6
2362.8	7.5°	2408.3	2459.1	2513.2	2571.9	2630.6	2697.3	2763.9	2832.4	2900.8	2974.8
2364.1	10°	2412.1	2466.6	2533.5	2603.0	2672.4	2753.4	2834.3	2924.7	3015.2	3108.8
2377.5	12.5°	2416.8	2467.6	2537.8	2616.4	2694.9	2790.4	2885.9	2988.3	3090.8	3193.6
2377.9	15°	2396.7	2437.3	2515.1	2606.1	2697.0	2806.9	2916.9	3028.0	3139.2	3246.5
2342.1	17.5°	2335.2	2360.3	2451.8	2561.2	2670.5	2798.1	2925.7	3047.0	3168.3	3277.1
2267.2	20°	2235.1	2241.7	2348.2	2483.7	2619.3	2773.9	2928.6	3061.9	3195.1	3308.3
2168.9	22.5°	2121.3	2108.4	2229.7	2392.9	2556.2	2744.3	2932.4	3081.9	3231.3	3347.0
2065.9	25°	2011.0	1976.1	2100.4	2291.5	2482.7	2715.0	2947.3	3118.2	3289.0	3402.2
1967.5	27.5°	1914.6	1872.1	1985.2	2198.8	2412.3	2695.4	2978.5	3174.9	3371.2	3479.3
1871.8	30°	1829.8	1796.5	1891.5	2121.2	2351.0	2686.2	3021.2	3248.4	3475.5	3579.8
1780.4	32.5°	1755.5	1740.7	1817.2	2054.4	2291.5	2674.9	3058.1	3325.0	3592.0	3695.2
1692.2	35°	1685.4	1691.5	1755.3	1988.7	2222.1	2653.5	3085.1	3412.4	3739.6	3838.6
1604.3	37.5°	1611.8	1634.3	1690.1	1911.4	2132.7	2616.9	3101.2	3510.2	3919.2	4045.3
1514.2	40°	1531.3	1565.8	1616.4	1819.1	2021.9	2566.6	3111.3	3634.4	4157.4	4341.2
1423.1	42.5°	1445.8	1489.2	1535.8	1717.3	1898.8	2514.6	3130.5	3796.9	4463.3	4728.5
1338.6	45°	1360.7	1402.8	1450.0	1609.2	1768.4	2466.3	3164.2	4010.7	4857.2	5215.0
1266.3	47.5°	1284.8	1321.0	1382.0	1523.7	1665.3	2426.4	3187.4	4238.5	5289.6	5793.3
1201.5	50°	1218.0	1260.0	1340.2	1466.8	1593.5	2382.9	3172.3	4449.9	5727.5	6486.7
1151.9	52.5°	1168.1	1226.9	1319.1	1429.4	1539.8	2309.4	3079.2	4587.1	6095.0	7215.1
1116.0	55°	1141.7	1230.2	1316.0	1402.3	1488.6	2187.7	2886.8	4556.9	6226.9	7860.9
1088.4	57.5°	1125.8	1233.6	1309.2	1370.1	1431.1	2016.0	2600.9	4344.0	6087.2	8318.6
1062.4	60°	1110.9	1223.2	1273.1	1321.0	1368.9	1793.1	2217.4	3947.8	5678.3	8433.0
1032.8	62.5°	1093.5	1197.6	1203.8	1235.5	1267.4	1526.4	1785.4	3412.2	5039.0	7951.4
992.3	65°	1056.8	1136.2	1135.4	1150.5	1165.5	1286.4	1407.3	2865.6	4324.1	7269.9
937.7	67.5°	991.4	1036.0	1038.1	1029.8	1021.3	1055.8	1090.1	2330.2	3570.4	6459.0
870.2	70°	908.4	923.0	923.0	884.2	845.2	835.5	825.7	1834.7	2843.8	5574.2
789.8	72.5°	815.9	815.8	806.5	751.4	696.2	666.5	636.9	1402.7	2168.4	4614.9
690.9	75°	711.0	714.6	671.9	610.1	548.2	521.4	494.6	1018.0	1541.5	3515.3
589.7	77.5°	605.9	607.8	537.4	477.4	417.3	399.0	380.7	689.8	998.9	2460.4
472.5	80°	486.0	486.3	402.2	351.4	300.6	293.0	285.5	444.5	603.5	1585.2
350.9	82.5°	357.5	353.5	281.7	244.3	206.8	205.3	204.0	273.4	342.9	917.5
228.3	85°	235.4	230.2	176.8	149.3	121.9	122.7	123.4	146.1	169.0	412.7
101.1	87.5°	104.0	97.4	75.1	63.9	52.7	53.4	54.1	60.6	67.1	135.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2649.1	2.5°	2659.1	2669.2	2683.5	2697.8	2706.3	2714.8	2719.0	2723.3	2721.4	2723.3
2848.5	5°	2883.6	2918.8	2953.5	2988.4	3007.3	3026.2	3037.7	3049.2	3057.9	3049.2
3048.9	7.5°	3106.0	3163.0	3214.3	3265.7	3296.6	3327.5	3344.2	3360.8	3368.9	3360.8
3202.5	10°	3270.0	3337.5	3397.7	3457.9	3494.4	3530.7	3547.0	3563.1	3569.3	3563.1
3296.6	12.5°	3369.7	3442.8	3497.2	3551.5	3578.0	3604.4	3613.3	3622.2	3623.2	3622.2
3353.8	15°	3416.9	3479.9	3514.1	3548.3	3549.2	3550.2	3540.7	3531.3	3520.1	3531.3
3385.9	17.5°	3428.5	3471.2	3471.8	3472.4	3434.1	3395.8	3360.8	3325.6	3300.8	3325.6
3421.3	20°	3436.2	3451.1	3406.2	3361.3	3276.8	3192.3	3130.8	3069.2	3031.4	3069.2
3462.5	22.5°	3443.0	3423.5	3330.5	3237.5	3113.2	2988.9	2911.9	2835.0	2793.2	2835.0
3515.4	25°	3454.0	3392.5	3251.3	3110.1	2959.1	2808.2	2727.2	2646.5	2607.0	2646.5
3587.2	27.5°	3477.4	3367.5	3180.4	2993.4	2826.1	2658.8	2579.2	2499.7	2462.4	2499.7
3684.1	30°	3520.3	3356.6	3126.3	2896.1	2721.8	2547.5	2473.6	2399.8	2365.0	2399.8
3798.5	32.5°	3574.2	3350.0	3089.5	2829.0	2665.1	2501.3	2443.4	2385.3	2360.3	2385.3
3937.5	35°	3662.9	3388.5	3117.1	2845.7	2731.9	2618.2	2604.6	2591.1	2589.0	2591.1
4171.4	37.5°	3848.5	3525.6	3278.9	3032.2	3024.8	3017.4	3079.3	3141.1	3173.2	3141.1
4524.9	40°	4173.8	3822.6	3639.1	3455.7	3585.2	3714.7	3865.0	4015.2	4090.1	4015.2
4993.8	42.5°	4645.4	4296.9	4191.3	4085.6	4368.0	4650.5	4923.8	5197.2	5357.7	5197.2
5572.7	45°	5259.8	4946.7	4900.1	4853.4	5305.9	5758.5	6207.7	6656.9	6929.6	6656.9
6296.8	47.5°	5992.3	5687.8	5678.3	5668.9	6321.7	6974.3	7631.9	8289.4	8675.5	8289.4
7245.8	50°	6869.7	6493.7	6495.3	6496.9	7338.2	8179.5	9047.5	9915.5	10440.3	9915.5
8335.2	52.5°	7879.8	7424.5	7378.5	7332.3	8337.2	9342.1	10416.1	11490.0	12119.1	11490.0
9495.1	55°	9045.1	8595.2	8415.7	8236.2	9354.6	10472.9	11753.3	13033.6	13781.8	13033.6
10550.0	57.5°	10305.0	10059.9	9699.8	9339.9	10469.1	11598.4	13048.7	14498.8	15426.5	14498.8
11187.5	60°	11568.1	11948.8	11501.6	11054.5	12123.2	13192.0	14744.6	16297.3	17300.0	16297.3
10863.8	62.5°	11903.7	12943.5	12893.2	12842.7	13821.7	14800.8	16278.0	17755.2	18682.0	17755.2
10215.8	65°	11191.8	12167.8	12360.9	12553.9	13798.0	15042.3	16474.7	17907.1	18696.2	17907.1
9347.6	67.5°	10275.8	11204.1	11294.6	11385.1	12681.4	13977.6	15416.2	16854.8	17473.0	16854.8
8304.5	70°	9314.1	10323.9	10364.3	10404.9	11564.1	12723.3	13961.3	15199.2	15542.8	15199.2
7061.5	72.5°	8220.1	9378.8	9407.9	9436.9	10343.9	11250.9	12178.1	13105.2	13140.0	13105.2
5489.1	75°	6688.2	7887.4	7995.0	8102.7	8808.3	9514.0	10166.7	10819.4	10644.5	10819.4
3921.9	77.5°	5041.2	6160.7	6314.8	6468.8	7005.3	7541.7	8004.6	8467.6	8167.0	8467.6
2566.8	80°	3508.6	4450.3	4641.8	4833.3	5238.4	5643.3	5886.5	6129.5	5646.0	6129.5
1492.1	82.5°	2135.9	2779.8	2993.7	3207.7	3486.6	3765.4	3866.8	3968.2	3588.2	3968.2
656.5	85°	998.2	1339.9	1521.9	1703.8	1932.9	2162.0	2219.5	2277.1	1972.7	2277.1
203.2	87.5°	318.1	432.9	534.4	636.0	750.5	865.1	870.0	874.8	734.5	874.8
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949189
 CATALOG NUMBER: GALN-SB4A-735-U-SLR

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
2463.3	0°	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3	2463.3
2719.0	2.5°	2714.8	2706.3	2697.8	2683.5	2669.2	2659.1	2649.1
3037.7	5°	3026.2	3007.3	2988.4	2953.5	2918.8	2883.6	2848.5
3344.2	7.5°	3327.5	3296.6	3265.7	3214.3	3163.0	3106.0	3048.9
3547.0	10°	3530.7	3494.4	3457.9	3397.7	3337.5	3270.0	3202.5
3613.3	12.5°	3604.4	3578.0	3551.5	3497.2	3442.8	3369.7	3296.6
3540.7	15°	3550.2	3549.2	3548.3	3514.1	3479.9	3416.9	3353.8
3360.8	17.5°	3395.8	3434.1	3472.4	3471.8	3471.2	3428.5	3385.9
3130.8	20°	3192.3	3276.8	3361.3	3406.2	3451.1	3436.2	3421.3
2911.9	22.5°	2988.9	3113.2	3237.5	3330.5	3423.5	3443.0	3462.5
2727.2	25°	2808.2	2959.1	3110.1	3251.3	3392.5	3454.0	3515.4
2579.2	27.5°	2658.8	2826.1	2993.4	3180.4	3367.5	3477.4	3587.2
2473.6	30°	2547.5	2721.8	2896.1	3126.3	3356.6	3520.3	3684.1
2443.4	32.5°	2501.3	2665.1	2829.0	3089.5	3350.0	3574.2	3798.5
2604.6	35°	2618.2	2731.9	2845.7	3117.1	3388.5	3662.9	3937.5
3079.3	37.5°	3017.4	3024.8	3032.2	3278.9	3525.6	3848.5	4171.4
3865.0	40°	3714.7	3585.2	3455.7	3639.1	3822.6	4173.8	4524.9
4923.8	42.5°	4650.5	4368.0	4085.6	4191.3	4296.9	4645.4	4993.8
6207.7	45°	5758.5	5305.9	4853.4	4900.1	4946.7	5259.8	5572.7
7631.9	47.5°	6974.3	6321.7	5668.9	5678.3	5687.8	5992.3	6296.8
9047.5	50°	8179.5	7338.2	6496.9	6495.3	6493.7	6869.7	7245.8
10416.1	52.5°	9342.1	8337.2	7332.3	7378.5	7424.5	7879.8	8335.2
11753.3	55°	10472.9	9354.6	8236.2	8415.7	8595.2	9045.1	9495.1
13048.7	57.5°	11598.4	10469.1	9339.9	9699.8	10059.9	10305.0	10550.0
14744.6	60°	13192.0	12123.2	11054.5	11501.6	11948.8	11568.1	11187.5
16278.0	62.5°	14800.8	13821.7	12842.7	12893.2	12943.5	11903.7	10863.8
16474.7	65°	15042.3	13798.0	12553.9	12360.9	12167.8	11191.8	10215.8
15416.2	67.5°	13977.6	12681.4	11385.1	11294.6	11204.1	10275.8	9347.6
13961.3	70°	12723.3	11564.1	10404.9	10364.3	10323.9	9314.1	8304.5
12178.1	72.5°	11250.9	10343.9	9436.9	9407.9	9378.8	8220.1	7061.5
10166.7	75°	9514.0	8808.3	8102.7	7995.0	7887.4	6688.2	5489.1
8004.6	77.5°	7541.7	7005.3	6468.8	6314.8	6160.7	5041.2	3921.9
5886.5	80°	5643.3	5238.4	4833.3	4641.8	4450.3	3508.6	2566.8
3866.8	82.5°	3765.4	3486.6	3207.7	2993.7	2779.8	2135.9	1492.1
2219.5	85°	2162.0	1932.9	1703.8	1521.9	1339.9	998.2	656.5
870.0	87.5°	865.1	750.5	636.0	534.4	432.9	318.1	203.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)