

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P943507

Luminaire Tested: **GALN-SB8A-735-U-T3**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P943507
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: MCGRAW-EDISON
Catalog Number: GALN-SB8A-735-U-T3
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(8) 70 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE III OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 36297 lumens
Efficiency: N/A
Efficacy: 159.8 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
IES Classification: Type III - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 227.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P943507
 CATALOG NUMBER: GALN-SB8A-735-U-T3

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 9.1 fc
 Type III - Short - N/A

REPORT NUMBER: P943507
CATALOG NUMBER: GALN-SB8A-735-U-T3

Luminous Intensity Polar Plot



— Vertical Plane Through 66-Deg Lateral - - - Horizontal Cone Through 67.5-Deg Vertical

REPORT NUMBER: P943507
 CATALOG NUMBER: GALN-SB8A-735-U-T3

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	9025.2	0.0	9025.2
	% Fixture	24.9	0.0	24.9
Street Side	Lumens	27271.9	0.0	27271.9
	% Fixture	75.1	0.0	75.1
Total	Lumens	36297.0	0.0	36297.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	399.1	1.1
10°-20°	1318.7	3.6
20°-30°	2541.8	7.0
30°-40°	4456.6	12.3
40°-50°	6625.6	18.3
50°-60°	8398.5	23.1
60°-70°	8217.8	22.6
70°-80°	3920.0	10.8
80°-90°	418.9	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	36297.0	100.0
0°-180°	36297.0	100.0

Coefficient of Utilization



REPORT NUMBER: P943507


CATALOG NUMBER: GALN-SB8A-735-U-T3

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2293.6	6.3			
FM (30°-60°)	14874.2	41.0			
FH (60°-80°)	9866.5	27.2			G4/12000
FVH (80°-90°)	237.5	0.7			G3/500
BL (0°-30°)	1966.0	5.4	B3/2500		
BM (30°-60°)	4606.5	12.7	B3/5000		
BH (60°-80°)	2271.2	6.3	B3/2500		G3/2500
BVH (80°-90°)	181.4	0.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G4

Type III Short



REPORT NUMBER: P943507

CATALOG NUMBER: GALN-SB8A-735-U-T3

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°
0°	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8
2.5°	3983.9	4006.7	4001.0	3991.5	3989.6	3993.4	3999.1	4004.8	4002.9	4012.5
5°	3972.4	3995.3	3993.4	3993.4	4001.0	4016.3	4025.8	4035.4	4025.8	4037.3
7.5°	3980.0	3997.2	4004.8	4012.5	4031.5	4060.1	4083.0	4104.0	4092.6	4105.9
10°	4077.3	4090.7	4098.3	4098.3	4111.6	4144.1	4166.9	4205.1	4195.5	4216.5
12.5°	4254.7	4268.0	4268.0	4260.4	4269.9	4290.9	4298.5	4340.5	4323.3	4357.6
15°	4472.1	4498.8	4477.8	4464.4	4468.3	4489.2	4487.3	4519.7	4502.6	4531.2
17.5°	4712.4	4746.7	4712.4	4710.5	4702.8	4725.7	4727.6	4756.2	4725.7	4746.7
20°	4996.5	5044.2	5015.6	5025.1	5008.0	5017.5	5027.0	5069.0	5021.3	5036.6
22.5°	5397.0	5454.2	5423.7	5459.9	5448.5	5440.9	5439.0	5513.3	5439.0	5444.7
25°	5980.6	6049.2	5995.8	6045.4	6045.4	6070.2	6098.8	6194.2	6070.2	6034.0
27.5°	6842.6	6911.2	6806.3	6836.8	6827.3	6888.3	6857.8	7094.3	6960.8	6901.7
30°	7880.0	8002.1	7803.7	7796.1	7786.6	7883.8	7927.7	8084.1	7948.7	7889.5
32.5°	9001.4	9129.1	8892.7	8824.0	8787.8	8846.9	8810.6	8936.5	8843.1	8751.5
35°	10187.5	10313.4	10088.4	9954.9	9809.9	9686.0	9556.3	9588.7	9501.0	9361.8
37.5°	11308.9	11539.7	11301.3	11158.2	10891.3	10649.1	10286.7	10136.1	10054.1	9926.3
40°	12451.2	12582.8	12401.7	12279.6	11989.7	11610.2	11030.5	10712.0	10601.4	10477.4
42.5°	13292.3	13418.1	13320.9	13236.9	13010.0	12569.5	11820.0	11421.4	11261.2	11122.0
45°	13959.7	14053.2	13992.1	14022.7	13925.4	13498.2	12638.1	12182.3	12016.4	11846.7
47.5°	14228.6	14327.8	14425.0	14606.2	14772.1	14457.5	13517.3	13006.2	12830.7	12657.2
50°	14198.1	14299.2	14581.4	14966.7	15481.6	15376.7	14444.1	13883.4	13721.3	13523.0
52.5°	13954.0	14068.4	14430.8	15071.5	15891.6	16065.1	15388.1	14789.3	14636.7	14400.3
55°	13313.2	13381.9	13925.4	14833.2	15988.8	16545.7	16313.0	15754.3	15601.7	15271.8
57.5°	12125.1	12224.3	13015.7	14190.5	15744.7	16871.8	17125.5	16768.8	16622.0	16147.1
60°	10574.7	10733.0	11638.8	13111.1	15123.0	16869.9	17863.5	17766.2	17644.2	17009.1
62.5°	8820.2	9003.3	9874.8	11585.4	14036.0	16391.2	18325.0	18601.5	18538.6	17804.4
65°	6773.9	6899.8	7767.5	9611.6	12344.4	15363.3	18378.4	19171.7	19183.2	18408.9
67.5°	4510.2	4872.6	5625.8	7212.5	10078.8	13683.2	17909.3	19265.2	19375.8	18616.8
70°	2200.8	2677.5	3415.6	4687.6	7212.5	11106.8	16683.0	18498.5	18744.6	18010.3
72.5°	913.5	1068.0	1470.3	2313.3	4140.2	7494.8	14219.1	16419.8	16875.6	15958.3
75°	616.0	667.5	841.0	1186.2	1886.1	3695.9	10254.3	12243.4	12977.6	12052.7
77.5°	474.9	507.3	612.2	829.6	1121.4	1397.9	5488.5	7378.4	7757.9	7182.0
80°	373.8	398.6	457.7	604.5	795.2	747.6	1870.8	3343.1	3562.4	2988.4
82.5°	324.2	333.7	328.0	410.0	528.3	436.7	614.1	1233.9	1361.6	987.9
85°	234.6	261.3	272.7	253.6	280.3	221.2	251.7	436.7	480.6	429.1
87.5°	95.4	141.1	173.5	164.0	103.0	62.9	78.2	127.8	146.8	160.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P943507
 CATALOG NUMBER: GALN-SB8A-735-U-T3

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
4025.8	0°	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8	4025.8
4027.7	2.5°	4029.6	4043.0	4052.5	4064.0	4071.6	4083.0	4105.9	4119.3	4121.2	4130.7
4058.2	5°	4065.9	4084.9	4105.9	4136.4	4170.8	4199.4	4243.2	4273.7	4285.2	4294.7
4132.6	7.5°	4144.1	4170.8	4208.9	4262.3	4311.9	4350.0	4403.4	4439.7	4475.9	4489.2
4250.9	10°	4260.4	4298.5	4353.8	4426.3	4479.7	4529.3	4584.6	4615.1	4651.3	4666.6
4392.0	12.5°	4405.3	4445.4	4517.8	4618.9	4668.5	4702.8	4721.9	4714.3	4721.9	4735.2
4561.7	15°	4571.2	4615.1	4697.1	4805.8	4840.1	4809.6	4767.7	4729.5	4723.8	4727.6
4767.7	17.5°	4767.7	4800.1	4895.4	4987.0	4962.2	4836.3	4744.8	4683.8	4653.2	4643.7
5030.8	20°	5042.3	5042.3	5120.5	5177.7	5011.8	4798.2	4655.1	4556.0	4493.0	4466.3
5389.4	22.5°	5376.0	5345.5	5395.1	5355.0	5002.2	4691.4	4493.0	4321.4	4226.1	4187.9
5890.9	25°	5799.4	5763.2	5749.8	5501.9	4933.6	4521.7	4199.4	3991.5	3907.6	3886.6
6613.7	27.5°	6438.3	6346.7	6173.2	5582.0	4807.7	4254.7	3856.1	3663.5	3615.8	3617.7
7542.4	30°	7288.8	7105.7	6680.5	5595.3	4601.8	3877.1	3505.2	3367.9	3345.0	3354.5
8322.4	32.5°	8076.4	7902.9	7199.2	5534.3	4285.2	3507.1	3190.5	3099.0	3064.7	3076.1
8917.4	35°	8694.3	8646.6	7679.8	5448.5	3896.1	3160.0	2908.3	2830.1	2763.3	2748.1
9478.1	37.5°	9277.9	9258.8	8040.2	5328.3	3510.9	2914.0	2681.3	2578.4	2481.1	2427.7
10097.9	40°	9918.7	9899.6	8276.7	5143.4	3169.5	2700.4	2477.3	2341.9	2221.7	2124.5
10799.7	42.5°	10639.5	10527.0	8389.2	4878.3	2879.7	2519.2	2311.4	2128.3	1970.0	1880.4
11593.1	45°	11427.1	11173.5	8387.3	4540.7	2635.6	2353.3	2134.0	1874.6	1727.8	1643.9
12407.4	47.5°	12262.4	11791.4	8284.3	4166.9	2399.1	2170.2	1859.4	1661.1	1563.8	1512.3
13292.3	50°	13124.4	12369.2	8108.8	3737.8	2156.9	1962.4	1687.8	1552.4	1478.0	1430.3
14169.5	52.5°	13934.9	12893.7	7897.2	3251.5	1910.9	1760.2	1611.5	1506.6	1428.4	1375.0
15020.1	55°	14688.2	13345.7	7597.8	2753.8	1710.6	1624.8	1575.2	1487.5	1397.9	1334.9
15884.0	57.5°	15357.6	13639.3	7080.9	2286.6	1567.6	1531.4	1537.1	1455.1	1352.1	1298.7
16734.5	60°	15914.5	13854.8	6316.2	1853.7	1451.3	1439.8	1478.0	1394.1	1273.9	1212.9
17453.5	62.5°	16248.2	13851.0	5377.9	1518.0	1352.1	1355.9	1399.8	1317.8	1195.7	1138.5
17829.2	65°	16219.6	13511.6	4348.1	1298.7	1256.8	1260.6	1317.8	1233.9	1130.9	1096.6
17640.4	67.5°	15645.6	12683.9	3335.5	1155.7	1151.9	1169.0	1235.8	1176.7	1090.8	1087.0
16515.2	70°	14091.3	10965.6	2402.9	1041.3	1043.2	1068.0	1155.7	1140.4	1069.9	1077.5
13885.3	72.5°	11299.4	8360.6	1613.4	921.1	923.0	963.1	1079.4	1111.8	1048.9	1150.0
9851.9	75°	7525.3	5213.9	1037.4	793.3	795.2	846.7	1012.7	1056.5	991.7	1146.1
5126.2	77.5°	3615.8	2343.8	751.4	667.5	667.5	715.1	875.3	945.9	844.8	890.6
1647.7	80°	1249.1	881.1	591.2	537.8	526.4	558.8	738.0	820.0	728.5	671.3
537.8	82.5°	492.0	457.7	474.9	417.6	379.5	400.5	574.0	677.0	535.9	484.4
303.2	85°	282.2	297.5	335.6	276.5	219.3	246.0	421.5	486.3	404.3	356.6
99.2	87.5°	76.3	104.9	154.5	143.0	99.2	104.9	200.2	268.9	232.7	179.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
4025.8
4128.8
4292.8
4491.1
4674.2
4739.1
4741.0
4657.1
4460.6
4182.2
3890.4
3623.4
3386.9
3091.4
2759.5
2429.6
2134.0
1886.1
1640.1
1500.9
1413.1
1352.1
1310.2
1264.4
1186.2
1121.4
1094.7
1092.7
1075.6
1165.2
1155.7
816.2
629.3
482.5
364.2
185.0
0.0

F REPORT)