

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P949551

Luminaire Tested: **GALN-SB4B-735-U-T3R-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P949551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4B-735-U-T3R-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 3500K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE III
ROADWAY OPTICS WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18789 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type III - Medium
BUG Rating: B2 - U0 - G3


Input Watts (W): 147
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P949551
 CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 5.5 fc
 Type III - Medium - N/A

REPORT NUMBER: P949551
CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 77-Deg Lateral - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P949551
 CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1980.6	0.0	1980.6
	% Fixture	10.5	0.0	10.5
Street Side	Lumens	16808.4	0.0	16808.4
	% Fixture	89.5	0.0	89.5
Total	Lumens	18789.0	0.0	18789.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.6	1.3
10°-20°	599.6	3.2
20°-30°	927.4	4.9
30°-40°	1682.9	9.0
40°-50°	3176.6	16.9
50°-60°	4589.9	24.4
60°-70°	4885.8	26.0
70°-80°	2589.2	13.8
80°-90°	85.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	18789.0	100.0
0°-180°	18789.0	100.0

Coefficient of Utilization



REPORT NUMBER: P949551


CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1150.3	6.1			
FM (30°-60°)	8463.4	45.0			
FH (60°-80°)	7111.9	37.9			G3/7500
FVH (80°-90°)	82.7	0.4			G1/100
BL (0°-30°)	629.3	3.3	B2/1000		
BM (30°-60°)	986.0	5.2	B1/1000		
BH (60°-80°)	363.1	1.9	B1/500		G1/500
BVH (80°-90°)	2.3	0.0			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B2-U0-G3

Type III Medium



REPORT NUMBER: P949551
 CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7
2.5°	2751.6	2776.5	2772.9	2789.5	2795.5	2819.2	2842.9	2875.0	2910.6	2909.4
5°	2596.1	2621.1	2627.0	2649.5	2678.0	2714.8	2763.4	2827.5	2894.0	2904.6
7.5°	2412.2	2438.3	2453.8	2498.8	2551.1	2627.0	2706.5	2800.2	2910.6	2926.0
10°	2228.3	2252.0	2272.2	2336.3	2419.3	2532.1	2661.4	2796.7	2945.0	2967.5
12.5°	2114.4	2137.0	2159.5	2215.3	2318.5	2456.1	2631.7	2813.3	3001.9	3034.0
15°	2074.1	2094.2	2112.0	2161.9	2258.0	2414.6	2625.8	2847.7	3074.3	3117.0
17.5°	2080.0	2090.7	2102.5	2140.5	2234.2	2395.6	2636.5	2907.0	3159.7	3197.7
20°	2114.4	2120.3	2121.5	2147.6	2230.7	2393.2	2657.8	2964.0	3240.4	3291.5
22.5°	2158.3	2160.7	2158.3	2176.1	2253.2	2411.0	2686.3	3032.8	3330.6	3378.1
25°	2363.6	2318.5	2261.5	2227.1	2291.2	2445.5	2729.0	3125.3	3429.1	3475.4
27.5°	3000.8	2871.4	2667.3	2438.3	2369.5	2495.3	2788.4	3219.1	3528.8	3570.3
30°	4035.4	3865.7	3519.3	3003.1	2621.1	2599.7	2865.5	3312.8	3634.4	3679.4
32.5°	5072.4	5030.9	4631.1	3916.8	3187.0	2832.3	2993.6	3439.8	3774.4	3810.0
35°	6121.3	6037.1	5709.6	5003.6	4059.1	3305.7	3207.2	3605.9	3958.3	3998.6
37.5°	6924.6	6873.6	6670.7	6089.3	5093.8	4036.6	3572.7	3863.4	4225.3	4270.3
40°	7634.2	7610.4	7541.6	7158.4	6250.7	4992.9	4141.0	4262.0	4595.5	4648.8
42.5°	8191.8	8247.6	8286.8	8180.0	7443.1	6084.6	4905.1	4822.1	5111.6	5166.2
45°	8762.6	8781.6	8939.4	9093.6	8627.3	7226.0	5766.6	5478.2	5753.5	5821.1
47.5°	9129.2	9205.1	9482.8	9754.5	9622.8	8358.0	6692.1	6253.0	6497.5	6624.4
50°	9156.5	9300.1	9682.1	10155.6	10347.8	9435.3	7698.2	7135.8	7395.7	7535.7
52.5°	8702.1	8925.1	9517.2	10210.1	10739.3	10347.8	8738.8	8018.6	8352.0	8534.8
55°	6671.9	6963.8	8896.6	9913.5	10754.8	11039.5	9752.1	8938.2	9417.5	9624.0
57.5°	5812.8	5960.0	6994.6	9398.6	10468.8	11318.4	10668.1	9813.8	10576.8	10833.1
60°	4836.3	5029.7	5866.2	8556.1	10080.8	11345.7	11477.4	10943.4	11833.3	12121.7
62.5°	3286.7	3496.7	4328.5	7108.5	9550.4	11332.6	12140.6	12106.2	13229.9	13539.6
65°	2036.1	2167.8	2716.0	5804.5	8808.8	11346.8	12834.8	13518.2	14703.6	15018.0
67.5°	1608.9	1669.5	1955.4	4456.6	7530.9	11026.5	13527.7	14845.9	16090.6	16339.8
70°	1080.9	1117.7	1422.7	2987.7	5602.8	9548.1	13514.6	15512.8	16804.9	16929.5
72.5°	569.5	598.0	831.8	1383.5	3384.0	6787.0	11391.9	14715.4	16094.2	15906.7
75°	284.8	332.2	560.0	702.4	1445.2	3785.1	7074.1	11602.0	12667.5	11941.3
77.5°	215.9	261.0	462.7	462.7	503.1	1274.3	2996.0	6327.8	5836.6	4860.1
80°	137.6	178.0	404.6	350.0	210.0	323.9	780.7	1772.7	1239.9	943.3
82.5°	80.7	116.3	337.0	231.4	117.5	119.8	220.7	377.3	321.6	250.4
85°	32.0	75.9	231.4	91.4	46.3	29.7	66.4	80.7	66.4	49.8
87.5°	0.0	17.8	40.3	0.0	3.6	2.4	4.7	5.9	5.9	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P949551
 CATALOG NUMBER: GALN-SB4B-735-U-T3R-HSS

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
2930.7	0°	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7	2930.7
2933.1	2.5°	2943.8	2946.2	2953.3	2954.5	2937.9	2916.5	2908.2	2904.6	2890.4	2889.2
2952.1	5°	2979.4	2990.1	2979.4	2948.5	2875.0	2771.7	2693.4	2629.4	2571.2	2553.4
3017.4	7.5°	3050.6	3061.3	3029.2	2908.2	2723.1	2517.8	2332.7	2202.2	2084.7	2040.8
3096.9	10°	3152.6	3166.9	3066.0	2821.6	2494.1	2164.2	1851.0	1630.3	1458.3	1388.2
3204.8	12.5°	3280.8	3286.7	3086.2	2689.9	2196.3	1725.2	1281.5	1045.3	892.3	835.3
3335.4	15°	3422.0	3413.7	3088.6	2510.7	1790.5	1219.8	836.5	687.0	625.3	606.3
3465.9	17.5°	3570.3	3535.9	3041.1	2252.0	1345.5	834.1	620.6	585.0	574.3	569.5
3595.2	20°	3716.2	3639.1	2954.5	1913.9	965.8	622.9	563.6	552.9	547.0	544.6
3725.7	22.5°	3849.1	3717.4	2806.2	1521.1	701.2	550.6	532.8	523.3	512.6	507.8
3852.7	25°	3978.5	3762.5	2597.3	1154.5	561.2	515.0	500.7	482.9	468.7	462.7
3989.1	27.5°	4104.2	3791.0	2336.3	854.3	500.7	481.7	455.6	430.7	420.0	417.7
4135.1	30°	4238.3	3800.5	2039.7	637.2	463.9	440.2	402.2	373.8	367.8	369.0
4332.0	32.5°	4402.0	3814.7	1740.6	522.1	433.1	390.4	345.3	315.6	310.9	315.6
4619.2	35°	4597.8	3843.2	1452.3	480.5	405.8	339.3	290.7	265.8	261.0	264.6
4987.0	37.5°	4863.6	3889.5	1183.0	472.2	383.3	296.6	244.4	224.3	224.3	225.4
5437.9	40°	5217.2	4012.9	942.1	466.3	371.4	264.6	206.5	198.2	201.7	204.1
6012.2	42.5°	5647.9	4275.1	779.6	459.2	358.3	250.4	187.5	183.9	189.8	192.2
6700.4	45°	6130.8	4607.3	722.6	447.3	346.5	259.9	179.2	174.4	181.5	182.7
7471.6	47.5°	6630.4	4932.4	715.5	434.3	334.6	274.1	176.8	166.1	174.4	175.6
8295.1	50°	7135.8	5144.8	722.6	414.1	315.6	274.1	178.0	157.8	164.9	168.5
9149.4	52.5°	7644.9	5242.1	717.9	370.2	282.4	257.5	178.0	150.7	157.8	160.2
10072.5	55°	8138.5	5223.1	645.5	304.9	239.7	227.8	173.2	144.8	149.5	150.7
10944.6	57.5°	8528.8	4958.5	511.4	237.3	194.6	189.8	157.8	137.6	141.2	140.0
11744.3	60°	8732.9	4377.1	365.5	182.7	153.1	149.5	138.8	128.1	130.5	124.6
12421.8	62.5°	8735.3	3608.3	244.4	144.8	122.2	118.7	118.7	115.1	112.7	100.9
12946.3	65°	8549.0	2755.1	162.6	115.1	98.5	92.5	99.7	98.5	90.2	73.6
13106.5	67.5°	8126.6	1805.9	123.4	90.2	75.9	72.4	79.5	83.1	77.1	61.7
12522.7	70°	7258.0	1051.3	102.0	70.0	57.0	53.4	64.1	71.2	64.1	49.8
10703.7	72.5°	6028.8	567.2	83.1	52.2	39.2	35.6	51.0	58.1	51.0	36.8
6867.7	75°	3912.0	303.8	64.1	34.4	20.2	22.5	38.0	42.7	35.6	23.7
2015.9	77.5°	1313.5	134.1	40.3	16.6	9.5	9.5	22.5	26.1	16.6	8.3
366.6	80°	293.1	55.8	16.6	7.1	3.6	3.6	4.7	4.7	2.4	0.0
112.7	82.5°	96.1	22.5	7.1	2.4	0.0	0.0	0.0	0.0	0.0	0.0
28.5	85°	36.8	8.3	2.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0
9.5	87.5°	14.2	1.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°
2930.7
2891.6
2542.7
2023.0
1358.6
817.5
606.3
568.4
542.2
506.7
460.4
415.3
369.0
314.4
263.4
224.3
204.1
192.2
183.9
176.8
169.7
160.2
150.7
140.0
123.4
97.3
71.2
60.5
47.5
35.6
21.4
7.1
0.0
0.0
0.0
0.0
0.0

F REPORT)