

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P951686

Luminaire Tested: **GALN-SB5D-735-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P951686  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB5D-735-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(5) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 51219 lumens  
Efficiency: N/A  
Efficacy: 140.4 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B4 - U0 - G5  
  
Input Watts (W): 364.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 15.6 fc  
 Type IV - Short - N/A

REPORT NUMBER: P951686  
CATALOG NUMBER: GALN-SB5D-735-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	13017.3	0.0	13017.3
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	38201.7	0.0	38201.7
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	51219.0	0.0	51219.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	698.7	1.4
10°-20°	2193.3	4.3
20°-30°	3387.8	6.6
30°-40°	4293.2	8.4
40°-50°	6475.3	12.6
50°-60°	10461.7	20.4
60°-70°	13042.2	25.5
70°-80°	8552.4	16.7
80°-90°	2114.4	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	51219.0	100.0
0°-180°	51219.0	100.0



REPORT NUMBER: P951686


CATALOG NUMBER: GALN-SB5D-735-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3445.1	6.7			
FM (30°-60°)	14939.5	29.2			
FH (60°-80°)	18075.4	35.3			G5
FVH (80°-90°)	1741.8	3.4			G5
BL (0°-30°)	2834.7	5.5	B4/5000		
BM (30°-60°)	6290.7	12.3	B4/8500		
BH (60°-80°)	3519.3	6.9	B4/5000		G4/5000
BVH (80°-90°)	372.6	0.7			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G5**

Type IV Short



REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
2.5°	7574.1	7602.8	7631.7	7672.5	7713.3	7737.6	7762.0	7774.1	7786.3	7780.9
5°	8144.4	8244.6	8345.2	8444.6	8544.4	8598.4	8652.5	8685.2	8718.1	8743.0
7.5°	8717.3	8880.6	9043.5	9190.3	9337.0	9425.4	9513.8	9561.6	9609.2	9632.2
10°	9156.5	9349.5	9542.4	9714.6	9886.8	9991.1	10094.9	10141.3	10187.6	10205.1
12.5°	9425.4	9634.6	9843.5	9999.2	10154.3	10230.0	10305.7	10331.1	10356.5	10359.2
15°	9588.9	9769.5	9949.7	10047.3	10145.1	10147.8	10150.5	10123.5	10096.5	10064.6
17.5°	9680.8	9802.7	9924.6	9926.5	9928.1	9818.7	9709.2	9608.9	9508.4	9437.6
20°	9782.2	9824.6	9867.3	9738.9	9610.6	9368.9	9127.3	8951.4	8775.4	8667.3
22.5°	9899.7	9844.1	9788.4	9522.4	9256.5	8901.1	8545.7	8325.7	8105.7	7986.3
25°	10051.1	9875.4	9699.7	9296.0	8892.2	8460.6	8029.0	7797.6	7566.8	7453.9
27.5°	10256.5	9942.4	9628.1	9093.3	8558.7	8080.3	7602.0	7374.4	7147.1	7040.4
30°	10533.5	10065.1	9597.0	8938.7	8280.3	7782.0	7283.6	7072.5	6861.4	6762.0
32.5°	10860.5	10219.2	9578.1	8833.3	8088.4	7620.1	7151.7	6986.0	6820.1	6748.5
35°	11257.8	10473.0	9688.4	8912.2	8136.3	7810.9	7485.7	7447.1	7408.4	7402.5
37.5°	11926.7	11003.5	10080.3	9374.9	8669.5	8648.4	8627.3	8804.1	8980.8	9072.7
40°	12937.5	11933.5	10929.4	10404.9	9880.3	10250.5	10620.8	11050.5	11480.2	11694.3
42.5°	14278.0	13281.8	12285.6	11983.5	11681.3	12488.9	13296.4	14078.0	14859.6	15318.5
45°	15933.4	15038.5	14143.4	14010.2	13876.7	15170.4	16464.4	17748.7	19033.3	19813.0
47.5°	18003.6	17133.1	16262.3	16235.2	16208.2	18074.6	19940.5	21820.8	23700.7	24804.7
50°	20717.0	19641.6	18566.5	18571.1	18575.7	20981.1	23386.4	25868.2	28350.0	29850.5
52.5°	23831.8	22529.7	21227.8	21096.2	20964.3	23837.5	26710.6	29781.4	32851.8	34650.4
55°	27147.9	25861.5	24575.0	24061.8	23548.6	26746.3	29943.8	33604.5	37265.2	39404.3
57.5°	30164.1	29463.5	28762.7	27733.3	26704.1	29933.0	33161.8	37308.2	41454.3	44106.9
60°	31987.0	33075.1	34163.4	32885.1	31606.7	34662.3	37717.9	42157.2	46596.6	49463.5
62.5°	31061.3	34034.5	37007.7	36863.6	36719.3	39518.4	42317.8	46541.4	50764.8	53414.8
65°	29208.7	31999.1	34789.6	35341.8	35893.6	39450.8	43008.3	47103.9	51199.2	53455.3
67.5°	26726.3	29380.3	32034.3	32293.2	32551.8	36258.2	39964.3	44077.5	48190.6	49958.1
70°	23744.0	26630.6	29517.6	29633.3	29749.2	33063.7	36377.9	39917.6	43456.9	44439.3
72.5°	20190.0	23502.6	26815.5	26898.7	26981.7	29574.9	32168.1	34819.1	37469.8	37569.3
75°	15694.2	19122.7	22551.3	22859.1	23166.9	25184.5	27202.0	29068.1	30934.3	30434.3
77.5°	11213.2	14413.7	17614.4	18054.9	18495.4	20029.2	21562.9	22886.4	24210.2	23350.7
80°	7339.0	10031.6	12724.0	13271.5	13819.1	14977.4	16135.2	16830.4	17525.2	16142.8
82.5°	4266.1	6106.9	7947.9	8559.5	9171.4	9968.7	10765.9	11055.9	11345.6	10259.2
85°	1877.0	2854.0	3831.0	4351.2	4871.5	5526.6	6181.5	6346.0	6510.6	5640.4
87.5°	581.1	909.4	1237.8	1528.1	1818.3	2145.9	2473.4	2487.5	2501.3	2099.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
7786.3	2.5°	7774.1	7762.0	7737.6	7713.3	7672.5	7631.7	7602.8	7574.1	7516.0	7457.9
8718.1	5°	8685.2	8652.5	8598.4	8544.4	8444.6	8345.2	8244.6	8144.4	8016.0	7887.6
9609.2	7.5°	9561.6	9513.8	9425.4	9337.0	9190.3	9043.5	8880.6	8717.3	8505.4	8293.8
10187.6	10°	10141.3	10094.9	9991.1	9886.8	9714.6	9542.4	9349.5	9156.5	8888.7	8620.8
10356.5	12.5°	10331.1	10305.7	10230.0	10154.3	9999.2	9843.5	9634.6	9425.4	9131.1	8837.1
10096.5	15°	10123.5	10150.5	10147.8	10145.1	10047.3	9949.7	9769.5	9588.9	9282.2	8975.4
9508.4	17.5°	9608.9	9709.2	9818.7	9928.1	9926.5	9924.6	9802.7	9680.8	9369.7	9058.7
8775.4	20°	8951.4	9127.3	9368.9	9610.6	9738.9	9867.3	9824.6	9782.2	9458.9	9135.4
8105.7	22.5°	8325.7	8545.7	8901.1	9256.5	9522.4	9788.4	9844.1	9899.7	9569.5	9238.9
7566.8	25°	7797.6	8029.0	8460.6	8892.2	9296.0	9699.7	9875.4	10051.1	9727.3	9403.8
7147.1	27.5°	7374.4	7602.0	8080.3	8558.7	9093.3	9628.1	9942.4	10256.5	9947.8	9638.9
6861.4	30°	7072.5	7283.6	7782.0	8280.3	8938.7	9597.0	10065.1	10533.5	10235.1	9937.0
6820.1	32.5°	6986.0	7151.7	7620.1	8088.4	8833.3	9578.1	10219.2	10860.5	10565.1	10270.0
7408.4	35°	7447.1	7485.7	7810.9	8136.3	8912.2	9688.4	10473.0	11257.8	10975.1	10692.1
8980.8	37.5°	8804.1	8627.3	8648.4	8669.5	9374.9	10080.3	11003.5	11926.7	11566.2	11205.6
11480.2	40°	11050.5	10620.8	10250.5	9880.3	10404.9	10929.4	11933.5	12937.5	12412.1	11886.7
14859.6	42.5°	14078.0	13296.4	12488.9	11681.3	11983.5	12285.6	13281.8	14278.0	13519.6	12761.3
19033.3	45°	17748.7	16464.4	15170.4	13876.7	14010.2	14143.4	15038.5	15933.4	14910.4	13887.5
23700.7	47.5°	21820.8	19940.5	18074.6	16208.2	16235.2	16262.3	17133.1	18003.6	16563.9	15123.9
28350.0	50°	25868.2	23386.4	20981.1	18575.7	18571.1	18566.5	19641.6	20717.0	18546.5	16375.8
32851.8	52.5°	29781.4	26710.6	23837.5	20964.3	21096.2	21227.8	22529.7	23831.8	20629.2	17426.6
37265.2	55°	33604.5	29943.8	26746.3	23548.6	24061.8	24575.0	25861.5	27147.9	22475.6	17803.6
41454.3	57.5°	37308.2	33161.8	29933.0	26704.1	27733.3	28762.7	29463.5	30164.1	23784.2	17404.4
46596.6	60°	42157.2	37717.9	34662.3	31606.7	32885.1	34163.4	33075.1	31987.0	24111.2	16235.2
50764.8	62.5°	46541.4	42317.8	39518.4	36719.3	36863.6	37007.7	34034.5	31061.3	22734.3	14407.2
51199.2	65°	47103.9	43008.3	39450.8	35893.6	35341.8	34789.6	31999.1	29208.7	20785.9	12363.2
48190.6	67.5°	44077.5	39964.3	36258.2	32551.8	32293.2	32034.3	29380.3	26726.3	18467.3	10208.4
43456.9	70°	39917.6	36377.9	33063.7	29749.2	29633.3	29517.6	26630.6	23744.0	15937.4	8130.9
37469.8	72.5°	34819.1	32168.1	29574.9	26981.7	26898.7	26815.5	23502.6	20190.0	13194.8	6199.8
30934.3	75°	29068.1	27202.0	25184.5	23166.9	22859.1	22551.3	19122.7	15694.2	10050.8	4407.4
24210.2	77.5°	22886.4	21562.9	20029.2	18495.4	18054.9	17614.4	14413.7	11213.2	7034.7	2856.1
17525.2	80°	16830.4	16135.2	14977.4	13819.1	13271.5	12724.0	10031.6	7339.0	4532.3	1725.6
11345.6	82.5°	11055.9	10765.9	9968.7	9171.4	8559.5	7947.9	6106.9	4266.1	2623.2	980.5
6510.6	85°	6346.0	6181.5	5526.6	4871.5	4351.2	3831.0	2854.0	1877.0	1180.0	483.2
2501.3	87.5°	2487.5	2473.4	2145.9	1818.3	1528.1	1237.8	909.4	581.1	386.5	191.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
7396.0	2.5°	7334.4	7272.2	7210.1	7150.6	7091.2	7033.6	6969.5	6917.7	6866.0	6819.3
7759.5	5°	7631.7	7502.8	7374.1	7253.9	7133.6	7020.1	6907.9	6810.1	6712.0	6629.8
8098.2	7.5°	7902.5	7712.0	7521.4	7353.6	7185.8	7030.9	6885.8	6755.5	6625.5	6517.4
8362.2	10°	8103.8	7872.5	7640.9	7442.5	7243.6	7052.5	6896.6	6759.3	6622.0	6513.9
8544.1	12.5°	8251.1	7978.2	7705.2	7480.6	7256.0	7055.2	6910.1	6797.7	6685.8	6613.9
8657.6	15°	8339.8	8025.5	7711.1	7451.2	7191.2	6968.7	6852.5	6798.7	6745.2	6755.0
8711.9	17.5°	8365.2	8000.3	7635.5	7322.8	7010.1	6748.5	6676.8	6696.6	6716.0	6833.9
8754.4	20°	8373.3	7931.1	7489.0	7101.4	6713.9	6409.3	6390.4	6482.3	6574.1	6778.7
8811.7	22.5°	8384.1	7846.3	7308.5	6841.7	6375.0	6028.2	6065.2	6201.2	6337.1	6570.6
8915.4	25°	8426.8	7762.5	7098.5	6551.7	6005.2	5649.8	5749.8	5906.6	6063.4	6273.3
9077.6	27.5°	8516.0	7706.5	6897.1	6286.6	5676.1	5352.6	5474.2	5625.5	5776.9	5949.6
9287.6	30°	8638.1	7680.3	6722.0	6065.0	5408.0	5136.3	5231.8	5351.7	5472.3	5615.5
9506.8	32.5°	8743.5	7647.9	6551.7	5873.9	5195.8	4976.9	5019.3	5090.4	5161.5	5275.8
9756.5	35°	8820.8	7586.8	6353.3	5686.1	5018.8	4836.4	4818.8	4838.2	4858.0	4945.3
10036.2	37.5°	8866.8	7482.2	6097.7	5465.0	4832.3	4672.8	4608.5	4586.9	4565.3	4628.0
10391.3	40°	8895.7	7338.2	5780.9	5201.2	4621.5	4476.9	4378.3	4329.3	4280.4	4325.6
10855.9	42.5°	8950.6	7189.5	5429.0	4910.1	4391.2	4258.0	4133.7	4068.8	4003.9	4040.7
11467.3	45°	9047.1	7051.4	5056.1	4601.0	4145.8	4010.7	3890.4	3827.2	3764.2	3795.0
12118.6	47.5°	9113.3	6937.4	4761.5	4356.4	3951.2	3776.9	3673.4	3620.4	3567.5	3596.7
12722.9	50°	9070.0	6813.1	4556.1	4193.9	3831.8	3602.6	3482.3	3435.3	3388.6	3434.0
13115.3	52.5°	8803.8	6603.1	4402.6	4086.9	3771.5	3508.0	3339.9	3293.4	3247.2	3315.6
13028.8	55°	8253.8	6255.0	4256.1	4009.4	3762.6	3517.5	3264.2	3190.7	3117.5	3214.5
12420.2	57.5°	7436.3	5764.2	4091.8	3917.5	3743.1	3526.9	3218.8	3111.8	3004.8	3109.1
11287.5	60°	6339.8	5126.9	3913.9	3776.9	3639.9	3497.2	3176.1	3037.5	2898.6	2990.2
9756.0	62.5°	5104.7	4364.2	3623.7	3532.6	3441.8	3424.2	3126.4	2952.9	2779.7	2837.8
8193.3	65°	4023.7	3678.0	3332.3	3289.4	3246.4	3248.6	3021.5	2837.2	2652.6	2675.1
6662.5	67.5°	3116.7	3018.6	2920.2	2944.2	2968.0	2962.1	2834.5	2681.0	2527.5	2520.5
5245.8	70°	2360.7	2388.9	2416.7	2528.0	2639.1	2639.1	2597.2	2488.0	2378.9	2354.5
4010.4	72.5°	1821.0	1905.6	1990.5	2148.3	2305.9	2332.4	2332.9	2258.0	2183.2	2147.5
2910.7	75°	1414.0	1490.8	1567.5	1744.3	1921.0	2043.2	2032.9	1975.4	1917.5	1883.5
1972.4	77.5°	1088.6	1140.8	1193.2	1364.8	1536.4	1737.8	1732.4	1686.2	1640.0	1605.4
1270.8	80°	816.2	837.8	859.4	1004.8	1150.0	1390.5	1389.7	1351.0	1312.1	1283.2
781.6	82.5°	583.2	587.0	591.3	698.4	805.4	1010.8	1022.1	1003.2	984.3	963.8
417.8	85°	352.7	350.8	348.6	427.0	505.4	658.1	673.0	652.7	632.4	609.4
173.2	87.5°	154.6	152.7	150.8	182.7	214.9	278.4	297.3	289.2	281.1	276.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
6772.8	2.5°	6732.0	6691.2	6650.1	6609.3	6577.7	6545.8	6520.1	6494.4	6474.4	6454.4
6547.9	5°	6475.5	6403.1	6337.4	6271.5	6220.9	6170.1	6134.7	6099.3	6074.2	6049.0
6409.3	7.5°	6318.2	6226.9	6146.3	6066.1	6005.8	5945.8	5903.6	5861.5	5832.5	5803.9
6405.8	10°	6307.7	6209.3	6118.8	6028.2	5956.3	5884.2	5837.1	5789.6	5762.3	5735.0
6542.5	12.5°	6465.2	6388.5	6294.7	6201.2	6109.3	6017.4	5956.6	5895.8	5865.2	5835.0
6764.7	15°	6744.7	6724.7	6643.3	6562.0	6431.2	6300.4	6207.9	6115.5	6073.1	6030.9
6951.7	17.5°	7014.4	7076.8	7011.2	6945.8	6772.5	6599.3	6463.1	6326.9	6264.2	6201.2
6983.6	20°	7114.7	7245.8	7215.5	7184.9	6986.8	6789.0	6622.0	6455.2	6375.0	6294.4
6804.7	22.5°	6975.2	7145.8	7164.1	7182.2	6993.1	6803.9	6632.0	6459.8	6375.2	6290.4
6483.6	25°	6651.4	6819.3	6882.0	6944.4	6789.3	6634.4	6481.4	6329.0	6255.5	6182.3
6122.0	27.5°	6256.6	6391.2	6460.9	6530.9	6420.4	6310.1	6191.5	6072.8	6023.6	5974.2
5758.8	30°	5870.4	5982.3	6039.0	6095.8	6011.7	5927.4	5842.5	5757.1	5732.0	5706.6
5390.4	32.5°	5497.4	5604.7	5667.7	5730.9	5653.6	5576.1	5508.2	5440.4	5423.9	5407.4
5032.3	35°	5138.2	5244.5	5320.1	5395.8	5340.7	5285.8	5223.1	5160.7	5135.5	5110.7
4690.4	37.5°	4796.1	4902.0	4995.5	5089.1	5063.6	5038.2	4980.7	4922.8	4877.2	4831.8
4370.7	40°	4472.9	4575.0	4682.6	4790.4	4796.6	4802.6	4753.7	4704.7	4638.3	4572.3
4077.7	42.5°	4174.5	4271.5	4387.7	4503.9	4535.0	4566.1	4524.7	4483.7	4401.2	4318.8
3826.4	45°	3918.3	4010.2	4130.7	4251.2	4295.8	4340.4	4303.1	4266.1	4171.8	4077.7
3625.6	47.5°	3715.6	3805.3	3924.2	4043.1	4094.5	4145.8	4119.9	4093.9	4010.2	3926.4
3479.6	50°	3564.5	3649.1	3755.6	3862.1	3928.0	3993.9	3992.3	3991.2	3924.2	3857.2
3383.7	52.5°	3461.5	3539.1	3638.3	3737.7	3815.8	3893.9	3908.0	3922.1	3867.5	3812.9
3311.3	55°	3395.0	3478.8	3565.8	3652.6	3735.3	3818.3	3837.7	3857.2	3809.6	3762.1
3213.4	57.5°	3311.8	3410.2	3496.1	3582.3	3665.8	3749.1	3768.8	3788.5	3740.4	3692.3
3081.5	60°	3194.5	3307.5	3394.8	3482.3	3566.1	3649.9	3671.5	3693.1	3646.1	3599.4
2895.9	62.5°	3027.5	3159.4	3252.6	3345.9	3422.6	3499.4	3520.2	3541.0	3498.6	3456.1
2697.2	65°	2838.3	2979.6	3068.8	3158.0	3225.6	3293.2	3314.5	3335.6	3294.8	3254.0
2513.4	67.5°	2643.7	2774.2	2858.8	2943.2	3001.5	3059.9	3080.7	3101.3	3063.7	3026.4
2330.2	70°	2444.8	2559.4	2632.4	2705.3	2758.0	2810.7	2830.7	2850.7	2820.2	2789.7
2112.1	72.5°	2202.4	2292.4	2358.3	2424.3	2475.9	2527.5	2551.3	2575.1	2549.7	2524.3
1849.1	75°	1916.2	1983.2	2042.9	2102.6	2149.7	2196.7	2221.6	2246.4	2234.0	2221.6
1570.8	77.5°	1625.4	1679.7	1731.0	1782.4	1831.8	1881.0	1904.3	1927.5	1910.2	1892.4
1254.0	80°	1299.4	1344.6	1387.8	1431.0	1468.6	1505.9	1536.7	1567.5	1560.0	1552.7
943.2	82.5°	939.4	935.7	920.5	905.4	985.4	1065.4	1117.8	1170.2	1167.0	1163.5
586.5	85°	567.0	547.3	505.4	463.5	538.4	613.5	678.4	743.2	737.8	732.4
272.4	87.5°	271.6	270.8	238.9	206.8	238.1	269.7	295.9	322.2	315.7	308.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
6436.0	2.5°	6417.4	6394.4	6417.4	6436.0	6454.4	6474.4	6494.4	6520.1	6545.8	6577.7
6029.8	5°	6010.6	5991.7	6010.6	6029.8	6049.0	6074.2	6099.3	6134.7	6170.1	6220.9
5786.6	7.5°	5769.6	5756.6	5769.6	5786.6	5803.9	5832.5	5861.5	5903.6	5945.8	6005.8
5720.4	10°	5705.8	5699.8	5705.8	5720.4	5735.0	5762.3	5789.6	5837.1	5884.2	5956.3
5822.5	12.5°	5810.1	5808.0	5810.1	5822.5	5835.0	5865.2	5895.8	5956.6	6017.4	6109.3
6014.7	15°	5998.5	5997.1	5998.5	6014.7	6030.9	6073.1	6115.5	6207.9	6300.4	6431.2
6180.6	17.5°	6159.8	6156.6	6159.8	6180.6	6201.2	6264.2	6326.9	6463.1	6599.3	6772.5
6268.8	20°	6243.1	6235.0	6243.1	6268.8	6294.4	6375.0	6455.2	6622.0	6789.0	6986.8
6262.0	22.5°	6233.6	6221.5	6233.6	6262.0	6290.4	6375.2	6459.8	6632.0	6803.9	6993.1
6155.5	25°	6129.0	6113.3	6129.0	6155.5	6182.3	6255.5	6329.0	6481.4	6634.4	6789.3
5962.0	27.5°	5949.8	5945.8	5949.8	5962.0	5974.2	6023.6	6072.8	6191.5	6310.1	6420.4
5706.6	30°	5706.6	5710.7	5706.6	5706.6	5706.6	5732.0	5757.1	5842.5	5927.4	6011.7
5409.6	32.5°	5412.0	5416.1	5412.0	5409.6	5407.4	5423.9	5440.4	5508.2	5576.1	5653.6
5105.3	35°	5099.9	5097.2	5099.9	5105.3	5110.7	5135.5	5160.7	5223.1	5285.8	5340.7
4807.7	37.5°	4783.7	4770.1	4783.7	4807.7	4831.8	4877.2	4922.8	4980.7	5038.2	5063.6
4527.4	40°	4483.1	4456.6	4483.1	4527.4	4572.3	4638.3	4704.7	4753.7	4802.6	4796.6
4253.7	42.5°	4188.5	4145.8	4188.5	4253.7	4318.8	4401.2	4483.7	4524.7	4566.1	4535.0
4001.2	45°	3924.8	3875.6	3924.8	4001.2	4077.7	4171.8	4266.1	4303.1	4340.4	4295.8
3855.6	47.5°	3785.0	3737.7	3785.0	3855.6	3926.4	4010.2	4093.9	4119.9	4145.8	4094.5
3791.8	50°	3726.4	3681.0	3726.4	3791.8	3857.2	3924.2	3991.2	3992.3	3993.9	3928.0
3754.2	52.5°	3695.8	3654.0	3695.8	3754.2	3812.9	3867.5	3922.1	3908.0	3893.9	3815.8
3710.7	55°	3659.4	3621.5	3659.4	3710.7	3762.1	3809.6	3857.2	3837.7	3818.3	3735.3
3641.5	57.5°	3590.4	3551.3	3590.4	3641.5	3692.3	3740.4	3788.5	3768.8	3749.1	3665.8
3546.9	60°	3494.5	3454.0	3494.5	3546.9	3599.4	3646.1	3693.1	3671.5	3649.9	3566.1
3401.0	62.5°	3345.9	3297.2	3345.9	3401.0	3456.1	3498.6	3541.0	3520.2	3499.4	3422.6
3200.5	65°	3147.2	3105.3	3147.2	3200.5	3254.0	3294.8	3335.6	3314.5	3293.2	3225.6
2976.7	67.5°	2926.9	2889.1	2926.9	2976.7	3026.4	3063.7	3101.3	3080.7	3059.9	3001.5
2742.1	70°	2694.5	2651.3	2694.5	2742.1	2789.7	2820.2	2850.7	2830.7	2810.7	2758.0
2478.9	72.5°	2433.7	2391.8	2433.7	2478.9	2524.3	2549.7	2575.1	2551.3	2527.5	2475.9
2183.5	75°	2145.3	2105.3	2145.3	2183.5	2221.6	2234.0	2246.4	2221.6	2196.7	2149.7
1854.0	77.5°	1815.6	1783.7	1815.6	1854.0	1892.4	1910.2	1927.5	1904.3	1881.0	1831.8
1501.0	80°	1449.2	1389.2	1449.2	1501.0	1552.7	1560.0	1567.5	1536.7	1505.9	1468.6
1120.0	82.5°	1076.2	1037.8	1076.2	1120.0	1163.5	1167.0	1170.2	1117.8	1065.4	985.4
698.4	85°	664.3	629.7	664.3	698.4	732.4	737.8	743.2	678.4	613.5	538.4
291.3	87.5°	273.5	256.7	273.5	291.3	308.6	315.7	322.2	295.9	269.7	238.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
6609.3	2.5°	6650.1	6691.2	6732.0	6772.8	6819.3	6866.0	6917.7	6969.5	7033.6	7091.2
6271.5	5°	6337.4	6403.1	6475.5	6547.9	6629.8	6712.0	6810.1	6907.9	7020.1	7133.6
6066.1	7.5°	6146.3	6226.9	6318.2	6409.3	6517.4	6625.5	6755.5	6885.8	7030.9	7185.8
6028.2	10°	6118.8	6209.3	6307.7	6405.8	6513.9	6622.0	6759.3	6896.6	7052.5	7243.6
6201.2	12.5°	6294.7	6388.5	6465.2	6542.5	6613.9	6685.8	6797.7	6910.1	7055.2	7256.0
6562.0	15°	6643.3	6724.7	6744.7	6764.7	6755.0	6745.2	6798.7	6852.5	6968.7	7191.2
6945.8	17.5°	7011.2	7076.8	7014.4	6951.7	6833.9	6716.0	6696.6	6676.8	6748.5	7010.1
7184.9	20°	7215.5	7245.8	7114.7	6983.6	6778.7	6574.1	6482.3	6390.4	6409.3	6713.9
7182.2	22.5°	7164.1	7145.8	6975.2	6804.7	6570.6	6337.1	6201.2	6065.2	6028.2	6375.0
6944.4	25°	6882.0	6819.3	6651.4	6483.6	6273.3	6063.4	5906.6	5749.8	5649.8	6005.2
6530.9	27.5°	6460.9	6391.2	6256.6	6122.0	5949.6	5776.9	5625.5	5474.2	5352.6	5676.1
6095.8	30°	6039.0	5982.3	5870.4	5758.8	5615.5	5472.3	5351.7	5231.8	5136.3	5408.0
5730.9	32.5°	5667.7	5604.7	5497.4	5390.4	5275.8	5161.5	5090.4	5019.3	4976.9	5195.8
5395.8	35°	5320.1	5244.5	5138.2	5032.3	4945.3	4858.0	4838.2	4818.8	4836.4	5018.8
5089.1	37.5°	4995.5	4902.0	4796.1	4690.4	4628.0	4565.3	4586.9	4608.5	4672.8	4832.3
4790.4	40°	4682.6	4575.0	4472.9	4370.7	4325.6	4280.4	4329.3	4378.3	4476.9	4621.5
4503.9	42.5°	4387.7	4271.5	4174.5	4077.7	4040.7	4003.9	4068.8	4133.7	4258.0	4391.2
4251.2	45°	4130.7	4010.2	3918.3	3826.4	3795.0	3764.2	3827.2	3890.4	4010.7	4145.8
4043.1	47.5°	3924.2	3805.3	3715.6	3625.6	3596.7	3567.5	3620.4	3673.4	3776.9	3951.2
3862.1	50°	3755.6	3649.1	3564.5	3479.6	3434.0	3388.6	3435.3	3482.3	3602.6	3831.8
3737.7	52.5°	3638.3	3539.1	3461.5	3383.7	3315.6	3247.2	3293.4	3339.9	3508.0	3771.5
3652.6	55°	3565.8	3478.8	3395.0	3311.3	3214.5	3117.5	3190.7	3264.2	3517.5	3762.6
3582.3	57.5°	3496.1	3410.2	3311.8	3213.4	3109.1	3004.8	3111.8	3218.8	3526.9	3743.1
3482.3	60°	3394.8	3307.5	3194.5	3081.5	2990.2	2898.6	3037.5	3176.1	3497.2	3639.9
3345.9	62.5°	3252.6	3159.4	3027.5	2895.9	2837.8	2779.7	2952.9	3126.4	3424.2	3441.8
3158.0	65°	3068.8	2979.6	2838.3	2697.2	2675.1	2652.6	2837.2	3021.5	3248.6	3246.4
2943.2	67.5°	2858.8	2774.2	2643.7	2513.4	2520.5	2527.5	2681.0	2834.5	2962.1	2968.0
2705.3	70°	2632.4	2559.4	2444.8	2330.2	2354.5	2378.9	2488.0	2597.2	2639.1	2639.1
2424.3	72.5°	2358.3	2292.4	2202.4	2112.1	2147.5	2183.2	2258.0	2332.9	2332.4	2305.9
2102.6	75°	2042.9	1983.2	1916.2	1849.1	1883.5	1917.5	1975.4	2032.9	2043.2	1921.0
1782.4	77.5°	1731.0	1679.7	1625.4	1570.8	1605.4	1640.0	1686.2	1732.4	1737.8	1536.4
1431.0	80°	1387.8	1344.6	1299.4	1254.0	1283.2	1312.1	1351.0	1389.7	1390.5	1150.0
905.4	82.5°	920.5	935.7	939.4	943.2	963.8	984.3	1003.2	1022.1	1010.8	805.4
463.5	85°	505.4	547.3	567.0	586.5	609.4	632.4	652.7	673.0	658.1	505.4
206.8	87.5°	238.9	270.8	271.6	272.4	276.7	281.1	289.2	297.3	278.4	214.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P951686  
 CATALOG NUMBER: GALN-SB5D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

325°		330°	335°	340°	345°	350°	355°	360°
7043.1	0°	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1	7043.1
7150.6	2.5°	7210.1	7272.2	7334.4	7396.0	7457.9	7516.0	7574.1
7253.9	5°	7374.1	7502.8	7631.7	7759.5	7887.6	8016.0	8144.4
7353.6	7.5°	7521.4	7712.0	7902.5	8098.2	8293.8	8505.4	8717.3
7442.5	10°	7640.9	7872.5	8103.8	8362.2	8620.8	8888.7	9156.5
7480.6	12.5°	7705.2	7978.2	8251.1	8544.1	8837.1	9131.1	9425.4
7451.2	15°	7711.1	8025.5	8339.8	8657.6	8975.4	9282.2	9588.9
7322.8	17.5°	7635.5	8000.3	8365.2	8711.9	9058.7	9369.7	9680.8
7101.4	20°	7489.0	7931.1	8373.3	8754.4	9135.4	9458.9	9782.2
6841.7	22.5°	7308.5	7846.3	8384.1	8811.7	9238.9	9569.5	9899.7
6551.7	25°	7098.5	7762.5	8426.8	8915.4	9403.8	9727.3	10051.1
6286.6	27.5°	6897.1	7706.5	8516.0	9077.6	9638.9	9947.8	10256.5
6065.0	30°	6722.0	7680.3	8638.1	9287.6	9937.0	10235.1	10533.5
5873.9	32.5°	6551.7	7647.9	8743.5	9506.8	10270.0	10565.1	10860.5
5686.1	35°	6353.3	7586.8	8820.8	9756.5	10692.1	10975.1	11257.8
5465.0	37.5°	6097.7	7482.2	8866.8	10036.2	11205.6	11566.2	11926.7
5201.2	40°	5780.9	7338.2	8895.7	10391.3	11886.7	12412.1	12937.5
4910.1	42.5°	5429.0	7189.5	8950.6	10855.9	12761.3	13519.6	14278.0
4601.0	45°	5056.1	7051.4	9047.1	11467.3	13887.5	14910.4	15933.4
4356.4	47.5°	4761.5	6937.4	9113.3	12118.6	15123.9	16563.9	18003.6
4193.9	50°	4556.1	6813.1	9070.0	12722.9	16375.8	18546.5	20717.0
4086.9	52.5°	4402.6	6603.1	8803.8	13115.3	17426.6	20629.2	23831.8
4009.4	55°	4256.1	6255.0	8253.8	13028.8	17803.6	22475.6	27147.9
3917.5	57.5°	4091.8	5764.2	7436.3	12420.2	17404.4	23784.2	30164.1
3776.9	60°	3913.9	5126.9	6339.8	11287.5	16235.2	24111.2	31987.0
3532.6	62.5°	3623.7	4364.2	5104.7	9756.0	14407.2	22734.3	31061.3
3289.4	65°	3332.3	3678.0	4023.7	8193.3	12363.2	20785.9	29208.7
2944.2	67.5°	2920.2	3018.6	3116.7	6662.5	10208.4	18467.3	26726.3
2528.0	70°	2416.7	2388.9	2360.7	5245.8	8130.9	15937.4	23744.0
2148.3	72.5°	1990.5	1905.6	1821.0	4010.4	6199.8	13194.8	20190.0
1744.3	75°	1567.5	1490.8	1414.0	2910.7	4407.4	10050.8	15694.2
1364.8	77.5°	1193.2	1140.8	1088.6	1972.4	2856.1	7034.7	11213.2
1004.8	80°	859.4	837.8	816.2	1270.8	1725.6	4532.3	7339.0
698.4	82.5°	591.3	587.0	583.2	781.6	980.5	2623.2	4266.1
427.0	85°	348.6	350.8	352.7	417.8	483.2	1180.0	1877.0
182.7	87.5°	150.8	152.7	154.6	173.2	191.9	386.5	581.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)