

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P953122

Luminaire Tested: **GALN-SB6D-735-U-T3R**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P953122  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB6D-735-U-T3R  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(6) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE III  
ROADWAY OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 63349 lumens  
Efficiency: N/A  
Efficacy: 143.9 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Medium  
BUG Rating: B4 - U0 - G5  
  
Input Watts (W): 440.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P953122  
 CATALOG NUMBER: GALN-SB6D-735-U-T3R

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 16.8 fc  
 Type III - Medium - N/A

REPORT NUMBER: P953122  
CATALOG NUMBER: GALN-SB6D-735-U-T3R

### Luminous Intensity Polar Plot



— Vertical Plane Through 77-Deg Lateral      - - - Horizontal Cone Through 70-Deg Vertical

REPORT NUMBER: P953122  
 CATALOG NUMBER: GALN-SB6D-735-U-T3R

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	13872.4	0.0	13872.4
	% Fixture	21.9	0.0	21.9
<b>Street Side</b>	Lumens	49476.6	0.0	49476.6
	% Fixture	78.1	0.0	78.1
<b>Total</b>	Lumens	63349.0	0.0	63349.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	842.9	1.3
10°-20°	2432.6	3.8
20°-30°	4160.2	6.6
30°-40°	6690.0	10.6
40°-50°	10444.8	16.5
50°-60°	13951.8	22.0
60°-70°	14870.4	23.5
70°-80°	9154.2	14.5
80°-90°	802.2	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	63349.0	100.0
0°-180°	63349.0	100.0



REPORT NUMBER: P953122


CATALOG NUMBER: GALN-SB6D-735-U-T3R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3881.1	6.1			
FM (30°-60°)	24717.4	39.0			
FH (60°-80°)	20317.1	32.1			G5
FVH (80°-90°)	560.9	0.9			G4/750
BL (0°-30°)	3554.6	5.6	B4/5000		
BM (30°-60°)	6369.1	10.1	B4/8500		
BH (60°-80°)	3707.5	5.9	B4/5000		G4/5000
BVH (80°-90°)	241.2	0.4			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G5**

Type III Medium



REPORT NUMBER: P953122  
 CATALOG NUMBER: GALN-SB6D-735-U-T3R

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8
2.5°	8146.7	8143.5	8185.6	8198.6	8276.5	8331.6	8435.5	8545.8	8688.5	8704.7
5°	7676.3	7676.3	7724.9	7776.8	7877.4	7987.7	8146.7	8338.1	8584.7	8623.6
7.5°	7277.2	7303.2	7345.3	7445.9	7562.7	7721.7	7965.0	8237.5	8562.0	8623.6
10°	6956.0	6985.2	7037.1	7118.2	7293.4	7514.0	7832.0	8182.4	8617.1	8714.5
12.5°	6855.4	6884.6	6913.8	6975.5	7137.7	7397.2	7776.8	8208.3	8750.2	8847.5
15°	7089.0	7124.7	7102.0	7085.8	7170.1	7407.0	7802.8	8302.4	8915.6	9055.1
17.5°	7627.6	7640.6	7588.7	7436.2	7423.2	7549.7	7926.1	8432.2	9123.3	9275.8
20°	8497.1	8474.4	8367.3	8065.6	7893.6	7867.7	8137.0	8626.9	9337.4	9499.6
22.5°	9678.1	9652.1	9438.0	8961.1	8578.2	8325.1	8441.9	8879.9	9577.5	9759.2
25°	11151.0	11115.3	10800.6	10151.7	9558.0	8931.9	8857.2	9214.1	9872.7	10041.4
27.5°	12870.6	12841.4	12500.7	11644.2	10787.7	9762.4	9373.1	9606.7	10180.9	10372.4
30°	14719.9	14804.2	14200.8	13279.4	12195.7	10846.1	10067.4	10090.1	10580.0	10752.0
32.5°	16893.6	17039.6	16312.9	15144.9	13665.4	12023.8	10943.4	10764.9	11160.8	11303.5
35°	19047.9	19213.4	18609.9	17318.6	15615.3	13412.4	11858.3	11540.4	11932.9	12088.7
37.5°	20910.2	21130.8	20819.4	19696.8	17701.5	15086.5	13052.2	12452.0	12883.5	13078.2
40°	22379.9	22717.3	22694.6	21993.8	20160.7	17117.5	14567.4	13577.8	14064.5	14275.4
42.5°	23573.9	23865.9	24118.9	24083.2	22727.1	19424.3	16348.6	15041.1	15410.9	15654.3
45°	24397.9	24709.4	25254.5	25841.7	25196.1	21893.3	18389.3	16776.8	17114.2	17480.9
47.5°	25134.4	25488.1	26195.3	27126.5	27291.9	24372.0	20624.7	18798.1	19106.3	19485.9
50°	25199.3	25504.3	26600.9	27921.4	28781.1	26753.4	23025.6	21065.9	21354.7	21760.2
52.5°	23632.3	24112.4	26026.6	27898.7	29465.7	28745.4	25410.2	23424.6	23749.1	24235.7
55°	18343.9	19047.9	24342.8	27029.2	29222.4	30033.5	27678.0	25932.5	26347.8	26857.2
57.5°	15800.3	16108.5	19323.7	25445.9	28112.8	30367.6	29592.2	28466.4	29134.8	29692.8
60°	14200.8	14457.1	16358.3	22983.4	26652.8	29838.8	31071.7	30828.4	31983.4	32648.5
62.5°	12487.7	12731.1	14460.3	19190.7	24784.0	28959.6	32006.1	33008.6	34903.3	35630.1
65°	10787.7	10995.3	12653.2	16124.7	22409.1	28080.3	32489.5	34893.6	37605.9	38358.6
67.5°	8892.9	9064.9	10631.9	13603.8	19521.6	26876.7	32729.6	36376.3	39958.1	40603.7
70°	6417.4	6550.5	8169.4	10758.5	15897.6	24806.7	32632.2	37427.5	41178.0	41693.9
72.5°	3033.5	3153.6	5054.8	6985.2	11228.9	20777.2	30662.9	36593.7	39938.6	39682.3
75°	1619.0	1722.8	2903.7	3831.6	5930.8	14242.9	25092.2	31522.7	33537.4	32291.6
77.5°	1096.6	1177.7	1797.4	2300.3	2709.1	6761.3	16127.9	21825.1	20997.8	18940.8
80°	869.5	953.9	1473.0	1557.3	1310.7	2443.0	6664.0	10103.1	7257.7	5804.2
82.5°	668.3	762.4	1239.4	1129.1	713.8	1002.5	1940.2	3195.7	1859.0	1414.6
85°	408.8	509.4	973.3	720.3	402.3	457.5	658.6	889.0	567.8	473.7
87.5°	207.6	292.0	493.1	262.8	181.7	107.1	175.2	175.2	149.2	129.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P953122  
 CATALOG NUMBER: GALN-SB6D-735-U-T3R

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
8837.8	0°	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8	8837.8
8792.3	2.5°	8870.2	8935.1	9045.4	9149.2	9230.3	9308.2	9386.1	9428.2	9441.2	9493.1
8841.0	5°	8974.0	9094.1	9308.2	9509.4	9635.9	9713.8	9768.9	9801.4	9807.8	9824.1
8974.0	7.5°	9165.4	9356.9	9655.4	9856.5	9950.6	9944.1	9921.4	9840.3	9807.8	9778.6
9168.7	10°	9434.7	9687.8	10054.4	10193.9	10135.5	9979.8	9778.6	9541.8	9431.5	9324.4
9434.7	12.5°	9768.9	10090.1	10450.2	10443.7	10155.0	9755.9	9288.7	8925.4	8695.0	8529.5
9762.4	15°	10174.5	10544.3	10820.1	10599.5	9966.8	9249.8	8565.2	8091.5	7883.9	7702.2
10093.3	17.5°	10593.0	10988.8	11115.3	10550.8	9493.1	8500.3	7724.9	7351.8	7147.4	7050.1
10450.2	20°	11001.8	11394.4	11290.5	10271.8	8772.9	7650.3	6959.3	6754.9	6712.7	6735.4
10797.4	22.5°	11433.3	11783.7	11326.2	9733.2	7854.7	6780.8	6401.2	6407.7	6501.8	6569.9
11160.8	25°	11874.5	12111.4	11232.1	8954.6	6868.4	6141.7	6047.6	6151.4	6336.3	6469.3
11569.6	27.5°	12299.5	12403.4	11027.7	7991.0	6021.6	5684.2	5700.4	5914.6	6193.6	6378.5
12065.9	30°	12779.7	12662.9	10635.2	6907.3	5434.4	5291.6	5427.9	5677.7	5956.7	6122.2
12692.1	32.5°	13321.5	12886.8	10012.2	5904.8	5019.1	4976.9	5200.8	5363.0	5486.3	5535.0
13522.7	35°	13996.4	13201.5	9214.1	5200.8	4646.0	4746.6	4960.7	4879.6	4830.9	4805.0
14638.8	37.5°	14872.4	13626.5	8279.7	4743.3	4344.3	4581.1	4668.7	4415.6	4224.2	4130.1
15991.7	40°	15926.8	14249.4	7381.0	4389.7	4152.8	4438.3	4285.9	3980.9	3737.6	3604.5
17513.3	42.5°	17098.0	14901.6	6625.1	4123.6	4045.8	4321.5	4003.6	3640.2	3247.7	3205.5
19326.9	45°	18327.7	15573.2	6109.2	3919.2	3993.9	4221.0	3841.4	3254.1	2975.1	3147.1
21147.0	47.5°	19557.3	16189.6	5797.8	3766.8	3967.9	4107.4	3698.6	3040.0	2842.1	3091.9
23096.9	50°	20926.4	16741.1	5658.2	3656.4	3938.7	4062.0	3484.5	2984.9	2702.6	2868.1
25115.0	52.5°	22285.8	17169.4	5554.4	3546.1	3896.5	4026.3	3380.7	2920.0	2533.9	2543.6
27145.9	55°	23642.0	17448.4	5440.9	3400.1	3802.4	3948.4	3370.9	2848.6	2407.3	2361.9
29293.7	57.5°	25089.0	17607.4	5301.4	3237.9	3640.2	3750.5	3361.2	2793.4	2368.4	2293.8
31490.2	60°	26562.0	17841.0	5119.7	3040.0	3422.8	3513.7	3338.5	2774.0	2345.7	2219.2
33560.1	62.5°	27882.4	17922.1	4902.3	2851.8	3143.8	3280.1	3289.8	2757.7	2284.1	2066.7
35279.7	65°	28748.7	17571.7	4522.7	2637.7	2842.1	3040.0	3195.7	2702.6	2173.8	1956.4
36129.7	67.5°	28713.0	16572.4	3929.0	2361.9	2550.1	2774.0	3059.5	2608.5	2040.7	1820.1
35487.3	70°	27376.3	14599.8	3176.3	2040.7	2228.9	2488.5	2884.3	2469.0	1881.8	1670.9
31555.1	72.5°	23479.8	11426.8	2306.8	1664.4	1855.8	2193.2	2657.2	2300.3	1719.5	1537.8
23320.8	75°	16773.6	7231.8	1563.8	1278.3	1443.8	1859.0	2374.9	2102.4	1570.3	1544.3
11679.9	77.5°	8568.5	3455.3	1035.0	934.4	1005.8	1466.5	1995.3	1878.5	1593.0	1275.1
3322.3	80°	2786.9	1275.1	652.1	635.9	668.3	976.6	1544.3	1541.1	1206.9	866.3
804.6	82.5°	889.0	548.3	425.0	408.8	392.6	613.2	1077.1	1219.9	814.3	548.3
288.8	85°	353.6	327.7	249.8	230.4	165.5	288.8	564.5	811.1	606.7	395.8
74.6	87.5°	129.8	129.8	68.1	48.7	35.7	97.3	152.5	243.3	347.2	204.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
8837.8
9522.3
9850.0
9785.1
9292.0
8490.6
7682.8
7079.3
6725.7
6586.1
6505.0
6423.9
6161.1
5560.9
4830.9
4152.8
3614.3
3247.7
3237.9
3208.7
2991.3
2611.7
2394.4
2303.5
2228.9
2066.7
1956.4
1829.8
1690.3
1528.1
1456.7
1135.5
765.7
545.1
405.6
201.2
0.0

F REPORT)