

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P947402

Luminaire Tested: **GALN-SB2D-735-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P947402  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SB2D-735-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(2) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20277 lumens  
Efficiency: N/A  
Efficacy: 137.4 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 147.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.2 fc  
 Type IV - Short - N/A

REPORT NUMBER: P947402  
CATALOG NUMBER: GALN-SB2D-735-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P947402

CATALOG NUMBER: GALN-SB2D-735-U-SLL

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5153.4	0.0	5153.4
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	15123.6	0.0	15123.6
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	20277.0	0.0	20277.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.6	1.4
10°-20°	868.3	4.3
20°-30°	1341.2	6.6
30°-40°	1699.6	8.4
40°-50°	2563.5	12.6
50°-60°	4141.7	20.4
60°-70°	5163.3	25.5
70°-80°	3385.8	16.7
80°-90°	837.1	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	20277.0	100.0
0°-180°	20277.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P947402


CATALOG NUMBER: GALN-SB2D-735-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1363.9	6.7			
FM (30°-60°)	5914.4	29.2			
FH (60°-80°)	7155.8	35.3			G3/7500
FVH (80°-90°)	689.6	3.4			G4/750
BL (0°-30°)	1122.2	5.5	B3/2500		
BM (30°-60°)	2490.4	12.3	B2/2500		
BH (60°-80°)	1393.2	6.9	B3/2500		G3/2500
BVH (80°-90°)	147.5	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**

Type IV Short



REPORT NUMBER: P947402

CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2.5°	2998.5	3009.8	3021.3	3037.5	3053.6	3063.2	3072.9	3077.7	3082.5	3080.4
5°	3224.3	3264.0	3303.8	3343.1	3382.6	3404.0	3425.4	3438.4	3451.4	3461.3
7.5°	3451.1	3515.7	3580.2	3638.3	3696.4	3731.4	3766.4	3785.3	3804.2	3813.3
10°	3625.0	3701.3	3777.7	3845.9	3914.1	3955.4	3996.4	4014.8	4033.1	4040.1
12.5°	3731.4	3814.2	3896.9	3958.6	4020.0	4049.9	4079.9	4090.0	4100.0	4101.1
15°	3796.1	3867.6	3939.0	3977.6	4016.3	4017.4	4018.5	4007.8	3997.1	3984.5
17.5°	3832.5	3880.8	3929.0	3929.8	3930.4	3887.1	3843.8	3804.1	3764.3	3736.2
20°	3872.6	3889.4	3906.3	3855.5	3804.7	3709.1	3613.4	3543.7	3474.1	3431.3
22.5°	3919.2	3897.1	3875.1	3769.8	3664.5	3523.8	3383.1	3296.1	3209.0	3161.7
25°	3979.1	3909.6	3840.0	3680.2	3520.3	3349.4	3178.6	3087.0	2995.6	2950.9
27.5°	4060.4	3936.1	3811.7	3599.9	3388.3	3198.9	3009.5	2919.4	2829.5	2787.2
30°	4170.1	3984.7	3799.4	3538.7	3278.1	3080.8	2883.5	2799.9	2716.4	2677.0
32.5°	4299.6	4045.7	3791.9	3497.0	3202.1	3016.7	2831.3	2765.7	2700.0	2671.6
35°	4456.8	4146.1	3835.5	3528.2	3221.1	3092.2	2963.5	2948.2	2932.9	2930.6
37.5°	4721.6	4356.2	3990.7	3711.4	3432.2	3423.8	3415.5	3485.4	3555.4	3591.8
40°	5121.8	4724.3	4326.8	4119.2	3911.5	4058.1	4204.6	4374.8	4544.9	4629.6
42.5°	5652.5	5258.1	4863.7	4744.1	4624.5	4944.2	5263.9	5573.3	5882.7	6064.4
45°	6307.8	5953.6	5599.2	5546.5	5493.6	6005.8	6518.1	7026.5	7535.0	7843.7
47.5°	7127.4	6782.8	6438.0	6427.3	6416.6	7155.5	7894.2	8638.6	9382.8	9819.9
50°	8201.6	7775.9	7350.3	7352.1	7353.9	8306.2	9258.4	10240.9	11223.5	11817.5
52.5°	9434.7	8919.2	8403.8	8351.7	8299.5	9437.0	10574.4	11790.1	13005.6	13717.7
55°	10747.5	10238.3	9729.0	9525.8	9322.6	10588.5	11854.4	13303.6	14752.9	15599.7
57.5°	11941.6	11664.3	11386.8	10979.3	10571.9	11850.1	13128.4	14769.9	16411.3	17461.4
60°	12663.3	13094.0	13524.9	13018.8	12512.7	13722.4	14932.1	16689.6	18447.0	19582.0
62.5°	12296.8	13473.9	14650.9	14593.9	14536.7	15644.9	16753.1	18425.2	20097.2	21146.3
65°	11563.4	12668.1	13772.8	13991.4	14209.9	15618.1	17026.5	18647.9	20269.1	21162.3
67.5°	10580.6	11631.3	12682.0	12784.5	12886.9	14354.2	15821.4	17449.7	19078.1	19777.8
70°	9400.0	10542.8	11685.7	11731.5	11777.4	13089.5	14401.6	15802.9	17204.1	17593.0
72.5°	7993.0	9304.4	10615.9	10648.9	10681.7	11708.3	12735.0	13784.5	14833.9	14873.2
75°	6213.1	7570.5	8927.8	9049.7	9171.5	9970.2	10768.9	11507.7	12246.5	12048.6
77.5°	4439.2	5706.2	6973.3	7147.7	7322.1	7929.3	8536.5	9060.5	9584.5	9244.3
80°	2905.4	3971.4	5037.3	5254.0	5470.8	5929.4	6387.8	6662.9	6938.0	6390.7
82.5°	1688.9	2417.6	3146.5	3388.6	3630.8	3946.5	4262.1	4376.9	4491.6	4061.5
85°	743.1	1129.9	1516.6	1722.6	1928.6	2187.9	2447.2	2512.3	2577.5	2233.0
87.5°	230.0	360.0	490.0	604.9	719.9	849.5	979.2	984.8	990.2	831.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
3082.5	2.5°	3077.7	3072.9	3063.2	3053.6	3037.5	3021.3	3009.8	2998.5	2975.5	2952.5
3451.4	5°	3438.4	3425.4	3404.0	3382.6	3343.1	3303.8	3264.0	3224.3	3173.4	3122.6
3804.2	7.5°	3785.3	3766.4	3731.4	3696.4	3638.3	3580.2	3515.7	3451.1	3367.2	3283.4
4033.1	10°	4014.8	3996.4	3955.4	3914.1	3845.9	3777.7	3701.3	3625.0	3518.9	3412.9
4100.0	12.5°	4090.0	4079.9	4049.9	4020.0	3958.6	3896.9	3814.2	3731.4	3614.9	3498.5
3997.1	15°	4007.8	4018.5	4017.4	4016.3	3977.6	3939.0	3867.6	3796.1	3674.7	3553.3
3764.3	17.5°	3804.1	3843.8	3887.1	3930.4	3929.8	3929.0	3880.8	3832.5	3709.4	3586.2
3474.1	20°	3543.7	3613.4	3709.1	3804.7	3855.5	3906.3	3889.4	3872.6	3744.7	3616.6
3209.0	22.5°	3296.1	3383.1	3523.8	3664.5	3769.8	3875.1	3897.1	3919.2	3788.4	3657.6
2995.6	25°	3087.0	3178.6	3349.4	3520.3	3680.2	3840.0	3909.6	3979.1	3850.9	3722.9
2829.5	27.5°	2919.4	3009.5	3198.9	3388.3	3599.9	3811.7	3936.1	4060.4	3938.2	3815.9
2716.4	30°	2799.9	2883.5	3080.8	3278.1	3538.7	3799.4	3984.7	4170.1	4052.0	3934.0
2700.0	32.5°	2765.7	2831.3	3016.7	3202.1	3497.0	3791.9	4045.7	4299.6	4182.6	4065.8
2932.9	35°	2948.2	2963.5	3092.2	3221.1	3528.2	3835.5	4146.1	4456.8	4344.9	4232.9
3555.4	37.5°	3485.4	3415.5	3423.8	3432.2	3711.4	3990.7	4356.2	4721.6	4578.9	4436.2
4544.9	40°	4374.8	4204.6	4058.1	3911.5	4119.2	4326.8	4724.3	5121.8	4913.8	4705.8
5882.7	42.5°	5573.3	5263.9	4944.2	4624.5	4744.1	4863.7	5258.1	5652.5	5352.3	5052.0
7535.0	45°	7026.5	6518.1	6005.8	5493.6	5546.5	5599.2	5953.6	6307.8	5902.9	5497.9
9382.8	47.5°	8638.6	7894.2	7155.5	6416.6	6427.3	6438.0	6782.8	7127.4	6557.4	5987.4
11223.5	50°	10240.9	9258.4	8306.2	7353.9	7352.1	7350.3	7775.9	8201.6	7342.4	6483.0
13005.6	52.5°	11790.1	10574.4	9437.0	8299.5	8351.7	8403.8	8919.2	9434.7	8166.8	6899.0
14752.9	55°	13303.6	11854.4	10588.5	9322.6	9525.8	9729.0	10238.3	10747.5	8897.8	7048.2
16411.3	57.5°	14769.9	13128.4	11850.1	10571.9	10979.3	11386.8	11664.3	11941.6	9415.9	6890.2
18447.0	60°	16689.6	14932.1	13722.4	12512.7	13018.8	13524.9	13094.0	12663.3	9545.4	6427.3
20097.2	62.5°	18425.2	16753.1	15644.9	14536.7	14593.9	14650.9	13473.9	12296.8	9000.2	5703.6
20269.1	65°	18647.9	17026.5	15618.1	14209.9	13991.4	13772.8	12668.1	11563.4	8228.9	4894.4
19078.1	67.5°	17449.7	15821.4	14354.2	12886.9	12784.5	12682.0	11631.3	10580.6	7311.0	4041.4
17204.1	70°	15802.9	14401.6	13089.5	11777.4	11731.5	11685.7	10542.8	9400.0	6309.4	3218.9
14833.9	72.5°	13784.5	12735.0	11708.3	10681.7	10648.9	10615.9	9304.4	7993.0	5223.7	2454.4
12246.5	75°	11507.7	10768.9	9970.2	9171.5	9049.7	8927.8	7570.5	6213.1	3979.0	1744.9
9584.5	77.5°	9060.5	8536.5	7929.3	7322.1	7147.7	6973.3	5706.2	4439.2	2784.9	1130.7
6938.0	80°	6662.9	6387.8	5929.4	5470.8	5254.0	5037.3	3971.4	2905.4	1794.3	683.2
4491.6	82.5°	4376.9	4262.1	3946.5	3630.8	3388.6	3146.5	2417.6	1688.9	1038.5	388.2
2577.5	85°	2512.3	2447.2	2187.9	1928.6	1722.6	1516.6	1129.9	743.1	467.1	191.3
990.2	87.5°	984.8	979.2	849.5	719.9	604.9	490.0	360.0	230.0	153.0	76.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2928.0	2.5°	2903.6	2879.0	2854.4	2830.8	2807.3	2784.5	2759.2	2738.6	2718.2	2699.7
3071.9	5°	3021.3	2970.3	2919.3	2871.7	2824.1	2779.2	2734.8	2696.0	2657.2	2624.7
3206.0	7.5°	3128.5	3053.1	2977.6	2911.2	2844.8	2783.4	2726.0	2674.4	2623.0	2580.2
3310.5	10°	3208.2	3116.6	3024.9	2946.4	2867.7	2792.0	2730.3	2675.9	2621.6	2578.8
3382.5	12.5°	3266.5	3158.5	3050.4	2961.5	2872.6	2793.1	2735.6	2691.1	2646.8	2618.4
3427.4	15°	3301.6	3177.2	3052.8	2949.8	2846.9	2758.8	2712.8	2691.5	2670.4	2674.2
3448.9	17.5°	3311.7	3167.2	3022.8	2899.0	2775.2	2671.6	2643.3	2651.1	2658.8	2705.4
3465.7	20°	3314.9	3139.8	2964.8	2811.4	2657.9	2537.4	2529.9	2566.2	2602.6	2683.6
3488.4	22.5°	3319.2	3106.2	2893.3	2708.6	2523.8	2386.5	2401.2	2455.0	2508.8	2601.2
3529.5	25°	3336.1	3073.1	2810.2	2593.7	2377.4	2236.7	2276.3	2338.4	2400.4	2483.5
3593.7	27.5°	3371.4	3050.9	2730.5	2488.8	2247.1	2119.0	2167.2	2227.1	2287.0	2355.4
3676.8	30°	3419.7	3040.6	2661.2	2401.1	2140.9	2033.4	2071.2	2118.7	2166.4	2223.1
3763.6	32.5°	3461.5	3027.7	2593.7	2325.4	2057.0	1970.3	1987.1	2015.2	2043.4	2088.6
3862.5	35°	3492.1	3003.5	2515.2	2251.0	1986.9	1914.7	1907.7	1915.4	1923.2	1957.8
3973.2	37.5°	3510.3	2962.1	2414.0	2163.5	1913.1	1849.9	1824.5	1815.9	1807.3	1832.2
4113.8	40°	3521.7	2905.1	2288.6	2059.1	1829.6	1772.4	1733.3	1713.9	1694.6	1712.4
4297.7	42.5°	3543.4	2846.3	2149.3	1943.9	1738.4	1685.7	1636.5	1610.8	1585.1	1599.7
4539.8	45°	3581.6	2791.6	2001.6	1821.5	1641.3	1587.8	1540.2	1515.1	1490.2	1502.4
4797.6	47.5°	3607.8	2746.4	1885.0	1724.6	1564.3	1495.2	1454.3	1433.3	1412.3	1423.9
5036.8	50°	3590.7	2697.2	1803.7	1660.3	1517.0	1426.2	1378.6	1360.0	1341.5	1359.5
5192.2	52.5°	3485.3	2614.1	1742.9	1618.0	1493.1	1388.8	1322.2	1303.8	1285.5	1312.6
5158.0	55°	3267.6	2476.3	1684.9	1587.3	1489.6	1392.5	1292.3	1263.2	1234.2	1272.6
4917.0	57.5°	2943.9	2282.0	1619.9	1550.9	1481.9	1396.3	1274.3	1231.9	1189.6	1230.9
4468.6	60°	2509.9	2029.7	1549.5	1495.2	1441.0	1384.5	1257.4	1202.5	1147.5	1183.8
3862.3	62.5°	2020.9	1727.7	1434.6	1398.5	1362.6	1355.6	1237.7	1169.0	1100.4	1123.4
3243.6	65°	1592.9	1456.1	1319.2	1302.2	1285.2	1286.1	1196.2	1123.2	1050.1	1059.0
2637.6	67.5°	1233.9	1195.0	1156.1	1165.6	1175.0	1172.7	1122.2	1061.4	1000.6	997.8
2076.8	70°	934.6	945.7	956.7	1000.8	1044.8	1044.8	1028.2	985.0	941.8	932.1
1587.7	72.5°	720.9	754.4	788.0	850.5	912.9	923.4	923.6	893.9	864.3	850.2
1152.3	75°	559.8	590.2	620.6	690.5	760.5	808.9	804.8	782.0	759.1	745.6
780.8	77.5°	431.0	451.6	472.4	540.3	608.3	688.0	685.8	667.5	649.2	635.5
503.1	80°	323.1	331.7	340.2	397.8	455.3	550.5	550.2	534.9	519.5	508.0
309.4	82.5°	230.9	232.4	234.1	276.5	318.8	400.2	404.7	397.2	389.7	381.5
165.4	85°	139.6	138.9	138.0	169.1	200.1	260.5	266.4	258.4	250.4	241.3
68.6	87.5°	61.2	60.5	59.7	72.3	85.1	110.2	117.7	114.5	111.3	109.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2681.3	2.5°	2665.1	2649.0	2632.7	2616.5	2604.0	2591.4	2581.2	2571.1	2563.1	2555.2
2592.2	5°	2563.6	2534.9	2508.9	2482.8	2462.8	2442.7	2428.7	2414.6	2404.7	2394.7
2537.4	7.5°	2501.3	2465.1	2433.3	2401.5	2377.6	2353.9	2337.2	2320.5	2309.0	2297.7
2536.0	10°	2497.1	2458.2	2422.3	2386.5	2358.0	2329.5	2310.9	2292.0	2281.2	2270.4
2590.1	12.5°	2559.5	2529.1	2492.0	2455.0	2418.6	2382.2	2358.1	2334.1	2322.0	2310.0
2678.1	15°	2670.1	2662.2	2630.0	2597.8	2546.0	2494.2	2457.7	2421.1	2404.3	2387.6
2752.1	17.5°	2776.9	2801.6	2775.6	2749.7	2681.2	2612.6	2558.7	2504.7	2479.9	2455.0
2764.7	20°	2816.6	2868.5	2856.5	2844.4	2766.0	2687.7	2621.6	2555.6	2523.8	2491.9
2693.9	22.5°	2761.4	2828.9	2836.2	2843.4	2768.5	2693.6	2625.5	2557.4	2523.9	2490.3
2566.8	25°	2633.2	2699.7	2724.5	2749.2	2687.8	2626.5	2565.9	2505.6	2476.5	2447.5
2423.6	27.5°	2476.9	2530.2	2557.8	2585.5	2541.7	2498.1	2451.1	2404.2	2384.7	2365.1
2279.8	30°	2324.0	2368.3	2390.8	2413.2	2380.0	2346.6	2313.0	2279.2	2269.2	2259.2
2134.0	32.5°	2176.4	2218.8	2243.8	2268.8	2238.2	2207.5	2180.6	2153.8	2147.3	2140.7
1992.2	35°	2034.2	2076.2	2106.2	2136.1	2114.3	2092.6	2067.8	2043.0	2033.1	2023.3
1856.9	37.5°	1898.7	1940.7	1977.7	2014.7	2004.6	1994.6	1971.8	1948.9	1930.8	1912.8
1730.3	40°	1770.7	1811.2	1853.8	1896.5	1898.9	1901.3	1881.9	1862.6	1836.2	1810.1
1614.3	42.5°	1652.6	1691.0	1737.0	1783.1	1795.4	1807.7	1791.3	1775.0	1742.4	1709.8
1514.8	45°	1551.2	1587.6	1635.3	1683.0	1700.7	1718.3	1703.6	1688.9	1651.6	1614.3
1435.3	47.5°	1471.0	1506.5	1553.6	1600.6	1621.0	1641.3	1631.0	1620.7	1587.6	1554.4
1377.5	50°	1411.1	1444.6	1486.8	1528.9	1555.0	1581.2	1580.5	1580.1	1553.6	1527.0
1339.6	52.5°	1370.4	1401.1	1440.4	1479.7	1510.6	1541.6	1547.1	1552.7	1531.1	1509.5
1310.9	55°	1344.1	1377.2	1411.7	1446.0	1478.8	1511.6	1519.3	1527.0	1508.2	1489.4
1272.2	57.5°	1311.1	1350.0	1384.1	1418.2	1451.3	1484.2	1492.0	1499.8	1480.8	1461.8
1219.9	60°	1264.7	1309.4	1344.0	1378.6	1411.8	1445.0	1453.5	1462.1	1443.5	1424.9
1146.4	62.5°	1198.5	1250.8	1287.7	1324.6	1355.0	1385.4	1393.6	1401.8	1385.0	1368.2
1067.8	65°	1123.7	1179.6	1214.9	1250.2	1277.0	1303.7	1312.2	1320.5	1304.4	1288.2
995.0	67.5°	1046.6	1098.3	1131.8	1165.2	1188.3	1211.4	1219.6	1227.8	1212.9	1198.1
922.5	70°	967.9	1013.2	1042.1	1071.0	1091.9	1112.7	1120.7	1128.6	1116.5	1104.4
836.2	72.5°	871.9	907.5	933.6	959.7	980.2	1000.6	1010.0	1019.4	1009.4	999.3
732.1	75°	758.6	785.1	808.8	832.4	851.0	869.6	879.5	889.3	884.4	879.5
621.8	77.5°	643.5	665.0	685.3	705.6	725.2	744.7	753.9	763.1	756.2	749.2
496.5	80°	514.4	532.3	549.4	566.5	581.4	596.2	608.4	620.6	617.6	614.7
373.4	82.5°	371.9	370.4	364.4	358.4	390.1	421.8	442.5	463.3	462.0	460.6
232.2	85°	224.5	216.7	200.1	183.5	213.1	242.9	268.6	294.2	292.1	290.0
107.8	87.5°	107.5	107.2	94.6	81.9	94.3	106.8	117.2	127.5	125.0	122.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2548.0	2.5°	2540.6	2531.5	2540.6	2548.0	2555.2	2563.1	2571.1	2581.2	2591.4	2604.0
2387.1	5°	2379.5	2372.1	2379.5	2387.1	2394.7	2404.7	2414.6	2428.7	2442.7	2462.8
2290.8	7.5°	2284.1	2279.0	2284.1	2290.8	2297.7	2309.0	2320.5	2337.2	2353.9	2377.6
2264.6	10°	2258.9	2256.5	2258.9	2264.6	2270.4	2281.2	2292.0	2310.9	2329.5	2358.0
2305.1	12.5°	2300.2	2299.3	2300.2	2305.1	2310.0	2322.0	2334.1	2358.1	2382.2	2418.6
2381.2	15°	2374.7	2374.2	2374.7	2381.2	2387.6	2404.3	2421.1	2457.7	2494.2	2546.0
2446.8	17.5°	2438.6	2437.3	2438.6	2446.8	2455.0	2479.9	2504.7	2558.7	2612.6	2681.2
2481.7	20°	2471.6	2468.4	2471.6	2481.7	2491.9	2523.8	2555.6	2621.6	2687.7	2766.0
2479.0	22.5°	2467.8	2463.0	2467.8	2479.0	2490.3	2523.9	2557.4	2625.5	2693.6	2768.5
2436.9	25°	2426.4	2420.2	2426.4	2436.9	2447.5	2476.5	2505.6	2565.9	2626.5	2687.8
2360.3	27.5°	2355.5	2353.9	2355.5	2360.3	2365.1	2384.7	2404.2	2451.1	2498.1	2541.7
2259.2	30°	2259.2	2260.8	2259.2	2259.2	2259.2	2269.2	2279.2	2313.0	2346.6	2380.0
2141.6	32.5°	2142.6	2144.2	2142.6	2141.6	2140.7	2147.3	2153.8	2180.6	2207.5	2238.2
2021.1	35°	2019.0	2017.9	2019.0	2021.1	2023.3	2033.1	2043.0	2067.8	2092.6	2114.3
1903.3	37.5°	1893.8	1888.4	1893.8	1903.3	1912.8	1930.8	1948.9	1971.8	1994.6	2004.6
1792.4	40°	1774.8	1764.3	1774.8	1792.4	1810.1	1836.2	1862.6	1881.9	1901.3	1898.9
1684.0	42.5°	1658.2	1641.3	1658.2	1684.0	1709.8	1742.4	1775.0	1791.3	1807.7	1795.4
1584.0	45°	1553.8	1534.3	1553.8	1584.0	1614.3	1651.6	1688.9	1703.6	1718.3	1700.7
1526.4	47.5°	1498.5	1479.7	1498.5	1526.4	1554.4	1587.6	1620.7	1631.0	1641.3	1621.0
1501.1	50°	1475.2	1457.3	1475.2	1501.1	1527.0	1553.6	1580.1	1580.5	1581.2	1555.0
1486.3	52.5°	1463.1	1446.6	1463.1	1486.3	1509.5	1531.1	1552.7	1547.1	1541.6	1510.6
1469.0	55°	1448.7	1433.7	1448.7	1469.0	1489.4	1508.2	1527.0	1519.3	1511.6	1478.8
1441.6	57.5°	1421.4	1405.9	1421.4	1441.6	1461.8	1480.8	1499.8	1492.0	1484.2	1451.3
1404.2	60°	1383.4	1367.4	1383.4	1404.2	1424.9	1443.5	1462.1	1453.5	1445.0	1411.8
1346.4	62.5°	1324.6	1305.3	1324.6	1346.4	1368.2	1385.0	1401.8	1393.6	1385.4	1355.0
1267.0	65°	1245.9	1229.4	1245.9	1267.0	1288.2	1304.4	1320.5	1312.2	1303.7	1277.0
1178.4	67.5°	1158.7	1143.8	1158.7	1178.4	1198.1	1212.9	1227.8	1219.6	1211.4	1188.3
1085.6	70°	1066.7	1049.6	1066.7	1085.6	1104.4	1116.5	1128.6	1120.7	1112.7	1091.9
981.3	72.5°	963.5	946.9	963.5	981.3	999.3	1009.4	1019.4	1010.0	1000.6	980.2
864.4	75°	849.3	833.5	849.3	864.4	879.5	884.4	889.3	879.5	869.6	851.0
734.0	77.5°	718.8	706.2	718.8	734.0	749.2	756.2	763.1	753.9	744.7	725.2
594.2	80°	573.7	549.9	573.7	594.2	614.7	617.6	620.6	608.4	596.2	581.4
443.4	82.5°	426.0	410.9	426.0	443.4	460.6	462.0	463.3	442.5	421.8	390.1
276.5	85°	263.0	249.3	263.0	276.5	290.0	292.1	294.2	268.6	242.9	213.1
115.3	87.5°	108.3	101.6	108.3	115.3	122.2	125.0	127.5	117.2	106.8	94.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2616.5	2.5°	2632.7	2649.0	2665.1	2681.3	2699.7	2718.2	2738.6	2759.2	2784.5	2807.3
2482.8	5°	2508.9	2534.9	2563.6	2592.2	2624.7	2657.2	2696.0	2734.8	2779.2	2824.1
2401.5	7.5°	2433.3	2465.1	2501.3	2537.4	2580.2	2623.0	2674.4	2726.0	2783.4	2844.8
2386.5	10°	2422.3	2458.2	2497.1	2536.0	2578.8	2621.6	2675.9	2730.3	2792.0	2867.7
2455.0	12.5°	2492.0	2529.1	2559.5	2590.1	2618.4	2646.8	2691.1	2735.6	2793.1	2872.6
2597.8	15°	2630.0	2662.2	2670.1	2678.1	2674.2	2670.4	2691.5	2712.8	2758.8	2846.9
2749.7	17.5°	2775.6	2801.6	2776.9	2752.1	2705.4	2658.8	2651.1	2643.3	2671.6	2775.2
2844.4	20°	2856.5	2868.5	2816.6	2764.7	2683.6	2602.6	2566.2	2529.9	2537.4	2657.9
2843.4	22.5°	2836.2	2828.9	2761.4	2693.9	2601.2	2508.8	2455.0	2401.2	2386.5	2523.8
2749.2	25°	2724.5	2699.7	2633.2	2566.8	2483.5	2400.4	2338.4	2276.3	2236.7	2377.4
2585.5	27.5°	2557.8	2530.2	2476.9	2423.6	2355.4	2287.0	2227.1	2167.2	2119.0	2247.1
2413.2	30°	2390.8	2368.3	2324.0	2279.8	2223.1	2166.4	2118.7	2071.2	2033.4	2140.9
2268.8	32.5°	2243.8	2218.8	2176.4	2134.0	2088.6	2043.4	2015.2	1987.1	1970.3	2057.0
2136.1	35°	2106.2	2076.2	2034.2	1992.2	1957.8	1923.2	1915.4	1907.7	1914.7	1986.9
2014.7	37.5°	1977.7	1940.7	1898.7	1856.9	1832.2	1807.3	1815.9	1824.5	1849.9	1913.1
1896.5	40°	1853.8	1811.2	1770.7	1730.3	1712.4	1694.6	1713.9	1733.3	1772.4	1829.6
1783.1	42.5°	1737.0	1691.0	1652.6	1614.3	1599.7	1585.1	1610.8	1636.5	1685.7	1738.4
1683.0	45°	1635.3	1587.6	1551.2	1514.8	1502.4	1490.2	1515.1	1540.2	1587.8	1641.3
1600.6	47.5°	1553.6	1506.5	1471.0	1435.3	1423.9	1412.3	1433.3	1454.3	1495.2	1564.3
1528.9	50°	1486.8	1444.6	1411.1	1377.5	1359.5	1341.5	1360.0	1378.6	1426.2	1517.0
1479.7	52.5°	1440.4	1401.1	1370.4	1339.6	1312.6	1285.5	1303.8	1322.2	1388.8	1493.1
1446.0	55°	1411.7	1377.2	1344.1	1310.9	1272.6	1234.2	1263.2	1292.3	1392.5	1489.6
1418.2	57.5°	1384.1	1350.0	1311.1	1272.2	1230.9	1189.6	1231.9	1274.3	1396.3	1481.9
1378.6	60°	1344.0	1309.4	1264.7	1219.9	1183.8	1147.5	1202.5	1257.4	1384.5	1441.0
1324.6	62.5°	1287.7	1250.8	1198.5	1146.4	1123.4	1100.4	1169.0	1237.7	1355.6	1362.6
1250.2	65°	1214.9	1179.6	1123.7	1067.8	1059.0	1050.1	1123.2	1196.2	1286.1	1285.2
1165.2	67.5°	1131.8	1098.3	1046.6	995.0	997.8	1000.6	1061.4	1122.2	1172.7	1175.0
1071.0	70°	1042.1	1013.2	967.9	922.5	932.1	941.8	985.0	1028.2	1044.8	1044.8
959.7	72.5°	933.6	907.5	871.9	836.2	850.2	864.3	893.9	923.6	923.4	912.9
832.4	75°	808.8	785.1	758.6	732.1	745.6	759.1	782.0	804.8	808.9	760.5
705.6	77.5°	685.3	665.0	643.5	621.8	635.5	649.2	667.5	685.8	688.0	608.3
566.5	80°	549.4	532.3	514.4	496.5	508.0	519.5	534.9	550.2	550.5	455.3
358.4	82.5°	364.4	370.4	371.9	373.4	381.5	389.7	397.2	404.7	400.2	318.8
183.5	85°	200.1	216.7	224.5	232.2	241.3	250.4	258.4	266.4	260.5	200.1
81.9	87.5°	94.6	107.2	107.5	107.8	109.6	111.3	114.5	117.7	110.2	85.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947402  
 CATALOG NUMBER: GALN-SB2D-735-U-SLL

**CANDELA DISTRIBUTION (continued):**

325°		330°	335°	340°	345°	350°	355°	360°
2788.3	0°	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3	2788.3
2830.8	2.5°	2854.4	2879.0	2903.6	2928.0	2952.5	2975.5	2998.5
2871.7	5°	2919.3	2970.3	3021.3	3071.9	3122.6	3173.4	3224.3
2911.2	7.5°	2977.6	3053.1	3128.5	3206.0	3283.4	3367.2	3451.1
2946.4	10°	3024.9	3116.6	3208.2	3310.5	3412.9	3518.9	3625.0
2961.5	12.5°	3050.4	3158.5	3266.5	3382.5	3498.5	3614.9	3731.4
2949.8	15°	3052.8	3177.2	3301.6	3427.4	3553.3	3674.7	3796.1
2899.0	17.5°	3022.8	3167.2	3311.7	3448.9	3586.2	3709.4	3832.5
2811.4	20°	2964.8	3139.8	3314.9	3465.7	3616.6	3744.7	3872.6
2708.6	22.5°	2893.3	3106.2	3319.2	3488.4	3657.6	3788.4	3919.2
2593.7	25°	2810.2	3073.1	3336.1	3529.5	3722.9	3850.9	3979.1
2488.8	27.5°	2730.5	3050.9	3371.4	3593.7	3815.9	3938.2	4060.4
2401.1	30°	2661.2	3040.6	3419.7	3676.8	3934.0	4052.0	4170.1
2325.4	32.5°	2593.7	3027.7	3461.5	3763.6	4065.8	4182.6	4299.6
2251.0	35°	2515.2	3003.5	3492.1	3862.5	4232.9	4344.9	4456.8
2163.5	37.5°	2414.0	2962.1	3510.3	3973.2	4436.2	4578.9	4721.6
2059.1	40°	2288.6	2905.1	3521.7	4113.8	4705.8	4913.8	5121.8
1943.9	42.5°	2149.3	2846.3	3543.4	4297.7	5052.0	5352.3	5652.5
1821.5	45°	2001.6	2791.6	3581.6	4539.8	5497.9	5902.9	6307.8
1724.6	47.5°	1885.0	2746.4	3607.8	4797.6	5987.4	6557.4	7127.4
1660.3	50°	1803.7	2697.2	3590.7	5036.8	6483.0	7342.4	8201.6
1618.0	52.5°	1742.9	2614.1	3485.3	5192.2	6899.0	8166.8	9434.7
1587.3	55°	1684.9	2476.3	3267.6	5158.0	7048.2	8897.8	10747.5
1550.9	57.5°	1619.9	2282.0	2943.9	4917.0	6890.2	9415.9	11941.6
1495.2	60°	1549.5	2029.7	2509.9	4468.6	6427.3	9545.4	12663.3
1398.5	62.5°	1434.6	1727.7	2020.9	3862.3	5703.6	9000.2	12296.8
1302.2	65°	1319.2	1456.1	1592.9	3243.6	4894.4	8228.9	11563.4
1165.6	67.5°	1156.1	1195.0	1233.9	2637.6	4041.4	7311.0	10580.6
1000.8	70°	956.7	945.7	934.6	2076.8	3218.9	6309.4	9400.0
850.5	72.5°	788.0	754.4	720.9	1587.7	2454.4	5223.7	7993.0
690.5	75°	620.6	590.2	559.8	1152.3	1744.9	3979.0	6213.1
540.3	77.5°	472.4	451.6	431.0	780.8	1130.7	2784.9	4439.2
397.8	80°	340.2	331.7	323.1	503.1	683.2	1794.3	2905.4
276.5	82.5°	234.1	232.4	230.9	309.4	388.2	1038.5	1688.9
169.1	85°	138.0	138.9	139.6	165.4	191.3	467.1	743.1
72.3	87.5°	59.7	60.5	61.2	68.6	76.0	153.0	230.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)