

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P950258

Luminaire Tested: **GALN-SB4D-735-U-SLL**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P950258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4D-735-U-SLL
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 70 CRI, 3500K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR LEFT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 40637 lumens
Efficiency: N/A
Efficacy: 138.4 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 293.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 12.4 fc
 Type IV - Short - N/A

REPORT NUMBER: P950258
CATALOG NUMBER: GALN-SB4D-735-U-SLL

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	10327.9	0.0	10327.9
	% Fixture	25.4	0.0	25.4
Street Side	Lumens	30309.1	0.0	30309.1
	% Fixture	74.6	0.0	74.6
Total	Lumens	40637.0	0.0	40637.0
	% Fixture	100.0	0.0	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	554.3	1.4
10°-20°	1740.1	4.3
20°-30°	2687.9	6.6
30°-40°	3406.2	8.4
40°-50°	5137.5	12.6
50°-60°	8300.3	20.4
60°-70°	10347.7	25.5
70°-80°	6785.5	16.7
80°-90°	1677.5	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	40637.0	100.0
0°-180°	40637.0	100.0



REPORT NUMBER: P950258


CATALOG NUMBER: GALN-SB4D-735-U-SLL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2733.3	6.7			
FM (30°-60°)	11852.9	29.2			
FH (60°-80°)	14341.0	35.3			G5
FVH (80°-90°)	1381.9	3.4			G5
BL (0°-30°)	2249.0	5.5	B3/2500		
BM (30°-60°)	4991.1	12.3	B3/5000		
BH (60°-80°)	2792.2	6.9	B4/5000		G4/5000
BVH (80°-90°)	295.6	0.7			G3/500
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
2.5°	6009.3	6032.0	6055.0	6087.3	6119.7	6139.0	6158.3	6168.0	6177.6	6173.3
5°	6461.7	6541.3	6621.0	6699.9	6779.1	6822.0	6864.8	6890.8	6916.9	6936.7
7.5°	6916.3	7045.8	7175.1	7291.6	7408.0	7478.1	7548.2	7586.2	7623.9	7642.1
10°	7264.7	7417.8	7570.9	7707.5	7844.1	7926.9	8009.2	8046.1	8082.8	8096.7
12.5°	7478.1	7644.1	7809.8	7933.3	8056.4	8116.4	8176.5	8196.6	8216.8	8218.9
15°	7607.8	7751.1	7894.1	7971.5	8049.1	8051.3	8053.4	8032.0	8010.5	7985.2
17.5°	7680.7	7777.4	7874.1	7875.6	7876.9	7790.1	7703.2	7623.7	7543.9	7487.8
20°	7761.1	7794.8	7828.7	7726.8	7625.0	7433.3	7241.6	7102.0	6962.4	6876.6
22.5°	7854.4	7810.2	7766.1	7555.1	7344.1	7062.1	6780.1	6605.6	6431.1	6336.3
25°	7974.5	7835.1	7695.7	7375.4	7055.0	6712.6	6370.2	6186.6	6003.5	5913.9
27.5°	8137.5	7888.3	7638.9	7214.6	6790.4	6410.9	6031.4	5850.8	5670.5	5585.8
30°	8357.2	7985.6	7614.3	7091.9	6569.6	6174.2	5778.8	5611.3	5443.8	5364.9
32.5°	8616.7	8107.9	7599.3	7008.3	6417.3	6045.7	5674.1	5542.7	5411.0	5354.2
35°	8931.9	8309.2	7686.7	7070.9	6455.3	6197.1	5939.2	5908.5	5877.8	5873.1
37.5°	9462.6	8730.1	7997.7	7438.0	6878.4	6861.6	6844.9	6985.1	7125.4	7198.3
40°	10264.6	9468.0	8671.4	8255.2	7839.0	8132.7	8426.5	8767.4	9108.4	9278.2
42.5°	11328.1	10537.7	9747.4	9507.6	9267.9	9908.6	10549.3	11169.4	11789.6	12153.7
45°	12641.5	11931.5	11221.3	11115.6	11009.7	12036.2	13062.8	14081.8	15100.9	15719.6
47.5°	14284.0	13593.3	12902.4	12881.0	12859.5	14340.4	15820.8	17312.5	18804.1	19680.0
50°	16436.8	15583.6	14730.6	14734.3	14737.9	16646.3	18554.7	20523.8	22492.8	23683.3
52.5°	18908.1	17875.0	16842.1	16737.7	16633.0	18912.6	21192.1	23628.4	26064.5	27491.5
55°	21539.1	20518.4	19497.7	19090.5	18683.4	21220.4	23757.3	26661.7	29566.1	31263.3
57.5°	23932.1	23376.3	22820.3	22003.5	21187.0	23748.7	26310.5	29600.2	32889.7	34994.3
60°	25378.4	26241.6	27105.1	26090.9	25076.7	27501.0	29925.3	33447.4	36969.6	39244.2
62.5°	24644.0	27002.9	29361.8	29247.5	29133.0	31353.8	33574.8	36925.8	40276.7	42379.1
65°	23174.1	25388.0	27602.0	28040.0	28477.9	31300.2	34122.7	37372.1	40621.3	42411.3
67.5°	21204.6	23310.2	25415.9	25621.3	25826.5	28767.2	31707.6	34970.9	38234.3	39636.6
70°	18838.4	21128.7	23419.2	23510.9	23602.9	26232.6	28862.1	31670.5	34478.6	35258.0
72.5°	16018.7	18646.9	21275.3	21341.4	21407.2	23464.6	25522.0	27625.3	29728.4	29807.3
75°	12451.7	15171.9	17892.1	18136.4	18380.6	19981.3	21582.0	23062.6	24543.2	24146.5
77.5°	8896.5	11435.8	13975.2	14324.7	14674.2	15891.1	17108.0	18158.0	19208.3	18526.4
80°	5822.7	7959.1	10095.2	10529.6	10964.0	11883.1	12801.7	13353.2	13904.4	12807.7
82.5°	3384.7	4845.2	6305.8	6791.1	7276.5	7909.1	8541.7	8771.7	9001.6	8139.6
85°	1489.2	2264.3	3039.5	3452.3	3865.0	4384.8	4904.3	5034.9	5165.5	4475.1
87.5°	461.0	721.5	982.1	1212.4	1442.7	1702.5	1962.4	1973.6	1984.5	1666.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
6177.6	2.5°	6168.0	6158.3	6139.0	6119.7	6087.3	6055.0	6032.0	6009.3	5963.2	5917.1
6916.9	5°	6890.8	6864.8	6822.0	6779.1	6699.9	6621.0	6541.3	6461.7	6359.9	6258.0
7623.9	7.5°	7586.2	7548.2	7478.1	7408.0	7291.6	7175.1	7045.8	6916.3	6748.2	6580.3
8082.8	10°	8046.1	8009.2	7926.9	7844.1	7707.5	7570.9	7417.8	7264.7	7052.3	6839.8
8216.8	12.5°	8196.6	8176.5	8116.4	8056.4	7933.3	7809.8	7644.1	7478.1	7244.6	7011.3
8010.5	15°	8032.0	8053.4	8051.3	8049.1	7971.5	7894.1	7751.1	7607.8	7364.5	7121.1
7543.9	17.5°	7623.7	7703.2	7790.1	7876.9	7875.6	7874.1	7777.4	7680.7	7433.9	7187.1
6962.4	20°	7102.0	7241.6	7433.3	7625.0	7726.8	7828.7	7794.8	7761.1	7504.7	7248.0
6431.1	22.5°	6605.6	6780.1	7062.1	7344.1	7555.1	7766.1	7810.2	7854.4	7592.4	7330.1
6003.5	25°	6186.6	6370.2	6712.6	7055.0	7375.4	7695.7	7835.1	7974.5	7717.6	7460.9
5670.5	27.5°	5850.8	6031.4	6410.9	6790.4	7214.6	7638.9	7888.3	8137.5	7892.6	7647.5
5443.8	30°	5611.3	5778.8	6174.2	6569.6	7091.9	7614.3	7985.6	8357.2	8120.5	7884.0
5411.0	32.5°	5542.7	5674.1	6045.7	6417.3	7008.3	7599.3	8107.9	8616.7	8382.3	8148.2
5877.8	35°	5908.5	5939.2	6197.1	6455.3	7070.9	7686.7	8309.2	8931.9	8707.6	8483.1
7125.4	37.5°	6985.1	6844.9	6861.6	6878.4	7438.0	7997.7	8730.1	9462.6	9176.6	8890.5
9108.4	40°	8767.4	8426.5	8132.7	7839.0	8255.2	8671.4	9468.0	10264.6	9847.7	9430.9
11789.6	42.5°	11169.4	10549.3	9908.6	9267.9	9507.6	9747.4	10537.7	11328.1	10726.4	10124.8
15100.9	45°	14081.8	13062.8	12036.2	11009.7	11115.6	11221.3	11931.5	12641.5	11829.9	11018.3
18804.1	47.5°	17312.5	15820.8	14340.4	12859.5	12881.0	12902.4	13593.3	14284.0	13141.7	11999.3
22492.8	50°	20523.8	18554.7	16646.3	14737.9	14734.3	14730.6	15583.6	16436.8	14714.8	12992.5
26064.5	52.5°	23628.4	21192.1	18912.6	16633.0	16737.7	16842.1	17875.0	18908.1	16367.1	13826.2
29566.1	55°	26661.7	23757.3	21220.4	18683.4	19090.5	19497.7	20518.4	21539.1	17832.1	14125.3
32889.7	57.5°	29600.2	26310.5	23748.7	21187.0	22003.5	22820.3	23376.3	23932.1	18870.3	13808.6
36969.6	60°	33447.4	29925.3	27501.0	25076.7	26090.9	27105.1	26241.6	25378.4	19129.8	12881.0
40276.7	62.5°	36925.8	33574.8	31353.8	29133.0	29247.5	29361.8	27002.9	24644.0	18037.3	11430.6
40621.3	65°	37372.1	34122.7	31300.2	28477.9	28040.0	27602.0	25388.0	23174.1	16491.5	9808.9
38234.3	67.5°	34970.9	31707.6	28767.2	25826.5	25621.3	25415.9	23310.2	21204.6	14651.9	8099.3
34478.6	70°	31670.5	28862.1	26232.6	23602.9	23510.9	23419.2	21128.7	18838.4	12644.7	6451.0
29728.4	72.5°	27625.3	25522.0	23464.6	21407.2	21341.4	21275.3	18646.9	16018.7	10468.7	4918.9
24543.2	75°	23062.6	21582.0	19981.3	18380.6	18136.4	17892.1	15171.9	12451.7	7974.3	3496.9
19208.3	77.5°	18158.0	17108.0	15891.1	14674.2	14324.7	13975.2	11435.8	8896.5	5581.3	2266.1
13904.4	80°	13353.2	12801.7	11883.1	10964.0	10529.6	10095.2	7959.1	5822.7	3595.9	1369.1
9001.6	82.5°	8771.7	8541.7	7909.1	7276.5	6791.1	6305.8	4845.2	3384.7	2081.2	777.9
5165.5	85°	5034.9	4904.3	4384.8	3865.0	3452.3	3039.5	2264.3	1489.2	936.2	383.4
1984.5	87.5°	1973.6	1962.4	1702.5	1442.7	1212.4	982.1	721.5	461.0	306.6	152.2
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
5868.0	2.5°	5819.1	5769.8	5720.5	5673.3	5626.1	5580.4	5529.6	5488.4	5447.5	5410.4
6156.4	5°	6055.0	5952.7	5850.6	5755.2	5659.8	5569.7	5480.7	5403.1	5325.3	5260.1
6425.1	7.5°	6269.8	6118.6	5967.5	5834.3	5701.2	5578.3	5463.1	5359.8	5256.6	5170.9
6634.6	10°	6429.6	6246.0	6062.2	5904.9	5747.0	5595.4	5471.7	5362.8	5253.9	5168.1
6778.9	12.5°	6546.4	6329.9	6113.3	5935.1	5756.9	5597.6	5482.4	5393.2	5304.5	5247.4
6868.9	15°	6616.8	6367.4	6118.0	5911.7	5705.4	5529.0	5436.8	5394.1	5351.6	5359.4
6912.0	17.5°	6636.9	6347.4	6058.0	5809.9	5561.8	5354.2	5297.4	5313.0	5328.5	5422.0
6945.7	20°	6643.3	6292.5	5941.7	5634.3	5326.8	5085.1	5070.1	5143.0	5215.9	5378.2
6991.1	22.5°	6651.9	6225.2	5798.5	5428.2	5057.9	4782.8	4812.1	4920.0	5027.9	5213.1
7073.5	25°	6685.8	6158.7	5631.9	5198.1	4764.5	4482.6	4561.9	4686.3	4810.6	4977.3
7202.1	27.5°	6756.6	6114.4	5472.1	4987.8	4503.4	4246.7	4343.2	4463.3	4583.4	4720.4
7368.7	30°	6853.5	6093.6	5333.2	4811.9	4290.7	4075.2	4150.9	4246.1	4341.7	4455.3
7542.6	32.5°	6937.1	6067.8	5198.1	4660.3	4122.3	3948.7	3982.3	4038.7	4095.1	4185.8
7740.8	35°	6998.4	6019.4	5040.7	4511.3	3981.9	3837.2	3823.2	3838.7	3854.3	3923.6
7962.7	37.5°	7034.9	5936.4	4837.9	4335.9	3833.9	3707.4	3656.4	3639.2	3622.1	3671.8
8244.5	40°	7057.8	5822.1	4586.6	4126.6	3666.7	3552.0	3473.7	3434.9	3396.1	3431.9
8613.1	42.5°	7101.4	5704.2	4307.4	3895.7	3484.0	3378.3	3279.6	3228.2	3176.7	3205.9
9098.1	45°	7177.9	5594.6	4011.5	3650.4	3289.3	3182.1	3086.7	3036.5	2986.5	3011.0
9614.9	47.5°	7230.4	5504.1	3777.8	3456.3	3134.9	2996.6	2914.5	2872.4	2830.4	2853.6
10094.3	50°	7196.1	5405.5	3614.8	3327.5	3040.1	2858.3	2762.9	2725.6	2688.5	2724.5
10405.7	52.5°	6984.9	5238.9	3493.0	3242.5	2992.3	2783.2	2649.9	2613.0	2576.3	2630.6
10337.0	55°	6548.6	4962.7	3376.8	3181.0	2985.2	2790.8	2589.8	2531.5	2473.4	2550.4
9854.2	57.5°	5899.9	4573.3	3246.4	3108.1	2969.8	2798.3	2553.8	2468.9	2384.0	2466.8
8955.5	60°	5030.0	4067.7	3105.3	2996.6	2887.9	2774.7	2519.9	2409.9	2299.7	2372.4
7740.3	62.5°	4050.1	3462.5	2875.0	2802.8	2730.7	2716.8	2480.5	2342.8	2205.4	2251.5
6500.5	65°	3192.4	2918.1	2643.9	2609.8	2575.7	2577.4	2397.3	2251.0	2104.6	2122.4
5286.0	67.5°	2472.8	2394.9	2316.9	2336.0	2354.8	2350.1	2248.9	2127.1	2005.3	1999.7
4162.0	70°	1873.0	1895.3	1917.4	2005.7	2093.9	2093.9	2060.6	1974.0	1887.4	1868.1
3181.9	72.5°	1444.8	1511.9	1579.2	1704.5	1829.5	1850.5	1850.9	1791.5	1732.1	1703.8
2309.4	75°	1121.9	1182.8	1243.7	1383.9	1524.1	1621.1	1612.9	1567.2	1521.4	1494.3
1564.9	77.5°	863.7	905.1	946.7	1082.9	1219.0	1378.8	1374.5	1337.8	1301.1	1273.7
1008.2	80°	647.6	664.7	681.9	797.2	912.4	1103.2	1102.6	1071.9	1041.0	1018.1
620.1	82.5°	462.7	465.7	469.2	554.1	639.0	802.0	811.0	795.9	780.9	764.6
331.5	85°	279.8	278.3	276.6	338.8	401.0	522.1	533.9	517.8	501.8	483.5
137.4	87.5°	122.7	121.2	119.6	145.0	170.5	220.9	235.9	229.4	223.0	219.6
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
5373.5	2.5°	5341.1	5308.8	5276.2	5243.8	5218.7	5193.4	5173.0	5152.7	5136.8	5120.9
5195.1	5°	5137.6	5080.2	5028.1	4975.8	4935.7	4895.3	4867.3	4839.2	4819.2	4799.3
5085.1	7.5°	5012.8	4940.4	4876.5	4812.8	4765.0	4717.4	4683.9	4650.5	4627.5	4604.8
5082.3	10°	5004.5	4926.4	4854.6	4782.8	4725.7	4668.5	4631.2	4593.4	4571.8	4550.1
5190.8	12.5°	5129.5	5068.6	4994.2	4920.0	4847.1	4774.2	4725.9	4677.7	4653.5	4629.5
5367.1	15°	5351.2	5335.3	5270.8	5206.3	5102.5	4998.7	4925.4	4852.0	4818.4	4784.9
5515.5	17.5°	5565.2	5614.7	5562.6	5510.7	5373.3	5235.9	5127.8	5019.7	4970.0	4920.0
5540.8	20°	5644.8	5748.8	5724.7	5700.5	5543.3	5386.4	5253.9	5121.6	5057.9	4994.0
5398.8	22.5°	5534.1	5669.4	5684.0	5698.4	5548.3	5398.2	5261.8	5125.2	5058.1	4990.8
5144.1	25°	5277.2	5410.4	5460.1	5509.7	5386.6	5263.7	5142.4	5021.4	4963.1	4905.0
4857.2	27.5°	4964.0	5070.7	5126.1	5181.6	5093.9	5006.4	4912.3	4818.1	4779.1	4739.9
4569.0	30°	4657.5	4746.3	4791.3	4836.4	4769.7	4702.8	4635.5	4567.7	4547.8	4527.6
4276.7	32.5°	4361.6	4446.8	4496.7	4546.9	4485.6	4424.0	4370.2	4316.4	4303.3	4290.2
3992.6	35°	4076.7	4160.9	4221.0	4281.0	4237.3	4193.7	4144.0	4094.5	4074.5	4054.8
3721.4	37.5°	3805.2	3889.3	3963.4	4037.6	4017.5	3997.3	3951.7	3905.8	3869.5	3833.5
3467.7	40°	3548.7	3629.8	3715.1	3800.7	3805.6	3810.3	3771.5	3732.7	3680.0	3627.7
3235.3	42.5°	3312.0	3389.0	3481.2	3573.4	3598.1	3622.7	3589.9	3557.3	3491.9	3426.5
3035.8	45°	3108.7	3181.7	3277.3	3372.9	3408.3	3443.7	3414.1	3384.7	3309.9	3235.3
2876.5	47.5°	2947.9	3019.1	3113.5	3207.8	3248.6	3289.3	3268.7	3248.1	3181.7	3115.2
2760.7	50°	2828.1	2895.2	2979.7	3064.1	3116.5	3168.8	3167.5	3166.6	3113.5	3060.3
2684.6	52.5°	2746.4	2807.9	2886.6	2965.5	3027.5	3089.4	3100.6	3111.7	3068.4	3025.1
2627.1	55°	2693.6	2760.1	2829.1	2898.0	2963.6	3029.4	3044.8	3060.3	3022.5	2984.8
2549.5	57.5°	2627.6	2705.6	2773.8	2842.2	2908.5	2974.5	2990.2	3005.8	2967.7	2929.5
2444.9	60°	2534.5	2624.1	2693.4	2762.9	2829.3	2895.8	2913.0	2930.1	2892.8	2855.7
2297.6	62.5°	2402.0	2506.6	2580.6	2654.6	2715.5	2776.4	2792.9	2809.4	2775.7	2742.1
2140.0	65°	2251.9	2364.0	2434.8	2505.6	2559.2	2612.8	2629.7	2646.4	2614.1	2581.7
1994.2	67.5°	2097.5	2201.1	2268.2	2335.1	2381.4	2427.7	2444.2	2460.5	2430.7	2401.1
1848.8	70°	1939.7	2030.6	2088.5	2146.4	2188.2	2230.0	2245.9	2261.8	2237.5	2213.3
1675.7	72.5°	1747.4	1818.8	1871.1	1923.4	1964.4	2005.3	2024.2	2043.0	2022.9	2002.7
1467.1	75°	1520.3	1573.5	1620.8	1668.2	1705.5	1742.9	1762.6	1782.3	1772.4	1762.6
1246.2	77.5°	1289.6	1332.7	1373.4	1414.1	1453.4	1492.4	1510.8	1529.3	1515.6	1501.4
994.9	80°	1031.0	1066.8	1101.1	1135.4	1165.2	1194.8	1219.2	1243.7	1237.7	1231.9
748.3	82.5°	745.3	742.3	730.3	718.3	781.8	845.3	886.9	928.5	925.9	923.1
465.3	85°	449.9	434.2	401.0	367.7	427.1	486.7	538.2	589.7	585.4	581.1
216.1	87.5°	215.5	214.9	189.6	164.0	188.9	214.0	234.8	255.6	250.4	244.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
5106.3	2.5°	5091.5	5073.3	5091.5	5106.3	5120.9	5136.8	5152.7	5173.0	5193.4	5218.7
4784.1	5°	4768.8	4753.8	4768.8	4784.1	4799.3	4819.2	4839.2	4867.3	4895.3	4935.7
4591.1	7.5°	4577.6	4567.3	4577.6	4591.1	4604.8	4627.5	4650.5	4683.9	4717.4	4765.0
4538.5	10°	4527.0	4522.2	4527.0	4538.5	4550.1	4571.8	4593.4	4631.2	4668.5	4725.7
4619.6	12.5°	4609.7	4608.0	4609.7	4619.6	4629.5	4653.5	4677.7	4725.9	4774.2	4847.1
4772.0	15°	4759.2	4758.1	4759.2	4772.0	4784.9	4818.4	4852.0	4925.4	4998.7	5102.5
4903.7	17.5°	4887.2	4884.6	4887.2	4903.7	4920.0	4970.0	5019.7	5127.8	5235.9	5373.3
4973.6	20°	4953.2	4946.8	4953.2	4973.6	4994.0	5057.9	5121.6	5253.9	5386.4	5543.3
4968.2	22.5°	4945.7	4936.1	4945.7	4968.2	4990.8	5058.1	5125.2	5261.8	5398.2	5548.3
4883.8	25°	4862.7	4850.3	4862.7	4883.8	4905.0	4963.1	5021.4	5142.4	5263.7	5386.6
4730.2	27.5°	4720.6	4717.4	4720.6	4730.2	4739.9	4779.1	4818.1	4912.3	5006.4	5093.9
4527.6	30°	4527.6	4530.8	4527.6	4527.6	4527.6	4547.8	4567.7	4635.5	4702.8	4769.7
4291.9	32.5°	4293.9	4297.1	4293.9	4291.9	4290.2	4303.3	4316.4	4370.2	4424.0	4485.6
4050.5	35°	4046.2	4044.1	4046.2	4050.5	4054.8	4074.5	4094.5	4144.0	4193.7	4237.3
3814.4	37.5°	3795.3	3784.6	3795.3	3814.4	3833.5	3869.5	3905.8	3951.7	3997.3	4017.5
3592.1	40°	3556.9	3535.9	3556.9	3592.1	3627.7	3680.0	3732.7	3771.5	3810.3	3805.6
3374.8	42.5°	3323.2	3289.3	3323.2	3374.8	3426.5	3491.9	3557.3	3589.9	3622.7	3598.1
3174.6	45°	3113.9	3074.9	3113.9	3174.6	3235.3	3309.9	3384.7	3414.1	3443.7	3408.3
3059.0	47.5°	3003.0	2965.5	3003.0	3059.0	3115.2	3181.7	3248.1	3268.7	3289.3	3248.6
3008.4	50°	2956.5	2920.5	2956.5	3008.4	3060.3	3113.5	3166.6	3167.5	3168.8	3116.5
2978.6	52.5°	2932.3	2899.0	2932.3	2978.6	3025.1	3068.4	3111.7	3100.6	3089.4	3027.5
2944.1	55°	2903.3	2873.3	2903.3	2944.1	2984.8	3022.5	3060.3	3044.8	3029.4	2963.6
2889.2	57.5°	2848.6	2817.6	2848.6	2889.2	2929.5	2967.7	3005.8	2990.2	2974.5	2908.5
2814.1	60°	2772.5	2740.4	2772.5	2814.1	2855.7	2892.8	2930.1	2913.0	2895.8	2829.3
2698.3	62.5°	2654.6	2616.0	2654.6	2698.3	2742.1	2775.7	2809.4	2792.9	2776.4	2715.5
2539.2	65°	2497.0	2463.8	2497.0	2539.2	2581.7	2614.1	2646.4	2629.7	2612.8	2559.2
2361.7	67.5°	2322.2	2292.2	2322.2	2361.7	2401.1	2430.7	2460.5	2444.2	2427.7	2381.4
2175.6	70°	2137.8	2103.5	2137.8	2175.6	2213.3	2237.5	2261.8	2245.9	2230.0	2188.2
1966.7	72.5°	1930.9	1897.7	1930.9	1966.7	2002.7	2022.9	2043.0	2024.2	2005.3	1964.4
1732.3	75°	1702.1	1670.4	1702.1	1732.3	1762.6	1772.4	1782.3	1762.6	1742.9	1705.5
1471.0	77.5°	1440.5	1415.2	1440.5	1471.0	1501.4	1515.6	1529.3	1510.8	1492.4	1453.4
1190.9	80°	1149.8	1102.1	1149.8	1190.9	1231.9	1237.7	1243.7	1219.2	1194.8	1165.2
888.6	82.5°	853.8	823.4	853.8	888.6	923.1	925.9	928.5	886.9	845.3	781.8
554.1	85°	527.1	499.6	527.1	554.1	581.1	585.4	589.7	538.2	486.7	427.1
231.2	87.5°	217.0	203.7	217.0	231.2	244.9	250.4	255.6	234.8	214.0	188.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
5243.8	2.5°	5276.2	5308.8	5341.1	5373.5	5410.4	5447.5	5488.4	5529.6	5580.4	5626.1
4975.8	5°	5028.1	5080.2	5137.6	5195.1	5260.1	5325.3	5403.1	5480.7	5569.7	5659.8
4812.8	7.5°	4876.5	4940.4	5012.8	5085.1	5170.9	5256.6	5359.8	5463.1	5578.3	5701.2
4782.8	10°	4854.6	4926.4	5004.5	5082.3	5168.1	5253.9	5362.8	5471.7	5595.4	5747.0
4920.0	12.5°	4994.2	5068.6	5129.5	5190.8	5247.4	5304.5	5393.2	5482.4	5597.6	5756.9
5206.3	15°	5270.8	5335.3	5351.2	5367.1	5359.4	5351.6	5394.1	5436.8	5529.0	5705.4
5510.7	17.5°	5562.6	5614.7	5665.2	5715.5	5722.0	5728.5	5813.0	5897.4	5994.2	6101.8
5700.5	20°	5724.7	5748.8	5644.8	5540.8	5378.2	5215.9	5143.0	5070.1	5085.1	5326.8
5698.4	22.5°	5684.0	5669.4	5534.1	5398.8	5213.1	5027.9	4920.0	4812.1	4782.8	5057.9
5509.7	25°	5460.1	5410.4	5277.2	5144.1	4977.3	4810.6	4686.3	4561.9	4482.6	4764.5
5181.6	27.5°	5126.1	5070.7	4964.0	4857.2	4720.4	4583.4	4463.3	4343.2	4246.7	4503.4
4836.4	30°	4791.3	4746.3	4657.5	4569.0	4455.3	4341.7	4246.1	4150.9	4075.2	4290.7
4546.9	32.5°	4496.7	4446.8	4361.6	4276.7	4185.8	4095.1	4038.7	3982.3	3948.7	4122.3
4281.0	35°	4221.0	4160.9	4076.7	3992.6	3923.6	3854.3	3838.7	3823.2	3837.2	3981.9
4037.6	37.5°	3963.4	3889.3	3805.2	3721.4	3671.8	3622.1	3639.2	3656.4	3707.4	3833.9
3800.7	40°	3715.1	3629.8	3548.7	3467.7	3431.9	3396.1	3434.9	3473.7	3552.0	3666.7
3573.4	42.5°	3481.2	3389.0	3312.0	3235.3	3205.9	3176.7	3228.2	3279.6	3378.3	3484.0
3372.9	45°	3277.3	3181.7	3108.7	3035.8	3011.0	2986.5	3036.5	3086.7	3182.1	3289.3
3207.8	47.5°	3113.5	3019.1	2947.9	2876.5	2853.6	2830.4	2872.4	2914.5	2996.6	3134.9
3064.1	50°	2979.7	2895.2	2828.1	2760.7	2724.5	2688.5	2725.6	2762.9	2858.3	3040.1
2965.5	52.5°	2886.6	2807.9	2746.4	2684.6	2630.6	2576.3	2613.0	2649.9	2783.2	2992.3
2898.0	55°	2829.1	2760.1	2693.6	2627.1	2550.4	2473.4	2531.5	2589.8	2790.8	2985.2
2842.2	57.5°	2773.8	2705.6	2627.6	2549.5	2466.8	2384.0	2468.9	2553.8	2798.3	2969.8
2762.9	60°	2693.4	2624.1	2534.5	2444.9	2372.4	2299.7	2409.9	2519.9	2774.7	2887.9
2654.6	62.5°	2580.6	2506.6	2402.0	2297.6	2251.5	2205.4	2342.8	2480.5	2716.8	2730.7
2505.6	65°	2434.8	2364.0	2251.9	2140.0	2122.4	2104.6	2251.0	2397.3	2577.4	2575.7
2335.1	67.5°	2268.2	2201.1	2097.5	1994.2	1999.7	2005.3	2127.1	2248.9	2350.1	2354.8
2146.4	70°	2088.5	2030.6	1939.7	1848.8	1868.1	1887.4	1974.0	2060.6	2093.9	2093.9
1923.4	72.5°	1871.1	1818.8	1747.4	1675.7	1703.8	1732.1	1791.5	1850.9	1850.5	1829.5
1668.2	75°	1620.8	1573.5	1520.3	1467.1	1494.3	1521.4	1567.2	1612.9	1621.1	1524.1
1414.1	77.5°	1373.4	1332.7	1289.6	1246.2	1273.7	1301.1	1337.8	1374.5	1378.8	1219.0
1135.4	80°	1101.1	1066.8	1031.0	994.9	1018.1	1041.0	1071.9	1102.6	1103.2	912.4
718.3	82.5°	730.3	742.3	745.3	748.3	764.6	780.9	795.9	811.0	802.0	639.0
367.7	85°	401.0	434.2	449.9	465.3	483.5	501.8	517.8	533.9	522.1	401.0
164.0	87.5°	189.6	214.9	215.5	216.1	219.6	223.0	229.4	235.9	220.9	170.5
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P950258
 CATALOG NUMBER: GALN-SB4D-735-U-SLL

CANDELA DISTRIBUTION (continued):

325°		330°	335°	340°	345°	350°	355°	360°
5587.9	0°	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9	5587.9
5673.3	2.5°	5720.5	5769.8	5819.1	5868.0	5917.1	5963.2	6009.3
5755.2	5°	5850.6	5952.7	6055.0	6156.4	6258.0	6359.9	6461.7
5834.3	7.5°	5967.5	6118.6	6269.8	6425.1	6580.3	6748.2	6916.3
5904.9	10°	6062.2	6246.0	6429.6	6634.6	6839.8	7052.3	7264.7
5935.1	12.5°	6113.3	6329.9	6546.4	6778.9	7011.3	7244.6	7478.1
5911.7	15°	6118.0	6367.4	6616.8	6868.9	7121.1	7364.5	7607.8
5809.9	17.5°	6058.0	6347.4	6636.9	6912.0	7187.1	7433.9	7680.7
5634.3	20°	5941.7	6292.5	6643.3	6945.7	7248.0	7504.7	7761.1
5428.2	22.5°	5798.5	6225.2	6651.9	6991.1	7330.1	7592.4	7854.4
5198.1	25°	5631.9	6158.7	6685.8	7073.5	7460.9	7717.6	7974.5
4987.8	27.5°	5472.1	6114.4	6756.6	7202.1	7647.5	7892.6	8137.5
4811.9	30°	5333.2	6093.6	6853.5	7368.7	7884.0	8120.5	8357.2
4660.3	32.5°	5198.1	6067.8	6937.1	7542.6	8148.2	8382.3	8616.7
4511.3	35°	5040.7	6019.4	6998.4	7740.8	8483.1	8707.6	8931.9
4335.9	37.5°	4837.9	5936.4	7034.9	7962.7	8890.5	9176.6	9462.6
4126.6	40°	4586.6	5822.1	7057.8	8244.5	9430.9	9847.7	10264.6
3895.7	42.5°	4307.4	5704.2	7101.4	8613.1	10124.8	10726.4	11328.1
3650.4	45°	4011.5	5594.6	7177.9	9098.1	11018.3	11829.9	12641.5
3456.3	47.5°	3777.8	5504.1	7230.4	9614.9	11999.3	13141.7	14284.0
3327.5	50°	3614.8	5405.5	7196.1	10094.3	12992.5	14714.8	16436.8
3242.5	52.5°	3493.0	5238.9	6984.9	10405.7	13826.2	16367.1	18908.1
3181.0	55°	3376.8	4962.7	6548.6	10337.0	14125.3	17832.1	21539.1
3108.1	57.5°	3246.4	4573.3	5899.9	9854.2	13808.6	18870.3	23932.1
2996.6	60°	3105.3	4067.7	5030.0	8955.5	12881.0	19129.8	25378.4
2802.8	62.5°	2875.0	3462.5	4050.1	7740.3	11430.6	18037.3	24644.0
2609.8	65°	2643.9	2918.1	3192.4	6500.5	9808.9	16491.5	23174.1
2336.0	67.5°	2316.9	2394.9	2472.8	5286.0	8099.3	14651.9	21204.6
2005.7	70°	1917.4	1895.3	1873.0	4162.0	6451.0	12644.7	18838.4
1704.5	72.5°	1579.2	1511.9	1444.8	3181.9	4918.9	10468.7	16018.7
1383.9	75°	1243.7	1182.8	1121.9	2309.4	3496.9	7974.3	12451.7
1082.9	77.5°	946.7	905.1	863.7	1564.9	2266.1	5581.3	8896.5
797.2	80°	681.9	664.7	647.6	1008.2	1369.1	3595.9	5822.7
554.1	82.5°	469.2	465.7	462.7	620.1	777.9	2081.2	3384.7
338.8	85°	276.6	278.3	279.8	331.5	383.4	936.2	1489.2
145.0	87.5°	119.6	121.2	122.7	137.4	152.2	306.6	461.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)