

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P948160

Luminaire Tested: **GALN-SB3B-750-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P948160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB3B-750-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(3) 70 CRI, 5000K, 450mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17811 lumens
Efficiency: N/A
Efficacy: 163.1 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B3 - U0 - G4


Input Watts (W): 109.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 4.8 fc
 Type IV - Short - N/A

REPORT NUMBER: P948160
CATALOG NUMBER: GALN-SB3B-750-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 4526.7 | 0.0 | 4526.7 |
| | % Fixture | 25.4 | 0.0 | 25.4 |
| Street Side | Lumens | 13284.3 | 0.0 | 13284.3 |
| | % Fixture | 74.6 | 0.0 | 74.6 |
| Total | Lumens | 17811.0 | 0.0 | 17811.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 243.0 | 1.4 |
| 10°-20° | 762.7 | 4.3 |
| 20°-30° | 1178.1 | 6.6 |
| 30°-40° | 1492.9 | 8.4 |
| 40°-50° | 2251.7 | 12.6 |
| 50°-60° | 3638.0 | 20.4 |
| 60°-70° | 4535.3 | 25.5 |
| 70°-80° | 2974.0 | 16.7 |
| 80°-90° | 735.3 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 17811.0 | 100.0 |
| 0°-180° | 17811.0 | 100.0 |



REPORT NUMBER: P948160


CATALOG NUMBER: GALN-SB3B-750-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|--------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 1198.0 | 6.7 | | | |
| FM (30°-60°) | 5195.1 | 29.2 | | | |
| FH (60°-80°) | 6285.6 | 35.3 | | | G3/7500 |
| FVH (80°-90°) | 605.7 | 3.4 | | | G4/750 |
| BL (0°-30°) | 985.7 | 5.5 | B2/1000 | | |
| BM (30°-60°) | 2187.6 | 12.3 | B2/2500 | | |
| BH (60°-80°) | 1223.8 | 6.9 | B3/2500 | | G3/2500 |
| BVH (80°-90°) | 129.6 | 0.7 | | | G2/225 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B3-U0-G4

Type IV Short



REPORT NUMBER: P948160

CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° |
|-------|---------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2.5° | 2633.8 | 2613.6 | 2593.4 | 2571.9 | 2550.5 | 2528.9 | 2507.2 | 2486.6 | 2465.9 | 2445.9 |
| 5° | 2832.1 | 2787.5 | 2742.9 | 2698.3 | 2653.9 | 2609.0 | 2564.3 | 2522.5 | 2480.6 | 2441.2 |
| 7.5° | 3031.4 | 2957.7 | 2884.1 | 2816.1 | 2748.0 | 2681.8 | 2615.5 | 2557.2 | 2498.8 | 2444.9 |
| 10° | 3184.1 | 3091.0 | 2997.8 | 2907.9 | 2818.0 | 2737.6 | 2657.1 | 2588.1 | 2518.9 | 2452.5 |
| 12.5° | 3277.6 | 3175.3 | 3073.0 | 2971.1 | 2869.3 | 2774.3 | 2679.4 | 2601.3 | 2523.2 | 2453.4 |
| 15° | 3334.5 | 3227.8 | 3121.1 | 3010.6 | 2900.1 | 2790.8 | 2681.5 | 2591.1 | 2500.7 | 2423.3 |
| 17.5° | 3366.4 | 3258.3 | 3150.1 | 3029.5 | 2908.9 | 2782.0 | 2655.2 | 2546.4 | 2437.7 | 2346.7 |
| 20° | 3401.7 | 3289.3 | 3176.8 | 3044.3 | 2911.7 | 2758.0 | 2604.2 | 2469.5 | 2334.7 | 2228.8 |
| 22.5° | 3442.6 | 3327.7 | 3212.8 | 3064.2 | 2915.5 | 2728.5 | 2541.5 | 2379.1 | 2216.8 | 2096.3 |
| 25° | 3495.2 | 3382.6 | 3270.1 | 3100.3 | 2930.4 | 2699.3 | 2468.4 | 2278.3 | 2088.3 | 1964.7 |
| 27.5° | 3566.6 | 3459.3 | 3351.9 | 3156.7 | 2961.4 | 2679.9 | 2398.4 | 2186.1 | 1973.8 | 1861.3 |
| 30° | 3662.9 | 3559.2 | 3455.5 | 3229.7 | 3003.8 | 2670.8 | 2337.5 | 2109.0 | 1880.6 | 1786.1 |
| 32.5° | 3776.7 | 3673.9 | 3571.3 | 3305.9 | 3040.5 | 2659.5 | 2278.3 | 2042.6 | 1806.8 | 1730.7 |
| 35° | 3914.8 | 3816.5 | 3718.1 | 3392.7 | 3067.4 | 2638.3 | 2209.3 | 1977.3 | 1745.2 | 1681.8 |
| 37.5° | 4147.4 | 4022.0 | 3896.7 | 3490.0 | 3083.4 | 2601.9 | 2120.4 | 1900.4 | 1680.4 | 1624.9 |
| 40° | 4498.9 | 4316.2 | 4133.5 | 3613.5 | 3093.4 | 2551.8 | 2010.3 | 1808.7 | 1607.1 | 1556.8 |
| 42.5° | 4965.1 | 4701.3 | 4437.6 | 3775.1 | 3112.5 | 2500.1 | 1887.9 | 1707.5 | 1527.0 | 1480.7 |
| 45° | 5540.7 | 5185.0 | 4829.3 | 3987.6 | 3146.0 | 2452.1 | 1758.2 | 1599.9 | 1441.7 | 1394.7 |
| 47.5° | 6260.6 | 5760.0 | 5259.2 | 4214.1 | 3169.1 | 2412.4 | 1655.8 | 1514.9 | 1374.0 | 1313.4 |
| 50° | 7204.2 | 6449.4 | 5694.5 | 4424.3 | 3154.0 | 2369.2 | 1584.3 | 1458.4 | 1332.5 | 1252.8 |
| 52.5° | 8287.3 | 7173.6 | 6059.9 | 4560.7 | 3061.5 | 2296.2 | 1531.0 | 1421.2 | 1311.5 | 1219.9 |
| 55° | 9440.5 | 7815.7 | 6191.1 | 4530.7 | 2870.2 | 2175.1 | 1480.0 | 1394.2 | 1308.4 | 1223.2 |
| 57.5° | 10489.3 | 8270.8 | 6052.2 | 4319.0 | 2585.9 | 2004.4 | 1422.9 | 1362.3 | 1301.6 | 1226.5 |
| 60° | 11123.2 | 8384.5 | 5645.7 | 3925.2 | 2204.6 | 1782.8 | 1361.0 | 1313.4 | 1265.7 | 1216.1 |
| 62.5° | 10801.3 | 7905.7 | 5010.0 | 3392.6 | 1775.1 | 1517.6 | 1260.1 | 1228.4 | 1196.9 | 1190.7 |
| 65° | 10157.1 | 7228.1 | 4299.2 | 2849.2 | 1399.2 | 1279.0 | 1158.8 | 1143.9 | 1128.9 | 1129.7 |
| 67.5° | 9293.9 | 6421.9 | 3549.9 | 2316.8 | 1083.8 | 1049.7 | 1015.5 | 1023.8 | 1032.1 | 1030.0 |
| 70° | 8256.8 | 5542.1 | 2827.4 | 1824.2 | 820.9 | 830.7 | 840.4 | 879.1 | 917.7 | 917.7 |
| 72.5° | 7020.9 | 4588.4 | 2155.9 | 1394.6 | 633.2 | 662.7 | 692.2 | 747.1 | 801.9 | 811.1 |
| 75° | 5457.5 | 3495.1 | 1532.7 | 1012.2 | 491.7 | 518.4 | 545.1 | 606.6 | 668.0 | 710.5 |
| 77.5° | 3899.3 | 2446.3 | 993.2 | 685.9 | 378.6 | 396.7 | 414.9 | 474.6 | 534.3 | 604.3 |
| 80° | 2552.1 | 1576.1 | 600.1 | 441.9 | 283.8 | 291.3 | 298.9 | 349.4 | 399.9 | 483.5 |
| 82.5° | 1483.5 | 912.2 | 341.0 | 271.8 | 202.8 | 204.1 | 205.6 | 242.8 | 280.1 | 351.5 |
| 85° | 652.7 | 410.3 | 168.0 | 145.3 | 122.6 | 122.0 | 121.2 | 148.5 | 175.7 | 228.8 |
| 87.5° | 202.1 | 134.4 | 66.7 | 60.2 | 53.8 | 53.1 | 52.4 | 63.5 | 74.7 | 96.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 50° | | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2423.6 | 2.5° | 2405.6 | 2387.6 | 2371.3 | 2355.2 | 2341.0 | 2326.8 | 2312.5 | 2298.3 | 2287.3 | 2276.2 |
| 2402.2 | 5° | 2368.2 | 2334.0 | 2305.5 | 2277.0 | 2251.8 | 2226.6 | 2203.8 | 2180.8 | 2163.3 | 2145.6 |
| 2394.5 | 7.5° | 2349.2 | 2304.0 | 2266.4 | 2228.8 | 2197.1 | 2165.3 | 2137.3 | 2109.4 | 2088.5 | 2067.6 |
| 2398.2 | 10° | 2350.5 | 2302.7 | 2265.1 | 2227.6 | 2193.4 | 2159.2 | 2127.7 | 2096.3 | 2071.3 | 2046.2 |
| 2402.9 | 12.5° | 2363.8 | 2324.9 | 2299.9 | 2275.1 | 2248.2 | 2221.5 | 2188.9 | 2156.4 | 2124.5 | 2092.5 |
| 2382.9 | 15° | 2364.2 | 2345.6 | 2349.0 | 2352.4 | 2345.4 | 2338.5 | 2310.2 | 2281.9 | 2236.4 | 2190.9 |
| 2321.8 | 17.5° | 2328.7 | 2335.4 | 2376.4 | 2417.4 | 2439.2 | 2460.9 | 2438.1 | 2415.3 | 2355.1 | 2294.8 |
| 2222.2 | 20° | 2254.2 | 2286.1 | 2357.3 | 2428.5 | 2474.1 | 2519.7 | 2509.1 | 2498.5 | 2429.6 | 2360.8 |
| 2109.1 | 22.5° | 2156.4 | 2203.7 | 2284.9 | 2366.3 | 2425.6 | 2484.9 | 2491.3 | 2497.6 | 2431.8 | 2366.0 |
| 1999.5 | 25° | 2054.0 | 2108.5 | 2181.5 | 2254.6 | 2313.0 | 2371.3 | 2393.2 | 2414.9 | 2360.9 | 2307.1 |
| 1903.6 | 27.5° | 1956.2 | 2008.9 | 2068.9 | 2128.9 | 2175.7 | 2222.5 | 2246.7 | 2271.1 | 2232.6 | 2194.3 |
| 1819.3 | 30° | 1861.0 | 1902.9 | 1952.8 | 2002.6 | 2041.4 | 2080.3 | 2100.0 | 2119.8 | 2090.5 | 2061.2 |
| 1745.4 | 32.5° | 1770.1 | 1794.9 | 1834.6 | 1874.5 | 1911.7 | 1949.0 | 1970.9 | 1992.9 | 1966.0 | 1939.0 |
| 1675.7 | 35° | 1682.5 | 1689.3 | 1719.7 | 1749.9 | 1786.8 | 1823.7 | 1850.0 | 1876.3 | 1857.2 | 1838.1 |
| 1602.6 | 37.5° | 1595.1 | 1587.5 | 1609.3 | 1631.1 | 1667.8 | 1704.6 | 1737.2 | 1769.7 | 1760.8 | 1752.0 |
| 1522.5 | 40° | 1505.5 | 1488.5 | 1504.2 | 1519.9 | 1555.4 | 1590.9 | 1628.3 | 1665.8 | 1668.0 | 1670.1 |
| 1437.5 | 42.5° | 1414.9 | 1392.3 | 1405.1 | 1418.0 | 1451.6 | 1485.4 | 1525.8 | 1566.2 | 1577.0 | 1587.8 |
| 1352.9 | 45° | 1330.9 | 1309.0 | 1319.7 | 1330.6 | 1362.5 | 1394.5 | 1436.4 | 1478.3 | 1493.8 | 1509.3 |
| 1277.4 | 47.5° | 1259.0 | 1240.6 | 1250.7 | 1260.8 | 1292.1 | 1323.3 | 1364.6 | 1406.0 | 1423.8 | 1441.7 |
| 1211.0 | 50° | 1194.6 | 1178.3 | 1194.1 | 1210.0 | 1239.5 | 1268.9 | 1306.0 | 1343.0 | 1365.9 | 1388.9 |
| 1161.4 | 52.5° | 1145.3 | 1129.2 | 1153.0 | 1176.7 | 1203.7 | 1230.7 | 1265.2 | 1299.8 | 1326.9 | 1354.1 |
| 1135.1 | 55° | 1109.5 | 1084.1 | 1117.8 | 1151.5 | 1180.6 | 1209.7 | 1240.0 | 1270.2 | 1298.9 | 1327.8 |
| 1119.3 | 57.5° | 1082.1 | 1044.9 | 1081.2 | 1117.4 | 1151.7 | 1185.9 | 1215.7 | 1245.7 | 1274.8 | 1303.7 |
| 1104.5 | 60° | 1056.3 | 1008.0 | 1039.8 | 1071.6 | 1110.9 | 1150.1 | 1180.5 | 1211.0 | 1240.1 | 1269.2 |
| 1087.2 | 62.5° | 1026.8 | 966.6 | 986.8 | 1007.0 | 1052.8 | 1098.6 | 1131.1 | 1163.5 | 1190.2 | 1216.9 |
| 1050.7 | 65° | 986.6 | 922.4 | 930.2 | 937.9 | 987.0 | 1036.1 | 1067.2 | 1098.2 | 1121.7 | 1145.2 |
| 985.7 | 67.5° | 932.3 | 878.9 | 876.5 | 874.0 | 919.3 | 964.7 | 994.1 | 1023.5 | 1043.8 | 1064.1 |
| 903.2 | 70° | 865.2 | 827.2 | 818.8 | 810.3 | 850.2 | 890.0 | 915.4 | 940.8 | 959.1 | 977.4 |
| 811.3 | 72.5° | 785.2 | 759.2 | 746.8 | 734.5 | 765.9 | 797.2 | 820.1 | 843.0 | 861.0 | 878.9 |
| 706.9 | 75° | 686.9 | 666.8 | 655.0 | 643.0 | 666.3 | 689.6 | 710.4 | 731.2 | 747.5 | 763.9 |
| 602.4 | 77.5° | 586.4 | 570.3 | 558.3 | 546.2 | 565.2 | 584.1 | 602.0 | 619.8 | 637.0 | 654.1 |
| 483.3 | 80° | 469.8 | 456.3 | 446.2 | 436.1 | 451.9 | 467.6 | 482.6 | 497.6 | 510.7 | 523.7 |
| 355.4 | 82.5° | 348.9 | 342.3 | 335.1 | 328.0 | 326.7 | 325.4 | 320.1 | 314.8 | 342.7 | 370.5 |
| 234.0 | 85° | 227.0 | 219.9 | 211.9 | 203.9 | 197.2 | 190.3 | 175.7 | 161.2 | 187.2 | 213.3 |
| 103.4 | 87.5° | 100.6 | 97.7 | 96.2 | 94.7 | 94.5 | 94.2 | 83.1 | 71.9 | 82.8 | 93.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 105° | | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2267.3 | 2.5° | 2258.4 | 2251.4 | 2244.5 | 2238.1 | 2231.6 | 2223.6 | 2231.6 | 2238.1 | 2244.5 | 2251.4 |
| 2133.3 | 5° | 2121.0 | 2112.2 | 2103.5 | 2096.8 | 2090.2 | 2083.6 | 2090.2 | 2096.8 | 2103.5 | 2112.2 |
| 2052.9 | 7.5° | 2038.3 | 2028.2 | 2018.3 | 2012.2 | 2006.3 | 2001.8 | 2006.3 | 2012.2 | 2018.3 | 2028.2 |
| 2029.8 | 10° | 2013.3 | 2003.8 | 1994.3 | 1989.2 | 1984.1 | 1982.1 | 1984.1 | 1989.2 | 1994.3 | 2003.8 |
| 2071.4 | 12.5° | 2050.2 | 2039.6 | 2029.1 | 2024.7 | 2020.4 | 2019.7 | 2020.4 | 2024.7 | 2029.1 | 2039.6 |
| 2158.8 | 15° | 2126.6 | 2111.9 | 2097.2 | 2091.6 | 2085.9 | 2085.5 | 2085.9 | 2091.6 | 2097.2 | 2111.9 |
| 2247.5 | 17.5° | 2200.1 | 2178.3 | 2156.4 | 2149.3 | 2142.0 | 2140.9 | 2142.0 | 2149.3 | 2156.4 | 2178.3 |
| 2302.7 | 20° | 2244.8 | 2216.8 | 2188.8 | 2179.9 | 2171.0 | 2168.2 | 2171.0 | 2179.9 | 2188.8 | 2216.8 |
| 2306.2 | 22.5° | 2246.4 | 2216.9 | 2187.4 | 2177.6 | 2167.7 | 2163.5 | 2167.7 | 2177.6 | 2187.4 | 2216.9 |
| 2253.9 | 25° | 2200.9 | 2175.3 | 2149.8 | 2140.5 | 2131.3 | 2125.9 | 2131.3 | 2140.5 | 2149.8 | 2175.3 |
| 2153.0 | 27.5° | 2111.8 | 2094.7 | 2077.5 | 2073.2 | 2069.0 | 2067.6 | 2069.0 | 2073.2 | 2077.5 | 2094.7 |
| 2031.7 | 30° | 2002.0 | 1993.3 | 1984.4 | 1984.4 | 1984.4 | 1985.8 | 1984.4 | 1984.4 | 1984.4 | 1993.3 |
| 1915.4 | 32.5° | 1891.9 | 1886.1 | 1880.4 | 1881.1 | 1882.0 | 1883.4 | 1882.0 | 1881.1 | 1880.4 | 1886.1 |
| 1816.3 | 35° | 1794.6 | 1785.8 | 1777.2 | 1775.3 | 1773.4 | 1772.5 | 1773.4 | 1775.3 | 1777.2 | 1785.8 |
| 1732.0 | 37.5° | 1711.9 | 1696.0 | 1680.2 | 1671.8 | 1663.5 | 1658.8 | 1663.5 | 1671.8 | 1680.2 | 1696.0 |
| 1653.0 | 40° | 1636.0 | 1612.9 | 1590.0 | 1574.4 | 1559.0 | 1549.8 | 1559.0 | 1574.4 | 1590.0 | 1612.9 |
| 1573.4 | 42.5° | 1559.2 | 1530.5 | 1501.8 | 1479.2 | 1456.5 | 1441.7 | 1456.5 | 1479.2 | 1501.8 | 1530.5 |
| 1496.4 | 45° | 1483.5 | 1450.7 | 1418.0 | 1391.4 | 1364.8 | 1347.7 | 1364.8 | 1391.4 | 1418.0 | 1450.7 |
| 1432.7 | 47.5° | 1423.6 | 1394.5 | 1365.4 | 1340.7 | 1316.2 | 1299.8 | 1316.2 | 1340.7 | 1365.4 | 1394.5 |
| 1388.3 | 50° | 1387.9 | 1364.6 | 1341.3 | 1318.6 | 1295.8 | 1280.0 | 1295.8 | 1318.6 | 1341.3 | 1364.6 |
| 1359.0 | 52.5° | 1363.9 | 1344.9 | 1325.9 | 1305.5 | 1285.2 | 1270.6 | 1285.2 | 1305.5 | 1325.9 | 1344.9 |
| 1334.5 | 55° | 1341.3 | 1324.8 | 1308.2 | 1290.4 | 1272.5 | 1259.4 | 1272.5 | 1290.4 | 1308.2 | 1324.8 |
| 1310.6 | 57.5° | 1317.4 | 1300.7 | 1284.0 | 1266.3 | 1248.5 | 1234.9 | 1248.5 | 1266.3 | 1284.0 | 1300.7 |
| 1276.7 | 60° | 1284.3 | 1267.9 | 1251.6 | 1233.4 | 1215.2 | 1201.1 | 1215.2 | 1233.4 | 1251.6 | 1267.9 |
| 1224.1 | 62.5° | 1231.3 | 1216.6 | 1201.8 | 1182.7 | 1163.5 | 1146.6 | 1163.5 | 1182.7 | 1201.8 | 1216.6 |
| 1152.6 | 65° | 1159.9 | 1145.7 | 1131.5 | 1112.9 | 1094.4 | 1079.9 | 1094.4 | 1112.9 | 1131.5 | 1145.7 |
| 1071.3 | 67.5° | 1078.4 | 1065.4 | 1052.4 | 1035.1 | 1017.8 | 1004.7 | 1017.8 | 1035.1 | 1052.4 | 1065.4 |
| 984.4 | 70° | 991.3 | 980.7 | 970.1 | 953.5 | 937.0 | 922.0 | 937.0 | 953.5 | 970.1 | 980.7 |
| 887.2 | 72.5° | 895.5 | 886.6 | 877.8 | 862.0 | 846.3 | 831.7 | 846.3 | 862.0 | 877.8 | 886.6 |
| 772.5 | 75° | 781.2 | 776.9 | 772.5 | 759.3 | 746.0 | 732.1 | 746.0 | 759.3 | 772.5 | 776.9 |
| 662.2 | 77.5° | 670.3 | 664.3 | 658.1 | 644.7 | 631.4 | 620.3 | 631.4 | 644.7 | 658.1 | 664.3 |
| 534.4 | 80° | 545.1 | 542.5 | 539.9 | 522.0 | 503.9 | 483.1 | 503.9 | 522.0 | 539.9 | 542.5 |
| 388.7 | 82.5° | 406.9 | 405.8 | 404.6 | 389.5 | 374.2 | 360.9 | 374.2 | 389.5 | 404.6 | 405.8 |
| 235.9 | 85° | 258.4 | 256.6 | 254.7 | 242.8 | 231.0 | 219.0 | 231.0 | 242.8 | 254.7 | 256.6 |
| 102.9 | 87.5° | 112.0 | 109.8 | 107.3 | 101.3 | 95.1 | 89.3 | 95.1 | 101.3 | 107.3 | 109.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 160° | | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2258.4 | 2.5° | 2267.3 | 2276.2 | 2287.3 | 2298.3 | 2312.5 | 2326.8 | 2341.0 | 2355.2 | 2371.3 | 2387.6 |
| 2121.0 | 5° | 2133.3 | 2145.6 | 2163.3 | 2180.8 | 2203.8 | 2226.6 | 2251.8 | 2277.0 | 2305.5 | 2334.0 |
| 2038.3 | 7.5° | 2052.9 | 2067.6 | 2088.5 | 2109.4 | 2137.3 | 2165.3 | 2197.1 | 2228.8 | 2266.4 | 2304.0 |
| 2013.3 | 10° | 2029.8 | 2046.2 | 2071.3 | 2096.3 | 2127.7 | 2159.2 | 2193.4 | 2227.6 | 2265.1 | 2302.7 |
| 2050.2 | 12.5° | 2071.4 | 2092.5 | 2124.5 | 2156.4 | 2188.9 | 2221.5 | 2248.2 | 2275.1 | 2299.9 | 2324.9 |
| 2126.6 | 15° | 2158.8 | 2190.9 | 2236.4 | 2281.9 | 2310.2 | 2338.5 | 2345.4 | 2352.4 | 2349.0 | 2345.6 |
| 2200.1 | 17.5° | 2247.5 | 2294.8 | 2355.1 | 2415.3 | 2438.1 | 2460.9 | 2439.2 | 2417.4 | 2376.4 | 2335.4 |
| 2244.8 | 20° | 2302.7 | 2360.8 | 2429.6 | 2498.5 | 2509.1 | 2519.7 | 2474.1 | 2428.5 | 2357.3 | 2286.1 |
| 2246.4 | 22.5° | 2306.2 | 2366.0 | 2431.8 | 2497.6 | 2491.3 | 2484.9 | 2425.6 | 2366.3 | 2284.9 | 2203.7 |
| 2200.9 | 25° | 2253.9 | 2307.1 | 2360.9 | 2414.9 | 2393.2 | 2371.3 | 2313.0 | 2254.6 | 2181.5 | 2108.5 |
| 2111.8 | 27.5° | 2153.0 | 2194.3 | 2232.6 | 2271.1 | 2246.7 | 2222.5 | 2175.7 | 2128.9 | 2068.9 | 2008.9 |
| 2002.0 | 30° | 2031.7 | 2061.2 | 2090.5 | 2119.8 | 2100.0 | 2080.3 | 2041.4 | 2002.6 | 1952.8 | 1902.9 |
| 1891.9 | 32.5° | 1915.4 | 1939.0 | 1966.0 | 1992.9 | 1970.9 | 1949.0 | 1911.7 | 1874.5 | 1834.6 | 1794.9 |
| 1794.6 | 35° | 1816.3 | 1838.1 | 1857.2 | 1876.3 | 1850.0 | 1823.7 | 1786.8 | 1749.9 | 1719.7 | 1689.3 |
| 1711.9 | 37.5° | 1732.0 | 1752.0 | 1760.8 | 1769.7 | 1737.2 | 1704.6 | 1667.8 | 1631.1 | 1609.3 | 1587.5 |
| 1636.0 | 40° | 1653.0 | 1670.1 | 1668.0 | 1665.8 | 1628.3 | 1590.9 | 1555.4 | 1519.9 | 1504.2 | 1488.5 |
| 1559.2 | 42.5° | 1573.4 | 1587.8 | 1577.0 | 1566.2 | 1525.8 | 1485.4 | 1451.6 | 1418.0 | 1405.1 | 1392.3 |
| 1483.5 | 45° | 1496.4 | 1509.3 | 1493.8 | 1478.3 | 1436.4 | 1394.5 | 1362.5 | 1330.6 | 1319.7 | 1309.0 |
| 1423.6 | 47.5° | 1432.7 | 1441.7 | 1423.8 | 1406.0 | 1364.6 | 1323.3 | 1292.1 | 1260.8 | 1250.7 | 1240.6 |
| 1387.9 | 50° | 1388.3 | 1388.9 | 1365.9 | 1343.0 | 1306.0 | 1268.9 | 1239.5 | 1210.0 | 1194.1 | 1178.3 |
| 1363.9 | 52.5° | 1359.0 | 1354.1 | 1326.9 | 1299.8 | 1265.2 | 1230.7 | 1203.7 | 1176.7 | 1153.0 | 1129.2 |
| 1341.3 | 55° | 1334.5 | 1327.8 | 1298.9 | 1270.2 | 1240.0 | 1209.7 | 1180.6 | 1151.5 | 1117.8 | 1084.1 |
| 1317.4 | 57.5° | 1310.6 | 1303.7 | 1274.8 | 1245.7 | 1215.7 | 1185.9 | 1151.7 | 1117.4 | 1081.2 | 1044.9 |
| 1284.3 | 60° | 1276.7 | 1269.2 | 1240.1 | 1211.0 | 1180.5 | 1150.1 | 1110.9 | 1071.6 | 1039.8 | 1008.0 |
| 1231.3 | 62.5° | 1224.1 | 1216.9 | 1190.2 | 1163.5 | 1131.1 | 1098.6 | 1052.8 | 1007.0 | 986.8 | 966.6 |
| 1159.9 | 65° | 1152.6 | 1145.2 | 1121.7 | 1098.2 | 1067.2 | 1036.1 | 987.0 | 937.9 | 930.2 | 922.4 |
| 1078.4 | 67.5° | 1071.3 | 1064.1 | 1043.8 | 1023.5 | 994.1 | 964.7 | 919.3 | 874.0 | 876.5 | 878.9 |
| 991.3 | 70° | 984.4 | 977.4 | 959.1 | 940.8 | 915.4 | 890.0 | 850.2 | 810.3 | 818.8 | 827.2 |
| 895.5 | 72.5° | 887.2 | 878.9 | 861.0 | 843.0 | 820.1 | 797.2 | 765.9 | 734.5 | 746.8 | 759.2 |
| 781.2 | 75° | 772.5 | 763.9 | 747.5 | 731.2 | 710.4 | 689.6 | 666.3 | 643.0 | 655.0 | 666.8 |
| 670.3 | 77.5° | 662.2 | 654.1 | 637.0 | 619.8 | 602.0 | 584.1 | 565.2 | 546.2 | 558.3 | 570.3 |
| 545.1 | 80° | 534.4 | 523.7 | 510.7 | 497.6 | 482.6 | 467.6 | 451.9 | 436.1 | 446.2 | 456.3 |
| 406.9 | 82.5° | 388.7 | 370.5 | 342.7 | 314.8 | 320.1 | 325.4 | 326.7 | 328.0 | 335.1 | 342.3 |
| 258.4 | 85° | 235.9 | 213.3 | 187.2 | 161.2 | 175.7 | 190.3 | 197.2 | 203.9 | 211.9 | 219.9 |
| 112.0 | 87.5° | 102.9 | 93.8 | 82.8 | 71.9 | 83.1 | 94.2 | 94.5 | 94.7 | 96.2 | 97.7 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 215° | | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2405.6 | 2.5° | 2423.6 | 2445.9 | 2465.9 | 2486.6 | 2507.2 | 2528.9 | 2550.5 | 2571.9 | 2593.4 | 2613.6 |
| 2368.2 | 5° | 2402.2 | 2441.2 | 2480.6 | 2522.5 | 2564.3 | 2609.0 | 2653.9 | 2698.3 | 2742.9 | 2787.5 |
| 2349.2 | 7.5° | 2394.5 | 2444.9 | 2498.8 | 2557.2 | 2615.5 | 2681.8 | 2748.0 | 2816.1 | 2884.1 | 2957.7 |
| 2350.5 | 10° | 2398.2 | 2452.5 | 2518.9 | 2588.1 | 2657.1 | 2737.6 | 2818.0 | 2907.9 | 2997.8 | 3091.0 |
| 2363.8 | 12.5° | 2402.9 | 2453.4 | 2523.2 | 2601.3 | 2679.4 | 2774.3 | 2869.3 | 2971.1 | 3073.0 | 3175.3 |
| 2364.2 | 15° | 2382.9 | 2423.3 | 2500.7 | 2591.1 | 2681.5 | 2790.8 | 2900.1 | 3010.6 | 3121.1 | 3227.8 |
| 2328.7 | 17.5° | 2321.8 | 2346.7 | 2437.7 | 2546.4 | 2655.2 | 2782.0 | 2908.9 | 3029.5 | 3150.1 | 3258.3 |
| 2254.2 | 20° | 2222.2 | 2228.8 | 2334.7 | 2469.5 | 2604.2 | 2758.0 | 2911.7 | 3044.3 | 3176.8 | 3289.3 |
| 2156.4 | 22.5° | 2109.1 | 2096.3 | 2216.8 | 2379.1 | 2541.5 | 2728.5 | 2915.5 | 3064.2 | 3212.8 | 3327.7 |
| 2054.0 | 25° | 1999.5 | 1964.7 | 2088.3 | 2278.3 | 2468.4 | 2699.3 | 2930.4 | 3100.3 | 3270.1 | 3382.6 |
| 1956.2 | 27.5° | 1903.6 | 1861.3 | 1973.8 | 2186.1 | 2398.4 | 2679.9 | 2961.4 | 3156.7 | 3351.9 | 3459.3 |
| 1861.0 | 30° | 1819.3 | 1786.1 | 1880.6 | 2109.0 | 2337.5 | 2670.8 | 3003.8 | 3229.7 | 3455.5 | 3559.2 |
| 1770.1 | 32.5° | 1745.4 | 1730.7 | 1806.8 | 2042.6 | 2278.3 | 2659.5 | 3040.5 | 3305.9 | 3571.3 | 3673.9 |
| 1682.5 | 35° | 1675.7 | 1681.8 | 1745.2 | 1977.3 | 2209.3 | 2638.3 | 3067.4 | 3392.7 | 3718.1 | 3816.5 |
| 1595.1 | 37.5° | 1602.6 | 1624.9 | 1680.4 | 1900.4 | 2120.4 | 2601.9 | 3083.4 | 3490.0 | 3896.7 | 4022.0 |
| 1505.5 | 40° | 1522.5 | 1556.8 | 1607.1 | 1808.7 | 2010.3 | 2551.8 | 3093.4 | 3613.5 | 4133.5 | 4316.2 |
| 1414.9 | 42.5° | 1437.5 | 1480.7 | 1527.0 | 1707.5 | 1887.9 | 2500.1 | 3112.5 | 3775.1 | 4437.6 | 4701.3 |
| 1330.9 | 45° | 1352.9 | 1394.7 | 1441.7 | 1599.9 | 1758.2 | 2452.1 | 3146.0 | 3987.6 | 4829.3 | 5185.0 |
| 1259.0 | 47.5° | 1277.4 | 1313.4 | 1374.0 | 1514.9 | 1655.8 | 2412.4 | 3169.1 | 4214.1 | 5259.2 | 5760.0 |
| 1194.6 | 50° | 1211.0 | 1252.8 | 1332.5 | 1458.4 | 1584.3 | 2369.2 | 3154.0 | 4424.3 | 5694.5 | 6449.4 |
| 1145.3 | 52.5° | 1161.4 | 1219.9 | 1311.5 | 1421.2 | 1531.0 | 2296.2 | 3061.5 | 4560.7 | 6059.9 | 7173.6 |
| 1109.5 | 55° | 1135.1 | 1223.2 | 1308.4 | 1394.2 | 1480.0 | 2175.1 | 2870.2 | 4530.7 | 6191.1 | 7815.7 |
| 1082.1 | 57.5° | 1119.3 | 1226.5 | 1301.6 | 1362.3 | 1422.9 | 2004.4 | 2585.9 | 4319.0 | 6052.2 | 8270.8 |
| 1056.3 | 60° | 1104.5 | 1216.1 | 1265.7 | 1313.4 | 1361.0 | 1782.8 | 2204.6 | 3925.2 | 5645.7 | 8384.5 |
| 1026.8 | 62.5° | 1087.2 | 1190.7 | 1196.9 | 1228.4 | 1260.1 | 1517.6 | 1775.1 | 3392.6 | 5010.0 | 7905.7 |
| 986.6 | 65° | 1050.7 | 1129.7 | 1128.9 | 1143.9 | 1158.8 | 1279.0 | 1399.2 | 2849.2 | 4299.2 | 7228.1 |
| 932.3 | 67.5° | 985.7 | 1030.0 | 1032.1 | 1023.8 | 1015.5 | 1049.7 | 1083.8 | 2316.8 | 3549.9 | 6421.9 |
| 865.2 | 70° | 903.2 | 917.7 | 917.7 | 879.1 | 840.4 | 830.7 | 820.9 | 1824.2 | 2827.4 | 5542.1 |
| 785.2 | 72.5° | 811.3 | 811.1 | 801.9 | 747.1 | 692.2 | 662.7 | 633.2 | 1394.6 | 2155.9 | 4588.4 |
| 686.9 | 75° | 706.9 | 710.5 | 668.0 | 606.6 | 545.1 | 518.4 | 491.7 | 1012.2 | 1532.7 | 3495.1 |
| 586.4 | 77.5° | 602.4 | 604.3 | 534.3 | 474.6 | 414.9 | 396.7 | 378.6 | 685.9 | 993.2 | 2446.3 |
| 469.8 | 80° | 483.3 | 483.5 | 399.9 | 349.4 | 298.9 | 291.3 | 283.8 | 441.9 | 600.1 | 1576.1 |
| 348.9 | 82.5° | 355.4 | 351.5 | 280.1 | 242.8 | 205.6 | 204.1 | 202.8 | 271.8 | 341.0 | 912.2 |
| 227.0 | 85° | 234.0 | 228.8 | 175.7 | 148.5 | 121.2 | 122.0 | 122.6 | 145.3 | 168.0 | 410.3 |
| 100.6 | 87.5° | 103.4 | 96.8 | 74.7 | 63.5 | 52.4 | 53.1 | 53.8 | 60.2 | 66.7 | 134.4 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 270° | | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2633.8 | 2.5° | 2643.8 | 2653.9 | 2668.0 | 2682.2 | 2690.7 | 2699.2 | 2703.4 | 2707.6 | 2705.7 | 2707.6 |
| 2832.1 | 5° | 2867.0 | 2902.0 | 2936.6 | 2971.2 | 2990.0 | 3008.8 | 3020.2 | 3031.7 | 3040.3 | 3031.7 |
| 3031.4 | 7.5° | 3088.1 | 3144.8 | 3195.9 | 3246.9 | 3277.6 | 3308.3 | 3325.0 | 3341.5 | 3349.5 | 3341.5 |
| 3184.1 | 10° | 3251.2 | 3318.3 | 3378.2 | 3438.0 | 3474.3 | 3510.4 | 3526.6 | 3542.6 | 3548.8 | 3542.6 |
| 3277.6 | 12.5° | 3350.4 | 3423.0 | 3477.1 | 3531.1 | 3557.4 | 3583.7 | 3592.5 | 3601.4 | 3602.3 | 3601.4 |
| 3334.5 | 15° | 3397.3 | 3459.9 | 3493.9 | 3527.9 | 3528.8 | 3529.8 | 3520.4 | 3511.0 | 3499.9 | 3511.0 |
| 3366.4 | 17.5° | 3408.8 | 3451.2 | 3451.9 | 3452.4 | 3414.4 | 3376.3 | 3341.4 | 3306.5 | 3281.8 | 3306.5 |
| 3401.7 | 20° | 3416.4 | 3431.3 | 3386.6 | 3342.0 | 3258.0 | 3174.0 | 3112.8 | 3051.6 | 3014.0 | 3051.6 |
| 3442.6 | 22.5° | 3423.2 | 3403.8 | 3311.4 | 3218.9 | 3095.3 | 2971.7 | 2895.2 | 2818.7 | 2777.2 | 2818.7 |
| 3495.2 | 25° | 3434.1 | 3373.0 | 3232.6 | 3092.2 | 2942.1 | 2792.0 | 2711.6 | 2631.3 | 2592.0 | 2631.3 |
| 3566.6 | 27.5° | 3457.4 | 3348.1 | 3162.1 | 2976.2 | 2809.9 | 2643.5 | 2564.4 | 2485.3 | 2448.2 | 2485.3 |
| 3662.9 | 30° | 3500.1 | 3337.3 | 3108.4 | 2879.4 | 2706.1 | 2532.8 | 2459.4 | 2386.0 | 2351.4 | 2386.0 |
| 3776.7 | 32.5° | 3553.6 | 3330.7 | 3071.7 | 2812.7 | 2649.8 | 2486.9 | 2429.3 | 2371.6 | 2346.7 | 2371.6 |
| 3914.8 | 35° | 3641.9 | 3369.1 | 3099.1 | 2829.3 | 2716.2 | 2603.1 | 2589.7 | 2576.2 | 2574.2 | 2576.2 |
| 4147.4 | 37.5° | 3826.4 | 3505.3 | 3260.0 | 3014.7 | 3007.4 | 3000.1 | 3061.6 | 3123.0 | 3155.0 | 3123.0 |
| 4498.9 | 40° | 4149.8 | 3800.6 | 3618.2 | 3435.8 | 3564.5 | 3693.3 | 3842.7 | 3992.2 | 4066.6 | 3992.2 |
| 4965.1 | 42.5° | 4618.6 | 4272.2 | 4167.2 | 4062.1 | 4342.9 | 4623.7 | 4895.5 | 5167.3 | 5326.9 | 5167.3 |
| 5540.7 | 45° | 5229.5 | 4918.3 | 4871.9 | 4825.5 | 5275.4 | 5725.4 | 6172.0 | 6618.7 | 6889.8 | 6618.7 |
| 6260.6 | 47.5° | 5957.9 | 5655.1 | 5645.7 | 5636.3 | 6285.3 | 6934.2 | 7588.0 | 8241.7 | 8625.7 | 8241.7 |
| 7204.2 | 50° | 6830.2 | 6456.4 | 6458.0 | 6459.6 | 7296.0 | 8132.4 | 8995.5 | 9858.5 | 10380.3 | 9858.5 |
| 8287.3 | 52.5° | 7834.5 | 7381.8 | 7336.0 | 7290.2 | 8289.3 | 9288.4 | 10356.2 | 11424.0 | 12049.4 | 11424.0 |
| 9440.5 | 55° | 8993.1 | 8545.8 | 8367.3 | 8188.8 | 9300.8 | 10412.7 | 11685.7 | 12958.7 | 13702.5 | 12958.7 |
| 10489.3 | 57.5° | 10245.7 | 10002.0 | 9644.0 | 9286.2 | 10409.0 | 11531.8 | 12973.6 | 14415.4 | 15337.8 | 14415.4 |
| 11123.2 | 60° | 11501.6 | 11880.1 | 11435.5 | 10991.0 | 12053.5 | 13116.1 | 14659.8 | 16203.6 | 17200.6 | 16203.6 |
| 10801.3 | 62.5° | 11835.2 | 12869.1 | 12819.0 | 12768.8 | 13742.2 | 14715.7 | 16184.4 | 17653.1 | 18574.6 | 17653.1 |
| 10157.1 | 65° | 11127.4 | 12097.8 | 12289.8 | 12481.7 | 13718.7 | 14955.8 | 16380.0 | 17804.1 | 18588.7 | 17804.1 |
| 9293.9 | 67.5° | 10216.8 | 11139.7 | 11229.7 | 11319.6 | 12608.5 | 13897.3 | 15327.6 | 16757.9 | 17372.5 | 16757.9 |
| 8256.8 | 70° | 9260.6 | 10264.5 | 10304.7 | 10345.0 | 11497.6 | 12650.1 | 13881.0 | 15111.8 | 15453.4 | 15111.8 |
| 7020.9 | 72.5° | 8172.8 | 9324.9 | 9353.8 | 9382.7 | 10284.4 | 11186.2 | 12108.1 | 13029.8 | 13064.4 | 13029.8 |
| 5457.5 | 75° | 6649.8 | 7842.0 | 7949.1 | 8056.1 | 8757.7 | 9459.3 | 10108.2 | 10757.2 | 10583.3 | 10757.2 |
| 3899.3 | 77.5° | 5012.2 | 6125.3 | 6278.5 | 6431.6 | 6965.0 | 7498.3 | 7958.6 | 8418.9 | 8120.0 | 8418.9 |
| 2552.1 | 80° | 3488.4 | 4424.7 | 4615.1 | 4805.5 | 5208.3 | 5610.9 | 5852.6 | 6094.3 | 5613.5 | 6094.3 |
| 1483.5 | 82.5° | 2123.6 | 2763.8 | 2976.5 | 3189.3 | 3466.5 | 3743.8 | 3844.6 | 3945.4 | 3567.5 | 3945.4 |
| 652.7 | 85° | 992.4 | 1332.2 | 1513.1 | 1694.0 | 1921.8 | 2149.6 | 2206.8 | 2264.0 | 1961.4 | 2264.0 |
| 202.1 | 87.5° | 316.2 | 430.4 | 531.4 | 632.3 | 746.2 | 860.1 | 865.0 | 869.8 | 730.2 | 869.8 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P948160
 CATALOG NUMBER: GALN-SB3B-750-U-SLR

CANDELA DISTRIBUTION (continued):

| 325° | | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 2449.2 | 0° | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 | 2449.2 |
| 2703.4 | 2.5° | 2699.2 | 2690.7 | 2682.2 | 2668.0 | 2653.9 | 2643.8 | 2633.8 |
| 3020.2 | 5° | 3008.8 | 2990.0 | 2971.2 | 2936.6 | 2902.0 | 2867.0 | 2832.1 |
| 3325.0 | 7.5° | 3308.3 | 3277.6 | 3246.9 | 3195.9 | 3144.8 | 3088.1 | 3031.4 |
| 3526.6 | 10° | 3510.4 | 3474.3 | 3438.0 | 3378.2 | 3318.3 | 3251.2 | 3184.1 |
| 3592.5 | 12.5° | 3583.7 | 3557.4 | 3531.1 | 3477.1 | 3423.0 | 3350.4 | 3277.6 |
| 3520.4 | 15° | 3529.8 | 3528.8 | 3527.9 | 3493.9 | 3459.9 | 3397.3 | 3334.5 |
| 3341.4 | 17.5° | 3376.3 | 3414.4 | 3452.4 | 3451.9 | 3451.2 | 3408.8 | 3366.4 |
| 3112.8 | 20° | 3174.0 | 3258.0 | 3342.0 | 3386.6 | 3431.3 | 3416.4 | 3401.7 |
| 2895.2 | 22.5° | 2971.7 | 3095.3 | 3218.9 | 3311.4 | 3403.8 | 3423.2 | 3442.6 |
| 2711.6 | 25° | 2792.0 | 2942.1 | 3092.2 | 3232.6 | 3373.0 | 3434.1 | 3495.2 |
| 2564.4 | 27.5° | 2643.5 | 2809.9 | 2976.2 | 3162.1 | 3348.1 | 3457.4 | 3566.6 |
| 2459.4 | 30° | 2532.8 | 2706.1 | 2879.4 | 3108.4 | 3337.3 | 3500.1 | 3662.9 |
| 2429.3 | 32.5° | 2486.9 | 2649.8 | 2812.7 | 3071.7 | 3330.7 | 3553.6 | 3776.7 |
| 2589.7 | 35° | 2603.1 | 2716.2 | 2829.3 | 3099.1 | 3369.1 | 3641.9 | 3914.8 |
| 3061.6 | 37.5° | 3000.1 | 3007.4 | 3014.7 | 3260.0 | 3505.3 | 3826.4 | 4147.4 |
| 3842.7 | 40° | 3693.3 | 3564.5 | 3435.8 | 3618.2 | 3800.6 | 4149.8 | 4498.9 |
| 4895.5 | 42.5° | 4623.7 | 4342.9 | 4062.1 | 4167.2 | 4272.2 | 4618.6 | 4965.1 |
| 6172.0 | 45° | 5725.4 | 5275.4 | 4825.5 | 4871.9 | 4918.3 | 5229.5 | 5540.7 |
| 7588.0 | 47.5° | 6934.2 | 6285.3 | 5636.3 | 5645.7 | 5655.1 | 5957.9 | 6260.6 |
| 8995.5 | 50° | 8132.4 | 7296.0 | 6459.6 | 6458.0 | 6456.4 | 6830.2 | 7204.2 |
| 10356.2 | 52.5° | 9288.4 | 8289.3 | 7290.2 | 7336.0 | 7381.8 | 7834.5 | 8287.3 |
| 11685.7 | 55° | 10412.7 | 9300.8 | 8188.8 | 8367.3 | 8545.8 | 8993.1 | 9440.5 |
| 12973.6 | 57.5° | 11531.8 | 10409.0 | 9286.2 | 9644.0 | 10002.0 | 10245.7 | 10489.3 |
| 14659.8 | 60° | 13116.1 | 12053.5 | 10991.0 | 11435.5 | 11880.1 | 11501.6 | 11123.2 |
| 16184.4 | 62.5° | 14715.7 | 13742.2 | 12768.8 | 12819.0 | 12869.1 | 11835.2 | 10801.3 |
| 16380.0 | 65° | 14955.8 | 13718.7 | 12481.7 | 12289.8 | 12097.8 | 11127.4 | 10157.1 |
| 15327.6 | 67.5° | 13897.3 | 12608.5 | 11319.6 | 11229.7 | 11139.7 | 10216.8 | 9293.9 |
| 13881.0 | 70° | 12650.1 | 11497.6 | 10345.0 | 10304.7 | 10264.5 | 9260.6 | 8256.8 |
| 12108.1 | 72.5° | 11186.2 | 10284.4 | 9382.7 | 9353.8 | 9324.9 | 8172.8 | 7020.9 |
| 10108.2 | 75° | 9459.3 | 8757.7 | 8056.1 | 7949.1 | 7842.0 | 6649.8 | 5457.5 |
| 7958.6 | 77.5° | 7498.3 | 6965.0 | 6431.6 | 6278.5 | 6125.3 | 5012.2 | 3899.3 |
| 5852.6 | 80° | 5610.9 | 5208.3 | 4805.5 | 4615.1 | 4424.7 | 3488.4 | 2552.1 |
| 3844.6 | 82.5° | 3743.8 | 3466.5 | 3189.3 | 2976.5 | 2763.8 | 2123.6 | 1483.5 |
| 2206.8 | 85° | 2149.6 | 1921.8 | 1694.0 | 1513.1 | 1332.2 | 992.4 | 652.7 |
| 865.0 | 87.5° | 860.1 | 746.2 | 632.3 | 531.4 | 430.4 | 316.2 | 202.1 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)