

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P952822

Luminaire Tested: **GALN-SB6C-760-U-SLR**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P952822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB6C-760-U-SLR
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(6) 70 CRI, 5700K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT
ELIMINATOR RIGHT OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 47875 lumens
Efficiency: N/A
Efficacy: 159.1 lumens/watt
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')
IES Classification: Type IV - Short
BUG Rating: B4 - U0 - G5


Input Watts (W): 300.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 13 fc
 Type IV - Short - N/A

REPORT NUMBER: P952822
CATALOG NUMBER: GALN-SB6C-760-U-SLR

Luminous Intensity Polar Plot



REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 12167.4 | 0.0 | 12167.4 |
| | % Fixture | 25.4 | 0.0 | 25.4 |
| Street Side | Lumens | 35707.6 | 0.0 | 35707.6 |
| | % Fixture | 74.6 | 0.0 | 74.6 |
| Total | Lumens | 47875.0 | 0.0 | 47875.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 653.0 | 1.4 |
| 10°-20° | 2050.1 | 4.3 |
| 20°-30° | 3166.6 | 6.6 |
| 30°-40° | 4012.9 | 8.4 |
| 40°-50° | 6052.5 | 12.6 |
| 50°-60° | 9778.7 | 20.4 |
| 60°-70° | 12190.7 | 25.5 |
| 70°-80° | 7994.1 | 16.7 |
| 80°-90° | 1976.3 | 4.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 47875.0 | 100.0 |
| 0°-180° | 47875.0 | 100.0 |



REPORT NUMBER: P952822


CATALOG NUMBER: GALN-SB6C-760-U-SLR

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|---------|
| | | | B | U | G |
| FL (0°-30°) | 3220.1 | 6.7 | | | |
| FM (30°-60°) | 13964.1 | 29.2 | | | |
| FH (60°-80°) | 16895.3 | 35.3 | | | G5 |
| FVH (80°-90°) | 1628.1 | 3.4 | | | G5 |
| BL (0°-30°) | 2649.6 | 5.5 | B4/5000 | | |
| BM (30°-60°) | 5880.0 | 12.3 | B4/8500 | | |
| BH (60°-80°) | 3289.5 | 6.9 | B4/5000 | | G4/5000 |
| BVH (80°-90°) | 348.3 | 0.7 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G5

Type IV Short



REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 10° | 15° | 20° | 25° | 30° | 35° | 40° | 45° |
|-------|---------|---------|---------|---------|--------|--------|--------|--------|--------|--------|
| 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 2.5° | 7079.6 | 7025.3 | 6971.0 | 6913.1 | 6855.5 | 6797.4 | 6739.3 | 6683.8 | 6628.2 | 6574.4 |
| 5° | 7612.6 | 7492.6 | 7372.7 | 7252.9 | 7133.4 | 7012.9 | 6892.7 | 6780.3 | 6667.9 | 6561.8 |
| 7.5° | 8148.2 | 7950.1 | 7752.3 | 7569.4 | 7386.6 | 7208.5 | 7030.4 | 6873.5 | 6716.6 | 6571.9 |
| 10° | 8558.7 | 8308.4 | 8058.0 | 7816.3 | 7574.8 | 7358.5 | 7142.0 | 6956.6 | 6770.7 | 6592.1 |
| 12.5° | 8810.1 | 8535.0 | 8260.1 | 7986.3 | 7712.4 | 7457.3 | 7202.1 | 6992.2 | 6782.3 | 6594.6 |
| 15° | 8962.9 | 8676.2 | 8389.4 | 8092.4 | 7795.3 | 7501.5 | 7207.7 | 6964.7 | 6721.7 | 6513.8 |
| 17.5° | 9048.8 | 8758.0 | 8467.2 | 8143.1 | 7819.0 | 7478.0 | 7137.0 | 6844.7 | 6552.4 | 6307.9 |
| 20° | 9143.5 | 8841.4 | 8539.0 | 8182.8 | 7826.6 | 7413.3 | 7000.0 | 6637.8 | 6275.5 | 5990.8 |
| 22.5° | 9253.4 | 8944.7 | 8635.7 | 8236.4 | 7836.7 | 7334.0 | 6831.3 | 6395.0 | 5958.8 | 5634.6 |
| 25° | 9394.9 | 9092.2 | 8789.8 | 8333.4 | 7876.6 | 7255.7 | 6635.0 | 6124.0 | 5613.2 | 5281.0 |
| 27.5° | 9586.9 | 9298.4 | 9009.6 | 8484.9 | 7960.0 | 7203.4 | 6446.8 | 5876.1 | 5305.5 | 5003.1 |
| 30° | 9845.8 | 9566.9 | 9288.3 | 8681.2 | 8074.2 | 7178.9 | 6283.1 | 5669.0 | 5054.9 | 4801.0 |
| 32.5° | 10151.5 | 9875.3 | 9599.5 | 8886.1 | 8172.7 | 7148.6 | 6124.0 | 5490.4 | 4856.6 | 4652.0 |
| 35° | 10522.8 | 10258.6 | 9994.1 | 9119.5 | 8244.9 | 7091.5 | 5938.5 | 5314.8 | 4691.1 | 4520.6 |
| 37.5° | 11148.0 | 10811.0 | 10474.0 | 9381.0 | 8287.9 | 6993.7 | 5699.6 | 5108.2 | 4516.8 | 4367.8 |
| 40° | 12092.8 | 11601.7 | 11110.6 | 9712.9 | 8314.9 | 6859.1 | 5403.5 | 4861.6 | 4319.8 | 4184.6 |
| 42.5° | 13345.8 | 12637.0 | 11928.1 | 10147.2 | 8366.2 | 6720.1 | 5074.6 | 4589.6 | 4104.5 | 3980.0 |
| 45° | 14893.1 | 13936.9 | 12980.8 | 10718.6 | 8456.4 | 6591.1 | 4726.0 | 4300.6 | 3875.2 | 3748.9 |
| 47.5° | 16828.1 | 15482.5 | 14136.5 | 11327.4 | 8518.3 | 6484.5 | 4450.6 | 4071.9 | 3693.3 | 3530.3 |
| 50° | 19364.4 | 17335.7 | 15306.6 | 11892.2 | 8477.9 | 6368.2 | 4258.6 | 3920.1 | 3581.6 | 3367.4 |
| 52.5° | 22275.9 | 19282.3 | 16288.8 | 12259.0 | 8229.0 | 6172.0 | 4115.1 | 3820.1 | 3525.3 | 3279.0 |
| 55° | 25375.5 | 21008.2 | 16641.2 | 12178.2 | 7715.0 | 5846.6 | 3978.2 | 3747.6 | 3516.9 | 3287.8 |
| 57.5° | 28194.7 | 22231.4 | 16268.1 | 11609.3 | 6950.8 | 5387.8 | 3824.6 | 3661.7 | 3498.8 | 3296.7 |
| 60° | 29898.6 | 22537.1 | 15175.3 | 10550.6 | 5925.9 | 4792.2 | 3658.4 | 3530.3 | 3402.3 | 3268.9 |
| 62.5° | 29033.4 | 21250.0 | 13466.6 | 9119.0 | 4771.4 | 4079.3 | 3387.1 | 3302.0 | 3217.1 | 3200.7 |
| 65° | 27301.7 | 19428.8 | 11556.0 | 7658.4 | 3761.0 | 3437.9 | 3114.8 | 3074.6 | 3034.4 | 3036.5 |
| 67.5° | 24981.4 | 17261.6 | 9541.9 | 6227.5 | 2913.2 | 2821.5 | 2729.5 | 2752.0 | 2774.3 | 2768.7 |
| 70° | 22193.8 | 14896.9 | 7600.0 | 4903.3 | 2206.6 | 2232.9 | 2258.9 | 2363.0 | 2466.8 | 2466.8 |
| 72.5° | 18871.8 | 12333.3 | 5795.1 | 3748.6 | 1702.1 | 1781.2 | 1860.5 | 2008.1 | 2155.3 | 2180.1 |
| 75° | 14669.5 | 9394.6 | 4119.7 | 2720.7 | 1321.7 | 1393.4 | 1465.2 | 1630.4 | 1795.6 | 1909.8 |
| 77.5° | 10481.1 | 6575.4 | 2669.7 | 1843.6 | 1017.5 | 1066.3 | 1115.3 | 1275.7 | 1436.1 | 1624.3 |
| 80° | 6859.8 | 4236.4 | 1613.0 | 1187.8 | 762.9 | 783.1 | 803.3 | 939.2 | 1074.9 | 1299.7 |
| 82.5° | 3987.6 | 2451.9 | 916.5 | 730.6 | 545.1 | 548.7 | 552.7 | 652.8 | 752.8 | 944.8 |
| 85° | 1754.4 | 1102.9 | 451.7 | 390.5 | 329.7 | 327.9 | 325.9 | 399.1 | 472.4 | 615.1 |
| 87.5° | 543.1 | 361.2 | 179.4 | 161.9 | 144.5 | 142.7 | 141.0 | 170.8 | 200.8 | 260.2 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 50° | | 55° | 60° | 65° | 70° | 75° | 80° | 85° | 90° | 95° | 100° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 6514.5 | 2.5° | 6466.0 | 6417.8 | 6374.1 | 6330.6 | 6292.5 | 6254.3 | 6215.9 | 6177.8 | 6148.2 | 6118.4 |
| 6456.9 | 5° | 6365.5 | 6273.8 | 6197.0 | 6120.4 | 6052.7 | 5985.0 | 5923.6 | 5862.0 | 5814.8 | 5767.3 |
| 6436.2 | 7.5° | 6314.4 | 6192.9 | 6091.9 | 5990.8 | 5905.7 | 5820.3 | 5745.0 | 5670.0 | 5613.7 | 5557.6 |
| 6446.3 | 10° | 6318.0 | 6189.6 | 6088.6 | 5987.6 | 5895.9 | 5803.9 | 5719.3 | 5634.6 | 5567.4 | 5500.0 |
| 6458.9 | 12.5° | 6353.8 | 6249.3 | 6182.1 | 6115.4 | 6043.1 | 5971.4 | 5883.7 | 5796.3 | 5710.4 | 5624.5 |
| 6405.1 | 15° | 6354.9 | 6304.8 | 6313.9 | 6323.0 | 6304.3 | 6285.6 | 6209.6 | 6133.6 | 6011.3 | 5889.0 |
| 6240.9 | 17.5° | 6259.4 | 6277.6 | 6387.7 | 6497.8 | 6556.4 | 6614.8 | 6553.4 | 6492.3 | 6330.4 | 6168.4 |
| 5973.2 | 20° | 6059.0 | 6144.9 | 6336.2 | 6527.6 | 6650.2 | 6772.7 | 6744.4 | 6715.8 | 6530.7 | 6345.8 |
| 5669.3 | 22.5° | 5796.3 | 5923.4 | 6141.6 | 6360.4 | 6519.8 | 6679.2 | 6696.4 | 6713.3 | 6536.5 | 6359.7 |
| 5374.4 | 25° | 5521.0 | 5667.5 | 5863.8 | 6060.3 | 6217.2 | 6374.1 | 6432.7 | 6491.0 | 6346.0 | 6201.3 |
| 5116.8 | 27.5° | 5258.2 | 5399.7 | 5561.1 | 5722.3 | 5848.1 | 5973.9 | 6039.1 | 6104.5 | 6001.2 | 5898.1 |
| 4890.2 | 30° | 5002.3 | 5115.0 | 5248.9 | 5382.8 | 5487.1 | 5591.7 | 5644.7 | 5697.8 | 5619.2 | 5540.4 |
| 4691.6 | 32.5° | 4758.1 | 4824.5 | 4931.4 | 5038.5 | 5138.5 | 5238.8 | 5297.7 | 5356.8 | 5284.5 | 5212.0 |
| 4504.2 | 35° | 4522.4 | 4540.8 | 4622.4 | 4703.7 | 4802.8 | 4902.1 | 4972.8 | 5043.5 | 4992.0 | 4940.7 |
| 4307.6 | 37.5° | 4287.4 | 4267.2 | 4325.8 | 4384.2 | 4483.0 | 4582.0 | 4669.4 | 4756.8 | 4733.1 | 4709.3 |
| 4092.4 | 40° | 4046.7 | 4001.0 | 4043.2 | 4085.3 | 4180.8 | 4276.3 | 4376.9 | 4477.7 | 4483.5 | 4489.0 |
| 3863.8 | 42.5° | 3803.2 | 3742.5 | 3776.9 | 3811.5 | 3901.9 | 3992.6 | 4101.3 | 4209.9 | 4238.9 | 4268.0 |
| 3636.4 | 45° | 3577.3 | 3518.5 | 3547.3 | 3576.6 | 3662.5 | 3748.3 | 3861.0 | 3973.7 | 4015.4 | 4057.0 |
| 3433.6 | 47.5° | 3384.1 | 3334.6 | 3361.8 | 3388.9 | 3473.0 | 3556.9 | 3668.0 | 3779.2 | 3827.2 | 3875.2 |
| 3255.0 | 50° | 3211.0 | 3167.3 | 3209.8 | 3252.5 | 3331.8 | 3410.8 | 3510.4 | 3609.9 | 3671.5 | 3733.2 |
| 3121.9 | 52.5° | 3078.4 | 3035.2 | 3099.1 | 3162.8 | 3235.5 | 3308.0 | 3400.7 | 3493.7 | 3566.7 | 3639.7 |
| 3051.1 | 55° | 2982.4 | 2913.9 | 3004.6 | 3095.1 | 3173.4 | 3251.7 | 3333.0 | 3414.1 | 3491.4 | 3569.0 |
| 3008.7 | 57.5° | 2908.6 | 2808.6 | 2906.1 | 3003.6 | 3095.6 | 3187.5 | 3267.9 | 3348.5 | 3426.5 | 3504.3 |
| 2968.8 | 60° | 2839.2 | 2709.3 | 2795.0 | 2880.4 | 2985.9 | 3091.5 | 3173.1 | 3255.0 | 3333.3 | 3411.6 |
| 2922.3 | 62.5° | 2760.1 | 2598.2 | 2652.5 | 2706.8 | 2829.8 | 2953.1 | 3040.3 | 3127.4 | 3199.2 | 3270.9 |
| 2824.3 | 65° | 2652.0 | 2479.4 | 2500.4 | 2521.1 | 2653.0 | 2785.1 | 2868.5 | 2951.8 | 3015.0 | 3078.2 |
| 2649.5 | 67.5° | 2506.0 | 2362.5 | 2355.9 | 2349.3 | 2471.1 | 2593.1 | 2672.2 | 2751.0 | 2805.6 | 2860.1 |
| 2427.7 | 70° | 2325.6 | 2223.5 | 2200.8 | 2178.1 | 2285.2 | 2392.3 | 2460.5 | 2528.7 | 2578.0 | 2627.2 |
| 2180.6 | 72.5° | 2110.6 | 2040.6 | 2007.3 | 1974.2 | 2058.6 | 2142.7 | 2204.3 | 2266.0 | 2314.2 | 2362.5 |
| 1900.2 | 75° | 1846.4 | 1792.3 | 1760.5 | 1728.4 | 1791.1 | 1853.7 | 1909.5 | 1965.4 | 2009.3 | 2053.3 |
| 1619.3 | 77.5° | 1576.1 | 1532.9 | 1500.6 | 1468.2 | 1519.2 | 1570.0 | 1618.0 | 1666.0 | 1712.2 | 1758.2 |
| 1299.0 | 80° | 1262.8 | 1226.5 | 1199.4 | 1172.1 | 1214.6 | 1256.8 | 1297.2 | 1337.6 | 1372.7 | 1407.6 |
| 955.4 | 82.5° | 937.7 | 920.0 | 900.8 | 881.6 | 878.1 | 874.6 | 860.4 | 846.3 | 921.0 | 995.8 |
| 629.0 | 85° | 610.1 | 591.1 | 569.7 | 548.2 | 530.0 | 511.6 | 472.4 | 433.2 | 503.2 | 573.4 |
| 277.9 | 87.5° | 270.3 | 262.7 | 258.7 | 254.6 | 253.9 | 253.1 | 223.3 | 193.3 | 222.6 | 252.1 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 105° | | 110° | 115° | 120° | 125° | 130° | 135° | 140° | 145° | 150° | 155° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 6094.4 | 2.5° | 6070.4 | 6051.7 | 6033.0 | 6015.8 | 5998.4 | 5976.9 | 5998.4 | 6015.8 | 6033.0 | 6051.7 |
| 5734.2 | 5° | 5701.1 | 5677.6 | 5654.1 | 5636.2 | 5618.2 | 5600.5 | 5618.2 | 5636.2 | 5654.1 | 5677.6 |
| 5518.2 | 7.5° | 5478.8 | 5451.7 | 5425.0 | 5408.8 | 5392.9 | 5380.8 | 5392.9 | 5408.8 | 5425.0 | 5451.7 |
| 5456.0 | 10° | 5411.6 | 5386.1 | 5360.6 | 5346.9 | 5333.3 | 5327.7 | 5333.3 | 5346.9 | 5360.6 | 5386.1 |
| 5567.7 | 12.5° | 5510.9 | 5482.3 | 5454.0 | 5442.4 | 5430.8 | 5428.8 | 5430.8 | 5442.4 | 5454.0 | 5482.3 |
| 5802.6 | 15° | 5716.2 | 5676.6 | 5637.2 | 5622.0 | 5606.9 | 5605.6 | 5606.9 | 5622.0 | 5637.2 | 5676.6 |
| 6041.1 | 17.5° | 5913.8 | 5855.2 | 5796.3 | 5777.1 | 5757.7 | 5754.6 | 5757.7 | 5777.1 | 5796.3 | 5855.2 |
| 6189.6 | 20° | 6033.8 | 5958.8 | 5883.5 | 5859.5 | 5835.5 | 5827.9 | 5835.5 | 5859.5 | 5883.5 | 5958.8 |
| 6199.0 | 22.5° | 6038.1 | 5959.0 | 5879.7 | 5853.2 | 5826.6 | 5815.3 | 5826.6 | 5853.2 | 5879.7 | 5959.0 |
| 6058.3 | 25° | 5915.8 | 5847.1 | 5778.6 | 5753.6 | 5728.9 | 5714.2 | 5728.9 | 5753.6 | 5778.6 | 5847.1 |
| 5787.2 | 27.5° | 5676.3 | 5630.3 | 5584.1 | 5572.8 | 5561.4 | 5557.6 | 5561.4 | 5572.8 | 5584.1 | 5630.3 |
| 5461.1 | 30° | 5381.3 | 5357.8 | 5334.0 | 5334.0 | 5334.0 | 5337.8 | 5334.0 | 5334.0 | 5334.0 | 5357.8 |
| 5148.6 | 32.5° | 5085.2 | 5069.8 | 5054.4 | 5056.4 | 5058.7 | 5062.5 | 5058.7 | 5056.4 | 5054.4 | 5069.8 |
| 4882.1 | 35° | 4823.7 | 4800.2 | 4777.0 | 4772.0 | 4766.9 | 4764.4 | 4766.9 | 4772.0 | 4777.0 | 4800.2 |
| 4655.5 | 37.5° | 4601.4 | 4558.7 | 4516.3 | 4493.8 | 4471.3 | 4458.7 | 4471.3 | 4493.8 | 4516.3 | 4558.7 |
| 4443.3 | 40° | 4397.6 | 4335.4 | 4273.8 | 4231.9 | 4190.4 | 4165.7 | 4190.4 | 4231.9 | 4273.8 | 4335.4 |
| 4229.3 | 42.5° | 4190.9 | 4113.9 | 4036.8 | 3976.0 | 3915.1 | 3875.2 | 3915.1 | 3976.0 | 4036.8 | 4113.9 |
| 4022.2 | 45° | 3987.6 | 3899.4 | 3811.5 | 3740.0 | 3668.5 | 3622.5 | 3668.5 | 3740.0 | 3811.5 | 3899.4 |
| 3850.9 | 47.5° | 3826.7 | 3748.3 | 3670.0 | 3603.8 | 3537.9 | 3493.7 | 3537.9 | 3603.8 | 3670.0 | 3748.3 |
| 3731.7 | 50° | 3730.7 | 3668.0 | 3605.4 | 3544.2 | 3483.1 | 3440.7 | 3483.1 | 3544.2 | 3605.4 | 3668.0 |
| 3652.9 | 52.5° | 3666.0 | 3615.0 | 3563.9 | 3509.1 | 3454.6 | 3415.4 | 3454.6 | 3509.1 | 3563.9 | 3615.0 |
| 3587.2 | 55° | 3605.4 | 3560.9 | 3516.4 | 3468.4 | 3420.4 | 3385.1 | 3420.4 | 3468.4 | 3516.4 | 3560.9 |
| 3522.8 | 57.5° | 3541.2 | 3496.2 | 3451.3 | 3403.8 | 3356.0 | 3319.4 | 3356.0 | 3403.8 | 3451.3 | 3496.2 |
| 3431.8 | 60° | 3452.0 | 3408.1 | 3364.4 | 3315.4 | 3266.4 | 3228.5 | 3266.4 | 3315.4 | 3364.4 | 3408.1 |
| 3290.3 | 62.5° | 3309.8 | 3270.1 | 3230.5 | 3178.9 | 3127.4 | 3081.9 | 3127.4 | 3178.9 | 3230.5 | 3270.1 |
| 3098.1 | 65° | 3117.8 | 3079.7 | 3041.5 | 2991.5 | 2941.7 | 2902.6 | 2941.7 | 2991.5 | 3041.5 | 3079.7 |
| 2879.6 | 67.5° | 2898.8 | 2863.7 | 2828.8 | 2782.3 | 2735.9 | 2700.5 | 2735.9 | 2782.3 | 2828.8 | 2863.7 |
| 2645.9 | 70° | 2664.6 | 2636.1 | 2607.5 | 2563.1 | 2518.6 | 2478.2 | 2518.6 | 2563.1 | 2607.5 | 2636.1 |
| 2384.7 | 72.5° | 2406.9 | 2383.2 | 2359.5 | 2317.0 | 2274.8 | 2235.7 | 2274.8 | 2317.0 | 2359.5 | 2383.2 |
| 2076.5 | 75° | 2099.8 | 2088.1 | 2076.5 | 2040.9 | 2005.3 | 1967.9 | 2005.3 | 2040.9 | 2076.5 | 2088.1 |
| 1779.9 | 77.5° | 1801.7 | 1785.5 | 1768.8 | 1733.0 | 1697.1 | 1667.3 | 1697.1 | 1733.0 | 1768.8 | 1785.5 |
| 1436.4 | 80° | 1465.2 | 1458.1 | 1451.3 | 1403.0 | 1354.5 | 1298.5 | 1354.5 | 1403.0 | 1451.3 | 1458.1 |
| 1044.8 | 82.5° | 1093.8 | 1090.8 | 1087.5 | 1046.8 | 1005.9 | 970.1 | 1005.9 | 1046.8 | 1087.5 | 1090.8 |
| 634.1 | 85° | 694.7 | 689.6 | 684.6 | 652.8 | 620.9 | 588.6 | 620.9 | 652.8 | 684.6 | 689.6 |
| 276.6 | 87.5° | 301.1 | 295.1 | 288.5 | 272.3 | 255.6 | 240.0 | 255.6 | 272.3 | 288.5 | 295.1 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 160° | | 165° | 170° | 175° | 180° | 185° | 190° | 195° | 200° | 205° | 210° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 6070.4 | 2.5° | 6094.4 | 6118.4 | 6148.2 | 6177.8 | 6215.9 | 6254.3 | 6292.5 | 6330.6 | 6374.1 | 6417.8 |
| 5701.1 | 5° | 5734.2 | 5767.3 | 5814.8 | 5862.0 | 5923.6 | 5985.0 | 6052.7 | 6120.4 | 6197.0 | 6273.8 |
| 5478.8 | 7.5° | 5518.2 | 5557.6 | 5613.7 | 5670.0 | 5745.0 | 5820.3 | 5905.7 | 5990.8 | 6091.9 | 6192.9 |
| 5411.6 | 10° | 5456.0 | 5500.0 | 5567.4 | 5634.6 | 5719.3 | 5803.9 | 5895.9 | 5987.6 | 6088.6 | 6189.6 |
| 5510.9 | 12.5° | 5567.7 | 5624.5 | 5710.4 | 5796.3 | 5883.7 | 5971.4 | 6043.1 | 6115.4 | 6182.1 | 6249.3 |
| 5716.2 | 15° | 5802.6 | 5889.0 | 6011.3 | 6133.6 | 6209.6 | 6285.6 | 6304.3 | 6323.0 | 6313.9 | 6304.8 |
| 5913.8 | 17.5° | 6041.1 | 6168.4 | 6330.4 | 6492.3 | 6553.4 | 6614.8 | 6556.4 | 6497.8 | 6387.7 | 6277.6 |
| 6033.8 | 20° | 6189.6 | 6345.8 | 6530.7 | 6715.8 | 6744.4 | 6772.7 | 6650.2 | 6527.6 | 6336.2 | 6144.9 |
| 6038.1 | 22.5° | 6199.0 | 6359.7 | 6536.5 | 6713.3 | 6696.4 | 6679.2 | 6519.8 | 6360.4 | 6141.6 | 5923.4 |
| 5915.8 | 25° | 6058.3 | 6201.3 | 6346.0 | 6491.0 | 6432.7 | 6374.1 | 6217.2 | 6060.3 | 5863.8 | 5667.5 |
| 5676.3 | 27.5° | 5787.2 | 5898.1 | 6001.2 | 6104.5 | 6039.1 | 5973.9 | 5848.1 | 5722.3 | 5561.1 | 5399.7 |
| 5381.3 | 30° | 5461.1 | 5540.4 | 5619.2 | 5697.8 | 5644.7 | 5591.7 | 5487.1 | 5382.8 | 5248.9 | 5115.0 |
| 5085.2 | 32.5° | 5148.6 | 5212.0 | 5284.5 | 5356.8 | 5297.7 | 5238.8 | 5138.5 | 5038.5 | 4931.4 | 4824.5 |
| 4823.7 | 35° | 4882.1 | 4940.7 | 4992.0 | 5043.5 | 4972.8 | 4902.1 | 4802.8 | 4703.7 | 4622.4 | 4540.8 |
| 4601.4 | 37.5° | 4655.5 | 4709.3 | 4733.1 | 4756.8 | 4669.4 | 4582.0 | 4483.0 | 4384.2 | 4325.8 | 4267.2 |
| 4397.6 | 40° | 4443.3 | 4489.0 | 4483.5 | 4477.7 | 4376.9 | 4276.3 | 4180.8 | 4085.3 | 4043.2 | 4001.0 |
| 4190.9 | 42.5° | 4229.3 | 4268.0 | 4238.9 | 4209.9 | 4101.3 | 3992.6 | 3901.9 | 3811.5 | 3776.9 | 3742.5 |
| 3987.6 | 45° | 4022.2 | 4057.0 | 4015.4 | 3973.7 | 3861.0 | 3748.3 | 3662.5 | 3576.6 | 3547.3 | 3518.5 |
| 3826.7 | 47.5° | 3850.9 | 3875.2 | 3827.2 | 3779.2 | 3668.0 | 3556.9 | 3473.0 | 3388.9 | 3361.8 | 3334.6 |
| 3730.7 | 50° | 3731.7 | 3733.2 | 3671.5 | 3609.9 | 3510.4 | 3410.8 | 3331.8 | 3252.5 | 3209.8 | 3167.3 |
| 3666.0 | 52.5° | 3652.9 | 3639.7 | 3566.7 | 3493.7 | 3400.7 | 3308.0 | 3235.5 | 3162.8 | 3099.1 | 3035.2 |
| 3605.4 | 55° | 3587.2 | 3569.0 | 3491.4 | 3414.1 | 3333.0 | 3251.7 | 3173.4 | 3095.1 | 3004.6 | 2913.9 |
| 3541.2 | 57.5° | 3522.8 | 3504.3 | 3426.5 | 3348.5 | 3267.9 | 3187.5 | 3095.6 | 3003.6 | 2906.1 | 2808.6 |
| 3452.0 | 60° | 3431.8 | 3411.6 | 3333.3 | 3255.0 | 3173.1 | 3091.5 | 2985.9 | 2880.4 | 2795.0 | 2709.3 |
| 3309.8 | 62.5° | 3290.3 | 3270.9 | 3199.2 | 3127.4 | 3040.3 | 2953.1 | 2829.8 | 2706.8 | 2652.5 | 2598.2 |
| 3117.8 | 65° | 3098.1 | 3078.2 | 3015.0 | 2951.8 | 2868.5 | 2785.1 | 2653.0 | 2521.1 | 2500.4 | 2479.4 |
| 2898.8 | 67.5° | 2879.6 | 2860.1 | 2805.6 | 2751.0 | 2672.2 | 2593.1 | 2471.1 | 2349.3 | 2355.9 | 2362.5 |
| 2664.6 | 70° | 2645.9 | 2627.2 | 2578.0 | 2528.7 | 2460.5 | 2392.3 | 2285.2 | 2178.1 | 2200.8 | 2223.5 |
| 2406.9 | 72.5° | 2384.7 | 2362.5 | 2314.2 | 2266.0 | 2204.3 | 2142.7 | 2058.6 | 1974.2 | 2007.3 | 2040.6 |
| 2099.8 | 75° | 2076.5 | 2053.3 | 2009.3 | 1965.4 | 1909.5 | 1853.7 | 1791.1 | 1728.4 | 1760.5 | 1792.3 |
| 1801.7 | 77.5° | 1779.9 | 1758.2 | 1712.2 | 1666.0 | 1618.0 | 1570.0 | 1519.2 | 1468.2 | 1500.6 | 1532.9 |
| 1465.2 | 80° | 1436.4 | 1407.6 | 1372.7 | 1337.6 | 1297.2 | 1256.8 | 1214.6 | 1172.1 | 1199.4 | 1226.5 |
| 1093.8 | 82.5° | 1044.8 | 995.8 | 921.0 | 846.3 | 860.4 | 874.6 | 878.1 | 881.6 | 900.8 | 920.0 |
| 694.7 | 85° | 634.1 | 573.4 | 503.2 | 433.2 | 472.4 | 511.6 | 530.0 | 548.2 | 569.7 | 591.1 |
| 301.1 | 87.5° | 276.6 | 252.1 | 222.6 | 193.3 | 223.3 | 253.1 | 253.9 | 254.6 | 258.7 | 262.7 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 215° | | 220° | 225° | 230° | 235° | 240° | 245° | 250° | 255° | 260° | 265° |
|--------|-------|--------|--------|--------|--------|--------|--------|--------|---------|---------|---------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 6466.0 | 2.5° | 6514.5 | 6574.4 | 6628.2 | 6683.8 | 6739.3 | 6797.4 | 6855.5 | 6913.1 | 6971.0 | 7025.3 |
| 6365.5 | 5° | 6456.9 | 6561.8 | 6667.9 | 6780.3 | 6892.7 | 7012.9 | 7133.4 | 7252.9 | 7372.7 | 7492.6 |
| 6314.4 | 7.5° | 6436.2 | 6571.9 | 6716.6 | 6873.5 | 7030.4 | 7208.5 | 7386.6 | 7569.4 | 7752.3 | 7950.1 |
| 6318.0 | 10° | 6446.3 | 6592.1 | 6770.7 | 6956.6 | 7142.0 | 7358.5 | 7574.8 | 7816.3 | 8058.0 | 8308.4 |
| 6353.8 | 12.5° | 6458.9 | 6594.6 | 6782.3 | 6992.2 | 7202.1 | 7457.3 | 7712.4 | 7986.3 | 8260.1 | 8535.0 |
| 6354.9 | 15° | 6405.1 | 6513.8 | 6721.7 | 6964.7 | 7207.7 | 7501.5 | 7795.3 | 8092.4 | 8389.4 | 8676.2 |
| 6259.4 | 17.5° | 6240.9 | 6307.9 | 6552.4 | 6844.7 | 7137.0 | 7478.0 | 7819.0 | 8143.1 | 8467.2 | 8758.0 |
| 6059.0 | 20° | 5973.2 | 5990.8 | 6275.5 | 6637.8 | 7000.0 | 7413.3 | 7826.6 | 8182.8 | 8539.0 | 8841.4 |
| 5796.3 | 22.5° | 5669.3 | 5634.6 | 5958.8 | 6395.0 | 6831.3 | 7334.0 | 7836.7 | 8236.4 | 8635.7 | 8944.7 |
| 5521.0 | 25° | 5374.4 | 5281.0 | 5613.2 | 6124.0 | 6635.0 | 7255.7 | 7876.6 | 8333.4 | 8789.8 | 9092.2 |
| 5258.2 | 27.5° | 5116.8 | 5003.1 | 5305.5 | 5876.1 | 6446.8 | 7203.4 | 7960.0 | 8484.9 | 9009.6 | 9298.4 |
| 5002.3 | 30° | 4890.2 | 4801.0 | 5054.9 | 5669.0 | 6283.1 | 7178.9 | 8074.2 | 8681.2 | 9288.3 | 9566.9 |
| 4758.1 | 32.5° | 4691.6 | 4652.0 | 4856.6 | 5490.4 | 6124.0 | 7148.6 | 8172.7 | 8886.1 | 9599.5 | 9875.3 |
| 4522.4 | 35° | 4504.2 | 4520.6 | 4691.1 | 5314.8 | 5938.5 | 7091.5 | 8244.9 | 9119.5 | 9994.1 | 10258.6 |
| 4287.4 | 37.5° | 4307.6 | 4367.8 | 4516.8 | 5108.2 | 5699.6 | 6993.7 | 8287.9 | 9381.0 | 10474.0 | 10811.0 |
| 4046.7 | 40° | 4092.4 | 4184.6 | 4319.8 | 4861.6 | 5403.5 | 6859.1 | 8314.9 | 9712.9 | 11110.6 | 11601.7 |
| 3803.2 | 42.5° | 3863.8 | 3980.0 | 4104.5 | 4589.6 | 5074.6 | 6720.1 | 8366.2 | 10147.2 | 11928.1 | 12637.0 |
| 3577.3 | 45° | 3636.4 | 3748.9 | 3875.2 | 4300.6 | 4726.0 | 6591.1 | 8456.4 | 10718.6 | 12980.8 | 13936.9 |
| 3384.1 | 47.5° | 3433.6 | 3530.3 | 3693.3 | 4071.9 | 4450.6 | 6484.5 | 8518.3 | 11327.4 | 14136.5 | 15482.5 |
| 3211.0 | 50° | 3255.0 | 3367.4 | 3581.6 | 3920.1 | 4258.6 | 6368.2 | 8477.9 | 11892.2 | 15306.6 | 17335.7 |
| 3078.4 | 52.5° | 3121.9 | 3279.0 | 3525.3 | 3820.1 | 4115.1 | 6172.0 | 8229.0 | 12259.0 | 16288.8 | 19282.3 |
| 2982.4 | 55° | 3051.1 | 3287.8 | 3516.9 | 3747.6 | 3978.2 | 5846.6 | 7715.0 | 12178.2 | 16641.2 | 21008.2 |
| 2908.6 | 57.5° | 3008.7 | 3296.7 | 3498.8 | 3661.7 | 3824.6 | 5387.8 | 6950.8 | 11609.3 | 16268.1 | 22231.4 |
| 2839.2 | 60° | 2968.8 | 3268.9 | 3402.3 | 3530.3 | 3658.4 | 4792.2 | 5925.9 | 10550.6 | 15175.3 | 22537.1 |
| 2760.1 | 62.5° | 2922.3 | 3200.7 | 3217.1 | 3302.0 | 3387.1 | 4079.3 | 4771.4 | 9119.0 | 13466.6 | 21250.0 |
| 2652.0 | 65° | 2824.3 | 3036.5 | 3034.4 | 3074.6 | 3114.8 | 3437.9 | 3761.0 | 7658.4 | 11556.0 | 19428.8 |
| 2506.0 | 67.5° | 2649.5 | 2768.7 | 2774.3 | 2752.0 | 2729.5 | 2821.5 | 2913.2 | 6227.5 | 9541.9 | 17261.6 |
| 2325.6 | 70° | 2427.7 | 2466.8 | 2466.8 | 2363.0 | 2258.9 | 2232.9 | 2206.6 | 4903.3 | 7600.0 | 14896.9 |
| 2110.6 | 72.5° | 2180.6 | 2180.1 | 2155.3 | 2008.1 | 1860.5 | 1781.2 | 1702.1 | 3748.6 | 5795.1 | 12333.3 |
| 1846.4 | 75° | 1900.2 | 1909.8 | 1795.6 | 1630.4 | 1465.2 | 1393.4 | 1321.7 | 2720.7 | 4119.7 | 9394.6 |
| 1576.1 | 77.5° | 1619.3 | 1624.3 | 1436.1 | 1275.7 | 1115.3 | 1066.3 | 1017.5 | 1843.6 | 2669.7 | 6575.4 |
| 1262.8 | 80° | 1299.0 | 1299.7 | 1074.9 | 939.2 | 803.3 | 783.1 | 762.9 | 1187.8 | 1613.0 | 4236.4 |
| 937.7 | 82.5° | 955.4 | 944.8 | 752.8 | 652.8 | 552.7 | 548.7 | 545.1 | 730.6 | 916.5 | 2451.9 |
| 610.1 | 85° | 629.0 | 615.1 | 472.4 | 399.1 | 325.9 | 327.9 | 329.7 | 390.5 | 451.7 | 1102.9 |
| 270.3 | 87.5° | 277.9 | 260.2 | 200.8 | 170.8 | 141.0 | 142.7 | 144.5 | 161.9 | 179.4 | 361.2 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 270° | | 275° | 280° | 285° | 290° | 295° | 300° | 305° | 310° | 315° | 320° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 7079.6 | 2.5° | 7106.4 | 7133.4 | 7171.6 | 7209.7 | 7232.5 | 7255.2 | 7266.6 | 7277.9 | 7272.9 | 7277.9 |
| 7612.6 | 5° | 7706.4 | 7800.3 | 7893.3 | 7986.5 | 8037.0 | 8087.6 | 8118.1 | 8149.0 | 8172.2 | 8149.0 |
| 8148.2 | 7.5° | 8300.8 | 8453.1 | 8590.3 | 8727.4 | 8810.1 | 8892.7 | 8937.4 | 8981.8 | 9003.3 | 8981.8 |
| 8558.7 | 10° | 8739.1 | 8919.4 | 9080.4 | 9241.3 | 9338.8 | 9435.8 | 9479.2 | 9522.4 | 9538.9 | 9522.4 |
| 8810.1 | 12.5° | 9005.6 | 9200.9 | 9346.4 | 9491.4 | 9562.1 | 9632.8 | 9656.6 | 9680.3 | 9682.8 | 9680.3 |
| 8962.9 | 15° | 9131.6 | 9300.1 | 9391.3 | 9482.8 | 9485.3 | 9487.8 | 9462.6 | 9437.3 | 9407.5 | 9437.3 |
| 9048.8 | 17.5° | 9162.7 | 9276.6 | 9278.4 | 9279.9 | 9177.6 | 9075.3 | 8981.6 | 8887.6 | 8821.4 | 8887.6 |
| 9143.5 | 20° | 9183.2 | 9223.1 | 9103.1 | 8983.1 | 8757.3 | 8531.4 | 8367.0 | 8202.5 | 8101.5 | 8202.5 |
| 9253.4 | 22.5° | 9201.4 | 9149.3 | 8900.7 | 8652.2 | 8320.0 | 7987.8 | 7782.1 | 7576.5 | 7464.9 | 7576.5 |
| 9394.9 | 25° | 9230.7 | 9066.5 | 8689.0 | 8311.6 | 7908.2 | 7504.8 | 7288.5 | 7072.8 | 6967.2 | 7072.8 |
| 9586.9 | 27.5° | 9293.3 | 8999.5 | 8499.6 | 7999.9 | 7552.8 | 7105.6 | 6892.9 | 6680.5 | 6580.7 | 6680.5 |
| 9845.8 | 30° | 9408.0 | 8970.5 | 8355.1 | 7739.7 | 7273.9 | 6808.1 | 6610.8 | 6413.5 | 6320.5 | 6413.5 |
| 10151.5 | 32.5° | 9552.0 | 8952.8 | 8256.6 | 7560.4 | 7122.6 | 6684.8 | 6529.9 | 6374.8 | 6307.9 | 6374.8 |
| 10522.8 | 35° | 9789.2 | 9055.8 | 8330.3 | 7605.1 | 7300.9 | 6997.0 | 6960.9 | 6924.8 | 6919.2 | 6924.8 |
| 11148.0 | 37.5° | 10285.1 | 9422.1 | 8762.8 | 8103.5 | 8083.8 | 8064.1 | 8229.3 | 8394.5 | 8480.4 | 8394.5 |
| 12092.8 | 40° | 11154.3 | 10215.9 | 9725.5 | 9235.2 | 9581.3 | 9927.4 | 10329.0 | 10730.7 | 10930.8 | 10730.7 |
| 13345.8 | 42.5° | 12414.7 | 11483.5 | 11201.1 | 10918.7 | 11673.5 | 12428.3 | 13158.9 | 13889.4 | 14318.4 | 13889.4 |
| 14893.1 | 45° | 14056.7 | 13220.0 | 13095.5 | 12970.7 | 14180.0 | 15389.5 | 16589.9 | 17790.6 | 18519.4 | 17790.6 |
| 16828.1 | 47.5° | 16014.5 | 15200.5 | 15175.3 | 15150.0 | 16894.6 | 18638.7 | 20396.1 | 22153.3 | 23185.3 | 22153.3 |
| 19364.4 | 50° | 18359.3 | 17354.4 | 17358.6 | 17362.9 | 19611.2 | 21859.5 | 24179.3 | 26499.1 | 27901.7 | 26499.1 |
| 22275.9 | 52.5° | 21058.7 | 19841.9 | 19718.9 | 19595.6 | 22281.2 | 24966.7 | 27837.0 | 30707.0 | 32388.2 | 30707.0 |
| 25375.5 | 55° | 24173.0 | 22970.6 | 22490.8 | 22011.1 | 25000.1 | 27988.8 | 31410.5 | 34832.2 | 36831.7 | 34832.2 |
| 28194.7 | 57.5° | 27539.9 | 26884.9 | 25922.6 | 24960.7 | 27978.7 | 30996.7 | 34872.4 | 38747.8 | 41227.3 | 38747.8 |
| 29898.6 | 60° | 30915.6 | 31932.9 | 30738.1 | 29543.2 | 32399.3 | 35255.4 | 39404.9 | 43554.4 | 46234.1 | 43554.4 |
| 29033.4 | 62.5° | 31812.4 | 34591.5 | 34456.8 | 34321.9 | 36938.3 | 39554.9 | 43502.8 | 47450.5 | 49927.4 | 47450.5 |
| 27301.7 | 65° | 29910.0 | 32518.3 | 33034.3 | 33550.2 | 36875.2 | 40200.4 | 44028.5 | 47856.5 | 49965.3 | 47856.5 |
| 24981.4 | 67.5° | 27462.1 | 29942.8 | 30184.8 | 30426.6 | 33891.0 | 37355.1 | 41199.7 | 45044.3 | 46696.4 | 45044.3 |
| 22193.8 | 70° | 24892.0 | 27590.4 | 27698.6 | 27806.9 | 30905.0 | 34002.9 | 37311.4 | 40619.7 | 41538.0 | 40619.7 |
| 18871.8 | 72.5° | 21968.2 | 25064.8 | 25142.6 | 25220.1 | 27644.0 | 30067.9 | 32545.8 | 35023.5 | 35116.4 | 35023.5 |
| 14669.5 | 75° | 17874.2 | 21079.0 | 21366.7 | 21654.4 | 23540.2 | 25426.0 | 27170.3 | 28914.7 | 28447.3 | 28914.7 |
| 10481.1 | 77.5° | 13472.6 | 16464.4 | 16876.1 | 17287.9 | 18721.5 | 20155.1 | 21392.2 | 22629.5 | 21826.2 | 22629.5 |
| 6859.8 | 80° | 9376.7 | 11893.3 | 12405.1 | 12916.9 | 13999.6 | 15081.8 | 15731.5 | 16381.0 | 15088.9 | 16381.0 |
| 3987.6 | 82.5° | 5708.2 | 7429.0 | 8000.7 | 8572.6 | 9317.8 | 10063.0 | 10334.1 | 10604.9 | 9589.4 | 10604.9 |
| 1754.4 | 85° | 2667.6 | 3580.9 | 4067.1 | 4553.4 | 5165.8 | 5777.9 | 5931.7 | 6085.6 | 5272.1 | 6085.6 |
| 543.1 | 87.5° | 850.1 | 1157.0 | 1428.3 | 1699.6 | 2005.8 | 2312.0 | 2325.1 | 2338.0 | 1962.8 | 2338.0 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

REPORT NUMBER: P952822
 CATALOG NUMBER: GALN-SB6C-760-U-SLR

CANDELA DISTRIBUTION (continued):

| 325° | | 330° | 335° | 340° | 345° | 350° | 355° | 360° |
|---------|-------|---------|---------|---------|---------|---------|---------|---------|
| 6583.2 | 0° | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 | 6583.2 |
| 7266.6 | 2.5° | 7255.2 | 7232.5 | 7209.7 | 7171.6 | 7133.4 | 7106.4 | 7079.6 |
| 8118.1 | 5° | 8087.6 | 8037.0 | 7986.5 | 7893.3 | 7800.3 | 7706.4 | 7612.6 |
| 8937.4 | 7.5° | 8892.7 | 8810.1 | 8727.4 | 8590.3 | 8453.1 | 8300.8 | 8148.2 |
| 9479.2 | 10° | 9435.8 | 9338.8 | 9241.3 | 9080.4 | 8919.4 | 8739.1 | 8558.7 |
| 9656.6 | 12.5° | 9632.8 | 9562.1 | 9491.4 | 9346.4 | 9200.9 | 9005.6 | 8810.1 |
| 9462.6 | 15° | 9487.8 | 9485.3 | 9482.8 | 9391.3 | 9300.1 | 9131.6 | 8962.9 |
| 8981.6 | 17.5° | 9075.3 | 9177.6 | 9279.9 | 9278.4 | 9276.6 | 9162.7 | 9048.8 |
| 8367.0 | 20° | 8531.4 | 8757.3 | 8983.1 | 9103.1 | 9223.1 | 9183.2 | 9143.5 |
| 7782.1 | 22.5° | 7987.8 | 8320.0 | 8652.2 | 8900.7 | 9149.3 | 9201.4 | 9253.4 |
| 7288.5 | 25° | 7504.8 | 7908.2 | 8311.6 | 8689.0 | 9066.5 | 9230.7 | 9394.9 |
| 6892.9 | 27.5° | 7105.6 | 7552.8 | 7999.9 | 8499.6 | 8999.5 | 9293.3 | 9586.9 |
| 6610.8 | 30° | 6808.1 | 7273.9 | 7739.7 | 8355.1 | 8970.5 | 9408.0 | 9845.8 |
| 6529.9 | 32.5° | 6684.8 | 7122.6 | 7560.4 | 8256.6 | 8952.8 | 9552.0 | 10151.5 |
| 6960.9 | 35° | 6997.0 | 7300.9 | 7605.1 | 8330.3 | 9055.8 | 9789.2 | 10522.8 |
| 8229.3 | 37.5° | 8064.1 | 8083.8 | 8103.5 | 8762.8 | 9422.1 | 10285.1 | 11148.0 |
| 10329.0 | 40° | 9927.4 | 9581.3 | 9235.2 | 9725.5 | 10215.9 | 11154.3 | 12092.8 |
| 13158.9 | 42.5° | 12428.3 | 11673.5 | 10918.7 | 11201.1 | 11483.5 | 12414.7 | 13345.8 |
| 16589.9 | 45° | 15389.5 | 14180.0 | 12970.7 | 13095.5 | 13220.0 | 14056.7 | 14893.1 |
| 20396.1 | 47.5° | 18638.7 | 16894.6 | 15150.0 | 15175.3 | 15200.5 | 16014.5 | 16828.1 |
| 24179.3 | 50° | 21859.5 | 19611.2 | 17362.9 | 17358.6 | 17354.4 | 18359.3 | 19364.4 |
| 27837.0 | 52.5° | 24966.7 | 22281.2 | 19595.6 | 19718.9 | 19841.9 | 21058.7 | 22275.9 |
| 31410.5 | 55° | 27988.8 | 25000.1 | 22011.1 | 22490.8 | 22970.6 | 24173.0 | 25375.5 |
| 34872.4 | 57.5° | 30996.7 | 27978.7 | 24960.7 | 25922.6 | 26884.9 | 27539.9 | 28194.7 |
| 39404.9 | 60° | 35255.4 | 32399.3 | 29543.2 | 30738.1 | 31932.9 | 30915.6 | 29898.6 |
| 43502.8 | 62.5° | 39554.9 | 36938.3 | 34321.9 | 34456.8 | 34591.5 | 31812.4 | 29033.4 |
| 44028.5 | 65° | 40200.4 | 36875.2 | 33550.2 | 33034.3 | 32518.3 | 29910.0 | 27301.7 |
| 41199.7 | 67.5° | 37355.1 | 33891.0 | 30426.6 | 30184.8 | 29942.8 | 27462.1 | 24981.4 |
| 37311.4 | 70° | 34002.9 | 30905.0 | 27806.9 | 27698.6 | 27590.4 | 24892.0 | 22193.8 |
| 32545.8 | 72.5° | 30067.9 | 27644.0 | 25220.1 | 25142.6 | 25064.8 | 21968.2 | 18871.8 |
| 27170.3 | 75° | 25426.0 | 23540.2 | 21654.4 | 21366.7 | 21079.0 | 17874.2 | 14669.5 |
| 21392.2 | 77.5° | 20155.1 | 18721.5 | 17287.9 | 16876.1 | 16464.4 | 13472.6 | 10481.1 |
| 15731.5 | 80° | 15081.8 | 13999.6 | 12916.9 | 12405.1 | 11893.3 | 9376.7 | 6859.8 |
| 10334.1 | 82.5° | 10063.0 | 9317.8 | 8572.6 | 8000.7 | 7429.0 | 5708.2 | 3987.6 |
| 5931.7 | 85° | 5777.9 | 5165.8 | 4553.4 | 4067.1 | 3580.9 | 2667.6 | 1754.4 |
| 2325.1 | 87.5° | 2312.0 | 2005.8 | 1699.6 | 1428.3 | 1157.0 | 850.1 | 543.1 |
| 0.0 | 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

(END OF REPORT)