

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P947465

Luminaire Tested: **GALN-SB2D-760-U-SLL**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P947465  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB2D-760-U-SLL  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(2) 70 CRI, 5700K, 900mA LIGHTSQUARES WITH 26 LEDS EACH AND SPILL LIGHT  
ELIMINATOR LEFT OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 21453 lumens  
Efficiency: N/A  
Efficacy: 145.3 lumens/watt  
Luminous Opening: Rectangular (W 0.5' x L: 1' x H: 0')  
IES Classification: Type IV - Short  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 147.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.5 fc  
 Type IV - Short - N/A

REPORT NUMBER: P947465  
CATALOG NUMBER: GALN-SB2D-760-U-SLL

### Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P947465

CATALOG NUMBER: GALN-SB2D-760-U-SLL

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	5452.3	0.0	5452.3
	% Fixture	25.4	0.0	25.4
<b>Street Side</b>	Lumens	16000.7	0.0	16000.7
	% Fixture	74.6	0.0	74.6
<b>Total</b>	Lumens	21453.0	0.0	21453.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	292.6	1.4
10°-20°	918.6	4.3
20°-30°	1419.0	6.6
30°-40°	1798.2	8.4
40°-50°	2712.2	12.6
50°-60°	4381.9	20.4
60°-70°	5462.7	25.5
70°-80°	3582.2	16.7
80°-90°	885.6	4.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	21453.0	100.0
0°-180°	21453.0	100.0

**Coefficient of Utilization**




REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1443.0	6.7			
FM (30°-60°)	6257.4	29.2			
FH (60°-80°)	7570.9	35.3			G4/12000
FVH (80°-90°)	729.5	3.4			G4/750
BL (0°-30°)	1187.3	5.5	B3/2500		
BM (30°-60°)	2634.9	12.3	B3/5000		
BH (60°-80°)	1474.0	6.9	B3/2500		G3/2500
BVH (80°-90°)	156.1	0.7			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**

Type IV Short



REPORT NUMBER: P947465

CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°
0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
2.5°	3172.4	3184.4	3196.5	3213.6	3230.7	3240.9	3251.1	3256.2	3261.3	3259.0
5°	3411.3	3453.3	3495.4	3537.0	3578.8	3601.4	3624.1	3637.8	3651.6	3662.0
7.5°	3651.2	3719.6	3787.9	3849.3	3910.8	3947.8	3984.8	4004.9	4024.8	4034.4
10°	3835.2	3916.0	3996.8	4068.9	4141.1	4184.7	4228.2	4247.7	4267.0	4274.4
12.5°	3947.8	4035.4	4122.9	4188.1	4253.1	4284.8	4316.5	4327.2	4337.8	4338.9
15°	4016.3	4091.9	4167.4	4208.3	4249.3	4250.4	4251.5	4240.2	4228.9	4215.5
17.5°	4054.8	4105.8	4156.9	4157.7	4158.4	4112.5	4066.7	4024.7	3982.6	3952.9
20°	4097.2	4115.0	4132.9	4079.1	4025.4	3924.2	3823.0	3749.3	3675.6	3630.3
22.5°	4146.5	4123.2	4099.9	3988.5	3877.1	3728.2	3579.4	3487.2	3395.1	3345.0
25°	4209.9	4136.3	4062.7	3893.6	3724.5	3543.7	3362.9	3266.0	3169.4	3122.0
27.5°	4295.9	4164.4	4032.7	3808.7	3584.8	3384.4	3184.1	3088.8	2993.6	2948.8
30°	4411.9	4215.8	4019.7	3744.0	3468.2	3259.5	3050.7	2962.3	2873.9	2832.2
32.5°	4548.9	4280.3	4011.8	3699.8	3387.8	3191.7	2995.5	2926.1	2856.6	2826.6
35°	4715.3	4386.6	4058.0	3732.9	3407.9	3271.6	3135.4	3119.2	3103.0	3100.5
37.5°	4995.5	4608.8	4222.1	3926.7	3631.2	3622.4	3613.5	3687.6	3761.6	3800.1
40°	5418.8	4998.3	4577.8	4358.1	4138.3	4293.4	4448.5	4628.5	4808.5	4898.1
42.5°	5980.3	5563.1	5145.8	5019.3	4892.7	5230.9	5569.2	5896.5	6223.9	6416.1
45°	6673.7	6298.9	5923.9	5868.1	5812.2	6354.1	6896.1	7434.0	7972.1	8298.6
47.5°	7540.8	7176.2	6811.4	6800.1	6788.8	7570.5	8352.1	9139.6	9927.0	10389.4
50°	8677.3	8226.9	7776.6	7778.5	7780.4	8787.9	9795.4	10834.9	11874.4	12502.9
52.5°	9981.9	9436.5	8891.2	8836.1	8780.9	9984.3	11187.7	12473.9	13759.9	14513.3
55°	11370.9	10832.0	10293.2	10078.2	9863.3	11202.6	12541.9	14075.2	15608.5	16504.4
57.5°	12634.2	12340.8	12047.2	11616.1	11185.0	12537.4	13889.8	15626.5	17363.1	18474.1
60°	13397.7	13853.4	14309.3	13773.9	13238.4	14518.3	15798.1	17657.5	19516.9	20717.7
62.5°	13010.0	14255.3	15500.6	15440.3	15379.8	16552.2	17724.7	19493.8	21262.8	22372.7
65°	12234.0	13402.8	14571.6	14802.8	15034.0	16523.9	18014.0	19729.4	21444.7	22389.7
67.5°	11194.3	12305.9	13417.5	13526.0	13634.3	15186.7	16739.0	18461.8	20184.6	20924.9
70°	9945.1	11154.2	12363.4	12411.8	12460.4	13848.7	15236.8	16719.4	18201.9	18613.4
72.5°	8456.5	9844.0	11231.6	11266.5	11301.2	12387.4	13473.5	14583.9	15694.2	15735.8
75°	6573.5	8009.5	9445.6	9574.5	9703.4	10548.5	11393.5	12175.1	12956.8	12747.4
77.5°	4696.6	6037.1	7377.8	7562.3	7746.8	8389.2	9031.6	9585.9	10140.4	9780.4
80°	3073.9	4201.7	5329.4	5558.8	5788.1	6273.3	6758.2	7049.4	7340.4	6761.4
82.5°	1786.9	2557.9	3329.0	3585.1	3841.4	4175.4	4509.3	4630.8	4752.1	4297.0
85°	786.2	1195.4	1604.6	1822.5	2040.4	2314.8	2589.1	2658.0	2727.0	2362.5
87.5°	243.4	380.9	518.5	640.0	761.6	898.8	1036.0	1041.9	1047.7	879.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

50°		55°	60°	65°	70°	75°	80°	85°	90°	95°	100°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
3261.3	2.5°	3256.2	3251.1	3240.9	3230.7	3213.6	3196.5	3184.4	3172.4	3148.1	3123.7
3651.6	5°	3637.8	3624.1	3601.4	3578.8	3537.0	3495.4	3453.3	3411.3	3357.5	3303.7
4024.8	7.5°	4004.9	3984.8	3947.8	3910.8	3849.3	3787.9	3719.6	3651.2	3562.5	3473.9
4267.0	10°	4247.7	4228.2	4184.7	4141.1	4068.9	3996.8	3916.0	3835.2	3723.0	3610.8
4337.8	12.5°	4327.2	4316.5	4284.8	4253.1	4188.1	4122.9	4035.4	3947.8	3824.5	3701.4
4228.9	15°	4240.2	4251.5	4250.4	4249.3	4208.3	4167.4	4091.9	4016.3	3887.8	3759.3
3982.6	17.5°	4024.7	4066.7	4112.5	4158.4	4157.7	4156.9	4105.8	4054.8	3924.5	3794.2
3675.6	20°	3749.3	3823.0	3924.2	4025.4	4079.1	4132.9	4115.0	4097.2	3961.9	3826.4
3395.1	22.5°	3487.2	3579.4	3728.2	3877.1	3988.5	4099.9	4123.2	4146.5	4008.2	3869.7
3169.4	25°	3266.0	3362.9	3543.7	3724.5	3893.6	4062.7	4136.3	4209.9	4074.3	3938.8
2993.6	27.5°	3088.8	3184.1	3384.4	3584.8	3808.7	4032.7	4164.4	4295.9	4166.6	4037.3
2873.9	30°	2962.3	3050.7	3259.5	3468.2	3744.0	4019.7	4215.8	4411.9	4287.0	4162.1
2856.6	32.5°	2926.1	2995.5	3191.7	3387.8	3699.8	4011.8	4280.3	4548.9	4425.2	4301.6
3103.0	35°	3119.2	3135.4	3271.6	3407.9	3732.9	4058.0	4386.6	4715.3	4596.9	4478.4
3761.6	37.5°	3687.6	3613.5	3622.4	3631.2	3926.7	4222.1	4608.8	4995.5	4844.5	4693.5
4808.5	40°	4628.5	4448.5	4293.4	4138.3	4358.1	4577.8	4998.3	5418.8	5198.8	4978.7
6223.9	42.5°	5896.5	5569.2	5230.9	4892.7	5019.3	5145.8	5563.1	5980.3	5662.7	5345.0
7972.1	45°	7434.0	6896.1	6354.1	5812.2	5868.1	5923.9	6298.9	6673.7	6245.2	5816.7
9927.0	47.5°	9139.6	8352.1	7570.5	6788.8	6800.1	6811.4	7176.2	7540.8	6937.8	6334.6
11874.4	50°	10834.9	9795.4	8787.9	7780.4	7778.5	7776.6	8226.9	8677.3	7768.2	6859.0
13759.9	52.5°	12473.9	11187.7	9984.3	8780.9	8836.1	8891.2	9436.5	9981.9	8640.5	7299.1
15608.5	55°	14075.2	12541.9	11202.6	9863.3	10078.2	10293.2	10832.0	11370.9	9413.9	7457.0
17363.1	57.5°	15626.5	13889.8	12537.4	11185.0	11616.1	12047.2	12340.8	12634.2	9962.0	7289.8
19516.9	60°	17657.5	15798.1	14518.3	13238.4	13773.9	14309.3	13853.4	13397.7	10099.0	6800.1
21262.8	62.5°	19493.8	17724.7	16552.2	15379.8	15440.3	15500.6	14255.3	13010.0	9522.2	6034.4
21444.7	65°	19729.4	18014.0	16523.9	15034.0	14802.8	14571.6	13402.8	12234.0	8706.2	5178.3
20184.6	67.5°	18461.8	16739.0	15186.7	13634.3	13526.0	13417.5	12305.9	11194.3	7735.0	4275.8
18201.9	70°	16719.4	15236.8	13848.7	12460.4	12411.8	12363.4	11154.2	9945.1	6675.4	3405.6
15694.2	72.5°	14583.9	13473.5	12387.4	11301.2	11266.5	11231.6	9844.0	8456.5	5526.6	2596.8
12956.8	75°	12175.1	11393.5	10548.5	9703.4	9574.5	9445.6	8009.5	6573.5	4209.8	1846.1
10140.4	77.5°	9585.9	9031.6	8389.2	7746.8	7562.3	7377.8	6037.1	4696.6	2946.5	1196.3
7340.4	80°	7049.4	6758.2	6273.3	5788.1	5558.8	5329.4	4201.7	3073.9	1898.4	722.8
4752.1	82.5°	4630.8	4509.3	4175.4	3841.4	3585.1	3329.0	2557.9	1786.9	1098.7	410.7
2727.0	85°	2658.0	2589.1	2314.8	2040.4	1822.5	1604.6	1195.4	786.2	494.2	202.4
1047.7	87.5°	1041.9	1036.0	898.8	761.6	640.0	518.5	380.9	243.4	161.9	80.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

105°		110°	115°	120°	125°	130°	135°	140°	145°	150°	155°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
3097.8	2.5°	3072.0	3046.0	3019.9	2995.0	2970.1	2946.0	2919.2	2897.4	2875.8	2856.2
3250.1	5°	3196.5	3142.5	3088.6	3038.3	2987.9	2940.4	2893.4	2852.4	2811.3	2776.9
3391.9	7.5°	3309.9	3230.1	3150.3	3080.0	3009.7	2944.9	2884.1	2829.5	2775.1	2729.8
3502.5	10°	3394.3	3297.4	3200.4	3117.3	3034.0	2953.9	2888.6	2831.1	2773.6	2728.3
3578.7	12.5°	3456.0	3341.6	3227.3	3133.2	3039.2	2955.1	2894.3	2847.2	2800.3	2770.2
3626.2	15°	3493.1	3361.5	3229.8	3120.9	3012.0	2918.8	2870.2	2847.6	2825.2	2829.3
3649.0	17.5°	3503.7	3350.9	3198.1	3067.1	2936.2	2826.6	2796.6	2804.9	2813.0	2862.4
3666.7	20°	3507.1	3321.9	3136.8	2974.4	2812.1	2684.5	2676.6	2715.1	2753.6	2839.3
3690.7	22.5°	3511.7	3286.4	3061.1	2865.6	2670.1	2524.9	2540.4	2597.4	2654.3	2752.1
3734.2	25°	3529.6	3251.3	2973.2	2744.2	2515.3	2366.4	2408.3	2474.0	2539.6	2627.6
3802.1	27.5°	3566.9	3227.9	2888.8	2633.1	2377.4	2241.9	2292.9	2356.2	2419.6	2492.0
3890.1	30°	3618.1	3216.9	2815.5	2540.3	2265.1	2151.4	2191.3	2241.6	2292.1	2352.1
3981.9	32.5°	3662.2	3203.3	2744.2	2460.3	2176.3	2084.6	2102.3	2132.1	2161.9	2209.8
4086.5	35°	3694.6	3177.7	2661.1	2381.6	2102.1	2025.7	2018.3	2026.5	2034.8	2071.3
4203.7	37.5°	3713.8	3133.9	2554.0	2289.0	2024.0	1957.2	1930.3	1921.2	1912.2	1938.4
4352.4	40°	3726.0	3073.6	2421.3	2178.5	1935.7	1875.1	1833.8	1813.3	1792.8	1811.8
4547.0	42.5°	3748.9	3011.3	2273.9	2056.6	1839.3	1783.5	1731.4	1704.2	1677.0	1692.4
4803.0	45°	3789.3	2953.5	2117.7	1927.1	1736.5	1679.9	1629.5	1603.0	1576.6	1589.5
5075.9	47.5°	3817.1	2905.7	1994.3	1824.7	1655.0	1582.0	1538.6	1516.4	1494.2	1506.5
5329.0	50°	3799.0	2853.6	1908.3	1756.6	1604.9	1508.9	1458.6	1438.9	1419.3	1438.3
5493.3	52.5°	3687.5	2765.7	1844.0	1711.8	1579.7	1469.3	1398.9	1379.4	1360.1	1388.7
5457.1	55°	3457.1	2619.9	1782.7	1679.3	1576.0	1473.3	1367.2	1336.4	1305.8	1346.4
5202.2	57.5°	3114.7	2414.3	1713.8	1640.8	1567.8	1477.3	1348.2	1303.4	1258.5	1302.2
4727.8	60°	2655.4	2147.4	1639.4	1582.0	1524.6	1464.8	1330.3	1272.2	1214.1	1252.4
4086.3	62.5°	2138.1	1827.9	1517.8	1479.6	1441.6	1434.2	1309.5	1236.8	1164.3	1188.6
3431.7	65°	1685.3	1540.5	1395.7	1377.7	1359.7	1360.7	1265.6	1188.4	1111.1	1120.4
2790.6	67.5°	1305.4	1264.3	1223.1	1233.2	1243.2	1240.7	1187.2	1122.9	1058.6	1055.7
2197.2	70°	988.8	1000.6	1012.2	1058.9	1105.4	1105.4	1087.8	1042.1	996.4	986.2
1679.8	72.5°	762.7	798.2	833.7	899.8	965.8	976.9	977.1	945.8	914.4	899.5
1219.2	75°	592.3	624.4	656.6	730.6	804.6	855.8	851.5	827.4	803.1	788.9
826.1	77.5°	456.0	477.8	499.8	571.7	643.5	727.9	725.6	706.3	686.9	672.4
532.3	80°	341.9	350.9	360.0	420.9	481.7	582.4	582.1	565.9	549.6	537.5
327.4	82.5°	244.3	245.9	247.7	292.5	337.3	423.4	428.1	420.2	412.3	403.7
175.0	85°	147.7	146.9	146.0	178.9	211.7	275.6	281.9	273.4	264.9	255.3
72.6	87.5°	64.7	64.0	63.2	76.5	90.0	116.6	124.5	121.1	117.7	115.9
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

160°		165°	170°	175°	180°	185°	190°	195°	200°	205°	210°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
2836.8	2.5°	2819.7	2802.6	2785.4	2768.3	2755.0	2741.7	2730.9	2720.2	2711.8	2703.4
2742.6	5°	2712.3	2681.9	2654.4	2626.8	2605.6	2584.3	2569.5	2554.7	2544.2	2533.6
2684.5	7.5°	2646.4	2608.1	2574.4	2540.8	2515.5	2490.4	2472.7	2455.1	2443.0	2431.0
2683.0	10°	2642.0	2600.8	2562.8	2524.9	2494.8	2464.6	2444.9	2425.0	2413.5	2402.1
2740.3	12.5°	2708.0	2675.8	2636.5	2597.4	2558.9	2520.4	2494.9	2469.4	2456.6	2444.0
2833.4	15°	2825.0	2816.6	2782.6	2748.5	2693.7	2638.9	2600.2	2561.5	2543.7	2526.0
2911.7	17.5°	2938.0	2964.1	2936.6	2909.2	2836.7	2764.1	2707.0	2650.0	2623.7	2597.4
2925.1	20°	2980.0	3034.9	3022.2	3009.4	2926.4	2843.6	2773.6	2703.8	2670.1	2636.4
2850.1	22.5°	2921.6	2993.0	3000.7	3008.3	2929.0	2849.8	2777.8	2705.7	2670.3	2634.7
2715.6	25°	2785.9	2856.2	2882.5	2908.7	2843.7	2778.8	2714.7	2650.9	2620.1	2589.4
2564.2	27.5°	2620.6	2676.9	2706.1	2735.5	2689.2	2643.0	2593.3	2543.6	2523.0	2502.3
2412.0	30°	2458.8	2505.7	2529.4	2553.2	2518.0	2482.7	2447.1	2411.4	2400.8	2390.2
2257.8	32.5°	2302.6	2347.5	2373.9	2400.4	2368.0	2335.5	2307.1	2278.7	2271.8	2264.9
2107.8	35°	2152.1	2196.6	2228.3	2260.0	2236.9	2214.0	2187.7	2161.5	2151.0	2140.6
1964.6	37.5°	2008.8	2053.2	2092.4	2131.5	2120.9	2110.3	2086.1	2061.9	2042.8	2023.8
1830.7	40°	1873.4	1916.2	1961.3	2006.5	2009.1	2011.6	1991.1	1970.6	1942.7	1915.1
1708.0	42.5°	1748.5	1789.1	1837.8	1886.5	1899.5	1912.5	1895.2	1878.0	1843.4	1808.9
1602.7	45°	1641.2	1679.7	1730.1	1780.6	1799.3	1818.0	1802.4	1786.9	1747.3	1708.0
1518.6	47.5°	1556.3	1593.8	1643.7	1693.5	1715.0	1736.5	1725.6	1714.7	1679.7	1644.6
1457.4	50°	1493.0	1528.4	1573.0	1617.6	1645.2	1672.9	1672.2	1671.7	1643.7	1615.6
1417.3	52.5°	1449.9	1482.3	1523.9	1565.5	1598.3	1631.0	1636.9	1642.7	1619.9	1597.0
1386.9	55°	1422.0	1457.1	1493.6	1529.9	1564.5	1599.3	1607.4	1615.6	1595.7	1575.7
1345.9	57.5°	1387.1	1428.3	1464.3	1500.5	1535.4	1570.3	1578.6	1586.8	1566.7	1546.5
1290.7	60°	1338.0	1385.3	1421.9	1458.6	1493.7	1528.8	1537.8	1546.9	1527.2	1507.6
1212.9	62.5°	1268.1	1323.3	1362.4	1401.4	1433.6	1465.7	1474.4	1483.1	1465.4	1447.6
1129.7	65°	1188.8	1248.0	1285.4	1322.7	1351.0	1379.3	1388.3	1397.1	1380.0	1362.9
1052.8	67.5°	1107.3	1162.0	1197.4	1232.7	1257.2	1281.6	1290.4	1299.0	1283.2	1267.6
976.0	70°	1024.0	1072.0	1102.6	1133.1	1155.2	1177.3	1185.6	1194.0	1181.2	1168.4
884.7	72.5°	922.5	960.2	987.8	1015.4	1037.0	1058.6	1068.6	1078.6	1067.9	1057.3
774.5	75°	802.6	830.7	855.7	880.7	900.4	920.1	930.5	940.9	935.7	930.5
657.9	77.5°	680.8	703.5	725.0	746.5	767.3	787.9	797.6	807.3	800.1	792.6
525.2	80°	544.3	563.2	581.3	599.4	615.1	630.7	643.7	656.6	653.4	650.3
395.1	82.5°	393.5	391.9	385.6	379.2	412.7	446.2	468.2	490.2	488.8	487.3
245.6	85°	237.5	229.2	211.7	194.1	225.5	257.0	284.1	311.3	309.0	306.8
114.1	87.5°	113.8	113.4	100.1	86.6	99.7	113.0	124.0	134.9	132.2	129.3
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

215°		220°	225°	230°	235°	240°	245°	250°	255°	260°	265°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
2695.7	2.5°	2687.9	2678.3	2687.9	2695.7	2703.4	2711.8	2720.2	2730.9	2741.7	2755.0
2525.6	5°	2517.6	2509.6	2517.6	2525.6	2533.6	2544.2	2554.7	2569.5	2584.3	2605.6
2423.7	7.5°	2416.6	2411.1	2416.6	2423.7	2431.0	2443.0	2455.1	2472.7	2490.4	2515.5
2396.0	10°	2389.9	2387.4	2389.9	2396.0	2402.1	2413.5	2425.0	2444.9	2464.6	2494.8
2438.8	12.5°	2433.6	2432.7	2433.6	2438.8	2444.0	2456.6	2469.4	2494.9	2520.4	2558.9
2519.2	15°	2512.5	2511.9	2512.5	2519.2	2526.0	2543.7	2561.5	2600.2	2638.9	2693.7
2588.8	17.5°	2580.0	2578.7	2580.0	2588.8	2597.4	2623.7	2650.0	2707.0	2764.1	2836.7
2625.7	20°	2614.9	2611.5	2614.9	2625.7	2636.4	2670.1	2703.8	2773.6	2843.6	2926.4
2622.8	22.5°	2610.9	2605.8	2610.9	2622.8	2634.7	2670.3	2705.7	2777.8	2849.8	2929.0
2578.2	25°	2567.1	2560.6	2567.1	2578.2	2589.4	2620.1	2650.9	2714.7	2778.8	2843.7
2497.2	27.5°	2492.1	2490.4	2492.1	2497.2	2502.3	2523.0	2543.6	2593.3	2643.0	2689.2
2390.2	30°	2390.2	2391.9	2390.2	2390.2	2390.2	2400.8	2411.4	2447.1	2482.7	2518.0
2265.8	32.5°	2266.8	2268.5	2266.8	2265.8	2264.9	2271.8	2278.7	2307.1	2335.5	2368.0
2138.3	35°	2136.1	2134.9	2136.1	2138.3	2140.6	2151.0	2161.5	2187.7	2214.0	2236.9
2013.7	37.5°	2003.6	1998.0	2003.6	2013.7	2023.8	2042.8	2061.9	2086.1	2110.3	2120.9
1896.3	40°	1877.7	1866.7	1877.7	1896.3	1915.1	1942.7	1970.6	1991.1	2011.6	2009.1
1781.6	42.5°	1754.4	1736.5	1754.4	1781.6	1808.9	1843.4	1878.0	1895.2	1912.5	1899.5
1675.9	45°	1643.9	1623.3	1643.9	1675.9	1708.0	1747.3	1786.9	1802.4	1818.0	1799.3
1614.9	47.5°	1585.4	1565.5	1585.4	1614.9	1644.6	1679.7	1714.7	1725.6	1736.5	1715.0
1588.2	50°	1560.8	1541.8	1560.8	1588.2	1615.6	1643.7	1671.7	1672.2	1672.9	1645.2
1572.5	52.5°	1548.0	1530.5	1548.0	1572.5	1597.0	1619.9	1642.7	1636.9	1631.0	1598.3
1554.2	55°	1532.7	1516.9	1532.7	1554.2	1575.7	1595.7	1615.6	1607.4	1599.3	1564.5
1525.2	57.5°	1503.9	1487.4	1503.9	1525.2	1546.5	1566.7	1586.8	1578.6	1570.3	1535.4
1485.6	60°	1463.7	1446.7	1463.7	1485.6	1507.6	1527.2	1546.9	1537.8	1528.8	1493.7
1424.5	62.5°	1401.4	1381.0	1401.4	1424.5	1447.6	1465.4	1483.1	1474.4	1465.7	1433.6
1340.5	65°	1318.2	1300.7	1318.2	1340.5	1362.9	1380.0	1397.1	1388.3	1379.3	1351.0
1246.8	67.5°	1225.9	1210.1	1225.9	1246.8	1267.6	1283.2	1299.0	1290.4	1281.6	1257.2
1148.5	70°	1128.6	1110.5	1128.6	1148.5	1168.4	1181.2	1194.0	1185.6	1177.3	1155.2
1038.3	72.5°	1019.4	1001.8	1019.4	1038.3	1057.3	1067.9	1078.6	1068.6	1058.6	1037.0
914.5	75°	898.6	881.8	898.6	914.5	930.5	935.7	940.9	930.5	920.1	900.4
776.5	77.5°	760.5	747.1	760.5	776.5	792.6	800.1	807.3	797.6	787.9	767.3
628.7	80°	607.0	581.8	607.0	628.7	650.3	653.4	656.6	643.7	630.7	615.1
469.1	82.5°	450.8	434.7	450.8	469.1	487.3	488.8	490.2	468.2	446.2	412.7
292.5	85°	278.2	263.8	278.2	292.5	306.8	309.0	311.3	284.1	257.0	225.5
122.0	87.5°	114.6	107.5	114.6	122.0	129.3	132.2	134.9	124.0	113.0	99.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

270°		275°	280°	285°	290°	295°	300°	305°	310°	315°	320°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
2768.3	2.5°	2785.4	2802.6	2819.7	2836.8	2856.2	2875.8	2897.4	2919.2	2946.0	2970.1
2626.8	5°	2654.4	2681.9	2712.3	2742.6	2776.9	2811.3	2852.4	2893.4	2940.4	2987.9
2540.8	7.5°	2574.4	2608.1	2646.4	2684.5	2729.8	2775.1	2829.5	2884.1	2944.9	3009.7
2524.9	10°	2562.8	2600.8	2642.0	2683.0	2728.3	2773.6	2831.1	2888.6	2953.9	3034.0
2597.4	12.5°	2636.5	2675.8	2708.0	2740.3	2770.2	2800.3	2847.2	2894.3	2955.1	3039.2
2748.5	15°	2782.6	2816.6	2825.0	2833.4	2829.3	2825.2	2847.6	2870.2	2918.8	3012.0
2909.2	17.5°	2936.6	2964.1	2938.0	2911.7	2862.4	2813.0	2804.9	2796.6	2826.6	2936.2
3009.4	20°	3022.2	3034.9	2980.0	2925.1	2839.3	2753.6	2715.1	2676.6	2684.5	2812.1
3008.3	22.5°	3000.7	2993.0	2921.6	2850.1	2752.1	2654.3	2597.4	2540.4	2524.9	2670.1
2908.7	25°	2882.5	2856.2	2785.9	2715.6	2627.6	2539.6	2474.0	2408.3	2366.4	2515.3
2735.5	27.5°	2706.1	2676.9	2620.6	2564.2	2492.0	2419.6	2356.2	2292.9	2241.9	2377.4
2553.2	30°	2529.4	2505.7	2458.8	2412.0	2352.1	2292.1	2241.6	2191.3	2151.4	2265.1
2400.4	32.5°	2373.9	2347.5	2302.6	2257.8	2209.8	2161.9	2132.1	2102.3	2084.6	2176.3
2260.0	35°	2228.3	2196.6	2152.1	2107.8	2071.3	2034.8	2026.5	2018.3	2025.7	2102.1
2131.5	37.5°	2092.4	2053.2	2008.8	1964.6	1938.4	1912.2	1921.2	1930.3	1957.2	2024.0
2006.5	40°	1961.3	1916.2	1873.4	1830.7	1811.8	1792.8	1813.3	1833.8	1875.1	1935.7
1886.5	42.5°	1837.8	1789.1	1748.5	1708.0	1692.4	1677.0	1704.2	1731.4	1783.5	1839.3
1780.6	45°	1730.1	1679.7	1641.2	1602.7	1589.5	1576.6	1603.0	1629.5	1679.9	1736.5
1693.5	47.5°	1643.7	1593.8	1556.3	1518.6	1506.5	1494.2	1516.4	1538.6	1582.0	1655.0
1617.6	50°	1573.0	1528.4	1493.0	1457.4	1438.3	1419.3	1438.9	1458.6	1508.9	1604.9
1565.5	52.5°	1523.9	1482.3	1449.9	1417.3	1388.7	1360.1	1379.4	1398.9	1469.3	1579.7
1529.9	55°	1493.6	1457.1	1422.0	1386.9	1346.4	1305.8	1336.4	1367.2	1473.3	1576.0
1500.5	57.5°	1464.3	1428.3	1387.1	1345.9	1302.2	1258.5	1303.4	1348.2	1477.3	1567.8
1458.6	60°	1421.9	1385.3	1338.0	1290.7	1252.4	1214.1	1272.2	1330.3	1464.8	1524.6
1401.4	62.5°	1362.4	1323.3	1268.1	1212.9	1188.6	1164.3	1236.8	1309.5	1434.2	1441.6
1322.7	65°	1285.4	1248.0	1188.8	1129.7	1120.4	1111.1	1188.4	1265.6	1360.7	1359.7
1232.7	67.5°	1197.4	1162.0	1107.3	1052.8	1055.7	1058.6	1122.9	1187.2	1240.7	1243.2
1133.1	70°	1102.6	1072.0	1024.0	976.0	986.2	996.4	1042.1	1087.8	1105.4	1105.4
1015.4	72.5°	987.8	960.2	922.5	884.7	899.5	914.4	945.8	977.1	976.9	965.8
880.7	75°	855.7	830.7	802.6	774.5	788.9	803.1	827.4	851.5	855.8	804.6
746.5	77.5°	725.0	703.5	680.8	657.9	672.4	686.9	706.3	725.6	727.9	643.5
599.4	80°	581.3	563.2	544.3	525.2	537.5	549.6	565.9	582.1	582.4	481.7
379.2	82.5°	385.6	391.9	393.5	395.1	403.7	412.3	420.2	428.1	423.4	337.3
194.1	85°	211.7	229.2	237.5	245.6	255.3	264.9	273.4	281.9	275.6	211.7
86.6	87.5°	100.1	113.4	113.8	114.1	115.9	117.7	121.1	124.5	116.6	90.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P947465  
 CATALOG NUMBER: GALN-SB2D-760-U-SLL

**CANDELA DISTRIBUTION (continued):**

325°		330°	335°	340°	345°	350°	355°	360°
2950.0	0°	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0	2950.0
2995.0	2.5°	3019.9	3046.0	3072.0	3097.8	3123.7	3148.1	3172.4
3038.3	5°	3088.6	3142.5	3196.5	3250.1	3303.7	3357.5	3411.3
3080.0	7.5°	3150.3	3230.1	3309.9	3391.9	3473.9	3562.5	3651.2
3117.3	10°	3200.4	3297.4	3394.3	3502.5	3610.8	3723.0	3835.2
3133.2	12.5°	3227.3	3341.6	3456.0	3578.7	3701.4	3824.5	3947.8
3120.9	15°	3229.8	3361.5	3493.1	3626.2	3759.3	3887.8	4016.3
3067.1	17.5°	3198.1	3350.9	3503.7	3649.0	3794.2	3924.5	4054.8
2974.4	20°	3136.8	3321.9	3507.1	3666.7	3826.4	3961.9	4097.2
2865.6	22.5°	3061.1	3286.4	3511.7	3690.7	3869.7	4008.2	4146.5
2744.2	25°	2973.2	3251.3	3529.6	3734.2	3938.8	4074.3	4209.9
2633.1	27.5°	2888.8	3227.9	3566.9	3802.1	4037.3	4166.6	4295.9
2540.3	30°	2815.5	3216.9	3618.1	3890.1	4162.1	4287.0	4411.9
2460.3	32.5°	2744.2	3203.3	3662.2	3981.9	4301.6	4425.2	4548.9
2381.6	35°	2661.1	3177.7	3694.6	4086.5	4478.4	4596.9	4715.3
2289.0	37.5°	2554.0	3133.9	3713.8	4203.7	4693.5	4844.5	4995.5
2178.5	40°	2421.3	3073.6	3726.0	4352.4	4978.7	5198.8	5418.8
2056.6	42.5°	2273.9	3011.3	3748.9	4547.0	5345.0	5662.7	5980.3
1927.1	45°	2117.7	2953.5	3789.3	4803.0	5816.7	6245.2	6673.7
1824.7	47.5°	1994.3	2905.7	3817.1	5075.9	6334.6	6937.8	7540.8
1756.6	50°	1908.3	2853.6	3799.0	5329.0	6859.0	7768.2	8677.3
1711.8	52.5°	1844.0	2765.7	3687.5	5493.3	7299.1	8640.5	9981.9
1679.3	55°	1782.7	2619.9	3457.1	5457.1	7457.0	9413.9	11370.9
1640.8	57.5°	1713.8	2414.3	3114.7	5202.2	7289.8	9962.0	12634.2
1582.0	60°	1639.4	2147.4	2655.4	4727.8	6800.1	10099.0	13397.7
1479.6	62.5°	1517.8	1827.9	2138.1	4086.3	6034.4	9522.2	13010.0
1377.7	65°	1395.7	1540.5	1685.3	3431.7	5178.3	8706.2	12234.0
1233.2	67.5°	1223.1	1264.3	1305.4	2790.6	4275.8	7735.0	11194.3
1058.9	70°	1012.2	1000.6	988.8	2197.2	3405.6	6675.4	9945.1
899.8	72.5°	833.7	798.2	762.7	1679.8	2596.8	5526.6	8456.5
730.6	75°	656.6	624.4	592.3	1219.2	1846.1	4209.8	6573.5
571.7	77.5°	499.8	477.8	456.0	826.1	1196.3	2946.5	4696.6
420.9	80°	360.0	350.9	341.9	532.3	722.8	1898.4	3073.9
292.5	82.5°	247.7	245.9	244.3	327.4	410.7	1098.7	1786.9
178.9	85°	146.0	146.9	147.7	175.0	202.4	494.2	786.2
76.5	87.5°	63.2	64.0	64.7	72.6	80.4	161.9	243.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)