

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P1434845

Luminaire Tested: **GALN-SB8C-827-U-T3LG**

Issue Date: 03/24/202

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.

Report Generated By 670245763



Test Information

Test Method: LM-79-08
 Report Number: P1434845
 Test Lab: INNOVATION CENTER(G1)
 Issue Date: 03/24/202
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: McGRAW-EDISON
 Catalog Number: GALN-SB8C-827-U-T3LG
 Description: GALLEON II AREA AND ROADWAY HIGH DENSITY LUMINAIRE 615mA 8xLight
 Square PACKAGE 80CRI 2700K FIXTURE w/ TYPE III LOW GLARE
 Light Source: (208) 2700K CCT, 80 CRI LEDS
 Ballast/Driver: ELECTRONIC DRIVER
 Luminaire Equipment:

| <u>Sample No.</u> | <u>Condition</u> | <u>Description</u> |
|-------------------|------------------|--------------------|
| a | good | reflector |
| b | good | lens |
| c | good | housing |
| d | good | cord |

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 51369 lumens
 Efficiency: N/A
 Efficacy: 128.5 lumens/watt
 Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')
 IES Classification: Type III - Short
 BUG Rating: B4 - U0 - G4

 Input Watts (W): 399.8
 Input Voltage (V): 120
 Input Current (A_{in}): NR
 Voltage Rise (V): NR
 Power Factor: 0.97
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 28.75 FT

REPORT NUMBER: P1434845
 CATALOG NUMBER: GALN-SB8C-827-U-T3LG

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 20 foot mounting height. Maximum calculated value = 29.4 fc
 Type III - Short - N/A

REPORT NUMBER: P1434845
CATALOG NUMBER: GALN-SB8C-827-U-T3LG

Luminous Intensity Polar Plot



— Vertical Plane Through 79-Deg Lateral - - - Horizontal Cone Through 53-Deg Vertical

REPORT NUMBER: P1434845
 CATALOG NUMBER: GALN-SB8C-827-U-T3LG

FLUX DISTRIBUTION:

| | | Downward | Upward | Total |
|--------------------|-----------|----------|--------|---------|
| House Side | Lumens | 12949.8 | 0.0 | 12949.8 |
| | % Fixture | 25.2 | 0.0 | 25.2 |
| Street Side | Lumens | 38419.3 | 0.0 | 38419.3 |
| | % Fixture | 74.8 | 0.0 | 74.8 |
| Total | Lumens | 51369.0 | 0.0 | 51369.0 |
| | % Fixture | 100.0 | 0.0 | 100.0 |

Coefficient of Utilization

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 718.5 | 1.4 |
| 10°-20° | 2225.1 | 4.3 |
| 20°-30° | 4254.2 | 8.3 |
| 30°-40° | 7304.1 | 14.2 |
| 40°-50° | 10230.8 | 19.9 |
| 50°-60° | 11610.6 | 22.6 |
| 60°-70° | 10181.8 | 19.8 |
| 70°-80° | 3981.3 | 7.8 |
| 80°-90° | 862.6 | 1.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-90° | 51369.0 | 100.0 |
| 0°-180° | 51369.0 | 100.0 |




REPORT NUMBER: P1434845
 CATALOG NUMBER: GALN-SB8C-827-U-T3LG

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

| Zone | Lumens | % Fixture | Zone Rating/Lumen Limit | | |
|----------------|---------|-----------|-------------------------|------|----------|
| | | | B | U | G |
| FL (0°-30°) | 4083.4 | 7.9 | | | |
| FM (30°-60°) | 22389.9 | 43.6 | | | |
| FH (60°-80°) | 11527.6 | 22.4 | | | G4/12000 |
| FVH (80°-90°) | 418.4 | 0.8 | | | G3/500 |
| BL (0°-30°) | 3114.5 | 6.1 | B4/5000 | | |
| BM (30°-60°) | 6755.6 | 13.2 | B4/8500 | | |
| BH (60°-80°) | 2635.5 | 5.1 | B4/5000 | | G4/5000 |
| BVH (80°-90°) | 444.2 | 0.9 | | | G3/500 |
| UL (90°-100°) | 0.0 | 0.0 | | U0/0 | |
| UH (100°-180°) | 0.0 | 0.0 | | U0/0 | |

BUG Rating: B4-U0-G4
 Type III Short





REPORT NUMBER: P1434845

CATALOG NUMBER: GALN-SB8C-827-U-T3LG

CANDELA DISTRIBUTION (FULL):

| | 0° | 5° | 15° | 25° | 35° | 45° | 55° | 65° | 75° | 79° | 85° |
|-------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|---------|
| 0° | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 |
| 2.5° | 7552.5 | 7552.5 | 7506.8 | 7552.5 | 7529.7 | 7564.0 | 7586.9 | 7586.9 | 7632.7 | 7621.2 | 7621.2 |
| 5° | 7426.7 | 7403.8 | 7392.3 | 7472.4 | 7518.2 | 7609.8 | 7712.8 | 7758.5 | 7838.6 | 7838.6 | 7850.1 |
| 7.5° | 7094.8 | 7083.4 | 7140.6 | 7300.8 | 7449.6 | 7678.4 | 7895.8 | 8021.7 | 8147.6 | 8170.5 | 8170.5 |
| 10° | 6888.8 | 6877.4 | 6946.1 | 7140.6 | 7380.9 | 7712.8 | 8056.1 | 8319.2 | 8525.2 | 8582.4 | 8582.4 |
| 12.5° | 6888.8 | 6888.8 | 6946.1 | 7140.6 | 7392.3 | 7792.9 | 8262.0 | 8708.3 | 9028.7 | 9097.4 | 9074.5 |
| 15° | 7083.4 | 7071.9 | 7140.6 | 7346.6 | 7586.9 | 7964.5 | 8536.7 | 9131.7 | 9566.6 | 9692.4 | 9703.9 |
| 17.5° | 7289.4 | 7277.9 | 7380.9 | 7644.1 | 7930.2 | 8307.8 | 8891.4 | 9623.8 | 10241.7 | 10401.9 | 10436.2 |
| 20° | 7609.8 | 7598.3 | 7724.2 | 7975.9 | 8330.7 | 8765.5 | 9372.0 | 10207.4 | 11065.6 | 11237.3 | 11283.0 |
| 22.5° | 7975.9 | 7987.4 | 8124.7 | 8433.7 | 8788.4 | 9360.6 | 10104.4 | 11031.3 | 12061.2 | 12324.4 | 12370.2 |
| 25° | 8742.6 | 8708.3 | 8822.8 | 9040.2 | 9417.8 | 10104.4 | 11019.9 | 12026.9 | 13251.3 | 13571.7 | 13628.9 |
| 27.5° | 9761.1 | 9703.9 | 9829.8 | 10047.2 | 10321.8 | 10962.6 | 12015.4 | 13136.9 | 14613.0 | 15013.6 | 15025.0 |
| 30° | 10676.6 | 10642.2 | 10813.9 | 11260.2 | 11546.2 | 12038.3 | 13159.7 | 14441.4 | 16295.2 | 16878.8 | 16901.7 |
| 32.5° | 11466.1 | 11454.7 | 11775.1 | 12347.3 | 12999.5 | 13525.9 | 14613.0 | 16089.2 | 18423.6 | 19098.8 | 18950.0 |
| 35° | 12221.4 | 12255.7 | 12656.2 | 13251.3 | 14121.0 | 15173.8 | 16272.3 | 17954.5 | 20666.5 | 21479.0 | 21238.7 |
| 37.5° | 12988.1 | 13011.0 | 13537.4 | 14304.1 | 15219.5 | 16592.7 | 18068.9 | 19979.9 | 22611.9 | 23618.9 | 23092.5 |
| 40° | 13697.6 | 13766.2 | 14475.7 | 15299.6 | 16489.7 | 17885.8 | 19533.6 | 21387.4 | 24110.9 | 25106.5 | 24534.3 |
| 42.5° | 14407.1 | 14510.0 | 15276.7 | 16409.6 | 17679.8 | 19133.1 | 20552.1 | 22245.7 | 25072.2 | 26182.2 | 25301.0 |
| 45° | 15139.4 | 15208.1 | 16157.9 | 17336.5 | 18778.4 | 20117.2 | 21135.7 | 22795.0 | 25735.9 | 26937.4 | 25735.9 |
| 47.5° | 15631.5 | 15768.8 | 16810.1 | 18171.9 | 19613.7 | 20872.5 | 21604.9 | 23023.8 | 26159.3 | 27429.5 | 25896.1 |
| 50° | 15826.0 | 16020.6 | 17142.0 | 18652.5 | 20300.3 | 21582.0 | 21971.1 | 23149.7 | 26628.5 | 27864.3 | 25861.8 |
| 52.5° | 15791.7 | 15974.8 | 17199.2 | 18869.9 | 20849.6 | 22234.2 | 22325.8 | 23287.0 | 26960.3 | 28013.1 | 25564.2 |
| 53° | 15608.6 | 15860.4 | 17233.5 | 18881.4 | 20929.7 | 22405.9 | 22486.0 | 23298.5 | 27006.1 | 28219.1 | 25518.5 |
| 55° | 14979.2 | 15116.5 | 16878.8 | 18869.9 | 21307.3 | 23046.7 | 22932.3 | 23641.8 | 27132.0 | 28081.7 | 25015.0 |
| 57.5° | 14407.1 | 14544.4 | 16077.8 | 18652.5 | 21616.3 | 23950.7 | 23653.2 | 23584.5 | 26445.4 | 27303.6 | 23744.8 |
| 60° | 14040.9 | 14086.6 | 15379.7 | 17965.9 | 21490.4 | 24580.1 | 24122.4 | 22909.4 | 24751.8 | 25461.2 | 21513.3 |
| 62.5° | 13731.9 | 13720.5 | 14864.8 | 16981.8 | 21009.8 | 24671.7 | 24213.9 | 21238.7 | 22268.6 | 22383.0 | 18538.1 |
| 65° | 13033.9 | 12953.8 | 14063.8 | 15871.8 | 20014.3 | 24259.7 | 23092.5 | 18709.7 | 18972.9 | 18595.3 | 14887.7 |
| 67.5° | 11649.2 | 11477.6 | 12461.7 | 14178.2 | 17988.8 | 23092.5 | 20952.6 | 15768.8 | 14956.3 | 14201.1 | 11214.4 |
| 70° | 8342.1 | 8342.1 | 9131.7 | 10848.2 | 14441.4 | 19957.0 | 17988.8 | 11935.3 | 10298.9 | 9623.8 | 7495.3 |
| 72.5° | 4085.2 | 4188.2 | 5012.1 | 6408.2 | 9681.0 | 14487.2 | 13777.7 | 7735.6 | 6248.0 | 5916.2 | 4806.2 |
| 75° | 1739.4 | 1750.8 | 2139.9 | 2837.9 | 4909.2 | 8571.0 | 8628.2 | 4462.9 | 4005.1 | 3844.9 | 3181.2 |
| 77.5° | 1213.0 | 1235.9 | 1407.5 | 1670.7 | 2334.4 | 3936.5 | 4485.8 | 2700.6 | 2689.2 | 2574.7 | 2265.8 |
| 80° | 926.9 | 949.8 | 1064.2 | 1247.3 | 1567.7 | 2014.0 | 2323.0 | 1830.9 | 1922.5 | 1808.0 | 1636.4 |
| 82.5° | 698.0 | 720.9 | 801.0 | 938.3 | 1121.4 | 1350.3 | 1304.5 | 1350.3 | 1419.0 | 1350.3 | 1178.7 |
| 85° | 469.2 | 480.6 | 537.8 | 652.3 | 720.9 | 812.5 | 812.5 | 984.1 | 1029.9 | 1007.0 | 926.9 |
| 87.5° | 240.3 | 240.3 | 286.1 | 343.3 | 366.2 | 377.6 | 331.9 | 434.8 | 492.1 | 537.8 | 434.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |



REPORT NUMBER: P1434845
 CATALOG NUMBER: GALN-SB8C-827-U-T3LG

CANDELA DISTRIBUTION (continued):

| | 90° | 95° | 105° | 115° | 125° | 135° | 145° | 155° | 165° | 175° | 180° |
|-------|---------|---------|---------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0° | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 | 7541.1 |
| 2.5° | 7621.2 | 7632.7 | 7598.3 | 7586.9 | 7575.4 | 7518.2 | 7518.2 | 7461.0 | 7449.6 | 7461.0 | 7426.7 |
| 5° | 7873.0 | 7850.1 | 7758.5 | 7689.9 | 7609.8 | 7449.6 | 7358.0 | 7232.1 | 7197.8 | 7163.5 | 7129.1 |
| 7.5° | 8181.9 | 8147.6 | 7987.4 | 7804.3 | 7586.9 | 7277.9 | 7106.3 | 6900.3 | 6831.6 | 6774.4 | 6751.5 |
| 10° | 8571.0 | 8502.3 | 8250.6 | 7861.5 | 7461.0 | 7083.4 | 6843.1 | 6591.3 | 6476.9 | 6454.0 | 6396.8 |
| 12.5° | 9074.5 | 8948.6 | 8479.5 | 7873.0 | 7346.6 | 6854.5 | 6591.3 | 6396.8 | 6351.0 | 6339.6 | 6282.3 |
| 15° | 9635.2 | 9452.1 | 8696.9 | 7884.4 | 7197.8 | 6660.0 | 6499.8 | 6396.8 | 6396.8 | 6385.3 | 6351.0 |
| 17.5° | 10321.8 | 10024.3 | 8902.9 | 7838.6 | 7014.7 | 6602.8 | 6522.7 | 6431.1 | 6408.2 | 6419.7 | 6373.9 |
| 20° | 11145.7 | 10653.7 | 9120.3 | 7781.4 | 6934.6 | 6614.2 | 6522.7 | 6396.8 | 6339.6 | 6328.1 | 6293.8 |
| 22.5° | 12095.5 | 11374.6 | 9360.6 | 7689.9 | 6934.6 | 6602.8 | 6454.0 | 6282.3 | 6167.9 | 6122.1 | 6076.4 |
| 25° | 13182.6 | 12210.0 | 9612.3 | 7655.5 | 6957.5 | 6557.0 | 6316.7 | 6042.0 | 5858.9 | 5790.3 | 5756.0 |
| 27.5° | 14498.6 | 13091.1 | 9795.4 | 7689.9 | 6946.1 | 6454.0 | 6076.4 | 5721.6 | 5515.6 | 5401.2 | 5378.3 |
| 30° | 15951.9 | 14040.9 | 9921.3 | 7747.1 | 6877.4 | 6259.5 | 5790.3 | 5389.8 | 5103.7 | 4966.4 | 4932.0 |
| 32.5° | 17668.4 | 15105.1 | 10047.2 | 7747.1 | 6705.7 | 5984.8 | 5458.4 | 5023.6 | 4726.1 | 4565.9 | 4543.0 |
| 35° | 19568.0 | 16409.6 | 10161.6 | 7735.6 | 6499.8 | 5687.3 | 5126.6 | 4680.3 | 4371.3 | 4211.1 | 4199.7 |
| 37.5° | 21181.5 | 17393.7 | 10218.8 | 7621.2 | 6213.7 | 5344.0 | 4817.6 | 4371.3 | 4050.9 | 3879.3 | 3867.8 |
| 40° | 22177.0 | 17805.7 | 10104.4 | 7392.3 | 5870.4 | 4989.3 | 4474.3 | 4062.4 | 3741.9 | 3536.0 | 3490.2 |
| 42.5° | 22554.7 | 17611.2 | 9738.2 | 7014.7 | 5458.4 | 4634.5 | 4188.2 | 3753.4 | 3330.0 | 3158.3 | 3124.0 |
| 45° | 22428.8 | 16855.9 | 8960.1 | 6476.9 | 5000.7 | 4314.1 | 3936.5 | 3444.4 | 3169.8 | 3021.0 | 3009.6 |
| 47.5° | 22005.4 | 15688.7 | 7987.4 | 5801.7 | 4520.1 | 4028.0 | 3604.6 | 3364.3 | 3112.6 | 2952.4 | 2940.9 |
| 50° | 21261.6 | 14441.4 | 6820.2 | 5035.0 | 4085.2 | 3730.5 | 3524.5 | 3330.0 | 3124.0 | 2998.1 | 2975.2 |
| 52.5° | 20311.8 | 13033.9 | 5744.5 | 4291.2 | 3707.6 | 3467.3 | 3444.4 | 3307.1 | 3146.9 | 3009.6 | 2952.4 |
| 53° | 20094.4 | 12667.7 | 5538.5 | 4165.3 | 3650.4 | 3433.0 | 3421.5 | 3307.1 | 3124.0 | 2998.1 | 2952.4 |
| 55° | 19053.0 | 11534.8 | 4886.3 | 3719.1 | 3364.3 | 3318.5 | 3421.5 | 3295.7 | 3066.8 | 2963.8 | 2929.5 |
| 57.5° | 17382.3 | 10047.2 | 4256.9 | 3307.1 | 3066.8 | 3181.2 | 3387.2 | 3249.9 | 2998.1 | 2815.0 | 2757.8 |
| 60° | 15368.3 | 8342.1 | 3776.3 | 3032.5 | 2849.4 | 3009.6 | 3249.9 | 3089.7 | 2746.4 | 2654.8 | 2643.4 |
| 62.5° | 12965.2 | 6751.5 | 3410.1 | 2803.6 | 2666.3 | 2826.5 | 3043.9 | 2769.3 | 2517.5 | 2448.9 | 2426.0 |
| 65° | 10127.3 | 5366.9 | 3124.0 | 2631.9 | 2483.2 | 2609.1 | 2757.8 | 2586.2 | 2426.0 | 2368.8 | 2357.3 |
| 67.5° | 7529.7 | 4211.1 | 2895.1 | 2483.2 | 2300.1 | 2380.2 | 2551.8 | 2506.1 | 2368.8 | 2334.4 | 2323.0 |
| 70° | 5195.2 | 3421.5 | 2689.2 | 2345.9 | 2071.2 | 2162.8 | 2426.0 | 2460.3 | 2323.0 | 2300.1 | 2288.7 |
| 72.5° | 3639.0 | 2895.1 | 2471.7 | 2197.1 | 1888.1 | 1979.7 | 2368.8 | 2368.8 | 2220.0 | 2254.3 | 2231.4 |
| 75° | 2734.9 | 2437.4 | 2220.0 | 2014.0 | 1659.3 | 1796.6 | 2288.7 | 2265.8 | 2117.0 | 2265.8 | 2208.5 |
| 77.5° | 2059.8 | 1968.2 | 1922.5 | 1785.1 | 1453.3 | 1590.6 | 2128.4 | 2082.7 | 1888.1 | 1899.6 | 1796.6 |
| 80° | 1499.1 | 1522.0 | 1647.8 | 1522.0 | 1213.0 | 1316.0 | 1796.6 | 1773.7 | 1533.4 | 1579.2 | 1453.3 |
| 82.5° | 1075.7 | 1132.9 | 1407.5 | 1224.4 | 881.1 | 938.3 | 1235.9 | 1338.9 | 1201.5 | 1132.9 | 1155.8 |
| 85° | 812.5 | 846.8 | 1132.9 | 904.0 | 549.3 | 617.9 | 846.8 | 961.2 | 938.3 | 869.7 | 881.1 |
| 87.5° | 343.3 | 389.1 | 526.4 | 423.4 | 320.4 | 320.4 | 526.4 | 675.2 | 606.5 | 514.9 | 537.8 |
| 90° | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 | 0.0 |

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



LM-79-2019: Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Report Prepared for

Cooper Lighting Solutions

McGraw-Edison

Report Number: SP1-2407-184-8

Test Date: 10/10/2024

Luminaire Tested: GSS-SB1A-827-U-5WQ

Data in this report applies to families of products including GSS-SB1A-827-U-5WQ

Test Information

Test Method: LM-79-2019
 Report Number: SP1-2407-184-8
 Test Lab: COOPER LIGHTING SOLUTIONS
 Photometer: SP1 - 76IN SPHERE
 Measurement Geometry: 4π
 Issue Date: 10/15/2024
 Manufacturer: COOPER LIGHTING SOLUTIONS
 Product Line: McGraw-Edison
 Catalog Number: **GSS-SB1A-827-U-5WQ**
 Description: GALLEON II SITE SLIM 1SQ 350MA 5WQ HIGH DENSITY LIGHTSQUARE WITH 80 CRI 2700K CCT 26 LEDS

Spectral Parameters

CCT (K): 2756
 CIE u': 0.2599
 CIE v': 0.5271
 Duv: 0.0006
 CIE x: 0.4563
 CIE y: 0.4112
 CIE z: 0.1325
 Peak Wavelength (nm): 609
 Dominant Wavelength (nm): 583
 Purity: 60.41121
 Rf: 82.2
 Rg: 99.9

| | | | |
|-----------|------|------|------|
| CRI (Ra): | 82.9 | | |
| R1: | 81.6 | R9: | 10.8 |
| R2: | 88.8 | R10: | 74.8 |
| R3: | 96.0 | R11: | 84.3 |
| R4: | 83.4 | R12: | 72.1 |
| R5: | 81.4 | R13: | 82.9 |
| R6: | 87.0 | R14: | 97.3 |
| R7: | 84.0 | R15: | 73.7 |
| R8: | 60.8 | | |



Test Conditions

Stabilization Time: 29M
 Operation Time: 1H 29M
 Sphere Temperature (°C): 25.2

REPORT NUMBER: SP1-2407-184-8

| Measurement and Test Equipment | | | |
|--------------------------------|-----------------------|------------------|----------------------|
| Instrument | Identification Number | Calibration Date | Calibration Due Date |
| Photometer | IN0058 | 6/18/2024 | 12/18/2024 |
| Power Meter | INXT2011004 | 2/8/2024 | 2/8/2025 |
| AC Power Source | IN0063 | 10/24/2023 | 10/24/2024 |
| DC Power Source | IN0208 | 10/24/2023 | 10/24/2024 |
| Sphere Thermometer | IN0085 | 10/24/2023 | 10/24/2024 |
| Room Thermometer | IN0046 | 10/24/2023 | 10/24/2024 |

REPORT NUMBER: SP1-2407-184-8

CIE 1931 Chromaticity Diagram



CIE 1931 Chromaticity Diagram with 2017 ANSI 7-Step and 4-Step Quadrangles



Point lies inside the ANSI 2700K 4-step quadrangle

REPORT NUMBER: SP1-2407-184-8

Photopic Flux vs. Wavelength



Photopic Lumens: NR

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 158 | NR | 620 | 959 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 211 | NR | 625 | 918 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 264 | NR | 630 | 873 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 318 | NR | 635 | 816 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 363 | NR | 640 | 755 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 403 | NR | 645 | 689 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 435 | NR | 650 | 626 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 459 | NR | 655 | 564 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 481 | NR | 660 | 503 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 501 | NR | 665 | 447 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 13 | NR | 540 | 519 | NR | 670 | 392 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 26 | NR | 545 | 542 | NR | 675 | 343 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 51 | NR | 550 | 565 | NR | 680 | 299 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 93 | NR | 555 | 593 | NR | 685 | 260 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 156 | NR | 560 | 624 | NR | 690 | 225 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 250 | NR | 565 | 662 | NR | 695 | 194 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 391 | NR | 570 | 707 | NR | 700 | 166 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 460 | NR | 575 | 756 | NR | 705 | 143 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 293 | NR | 580 | 810 | NR | 710 | 122 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 188 | NR | 585 | 860 | NR | 715 | 105 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 149 | NR | 590 | 910 | NR | 720 | 90 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 103 | NR | 595 | 950 | NR | 725 | 77 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 80 | NR | 600 | 980 | NR | 730 | 66 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 82 | NR | 605 | 995 | NR | 735 | 56 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 92 | NR | 610 | 998 | NR | 740 | 48 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 116 | NR | 615 | 985 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-184-8

Scotopic Flux vs. Wavelength



Scotopic Lumens: NR

S/P: 1.2

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 158 | NR | 620 | 959 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 211 | NR | 625 | 918 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 264 | NR | 630 | 873 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 318 | NR | 635 | 816 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 363 | NR | 640 | 755 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 403 | NR | 645 | 689 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 435 | NR | 650 | 626 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 459 | NR | 655 | 564 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 481 | NR | 660 | 503 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 501 | NR | 665 | 447 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 13 | NR | 540 | 519 | NR | 670 | 392 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 26 | NR | 545 | 542 | NR | 675 | 343 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 51 | NR | 550 | 565 | NR | 680 | 299 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 93 | NR | 555 | 593 | NR | 685 | 260 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 156 | NR | 560 | 624 | NR | 690 | 225 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 250 | NR | 565 | 662 | NR | 695 | 194 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 391 | NR | 570 | 707 | NR | 700 | 166 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 460 | NR | 575 | 756 | NR | 705 | 143 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 293 | NR | 580 | 810 | NR | 710 | 122 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 188 | NR | 585 | 860 | NR | 715 | 105 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 149 | NR | 590 | 910 | NR | 720 | 90 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 103 | NR | 595 | 950 | NR | 725 | 77 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 80 | NR | 600 | 980 | NR | 730 | 66 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 82 | NR | 605 | 995 | NR | 735 | 56 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 92 | NR | 610 | 998 | NR | 740 | 48 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 116 | NR | 615 | 985 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

REPORT NUMBER: SP1-2407-184-8

Melanopic Flux vs. Wavelength



Melanopic Lumens: NR

M/P: 2.16

| λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) | λ (nm) | Power W [^] /nm | Lumens (ϕ /nm) |
|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|-------------------|-----------------------------|-------------------------|
| 360 | 0 | NR | 490 | 158 | NR | 620 | 959 | NR | 750 | 35 | NR | 880 | 1 | NR |
| 365 | 0 | NR | 495 | 211 | NR | 625 | 918 | NR | 755 | 30 | NR | 885 | 1 | NR |
| 370 | 0 | NR | 500 | 264 | NR | 630 | 873 | NR | 760 | 26 | NR | 890 | 1 | NR |
| 375 | 0 | NR | 505 | 318 | NR | 635 | 816 | NR | 765 | 22 | NR | 895 | 1 | NR |
| 380 | 0 | NR | 510 | 363 | NR | 640 | 755 | NR | 770 | 19 | NR | 900 | 1 | NR |
| 385 | 0 | NR | 515 | 403 | NR | 645 | 689 | NR | 775 | 16 | NR | 905 | 1 | NR |
| 390 | 0 | NR | 520 | 435 | NR | 650 | 626 | NR | 780 | 14 | NR | 910 | 0 | NR |
| 395 | 1 | NR | 525 | 459 | NR | 655 | 564 | NR | 785 | 12 | NR | 915 | 0 | NR |
| 400 | 3 | NR | 530 | 481 | NR | 660 | 503 | NR | 790 | 10 | NR | 920 | 0 | NR |
| 405 | 6 | NR | 535 | 501 | NR | 665 | 447 | NR | 795 | 9 | NR | 925 | 0 | NR |
| 410 | 13 | NR | 540 | 519 | NR | 670 | 392 | NR | 800 | 8 | NR | 930 | 0 | NR |
| 415 | 26 | NR | 545 | 542 | NR | 675 | 343 | NR | 805 | 7 | NR | 935 | 0 | NR |
| 420 | 51 | NR | 550 | 565 | NR | 680 | 299 | NR | 810 | 6 | NR | 940 | 0 | NR |
| 425 | 93 | NR | 555 | 593 | NR | 685 | 260 | NR | 815 | 5 | NR | 945 | 0 | NR |
| 430 | 156 | NR | 560 | 624 | NR | 690 | 225 | NR | 820 | 4 | NR | 950 | 0 | NR |
| 435 | 250 | NR | 565 | 662 | NR | 695 | 194 | NR | 825 | 4 | NR | 955 | 0 | NR |
| 440 | 391 | NR | 570 | 707 | NR | 700 | 166 | NR | 830 | 3 | NR | 960 | 0 | NR |
| 445 | 460 | NR | 575 | 756 | NR | 705 | 143 | NR | 835 | 3 | NR | 965 | 0 | NR |
| 450 | 293 | NR | 580 | 810 | NR | 710 | 122 | NR | 840 | 2 | NR | 970 | 0 | NR |
| 455 | 188 | NR | 585 | 860 | NR | 715 | 105 | NR | 845 | 2 | NR | 975 | 0 | NR |
| 460 | 149 | NR | 590 | 910 | NR | 720 | 90 | NR | 850 | 2 | NR | 980 | 0 | NR |
| 465 | 103 | NR | 595 | 950 | NR | 725 | 77 | NR | 855 | 2 | NR | 985 | 0 | NR |
| 470 | 80 | NR | 600 | 980 | NR | 730 | 66 | NR | 860 | 1 | NR | 990 | 0 | NR |
| 475 | 82 | NR | 605 | 995 | NR | 735 | 56 | NR | 865 | 1 | NR | 995 | 0 | NR |
| 480 | 92 | NR | 610 | 998 | NR | 740 | 48 | NR | 870 | 1 | NR | 1000 | 0 | NR |
| 485 | 116 | NR | 615 | 985 | NR | 745 | 41 | NR | 875 | 1 | NR | | | |

Summary

$R_f = 82.2$
 $R_g = 99.9$
 $CIE R_a = 82.9$
 $R_9 = 10.8$



Color Vector Graphics



Individual Sample Fidelity Index ($R_{f,i}$)

| | | | |
|------------|------------|------------|------------|
| CES01 = 86 | CES26 = 76 | CES51 = 89 | CES76 = 75 |
| CES02 = 63 | CES27 = 89 | CES52 = 91 | CES77 = 87 |
| CES03 = 31 | CES28 = 90 | CES53 = 82 | CES78 = 76 |
| CES04 = 71 | CES29 = 68 | CES54 = 88 | CES79 = 91 |
| CES05 = 50 | CES30 = 69 | CES55 = 87 | CES80 = 90 |
| CES06 = 52 | CES31 = 72 | CES56 = 80 | CES81 = 74 |
| CES07 = 43 | CES32 = 71 | CES57 = 78 | CES82 = 95 |
| CES08 = 42 | CES33 = 71 | CES58 = 80 | CES83 = 90 |
| CES09 = 29 | CES34 = 84 | CES59 = 93 | CES84 = 94 |
| CES10 = 77 | CES35 = 92 | CES60 = 96 | CES85 = 83 |
| CES11 = 59 | CES36 = 92 | CES61 = 94 | CES86 = 69 |
| CES12 = 66 | CES37 = 89 | CES62 = 84 | CES87 = 85 |
| CES13 = 44 | CES38 = 75 | CES63 = 79 | CES88 = 84 |
| CES14 = 74 | CES39 = 93 | CES64 = 85 | CES89 = 74 |
| CES15 = 72 | CES40 = 89 | CES65 = 79 | CES90 = 81 |
| CES16 = 48 | CES41 = 85 | CES66 = 83 | CES91 = 96 |
| CES17 = 50 | CES42 = 88 | CES67 = 82 | CES92 = 72 |
| CES18 = 57 | CES43 = 81 | CES68 = 86 | CES93 = 84 |
| CES19 = 73 | CES44 = 98 | CES69 = 92 | CES94 = 63 |
| CES20 = 67 | CES45 = 87 | CES70 = 81 | CES95 = 80 |
| CES21 = 87 | CES46 = 82 | CES71 = 81 | CES96 = 85 |
| CES22 = 79 | CES47 = 76 | CES72 = 93 | CES97 = 87 |
| CES23 = 92 | CES48 = 71 | CES73 = 75 | CES98 = 82 |
| CES24 = 91 | CES49 = 81 | CES74 = 91 | CES99 = 76 |
| CES25 = 72 | CES50 = 88 | CES75 = 79 | |



Color Rendition by Hue-Angle Bin



Measure Comparisons



(END OF REPORT)