

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P940842

Luminaire Tested: **GALN-SB4A-835-U-SL4**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P940842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB4A-835-U-SL4
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(4) 80 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL
LIGHT ELIMINATOR OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16530 lumens
Efficiency: N/A
Efficacy: 145.0 lumens/watt
Luminous Opening: Rectangular (W 1' x L: 1' x H: 0')
IES Classification: Type IV - Medium
BUG Rating: B3 - U0 - G3


Input Watts (W): 114
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P940842
 CATALOG NUMBER: GALN-SB4A-835-U-SL4

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 3.9 fc
 Type IV - Medium - N/A

REPORT NUMBER: P940842
CATALOG NUMBER: GALN-SB4A-835-U-SL4

Luminous Intensity Polar Plot



REPORT NUMBER: P940842

CATALOG NUMBER: GALN-SB4A-835-U-SL4

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	5121.6	0.0	5121.6
	% Fixture	31.0	0.0	31.0
Street Side	Lumens	11408.5	0.0	11408.5
	% Fixture	69.0	0.0	69.0
Total	Lumens	16530.0	0.0	16530.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.7	1.1
10°-20°	633.5	3.8
20°-30°	1156.7	7.0
30°-40°	1640.5	9.9
40°-50°	2215.2	13.4
50°-60°	2980.0	18.0
60°-70°	3782.3	22.9
70°-80°	3432.7	20.8
80°-90°	500.4	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	16530.0	100.0
0°-180°	16530.0	100.0

Coefficient of Utilization



REPORT NUMBER: P940842


CATALOG NUMBER: GALN-SB4A-835-U-SL4

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	869.5	5.3			
FM (30°-60°)	4057.7	24.5			
FH (60°-80°)	6049.7	36.6			G3/7500
FVH (80°-90°)	431.5	2.6			G3/500
BL (0°-30°)	1109.4	6.7	B3/2500		
BM (30°-60°)	2778.0	16.8	B3/5000		
BH (60°-80°)	1165.3	7.0	B3/2500		G3/2500
BVH (80°-90°)	68.9	0.4			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B3-U0-G3

Type IV Medium



REPORT NUMBER: P940842

CATALOG NUMBER: GALN-SB4A-835-U-SL4

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°
0°	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2
2.5°	1861.3	1871.8	1869.2	1865.7	1865.7	1866.6	1865.7	1871.8	1878.0	1884.1
5°	1880.6	1891.1	1885.8	1881.5	1878.0	1877.1	1874.4	1873.6	1877.1	1885.0
7.5°	1918.3	1928.8	1920.9	1913.0	1906.0	1902.5	1899.0	1893.7	1891.1	1895.5
10°	1960.4	1970.9	1961.2	1947.2	1935.8	1931.4	1927.9	1922.7	1919.2	1921.8
12.5°	2002.4	2013.0	1999.8	1980.5	1965.6	1963.0	1958.6	1956.9	1956.0	1955.1
15°	2041.9	2050.7	2034.0	2011.2	1995.4	1991.1	1986.7	1989.3	1993.7	1998.9
17.5°	2072.6	2081.4	2056.8	2027.0	2012.1	2010.3	2007.7	2016.5	2028.8	2041.9
20°	2100.6	2109.4	2077.8	2037.5	2020.0	2020.0	2020.9	2039.3	2056.8	2076.1
22.5°	2140.1	2147.1	2108.5	2053.3	2027.9	2029.6	2036.6	2055.1	2077.0	2103.3
25°	2198.8	2204.1	2156.8	2083.1	2054.2	2059.4	2065.6	2074.3	2095.4	2126.1
27.5°	2293.5	2297.9	2235.7	2135.7	2091.9	2100.6	2109.4	2103.3	2112.9	2139.2
30°	2426.8	2429.4	2350.5	2218.1	2155.9	2160.3	2162.0	2136.6	2118.2	2139.2
32.5°	2584.6	2583.7	2489.9	2318.1	2228.6	2224.3	2209.4	2159.4	2116.4	2134.8
35°	2829.2	2819.6	2698.6	2458.3	2311.1	2283.9	2248.8	2184.8	2125.2	2130.5
37.5°	3234.3	3204.4	3037.0	2688.1	2433.8	2364.5	2312.8	2226.0	2144.5	2128.7
40°	3691.0	3653.3	3469.2	3002.8	2617.9	2506.6	2423.3	2284.8	2176.0	2136.6
42.5°	4232.8	4179.4	3981.2	3373.7	2851.1	2689.8	2564.4	2359.3	2222.5	2162.0
45°	4898.3	4827.3	4546.7	3791.9	3144.8	2930.0	2762.6	2472.4	2293.5	2211.1
47.5°	5570.7	5588.3	5189.4	4270.5	3497.3	3226.4	3010.7	2642.5	2397.0	2290.0
50°	6285.3	6297.5	5828.5	4801.0	3897.1	3561.3	3289.5	2832.7	2540.8	2402.2
52.5°	6842.9	6844.6	6408.9	5355.9	4313.5	3929.5	3590.2	3050.1	2707.3	2551.3
55°	7191.8	7187.4	6815.7	5881.1	4792.2	4316.1	3923.4	3297.4	2910.7	2726.6
57.5°	7445.2	7432.0	7096.2	6332.6	5302.5	4772.9	4300.4	3577.9	3151.0	2935.3
60°	7541.6	7533.7	7286.5	6722.8	5839.0	5277.9	4735.2	3891.8	3423.6	3181.6
62.5°	7578.4	7593.3	7473.2	7100.6	6413.3	5837.3	5213.0	4267.0	3730.5	3460.4
65°	7708.2	7735.4	7710.8	7595.1	7062.1	6492.2	5846.9	4713.3	4065.4	3759.4
67.5°	7965.1	7992.3	8002.8	8186.9	7854.6	7308.4	6637.7	5269.1	4457.3	4069.8
70°	7958.9	7951.1	8136.9	8657.7	8847.1	8438.5	7703.8	5953.0	4924.6	4327.5
72.5°	7244.4	7181.3	7620.5	8652.4	9673.0	9618.6	9005.8	6835.0	5327.9	4359.1
75°	5434.8	5266.5	6042.4	7797.6	9810.6	10288.4	9833.4	7382.1	5232.3	3851.5
77.5°	2324.2	2155.0	3069.4	5772.4	8780.4	9617.7	9074.1	6440.5	4176.7	2546.9
80°	608.4	607.6	927.6	2617.0	5971.4	7102.4	6230.9	4159.2	2386.5	910.0
82.5°	251.6	245.5	341.0	1017.9	2917.8	3985.6	3252.7	1855.2	861.8	246.4
85°	93.8	92.9	165.7	351.6	1029.3	1643.9	1189.7	474.3	214.8	120.1
87.5°	26.3	25.4	35.9	121.9	250.7	380.5	203.4	78.0	60.5	47.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P940842
 CATALOG NUMBER: GALN-SB4A-835-U-SL4

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
1890.2	0°	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2	1890.2
1893.7	2.5°	1896.4	1900.7	1908.6	1914.8	1922.7	1931.4	1943.7	1951.6	1959.5	1964.7
1898.1	5°	1904.3	1913.9	1934.1	1954.2	1977.9	1999.8	2025.2	2043.7	2058.6	2062.9
1913.9	7.5°	1921.8	1937.6	1971.8	2006.0	2043.7	2079.6	2116.4	2148.0	2173.4	2183.1
1942.0	10°	1952.5	1973.5	2021.7	2070.0	2119.9	2175.2	2222.5	2268.1	2304.0	2318.9
1975.3	12.5°	1991.1	2017.4	2080.5	2147.1	2216.4	2292.6	2354.0	2410.1	2454.8	2475.0
2021.7	15°	2041.0	2075.2	2155.9	2245.3	2347.0	2453.1	2531.1	2593.4	2643.3	2667.9
2070.0	17.5°	2095.4	2141.0	2242.7	2377.7	2523.2	2662.6	2753.8	2799.4	2851.1	2874.8
2114.7	20°	2148.0	2204.1	2349.6	2546.0	2739.8	2887.9	2961.6	2973.9	2977.4	2980.0
2156.8	22.5°	2202.3	2277.7	2483.8	2758.2	2966.0	3068.6	3079.1	3026.5	2952.8	2918.6
2198.0	25°	2262.0	2361.9	2659.1	2992.3	3160.6	3172.9	3092.2	2964.2	2824.8	2760.8
2231.3	27.5°	2319.8	2459.2	2869.5	3215.8	3300.9	3193.0	3019.5	2838.0	2669.6	2602.1
2254.9	30°	2377.7	2570.6	3101.9	3411.4	3364.9	3143.1	2904.6	2702.1	2532.9	2461.9
2276.0	32.5°	2436.4	2700.3	3369.3	3552.5	3353.5	3037.0	2761.7	2549.5	2400.5	2326.0
2294.4	35°	2503.1	2859.9	3622.6	3629.7	3277.2	2880.9	2573.2	2367.2	2237.4	2177.8
2316.3	37.5°	2589.9	3062.4	3846.2	3648.9	3143.9	2652.1	2339.1	2151.5	2044.5	2017.4
2348.8	40°	2697.7	3306.1	4017.2	3618.3	2946.7	2374.2	2083.1	1933.2	1872.7	1878.8
2392.6	42.5°	2838.0	3578.8	4137.3	3539.4	2672.3	2087.5	1858.7	1792.0	1821.0	1845.5
2458.3	45°	3020.3	3862.0	4211.8	3405.2	2361.9	1844.6	1726.3	1742.1	1764.0	1766.6
2564.4	47.5°	3253.5	4148.7	4260.9	3202.7	2045.4	1673.7	1642.1	1645.6	1641.2	1622.8
2723.1	50°	3544.6	4427.5	4304.7	2934.4	1776.3	1566.7	1524.6	1512.4	1451.9	1392.2
2934.4	52.5°	3876.0	4683.5	4323.2	2601.3	1566.7	1477.3	1408.9	1331.8	1218.7	1200.2
3200.1	55°	4244.2	4920.2	4275.8	2191.8	1390.5	1362.4	1259.0	1166.0	1153.8	1138.0
3549.9	57.5°	4684.4	5175.3	4179.4	1735.0	1209.9	1228.3	1127.5	1138.0	1116.1	1091.5
3999.6	60°	5165.7	5439.2	4010.2	1318.6	1023.1	1060.8	1093.3	1092.4	1086.3	1066.1
4473.9	62.5°	5598.8	5612.8	3677.0	1010.0	859.2	931.1	1019.6	1018.8	1013.5	1002.1
4969.3	65°	5856.5	5586.5	3121.2	795.2	724.2	824.1	919.7	926.7	927.6	926.7
5341.9	67.5°	5811.0	5278.8	2358.4	633.0	612.8	715.4	820.6	830.3	837.3	839.0
5389.3	70°	5295.4	4602.8	1537.8	505.0	513.8	619.8	726.8	736.5	742.6	749.6
4676.5	72.5°	4127.6	3384.2	880.2	408.6	427.0	537.4	633.9	645.3	648.8	661.9
3254.4	75°	2515.3	1990.2	475.2	321.8	350.7	459.4	541.8	555.0	561.1	576.9
1598.3	77.5°	1195.9	861.8	270.9	250.7	282.3	375.2	457.7	472.6	455.9	464.7
441.0	80°	404.2	320.0	171.0	191.1	215.7	292.8	366.5	381.4	346.3	344.6
146.4	82.5°	141.2	129.8	108.7	127.1	139.4	209.5	277.0	296.3	257.8	256.9
65.8	85°	55.2	52.6	60.5	69.3	83.3	128.9	182.4	192.0	158.7	128.0
19.3	87.5°	11.4	12.3	14.9	15.8	25.4	44.7	65.8	80.7	64.0	54.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
1890.2
1961.2
2064.7
2183.9
2319.8
2475.0
2666.1
2873.9
2987.0
2928.3
2770.5
2610.0
2469.7
2335.6
2190.9
2036.6
1899.9
1868.3
1784.1
1636.9
1400.1
1206.4
1140.6
1087.1
1059.1
997.7
926.7
840.8
753.1
667.2
578.6
457.7
341.0
244.6
126.2
50.0
0.0

F REPORT)