

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P942207

Luminaire Tested: **GALN-SB6A-835-U-T3**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P942207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SB6A-835-U-T3  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(6) 80 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE III OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 25248 lumens  
Efficiency: N/A  
Efficacy: 147.7 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1' x H: 0')  
IES Classification: Type III - Short  
BUG Rating: B3 - U0 - G3  
  
Input Watts (W): 170.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P942207  
 CATALOG NUMBER: GALN-SB6A-835-U-T3

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 6.3 fc  
 Type III - Short - N/A

REPORT NUMBER: P942207  
CATALOG NUMBER: GALN-SB6A-835-U-T3

### Luminous Intensity Polar Plot



REPORT NUMBER: P942207

CATALOG NUMBER: GALN-SB6A-835-U-T3

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	6277.8	0.0	6277.8
	% Fixture	24.9	0.0	24.9
<b>Street Side</b>	Lumens	18970.2	0.0	18970.2
	% Fixture	75.1	0.0	75.1
<b>Total</b>	Lumens	25248.0	0.0	25248.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	277.6	1.1
10°-20°	917.3	3.6
20°-30°	1768.0	7.0
30°-40°	3100.0	12.3
40°-50°	4608.7	18.3
50°-60°	5842.0	23.1
60°-70°	5716.2	22.6
70°-80°	2726.7	10.8
80°-90°	291.4	1.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	25248.0	100.0
0°-180°	25248.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P942207


CATALOG NUMBER: GALN-SB6A-835-U-T3

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	1595.4	6.3			
FM (30°-60°)	10346.4	41.0			
FH (60°-80°)	6863.1	27.2			G3/7500
FVH (80°-90°)	165.2	0.7			G2/225
BL (0°-30°)	1367.5	5.4	B3/2500		
BM (30°-60°)	3204.3	12.7	B3/5000		
BH (60°-80°)	1579.8	6.3	B3/2500		G3/2500
BVH (80°-90°)	126.2	0.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G3**

Type III Short



REPORT NUMBER: P942207

CATALOG NUMBER: GALN-SB6A-835-U-T3

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	66°	75°
0°	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3
2.5°	2771.2	2787.1	2783.1	2776.5	2775.1	2777.8	2781.8	2785.7	2784.4	2791.1
5°	2763.2	2779.1	2777.8	2777.8	2783.1	2793.7	2800.3	2807.0	2800.3	2808.3
7.5°	2768.5	2780.4	2785.7	2791.1	2804.3	2824.2	2840.1	2854.7	2846.8	2856.1
10°	2836.2	2845.4	2850.7	2850.7	2860.0	2882.6	2898.5	2925.0	2918.4	2933.0
12.5°	2959.5	2968.8	2968.8	2963.5	2970.1	2984.7	2990.0	3019.2	3007.3	3031.2
15°	3110.7	3129.3	3114.7	3105.4	3108.1	3122.7	3121.4	3143.9	3132.0	3151.9
17.5°	3277.9	3301.8	3277.9	3276.6	3271.3	3287.2	3288.5	3308.4	3287.2	3301.8
20°	3475.5	3508.7	3488.8	3495.4	3483.5	3490.1	3496.8	3526.0	3492.8	3503.4
22.5°	3754.1	3793.9	3772.7	3797.9	3789.9	3784.6	3783.3	3835.0	3783.3	3787.3
25°	4160.0	4207.8	4170.7	4205.1	4205.1	4222.4	4242.3	4308.6	4222.4	4197.2
27.5°	4759.6	4807.4	4734.4	4755.7	4749.0	4791.5	4770.3	4934.7	4841.9	4800.8
30°	5481.3	5566.2	5428.2	5422.9	5416.3	5483.9	5514.4	5623.2	5529.0	5487.9
32.5°	6261.3	6350.2	6185.7	6137.9	6112.7	6153.8	6128.6	6216.2	6151.2	6087.5
35°	7086.4	7174.0	7017.4	6924.6	6823.7	6737.5	6647.3	6669.9	6608.8	6512.0
37.5°	7866.4	8026.9	7861.1	7761.6	7575.9	7407.4	7155.4	7050.6	6993.5	6904.7
40°	8661.0	8752.5	8626.5	8541.6	8340.0	8076.0	7672.7	7451.2	7374.3	7288.0
42.5°	9246.0	9333.6	9265.9	9207.6	9049.7	8743.3	8221.9	7944.7	7833.2	7736.4
45°	9710.3	9775.3	9732.9	9754.1	9686.4	9389.3	8791.0	8474.0	8358.6	8240.5
47.5°	9897.4	9966.3	10034.0	10160.0	10275.4	10056.5	9402.6	9047.0	8925.0	8804.3
50°	9876.1	9946.4	10142.8	10410.7	10768.9	10695.9	10047.3	9657.2	9544.5	9406.5
52.5°	9706.3	9785.9	10038.0	10483.7	11054.1	11174.8	10703.9	10287.4	10181.2	10016.7
55°	9260.6	9308.4	9686.4	10317.9	11121.8	11509.1	11347.3	10958.6	10852.5	10623.0
57.5°	8434.2	8503.2	9053.7	9870.8	10952.0	11735.9	11912.4	11664.3	11562.2	11231.9
60°	7355.7	7465.8	8095.9	9120.0	10519.5	11734.6	12425.7	12358.1	12273.2	11831.5
62.5°	6135.3	6262.6	6868.9	8058.8	9763.4	11401.7	12746.8	12939.1	12895.3	12384.6
65°	4711.9	4799.4	5403.0	6685.8	8586.7	10686.6	12783.9	13335.8	13343.7	12805.1
67.5°	3137.3	3389.3	3913.3	5017.0	7010.8	9518.0	12457.6	13400.8	13477.7	12949.7
70°	1530.8	1862.5	2375.8	3260.6	5017.0	7725.8	11604.6	12867.5	13038.6	12527.9
72.5°	635.4	742.9	1022.8	1609.1	2879.9	5213.3	9890.7	11421.6	11738.6	11100.5
75°	428.5	464.3	585.0	825.1	1312.0	2570.8	7132.8	8516.4	9027.1	8383.8
77.5°	330.3	352.9	425.8	577.0	780.0	972.4	3817.8	5132.4	5396.4	4995.8
80°	260.0	277.2	318.4	420.5	553.2	520.0	1301.3	2325.4	2478.0	2078.7
82.5°	225.5	232.1	228.2	285.2	367.5	303.8	427.1	858.3	947.2	687.2
85°	163.2	181.7	189.7	176.4	195.0	153.9	175.1	303.8	334.3	298.5
87.5°	66.3	98.2	120.7	114.1	71.6	43.8	54.4	88.9	102.1	111.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P942207  
 CATALOG NUMBER: GALN-SB6A-835-U-T3

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
2800.3	0°	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3	2800.3
2801.7	2.5°	2803.0	2812.3	2818.9	2826.9	2832.2	2840.1	2856.1	2865.3	2866.7	2873.3
2822.9	5°	2828.2	2841.5	2856.1	2877.3	2901.2	2921.1	2951.6	2972.8	2980.7	2987.4
2874.6	7.5°	2882.6	2901.2	2927.7	2964.8	2999.3	3025.8	3063.0	3088.2	3113.4	3122.7
2956.9	10°	2963.5	2990.0	3028.5	3078.9	3116.1	3150.5	3189.0	3210.2	3235.4	3246.1
3055.0	12.5°	3064.3	3092.2	3142.6	3212.9	3247.4	3271.3	3284.5	3279.2	3284.5	3293.8
3173.1	15°	3179.7	3210.2	3267.3	3342.9	3366.8	3345.5	3316.4	3289.8	3285.9	3288.5
3316.4	17.5°	3316.4	3338.9	3405.2	3468.9	3451.7	3364.1	3300.4	3258.0	3236.8	3230.1
3499.4	20°	3507.4	3507.4	3561.8	3601.6	3486.2	3337.6	3238.1	3169.1	3125.3	3106.8
3748.8	22.5°	3739.5	3718.3	3752.8	3724.9	3479.5	3263.3	3125.3	3006.0	2939.6	2913.1
4097.7	25°	4034.0	4008.8	3999.5	3827.1	3431.8	3145.2	2921.1	2776.5	2718.1	2703.5
4600.5	27.5°	4478.4	4414.7	4294.0	3882.8	3344.2	2959.5	2682.3	2548.3	2515.1	2516.5
5246.5	30°	5070.1	4942.7	4646.9	3892.1	3201.0	2696.9	2438.2	2342.7	2326.8	2333.4
5789.0	32.5°	5617.9	5497.2	5007.7	3849.6	2980.7	2439.5	2219.3	2155.6	2131.8	2139.7
6202.9	35°	6047.7	6014.6	5342.0	3789.9	2710.1	2198.1	2023.0	1968.6	1922.2	1911.6
6592.9	37.5°	6453.6	6440.4	5592.7	3706.4	2442.2	2027.0	1865.1	1793.5	1725.8	1688.7
7024.1	40°	6899.4	6886.1	5757.2	3577.7	2204.7	1878.4	1723.2	1629.0	1545.4	1477.8
7512.2	42.5°	7400.8	7322.5	5835.5	3393.3	2003.1	1752.4	1607.8	1480.4	1370.3	1308.0
8064.1	45°	7948.7	7772.2	5834.1	3158.5	1833.3	1637.0	1484.4	1304.0	1201.8	1143.5
8630.5	47.5°	8529.7	8202.0	5762.5	2898.5	1668.8	1509.6	1293.4	1155.4	1087.8	1052.0
9246.0	50°	9129.3	8604.0	5640.5	2600.0	1500.3	1365.0	1174.0	1079.8	1028.1	994.9
9856.2	52.5°	9693.1	8968.8	5493.2	2261.8	1329.2	1224.4	1120.9	1048.0	993.6	956.4
10447.9	55°	10217.1	9283.2	5285.0	1915.5	1189.9	1130.2	1095.7	1034.7	972.4	928.6
11048.8	57.5°	10682.7	9487.5	4925.5	1590.5	1090.4	1065.2	1069.2	1012.2	940.5	903.4
11640.4	60°	11070.0	9637.4	4393.5	1289.4	1009.5	1001.5	1028.1	969.7	886.1	843.7
12140.5	62.5°	11302.2	9634.7	3740.9	1055.9	940.5	943.2	973.7	916.6	831.7	791.9
12401.9	65°	11282.3	9398.6	3024.5	903.4	874.2	876.8	916.6	858.3	786.6	762.8
12270.5	67.5°	10883.0	8822.9	2320.1	803.9	801.2	813.2	859.6	818.5	758.8	756.1
11487.9	70°	9801.8	7627.6	1671.4	724.3	725.6	742.9	803.9	793.3	744.2	749.5
9658.6	72.5°	7859.8	5815.6	1122.3	640.7	642.0	669.9	750.8	773.4	729.6	799.9
6852.9	75°	5234.5	3626.8	721.6	551.8	553.2	589.0	704.4	734.9	689.8	797.3
3565.8	77.5°	2515.1	1630.3	522.7	464.3	464.3	497.5	608.9	658.0	587.7	619.5
1146.1	80°	868.9	612.9	411.2	374.1	366.1	388.7	513.4	570.4	506.7	466.9
374.1	82.5°	342.2	318.4	330.3	290.5	264.0	278.6	399.3	470.9	372.8	336.9
210.9	85°	196.3	206.9	233.5	192.3	152.6	171.1	293.2	338.3	281.2	248.1
69.0	87.5°	53.1	73.0	107.5	99.5	69.0	73.0	139.3	187.0	161.8	124.7
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
2800.3
2872.0
2986.1
3124.0
3251.4
3296.5
3297.8
3239.4
3102.8
2909.1
2706.2
2520.4
2355.9
2150.3
1919.5
1690.0
1484.4
1312.0
1140.8
1044.0
983.0
940.5
911.3
879.5
825.1
780.0
761.4
760.1
748.2
810.5
803.9
567.8
437.8
335.6
253.4
128.7
0.0

F REPORT)