

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P956457

Luminaire Tested: **GALN-SB9A-835-U-T2R**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P956457  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: McGRAW-EDISON  
Catalog Number: GALN-SB9A-835-U-T2R  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(9) 80 CRI, 3500K, 350mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE II  
ROADWAY OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 38600 lumens  
Efficiency: N/A  
Efficacy: 151.1 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type II - Medium  
BUG Rating: B3 - U0 - G4  
  
Input Watts (W): 255.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P956457  
 CATALOG NUMBER: GALN-SB9A-835-U-T2R

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 14.1 fc  
 Type II - Medium - N/A

REPORT NUMBER: P956457  
CATALOG NUMBER: GALN-SB9A-835-U-T2R

### Luminous Intensity Polar Plot



REPORT NUMBER: P956457  
 CATALOG NUMBER: GALN-SB9A-835-U-T2R

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	7301.6	0.0	7301.6
	% Fixture	18.9	0.0	18.9
<b>Street Side</b>	Lumens	31298.4	0.0	31298.4
	% Fixture	81.1	0.0	81.1
<b>Total</b>	Lumens	38600.0	0.0	38600.0
	% Fixture	100.0	0.0	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	485.4	1.3
10°-20°	1744.0	4.5
20°-30°	3292.9	8.5
30°-40°	5304.7	13.7
40°-50°	7255.9	18.8
50°-60°	8184.7	21.2
60°-70°	7639.4	19.8
70°-80°	4187.7	10.8
80°-90°	505.1	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	38600.0	100.0
0°-180°	38600.0	100.0



REPORT NUMBER: P956457


CATALOG NUMBER: GALN-SB9A-835-U-T2R

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	3934.8	10.2			
FM (30°-60°)	17257.6	44.7			
FH (60°-80°)	9790.1	25.4			G4/12000
FVH (80°-90°)	315.9	0.8			G3/500
BL (0°-30°)	1587.5	4.1	B3/2500		
BM (30°-60°)	3487.8	9.0	B3/5000		
BH (60°-80°)	2037.0	5.3	B3/2500		G3/2500
BVH (80°-90°)	189.2	0.5			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B3-U0-G4**

Type II Medium



REPORT NUMBER: P956457  
 CATALOG NUMBER: GALN-SB9A-835-U-T2R

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0
2.5°	5670.7	5710.5	5660.7	5660.7	5493.4	5405.7	5238.3	5110.8	4881.7	4841.8
5°	6702.8	6752.6	6682.9	6653.0	6455.7	6274.4	5993.5	5716.5	5308.1	5266.2
7.5°	7501.8	7565.6	7503.8	7471.9	7296.6	7093.3	6764.6	6378.0	5802.2	5720.5
10°	8153.4	8163.3	8143.4	8155.4	8017.9	7850.5	7513.8	7063.5	6344.2	6232.6
12.5°	8522.0	8567.8	8607.7	8679.4	8655.5	8551.9	8249.0	7711.0	6918.0	6774.5
15°	8695.3	8775.0	8864.7	9030.1	9163.6	9189.5	8958.3	8406.4	7501.8	7328.5
17.5°	8757.1	8832.8	8974.3	9213.4	9500.3	9693.6	9590.0	9081.9	8079.6	7880.4
20°	9069.9	9091.8	9177.5	9404.7	9715.5	10036.3	10114.0	9731.4	8651.5	8426.3
22.5°	9739.4	9695.6	9719.5	9823.1	10046.2	10357.1	10534.4	10305.3	9239.3	8980.3
25°	10845.2	10717.7	10590.2	10470.6	10584.2	10759.6	10960.8	10879.1	9855.0	9526.2
27.5°	12242.0	12086.6	11805.6	11413.1	11275.6	11337.4	11427.1	11411.1	10424.8	10092.1
30°	13616.8	13435.5	13100.8	12532.9	12170.3	12006.9	11939.1	11893.3	11044.5	10689.8
32.5°	14714.7	14571.2	14242.5	13606.9	13080.8	12801.9	12576.7	12413.3	11692.1	11337.4
35°	15675.1	15541.6	15165.0	14471.6	13899.8	13602.9	13308.0	12959.3	12365.5	12006.9
37.5°	16551.8	16418.3	15902.2	15180.9	14605.1	14399.9	14136.9	13545.1	13041.0	12702.3
40°	17105.7	17075.8	16593.6	15776.7	15179.0	15077.3	14989.7	14224.5	13790.2	13475.4
42.5°	17247.2	17312.9	16930.4	16258.9	15689.0	15607.3	15812.6	14993.7	14631.0	14330.1
45°	16906.5	17095.8	16844.7	16388.4	16051.7	16007.8	16541.8	15834.5	15561.5	15286.6
47.5°	16043.7	16364.5	16260.9	16197.1	16149.3	16338.6	17183.4	16727.1	16615.6	16376.5
50°	14302.2	14910.0	15091.3	15493.8	15956.0	16595.6	17767.2	17701.5	17846.9	17605.8
52.5°	11291.6	12128.4	13180.5	14188.7	15362.3	16510.0	18408.8	19100.2	19713.9	19582.4
55°	9321.0	9697.6	10506.5	12355.6	14210.6	16149.3	18697.7	20230.0	21566.9	21449.4
57.5°	7806.7	8143.4	8641.5	10185.7	12469.1	15330.4	18877.1	20919.4	22836.2	22824.2
60°	6182.8	6539.4	7049.5	8143.4	10434.8	13915.7	18837.2	21704.4	24456.1	24555.7
62.5°	4349.7	4742.2	5308.1	6328.2	8356.6	12082.6	18024.3	22272.3	26362.9	26633.9
65°	2859.3	3118.3	3544.7	4425.4	6226.6	9725.4	16472.1	22346.0	28403.3	28861.5
67.5°	2004.5	2104.1	2355.1	2833.4	4104.6	7458.0	13999.4	21582.9	29764.1	30280.2
70°	1564.1	1613.9	1741.5	1932.7	2578.3	5015.2	10727.7	19598.3	29473.2	30011.2
72.5°	1350.9	1398.7	1446.6	1470.5	1729.5	3096.4	7266.7	16386.4	26733.5	27098.2
75°	1225.4	1237.3	1277.2	1269.2	1319.0	2008.5	4194.2	11939.1	21092.7	20967.2
77.5°	1030.1	1046.1	1111.8	1101.9	1171.6	1372.8	2177.8	7705.0	13674.6	12821.8
80°	872.7	880.7	952.4	940.5	1018.2	994.3	1111.8	3927.2	5800.2	4913.5
82.5°	302.9	374.6	727.3	749.2	777.1	601.7	641.6	1602.0	1771.3	1356.9
85°	147.4	157.4	370.6	526.0	524.0	302.9	312.8	571.9	557.9	438.4
87.5°	23.9	29.9	43.8	205.2	163.4	79.7	107.6	111.6	115.6	99.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P956457  
 CATALOG NUMBER: GALN-SB9A-835-U-T2R

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
4529.0	0°	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0	4529.0
4690.4	2.5°	4578.8	4479.2	4270.0	4076.7	3925.2	3779.8	3698.1	3628.4	3588.5	3580.5
4909.5	5°	4702.3	4497.1	4116.5	3795.7	3586.5	3431.1	3349.4	3297.6	3271.7	3255.8
5204.4	7.5°	4879.7	4578.8	4036.8	3672.2	3453.0	3341.4	3299.6	3291.6	3289.6	3291.6
5561.1	10°	5124.7	4712.3	4028.9	3642.3	3459.0	3397.2	3395.2	3397.2	3405.2	3407.2
5949.6	12.5°	5389.7	4849.8	4060.7	3668.2	3534.7	3500.8	3494.9	3492.9	3498.9	3502.8
6342.2	15°	5678.7	5031.1	4114.5	3724.0	3618.4	3582.5	3576.6	3564.6	3562.6	3560.6
6754.6	17.5°	5975.5	5210.4	4174.3	3783.8	3672.2	3622.4	3600.5	3572.6	3550.7	3544.7
7181.0	20°	6276.4	5387.8	4216.2	3813.7	3676.2	3606.4	3562.6	3514.8	3476.9	3455.0
7611.4	22.5°	6597.2	5573.1	4242.1	3805.7	3640.3	3544.7	3465.0	3409.2	3351.4	3313.5
8045.8	25°	6910.0	5734.4	4240.1	3763.9	3570.6	3449.0	3347.4	3275.7	3196.0	3156.1
8494.1	27.5°	7210.9	5879.9	4190.3	3690.1	3471.0	3335.5	3213.9	3128.2	3050.5	3012.7
8946.4	30°	7521.7	6001.4	4112.5	3582.5	3353.4	3204.0	3070.5	2996.7	2927.0	2891.1
9424.6	32.5°	7830.6	6113.0	4003.0	3449.0	3217.9	3074.4	2942.9	2875.2	2833.4	2833.4
9938.6	35°	8157.3	6190.7	3857.5	3293.6	3074.4	2937.0	2833.4	2793.5	2789.5	2765.6
10482.6	37.5°	8502.0	6240.5	3680.2	3134.2	2933.0	2803.5	2771.6	2723.8	2683.9	2632.1
11080.4	40°	8864.7	6290.4	3467.0	2968.8	2783.5	2711.8	2697.9	2634.1	2520.5	2393.0
11757.8	42.5°	9305.0	6324.2	3245.8	2803.5	2626.1	2602.2	2622.1	2512.6	2331.2	2235.6
12574.7	45°	9815.1	6380.0	3042.6	2640.1	2464.7	2464.7	2548.4	2405.0	2255.5	2195.7
13507.2	47.5°	10476.6	6509.5	2853.3	2460.8	2315.3	2355.1	2385.0	2275.4	2191.8	2118.0
14643.0	50°	11433.0	6820.4	2658.0	2279.4	2201.7	2281.4	2239.6	2175.8	2078.2	2018.4
16448.2	52.5°	12620.6	7003.7	2484.7	2116.0	2104.1	2183.8	2124.0	2064.2	1990.5	1910.8
17817.0	55°	13429.5	7037.6	2339.2	1996.5	2038.3	2030.4	2008.5	1954.7	1914.8	1809.2
19168.0	57.5°	14334.1	7105.3	2219.7	1924.8	1996.5	1908.8	1900.9	1855.0	1803.2	1731.5
20815.8	60°	15416.1	7210.9	2116.0	1896.9	1960.6	1829.1	1789.3	1771.3	1719.5	1683.7
22798.3	62.5°	16595.6	7306.5	2010.4	1900.9	1918.8	1751.4	1691.6	1685.7	1653.8	1641.8
24659.3	65°	17400.6	7045.5	1878.9	1896.9	1853.0	1671.7	1596.0	1594.0	1568.1	1564.1
25466.3	67.5°	17119.7	6218.6	1701.6	1841.1	1785.3	1592.0	1508.3	1500.4	1466.5	1468.5
24623.5	70°	15712.9	5039.1	1456.5	1703.6	1701.6	1520.3	1416.7	1390.8	1344.9	1352.9
21409.5	72.5°	13074.9	3734.0	1127.8	1474.5	1568.1	1454.5	1311.1	1269.2	1211.4	1219.4
15804.6	75°	9442.5	2538.5	820.9	1121.8	1364.9	1376.8	1207.5	1135.7	1066.0	1077.9
8796.9	77.5°	4831.8	1438.6	603.7	773.1	1072.0	1251.3	1113.8	1018.2	1002.2	1113.8
2536.5	80°	1576.1	721.3	418.4	542.0	703.4	1024.2	976.3	866.7	862.8	888.7
532.0	82.5°	470.2	304.9	269.0	356.7	388.5	785.0	842.8	655.5	563.9	593.8
177.3	85°	161.4	147.4	153.4	177.3	185.3	460.3	589.8	434.4	410.5	452.3
39.9	87.5°	37.9	51.8	43.8	39.9	39.9	111.6	229.1	181.3	251.1	167.4
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
4529.0
3580.5
3253.8
3297.6
3409.2
3504.8
3558.6
3550.7
3463.0
3315.5
3156.1
3010.7
2889.1
2835.3
2759.6
2624.1
2375.1
2237.6
2205.7
2116.0
2012.4
1894.9
1811.2
1707.6
1693.6
1641.8
1562.1
1468.5
1360.9
1217.4
1081.9
1097.9
763.1
613.7
446.3
161.4
0.0

F REPORT)