

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P945390

Luminaire Tested: **GALN-SB1B-835-U-T2R**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P945390
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB1B-835-U-T2R
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(1) 80 CRI, 3500K, 450mA LIGHTSQUARE WITH 26 LEDS AND TYPE II ROADWAY OPTICS
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5322 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Medium
BUG Rating: B1 - U0 - G1


Input Watts (W): 39.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P945390
 CATALOG NUMBER: GALN-SB1B-835-U-T2R

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2 fc
 Type II - Medium - N/A

REPORT NUMBER: P945390
CATALOG NUMBER: GALN-SB1B-835-U-T2R

Luminous Intensity Polar Plot



REPORT NUMBER: P945390
 CATALOG NUMBER: GALN-SB1B-835-U-T2R

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1006.7	0.0	1006.7
	% Fixture	18.9	0.0	18.9
Street Side	Lumens	4315.3	0.0	4315.3
	% Fixture	81.1	0.0	81.1
Total	Lumens	5322.0	0.0	5322.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	1.3
10°-20°	240.5	4.5
20°-30°	454.0	8.5
30°-40°	731.4	13.7
40°-50°	1000.4	18.8
50°-60°	1128.5	21.2
60°-70°	1053.3	19.8
70°-80°	577.4	10.8
80°-90°	69.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	5322.0	100.0
0°-180°	5322.0	100.0

Coefficient of Utilization




REPORT NUMBER: P945390
 CATALOG NUMBER: GALN-SB1B-835-U-T2R

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	542.5	10.2			
FM (30°-60°)	2379.4	44.7			
FH (60°-80°)	1349.8	25.4			G1/1800
FVH (80°-90°)	43.6	0.8			G1/100
BL (0°-30°)	218.9	4.1	B1/500		
BM (30°-60°)	480.9	9.0	B1/1000		
BH (60°-80°)	280.9	5.3	B1/500		G1/500
BVH (80°-90°)	26.1	0.5			G1/100
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G1

Type II Medium



REPORT NUMBER: P945390
 CATALOG NUMBER: GALN-SB1B-835-U-T2R

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	65°	75°	77°
0°	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4
2.5°	781.8	787.3	780.5	780.5	757.4	745.3	722.2	704.7	673.1	667.6
5°	924.2	931.0	921.4	917.3	890.1	865.1	826.4	788.2	731.9	726.1
7.5°	1034.3	1043.1	1034.6	1030.2	1006.0	978.0	932.7	879.4	800.0	788.7
10°	1124.1	1125.5	1122.8	1124.4	1105.5	1082.4	1036.0	973.9	874.7	859.3
12.5°	1175.0	1181.3	1186.8	1196.7	1193.4	1179.1	1137.3	1063.2	953.8	934.0
15°	1198.9	1209.9	1222.2	1245.0	1263.4	1267.0	1235.1	1159.0	1034.3	1010.4
17.5°	1207.4	1217.8	1237.3	1270.3	1309.9	1336.5	1322.2	1252.2	1114.0	1086.5
20°	1250.5	1253.5	1265.4	1296.7	1339.5	1383.8	1394.5	1341.7	1192.8	1161.8
22.5°	1342.8	1336.8	1340.1	1354.4	1385.1	1428.0	1452.4	1420.8	1273.9	1238.2
25°	1495.3	1477.7	1460.1	1443.6	1459.3	1483.5	1511.2	1500.0	1358.8	1313.4
27.5°	1687.9	1666.4	1627.7	1573.6	1554.6	1563.2	1575.5	1573.3	1437.3	1391.5
30°	1877.4	1852.4	1806.3	1728.0	1678.0	1655.5	1646.1	1639.8	1522.8	1473.9
32.5°	2028.8	2009.0	1963.7	1876.1	1803.5	1765.1	1734.0	1711.5	1612.1	1563.2
35°	2161.2	2142.8	2090.9	1995.3	1916.4	1875.5	1834.8	1786.8	1704.9	1655.5
37.5°	2282.1	2263.7	2192.5	2093.1	2013.7	1985.4	1949.1	1867.5	1798.0	1751.3
40°	2358.5	2354.3	2287.9	2175.2	2092.8	2078.8	2066.7	1961.2	1901.3	1857.9
42.5°	2378.0	2387.0	2334.3	2241.7	2163.1	2151.9	2180.2	2067.3	2017.3	1975.8
45°	2331.0	2357.1	2322.5	2259.6	2213.1	2207.1	2280.7	2183.2	2145.6	2107.6
47.5°	2212.0	2256.3	2242.0	2233.2	2226.6	2252.7	2369.2	2306.3	2290.9	2257.9
50°	1971.9	2055.7	2080.7	2136.2	2199.9	2288.1	2449.7	2440.6	2460.7	2427.4
52.5°	1556.8	1672.2	1817.3	1956.3	2118.1	2276.3	2538.1	2633.5	2718.1	2699.9
55°	1285.1	1337.1	1448.6	1703.5	1959.3	2226.6	2578.0	2789.2	2973.6	2957.3
57.5°	1076.3	1122.8	1191.5	1404.4	1719.2	2113.7	2602.7	2884.3	3148.6	3146.9
60°	852.5	901.6	972.0	1122.8	1438.7	1918.6	2597.2	2992.5	3371.9	3385.6
62.5°	599.7	653.8	731.9	872.5	1152.2	1665.9	2485.1	3070.8	3634.8	3672.2
65°	394.2	429.9	488.7	610.2	858.5	1340.9	2271.1	3081.0	3916.1	3979.3
67.5°	276.4	290.1	324.7	390.7	565.9	1028.3	1930.2	2975.8	4103.8	4174.9
70°	215.7	222.5	240.1	266.5	355.5	691.5	1479.1	2702.1	4063.6	4137.8
72.5°	186.3	192.9	199.4	202.7	238.5	426.9	1001.9	2259.3	3685.9	3736.2
75°	169.0	170.6	176.1	175.0	181.9	276.9	578.3	1646.1	2908.2	2890.9
77.5°	142.0	144.2	153.3	151.9	161.5	189.3	300.3	1062.3	1885.4	1767.8
80°	120.3	121.4	131.3	129.7	140.4	137.1	153.3	541.5	799.7	677.5
82.5°	41.8	51.6	100.3	103.3	107.1	83.0	88.5	220.9	244.2	187.1
85°	20.3	21.7	51.1	72.5	72.3	41.8	43.1	78.8	76.9	60.4
87.5°	3.3	4.1	6.0	28.3	22.5	11.0	14.8	15.4	15.9	13.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P945390
 CATALOG NUMBER: GALN-SB1B-835-U-T2R

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
624.4	0°	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4	624.4
646.7	2.5°	631.3	617.6	588.7	562.1	541.2	521.1	509.9	500.3	494.8	493.7
676.9	5°	648.3	620.0	567.6	523.3	494.5	473.1	461.8	454.7	451.1	448.9
717.6	7.5°	672.8	631.3	556.6	506.3	476.1	460.7	454.9	453.8	453.6	453.8
766.7	10°	706.6	649.7	555.5	502.2	476.9	468.4	468.1	468.4	469.5	469.8
820.3	12.5°	743.1	668.7	559.9	505.8	487.4	482.7	481.9	481.6	482.4	483.0
874.4	15°	782.9	693.7	567.3	513.4	498.9	493.9	493.1	491.5	491.2	490.9
931.3	17.5°	823.9	718.4	575.5	521.7	506.3	499.4	496.4	492.6	489.5	488.7
990.1	20°	865.4	742.8	581.3	525.8	506.9	497.2	491.2	484.6	479.4	476.4
1049.4	22.5°	909.6	768.4	584.9	524.7	501.9	488.7	477.7	470.0	462.1	456.9
1109.3	25°	952.7	790.6	584.6	518.9	492.3	475.5	461.5	451.6	440.6	435.2
1171.1	27.5°	994.2	810.7	577.7	508.8	478.6	459.9	443.1	431.3	420.6	415.4
1233.5	30°	1037.1	827.5	567.0	493.9	462.4	441.7	423.3	413.2	403.6	398.6
1299.4	32.5°	1079.6	842.8	551.9	475.5	443.7	423.9	405.8	396.4	390.7	390.7
1370.3	35°	1124.7	853.6	531.9	454.1	423.9	404.9	390.7	385.2	384.6	381.3
1445.3	37.5°	1172.2	860.4	507.4	432.1	404.4	386.5	382.1	375.5	370.0	362.9
1527.7	40°	1222.2	867.3	478.0	409.3	383.8	373.9	372.0	363.2	347.5	329.9
1621.1	42.5°	1282.9	872.0	447.5	386.5	362.1	358.8	361.5	346.4	321.4	308.2
1733.8	45°	1353.3	879.6	419.5	364.0	339.8	339.8	351.4	331.6	311.0	302.7
1862.3	47.5°	1444.5	897.5	393.4	339.3	319.2	324.7	328.8	313.7	302.2	292.0
2018.9	50°	1576.3	940.4	366.5	314.3	303.6	314.6	308.8	300.0	286.5	278.3
2267.8	52.5°	1740.1	965.6	342.6	291.8	290.1	301.1	292.9	284.6	274.4	263.5
2456.5	55°	1851.6	970.3	322.5	275.3	281.0	279.9	276.9	269.5	264.0	249.4
2642.8	57.5°	1976.3	979.6	306.0	265.4	275.3	263.2	262.1	255.8	248.6	238.7
2870.0	60°	2125.5	994.2	291.8	261.5	270.3	252.2	246.7	244.2	237.1	232.1
3143.3	62.5°	2288.1	1007.4	277.2	262.1	264.6	241.5	233.2	232.4	228.0	226.4
3399.9	65°	2399.1	971.4	259.1	261.5	255.5	230.5	220.0	219.8	216.2	215.7
3511.2	67.5°	2360.4	857.4	234.6	253.8	246.1	219.5	208.0	206.9	202.2	202.5
3395.0	70°	2166.4	694.8	200.8	234.9	234.6	209.6	195.3	191.8	185.4	186.5
2951.9	72.5°	1802.7	514.8	155.5	203.3	216.2	200.5	180.8	175.0	167.0	168.1
2179.1	75°	1301.9	350.0	113.2	154.7	188.2	189.8	166.5	156.6	147.0	148.6
1212.9	77.5°	666.2	198.3	83.2	106.6	147.8	172.5	153.6	140.4	138.2	153.6
349.7	80°	217.3	99.4	57.7	74.7	97.0	141.2	134.6	119.5	119.0	122.5
73.3	82.5°	64.8	42.0	37.1	49.2	53.6	108.2	116.2	90.4	77.7	81.9
24.4	85°	22.3	20.3	21.2	24.4	25.5	63.5	81.3	59.9	56.6	62.4
5.5	87.5°	5.2	7.1	6.0	5.5	5.5	15.4	31.6	25.0	34.6	23.1
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
624.4
493.7
448.6
454.7
470.0
483.2
490.6
489.5
477.5
457.1
435.2
415.1
398.3
390.9
380.5
361.8
327.5
308.5
304.1
291.8
277.5
261.3
249.7
235.4
233.5
226.4
215.4
202.5
187.6
167.9
149.2
151.4
105.2
84.6
61.5
22.3
0.0

F REPORT)