

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P946105

Luminaire Tested: **GALN-SB1D-835-U-T2U-HSS**

Issue Date: 1/21/2025

Test Information

Test Method: LM-79-08
Report Number: P946105
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-289-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: McGRAW-EDISON
Catalog Number: GALN-SB1D-835-U-T2U-HSS
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE
(1) 80 CRI, 3500K, 900mA LIGHTSQUARE WITH 26 LEDS AND TYPE II U OPTICS
WITH HOUSE SIDE SHIELD
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7216 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
IES Classification: Type II - Short
BUG Rating: B1 - U0 - G2


Input Watts (W): 79.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



REPORT NUMBER: P946105
 CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 2.4 fc
 Type II - Short - N/A

REPORT NUMBER: P946105
CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

Luminous Intensity Polar Plot



— Vertical Plane Through 63-Deg Lateral - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P946105
 CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1060.7	0.0	1060.7
	% Fixture	14.7	0.0	14.7
Street Side	Lumens	6155.3	0.0	6155.3
	% Fixture	85.3	0.0	85.3
Total	Lumens	7216.0	0.0	7216.0
	% Fixture	100.0	0.0	100.0

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.9	1.2
10°-20°	232.8	3.2
20°-30°	405.4	5.6
30°-40°	730.7	10.1
40°-50°	1449.2	20.1
50°-60°	1974.0	27.4
60°-70°	1575.7	21.8
70°-80°	713.0	9.9
80°-90°	51.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	7216.0	100.0
0°-180°	7216.0	100.0

Coefficient of Utilization




REPORT NUMBER: P946105
 CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	492.6	6.8			
FM (30°-60°)	3603.5	49.9			
FH (60°-80°)	2011.8	27.9			G2/5000
FVH (80°-90°)	47.4	0.7			G1/100
BL (0°-30°)	229.5	3.2	B1/500		
BM (30°-60°)	550.4	7.6	B1/1000		
BH (60°-80°)	276.9	3.8	B1/500		G1/500
BVH (80°-90°)	3.8	0.1			G0/10
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

BUG Rating: B1-U0-G2
 Type II Short



REPORT NUMBER: P946105

CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

CANDELA DISTRIBUTION (FULL):

	0°	5°	15°	25°	35°	45°	55°	63°	65°	75°
0°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6
2.5°	911.4	909.0	912.4	910.9	910.0	908.0	907.0	906.0	904.0	902.5
5°	913.9	912.4	915.9	918.9	921.9	924.8	926.3	928.3	926.3	922.4
7.5°	893.1	892.1	899.5	908.5	921.9	933.3	945.7	952.6	953.1	951.7
10°	891.6	889.1	896.5	907.5	924.8	945.2	967.0	981.9	983.9	990.4
12.5°	914.9	912.4	922.9	934.8	952.6	974.0	1000.8	1021.6	1024.6	1033.6
15°	954.1	950.7	962.6	978.0	1000.8	1025.1	1053.4	1072.3	1074.8	1085.7
17.5°	999.8	996.3	1010.2	1026.6	1051.4	1084.7	1117.5	1138.3	1141.3	1148.2
20°	1058.4	1053.9	1064.8	1079.7	1106.0	1145.8	1185.0	1214.8	1214.3	1214.3
22.5°	1126.4	1119.4	1128.9	1140.8	1165.6	1213.8	1265.9	1301.1	1301.1	1287.2
25°	1199.4	1192.4	1202.8	1213.8	1235.6	1290.2	1351.3	1395.0	1396.9	1373.1
27.5°	1290.7	1281.8	1289.7	1302.6	1315.5	1371.1	1443.6	1494.2	1495.2	1458.5
30°	1466.4	1441.1	1416.3	1402.4	1408.4	1463.5	1540.9	1597.0	1602.0	1551.3
32.5°	1788.1	1783.2	1695.8	1581.6	1522.0	1562.8	1649.6	1717.1	1720.1	1655.1
35°	2288.0	2282.1	2141.6	1924.2	1730.0	1695.8	1781.7	1861.6	1859.6	1786.1
37.5°	2884.7	2879.3	2694.1	2403.2	2089.0	1896.8	1952.0	2035.8	2048.3	1952.0
40°	3394.6	3374.2	3257.1	2976.6	2565.5	2230.4	2194.2	2249.8	2262.7	2148.5
42.5°	3780.8	3763.4	3703.8	3528.6	3142.4	2723.9	2479.7	2501.0	2515.4	2378.4
45°	3980.9	3976.9	4000.7	3984.3	3730.2	3329.5	2887.7	2798.9	2804.3	2633.1
47.5°	4009.1	4007.2	4115.9	4269.8	4235.5	4012.6	3411.4	3170.2	3150.8	2920.5
50°	3842.3	3838.4	4046.9	4335.3	4573.1	4586.5	4006.2	3588.7	3546.0	3217.8
52.5°	3309.7	3308.7	3651.2	4131.3	4691.7	5088.9	4593.9	4048.4	3976.9	3532.6
55°	2546.7	2565.0	2957.7	3525.1	4475.3	5330.6	5121.6	4558.7	4449.0	3849.3
57.5°	1804.0	1830.8	2219.0	2724.4	3804.1	5187.7	5478.6	5070.0	4951.9	4165.0
60°	969.0	992.9	1381.6	1984.7	2830.1	4654.5	5666.7	5513.8	5402.1	4464.9
62.5°	577.3	585.3	746.1	1281.3	1914.2	3555.9	5586.8	5851.9	5760.0	4716.6
65°	414.5	416.0	496.9	782.4	1162.1	2160.5	5026.3	6013.7	5985.4	4906.2
67.5°	349.0	348.0	381.8	519.8	791.8	1082.2	3852.3	5784.9	5905.0	5026.3
70°	299.3	300.8	340.5	380.8	595.2	612.6	1915.2	5036.8	5292.9	5058.1
72.5°	222.9	227.9	264.6	347.0	449.3	421.5	661.2	3734.6	4197.8	4765.7
75°	157.4	159.8	186.2	291.9	335.1	306.8	337.6	1930.6	2524.3	3653.7
77.5°	121.1	125.6	141.0	204.0	330.1	215.4	206.5	668.2	1026.6	2207.1
80°	65.5	73.5	101.8	147.4	231.8	152.4	102.3	266.1	348.0	1032.1
82.5°	33.8	37.7	71.0	106.2	132.0	133.0	50.6	110.7	143.5	318.7
85°	13.4	16.4	47.7	58.6	68.0	65.5	22.8	44.7	51.6	88.4
87.5°	3.0	5.0	17.4	13.4	12.9	13.9	5.5	10.4	9.9	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P946105
 CATALOG NUMBER: GALN-SB1D-835-U-T2U-HSS

CANDELA DISTRIBUTION (continued):

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
890.6	0°	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6	890.6
896.5	2.5°	896.1	894.1	888.6	882.6	875.7	871.7	869.2	868.7	865.3	862.8
916.4	5°	910.9	909.0	898.5	886.1	872.7	862.3	852.4	843.4	830.5	828.0
945.2	7.5°	940.7	935.3	918.4	901.5	876.2	845.9	809.2	767.0	729.3	717.8
983.4	10°	977.5	970.0	948.7	918.9	862.8	780.4	691.5	609.1	543.6	525.2
1028.6	12.5°	1019.2	1012.7	984.4	929.3	806.7	657.3	521.2	419.0	355.4	339.6
1076.8	15°	1068.8	1059.4	1020.2	913.4	706.4	499.4	357.9	297.4	274.5	271.5
1131.9	17.5°	1121.4	1106.0	1051.9	856.3	571.4	354.9	276.5	259.1	249.2	246.2
1187.5	20°	1169.6	1149.7	1070.8	770.0	426.9	276.5	247.7	236.3	227.4	223.9
1243.1	22.5°	1217.7	1189.4	1070.8	652.3	320.2	245.2	227.4	216.9	206.5	202.0
1302.6	25°	1267.9	1230.1	1051.9	521.2	257.6	224.9	208.0	196.6	187.6	182.2
1359.2	27.5°	1316.5	1264.4	1008.7	397.1	229.3	207.0	190.1	179.2	170.8	166.8
1420.8	30°	1362.7	1298.2	948.2	301.3	211.0	189.6	173.7	164.3	155.9	151.9
1500.7	32.5°	1425.2	1340.9	883.6	247.2	195.1	173.3	158.9	149.9	142.5	139.5
1604.5	35°	1512.1	1403.9	828.0	242.8	181.7	159.8	145.5	137.0	129.6	127.1
1738.5	37.5°	1635.2	1505.7	798.8	272.5	170.8	147.9	134.5	125.6	118.6	116.7
1908.8	40°	1787.1	1643.7	814.6	302.3	163.3	137.5	124.6	115.7	109.7	107.2
2104.4	42.5°	1967.3	1813.9	902.5	325.2	158.4	128.6	115.2	105.2	101.3	100.3
2326.3	45°	2174.4	2001.1	1037.0	349.5	150.4	120.1	105.7	98.3	95.3	94.8
2567.5	47.5°	2409.7	2206.6	1192.9	379.8	142.5	112.2	98.3	93.3	90.8	89.9
2819.2	50°	2643.0	2413.6	1353.3	396.6	136.0	104.7	92.3	88.4	86.4	85.9
3085.3	52.5°	2887.2	2626.6	1482.8	380.8	130.6	98.8	87.4	84.4	82.4	81.9
3330.5	55°	3120.0	2798.9	1505.2	323.2	119.6	92.8	81.9	80.4	77.9	77.9
3579.2	57.5°	3320.6	2885.2	1347.3	237.3	108.7	83.9	76.4	75.0	73.0	72.5
3803.6	60°	3504.8	2860.4	1040.0	159.8	96.8	75.0	69.5	68.5	66.5	64.0
3998.7	62.5°	3608.5	2751.2	711.4	104.2	84.9	65.5	61.6	61.1	56.6	51.6
4143.2	65°	3647.7	2526.8	443.8	76.0	71.0	56.1	53.1	52.1	45.7	40.2
4225.1	67.5°	3613.5	2157.5	223.9	60.1	56.1	46.7	43.7	43.7	39.2	34.3
4220.1	70°	3476.5	1617.4	94.3	48.2	43.2	35.7	35.7	37.7	33.3	27.8
4001.2	72.5°	3179.1	1088.2	50.1	36.7	32.3	25.3	29.3	30.8	26.3	20.8
3274.9	75°	2527.3	663.7	34.7	27.3	20.4	17.9	22.3	23.3	17.9	13.9
2245.3	77.5°	1728.6	381.3	23.3	17.4	12.9	10.4	15.4	14.4	9.4	6.5
865.8	80°	759.0	158.9	13.4	7.9	5.0	4.0	5.5	4.0	3.0	2.0
118.6	82.5°	88.9	37.2	5.0	3.0	2.0	1.0	0.5	0.0	0.0	0.0
36.2	85°	18.4	4.5	2.5	1.0	0.5	0.0	0.0	0.0	0.0	0.0
6.5	87.5°	3.5	1.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

<u>180°</u>
890.6
865.3
827.0
712.4
518.3
335.1
268.6
244.7
221.9
199.6
180.2
166.8
152.4
139.5
127.1
116.2
106.7
100.3
94.3
89.9
85.9
81.9
77.4
72.0
63.5
50.6
39.7
33.8
27.3
20.8
13.4
6.9
2.0
0.0
0.0
0.0
0.0

F REPORT)