

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: McGRAW-EDISON

Report Number: P943222

Luminaire Tested: **GALN-SB7C-835-U-SL4**

Issue Date: 1/21/2025

**Test Information**

Test Method: LM-79-08  
Report Number: P943222  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2405-108-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/21/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: MCGRAW-EDISON  
Catalog Number: GALN-SB7C-835-U-SL4  
Description: GALLEON AREA AND ROADWAY HIGH DENSITY LED LUMINAIRE  
(7) 80 CRI, 3500K, 615mA LIGHTSQUARES WITH 26 LEDS EACH AND TYPE IV SPILL  
LIGHT ELIMINATOR OPTICS  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 48969 lumens  
Efficiency: N/A  
Efficacy: 139.7 lumens/watt  
Luminous Opening: Rectangular (W 1.5' x L: 1.5' x H: 0')  
IES Classification: Type IV - Medium  
BUG Rating: B4 - U0 - G5  
  
Input Watts (W): 350.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



REPORT NUMBER: P943222  
 CATALOG NUMBER: GALN-SB7C-835-U-SL4

### Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd  
 - - - 1/2 Max cd



Based on 25 foot mounting height. Maximum calculated value = 11.6 fc  
 Type IV - Medium - N/A

REPORT NUMBER: P943222  
CATALOG NUMBER: GALN-SB7C-835-U-SL4

### Luminous Intensity Polar Plot



— Vertical Plane Through 40-Deg Lateral      - - - Horizontal Cone Through 75-Deg Vertical

REPORT NUMBER: P943222

CATALOG NUMBER: GALN-SB7C-835-U-SL4

**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	15172.2	0.0	15172.2
	% Fixture	31.0	0.0	31.0
<b>Street Side</b>	Lumens	33796.8	0.0	33796.8
	% Fixture	69.0	0.0	69.0
<b>Total</b>	Lumens	48969.0	0.0	48969.0
	% Fixture	100.0	0.0	100.0

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	559.0	1.1
10°-20°	1876.7	3.8
20°-30°	3426.6	7.0
30°-40°	4859.9	9.9
40°-50°	6562.3	13.4
50°-60°	8828.1	18.0
60°-70°	11204.9	22.9
70°-80°	10169.1	20.8
80°-90°	1482.3	3.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-90°	48969.0	100.0
0°-180°	48969.0	100.0

**Coefficient of Utilization**



REPORT NUMBER: P943222


CATALOG NUMBER: GALN-SB7C-835-U-SL4

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	2575.8	5.3			
FM (30°-60°)	12020.8	24.5			
FH (60°-80°)	17921.9	36.6			G5
FVH (80°-90°)	1278.3	2.6			G5
BL (0°-30°)	3286.4	6.7	B4/5000		
BM (30°-60°)	8229.6	16.8	B4/8500		
BH (60°-80°)	3452.1	7.0	B4/5000		G4/5000
BVH (80°-90°)	204.1	0.4			G2/225
UL (90°-100°)	0.0	0.0		U0/0	
UH (100°-180°)	0.0	0.0		U0/0	

**BUG Rating: B4-U0-G5**

Type IV Medium



REPORT NUMBER: P943222

CATALOG NUMBER: GALN-SB7C-835-U-SL4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	15°	25°	35°	40°	45°	55°	65°	75°
0°	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7
2.5°	5514.0	5545.1	5537.3	5526.9	5526.9	5529.5	5526.9	5545.1	5563.3	5581.5
5°	5571.1	5602.3	5586.7	5573.7	5563.3	5560.7	5552.9	5550.3	5560.7	5584.1
7.5°	5682.8	5713.9	5690.6	5667.2	5646.4	5636.0	5625.6	5610.1	5602.3	5615.3
10°	5807.5	5838.6	5810.0	5768.5	5734.7	5721.7	5711.4	5695.8	5685.4	5693.2
12.5°	5932.1	5963.3	5924.3	5867.2	5823.0	5815.2	5802.3	5797.1	5794.5	5791.9
15°	6049.0	6075.0	6025.6	5958.1	5911.3	5898.4	5885.4	5893.2	5906.1	5921.7
17.5°	6139.9	6165.9	6093.1	6004.8	5960.7	5955.5	5947.7	5973.7	6010.0	6049.0
20°	6223.0	6249.0	6155.5	6036.0	5984.1	5984.1	5986.7	6041.2	6093.1	6150.3
22.5°	6339.9	6360.7	6246.4	6082.8	6007.4	6012.6	6033.4	6088.0	6152.9	6230.8
25°	6513.9	6529.5	6389.2	6171.1	6085.4	6100.9	6119.1	6145.1	6207.4	6298.3
27.5°	6794.4	6807.4	6623.0	6326.9	6197.0	6223.0	6249.0	6230.8	6259.4	6337.3
30°	7189.2	7197.0	6963.2	6571.0	6386.6	6399.6	6404.8	6329.5	6275.0	6337.3
32.5°	7656.7	7654.1	7376.2	6867.1	6602.2	6589.2	6545.1	6397.0	6269.8	6324.3
35°	8381.3	8352.8	7994.3	7282.7	6846.4	6765.8	6661.9	6472.3	6295.7	6311.3
37.5°	9581.3	9492.9	8996.9	7963.2	7210.0	7004.8	6851.5	6594.4	6352.9	6306.1
40°	10934.4	10822.7	10277.3	8895.6	7755.4	7425.5	7178.8	6768.4	6446.4	6329.5
42.5°	12539.5	12381.1	11794.1	9994.2	8446.3	7968.4	7597.0	6989.2	6584.0	6404.8
45°	14510.8	14300.5	13469.3	11233.1	9316.3	8680.0	8183.9	7324.2	6794.4	6550.3
47.5°	16502.9	16554.9	15373.1	12651.2	10360.4	9557.9	8919.0	7828.1	7100.9	6784.0
50°	18619.7	18656.0	17266.5	14222.5	11544.8	10550.0	9744.9	8391.7	7526.8	7116.5
52.5°	20271.5	20276.7	18985.9	15866.6	12778.5	11640.9	10635.7	9035.8	8020.3	7558.0
55°	21305.2	21292.3	20191.0	17422.4	14196.6	12786.3	11622.7	9768.3	8622.9	8077.4
57.5°	22055.8	22016.9	21022.1	18759.9	15708.2	14139.4	12739.5	10599.4	9334.5	8695.6
60°	22341.5	22318.2	21585.7	19915.7	17297.7	15635.4	14027.7	11529.2	10142.3	9425.4
62.5°	22450.6	22494.8	22139.0	21035.1	18998.9	17292.5	15443.2	12640.8	11051.3	10251.3
65°	22835.0	22915.5	22842.8	22500.0	20920.8	19232.6	17321.1	13962.8	12043.4	11137.0
67.5°	23596.0	23676.5	23707.7	24253.1	23268.8	21650.7	19663.8	15609.5	13204.4	12056.4
70°	23577.8	23554.5	24105.1	25647.8	26208.8	24998.5	22822.0	17635.3	14588.8	12820.0
72.5°	21461.1	21274.1	22575.3	25632.3	28655.5	28494.4	26678.9	20248.2	15783.5	12913.5
75°	16100.4	15601.7	17900.2	23099.9	29063.2	30478.7	29130.8	21868.8	15500.4	11409.7
77.5°	6885.3	6384.0	9093.0	17100.3	26011.5	28491.8	26881.5	19079.4	12373.3	7545.0
80°	1802.5	1799.9	2747.9	7752.8	17689.9	21040.3	18458.7	12321.4	7069.7	2695.9
82.5°	745.4	727.2	1010.3	3015.4	8643.6	11807.1	9635.8	5495.8	2553.1	729.8
85°	277.9	275.3	490.9	1041.5	3049.2	4869.8	3524.5	1405.1	636.3	355.8
87.5°	77.9	75.3	106.5	361.0	742.8	1127.2	602.6	231.2	179.2	140.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P943222  
 CATALOG NUMBER: GALN-SB7C-835-U-SL4

**CANDELA DISTRIBUTION (continued):**

85°		90°	95°	105°	115°	125°	135°	145°	155°	165°	175°
5599.7	0°	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7	5599.7
5610.1	2.5°	5617.9	5630.8	5654.2	5672.4	5695.8	5721.7	5758.1	5781.5	5804.9	5820.4
5623.0	5°	5641.2	5669.8	5729.5	5789.3	5859.4	5924.3	5999.6	6054.2	6098.3	6111.3
5669.8	7.5°	5693.2	5739.9	5841.2	5942.5	6054.2	6160.7	6269.8	6363.3	6438.6	6467.2
5752.9	10°	5784.1	5846.4	5989.3	6132.1	6280.1	6443.8	6584.0	6719.1	6825.6	6869.7
5851.6	12.5°	5898.4	5976.3	6163.3	6360.7	6565.8	6791.8	6973.6	7139.8	7272.3	7332.0
5989.3	15°	6046.4	6147.7	6386.6	6651.6	6952.8	7267.1	7498.3	7682.7	7830.7	7903.4
6132.1	17.5°	6207.4	6342.5	6643.8	7043.7	7474.9	7887.8	8158.0	8293.0	8446.3	8516.4
6264.6	20°	6363.3	6529.5	6960.6	7542.4	8116.4	8555.3	8773.5	8809.9	8820.3	8828.1
6389.2	22.5°	6524.3	6747.7	7358.0	8170.9	8786.5	9090.4	9121.5	8965.7	8747.5	8646.2
6511.3	25°	6700.9	6997.0	7877.5	8864.4	9363.1	9399.4	9160.5	8781.3	8368.3	8178.7
6610.0	27.5°	6872.3	7285.3	8500.8	9526.7	9778.6	9459.2	8944.9	8407.3	7908.6	7708.6
6680.1	30°	7043.7	7615.1	9189.1	10105.9	9968.2	9311.1	8604.7	8004.7	7503.5	7293.1
6742.5	32.5°	7217.8	7999.5	9981.2	10524.1	9934.5	8996.9	8181.3	7552.8	7111.3	6890.5
6797.0	35°	7415.1	8472.2	10731.8	10752.6	9708.5	8534.6	7622.9	7012.6	6628.2	6451.6
6861.9	37.5°	7672.3	9072.2	11394.1	10809.8	9313.7	7856.7	6929.5	6373.7	6056.8	5976.3
6958.0	40°	7991.7	9794.2	11900.6	10718.8	8729.4	7033.4	6171.1	5726.9	5547.7	5565.9
7087.9	42.5°	8407.3	10602.0	12256.4	10485.1	7916.4	6184.1	5506.2	5308.8	5394.5	5467.2
7282.7	45°	8947.5	11440.9	12477.2	10087.7	6997.0	5464.6	5114.0	5160.7	5225.7	5233.5
7597.0	47.5°	9638.4	12290.2	12622.6	9487.8	6059.4	4958.1	4864.6	4875.0	4862.1	4807.5
8067.1	50°	10500.7	13116.1	12752.5	8693.0	5262.0	4641.3	4516.6	4480.3	4301.0	4124.4
8693.0	52.5°	11482.4	13874.5	12807.0	7706.0	4641.3	4376.4	4173.8	3945.2	3610.2	3555.6
9480.0	55°	12573.3	14575.8	12666.8	6493.1	4119.2	4036.1	3729.7	3454.3	3418.0	3371.2
10516.3	57.5°	13877.1	15331.6	12381.1	5140.0	3584.2	3638.7	3340.1	3371.2	3306.3	3233.6
11848.7	60°	15303.0	16113.3	11879.8	3906.3	3031.0	3142.7	3238.8	3236.2	3218.0	3158.3
13253.8	62.5°	16586.0	16627.6	10892.9	2992.0	2545.3	2758.3	3020.6	3018.0	3002.4	2968.7
14721.2	65°	17349.6	16549.7	9246.2	2355.7	2145.3	2441.4	2724.5	2745.3	2747.9	2745.3
15825.0	67.5°	17214.6	15638.0	6986.6	1875.2	1815.5	2119.4	2431.0	2459.6	2480.4	2485.6
15965.3	70°	15687.4	13635.6	4555.6	1496.0	1522.0	1836.3	2153.1	2181.7	2199.9	2220.6
13853.7	72.5°	12227.9	10025.4	2607.6	1210.3	1264.9	1592.1	1877.8	1911.6	1922.0	1960.9
9641.0	75°	7451.5	5895.8	1407.7	953.2	1038.9	1361.0	1605.1	1644.1	1662.2	1709.0
4734.8	77.5°	3542.6	2553.1	802.6	742.8	836.3	1111.6	1355.8	1399.9	1350.6	1376.5
1306.4	80°	1197.3	948.0	506.5	566.2	638.9	867.5	1085.7	1129.8	1025.9	1020.7
433.7	82.5°	418.2	384.4	322.1	376.6	413.0	620.7	820.7	877.9	763.6	761.0
194.8	85°	163.6	155.8	179.2	205.2	246.7	381.8	540.2	568.8	470.1	379.2
57.1	87.5°	33.8	36.4	44.2	46.8	75.3	132.5	194.8	238.9	189.6	161.0
0.0	90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END O

180°  
5599.7  
5810.0  
6116.5  
6469.7  
6872.3  
7332.0  
7898.2  
8513.8  
8848.8  
8674.8  
8207.3  
7732.0  
7316.5  
6919.1  
6490.5  
6033.4  
5628.2  
5534.7  
5285.4  
4849.1  
4147.8  
3573.8  
3379.0  
3220.6  
3137.5  
2955.7  
2745.3  
2490.8  
2231.0  
1976.5  
*1714.2*  
1355.8  
1010.3  
724.6  
374.0  
148.0  
0.0

F REPORT)